








8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION		
1852604-1	A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER		
1852604-2	A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER		
1852604-3	A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER		
1852604-6	A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER		
7-1852604-7	A	-	-	-	SPARE PARTS		

- △ RECOMMENDED SPARE PARTS
- △ GREASE LIGHTLY
- △ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE
- △ STRIP GUIDE MUST BE ADJUSTED WHEN CHANGING FROM ONE TERMINAL TO ANOTHER.



TERMINAL NAME: TERMINAL					
TE PN	COMP PN	LUMBERG TERMINAL - TE CRIMP SPECS			
1949575-1	△ 0364				
1949576-1	△ 0369	PAD LTR	CRIMP HEIGHT	WIRE SIZE	
-	-	A	1.06±0.05mm [.042±.002]	0.75mm2	
-	-	B	1.04±0.05mm [.041±.002]	0.5mm2	
-	-	C	.97±0.05mm [.038±.002]	0.35mm2	
-	-	D	.91±0.05mm [.036±.002]	0.25mm2	
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	1.57mm [.062]	F	0.25-0.75mm
-	-	INSUL	2.16mm [.085]	O	Ø1.8mm MAX
WIRE STRIP LENGTH 3.50-3.89	TERM APPL SPEC NONE	FEED 9.53mm	APPLICATOR INSTRUCTIONS 408-8040		SET UP GAGE 458637-1



	-	2	2	2	2	-	4-354779-6	PIN, WIRE DISC, .3220	129
	-	2	2	2	2	-	4-354779-0	PIN, WIRE DISC, .3190	128
	-	2	2	2	2	-	3-354779-5	PIN, WIRE DISC, .3165	127
	-	2	2	2	2	-	3-354779-4	PIN, WIRE DISC, .3160	126
3	-	-	-	REF	-	...	455749-1	GUARD WINDOW	116
3	-	-	-	REF	-	...	679532-1	INSERT, GUARD	115
	-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
	-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
	-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
	-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
	-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
	-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
	-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
	-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
	-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
	-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
	-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
	-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
	-	1	1	1	1	-	458537-2	PAWL, FEED	56
	-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
	-	2	2	2	2	-	2-21000-8	SCR, SKT HD CAP 8-32 X .625	53
	-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
	-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
	-	1	1	1	1	-	690753-1	SPACER, TONKER	50
	-	-	1	-	-	...	690602-6	CAM, PRE FEED, 1 5/8	49
	-	-	-	1	-	...	690602-5	CAM, PRE FEED, 1 1/8	48
	-	1	-	-	1	-	690501-4	CAM, POST FEED, 1 5/8	47
	-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MOCA)	46
	-	1	1	1	1	-	690191-1	PLUG,NYLON	45
	-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
	-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
	-	1	1	1	1	-	1-690124-4	WASHER, RAM (.120)	42
	-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
	-	1	1	1	1	-	23241-6	BALL, STEEL	40
	-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
	-	1	1	1	1	-	690142-1	DISC, INSULATION	38
	-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
	-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
	-	1	1	1	1	-	690212-1	POST, RAM	35
	-	1	1	1	1	-	3-690786-3	TERMINAL SUPPORT	34
	-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
	-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
	-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
	-	1	1	1	1	-	1-1320908-5	SPACER, STRIP GUIDE	30
	-	1	1	1	1	-	1633091-1	ASSEMBLY, STRIP GUIDE	29
	-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
	-	1	1	1	1	-	1320928-1	PLATE, STRIP GUIDE	24
	-	1	-	-	1	-	690472-2	STRIPPER	22
	-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
	-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
	-	-	1	1	-	-	691353-1	STRIPPER	19
	-	1	-	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	13
	-	1	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
	-	1	1	1	1	-	690461-1	STOP, SHEAR	11
	-	-	1	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
	-	1	1	1	1	-	462006-1	FLOATING SHEAR, FRONT	9
	1	1	1	1	1	-	3-1633107-7	ANVIL, COMBINATION .062	8
	-	1	1	1	1	-	240641-5	SPACER	7
	-	-	-	-	-	...	-	-	6
	-	1	1	1	1	-	2-455889-0	DEPRESSOR, SHEAR	5
	-	1	1	1	1	-	238011-4	BLOCK, CRIMPER SPACER	4
	1	1	1	1	1	-	7-904741-5	CRIMPER, INSUL O PREMIUM	3
	-	1	1	1	1	-	455888-4	SPACER, CRIMPER	2
	1	1	1	1	1	-	4-456403-4	CRIMPER, WIRE PREMIUM	1
	-77	-6	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO.