



SUPERPRO M

Lowest cost Universal Device Programmer equipped w/ 48pin drive, USB 2.0, ultra-high speed

- Fastest Lowest-cost Programmer: With ARM7 MCU it gives ultra-fast programming experience.
- Programs devices with Vcc as low as 1.2V
- Built-in 48 universal pin drivers
- CE and ROHS Compliant

Products informations : www.seeit.fr

Distributors : www.rs-components.com

↓ **Devices list programmed below** ↓



SUPERPRO



Features:

- Supports **20.000** IC devices from **158** manufacturers .
- Programs devices with Vcc as low as 1.2V.
- Ultra fast programming.
- Built with 48 universal pin-drivers for support of today's most complex devices. Universal and device independent socket adapters are available for various packages.
- The programmer operates in PC hosted mode.
 - o Under PC hosted mode, a PC controls the programmer via a high-speed USB2.0 connection to program a chip.
- ISP/ICP programming capability through optional ISP/ICP adapter.
- Only IC manufacturer approved programming algorithms provide high reliability. Vcc verification at (+5%~-5%) and (10%~-10%) enhances programming reliability.
- Provides over-current and over-voltage protection for safety of the chip and programmer hardware.
- Compatible with Windows 7 / Windows 8 & Vista & XP 32/64 bit
- Includes the following advanced and powerful software functions:
 - o Chip operation starts immediately upon proper chip insertion in Production Mode.
 - o The Project function simplifies processes such as device selection, file loading, device configuration setting, program option, and batch file setting into one step.
 - o Password protection provides security for project files and production volume control.
 - o The Batch command combines device operations like program, verify, security into a single command at any sequence.
 - o Serial number generators are available as standard or customer-specific functions.
 - o A Log file provides quality tracking.

Speed Comparison:

Device	Program + Verify (Sec)	Compare with SP3000U	Type
AT28C64B	0.8(P)+0.1(V)= 0.9(s)	1.2(P)+0.8(V)= 2.0(s)	64Kb EEPROM
24AA128	2.7(P)+1.8(V)= 4.5(s)	5.0(P)+4.0(V)= 9.0(s)	128Kb EEPROM
QB25F640S33B60	29.0(P)+14.4(V)= 43.4(s)	55.2(P)+41.4(V)= 96.6(s)	64Mb EEPROM
AT89C55WD	2.5(P)+0.4(V)= 2.9(s)	3.3(P)+1.0(V)= 4.3(s)	20KB FLASH MCU
S25FL064A	43.9(P)+14.7(V)= 58.6(s)	72.8(P)+41.4(V)= 114.2(s)	64Mb SPI EEPROM
PIC16F876A	10.1(P)+0.8(V)= 10.9(s)	22.1(P)+06.2(V)= 28.3(s)	

Hardware & Electrical Specifications:

- Devices Supported: EPROM, Paged EPROM, Parallel and Serial EEPROM, FPGA Configuration PROM, FLASH memory (NOR), BPROM, NVRAM, SPLD, CPLD, EPLD, Firmware HUB, Microcontroller, MCU, Standard Logic
- Package: DIP, SDIP, PLCC, JLCC, SOIC, QFP, TQFP, PQFP, VQFP, TSOP, SOP, TSOPII, PSOP, TSSOP, SON, EBGA, FBGA, VFBGA, uBGA, CSP, SCSP,...
- PC interface: USB2.0 (High speed)
- Power supply: AC Adapter: Input AC 90V- 250V, 50/60Hz; DC Output: 12V/2A; power 15W
- Main unit: Dimensions 178mm (L) * 130mm (W) * 40mm (H) Weight 0.85 lbs (0.8Kg)
- Package: Dimensions 320mm (L) * 300mm (W) * 85mm (H) Weight 3 lbs (1.8Kg)

Items Included:

- Programmer with a DIP48 Adapter
- AC adapter
- Software CD

Products informations : www.seeit.fr

Distributors : www.rs-components.com

↓ **Devices list programmed below** ↓

www.seeit.fr



DEVICES LIST SUPERPRO-M

(Economical universal programmer with ZIF48)

Push "CTRL + F" keys to find a component

Universal programmer SuperPro-M

Total manufacturers : 158

Total devices : 20100

Version 6.3

Explanation to read a device:

Example: 24LC16B@S0IC8 [SA602A]

24LC16B: Device name

@S0IC8: Package name

[SA602A]: Adapter name (if needed)

Manufacturers:

ABOV	ACE Technology	ACT	ACTRANS
ADVANCE GROUP	ALI(Acer)	ALLIANCE	ALTERA
AMD	AMIC	ANACHIP	APLUS FLASH
ARTSCHIP	ASAHI KASEI(AKM)	ASD	ASI
ASP	ATC	ATMEL	ATMEL W&M
AUSTIN	BENCHMARQ	BMT	BRIGHT
CATALYST	CERAMATE	CFEON	CHINA CORE
CHINGIS	CHIPON	CHIPSWINNER	CWI
CYPRESS	DALLAS	DENSE-PAC	DEUTRON
E-CMOS	EFST	ELECTRONIC ARRAYS	
EMTC	EON	ESMT	EXCELSEMI
EXEL	FAIRCHILD	FIDELIX	FMD
FORCE TECHNOLOGIES		FORWARD	
Fremont Micro Devices		FUDAN	FUJITSU
GENERAL(GI)	GENERIC	GIANTEC	GIGADEVICE
GOAL	GREENWICH	HITACHI	HOLTEK
HONGKONG	HYNIX	HYUNDAI	ICE
ICSI	ICT	IMT	INTEL
INTELSIL	INTERSIL	ISSI	K-LINE
LATTICE	LG Semicon	LINKSMART	MACRONIX
MAGNACHIP	MAXIM	MAXWELL	MEGAWIN
MICROCHIP	MICRON	MITSUBISHI	MOSEL-VITELIC
MOSTEK	MOTOROLA	NANSI	NANTRONICS
NATRONICS	NEC	NEXFLASH	NSC
NTE	NUMONYX	NUVOTON	NXP
OKI	ON Semiconductor	PHILIPS	PJ
PMC	PSS	PTC	QISDA-CUSTOMER
Quick Pulse	RAMTRON	RATO	RAYDIUM
REALTEK	RENESAS	RICOH	ROCKWELL
ROHM	SAIFUN	SAMSUNG	SANYO
SEEQ	SEIKO	SGS-THOMSON	SHARP
SIEMENS	SIERRA	SIGNETICS	SIMTEK
SMOS	SONIX	SONY	
SPACE ELECTRONICS[Sei]		SPANSION	SST
SST-CUSTOMER	ST	STC	SUMMIT
SYNCMOS	SYNERTEK	TECHCODE	TEKMOS
TEMIC	Terra Semiconductor		TI
TMC	TOSHIBA	TSI	TURBO IC
UMC	VERSACHIPS	VLSI	
WHITE ELECTRONIC DESIGNS		WINBOND	WSI
XELTEK	XICOR	XILINX	YMC

YSS

YXLDZ

ZMD

ABOV

MICROCONTROLLER

GMS97C1051
GMS97C2051
GMS97C51
GMS97C51@TQFP44 [SA675-B4805]
GMS97C51H@PLCC44 [SA244]
GMS97C52
GMS97C52@TQFP44 [SA675-B4805]
GMS97C52H@PLCC44 [SA244]
GMS97C54
GMS97C54@TQFP44 [SA675-B4805]
GMS97C54H@PLCC44 [SA244]
GMS97C56
GMS97C56@TQFP44 [SA675-B4805]
GMS97C56H@PLCC44 [SA244]
GMS97C58
GMS97C58@TQFP44 [SA675-B4805]
GMS97C58H@PLCC44 [SA244]
GMS97L1051
GMS97L2051
GMS97L51
GMS97L51@TQFP44 [SA675-B4805]
GMS97L52@PLCC44 [SA244]
GMS97L54
GMS97L54@TQFP44 [SA675-B4805]
GMS97L56@PLCC44 [SA244]
GMS97L58
GMS97L58@TQFP44 [SA675-B4805]
GMS99C51@PLCC44 [SA244]
GMS99C52
GMS99C52@TQFP44 [SA675-B4805]
GMS99C58@PLCC44 [SA244]
HMS99C51
HMS99C51@TQFP44 [SA675-B4805]
HMS99C52@PLCC44 [SA244]
HMS99C58
HMS99C58@TQFP44 [SA675-B4805]

GMS97C1051@S0IC20 [SA404]
GMS97C2051@S0IC20 [SA404]
GMS97C51@PLCC44 [SA244]
GMS97C51H
GMS97C51H@TQFP44 [SA675-B4805]
GMS97C52@PLCC44 [SA244]
GMS97C52H
GMS97C52H@TQFP44 [SA675-B4805]
GMS97C54@PLCC44 [SA244]
GMS97C54H
GMS97C54H@TQFP44 [SA675-B4805]
GMS97C56@PLCC44 [SA244]
GMS97C56H
GMS97C56H@TQFP44 [SA675-B4805]
GMS97C58@PLCC44 [SA244]
GMS97C58H
GMS97C58H@TQFP44 [SA675-B4805]
GMS97L1051@S0IC20 [SA404]
GMS97L2051@S0IC20 [SA404]
GMS97L51@PLCC44 [SA244]
GMS97L52
GMS97L52@TQFP44 [SA675-B4805]
GMS97L54@PLCC44 [SA244]
GMS97L56
GMS97L56@TQFP44 [SA675-B4805]
GMS97L58@PLCC44 [SA244]
GMS99C51
GMS99C51@TQFP44 [SA675-B4805]
GMS99C52@PLCC44 [SA244]
GMS99C58
GMS99C58@TQFP44 [SA675-B4805]
HMS99C51@PLCC44 [SA244]
HMS99C52
HMS99C52@TQFP44 [SA675-B4805]
HMS99C58@PLCC44 [SA244]

ACE Technology

E(E)PROM/FRAM/NVRAM

ACE24C02A
ACE24C02A@TSSOP8 [SA026-B3201]
ACE24C04A@S0IC8 [SA602A]
ACE24C08A

ACE24C02A@S0IC8 [SA602A]
ACE24C04A
ACE24C04A@TSSOP8 [SA026-B3201]
ACE24C08A@S0IC8 [SA602A]

ACE24C08A@TSSOP8 [SA026-B3201]	ACE24C128
ACE24C128@S0IC8 [SA602A]	ACE24C128@TSSOP8 [SA026-B3201]
ACE24C16A	ACE24C16A@S0IC8 [SA602A]
ACE24C16A@TSSOP8 [SA026-B3201]	ACE24C256
ACE24C256@S0IC8 [SA602A]	ACE24C256@TSSOP8 [SA026-B3201]
ACE24C32	ACE24C32@S0IC8 [SA602A]
ACE24C32@TSSOP8 [SA026-B3201]	ACE24C64
ACE24C64@S0IC8 [SA602A]	ACE24C64@TSSOP8 [SA026-B3201]
ACE24LC02	ACE24LC02@S0IC8 [SA602A]
ACE24LC02@TSSOP8 [SA026-B3201]	ACE24LC04
ACE24LC04@S0IC8 [SA602A]	ACE24LC04@TSSOP8 [SA026-B3201]
ACE24LC08	ACE24LC08@S0IC8 [SA602A]
ACE24LC08@TSSOP8 [SA026-B3201]	ACE24LC16
ACE24LC16@S0IC8 [SA602A]	ACE24LC16@TSSOP8 [SA026-B3201]
ACE93C46(08bit)	ACE93C46(08bit)@S0IC8 [SA602A]
ACE93C46(08bit)@TSSOP8 [SA026-B3201]	ACE93C46(16bit)@S0IC8 [SA602A]
ACE93C46(16bit)	
ACE93C46(16bit)@TSSOP8 [SA026-B3201]	

ACT

E(E) PROM/FRAM/NVRAM

93LC46(08bit)	93LC46(08bit)@S0IC8 [SA602A]
93LC46(16bit)	93LC46(16bit)@S0IC8 [SA602A]
93LC56(08bit)	93LC56(08bit)@S0IC8 [SA602A]
93LC56(16bit)	93LC56(16bit)@S0IC8 [SA602A]
93LC66(08bit)	93LC66(08bit)@S0IC8 [SA602A]
93LC66(16bit)	93LC66(16bit)@S0IC8 [SA602A]
93LC86(08bit)	93LC86(08bit)@S0IC8 [SA602A]
93LC86(16bit)	93LC86(16bit)@S0IC8 [SA602A]

ACTTRANS

E(E) PROM/FRAM/NVRAM

AC25010@S0IC8 [SA602A]	AC25512@S0IC8 [SA602A]
AC25LC010@S0IC8 [SA602A]	AC25LC512@S0IC8 [SA602A]
AC39LV010@PLCC32 [SA015A1T]	AC39LV010@VSOP32 [SA620-B4807]
AC39LV020@PLCC32 [SA015A1T]	AC39LV020@VSOP32 [SA620-B4807]
AC39LV040@PLCC32 [SA015A1T]	AC39LV040@VSOP32 [SA620-B4807]
AC39LV080@TSOP40 [SA409T-B4002]	AC39LV088@TSOP48 [SB247-B4806]
AC39LV512@PLCC32 [SA015A1T]	AC39LV512@VSOP32 [SA620-B4807]
AC39LV800@TSOP48 [SB247-B4806]	AC39VF800@TSOP48 [SB247-B4806]

ADVANCE GROUP

E(E) PROM/FRAM/NVRAM

AF24BC01	AF24BC01@S0IC8 [SA602A]
AF24BC01@TSOP8 [SA026-B3201]	AF24BC02
AF24BC02@S0IC8 [SA602A]	AF24BC02@TSOP8 [SA026-B3201]
AF24BC04	AF24BC04@S0IC8 [SA602A]
AF24BC04@TSOP8 [SA026-B3201]	AF24BC08
AF24BC08@S0IC8 [SA602A]	AF24BC08@TSOP8 [SA026-B3201]
AF24BC16	AF24BC16@S0IC8 [SA602A]

AF24BC16@TSOP8 [SA026-B3201]
AF24C128@S0IC8 [SA602A]
AF24C256
AF24C256@TSOP8 [SA026-B3201]
AF24C32@S0IC8 [SA602A]
AF24C64
AF24C64@TSOP8 [SA026-B3201]
AF93C46(08bit)@S0IC8 [SA602A]
AF93C46(08bit)@TSOP8 [SA026-B3201]
AF93C46(16bit)
AF93C46(16bit)@TSOP8 [SA026-B3201]
AF93C56(08bit)
AF93C56(08bit)@TSOP8 [SA026-B3201]
AF93C56(16bit)
AF93C56(16bit)@TSOP8 [SA026-B3201]
AF93C66(08bit)
AF93C66(08bit)@TSOP8 [SA026-B3201]
AF93C66(16bit)
AF93C66(16bit)@TSOP8 [SA026-B3201]
AF93C86(08bit)
AF93C86(08bit)@TSOP8 [SA026-B3201]
AF93C86(16bit)
AF93C86(16bit)@TSOP8 [SA026-B3201]

AF24C128
AF24C128@TSOP8 [SA026-B3201]
AF24C256@S0IC8 [SA602A]
AF24C32
AF24C32@TSOP8 [SA026-B3201]
AF24C64@S0IC8 [SA602A]
AF93C46(08bit)
AF93C46(16bit)@S0IC8 [SA602A]
AF93C56(08bit)@S0IC8 [SA602A]
AF93C56(16bit)@S0IC8 [SA602A]
AF93C66(08bit)@S0IC8 [SA602A]
AF93C66(16bit)@S0IC8 [SA602A]
AF93C86(08bit)@S0IC8 [SA602A]
AF93C86(16bit)@S0IC8 [SA602A]

MICROCONTROLLER

AG89P51
AG89P51@PQFP44
AG89P51A@PLCC44
AG89P52
AG89P52@PQFP44

AG89P51@PLCC44
AG89P51A
AG89P51A@PQFP44
AG89P52@PLCC44

ALI(Acer)

E(E)PROM/FRAM/NVRAM

M8720
M8720@PLCC32 [SA015A1T]

MICROCONTROLLER

M6759
M6759@TQFP44 [SA675-B4805]

M6759@PLCC44 [SA244]

ALLIANCE

E(E)PROM/FRAM/NVRAM

AS29F200B@PSOP44 [SA638]
AS29F200T@PSOP44 [SA638]
AS29LV160B@TSOP48 [SB247-B4806]
AS29LV400B@TSOP48 [SB247-B4806]
AS29LV800B@TSOP48 [SB247-B4806]

AS29F200B@TSOP48 [SB247-B4806]
AS29F200T@TSOP48 [SB247-B4806]
AS29LV160T@TSOP48 [SB247-B4806]
AS29LV400T@TSOP48 [SB247-B4806]
AS29LV800T@TSOP48 [SB247-B4806]

ALTERA

E(E) PROM/FRAM/NVRAM

EPC1(LC)@PLCC20 [SA001A-B2001]
EPC1(PC8)
EPC1441(LC)@PLCC20 [SA001A-B2001]
EPC1441(LI)@PLCC20 [SA001A-B2001]
EPC1441(PC8)
EPC1441(TC)@TQFP32 [SA636]
EPC2(LC)@PLCC20 [SA001A-B2001]
EPC2(TC)@TQFP32 [SA636]
EPCS128@S0IC16 [SA404]
EPCS16@S0IC8 [SA602A]
EPCS4SI8@S0IC8 [SA602]

EPC1(LI)@PLCC20 [SA001A-B2001]
EPC1(PI8)

EPC1441(PI8)
EPC1441(TI)@TQFP32 [SA636]
EPC2(LI)@PLCC20 [SA001A-B2001]
EPC2(TI)@TQFP32 [SA636]
EPCS16@S0IC16 [SA404]
EPCS1SI8@S0IC8 [SA602]
EPCS64@S0IC16 [SA404]

PLD

EP600
EP600@S0IC24 [SA404]
EP600I@PLCC28 [SA008A]
EP610
EP610@S0IC24 [SA404]
EP610A@PLCC28 [SA008A]
EP610I
EP610I@S0IC24 [SA404]
EP610T@PLCC28 [SA008A]
EP630
EP630@S0IC24 [SA404]

EP600@PLCC28 [SA008A]
EP600I
EP600I@S0IC24 [SA404]
EP610@PLCC28 [SA008A]
EP610A
EP610A@S0IC24 [SA404]
EP610I@PLCC28 [SA008A]
EP610T
EP610T@S0IC24 [SA404]
EP630@PLCC28 [SA008A]

AMD

E(E) PROM/FRAM/NVRAM

AM25FL005D@S0IC8 [SA602A]
AM25FL010D@S0IC8 [SA602A]
AM25FL016A@S0IC16 [SA404]
AM25FL020D@S0IC8 [SA602A]
AM25FL032A@S0IC16 [SA404]
AM25FL040D@S0IC8 [SA602A]
AM25FL080D@S0IC8 [SA602A]
AM27128
AM27128(DC)@PLCC32 [SA015A1T]
AM27128A
AM27128A(F)@PLCC32 [SA015A1T]
AM27128A(PC)@PLCC32 [SA015A1T]
AM2716
AM27256
AM27256AP
AM27256F
AM27256PC
AM2732
AM2732B
AM27512@PLCC32 [SA015A1T]
AM27512DC@PLCC32 [SA015A1T]
AM27512F@PLCC32 [SA015A1T]
AM27512PC@PLCC32 [SA015A1T]
AM2764
AM2764A

AM25FL005D@US0N8 [SA683]
AM25FL010D@US0N8 [SA683]
AM25FL016A@WSON8 [SA684]
AM25FL020D@US0N8 [SA683]
AM25FL032A@WSON8 [SA684]
AM25FL040D@US0N8 [SA683]
AM25FL080D@US0N8 [SA683]
AM27128(DC)
AM27128@PLCC32 [SA015A1T]
AM27128A(F)
AM27128A(PC)
AM27128A@PLCC32 [SA015A1T]
AM2716B
AM27256@PLCC32 [SA015A1T]
AM27256AP@PLCC32 [SA015A1T]
AM27256F@PLCC32 [SA015A1T]
AM27256PC@PLCC32 [SA015A1T]
AM2732A
AM27512
AM27512DC
AM27512F
AM27512PC
AM27513
AM2764@PLCC32 [SA015A1T]
AM2764A(DC)

AM2764A(DC)@PLCC32 [SA015A1T]	AM2764A(DCB)
AM2764A(DI)	AM2764A(DIB)
AM2764A(F)	AM2764A(F)@PLCC32 [SA015A1T]
AM2764A(JC)	AM2764A(LC)
AM2764A(LCB)	AM2764A(LE)
AM2764A(LEB)	AM2764A(PC)
AM2764A(PC)@PLCC32 [SA015A1T]	AM2764A@PLCC32 [SA015A1T]
AM27C010	AM27C010@PLCC32 [SA015A1T]
AM27C010@TSOP32 [SA410T-B4001]	AM27C020
AM27C020@PLCC32 [SA015A1T]	AM27C020@TSOP32 [SA410T-B4001]
AM27C040	AM27C040@PLCC32 [SA015A1T]
AM27C040@TSOP32 [SA410T-B4001]	AM27C080
AM27C080@PLCC32 [SA015A1T]	AM27C080@TSOP32 [SA410T-B4001]
AM27C100	AM27C100@PLCC32 [SA015A1T]
AM27C100@TSOP32 [SA410T-B4001]	AM27C1024
AM27C1024@PLCC44 [SA244]	AM27C128
AM27C128@PLCC32 [SA015A1T]	AM27C2048
AM27C2048@PLCC44 [SA244]	AM27C2048@TSOP40 [SA409T-B4002]
AM27C256	AM27C256(F)
AM27C256(F)@PLCC32 [SA015A1T]	AM27C256(PC)
AM27C256(PC)@PLCC32 [SA015A1T]	AM27C256@PLCC32 [SA015A1T]
AM27C400	AM27C400@PLCC44 [SA244]
AM27C4096	AM27C4096@PLCC44 [SA244]
AM27C512	AM27C512(P)
AM27C512(P)@PLCC32 [SA015A1T]	AM27C512@PLCC32 [SA015A1T]
AM27C64	AM27C64@PLCC32 [SA015A1T]
AM27H010	AM27H010@PLCC32 [SA015A1T]
AM27H010@TSOP32 [SA410T-B4001]	AM27H256
AM27H256@PLCC32 [SA015A1T]	AM27HB010
AM27HB010@PLCC32 [SA015A1T]	AM27HB010@TSOP32 [SA410T-B4001]
AM27LV010	AM27LV010@PLCC32 [SA015A1T]
AM27LV010@TSOP32 [SA603]	AM27LV010B
AM27LV010B@PLCC32 [SA015A1T]	AM27LV010B@TSOP32 [SA410T-B4001]
AM27LV020	AM27LV020@PLCC32 [SA015A1T]
AM27LV020@TSOP32 [SA410T-B4001]	AM27LV020B
AM27LV020B@PLCC32 [SA015A1T]	AM27LV020B@TSOP32 [SA410T-B4001]
AM2816A	AM2817A
AM2817A@PLCC32 [SA015A1T]	AM2817A@SOIC28 [SA404]
AM2864A	AM2864A(E)
AM2864A(E)@PLCC32 [SA015A1T]	AM2864A@PLCC32 [SA015A1T]
AM2864B	AM2864B(E)
AM2864B(E)@PLCC32 [SA015A1T]	AM2864B@PLCC32 [SA015A1T]
AM28F001	AM28F001@PLCC32 [SA015A1T]
AM28F001@TSOP32 [SA410T-B4001]	AM28F010
AM28F010(REVERSE)@TSOP32 [SA410T-B4001]	AM28F010@TSOP32 [SA410T-B4001]
AM28F010@PLCC32 [SA015A1T]	
AM28F010A	
AM28F010A(REVERSE)@TSOP32 [SA410T-B4001]	
AM28F010A@PLCC32 [SA015A1T]	AM28F010A@TSOP32 [SA410T-B4001]
AM28F020	
AM28F020(REVERSE)@TSOP32 [SA410T-B4001]	
AM28F020@PLCC32 [SA015A1T]	AM28F020@TSOP32 [SA410T-B4001]
AM28F020A	
AM28F020A(REVERSE)@TSOP32 [SA410T-B4001]	
AM28F020A@PLCC32 [SA015A1T]	AM28F020A@TSOP32 [SA410T-B4001]
AM28F256	
AM28F256(REVERSE)@TSOP32 [SA410T-B4001]	
AM28F256@PLCC32 [SA015A1T]	AM28F256@TSOP32 [SA410T-B4001]
AM28F256A	

AM28F256A(REVERSE)@TSOP32 [SA410T-B4001]
AM28F256A@PLCC32 [SA015A1T] AM28F256A@TSOP32 [SA410T-B4001]
AM28F512
AM28F512(REVERSE)@TSOP32 [SA410T-B4001]
AM28F512@PLCC32 [SA015A1T] AM28F512@TSOP32 [SA410T-B4001]
AM28F512A
AM28F512A(REVERSE)@TSOP32 [SA410T-B4001]
AM28F512A@PLCC32 [SA015A1T] AM28F512A@TSOP32 [SA410T-B4001]
AM28F512AF
AM28F512AF(REVERSE)@TSOP32 [SA410T-B4001]
AM28F512AF@PLCC32 [SA015A1T] AM28F512AF@TSOP32 [SA410T-B4001]
AM28F512F
AM28F512F(REVERSE)@TSOP32 [SA410T-B4001]
AM28F512F@PLCC32 [SA015A1T] AM28F512F@TSOP32 [SA410T-B4001]
AM29DL161DB@TSOP48 [SB247-B4806] AM29DL161DT@TSOP48 [SB247-B4806]
AM29DL162CB@TSOP48 [SB247-B4806] AM29DL162CT@TSOP48 [SB247-B4806]
AM29DL162DB@TSOP48 [SB247-B4806] AM29DL162DT@TSOP48 [SB247-B4806]
AM29DL163CB@TSOP48 [SB247-B4806] AM29DL163CT@TSOP48 [SB247-B4806]
AM29DL163DB@TSOP48 [SB247-B4806] AM29DL163DT@TSOP48 [SB247-B4806]
AM29DL164CB@TSOP48 [SB247-B4806] AM29DL164CT@TSOP48 [SB247-B4806]
AM29DL164DB@TSOP48 [SB247-B4806] AM29DL164DT@TSOP48 [SB247-B4806]
AM29DL320GB@TSOP48 [SB247-B4806] AM29DL320GT@TSOP48 [SB247-B4806]
AM29DL321CB@TSOP48 [SB247-B4806] AM29DL321CT@TSOP48 [SB247-B4806]
AM29DL322CB@TSOP48 [SB247-B4806] AM29DL322CT@TSOP48 [SB247-B4806]
AM29DL322DB@TSOP48 [SB247-B4806] AM29DL322DT@TSOP48 [SB247-B4806]
AM29DL322GB@TSOP48 [SB247-B4806] AM29DL322GT@TSOP48 [SB247-B4806]
AM29DL323CB@TSOP48 [SB247-B4806] AM29DL323CT@TSOP48 [SB247-B4806]
AM29DL323DB@TSOP48 [SB247-B4806] AM29DL323DT@TSOP48 [SB247-B4806]
AM29DL323GB@TSOP48 [SB247-B4806] AM29DL323GT@TSOP48 [SB247-B4806]
AM29DL324CB@TSOP48 [SB247-B4806] AM29DL324CT@TSOP48 [SB247-B4806]
AM29DL324DB@TSOP48 [SB247-B4806] AM29DL324DT@TSOP48 [SB247-B4806]
AM29DL324GB@TSOP48 [SB247-B4806] AM29DL324GT@TSOP48 [SB247-B4806]
AM29DL400BB(REVERSE)@TSOP48 [SB247-B4806]
AM29DL400BB@PSOP44 [SA638] AM29DL400BB@TSOP48 [SB247-B4806]
AM29DL400BT(REVERSE)@TSOP48 [SB247-B4806]
AM29DL400BT@PLCC44 [SA638] AM29DL400BT@TSOP48 [SB247-B4806]
AM29DL640D@TSOP48 [SB247-B4806] AM29DL640G@TSOP48 [SB247-B4806]
AM29DL800B@PSOP44 [SA638] AM29DL800B@TSOP48 [SB247-B4806]
AM29DL800BB(REVERSE)@TSOP48 [SB247-B4806]
AM29DL800BB@PSOP44 [SA638] AM29DL800BB@TSOP48 [SB247-B4806]
AM29DL800BT(REVERSE)@TSOP48 [SB247-B4806]
AM29DL800BT@PSOP44 [SA638] AM29DL800BT@TSOP48 [SB247-B4806]
AM29DL800T@PSOP44 [SA638] AM29DL800T@TSOP48 [SB247-B4806]
AM29DS163CB@TSOP48 [SB247-B4806] AM29DS163CT@TSOP48 [SB247-B4806]
AM29DS163DB@TSOP48 [SB247-B4806] AM29DS163DT@TSOP48 [SB247-B4806]
AM29DS323DB@TSOP48 [SB247-B4806] AM29DS323DT@TSOP48 [SB247-B4806]
AM29F002B AM29F002B@PLCC32 [SA015A1T]
AM29F002B@TSOP32 [SA410T-B4001] AM29F002BB
AM29F002BB@PLCC32 [SA015A1T] AM29F002BB@TSOP32 [SA410T-B4001]
AM29F002BT AM29F002BT@PLCC32 [SA015A1T]
AM29F002BT@TSOP32 [SA410T-B4001] AM29F002NB
AM29F002NB@PLCC32 [SA015A1T] AM29F002NB@TSOP32 [SA410T-B4001]
AM29F002NBB AM29F002NBB@PLCC32 [SA015A1T]
AM29F002NBB@TSOP32 [SA410T-B4001]
AM29F002NBT AM29F002NBT@PLCC32 [SA015A1T]
AM29F002NBT@TSOP32 [SA410T-B4001]
AM29F002NT AM29F002NT@PLCC32 [SA015A1T]
AM29F002NT@TSOP32 [SA410T-B4001] AM29F002T
AM29F002T@PLCC32 [SA015A1T] AM29F002T@TSOP32 [SA410T-B4001]

AM29F004BB
AM29F004BB@TSOP32 [SA410T-B4001]
AM29F004BT@PLCC32 [SA015A1T]
AM29F004BT@TSOP32 [SA410T-B4001]
AM29F010
AM29F010(REVERSE)@TSOP32 [SA410T-B4001]
AM29F010@PLCC32 [SA015A1T]
AM29F010@TSOP32 [SA410T-B4001]
AM29F010A
AM29F010A(REVERSE)@TSOP32 [SA410T-B4001]
AM29F010A@PLCC32 [SA015A1T]
AM29F010A@TSOP32 [SA410T-B4001]
AM29F010B
AM29F010B(REVERSE)@TSOP32 [SA410T-B4001]
AM29F010B@PLCC32 [SA015A1T]
AM29F010B@TSOP32 [SA410T-B4001]
AM29F016@PSOP44 [SA638]
AM29F016@TSOP40 [SA409T-B4002]
AM29F016@TSOP48 [SB247-B4806]
AM29F016B@PSOP44 [SA638]
AM29F016B@TSOP40 [SA409T-B4002]
AM29F016B@TSOP48 [SB247-B4806]
AM29F016D(REVERSE)@TSOP48 [SB247-B4806]
AM29F016D@PSOP44 [SA638]
AM29F016D@TSOP40 [SA409T-B4002]
AM29F016D@TSOP48 [SB247-B4806]
AM29F017B(REVERSE)@TSOP40 [SA409T-B4002]
AM29F017B(REVERSE)@TSOP48 [SB247-B4806]
AM29F017B@TSOP40 [SA409T-B4002]
AM29F017B@TSOP48 [SB247-B4806]
AM29F017D(REVERSE)@TSOP48 [SB247-B4806]
AM29F017D@TSOP40 [SA409T-B4002]
AM29F017D@TSOP48 [SB247-B4806]
AM29F032B@PSOP44 [SA638]
AM29F032B@TSOP40 [SA409T-B4002]
AM29F040
AM29F040@PLCC32 [SA015A1T]
AM29F040@TSOP32 [SA410T-B4001]
AM29F040A
AM29F040A@TSOP32 [SA410T-B4001]
AM29F040B
AM29F040B(Reverse)@TSOP32 [SA410T-B4001]
AM29F040B@PLCC32 [SA015A1T]
AM29F040B@TSOP32 [SA410T-B4001]
AM29F080(REVERSE)@TSOP40 [SA409T-B4002]
AM29F080@PSOP44 [SA638]
AM29F080@TSOP40 [SA409T-B4002]
AM29F080B@PSOP44 [SA638]
AM29F080B@TSOP40 [SA409T-B4002]
AM29F100B(REVERSE)@TSOP48 [SB247-B4806]
AM29F100B@PSOP44 [SA638]
AM29F100B@TSOP48 [SB247-B4806]
AM29F100T(REVERSE)@TSOP48 [SB247-B4806]
AM29F100T@PSOP44 [SA638]
AM29F100T@TSOP48 [SB247-B4806]
AM29F160DB(REVERSE)@TSOP48 [SB247-B4806]
AM29F160DB@TSOP48 [SB247-B4806]
AM29F160DT(REVERSE)@TSOP48 [SB247-B4806]
AM29F160DT@TSOP48 [SB247-B4806]
AM29F200AB(REVERSE)@TSOP48 [SB247-B4806]
AM29F200AB@PSOP44 [SA638]
AM29F200AB@TSOP48 [SB247-B4806]
AM29F200AT(REVERSE)@TSOP48 [SB247-B4806]
AM29F200AT@PSOP44 [SA638]
AM29F200AT@TSOP48 [SB247-B4806]
AM29F200BB(REVERSE)@TSOP48 [SB247-B4806]
AM29F200BB@PSOP44 [SA638]
AM29F200BB@TSOP48 [SB247-B4806]
AM29F200BT(REVERSE)@TSOP48 [SB247-B4806]
AM29F200BT@PSOP44 [SA638]
AM29F200BT@TSOP48 [SB247-B4806]
AM29F400AB(REVERSE)@TSOP48 [SB247-B4806]
AM29F400AB@PSOP44 [SA638]
AM29F400AB@TSOP48 [SB247-B4806]
AM29F400AT(REVERSE)@TSOP48 [SB247-B4806]
AM29F400AT@PSOP44 [SA638]
AM29F400AT@TSOP48 [SB247-B4806]
AM29F400BB(REVERSE)@TSOP48 [SB247-B4806]
AM29F400BB@PSOP44 [SA638]
AM29F400BB@TSOP48 [SB247-B4806]
AM29F400BT(REVERSE)@TSOP48 [SB247-B4806]
AM29F400BT@PSOP44 [SA638]
AM29F400BT@TSOP48 [SB247-B4806]
AM29F800B(REVERSE)@TSOP48 [SB247-B4806]
AM29F800B@PSOP44 [SA638]
AM29F800B@TSOP48 [SB247-B4806]

AM29F800BB(REVERSE)@TSOP48 [SB247-B4806]
AM29F800BB@PSOP44 [SA638] AM29F800BB@TSOP48 [SB247-B4806]
AM29F800BT(REVERSE)@TSOP48 [SB247-B4806]
AM29F800BT@PSOP44 [SA638] AM29F800BT@TSOP48 [SB247-B4806]
AM29F800T(REVERSE)@TSOP48 [SB247-B4806]
AM29F800T@PSOP44 [SA638] AM29F800T@TSOP48 [SB247-B4806]
AM29LL800B@TSOP48 [SB247-B4806] AM29LL800BB@TSOP48 [SB247-B4806]
AM29LL800BT@TSOP48 [SB247-B4806] AM29LL800T@TSOP48 [SB247-B4806]
AM29LV001BB(REVERSE)@TSOP32 [SA410T-B4001]
AM29LV001BB@PLCC32 [SA015A1T]
AM29LV001BB@TSOP32 [SA410T-B4001]
AM29LV001BT(REVERSE)@TSOP32 [SA410T-B4001]
AM29LV001BT@PLCC32 [SA015A1T]
AM29LV001BT@TSOP32 [SA410T-B4001]
AM29LV002@TSOP40 [SA409T-B4002] AM29LV002B@TSOP40 [SA409T-B4002]
AM29LV002BB@TSOP40 [SA409T-B4002]
AM29LV002BT@TSOP40 [SA409T-B4002]
AM29LV004B@TSOP40 [SA409T-B4002]
AM29LV004BB@TSOP40 [SA409T-B4002]
AM29LV004BT@TSOP40 [SA409T-B4002]
AM29LV004T@TSOP40 [SA409T-B4002] AM29LV008B@TSOP40 [SA409T-B4002]
AM29LV008BB@TSOP40 [SA409T-B4002]
AM29LV008BT@TSOP40 [SA409T-B4002]
AM29LV008T@TSOP40 [SA409T-B4002] AM29LV010B@PLCC32 [SA015A1T]
AM29LV010B@TSOP32 [SA410T-B4001]
AM29LV017B(REVERSE)@TSOP40 [SA409T-B4002]
AM29LV017B@TSOP40 [SA409T-B4002]
AM29LV017D(REVERSE)@TSOP40 [SA409T-B4002]
AM29LV017D@TSOP40 [SA409T-B4002] AM29LV020B@PLCC32 [SA015A1T]
AM29LV020B@TSOP32 [SA410T-B4001] AM29LV033C@TSOP40 [SA409T-B4002]
AM29LV033MU@TSOP40 [SA409T-B4002]
AM29LV040B@PLCC32 [SA015A1T] AM29LV040B@TSOP32 [SA410T-B4001]
AM29LV040E@PLCC32 [SA015A1T] AM29LV040E@TSOP32 [SA410T-B4001]
AM29LV040J@PLCC32 [SA015A1T] AM29LV040J@TSOP32 [SA410T-B4001]
AM29LV065D@TSOP48 [SB247-B4806] AM29LV065MU@TSOP48 [SB247-B4806]
AM29LV080@TSOP40 [SA409T-B4002] AM29LV081@TSOP40 [SA409T-B4002]
AM29LV081B@TSOP40 [SA409T-B4002]
AM29LV116BB@TSOP40 [SA409T-B4002]
AM29LV116BT@TSOP40 [SA409T-B4002]
AM29LV116DB@TSOP40 [SA409T-B4002]
AM29LV116DT@TSOP40 [SA409T-B4002]
AM29LV160BB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160BB@PSOP44 [SA638] AM29LV160BB@TSOP48 [SB247-B4806]
AM29LV160BT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160BT@PSOP44 [SA638] AM29LV160BT@TSOP48 [SB247-B4806]
AM29LV160DB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160DB@PSOP44 [SA638] AM29LV160DB@TSOP48 [SB247-B4806]
AM29LV160DB@TSOP48(SLOW) [SA247-B4806]
AM29LV160DT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160DT@PSOP44 [SA638] AM29LV160DT@TSOP48 [SB247-B4806]
AM29LV160MB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160MB@PSOP44 [SA638] AM29LV160MB@TSOP48 [SB247-B4806]
AM29LV160MT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160MT@PSOP44 [SA638] AM29LV160MT@TSOP48 [SB247-B4806]
AM29LV200B(REVERSE)@TSOP48 [SB247-B4806]
AM29LV200B@PSOP44 [SA638] AM29LV200B@TSOP48 [SB247-B4806]
AM29LV200BB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV200BB@PSOP44 [SA638] AM29LV200BB@TSOP48 [SB247-B4806]
AM29LV200BT(REVERSE)@TSOP48 [SB247-B4806]

AM29LV200BT@PSOP44 [SA638]	AM29LV200BT@TSOP48 [SB247-B4806]
AM29LV200T(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV200T@PSOP44 [SA638]	AM29LV200T@TSOP48 [SB247-B4806]
AM29LV320DB@TSOP48 [SB247-B4806]	AM29LV320DT@TSOP48 [SB247-B4806]
AM29LV320FB@TSOP48 [SB247-B4806]	AM29LV320FT@TSOP48 [SB247-B4806]
AM29LV320MB@TSOP48 [SB247-B4806]	AM29LV320MT@TSOP48 [SB247-B4806]
AM29LV400B(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV400B@PSOP44 [SA638]	AM29LV400B@TSOP48 [SB247-B4806]
AM29LV400BB(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV400BB@PSOP44 [SA638]	AM29LV400BB@TSOP48 [SB247-B4806]
AM29LV400BT(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV400BT@PSOP44 [SA638]	AM29LV400BT@TSOP48 [SB247-B4806]
AM29LV400T(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV400T@PSOP44 [SA638]	AM29LV400T@TSOP48 [SB247-B4806]
AM29LV640MB@TSOP48 [SB247-B4806]	AM29LV640MT@TSOP48 [SB247-B4806]
AM29LV641DH(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV641DH@TSOP48 [SB247-B4806]	
AM29LV641DL(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV641DL@TSOP48 [SB247-B4806]	
AM29LV641GH(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV641GH@TSOP48 [SB247-B4806]	
AM29LV641GL(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV641GL@TSOP48 [SB247-B4806]	
AM29LV641MH(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV641MH@TSOP48 [SB247-B4806]	
AM29LV641ML(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV641ML@TSOP48 [SB247-B4806]	
AM29LV800B(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV800B@PSOP44 [SA638]	AM29LV800B@TSOP48 [SB247-B4806]
AM29LV800BB(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV800BB@PSOP44 [SA638]	AM29LV800BB@TSOP48 [SB247-B4806]
AM29LV800BT(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV800BT@PSOP44 [SA638]	AM29LV800BT@TSOP48 [SB247-B4806]
AM29LV800DB(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV800DB@PSOP44 [SA638]	AM29LV800DB@TSOP48 [SB247-B4806]
AM29LV800DT(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV800DT@PSOP44 [SA638]	AM29LV800DT@TSOP48 [SB247-B4806]
AM29LV800T(REVERSE)@TSOP48 [SB247-B4806]	
AM29LV800T@PSOP44 [SA638]	AM29LV800T@TSOP48 [SB247-B4806]
AM29PL160CB@PSOP44 [SA638]	AM29PL160CB@TSOP48 [SB247-B4806]
AM29PL160CT@TSOP48 [SB247-B4806]	AM29SL160BB@TSOP48 [SB247-B4806]
AM29SL160BT@TSOP48 [SB247-B4806]	AM29SL160CB@TSOP48 [SB247-B4806]
AM29SL160CT@TSOP48 [SB247-B4806]	AM29SL400CB@TSOP48 [SB247-B4806]
AM29SL400CT@TSOP48 [SB247-B4806]	
AM29SL800BB(REVERSE)@TSOP48 [SB247-B4806]	
AM29SL800BB@TSOP48 [SB247-B4806]	
AM29SL800BT(REVERSE)@TSOP48 [SB247-B4806]	
AM29SL800BT@TSOP48 [SB247-B4806]	
AM29SL800CB(REVERSE)@TSOP48 [SB247-B4806]	
AM29SL800CB@TSOP48 [SB247-B4806]	
AM29SL800CT(REVERSE)@TSOP48 [SB247-B4806]	
AM29SL800CT@TSOP48 [SB247-B4806]	
AM29SL800DB(REVERSE)@TSOP48 [SB247-B4806]	
AM29SL800DB@TSOP48 [SB247-B4806]	
AM29SL800DT(REVERSE)@TSOP48 [SB247-B4806]	
AM29SL800DT@TSOP48 [SB247-B4806]	AM9716
AM9732	AM9732A
AM9764	AM9764@PLCC32 [SA015A1T]

PLD

PALCE16V8H	PALCE16V8H@PLCC20 [SA001A-B2001]
PALCE16V8H@S0IC20 [SA404]	PALCE16V8Q
PALCE16V8Q@PLCC20 [SA001A-B2001]	PALCE16V8Q@S0IC20 [SA404]
PALCE16V8Z	PALCE16V8Z@PLCC20 [SA001A-B2001]
PALCE16V8Z@S0IC20 [SA404]	PALLV16V8
PALLV16V8@PLCC20 [SA001A-B2001]	PALLV16V8@S0IC20 [SA404]
PALLV16V8Z	PALLV16V8Z@PLCC20 [SA001A-B2001]
PALLV16V8Z@S0IC20 [SA404]	

MICROCONTROLLER

AM87C51	AM87C51@PLCC44 [SA244]
AM87C51@TQFP44 [SA675-B4805]	AM87C521
AM87C521@PLCC44 [SA244]	AM87C521@TQFP44 [SA675-B4805]
AM87C541	AM87C541@PLCC44 [SA244]
AM87C541@TQFP44 [SA675-B4805]	

AMIC

E (E) PROM / FRAM / NVRAM

A25L010	A25L010@SOP8[150mil] [SA602A]
A25L010@SOP8[209mil] [SA605B]	A25L016
A25L016@SOP8 [SA605B]	A25L020
A25L020@SOP8[150mil] [SA602A]	A25L020@SOP8[209mil] [SA605B]
A25L032	A25L032@SOP16 [SA404]
A25L032@SOP8 [SA605B]	A25L040
A25L040@QFN8 [SA683]	A25L040@SOP16 [SA404]
A25L040@SOP8 [SA602A]	A25L05P(Bottom)
A25L05P(Bottom)@QFN8 [SA683]	
A25L05P(Bottom)[150mil]@SOP8 [SA602A]	A25L05P(Top)@QFN8 [SA683]
A25L05P(Bottom)[209mil]@SOP8 [SA605B]	
A25L05P(Top)	
A25L05P(Top)[150mil]@SOP8 [SA602A]	A25L080@QFN8 [SA683]
A25L05P(Top)[209mil]@SOP8 [SA605B]	A25L080@SOP8 [SA605B]
A25L080	A25L10P(Bottom)@QFN8 [SA683]
A25L080@SOP16	
A25L10P(Bottom)	
A25L10P(Bottom)[150mil]@SOP8 [SA602A]	A25L10P(Top)@QFN8 [SA683]
A25L10P(Bottom)[209mil]@SOP8 [SA605B]	
A25L10P(Top)	
A25L10P(Top)[150mil]@SOP8 [SA602A]	
A25L10P(Top)[209mil]@SOP8 [SA605B]	
A25L16P(Bottom Boot)@QFN8 [SA683]	
A25L16P(Bottom Boot)@SOP16 [SA404]	
A25L16P(Bottom Boot)@SOP8 [SA605B]	
A25L16P(Top Boot)@QFN8 [SA684]	A25L16P(Top Boot)@SOP16 [SA404]
A25L16P(Top Boot)@SOP8 [SA605B]	A25L20P(Bottom)
A25L20P(Bottom)@QFN8 [SA683]	
A25L20P(Bottom)[150mil]@SOP8 [SA602A]	
A25L20P(Bottom)[209mil]@SOP8 [SA605B]	
A25L20P(Top)	A25L20P(Top)@QFN8 [SA683]
A25L20P(Top)[150mil]@SOP8 [SA602A]	
A25L20P(Top)[209mil]@SOP8 [SA605B]	
A25L40P(Bottom)	A25L40P(Bottom)@QFN8 [SA683]
A25L40P(Bottom)@SOP16	A25L40P(Bottom)@SOP8 [SA602A]

A25L40P(Top)
A25L40P(Top)@SOP16
A25L42P(Bottom Boot)
A25L42P(Bottom Boot)@QFN8 [SA683]
A25L42P(Bottom Boot)@SOP16 [SA404]
A25L42P(Bottom Boot)@SOP8 [SA602A]
A25L42P(Top Boot)
A25L42P(Top Boot)@SOP16 [SA404]
A25L512
A25L512[209mil]@SOP8 [SA605B]
A25L80P@QFN8 [SA683]
A25L80P@SOP8 [SA605B]
A25L82P(Bottom Boot)@QFN8 [SA683]
A25L82P(Bottom Boot)@SOP16 [SA404]
A25L82P(Bottom Boot)@SOP8 [SA605B]
A25L82P(Top Boot)
A25L82P(Top Boot)@SOP16 [SA404]
A25LS080
A25LS080@SOP16 [SA404]
A27020
A27020@TSOP32 [SA410T-B4001]
A27020L@PLCC32 [SA015A1T]
A275308
A276308
A276308(E)@PLCC32 [SA015A1T]
A276308@PLCC32 [SA015A1T]
A276308A
A276308A(L)@PLCC32 [SA015A1T]
A276308A@PLCC32 [SA015A1T]
A277308
A277308A
A278308
A278308A
A278308A(L)@PLCC32 [SA015A1T]
A279308
A290011T
A290011T@TSOP32 [SA410T-B4001]
A290011U@PLCC32 [SA015A1T]
A29001T
A29001T@TSOP32 [SA410T-B4001]
A29001U@PLCC32 [SA015A1T]
A290021T
A290021T@TSOP32 [SA410T-B4001]
A290021U@PLCC32 [SA015A1T]
A29002T
A29002T@TSOP32 [SA410T-B4001]
A29002U@PLCC32 [SA015A1T]
A29010
A29010@TSOP32 [SA410T-B4001]
A29040@PLCC32 [SA015A1T]
A29040A
A29040A@TSOP32 [SA410T-B4001]
A29040B@PLCC32 [SA015A1T]
A29160TM@PSOP44 [SA638]
A29160UM@PSOP44 [SA638]
A29400TM@PSOP44 [SA638]
A29400UM@PSOP44 [SA638]
A29512
A29512@TSOP32 [SA410T-B4001]

A25L40P(Top)@QFN8 [SA683]
A25L40P(Top)@SOP8 [SA602A]

A25L42P(Top Boot)@QFN8 [SA683]
A25L42P(Top Boot)@SOP8 [SA602A]
A25L512[150mil]@SOP8 [SA602A]
A25L80P
A25L80P@SOP16
A25L82P(Bottom Boot)

A25L82P(Top Boot)@QFN8 [SA683]
A25L82P(Top Boot)@SOP8 [SA605B]
A25LS080@QFN8 [SA683]
A25LS080@SOP8 [SA605B]
A27020@PLCC32 [SA015A1T]
A27020L
A27020L@TSOP32 [SA410T-B4001]
A275308@PLCC32 [SA015A1T]
A276308(E)
A276308(E)@S0IC28 [SA404]
A276308@S0IC28 [SA404]
A276308A(L)
A276308A(L)@S0IC28 [SA404]
A276308A@S0IC28 [SA404]
A277308@PLCC32 [SA015A1T]
A277308A@PLCC32 [SA015A1T]
A278308@PLCC32 [SA015A1T]
A278308A(L)
A278308A@PLCC32 [SA015A1T]
A279308@PLCC32 [SA015A1T]
A290011T@PLCC32 [SA015A1T]
A290011U
A290011U@TSOP32 [SA410T-B4001]
A29001T@PLCC32 [SA015A1T]
A29001U
A29001U@TSOP32 [SA410T-B4001]
A290021T@PLCC32 [SA015A1T]
A290021U
A290021U@TSOP32 [SA410T-B4001]
A29002T@PLCC32 [SA015A1T]
A29002U
A29002U@TSOP32 [SA410T-B4001]
A29010@PLCC32 [SA015A1T]
A29040
A29040@TSOP32 [SA410T-B4001]
A29040A@PLCC32 [SA015A1T]
A29040B
A29040B@TSOP32 [SA410T-B4001]
A29160TV@TSOP48 [SB247-B4806]
A29160UV@TSOP48 [SB247-B4806]
A29400TV@TSOP48 [SB247-B4806]
A29400UV@TSOP48 [SB247-B4806]
A29512@PLCC32 [SA015A1T]
A29512A

A29512A@PLCC32 [SA015A1T]	A29512A@TSOP32 [SA410T-B4001]
A29800TM@PSOP44 [SA638]	A29800TV@TSOP48 [SB247-B4806]
A29800UM@PSOP44 [SA638]	A29800UV@TSOP48 [SB247-B4806]
A29801TM@PSOP44 [SA638]	A29801TV@TSOP48 [SB247-B4806]
A29801UM@PSOP44 [SA638]	A29801UV@TSOP48 [SB247-B4806]
A29DL162TV@TSOP48 [SB247-B4806]	A29DL162UV@TSOP48 [SB247-B4806]
A29DL163TV@TSOP48 [SB247-B4806]	A29DL163UV@TSOP48 [SB247-B4806]
A29DL164TV@TSOP48 [SB247-B4806]	A29DL164UV@TSOP48 [SB247-B4806]
A29DL320FTV@TSOP48 [SB247-B4806]	A29DL320FUV@TSOP48 [SB247-B4806]
A29DL322TV@TSOP48 [SB247-B4806]	A29DL322UV@TSOP48 [SB247-B4806]
A29DL323TV(olD)@TSOP48 [SB247-B4806]	
A29DL323TV@TSOP48 [SB247-B4806]	
A29DL323UV(olD)@TSOP48 [SB247-B4806]	
A29DL323UV@TSOP48 [SB247-B4806]	
A29DL324TV(olD)@TSOP48 [SB247-B4806]	
A29DL324TV@TSOP48 [SB247-B4806]	
A29DL324UV(olD)@TSOP48 [SB247-B4806]	
A29DL324UV@TSOP48 [SB247-B4806]	A29L004ATL@PLCC32 [SA015A1T]
A29L004ATV@TSOP32 [SA410T-B4001]	A29L004ATW@TSOP40 [SA409T-B4002]
A29L004ATY@VSOP32 [SA620-B4807]	A29L004AUL@PLCC32 [SA015A1T]
A29L004AUV@TSOP32 [SA410T-B4001]	A29L004AUW@TSOP40 [SA409T-B4002]
A29L004AUY@VSOP32 [SA620-B4807]	A29L004T@PLCC32 [SA015A1T]
A29L004T@TSOP32 [SA410T-B4001]	A29L004T@TSOP40 [SA409T-B4002]
A29L004T@VSOP32 [SA620-B4807]	A29L004U@PLCC32 [SA015A1T]
A29L004U@TSOP32 [SA410T-B4001]	A29L004U@TSOP40 [SA409T-B4002]
A29L004U@VSOP32 [SA620-B4807]	A29L008ATV@TSOP40 [SA409T-B4002]
A29L008AUV@TSOP40 [SA409T-B4002]	A29L008T@TSOP40 [SA409T-B4002]
A29L008U@TSOP40 [SA409T-B4002]	A29L040
A29L040@PLCC32 [SA015A1T]	A29L040@TSOP32 [SA410T-B4001]
A29L040@VSOP32 [SA620-B4807]	A29L160ATM@PSOP44 [SA638]
A29L160ATV@TSOP48 [SB247-B4806]	A29L160AUM@PSOP44 [SA638]
A29L160AUV@TSOP48 [SB247-B4806]	A29L160BTV@TSOP48 [SB247-B4806]
A29L160BUV@TSOP48 [SB247-B4806]	A29L160FTV@TSOP48 [SB247-B4806]
A29L160FUV@TSOP48 [SB247-B4806]	A29L160HTV@TSOP48 [SB247-B4806]
A29L160HUV@TSOP48 [SB247-B4806]	A29L160TM@PSOP44 [SA638]
A29L160TV@TSOP48 [SB247-B4806]	A29L160UM@PSOP44 [SA638]
A29L160UV@TSOP48 [SB247-B4806]	A29L320ATV@TSOP48 [SB247-B4806]
A29L320AUV@TSOP48 [SB247-B4806]	A29L400ATM@PSOP44 [SA638]
A29L400ATV@TSOP48 [SB247-B4806]	A29L400AUM@PSOP44 [SA638]
A29L400AUV@TSOP48 [SB247-B4806]	A29L400TM@PSOP44 [SA638]
A29L400TV@TSOP48 [SB247-B4806]	A29L400UM@PSOP44 [SA638]
A29L400UV@TSOP48 [SB247-B4806]	A29L800ATM@PSOP44 [SA638]
A29L800ATV@TSOP48 [SB247-B4806]	A29L800AUM@PSOP44 [SA638]
A29L800AUV@TSOP48 [SB247-B4806]	A29L800HTM@PSOP44 [SA638]
A29L800HTV@TSOP48 [SB247-B4806]	A29L800HUM@PSOP44 [SA638]
A29L800HUV@TSOP48 [SB247-B4806]	A29L800TM@PSOP44 [SA638]
A29L800TV@TSOP48 [SB247-B4806]	A29L800UM@PSOP44 [SA638]
A29L800UV@TSOP48 [SB247-B4806]	A49LF004@PLCC32 [SA015A1T]
A49LF004@VSOP32 [SA620-B4807]	A49LF004M@PLCC32 [SA015A1T]
A49LF004M@VSOP32 [SA620-B4807]	A49LF040AT@PLCC32 [SA015A1T]
A49LF040AT@VSOP32 [SA620-B4807]	A49LF040T@PLCC32 [SA015A1T]
A49LF040T@VSOP32 [SA620-B4807]	A50FW040@PLCC32 [SA015A1T]
A50FW040@VSOP32 [SA620-B4807]	A50FW040M@PLCC32 [SA015A1T]
A50FW040M@VSOP32 [SA620-B4807]	A50LPW040@PLCC32 [SA015A1T]
A50LPW040@VSOP32 [SA620-B4807]	

E (E) PROM/FRAM/NVRAM

27CX010	27CX010@PLCC32 [SA015A1T]
27CX010@TSOP32 [SA410T-B4001]	27CX256
27CX321	27CX322
27CX641	27CX642
93C46	93C46@S0IC8 [SA602A]
93C46A	93C46A@S0IC8 [SA602A]
93C56A	93C56A@S0IC8 [SA602A]
93C66A	93C66A@S0IC8 [SA602A]
93CX46	93CX46@S0IC8 [SA602A]
93CX56	93CX56@S0IC8 [SA602A]
93CX66	93CX66@S0IC8 [SA602A]
AM24LC02	AM24LC02@S0IC8 [SA602A]
AM24LC02@TSSOP8 [SA026-B3201]	AM24LC04
AM24LC04@S0IC8 [SA602A]	AM24LC04@TSSOP8 [SA026-B3201]
AM24LC08	AM24LC08@S0IC8 [SA602A]
AM24LC08@TSSOP8 [SA026-B3201]	AM24LC16
AM24LC16@S0IC8 [SA602A]	AM24LC16@TSSOP8 [SA026-B3201]
AM24LC21	AM24LC21@S0IC8 [SA602A]
AM24LC21@TSSOP8 [SA026-B3201]	AM24LC21B
AM24LC21B@S0IC8 [SA602A]	AM24LC21B@TSSOP8 [SA026-B3201]
AM93LC46(08bit)	AM93LC46(08bit)@S0IC8 [SA602A]
AM93LC46(08bit)@TSOP8 [SA026-B3201]	AM93LC46(16bit)@S0IC8 [SA602A]
AM93LC46(16bit)	
AM93LC46(16bit)@TSOP8 [SA026-B3201]	AM93LC56(08bit)@S0IC8 [SA602A]
AM93LC56(08bit)	
AM93LC56(08bit)@TSOP8 [SA026-B3201]	AM93LC56(16bit)@S0IC8 [SA602A]
AM93LC56(16bit)	
AM93LC56(16bit)@TSOP8 [SA026-B3201]	AM93LC66(08bit)@S0IC8 [SA602A]
AM93LC66(08bit)	
AM93LC66(08bit)@TSOP8 [SA026-B3201]	AM93LC66(16bit)@S0IC8 [SA602A]
AM93LC66(16bit)	
AM93LC66(16bit)@TSOP8 [SA026-B3201]	AM93LC86(08bit)@S0IC8 [SA602A]
AM93LC86(08bit)	
AM93LC86(08bit)@TSOP8 [SA026-B3201]	AM93LC86(16bit)@S0IC8 [SA602A]
AM93LC86(16bit)	
AM93LC86(16bit)@TSOP8 [SA026-B3201]	

PLD

PEEL18CV8Z	PEEL18CV8Z@PLCC20 [SA001A-B2001]
PEEL18CV8Z@S0IC20 [SA404]	PEEL18CV8Z@TSOP20 [SA026-B3201]
PEEL18LV8Z	PEEL18LV8Z@PLCC20 [SA001A-B2001]
PEEL18LV8Z@S0IC20 [SA404]	PEEL18LV8Z@TSOP20 [SA026-B3201]
PEEL22CV10A	PEEL22CV10A@PLCC28 [SA008A]
PEEL22CV10A@S0IC24 [SA404]	PEEL22CV10A@TSOP24 [SA026-B3201]
PEEL22CV10A+	PEEL22CV10A+@PLCC28 [SA008A]
PEEL22CV10A+@S0IC24 [SA404]	
PEEL22CV10A+@TSOP24 [SA026-B3201]	PEEL22CV10A++@PLCC28 [SA008A]
PEEL22CV10A++	
PEEL22CV10A++@S0IC24 [SA404]	
PEEL22CV10A++@TSOP24 [SA026-B3201]	PEEL22CV10AZ@PLCC28 [SA008A]
PEEL22CV10AZ	
PEEL22CV10AZ@S0IC24 [SA404]	
PEEL22CV10AZ@TSOP24 [SA026-B3201]	PEEL22CV10AZ+@PLCC28 [SA008A]
PEEL22CV10AZ+	
PEEL22CV10AZ+@S0IC24 [SA404]	
PEEL22CV10AZ+@TSOP24 [SA026-B3201]	

PEEL22CV10AZ++	PEEL22CV10AZ++@PLCC28 [SA008A]
PEEL22CV10AZ++@S0IC24 [SA404]	
PEEL22CV10AZ++@TSOP24 [SA026-B3201]	
PEEL22LV10AZ	PEEL22LV10AZ@PLCC28 [SA008A]
PEEL22LV10AZ@S0IC24 [SA404]	
PEEL22LV10AZ@TSOP24 [SA026-B3201]	
PEEL22LV10AZ+	PEEL22LV10AZ+@PLCC28 [SA008A]
PEEL22LV10AZ+@S0IC24 [SA404]	
PEEL22LV10AZ+@TSOP24 [SA026-B3201]	
PEEL22LV10AZ++	PEEL22LV10AZ++@PLCC28 [SA008A]
PEEL22LV10AZ++@S0IC24 [SA404]	
PEEL22LV10AZ++@TSOP24 [SA026-B3201]	

APLUS FLASH

E (E) PROM/FRAM/NVRAM

AF24BC01	AF24BC01@S0IC8 [SA602A]
AF24BC01@TSSOP8 [SA026-B3201]	AF24BC02
AF24BC02@S0IC8 [SA602A]	AF24BC02@TSSOP8 [SA026-B3201]
AF24BC04	AF24BC04@S0IC8 [SA602A]
AF24BC04@TSSOP8 [SA026-B3201]	AF24BC08
AF24BC08@S0IC8 [SA602A]	AF24BC08@TSSOP8 [SA026-B3201]
AF24BC128	AF24BC128@S0IC8 [SA602A]
AF24BC128@TSOP8 [SA026-B3201]	AF24BC16
AF24BC16@S0IC8 [SA602A]	AF24BC16@TSSOP8 [SA026-B3201]
AF24BC256	AF24BC256@S0IC8 [SA602A]
AF24BC256@TSOP8 [SA026-B3201]	AF24BC32
AF24BC32@S0IC8 [SA602A]	AF24BC32@TSOP8 [SA026-B3201]
AF24BC64	AF24BC64@S0IC8 [SA602A]
AF24BC64@TSOP8 [SA026-B3201]	AF24C128
AF24C128@S0IC8 [SA602A]	AF24C128@TSOP8 [SA026-B3201]
AF24C256	AF24C256@S0IC8 [SA602A]
AF24C256@TSOP8 [SA026-B3201]	AF24C32
AF24C32@S0IC8 [SA602A]	AF24C32@TSOP8 [SA026-B3201]
AF24C64	AF24C64@S0IC8 [SA602A]
AF24C64@TSOP8 [SA026-B3201]	AF25BC08
AF25BC08@S0IC8 [SA602A]	AF25BC08@TSOP8 [SA026-B3201]
AF25BC128	AF25BC128@S0IC8 [SA602A]
AF25BC128@TSOP8 [SA026-B3201]	AF25BC16
AF25BC16@S0IC8 [SA602A]	AF25BC16@TSOP8 [SA026-B3201]
AF25BC256	AF25BC256@S0IC8 [SA602A]
AF25BC256@TSOP8 [SA026-B3201]	AF25BC32
AF25BC32@S0IC8 [SA602A]	AF25BC32@TSOP8 [SA026-B3201]
AF25BC64	AF25BC64@S0IC8 [SA602A]
AF25BC64@TSOP8 [SA026-B3201]	AF93BC46(08bit)
AF93BC46(08bit)@S0IC8 [SA602A]	AF93BC46(16bit)@S0IC8 [SA602A]
AF93BC46(08bit)@TSOP8 [SA026-B3201]	AF93BC56(08bit)@S0IC8 [SA602A]
AF93BC46(16bit)	AF93BC56(16bit)@S0IC8 [SA602A]
AF93BC46(16bit)@TSOP8 [SA026-B3201]	AF93BC66(08bit)@S0IC8 [SA602A]
AF93BC56(08bit)	AF93BC66(16bit)@S0IC8 [SA602A]
AF93BC56(08bit)@TSOP8 [SA026-B3201]	
AF93BC56(16bit)	
AF93BC56(16bit)@TSOP8 [SA026-B3201]	
AF93BC66(08bit)	
AF93BC66(08bit)@TSOP8 [SA026-B3201]	
AF93BC66(16bit)	
AF93BC66(16bit)@TSOP8 [SA026-B3201]	

AF93BC86(08bit)	AF93BC86(08bit)@S0IC8 [SA602A]
AF93BC86(08bit)@TSOP8 [SA026-B3201]	
AF93BC86(16bit)	AF93BC86(16bit)@S0IC8 [SA602A]
AF93BC86(16bit)@TSOP8 [SA026-B3201]	
AF93C46(08bit)	AF93C46(08bit)@S0IC8 [SA602A]
AF93C46(08bit)@TSOP8 [SA026-B3201]	
AF93C46(16bit)	AF93C46(16bit)@S0IC8 [SA602A]
AF93C46(16bit)@TSOP8 [SA026-B3201]	
AF93C56(08bit)	AF93C56(08bit)@S0IC8 [SA602A]
AF93C56(08bit)@TSOP8 [SA026-B3201]	
AF93C56(16bit)	AF93C56(16bit)@S0IC8 [SA602A]
AF93C56(16bit)@TSOP8 [SA026-B3201]	
AF93C66(08bit)	AF93C66(08bit)@S0IC8 [SA602A]
AF93C66(08bit)@TSOP8 [SA026-B3201]	
AF93C66(16bit)	AF93C66(16bit)@S0IC8 [SA602A]
AF93C66(16bit)@TSOP8 [SA026-B3201]	
AF93C86(08bit)	AF93C86(08bit)@S0IC8 [SA602A]
AF93C86(08bit)@TSOP8 [SA026-B3201]	
AF93C86(16bit)	AF93C86(16bit)@S0IC8 [SA602A]
AF93C86(16bit)@TSOP8 [SA026-B3201]	

ARTSCHIP

E(E)PROM/FRAM/NVRAM

24AA02	24AA02@DFN8 [SA724]
24AA02@MSOP8 [SA666]	24AA02@S0IC8 [SA602A]
24AA02@S0T5 [SA717]	24AA02@TSSOP8 [SA026-B3201]
24LC01A	24LC01A@dBGA8
24LC01A@MAP8	24LC01A@S0IC8 [SA602A]
24LC01A@S0T5 [SA717]	24LC01A@TSSOP8 [SA026-B3201]
24LC01B	24LC01B@S0IC8 [SA602A]
24LC01B@S0T5 [SA717]	24LC01B@TSSOP8 [SA026-B3201]
24LC02A	24LC02A@dBGA8
24LC02A@MAP8	24LC02A@S0IC8 [SA602A]
24LC02A@S0T5 [SA717]	24LC02A@TSSOP8 [SA026-B3201]
24LC02B	24LC02B@DFN8 [SA724]
24LC02B@MSOP8 [SA666]	24LC02B@S0IC8 [SA602A]
24LC02B@S0T5 [SA717]	24LC02B@TSSOP8 [SA026-B3201]
24LC04A	24LC04A@dBGA8
24LC04A@MAP8	24LC04A@S0IC8 [SA602A]
24LC04A@S0T5 [SA717]	24LC04A@TSSOP8 [SA026-B3201]
24LC04B	24LC04B@DFN8 [SA724]
24LC04B@MSOP8 [SA666]	24LC04B@S0IC8 [SA602A]
24LC04B@S0T5 [SA717]	24LC04B@TSSOP8 [SA026-B3201]
24LC08A	24LC08A@dBGA8
24LC08A@MAP8	24LC08A@S0IC8 [SA602A]
24LC08A@S0T5 [SA717]	24LC08A@TSSOP8 [SA026-B3201]
24LC08B	24LC08B@DFN8 [SA724]
24LC08B@MSOP8 [SA666]	24LC08B@S0IC8 [SA602A]
24LC08B@S0T5 [SA717]	24LC08B@TSSOP8 [SA026-B3201]
24LC16A	24LC16A@dBGA8
24LC16A@MAP8	24LC16A@S0IC8 [SA602A]
24LC16A@S0T5 [SA717]	24LC16A@TSSOP8 [SA026-B3201]
24LC256B	24LC256B@MSOP8 [SA666]
24LC256B@S0IC8 [SA602A]	24LC256B@TSSOP8 [SA026-B3201]
24LC32	24LC32@S0IC14 [SA026-B3201]
24LC32@S0IC8 [SA602A]	24LC32@TSSOP8 [SA026-B3201]

24LC64
24LC64@S0IC8 [SA602A]

24LC64@S0IC14 [SA026-B3201]
24LC64@TSSOP8 [SA026-B3201]

ASAHI KASEI(AKM)

E(E)PROM/FRAM/NVRAM

AK27CX321
AK27CX641
AK6002A(F)@SOP8 [SA602A]
AK6003A(V)@TSSOP8 [SA026-B3201]
AK6004A(M)@SSOP8 [SA605B]
AK6010A(F)@SOP8 [SA602A]
AK6416A(M)@SSOP8 [SA026-B3201]
AK6420A(F)@SOP8 [SA602A]
AK6420B(H)@MSOP8 [SA666]
AK6440A(M)@SSOP8 [SA026-B3201]
AK6480A(F)@SOP8 [SA602A]
AK6480B(H)@MSOP8 [SA666]
AK6480C(H)@MSOP8 [SA666]
AK6480C(M)@SSOP8 [SA026-B3201]
AK6481C(M)@SSOP8 [SA026-B3201]
AK6508C(U)@USON8
AK6510C(M)@SSOP8 [SA026-B3201]
AK6512C(M)@SSOP8 [SA026-B3201]
AK6514C(N)@QFN20 [SA692]
AK93C10A(F)@SOP8 [SA602A]
AK93C45
AK93C45A(F)@SOP8 [SA602A]
AK93C45A(V)@TSSOP8 [SA026-B3201]
AK93C45B(L)@SON8 [\$\$\$\$\$]
AK93C45C(U)@USON8 [\$\$\$\$\$]
AK93C45L(F)@SOP8 [SA602A]
AK93C46(F)@SOP8 [SA602A]
AK93C46A(NF)@SOP8 [SA602A]
AK93C46B(H)@MSOP8 [SA666]
AK93C46C(T)@MSOP8 [SA666]
AK93C46L
AK93C51A(V)@TSSOP8 [SA026-B3201]
AK93C55(F)@SOP8 [SA602A]
AK93C55A(NF)@SOP8 [SA602A]
AK93C55B(H)@MSOP8 [SA666]
AK93C55C(T)@MSOP8 [SA666]
AK93C55L
AK93C56
AK93C56A(F)@SOP8 [SA602A]
AK93C56A(V)@TSSOP8 [SA026-B3201]
AK93C56B(L)@SON8 [\$\$\$\$\$]
AK93C56C(U)@USON8 [\$\$\$\$\$]
AK93C56L(F)@SOP8 [SA602A]
AK93C65
AK93C65A(F)@SOP8 [SA602A]
AK93C65A(V)@TSSOP8 [SA026-B3201]
AK93C65B(L)@SON8 [\$\$\$\$\$]
AK93C65C(U)@USON8 [\$\$\$\$\$]
AK93C65L(F)@SOP8 [SA602A]
AK93C66(F)@SOP8 [SA602A]
AK93C66A(NF)@SOP8 [SA602A]

AK27CX322
AK27CX642
AK6002A(V)@TSSOP8 [SA026-B3201]
AK6004A(F)@SOP8 [SA602A]
AK6008A(F)@SOP8 [SA602A]
AK6012A(F)@SOP8 [SA602A]
AK6416C(F)@SOP8 [SA602A]
AK6420A(M)@SSOP8 [SA026-B3201]
AK6440A(F)@SOP8 [SA602A]
AK6440B(H)@MSOP8 [SA666]
AK6480A(M)@SSOP8 [SA026-B3201]
AK6480C(F)@SOP8 [SA602A]
AK6480C(L)@SON8
AK6481C(H)@MSOP8 [SA666]
AK6508C(T)@MSOP8 [SA666]
AK6510C(L)@SONW8
AK6512C(L)@SONW8
AK6514C(F)@SOP8 [SA602]
AK6516C(F)@SOP8 [SA602]
AK93C41A(V)@TSSOP8 [SA026-B3201]
AK93C45(F)@SOP8 [SA602A]
AK93C45A(NF)@SOP8 [SA602A]
AK93C45B(H)@MSOP8 [SA666]
AK93C45C(T)@MSOP8 [SA666]
AK93C45L
AK93C46
AK93C46A(F)@SOP8 [SA602A]
AK93C46A(V)@TSSOP8 [SA026-B3201]
AK93C46B(L)@SON8 [\$\$\$\$\$]
AK93C46C(U)@USON8 [\$\$\$\$\$]
AK93C46L(F)@SOP8 [SA602A]
AK93C55
AK93C55A(F)@SOP8 [SA602A]
AK93C55A(V)@TSSOP8 [SA026-B3201]
AK93C55B(L)@SON8 [\$\$\$\$\$]
AK93C55C(U)@USON8 [\$\$\$\$\$]
AK93C55L(F)@SOP8 [SA602A]
AK93C56(F)@SOP8 [SA602A]
AK93C56A(NF)@SOP8 [SA602A]
AK93C56B(H)@MSOP8 [SA666]
AK93C56C(T)@MSOP8 [SA666]
AK93C56L
AK93C61A(V)@TSSOP8 [SA026-B3201]
AK93C65(F)@SOP8 [SA602A]
AK93C65A(NF)@SOP8 [SA602A]
AK93C65B(H)@MSOP8 [SA666]
AK93C65C(T)@MSOP8 [SA666]
AK93C65L
AK93C66
AK93C66A(F)@SOP8 [SA602A]
AK93C66A(V)@TSSOP8 [SA026-B3201]

AK93C66B(H)@MSOP8 [SA666]
AK93C66C(T)@MSOP8 [SA666]
AK93C66L
AK93C75
AK93C75A(F)@SOP8 [SA602A]
AK93C75A(V)@TSSOP8 [SA026-B3201]
AK93C75L
AK93C85
AK93C85L
AK93C95A(F)@SOP8 [SA602A]
AK9824(M)@SSOP8 [SA026-B3201]

AK93C66B(L)@SON8 [\$\$\$\$\$]
AK93C66C(U)@USON8 [\$\$\$\$\$]
AK93C66L(F)@SOP8 [SA602A]
AK93C75(F)@SOP8 [SA602A]
AK93C75A(NF)@SOP8 [SA602A]
AK93C75B(H)@MSOP8 [SA666]
AK93C75L(F)@SOP8 [SA602A]
AK93C85(F)@SOP8 [SA602A]
AK93C85L(F)@SOP8 [SA602A]
AK9822(M)@SSOP8 [SA026-B3201]
AK9844@S0IC14 [SA602]

ASD

E(E)PROM/FRAM/NVRAM

AE29F1008

AE29F2008

ASI

E(E)PROM/FRAM/NVRAM

AS58C1001
AS58C1001@SSOP32 [SA687]

AS58C1001@PLCC32 [SA015A1T]

ASP

MICROCONTROLLER

AP827C51
AP827C52
AP827C54
AP827C58

AP827C51@PLCC44 [SA244]
AP827C52@PLCC44 [SA244]
AP827C54@PLCC44 [SA244]
AP827C58@PLCC44 [SA244]

ATC

E(E)PROM/FRAM/NVRAM

ATC24C02
ATC24C02@TSSOP8 [SA026-B3201]
ATC24C04@S0IC8 [SA602A]
ATC24C08
ATC24C08@TSSOP8 [SA026-B3201]
ATC24C16@S0IC8 [SA602A]
ATC24LC02
ATC24LC02@TSSOP8 [SA026-B3201]
ATC24LC02A@S0IC8 [SA602A]
ATC24LC04
ATC24LC04@TSSOP8 [SA026-B3201]
ATC24LC08@S0IC8 [SA602A]
ATC24LC16
ATC24LC16@TSSOP8 [SA026-B3201]
ATC93C46(08bit)@S0IC8 [SA602A]
ATC93C46(16bit)@S0IC8 [SA602A]
ATC93C46R(16bit)@S0IC8 [SA602A]

ATC24C02@S0IC8 [SA602A]
ATC24C04
ATC24C04@TSSOP8 [SA026-B3201]
ATC24C08@S0IC8 [SA602A]
ATC24C16
ATC24C16@TSSOP8 [SA026-B3201]
ATC24LC02@S0IC8 [SA602A]
ATC24LC02A
ATC24LC02A@TSSOP8 [SA026-B3201]
ATC24LC04@S0IC8 [SA602A]
ATC24LC08
ATC24LC08@TSSOP8 [SA026-B3201]
ATC24LC16@S0IC8 [SA602A]
ATC93C46(08bit)
ATC93C46(16bit)
ATC93C46R(08bit)@S0IC8 [SA602A]
ATC93C56(08bit)

ATC93C56(08bit)@S0IC8 [SA602A]
ATC93C56(16bit)@S0IC8 [SA602A]
ATC93C56R(16bit)@S0IC8 [SA602A]
ATC93C66(08bit)@S0IC8 [SA602A]
ATC93C66(16bit)@S0IC8 [SA602A]
ATC93C66R(16bit)@S0IC8 [SA602A]
ATC93LC46(08bit)@S0IC8 [SA602A]
ATC93LC46(16bit)@S0IC8 [SA602A]
ATC93LC46R(16bit)@S0IC8 [SA602A]
ATC93LC56(08bit)@S0IC8 [SA602A]
ATC93LC56(16bit)@S0IC8 [SA602A]
ATC93LC56R(16bit)@S0IC8 [SA602A]
ATC93LC66(08bit)@S0IC8 [SA602A]
ATC93LC66(16bit)@S0IC8 [SA602A]
ATC93LC66R(16bit)@S0IC8 [SA602A]

ATC93C56(16bit)
ATC93C56R(08bit)@S0IC8 [SA602A]
ATC93C66(08bit)
ATC93C66(16bit)
ATC93C66R(08bit)@S0IC8 [SA602A]
ATC93LC46(08bit)
ATC93LC46(16bit)
ATC93LC46R(08bit)@S0IC8 [SA602A]
ATC93LC56(08bit)
ATC93LC56(16bit)
ATC93LC56R(08bit)@S0IC8 [SA602A]
ATC93LC66(08bit)
ATC93LC66(16bit)
ATC93LC66R(08bit)@S0IC8 [SA602A]

ATMEL

E(E)PROM/FRAM/NVRAM

AT17C002@PLCC20 [SA001A-B2001]
AT17C002@S0IC20 [SA404]
AT17C002A@PLCC20 [SA001A-B2001]
AT17C010
AT17C010A
AT17C020@PLCC20 [SA001A-B2001]
AT17C040@PLCC44 [SA244]
AT17C128
AT17C128@S0IC20 [SA404]
AT17C128A@PLCC20 [SA001A-B2001]
AT17C256@PLCC20 [SA001A-B2001]
AT17C256@S0IC8 [SA602A]
AT17C512
AT17C512A
AT17C65
AT17C65@S0IC20 [SA404]
AT17C65A@PLCC20 [SA001A-B2001]
AT17F040@PLCC20 [SA001A-B2001]
AT17F040@PLCC20(Virtex Pinout) [SA001A-B2001]
AT17F040A@LAP8 [SA760]
AT17F040A@TQFP32 [SA636]
AT17F080@PLCC20 [SA001A-B2001]
AT17F080@TQFP44 [SA245A-B4805]
AT17F080A@PLCC20 [SA001A-B2001]
AT17F16@LAP8 [SA760]
AT17F16@PLCC44 [SA244]
AT17F16A@LAP8 [SA760]
AT17F32@PLCC44 [SA244]
AT17LV002@PLCC20 [SA001A-B2001]
AT17LV002@S0IC20 [SA404]
AT17LV002A@PLCC20 [SA001A-B2001]
AT17LV010
AT17LV010A
AT17LV020@PLCC20 [SA001A-B2001]
AT17LV040@PLCC44 [SA244]
AT17LV128
AT17LV128@S0IC20 [SA404]
AT17LV128A@PLCC20 [SA001A-B2001]

AT17C002@PLCC44 [SA244]
AT17C002@TQFP44 [SA245A-B4805]
AT17C002A@TQFP32 [SA636]
AT17C010@PLCC20 [SA001A-B2001]
AT17C010A@PLCC20 [SA001A-B2001]
AT17C020A@PLCC20 [SA001A-B2001]
AT17C040@TQFP44 [SA245A-B4805]
AT17C128@PLCC20 [SA001A-B2001]
AT17C128@S0IC8 [SA602A]
AT17C256
AT17C256@S0IC20 [SA404]
AT17C256A@PLCC20 [SA001A-B2001]
AT17C512@PLCC20 [SA001A-B2001]
AT17C512A@PLCC20 [SA001A-B2001]
AT17C65@PLCC20 [SA001A-B2001]
AT17C65@S0IC8 [SA602A]
AT17F040@LAP8 [SA760]
AT17F040A@PLCC20 [SA001A-B2001]
AT17F080@LAP8 [SA760]
AT17F080@PLCC44 [SA244]
AT17F080A@LAP8 [SA760]
AT17F080A@TQFP32 [SA636]
AT17F16@PLCC20 [SA001A-B2001]
AT17F16@TQFP44 [SA245A-B4805]
AT17F16A@PLCC20 [SA001A-B2001]
AT17F32A@PLCC44 [SA244]
AT17LV002@PLCC44 [SA244]
AT17LV002@TQFP44 [SA245A-B4805]
AT17LV002A@TQFP32 [SA636]
AT17LV010@PLCC20 [SA001A-B2001]
AT17LV010A@PLCC20 [SA001A-B2001]
AT17LV020A@PLCC20 [SA001A-B2001]
AT17LV040@TQFP44 [SA245A-B4805]
AT17LV128@PLCC20 [SA001A-B2001]
AT17LV128@S0IC8 [SA602A]
AT17LV256

AT17LV256@PLCC20 [SA001A-B2001]	AT17LV256@S0IC20 [SA404]
AT17LV256@S0IC8 [SA602A]	AT17LV256A@PLCC20 [SA001A-B2001]
AT17LV512	AT17LV512@PLCC20 [SA001A-B2001]
AT17LV512A	AT17LV512A@PLCC20 [SA001A-B2001]
AT17LV65	AT17LV65@PLCC20 [SA001A-B2001]
AT17LV65@S0IC20 [SA404]	AT17LV65@S0IC8 [SA602A]
AT17LV65A@PLCC20 [SA001A-B2001]	AT17N002@S0IC20 [SA404]
AT17N002@TQFP44 [SA245A-B4805]	AT17N010
AT17N010@S0IC20 [SA404]	AT17N040@TQFP44 [SA245A-B4805]
AT17N256	AT17N256@S0IC20 [SA404]
AT17N256@S0IC8 [SA602A]	AT17N512
AT17N512@S0IC20 [SA404]	AT24C01
AT24C01@MSOP8 [SA666]	AT24C01@S0IC8 [SA602A]
AT24C01@TSSOP8 [SA026-B3201]	AT24C01A
AT24C01A@MAP8 [SA724]	AT24C01A@S0IC8 [SA602A]
AT24C01A@S0T23-5 [SA717]	AT24C01A@TSSOP8 [SA026-B3201]
AT24C01B	AT24C01B@MAP8 [SA724]
AT24C01B@S0IC8 [SA602A]	AT24C01B@S0T23 [SA717]
AT24C01B@TSSOP8 [SA026-B3201]	AT24C02
AT24C02@S0IC8 [SA602A]	AT24C02@TSSOP8 [SA026-B3201]
AT24C02A	AT24C02A@S0IC8 [SA602A]
AT24C02A@TSSOP8 [SA026-B3201]	AT24C02B
AT24C02B@MAP8 [SA724]	AT24C02B@S0IC8 [SA602A]
AT24C02B@S0T23 [SA717]	AT24C02B@TSSOP8 [SA026-B3201]
AT24C02C	AT24C02C@S0IC8 [SA602A]
AT24C02C@TSSOP8 [SA026-B3201]	AT24C04
AT24C04@MAP8 [SA724]	AT24C04@S0IC8 [SA602A]
AT24C04@S0T23-5 [SA717]	AT24C04@TSSOP8 [SA026-B3201]
AT24C04A	AT24C04A@MAP8 [SA724]
AT24C04A@S0IC8 [SA602A]	AT24C04A@TSSOP8 [SA026-B3201]
AT24C04B	AT24C04B@MAP8 [SA724]
AT24C04B@S0IC8 [SA602A]	AT24C04B@S0T23 [SA717]
AT24C04B@TSSOP8 [SA026-B3201]	AT24C08
AT24C08@MAP8 [SA724]	AT24C08@S0IC8 [SA602A]
AT24C08@TSSOP8 [SA026-B3201]	AT24C08A
AT24C08A@MAP8 [SA724]	AT24C08A@S0IC8 [SA602A]
AT24C08A@TSSOP8 [SA026-B3201]	AT24C08B
AT24C08B@MAP8 [SA724]	AT24C08B@S0IC8 [SA602A]
AT24C08B@S0T23 [SA717]	AT24C08B@TSSOP8 [SA026-B3201]
AT24C1024	AT24C1024@LAP8 [SA684]
AT24C1024@SAP8 [SA683]	AT24C1024@S0IC8 [SA605B]
AT24C1024B(1.8V)	AT24C1024B(1.8V)@LAP8 [SA684]
AT24C1024B(1.8V)@SAP8 [SA683]	AT24C1024B(1.8V)@S0IC8 [SA605B]
AT24C1024B(1.8V)@TSSOP8 [SA026-B3201]	AT24C1024B(2.5V)@LAP8 [SA684]
AT24C1024B(2.5V)	AT24C1024B(2.5V)@S0IC8 [SA605B]
AT24C1024B(2.5V)@SAP8 [SA683]	
AT24C1024B(2.5V)@TSSOP8 [SA026-B3201]	
AT24C128(1.8V)	AT24C128(1.8V)@MAP8 [SA724]
AT24C128(1.8V)@SAP8 [SA683]	AT24C128(1.8V)@S0IC8 [SA602A]
AT24C128(1.8V)@TSSOP8 [SA026-B3201]	
AT24C128(2.7V)	AT24C128(2.7V)@MAP8 [SA724]
AT24C128(2.7V)@SAP8 [SA683]	AT24C128(2.7V)@S0IC8 [SA602A]
AT24C128(2.7V)@TSSOP8 [SA026-B3201]	
AT24C128B	AT24C128B@MAP8 [SA724]
AT24C128B@SAP8 [SA683]	AT24C128B@S0IC8 [SA602A]
AT24C128B@TSSOP8 [SA026-B3201]	AT24C16
AT24C16@S0IC8 [SA602A]	AT24C16@TSSOP8 [SA026-B3201]
AT24C16A	AT24C16A@S0IC8 [SA602A]
AT24C16A	AT24C16A@MAP8 [SA724]

AT24C16A@S0IC8 [SA602A]	AT24C16A@TSSOP8 [SA026-B3201]
AT24C16B	AT24C16B@MAP8 [SA724]
AT24C16B@S0IC8 [SA602A]	AT24C16B@TSSOP8 [SA026-B3201]
AT24C21 [SA724]	AT24C21@S0IC8 [SA602A]
AT24C256(1.8V)	AT24C256(1.8V)@MAP8 [SA724]
AT24C256(1.8V)@SAP8 [SA683]	AT24C256(1.8V)@S0IC8 [SA602A]
AT24C256(1.8V)@TSSOP8 [SA026-B3201]	
AT24C256(2.7V)	AT24C256(2.7V)@MAP8 [SA724]
AT24C256(2.7V)@SAP8 [SA683]	AT24C256(2.7V)@S0IC8 [SA602A]
AT24C256(2.7V)@TSSOP8 [SA026-B3201]	
AT24C256B	AT24C256B@MAP8 [SA724]
AT24C256B@SAP8 [SA683]	AT24C256B@S0IC8 [SA602A]
AT24C256B@TSSOP8 [SA026-B3201]	AT24C32
AT24C32@S0IC8 [SA602A]	AT24C32@TSSOP8 [SA026-B3201]
AT24C32A	AT24C32A@MAP8 [SA724]
AT24C32A@S0IC8 [SA602A]	AT24C32A@TSSOP8 [SA026-B3201]
AT24C32C	AT24C32C@MAP8 [SA724]
AT24C32C@SAP8 [SA683]	AT24C32C@S0IC8 [SA602A]
AT24C32C@TSSOP8 [SA026-B3201]	AT24C512(1.8V)
AT24C512(1.8V)@LAP8 [SA684]	AT24C512(1.8V)@SAP8 [SA683]
AT24C512(1.8V)@S0IC8 [SA602A]	
AT24C512(1.8V)@TSSOP8 [SA026-B3201]	AT24C512(2.7V)@LAP8 [SA684]
AT24C512(2.7V)	AT24C512(2.7V)@S0IC8 [SA602A]
AT24C512(2.7V)@SAP8 [SA683]	
AT24C512(2.7V)@TSSOP8 [SA026-B3201]	AT24C512B@LAP8 [SA684]
AT24C512B	AT24C512B@S0IC8 [SA602A]
AT24C512B@SAP8 [SA683]	AT24C64
AT24C512B@TSSOP8 [SA026-B3201]	AT24C64@TSSOP8 [SA026-B3201]
AT24C64@S0IC8 [SA602A]	AT24C64A@MAP8 [SA724]
AT24C64A	AT24C64A@TSSOP8 [SA026-B3201]
AT24C64A@S0IC8 [SA602A]	AT24C64B@S0IC8 [SA602A]
AT24C64B	AT24C64C
AT24C64B@TSSOP8 [SA026-B3201]	AT24C64C@SAP8 [SA683]
AT24C64C@MAP8 [SA724]	AT24C64C@TSSOP8 [SA026-B3201]
AT24C64C@S0IC8 [SA602A]	AT24CS128@S0IC8 [SA602A]
AT24CS128	AT24HC02B@S0IC8 [SA602A]
AT24HC02B	AT24RF08AN@S0IC8 [SA602A]
AT24HC02B@TSSOP8 [SA026-B3201]	AT24RF08BN@S0IC8 [SA602A]
AT24RF08AT@TSSOP14 [SA026-B3201]	AT24RF08CN@S0IC8 [SA602A]
AT24RF08BT@TSSOP14 [SA026-B3201]	AT25010
AT24RF08CT@TSSOP14 [SA026-B3201]	AT25010A
AT25010@S0IC8 [SA602A]	AT25010A@TSSOP8 [SA026-B3201]
AT25010A@S0IC8 [SA602A]	AT25020@S0IC8 [SA602A]
AT25020	AT25020A@S0IC8 [SA602A]
AT25020A	AT25040
AT25020A@TSSOP8 [SA026-B3201]	AT25040A
AT25040@S0IC8 [SA602A]	AT25080
AT25040A@S0IC8 [SA602A]	AT25080@TSSOP14 [SA026-B3201]
AT25080@S0IC8 [SA602A]	AT25080A
AT25080@TSSOP20 [SA026-B3201]	AT25080A@TSSOP14 [SA026-B3201]
AT25080A@S0IC8 [SA602A]	AT25080B@MAP8 [SA724]
AT25080B	AT25080B@TSSOP8 [SA026-B3201]
AT25080B@S0IC8 [SA602A]	AT25128@S0IC16 [SA602]
AT25128	AT25128@TSSOP14 [SA026-B3201]
AT25128@S0IC8 [SA602A]	AT25128A
AT25128@TSSOP20 [SA026-B3201]	AT25128A@S0IC8(4.0) [SA602A]
AT25128A@SAP8 [SA683]	AT25128A@TSSOP14 [SA026-B3201]
AT25128A@S0IC8(5.4) [SA605B]	AT25128B
AT25128A@TSSOP8 [SA026-B3201]	

AT25128B@S0IC8 [SA602A]
AT25128B@UDFN8 [SA724]
AT25160
AT25160@TSSOP14 [SA026-B3201]
AT25160A
AT25160A@TSSOP14 [SA026-B3201]
AT25160B@MAP8 [SA724]
AT25160B@TSSOP8 [SA026-B3201]
AT25256@S0IC16 [SA602]
AT25256@TSSOP14 [SA026-B3201]
AT25256A
AT25256A@S0IC8(4.0) [SA602A]
AT25256A@TSSOP14 [SA026-B3201]
AT25256B
AT25256B@TSSOP8 [SA026-B3201]
AT25256B@VFBGA8
AT25320@S0IC8 [SA602A]
AT25320@TSSOP20 [SA026-B3201]
AT25320A@S0IC8 [SA602A]
AT25320B
AT25320B@S0IC8 [SA602A]
AT25640
AT25640@TSSOP14 [SA026-B3201]
AT25640A
AT25640A@TSSOP14 [SA026-B3201]
AT25640B@MAP8 [SA724]
AT25640B@TSSOP8 [SA026-B3201]
AT25DF021(OTP)@UDFN8 [SA683]
AT25DF021@UDFN8 [SA683]
AT25DF041A@S0IC8(4.0) [SA602A]
AT25DF081@S0IC8 [SA602A]
AT25DF161(OTP)@S0IC8(4.0) [SA602A]
AT25DF161(OTP)@S0IC8(5.4) [SA023A]
AT25DF161(OTP)@UDFN8 [SA683]
AT25DF161@S0IC8(4.0) [SA602A]
AT25DF321@S0IC16 [SA404]
AT25DF321A(OTP)@S0IC16 [SA404]
AT25DF321A(OTP)@UDFN8 [SA683]
AT25DF641(OTP)@UDFN8 [SA683]
AT25F1024(W)@S0IC8 [SA605B]
AT25F1024@S0IC8 [SA602A]
AT25F1024A
AT25F1024A(W)@VQFPN8 [SA684]
AT25F1024A@VQFPN8 [SA683]
AT25F2048(W)@S0IC8 [SA605B]
AT25F2048@S0IC8 [SA602A]
AT25F2048A
AT25F2048A(W)@VQFPN8 [SA684]
AT25F2048A@VQFPN8 [SA683]
AT25F4096(W)@S0IC8 [SA605B]
AT25F4096@S0IC8 [SA602A]
AT25F4096A
AT25F4096A(W)@VQFPN8 [SA684]
AT25F4096A@VQFPN8 [SA683]
AT25F512(W)@S0IC8 [SA605B]
AT25F512@S0IC8 [SA602A]
AT25F512A
AT25F512A(W)@VQFPN8 [SA684]
AT25F512A@VQFPN8 [SA683]

AT25128B@TSSOP8 [SA026-B3201]
AT25128B@VFBGA8
AT25160@S0IC8 [SA602A]
AT25160@TSSOP20 [SA026-B3201]
AT25160A@S0IC8 [SA602A]
AT25160B
AT25160B@S0IC8 [SA602A]
AT25256
AT25256@S0IC8 [SA602A]
AT25256@TSSOP20 [SA643]
AT25256A@SAP8 [SA683]
AT25256A@S0IC8(5.4) [SA605B]
AT25256A@TSSOP8 [SA026-B3201]
AT25256B@S0IC8 [SA602A]
AT25256B@UDFN8 [SA724]
AT25320
AT25320@TSSOP14 [SA026-B3201]
AT25320A
AT25320A@TSSOP14 [SA026-B3201]
AT25320B@MAP8 [SA724]
AT25320B@TSSOP8 [SA026-B3201]
AT25640@S0IC8 [SA602A]
AT25640@TSSOP20 [SA026-B3201]
AT25640A@S0IC8 [SA602A]
AT25640B
AT25640B@S0IC8 [SA602A]
AT25DF021(OTP)@S0IC8 [SA602A]
AT25DF021@S0IC8 [SA602A]
AT25DF041A@MLF8 [SA683]
AT25DF041A@S0IC8(5.4) [SA023A]
AT25DF081@UDFN8 [SA683]

AT25DF161@MLF8 [SA683]
AT25DF161@S0IC8(5.4) [SA023A]
AT25DF321@S0IC8 [SA023A]
AT25DF321A(OTP)@S0IC8 [SA023A]
AT25DF641(OTP)@S0IC16 [SA404]
AT25F1024
AT25F1024(W)@VQFPN8 [SA684]
AT25F1024@VQFPN8 [SA683]
AT25F1024A(W)@S0IC8 [SA605B]
AT25F1024A@S0IC8 [SA602A]
AT25F2048
AT25F2048(W)@VQFPN8 [SA684]
AT25F2048@VQFPN8 [SA683]
AT25F2048A(W)@S0IC8 [SA605B]
AT25F2048A@S0IC8 [SA602A]
AT25F4096
AT25F4096(W)@VQFPN8 [SA684]
AT25F4096@VQFPN8 [SA683]
AT25F4096A(W)@S0IC8 [SA605B]
AT25F4096A@S0IC8 [SA602A]
AT25F512
AT25F512(W)@VQFPN8 [SA684]
AT25F512@VQFPN8 [SA683]
AT25F512A(W)@S0IC8 [SA605B]
AT25F512A@S0IC8 [SA602A]
AT25F512B@S0IC8 [SA602A]

AT25F512B@UDFN8 [SA724]
AT25FS010@S0IC8 [SA602A]
AT25FS040@S0IC8 [SA602A]
AT25HP256(W)@VQFPN8 [SA684]
AT25HP256@S0IC8 [SA602A]
AT25HP512
AT25HP512@S0IC16 [SA404]
AT25HP512@VQFPN8 [SA683]
AT25P1024@VQFPN8 [SA684]
AT26DF081@S0IC8(5.4) [SA023A]
AT26DF081A@S0IC8(5.4) [SA023A]
AT26DF161@S0IC8 [SA023A]
AT26DF161A@S0IC8 [SA023A]
AT26DF321@MLF8(6*8mm) [SA684]
AT26DF321@S0IC8 [SA023A]
AT26F004@S0IC8(4.0) [SA602A]
AT27011
AT27256
AT27BV010
AT27BV010@TSOP32 [SA410T-B4001]
AT27BV020
AT27BV020@TSOP32 [SA410T-B4001]
AT27BV040
AT27BV040@TSOP32 [SA410T-B4001]
AT27BV1024@PLCC44 [SA244]
AT27BV256
AT27BV256@TSOP28 [SA430T-B4003]
AT27BV400@PSOP44 [SA638]
AT27BV4096
AT27BV4096@VSOP40 [SA623-B4002]
AT27BV512@PLCC32 [SA015A1T]
AT27BV512@TSOP28 [SA430T-B4003]
AT27C010@PLCC32 [SA015A1T]
AT27C010L
AT27C010L@TSOP32 [SA410T-B4001]
AT27C020@PLCC32 [SA015A1T]
AT27C040
AT27C040@TSOP32 [SA410T-B4001]
AT27C080@PLCC32 [SA015A1T]
AT27C1024
AT27C1024@VSOP40 [SA623-B4002]
AT27C1024L@PLCC44 [SA244]
AT27C128@PLCC32 [SA015A1T]
AT27C2048@PLCC44 [SA244]
AT27C256
AT27C256R
AT27C256R@S0IC28 [SA630]
AT27C4096
AT27C4096@VSOP40 [SA623-B4002]
AT27C512@PLCC32 [SA015A1T]
AT27C512R@PLCC32 [SA015A1T]
AT27C512R@TSOP28 [SA430T-B4003]
AT27C513@PLCC32 [SA015A1T]
AT27C513R@PLCC32 [SA015A1T]
AT27C515
AT27C516
AT27C516@VSOP40 [SA623-B4002]
AT27C800
AT27C800@PSOP44 [SA638]

AT25FS010@SAP8 [SA683]
AT25FS040@SAP8 [SA683]
AT25HP256
AT25HP256@S0IC16 [SA404]
AT25HP256@VQFPN8 [SA683]
AT25HP512(W)@VQFPN8 [SA684]
AT25HP512@S0IC8 [SA602A]
AT25P1024@S0IC20 [SA404]
AT26DF081@S0IC8(4.0) [SA602A]
AT26DF081A@S0IC8(4.0) [SA602A]
AT26DF161@MLF8 [SA683]
AT26DF161A@MLF8 [SA683]
AT26DF321@MLF8(5*6mm) [SA683]
AT26DF321@S0IC16 [SA404]
AT26F004@MLF8 [SA683]
AT26F004@S0IC8(5.4) [SA023A]
AT27011@PLCC32 [SA015A1T]
AT2732A
AT27BV010@PLCC32 [SA015A1T]
AT27BV010@VSOP32 [SA620-B4807]
AT27BV020@PLCC32 [SA015A1T]
AT27BV020@VSOP32 [SA620-B4807]
AT27BV040@PLCC32 [SA015A1T]
AT27BV040@VSOP32 [SA620-B4807]
AT27BV1024@VSOP40 [SA623-B4002]
AT27BV256@PLCC32 [SA015A1T]
AT27BV400@PLCC44 [SA244]
AT27BV400@TSOP48 [SB247-B4806]
AT27BV4096@PLCC44 [SA244]
AT27BV512
AT27BV512@S0IC28 [SA404]
AT27C010
AT27C010@TSOP32 [SA410T-B4001]
AT27C010L@PLCC32 [SA015A1T]
AT27C020
AT27C020@TSOP32 [SA410T-B4001]
AT27C040@PLCC32 [SA015A1T]
AT27C080
AT27C080@TSOP32 [SA410T-B4001]
AT27C1024@PLCC44 [SA244]
AT27C1024L
AT27C128
AT27C2048
AT27C2048@VSOP40 [SA623-B4002]
AT27C256@PLCC32 [SA015A1T]
AT27C256R@PLCC32 [SA015A1T]
AT27C256R@TSOP28 [SA430T-B4003]
AT27C4096@PLCC44 [SA244]
AT27C512
AT27C512R
AT27C512R@S0IC28 [SA404]
AT27C513
AT27C513@S0IC28 [SA404]
AT27C513R@S0IC28 [SA404]
AT27C515@PLCC32 [SA015A1T]
AT27C516@PLCC44 [SA244]
AT27C64
AT27C800@PLCC44 [SA244]
AT27C800@TSOP48 [SB247-B4806]

AT27HC1024
AT27HC256
AT27HC256L
AT27HC256R
AT27HC256RL
AT27HC64
AT27HC641
AT27HC641R
AT27HC642
AT27HC642R
AT27HC64L
AT27LV010
AT27LV010@TSOP32 [SA410T-B4001]
AT27LV010A
AT27LV010A@TSOP32 [SA410T-B4001]
AT27LV020A
AT27LV020A@TSOP32 [SA410T-B4001]
AT27LV040
AT27LV040@TSOP32 [SA410T-B4001]
AT27LV040A
AT27LV040A@TSOP32 [SA410T-B4001]
AT27LV1024
AT27LV1026@PLCC44 [SA244]
AT27LV256A
AT27LV256A@S0IC28 [SA630]
AT27LV256R
AT27LV256R@S0IC28 [SA630]
AT27LV4096
AT27LV512A
AT27LV512A@S0IC28 [SA404]
AT27LV512R
AT27LV512R@TSOP28 [SA430T-B4003]
AT27LV800@PSOP44 [SA638]
AT27RW1024@TSOP40 [SA623-B4002]
AT28BV16@PLCC32 [SA015A1T]
AT28BV16@TSOP28 [SA430TA-B4003]
AT28BV256@PLCC32 [SA015A1T]
AT28BV256@TSOP28 [SA430T-B4003]
AT28BV64@PLCC32 [SA015A1T]
AT28BV64@TSOP28 [SA430T-B4003]
AT28BV64B@PLCC32 [SA015A1T]
AT28BV64B@TSOP28 [SA430T-B4003]
AT28C010@PLCC32 [SA015A1T]
AT28C010@TSOP32 [SA410T-B4001]
AT28C010E@PLCC32 [SA015A1T]
AT28C010E@TSOP32 [SA410T-B4001]
AT28C04@PLCC32 [SA015A1T]
AT28C040@PLCC32 [SA015A1T]
AT28C040@TSOP48 [SB247-B4806]
AT28C04E@PLCC32 [SA015A1T]
AT28C04F@PLCC32 [SA015A1T]
AT28C16@PLCC32 [SA015A1T]
AT28C16@TSOP28 [SA430TA-B4003]
AT28C16E@PLCC32 [SA015A1T]
AT28C16F@PLCC32 [SA015A1T]
AT28C17@PLCC32 [SA015A1T]
AT28C17E
AT28C17F
AT28C256

AT27HC1024@PLCC44 [SA244]
AT27HC256@PLCC32 [SA015A1T]
AT27HC256L@PLCC32 [SA015A1T]
AT27HC256R@PLCC32 [SA015A1T]
AT27HC256RL@PLCC32 [SA015A1T]
AT27HC64@PLCC32 [SA015A1T]
AT27HC641@PLCC28 [SA008A]
AT27HC641R@PLCC28 [SA008A]
AT27HC642@PLCC28 [SA008A]
AT27HC642R@PLCC28 [SA008A]
AT27HC64L@PLCC32 [SA015A1T]
AT27LV010@PLCC32 [SA015A1T]
AT27LV010@VSOP32 [SA620-B4807]
AT27LV010A@PLCC32 [SA015A1T]
AT27LV010A@VSOP32 [SA620-B4807]
AT27LV020A@PLCC32 [SA015A1T]
AT27LV020A@VSOP32 [SA620-B4807]
AT27LV040@PLCC32 [SA015A1T]
AT27LV040@VSOP32 [SA620-B4807]
AT27LV040A@PLCC32 [SA015A1T]
AT27LV040A@VSOP32 [SA620-B4807]
AT27LV1024@PLCC44 [SA244]
AT27LV1026@TSOP40 [SA623-B4002]
AT27LV256A@PLCC32 [SA015A1T]
AT27LV256A@TSOP28 [SA430T-B4003]
AT27LV256R@PLCC32 [SA015A1T]
AT27LV256R@TSOP28 [SA430T-B4003]
AT27LV4096@PLCC44 [SA244]
AT27LV512A@PLCC32 [SA015A1T]
AT27LV512A@TSOP28 [SA430T-B4003]
AT27LV512R@PLCC32 [SA015A1T]
AT27LV800
AT27RW1024@PLCC44 [SA244]
AT28BV16
AT28BV16@S0IC24 [SA404]
AT28BV256
AT28BV256@S0IC28 [SA404]
AT28BV64
AT28BV64@S0IC28 [SA404]
AT28BV64B
AT28BV64B@S0IC28 [SA404]
AT28C010
AT28C010@PLCC44 [SA244]
AT28C010E
AT28C010E@PLCC44 [SA244]
AT28C04
AT28C040
AT28C040@PLCC44 [SA244]
AT28C04E
AT28C04F
AT28C16
AT28C16@S0IC24 [SA404]
AT28C16E
AT28C16F
AT28C17
AT28C17@S0IC28 [SA404]
AT28C17E@PLCC32 [SA015A1T]
AT28C17F@PLCC32 [SA015A1T]
AT28C256@PLCC32 [SA015A1T]

AT28C256@S0IC28 [SA404]
AT28C256E
AT28C256E@S0IC28 [SA404]
AT28C256F
AT28C64
AT28C64@S0IC28 [SA404]
AT28C64B
AT28C64B@S0IC28 [SA404]
AT28C64E
AT28C64E@TSOP28 [SA430T-B4003]
AT28C64F@PLCC32 [SA015A1T]
AT28C64X
AT28C64X@S0IC28 [SA404]
AT28HC04
AT28HC16
AT28HC191
AT28HC256
AT28HC256@TSOP28 [SA430T-B4003]
AT28HC256E@PLCC32 [SA015A1T]
AT28HC256F@PLCC32 [SA015A1T]
AT28HC256L@PLCC32 [SA015A1T]
AT28HC256LE@PLCC32 [SA015A1T]
AT28HC291@PLCC28 [SA008A]
AT28HC291L@PLCC28 [SA008A]
AT28HC64@PLCC32 [SA015A1T]
AT28HC64B
AT28HC64B@S0IC28 [SA404]
AT28HC64BF
AT28HC64BF@S0IC28 [SA404]
AT28HC64L
AT28HC64L@TSOP28 [SA430T-B4003]
AT28LV010@PLCC32 [SA015A1T]
AT28LV256
AT28LV256@TSOP28 [SA430T-B4003]
AT28LV64@PLCC32 [SA015A1T]
AT28LV64B@PLCC32 [SA015A1T]
AT28LV64B@TSOP28 [SA430T-B4003]
AT28MC010@PLCC32 [SA015A1T]
AT28MC010@TSOP32 [SA410T-B4001]
AT28MC020@PLCC32 [SA015A1T]
AT28MC020@TSOP32 [SA410T-B4001]
AT28MC040@PLCC32 [SA015A1T]
AT28MC040@TSOP32 [SA410T-B4001]
AT28PC64@PLCC32 [SA015A1T]
AT28PC64E
AT28PC64E@TSOP28 [SA430T-B4003]
AT29BV010A@TSOP32 [SA410T-B4001]
AT29BV020@TSOP32 [SA410T-B4001]
AT29C010
AT29C010@TSOP32 [SA410T-B4001]
AT29C010A@PLCC32 [SA015A1T]
AT29C020
AT29C020@TSOP32 [SA410T-B4001]
AT29C040@PLCC32 [SA015A1T]
AT29C040A
AT29C040A@TSOP32 [SA410T-B4001]
AT29C1024@TSOP48 [SB247-B4806]
AT29C256@PLCC32 [SA015A1T]
AT29C257

AT28C256@TSOP28 [SA430T-B4003]
AT28C256E@PLCC32 [SA015A1T]
AT28C256E@TSOP28 [SA430T-B4003]
AT28C256F@PLCC32 [SA015A1T]
AT28C64@PLCC32 [SA015A1T]
AT28C64@TSOP28 [SA430T-B4003]
AT28C64B@PLCC32 [SA015A1T]
AT28C64B@TSOP28 [SA430T-B4003]
AT28C64E@PLCC32 [SA015A1T]
AT28C64F
AT28C64F@TSOP28 [SA430T-B4003]
AT28C64X@PLCC32 [SA015A1T]
AT28C64X@TSOP28 [SA430T-B4003]
AT28HC04@PLCC32 [SA015A1T]
AT28HC16L
AT28HC191L
AT28HC256@PLCC32 [SA015A1T]
AT28HC256E
AT28HC256F
AT28HC256L
AT28HC256LE
AT28HC291
AT28HC291L
AT28HC64
AT28HC64@TSOP28 [SA430T-B4003]
AT28HC64B@PLCC32 [SA015A1T]
AT28HC64B@TSOP28 [SA430T-B4003]
AT28HC64BF@PLCC32 [SA015A1T]
AT28HC64BF@TSOP28 [SA430T-B4003]
AT28HC64L@PLCC32 [SA015A1T]
AT28LV010
AT28LV010@TSOP32 [SA410T-B4001]
AT28LV256@PLCC32 [SA015A1T]
AT28LV64
AT28LV64B
AT28LV64B@S0IC28 [SA404]
AT28MC010
AT28MC010@PLCC44 [SA244]
AT28MC020
AT28MC020@PLCC44 [SA244]
AT28MC040
AT28MC040@PLCC44 [SA244]
AT28PC64
AT28PC64@TSOP28 [SA430T-B4003]
AT28PC64E@PLCC32 [SA015A1T]
AT29BV010A@PLCC32 [SA015A1T]
AT29BV020@PLCC32 [SA015A1T]
AT29BV040A@TSOP32 [SA410T-B4001]
AT29C010@PLCC32 [SA015A1T]
AT29C010A
AT29C010A@TSOP32 [SA410T-B4001]
AT29C020@PLCC32 [SA015A1T]
AT29C040
AT29C040@TSOP32 [SA410T-B4001]
AT29C040A@PLCC32 [SA015A1T]
AT29C1024@PLCC44 [SA244]
AT29C256
AT29C256@TSOP28 [SA430T-B4003]
AT29C257@PLCC32 [SA015A1T]

AT29C512
AT29C512@TSOP32 [SA410T-B4001]
AT29LV010@PLCC32 [SA015A1T]
AT29LV010A@PLCC32 [SA015A1T]
AT29LV020
AT29LV020@TSOP32 [SA410T-B4001]
AT29LV040A@PLCC32 [SA015A1T]
AT29LV1024@PLCC44 [SA244]
AT29LV256
AT29LV256@TSOP28 [SA430T-B4003]
AT29LV512@PLCC32 [SA015A1T]
AT32C16
AT34C02
AT34C02@TSSOP8 [SA026-B3201]
AT34C02B@S0IC8 [SA602A]
AT34C02C
AT34C02C@S0IC8 [SA602A]
AT45D011@PLCC32 [SA015A1T]
AT45D011@TSSOP14 [SA026-B3201]
AT45D021@S0IC28 [SA630]
AT45D041@PLCC32 [SA015A1T]
AT45D041@TSOP28 [SA430T-B4003]
AT45D081@TSOP32 [SA410T-B4001]
AT45D161@S0IC28 [SA630]
AT45DB011@PLCC32 [SA015A1T]
AT45DB011@TSSOP14 [SA026-B3201]
AT45DB011B@S0IC8 [SA023A]
AT45DB021@PLCC32 [SA015A1T]
AT45DB021@TSOP28 [SA430T-B4003]
AT45DB021A@S0IC28 [SA630]
AT45DB021B@S0IC28 [SA630]
AT45DB021B@TSOP28 [SA430T-B4003]
AT45DB041@S0IC28 [SA630]
AT45DB041A@PLCC32 [SA015A1T]
AT45DB041A@TSOP28 [SA430T-B4003]
AT45DB041B@S0IC28 [SA630]
AT45DB041B@TSOP28 [SA430T-B4003]
AT45DB081@TSOP32 [SA410T-B4001]
AT45DB081A@S0IC28 [SA630]
AT45DB081B@CASON8 [SA684]
AT45DB081B@S0IC8 [SA023A]
AT45DB161@PLCC32 [SA015A1T]
AT45DB161@TSOP28 [SA430T-B4003]
AT45DB161B@S0IC28 [SA630]
AT45DB321@TSOP32 [SA410T-B4001]
AT45DB321B@TSOP32 [SA410T-B4001]
AT45DB321C@S0IC28 [SA630]
AT45DB642@TSOP40 [SA409T-B4002]
AT45DB642D@TSOP28 [SA430T-B4003]
AT49BV001@PLCC32 [SA015A1T]
AT49BV001@VSOP32 [SA620-B4807]
AT49BV001A@PLCC32 [SA015A1T]
AT49BV001A@VSOP32 [SA620-B4807]
AT49BV001AN@PLCC32 [SA015A1T]
AT49BV001AN@TSOP32 [SA410T-B4001]
AT49BV001AN@VSOP32 [SA620-B4807]
AT49BV001ANT@PLCC32 [SA015A1T]
AT49BV001ANT@TSOP32 [SA410T-B4001]
AT49BV001ANT@VSOP32 [SA620-B4807]

AT29C512@PLCC32 [SA015A1T]
AT29LV010
AT29LV010@TSOP32 [SA410T-B4001]
AT29LV010A@TSOP32 [SA410T-B4001]
AT29LV020@PLCC32 [SA015A1T]
AT29LV040A
AT29LV040A@TSOP32 [SA410T-B4001]
AT29LV1024@TSOP48 [SB247-B4806]
AT29LV256@PLCC32 [SA015A1T]
AT29LV512
AT29LV512@TSOP32 [SA410T-B4001]
AT32C16@PLCC44
AT34C02@S0IC8 [SA602A]
AT34C02B
AT34C02B@TSSOP8 [SA026-B3201]
AT34C02C@MAP8 [SA724]
AT34C02C@TSSOP8 [SA026-B3201]
AT45D011@S0IC8 [SA023A]
AT45D021@PLCC32 [SA015A1T]
AT45D021@TSOP28 [SA430T-B4003]
AT45D041@S0IC28 [SA630]
AT45D081@S0IC28 [SA630]
AT45D161@PLCC32 [SA015A1T]
AT45D161@TSOP28 [SA430T-B4003]
AT45DB011@S0IC8 [SA023A]
AT45DB011B@PLCC32 [SA015A1T]
AT45DB011B@TSSOP14 [SA026-B3201]
AT45DB021@S0IC28 [SA630]
AT45DB021A@PLCC32 [SA015A1T]
AT45DB021A@TSOP28 [SA430T-B4003]
AT45DB021B@S0IC8 [SA023A]
AT45DB041@PLCC32 [SA015A1T]
AT45DB041@TSOP28 [SA430T-B4003]
AT45DB041A@S0IC28 [SA630]
AT45DB041B@CASON8 [SA684]
AT45DB041B@S0IC8 [SA023A]
AT45DB081@S0IC28 [SA630]
AT45DB081A@PLCC32 [SA015A1T]
AT45DB081A@TSOP28 [SA430T-B4003]
AT45DB081B@S0IC28 [SA630]
AT45DB081B@TSOP28 [SA430T-B4003]
AT45DB161@S0IC28 [SA630]
AT45DB161B@CASON8 [SA684]
AT45DB161B@TSOP28 [SA430T-B4003]
AT45DB321B@S0IC28 [SA630]
AT45DB321C@CASON8 [SA684]
AT45DB321C@TSOP28 [SA430T-B4003]
AT45DB642D@CASON8 [SA684]
AT49BV001
AT49BV001@TSOP32 [SA410T-B4001]
AT49BV001A
AT49BV001A@TSOP32 [SA410T-B4001]
AT49BV001AN

AT49BV001ANT

AT49BV001AT
AT49BV001AT@TSOP32 [SA410T-B4001]
AT49BV001AT@VSOP32 [SA620-B4807]
AT49BV001N@PLCC32 [SA015A1T]
AT49BV001N@VSOP32 [SA620-B4807]
AT49BV001NT@PLCC32 [SA015A1T]
AT49BV001NT@TSOP32 [SA410T-B4001]
AT49BV001NT@VSOP32 [SA620-B4807]
AT49BV001T@PLCC32 [SA015A1T]
AT49BV001T@VSOP32 [SA620-B4807]
AT49BV002@PLCC32 [SA015A1T]
AT49BV002@VSOP32 [SA620-B4807]
AT49BV002A@PLCC32 [SA015A1T]
AT49BV002A@VSOP32 [SA620-B4807]
AT49BV002AN@PLCC32 [SA015A1T]
AT49BV002AN@TSOP32 [SA410T-B4001]
AT49BV002AN@VSOP32 [SA620-B4807]
AT49BV002ANT@PLCC32 [SA015A1T]
AT49BV002ANT@TSOP32 [SA410T-B4001]
AT49BV002ANT@VSOP32 [SA620-B4807]
AT49BV002AT
AT49BV002AT@TSOP32 [SA410T-B4001]
AT49BV002AT@VSOP32 [SA620-B4807]
AT49BV002N@PLCC32 [SA015A1T]
AT49BV002N@VSOP32 [SA620-B4807]
AT49BV002NT@PLCC32 [SA015A1T]
AT49BV002NT@TSOP32 [SA410T-B4001]
AT49BV002NT@VSOP32 [SA620-B4807]
AT49BV002T@PLCC32 [SA015A1T]
AT49BV002T@VSOP32 [SA620-B4807]
AT49BV008A@TSOP40 [SA409T-B4002]
AT49BV008AT@TSOP40 [SA409T-B4002]
AT49BV010
AT49BV010@TSOP32 [SA410T-B4001]
AT49BV020
AT49BV020@TSOP32 [SA410T-B4001]
AT49BV040
AT49BV040@TSOP32 [SA410T-B4001]
AT49BV040A@PLCC32 [SA015A1T]
AT49BV040A@VSOP32 [SA620-B4807]
AT49BV040B@TSOP32 [SA410T-B4001]
AT49BV040T
AT49BV040T@TSOP32 [SA410T-B4001]
AT49BV080@PSOP44 [SA638]
AT49BV080T@PSOP44 [SA638]
AT49BV1024A@TSOP40 [SA623-B4002]
AT49BV1604@TSOP48 [SB247-B4806]
AT49BV1604AT@TSOP48 [SB247-B4806]
AT49BV1604T@TSOP48 [SB247-B4806]
AT49BV160CT@TSOP48 [SB247-B4806]
AT49BV160DT@TSOP48 [SB247-B4806]
AT49BV161@TSOP48 [SB247-B4806]
AT49BV1614A@TSOP48 [SB247-B4806]
AT49BV1614AT@TSOP48 [SB247-B4806]
AT49BV1614T@TSOP48 [SB247-B4806]
AT49BV1618T@TSOP48 [SB247-B4806]
AT49BV162A@TSOP48 [SB247-B4806]
AT49BV163A@TSOP48 [SB247-B4806]
AT49BV163D@TSOP48 [SB247-B4806]

AT49BV001AT@PLCC32 [SA015A1T]

AT49BV001N
AT49BV001N@TSOP32 [SA410T-B4001]
AT49BV001NT

AT49BV001T
AT49BV001T@TSOP32 [SA410T-B4001]
AT49BV002
AT49BV002@TSOP32 [SA410T-B4001]
AT49BV002A
AT49BV002A@TSOP32 [SA410T-B4001]
AT49BV002AN

AT49BV002ANT

AT49BV002AT@PLCC32 [SA015A1T]

AT49BV002N
AT49BV002N@TSOP32 [SA410T-B4001]
AT49BV002NT

AT49BV002T
AT49BV002T@TSOP32 [SA410T-B4001]
AT49BV008@TSOP40 [SA409T-B4002]

AT49BV010@PLCC32 [SA015A1T]
AT49BV010@VSOP32 [SA620-B4807]
AT49BV020@PLCC32 [SA015A1T]
AT49BV020@VSOP32 [SA620-B4807]
AT49BV040@PLCC32 [SA015A1T]
AT49BV040@VSOP32 [SA620-B4807]
AT49BV040A@TSOP32 [SA410T-B4001]
AT49BV040B@PLCC32 [SA015A1T]
AT49BV040B@VSOP32 [SA620-B4807]
AT49BV040T@PLCC32 [SA015A1T]
AT49BV040T@VSOP32 [SA620-B4807]
AT49BV080@TSOP40 [SA409T-B4002]
AT49BV080T@TSOP40 [SA409T-B4002]
AT49BV160@TSOP48 [SB247-B4806]
AT49BV1604A@TSOP48 [SB247-B4806]

AT49BV160C@TSOP48 [SB247-B4806]
AT49BV160D@TSOP48 [SB247-B4806]
AT49BV160T@TSOP48 [SB247-B4806]
AT49BV1614@TSOP48 [SB247-B4806]

AT49BV1618@TSOP48 [SB247-B4806]
AT49BV161T@TSOP48 [SB247-B4806]
AT49BV162AT@TSOP48 [SB247-B4806]
AT49BV163AT@TSOP48 [SB247-B4806]
AT49BV163DT@TSOP48 [SB247-B4806]

AT49BV2048@PSOP44 [SA638]
AT49BV2048A@PSOP44 [SA638]
AT49BV2048B@TSOP48 [SB247-B4806]
AT49BV320A@TSOP48 [SB247-B4806]
AT49BV320C@TSOP48 [SB247-B4806]
AT49BV320D@TSOP48 [SB247-B4806]
AT49BV320T@TSOP48 [SB247-B4806]
AT49BV3214T@TSOP48 [SB247-B4806]
AT49BV3218T@TSOP48 [SB247-B4806]
AT49BV322A@TSOP48 [SB247-B4806]
AT49BV322D@TSOP48 [SB247-B4806]
AT49BV4096@PSOP44 [SA638]
AT49BV4096A@PSOP44 [SA638]
AT49BV512
AT49BV512@TSOP32 [SA410T-B4001]
AT49BV6416@TSOP48 [SB247-B4806]
AT49BV642D@TSOP48 [SB247-B4806]
AT49BV8004@TSOP48 [SB247-B4806]
AT49BV8011@TSOP48 [SB247-B4806]
AT49BV802A@TSOP48 [SB247-B4806]
AT49BV802D@TSOP48 [SB247-B4806]
AT49BV8192@PSOP44 [SA638]
AT49BV8192A@PSOP44 [SA638]
AT49BV8192AT@PSOP44 [SA638]
AT49BV8192AT@TSOP48 [SB247-B4806]
AT49BV8192T@PSOP44 [SA638]
AT49F001
AT49F001@TSOP32 [SA410T-B4001]
AT49F001A
AT49F001A@TSOP32 [SA410T-B4001]
AT49F001AN
AT49F001AN@TSOP32 [SA410T-B4001]
AT49F001ANT
AT49F001ANT@TSOP32 [SA410T-B4001]
AT49F001ANT@VSOP32 [SA620-B4807]
AT49F001AT@PLCC32 [SA015A1T]
AT49F001AT@VSOP32 [SA620-B4807]
AT49F001N@PLCC32 [SA015A1T]
AT49F001N@VSOP32 [SA620-B4807]
AT49F001NT@PLCC32 [SA015A1T]
AT49F001NT@VSOP32 [SA620-B4807]
AT49F001T@PLCC32 [SA015A1T]
AT49F001T@VSOP32 [SA620-B4807]
AT49F002@PLCC32 [SA015A1T]
AT49F002@VSOP32 [SA620-B4807]
AT49F002A@PLCC32 [SA015A1T]
AT49F002A@VSOP32 [SA620-B4807]
AT49F002AN@PLCC32 [SA015A1T]
AT49F002AN@VSOP32 [SA620-B4807]
AT49F002ANT@PLCC32 [SA015A1T]
AT49F002ANT@TSOP32 [SA410T-B4001]
AT49F002ANT@VSOP32 [SA620-B4807]
AT49F002AT@PLCC32 [SA015A1T]
AT49F002AT@VSOP32 [SA620-B4807]
AT49F002N@PLCC32 [SA015A1T]
AT49F002N@VSOP32 [SA620-B4807]
AT49F002NT@PLCC32 [SA015A1T]
AT49F002NT@VSOP32 [SA620-B4807]
AT49F002T@PLCC32 [SA015A1T]

AT49BV2048@TSOP48 [SB247-B4806]
AT49BV2048A@TSOP48 [SB247-B4806]
AT49BV320@TSOP48 [SB247-B4806]
AT49BV320AT@TSOP48 [SB247-B4806]
AT49BV320CT@TSOP48 [SB247-B4806]
AT49BV320DT@TSOP48 [SB247-B4806]
AT49BV321@TSOP48 [SB247-B4806]
AT49BV3218@TSOP48 [SB247-B4806]
AT49BV321T@TSOP48 [SB247-B4806]
AT49BV322AT@TSOP48 [SB247-B4806]
AT49BV322DT@TSOP48 [SB247-B4806]
AT49BV4096@TSOP48 [SB247-B4806]
AT49BV4096A@TSOP48 [SB247-B4806]
AT49BV512@PLCC32 [SA015A1T]
AT49BV512@VSOP32 [SA620-B4807]
AT49BV6416T@TSOP48 [SB247-B4806]
AT49BV642DT@TSOP48 [SB247-B4806]
AT49BV8004T@TSOP48 [SB247-B4806]
AT49BV8011T@TSOP48 [SB247-B4806]
AT49BV802AT@TSOP48 [SB247-B4806]
AT49BV802DT@TSOP48 [SB247-B4806]
AT49BV8192@TSOP48 [SB247-B4806]
AT49BV8192A@TSOP48 [SB247-B4806]
AT49BV8192T@TSOP48 [SB247-B4806]
AT49F001@PLCC32 [SA015A1T]
AT49F001@VSOP32 [SA620-B4807]
AT49F001A@PLCC32 [SA015A1T]
AT49F001A@VSOP32 [SA620-B4807]
AT49F001AN@PLCC32 [SA015A1T]
AT49F001AN@VSOP32 [SA620-B4807]
AT49F001ANT@PLCC32 [SA015A1T]
AT49F001AT
AT49F001AT@TSOP32 [SA410T-B4001]
AT49F001N
AT49F001N@TSOP32 [SA410T-B4001]
AT49F001NT
AT49F001NT@TSOP32 [SA410T-B4001]
AT49F001T
AT49F001T@TSOP32 [SA410T-B4001]
AT49F002
AT49F002@TSOP32 [SA410T-B4001]
AT49F002A
AT49F002A@TSOP32 [SA410T-B4001]
AT49F002AN
AT49F002AN@TSOP32 [SA410T-B4001]
AT49F002ANT
AT49F002AT
AT49F002AT@TSOP32 [SA410T-B4001]
AT49F002N
AT49F002N@TSOP32 [SA410T-B4001]
AT49F002NT
AT49F002NT@TSOP32 [SA410T-B4001]
AT49F002T
AT49F002T@TSOP32 [SA410T-B4001]

AT49F002T@VSOP32 [SA620-B4807]
AT49F008A@TSOP40 [SA409T-B4002]
AT49F010
AT49F010@TSOP32 [SA410T-B4001]
AT49F020@PLCC32 [SA015A1T]
AT49F040
AT49F040@TSOP32 [SA410T-B4001]
AT49F040A@PLCC32 [SA015A1T]
AT49F040T
AT49F040T@TSOP32 [SA410T-B4001]
AT49F080@TSOP40 [SA409T-B4002]
AT49F080T@TSOP40 [SA409T-B4002]
AT49F1024A@TSOP40 [SA623-B4002]
AT49F1025@TSOP40 [SA623-B4002]
AT49F1604T@TSOP48 [SB247-B4806]
AT49F1614T@TSOP48 [SB247-B4806]
AT49F2048@TSOP48 [SB247-B4806]
AT49F2048A@TSOP48 [SB247-B4806]
AT49F4096@TSOP48 [SB247-B4806]
AT49F4096A@TSOP48 [SB247-B4806]
AT49F512@PLCC32 [SA015A1T]
AT49F512@VSOP32 [SA620-B4807]
AT49F516@TSOP40 [SA623-B4002]
AT49F8004T@TSOP48 [SB247-B4806]
AT49F8011T@TSOP48 [SB247-B4806]
AT49F8192@TSOP48 [SB247-B4806]
AT49F8192A@TSOP48 [SB247-B4806]
AT49F8192AT@TSOP48 [SB247-B4806]
AT49F8192T@TSOP48 [SB247-B4806]
AT49HBV010@PLCC32 [SA015A1T]
AT49HBV010@VSOP32 [SA620-B4807]
AT49HF010@PLCC32 [SA015A1T]
AT49HLV010
AT49HLV010@TSOP32 [SA410T-B4001]
AT49LH002@PLCC32 [SA015A1T]
AT49LH004@PLCC32 [SA015A1T]
AT49LH00B4@PLCC32 [SA015A1T]
AT49LL020@PLCC32 [SA015A1T]
AT49LL040@PLCC32 [SA015A1T]
AT49LL080@PLCC32 [SA015A1T]
AT49LV001
AT49LV001@TSOP32 [SA410T-B4001]
AT49LV001N
AT49LV001N@TSOP32 [SA410T-B4001]
AT49LV001NT
AT49LV001NT@TSOP32 [SA410T-B4001]
AT49LV001NT@VSOP32 [SA620-B4807]
AT49LV001T@PLCC32 [SA015A1T]
AT49LV001T@VSOP32 [SA620-B4807]
AT49LV002@PLCC32 [SA015A1T]
AT49LV002@VSOP32 [SA620-B4807]
AT49LV002N@PLCC32 [SA015A1T]
AT49LV002N@VSOP32 [SA620-B4807]
AT49LV002NT@PLCC32 [SA015A1T]
AT49LV002NT@TSOP32 [SA410T-B4001]
AT49LV002NT@VSOP32 [SA620-B4807]
AT49LV002T@PLCC32 [SA015A1T]
AT49LV002T@VSOP32 [SA620-B4807]
AT49LV008A@TSOP40 [SA409T-B4002]

AT49F008@TSOP40 [SA409T-B4002]
AT49F008AT@TSOP40 [SA409T-B4002]
AT49F010@PLCC32 [SA015A1T]
AT49F020
AT49F020@TSOP32 [SA410T-B4001]
AT49F040@PLCC32 [SA015A1T]
AT49F040A
AT49F040A@TSOP32 [SA410T-B4001]
AT49F040T@PLCC32 [SA015A1T]
AT49F080@PSOP44 [SA638]
AT49F080T@PSOP44 [SA638]
AT49F1024@TSOP40 [SA623-B4002]
AT49F1025@PLCC44 [SA244]
AT49F1604@TSOP48 [SB247-B4806]
AT49F1614@TSOP48 [SB247-B4806]
AT49F2048@PSOP44 [SA638]
AT49F2048A@PSOP44 [SA638]
AT49F4096@PSOP44 [SA638]
AT49F4096A@PSOP44 [SA638]
AT49F512
AT49F512@TSOP32 [SA410T-B4001]
AT49F516@PLCC44 [SA244]
AT49F8004@TSOP48 [SB247-B4806]
AT49F8011@TSOP48 [SB247-B4806]
AT49F8192@PSOP44 [SA638]
AT49F8192A@PSOP44 [SA638]
AT49F8192AT@PSOP44 [SA638]
AT49F8192T@PSOP44 [SA638]
AT49HBV010
AT49HBV010@TSOP32 [SA410T-B4001]
AT49HF010
AT49HF010@TSOP32 [SA410T-B4001]
AT49HLV010@PLCC32 [SA015A1T]
AT49HLV010@VSOP32 [SA620-B4807]
AT49LH002@TSOP40 [SA409T-B4002]
AT49LH004@TSOP40 [SA409T-B4002]
AT49LH00B4@TSOP40 [SA409T-B4002]
AT49LL020@TSOP40 [SA409T-B4002]
AT49LL040@TSOP40 [SA409T-B4002]
AT49LL080@TSOP40 [SA409T-B4002]
AT49LV001@PLCC32 [SA015A1T]
AT49LV001@VSOP32 [SA620-B4807]
AT49LV001N@PLCC32 [SA015A1T]
AT49LV001N@VSOP32 [SA620-B4807]
AT49LV001NT@PLCC32 [SA015A1T]

AT49LV001T
AT49LV001T@TSOP32 [SA410T-B4001]
AT49LV002
AT49LV002@TSOP32 [SA410T-B4001]
AT49LV002N
AT49LV002N@TSOP32 [SA410T-B4001]
AT49LV002NT

AT49LV002T
AT49LV002T@TSOP32 [SA410T-B4001]
AT49LV008@TSOP40 [SA409T-B4002]

AT49LV008AT@TSOP40 [SA409T-B4002]	
AT49LV010	AT49LV010@PLCC32 [SA015A1T]
AT49LV010@TSOP32 [SA410T-B4001]	AT49LV010@VSOP32 [SA620-B4807]
AT49LV020	AT49LV020@PLCC32 [SA015A1T]
AT49LV020@TSOP32 [SA410T-B4001]	AT49LV020@VSOP32 [SA620-B4807]
AT49LV040	AT49LV040@PLCC32 [SA015A1T]
AT49LV040@TSOP32 [SA410T-B4001]	AT49LV040@VSOP32 [SA620-B4807]
AT49LV040T	AT49LV040T@PLCC32 [SA015A1T]
AT49LV040T@TSOP32 [SA410T-B4001]	AT49LV040T@VSOP32 [SA620-B4807]
AT49LV080@PSOP44 [SA638]	AT49LV080@TSOP40 [SA409T-B4002]
AT49LV080T@PSOP44 [SA638]	AT49LV080T@TSOP40 [SA409T-B4002]
AT49LV1024@TSOP40 [SA623-B4002]	AT49LV1024A@TSOP40 [SA623-B4002]
AT49LV1025@PLCC44 [SA244]	AT49LV160@TSOP48 [SB247-B4806]
AT49LV1604@TSOP48 [SB247-B4806]	AT49LV1604T@TSOP48 [SB247-B4806]
AT49LV160T@TSOP48 [SB247-B4806]	AT49LV161@TSOP48 [SB247-B4806]
AT49LV1614@TSOP48 [SB247-B4806]	AT49LV1614A@TSOP48 [SB247-B4806]
AT49LV1614AT@TSOP48 [SB247-B4806]	
AT49LV1614T@TSOP48 [SB247-B4806]	AT49LV161T@TSOP48 [SB247-B4806]
AT49LV2048@PSOP44 [SA638]	AT49LV2048@TSOP48 [SB247-B4806]
AT49LV2048A@PSOP44 [SA638]	AT49LV2048A@TSOP48 [SB247-B4806]
AT49LV2048B@TSOP48 [SB247-B4806]	AT49LV320@TSOP48 [SB247-B4806]
AT49LV320T@TSOP48 [SB247-B4806]	AT49LV321@TSOP48 [SB247-B4806]
AT49LV3218@TSOP48 [SB247-B4806]	AT49LV3218T@TSOP48 [SB247-B4806]
AT49LV321T@TSOP48 [SB247-B4806]	AT49LV4096A@PSOP44 [SA638]
AT49LV4096A@TSOP48 [SB247-B4806]	AT49LV8011@TSOP48 [SB247-B4806]
AT49LV8011T@TSOP48 [SB247-B4806]	AT49LV8192@PSOP44 [SA638]
AT49LV8192@TSOP48 [SB247-B4806]	AT49LV8192A@PSOP44 [SA638]
AT49LV8192A@TSOP48 [SB247-B4806]	AT49LV8192AT@PSOP44 [SA638]
AT49LV8192AT@TSOP48 [SB247-B4806]	
AT49LV8192T@PSOP44 [SA638]	AT49LV8192T@TSOP48 [SB247-B4806]
AT49LW040@PLCC32 [SA015A1T]	AT49LW040@TSOP40 [SA409T-B4002]
AT49LW080@PLCC32 [SA015A1T]	AT49LW080@TSOP40 [SA409T-B4002]
AT49SV163D@TSOP48 [SB247-B4806]	AT49SV163DT@TSOP48 [SB247-B4806]
AT49SV322A@TSOP48 [SB247-B4806]	AT49SV322AT@TSOP48 [SB247-B4806]
AT49SV322D@TSOP48 [SB247-B4806]	AT49SV322DT@TSOP48 [SB247-B4806]
AT49SV802A@TSOP48 [SB247-B4806]	AT49SV802AT@TSOP48 [SB247-B4806]
AT93C46(08bit)	AT93C46(08bit)@S0IC8 [SA602A]
AT93C46(08bit)@TSSOP8 [SA026-B3201]	
AT93C46(16bit)	AT93C46(16bit)@S0IC8 [SA602A]
AT93C46(16bit)@TSSOP8 [SA026-B3201]	
AT93C46A	AT93C46A@S0IC8 [SA602A]
AT93C46A@TSSOP8 [SA026-B3201]	AT93C46C
AT93C46C@S0IC8 [SA602A]	AT93C46C@TSSOP8 [SA026-B3201]
AT93C46D(08bit)	AT93C46D(08bit)@MAP8 [SA724]
AT93C46D(08bit)@S0IC8 [SA602A]	
AT93C46D(08bit)@TSSOP8 [SA026-B3201]	
AT93C46D(16bit)	AT93C46D(16bit)@MAP8 [SA724]
AT93C46D(16bit)@S0IC8 [SA602A]	
AT93C46D(16bit)@TSSOP8 [SA026-B3201]	
AT93C46E	AT93C46E@S0IC8 [SA602A]
AT93C46E@TSSOP8 [SA026-B3201]	AT93C56(08bit)
AT93C56(08bit)@S0IC8 [SA602A]	AT93C56(16bit)
AT93C56(16bit)@S0IC8 [SA602A]	AT93C56A(08bit)
AT93C56A(08bit)@S0IC8 [SA602A]	
AT93C56A(08bit)@TSSOP8 [SA026-B3201]	
AT93C56A(16bit)	AT93C56A(16bit)@S0IC8 [SA602A]
AT93C56A(16bit)@TSSOP8 [SA026-B3201]	
AT93C57	AT93C57@S0IC8 [SA602A]
AT93C66(08bit)	AT93C66(08bit)@S0IC8 [SA602A]

AT93C66(16bit)	AT93C66(16bit)@S0IC8 [SA602A]
AT93C66A(08bit)	AT93C66A(08bit)@S0IC8 [SA602A]
AT93C66A(08bit)@TSSOP8 [SA026-B3201]	
AT93C66A(16bit)	AT93C66A(16bit)@S0IC8 [SA602A]
AT93C66A(16bit)@TSSOP8 [SA026-B3201]	
AT93C86(08bit)	AT93C86(08bit)@S0IC8 [SA602A]
AT93C86(08bit)@TSSOP8 [SA026-B3201]	
AT93C86(16bit)	AT93C86(16bit)@S0IC8 [SA602A]
AT93C86(16bit)@TSSOP8 [SA026-B3201]	
AT93C86A(08bit)	AT93C86A(08bit)@S0IC8 [SA602A]
AT93C86A(08bit)@TSSOP8 [SA026-B3201]	
AT93C86A(16bit)	AT93C86A(16bit)@S0IC8 [SA602A]
AT93C86A(16bit)@TSSOP8 [SA026-B3201]	

PLD

ATF16LV8C	ATF16LV8C@PLCC20 [SA001A-B2001]
ATF16LV8C@S0IC20 [SA404]	ATF16LV8C@TSOP20 [SA026-B3201]
ATF16LV8CEXT	
ATF16LV8CEXT@PLCC20 [SA001A-B2001]	
ATF16LV8CEXT@S0IC20 [SA404]	
ATF16LV8CEXT@TSOP20 [SA026-B3201]	
ATF16V8B	ATF16V8B@PLCC20 [SA001A-B2001]
ATF16V8B@S0IC20 [SA404]	ATF16V8B@TSOP20 [SA026-B3201]
ATF16V8BL	ATF16V8BL@PLCC20 [SA001A-B2001]
ATF16V8BL@S0IC20 [SA404]	ATF16V8BL@TSOP20 [SA026-B3201]
ATF16V8BQ	ATF16V8BQ@PLCC20 [SA001A-B2001]
ATF16V8BQ@S0IC20 [SA404]	ATF16V8BQ@TSOP20 [SA026-B3201]
ATF16V8BQL	ATF16V8BQL@PLCC20 [SA001A-B2001]
ATF16V8BQL@S0IC20 [SA404]	ATF16V8BQL@TSOP20 [SA026-B3201]
ATF16V8C	ATF16V8C@PLCC20 [SA001A-B2001]
ATF16V8C@S0IC20 [SA404]	ATF16V8C@TSOP20 [SA026-B3201]
ATF16V8CEXT	
ATF16V8CEXT@PLCC20 [SA001A-B2001]	
ATF16V8CEXT@S0IC20 [SA404]	ATF16V8CEXT@TSOP20 [SA026-B3201]
ATF16V8CZ	ATF16V8CZ@PLCC20 [SA001A-B2001]
ATF16V8CZ@S0IC20 [SA404]	ATF16V8CZ@TSOP20 [SA026-B3201]
ATF20V8B	ATF20V8B@PLCC28 [SA008A]
ATF20V8B@S0IC24 [SA620-B4807]	ATF20V8BL
ATF20V8BL@PLCC28 [SA008A]	ATF20V8BL@S0IC24 [SA620-B4807]
ATF20V8BQ	ATF20V8BQ@PLCC28 [SA008A]
ATF20V8BQ@S0IC24 [SA620-B4807]	ATF20V8BQL
ATF20V8BQL@PLCC28 [SA008A]	ATF20V8BQL@S0IC24 [SA620-B4807]
ATF22LV10C	ATF22LV10C(UES)
ATF22LV10C(UES)@PLCC28 [SA008A]	ATF22LV10C(UES)@S0IC24 [SA404]
ATF22LV10C(UES)@TSSOP24 [SA026-B3201]	
ATF22LV10C@PLCC28 [SA008A]	ATF22LV10C@S0IC24 [SA404]
ATF22LV10C@TSSOP24 [SA026-B3201]	ATF22LV10CEXT
ATF22LV10CEXT@PLCC28 [SA008A]	ATF22LV10CEXT@S0IC24 [SA404]
ATF22LV10CEXT@TSSOP24 [SA026-B3201]	
ATF22LV10CQ	ATF22LV10CQ(UES)
ATF22LV10CQ(UES)@PLCC28 [SA008A]	ATF22LV10CQ(UES)@S0IC24 [SA404]
ATF22LV10CQ(UES)@TSSOP24 [SA026-B3201]	
ATF22LV10CQ@PLCC28 [SA008A]	ATF22LV10CQ@S0IC24 [SA404]
ATF22LV10CQ@TSSOP24 [SA026-B3201]	
ATF22LV10CQZ	ATF22LV10CQZ(UES)
ATF22LV10CQZ(UES)@PLCC28 [SA008A]	
ATF22LV10CQZ(UES)@S0IC24 [SA404]	
ATF22LV10CQZ(UES)@TSSOP24 [SA026-B3201]	

ATF22LV10CQZ@PLCC28 [SA008A]	ATF22LV10CQZ@S0IC24 [SA404]
ATF22LV10CQZ@TSSOP24 [SA026-B3201]	
ATF22LV10CZ	ATF22LV10CZ(UES)
ATF22LV10CZ(UES)@PLCC28 [SA008A]	ATF22LV10CZ(UES)@S0IC24 [SA404]
ATF22LV10CZ(UES)@TSSOP24 [SA026-B3201]	
ATF22LV10CZ@PLCC28 [SA008A]	ATF22LV10CZ@S0IC24 [SA404]
ATF22LV10CZ@TSSOP24 [SA026-B3201]	
ATF22V10B	ATF22V10B@PLCC28 [SA008A]
ATF22V10B@S0IC24 [SA404]	ATF22V10BL
ATF22V10BL@PLCC28 [SA008A]	ATF22V10BL@S0IC24 [SA404]
ATF22V10BQ	ATF22V10BQ@PLCC28 [SA008A]
ATF22V10BQ@S0IC24 [SA404]	ATF22V10BQL
ATF22V10BQL@PLCC28 [SA008A]	ATF22V10BQL@S0IC24 [SA404]
ATF22V10C	ATF22V10C(UES)
ATF22V10C(UES)@PLCC28 [SA008A]	ATF22V10C(UES)@S0IC24 [SA404]
ATF22V10C(UES)@TSSOP24 [SA026-B3201]	
ATF22V10C@PLCC28 [SA008A]	ATF22V10C@S0IC24 [SA404]
ATF22V10C@TSSOP24 [SA026-B3201]	ATF22V10CEXT
ATF22V10CEXT@PLCC28 [SA008A]	ATF22V10CEXT@S0IC24 [SA404]
ATF22V10CEXT@TSSOP24 [SA026-B3201]	
ATF22V10CQ	ATF22V10CQ(UES)
ATF22V10CQ(UES)@PLCC28 [SA008A]	ATF22V10CQ(UES)@S0IC24 [SA404]
ATF22V10CQ(UES)@TSSOP24 [SA026-B3201]	
ATF22V10CQ@PLCC28 [SA008A]	ATF22V10CQ@S0IC24 [SA404]
ATF22V10CQ@TSSOP24 [SA026-B3201]	ATF22V10CQZ
ATF22V10CQZ(UES)	ATF22V10CQZ(UES)@PLCC28 [SA008A]
ATF22V10CQZ(UES)@S0IC24 [SA404]	
ATF22V10CQZ(UES)@TSSOP24 [SA026-B3201]	
ATF22V10CQZ@PLCC28 [SA008A]	ATF22V10CQZ@S0IC24 [SA404]
ATF22V10CQZ@TSSOP24 [SA026-B3201]	
ATF22V10CZ	ATF22V10CZ(UES)
ATF22V10CZ(UES)@PLCC28 [SA008A]	ATF22V10CZ(UES)@S0IC24 [SA404]
ATF22V10CZ(UES)@TSSOP24 [SA026-B3201]	
ATF22V10CZ@PLCC28 [SA008A]	ATF22V10CZ@S0IC24 [SA404]
ATF22V10CZ@TSSOP24 [SA026-B3201]	

MICROCONTROLLER

AT80F51	AT80F51@PLCC44 [SA244]
AT80F51@TQFP44 [SA245A-B4805]	AT80F52
AT80F52@PLCC44 [SA244]	AT80F52@TQFP44 [SA245A-B4805]
AT87C51RB2	AT87C51RB2@PLCC44 [SA244]
AT87C51RB2@TQFP44 [SA675-B4805]	AT87C51RC2
AT87C51RC2@PLCC44 [SA244]	AT87C51RC2@TQFP44 [SA675-B4805]
AT87C51RD2	AT87C51RD2@PLCC44 [SA244]
AT87C51RD2@TQFP44 [SA675-B4805]	AT87C51U2
AT87C51U2@PLCC44 [SA244]	AT87C51U2@TQFP44 [SA675-B4805]
AT87C52X2	AT87C52X2@PLCC44 [SA244]
AT87C52X2@TQFP44 [SA675-B4805]	AT87C54X2
AT87C54X2@PLCC44 [SA244]	AT87C54X2@TQFP44 [SA675-B4805]
AT87C58X2	AT87C58X2@PLCC44 [SA244]
AT87C58X2@TQFP44 [SA675-B4805]	AT87F51
AT87F51@PLCC44 [SA244]	AT87F51@TQFP44 [SA675-B4805]
AT87F51RC	AT87F51RC@PLCC44 [SA244]
AT87F51RC@TQFP44 [SA675-B4805]	AT87F52
AT87F52@PLCC44 [SA244]	AT87F52@TQFP44 [SA675-B4805]
AT87F55	AT87F55@PLCC44 [SA244]
AT87F55@TQFP44 [SA675-B4805]	AT87F55WD
AT87F55WD@PLCC44 [SA244]	AT87F55WD@TQFP44 [SA675-B4805]

AT87LV51
AT87LV51@TQFP44 [SA675-B4805]
AT87LV52@PLCC44 [SA244]
AT89C1051
AT89C1051U
AT89C2051
AT89C2051X2
AT89C4051
AT89C51
AT89C51@PQFP44 [SA675-B4805]
AT89C51AC2@PLCC44 [SA244]
AT89C51AC3@PLCC44 [SA244]
AT89C51CC01@PLCC44 [SA244]
AT89C51CC01@TQFP44 [SA245A-B4805]
AT89C51CC03C@PLCC44 [SA244]
AT89C51CC03C@TQFP44 [SA245A-B4805]
AT89C51CC03U@PLCC44 [SA244]
AT89C51CC03U@TQFP44 [SA245A-B4805]
AT89C51ED2
AT89C51ED2@PLCC68(*) [SA648-B6808]
AT89C51ED2@TQFP44 [SA245A-B4805]
AT89C51ED2@TQFP64(*) [TA054-B006]
AT89C51IC2@PLCC44 [SA244]
AT89C51ID2
AT89C51ID2@PLCC68(*) [SA648-B6808]
AT89C51ID2@TQFP44 [SA245A-B4805]
AT89C51ID2@TQFP64(*) [TA054-B006]
AT89C51RB2
AT89C51RB2@TQFP44 [SA245A-B4805]
AT89C51RC@PLCC44 [SA244]
AT89C51RC2
AT89C51RC2@TQFP44 [SA245A-B4805]
AT89C51RD2@PLCC44 [SA244]
AT89C51RD2@PLCC68(*) [SA648-B6808]
AT89C51RD2@TQFP44 [SA245A-B4805]
AT89C51RD2@TQFP64(*) [TA054-B006]
AT89C51RE2@PLCC44 [SA244]
AT89C52
AT89C52@PQFP44 [SA675-B4805]
AT89C55
AT89C55@PQFP44 [SA675-B4805]
AT89C55WD
AT89C55WD@TQFP44 [SA245A-B4805]
AT89LP2051@S0IC20 [SA404]
AT89LP2052
AT89LP2052@TSSOP20 [SA026-B3201]
AT89LP213@TSSOP14 [SA626A]
AT89LP214@TSSOP14 [SA626A]
AT89LP216@S0IC16 [SA404]
AT89LP4051
AT89LP4051@TSSOP20 [SA026-B3201]
AT89LP4052@S0IC20 [SA404]
AT89LP428
AT89LP428@TQFP32 [SA636]
AT89LP6440@MLF44 [SA712]
AT89LP6440@TQFP44 [SA245A-B4805]
AT89LP828@PLCC32 [SA015A1T]
AT89LS51
AT89LS51@TQFP44 [SA245A-B4805]

AT87LV51@PLCC44 [SA244]
AT87LV52
AT87LV52@TQFP44 [SA675-B4805]
AT89C1051@S0IC20 [SA404]
AT89C1051U@S0IC20 [SA404]
AT89C2051@S0IC20 [SA404]
AT89C2051X2@S0IC20 [SA404]
AT89C4051@S0IC20 [SA404]
AT89C51@PLCC44 [SA244]
AT89C51@TQFP44 [SA245A-B4805]
AT89C51AC2@TQFP44 [SA245A-B4805]
AT89C51AC3@TQFP44 [SA245A-B4805]

AT89C51ED2@PLCC44 [SA244]

AT89C51IC2@TQFP44 [SA245A-B4805]
AT89C51ID2@PLCC44 [SA244]

AT89C51RB2@PLCC44 [SA244]
AT89C51RC
AT89C51RC@TQFP44 [SA245A-B4805]
AT89C51RC2@PLCC44 [SA244]
AT89C51RD2

AT89C51RE2@VQFP44 [SA245A-B4805]
AT89C52@PLCC44 [SA244]
AT89C52@TQFP44 [SA245A-B4805]
AT89C55@PLCC44 [SA244]
AT89C55@TQFP44 [SA245A-B4805]
AT89C55WD@PLCC44 [SA244]
AT89LP2051
AT89LP2051@TSSOP20 [SA026-B3201]
AT89LP2052@S0IC20 [SA404]
AT89LP213
AT89LP214
AT89LP216
AT89LP216@TSSOP16 [SA626A]
AT89LP4051@S0IC20 [SA404]
AT89LP4052
AT89LP4052@TSSOP20 [SA026-B3201]
AT89LP428@PLCC32 [SA015A1T]
AT89LP6440
AT89LP6440@PLCC44 [SA244]
AT89LP828
AT89LP828@TQFP32 [SA636]
AT89LS51@PLCC44 [SA244]
AT89LS52

AT89LS52@PLCC44 [SA244]
AT89LS53
AT89LS53@TQFP44 [SA245A-B4805]
AT89LS8252@PLCC44 [SA244]
AT89LV51
AT89LV51@TQFP44 [SA245A-B4805]
AT89LV52@PLCC44 [SA244]
AT89LV55
AT89LV55@TQFP44 [SA245A-B4805]
AT89S2051@S0IC20 [SA404]
AT89S4051@S0IC20 [SA404]
AT89S51@PLCC44 [SA244]
AT89S52
AT89S52@TQFP44 [SA245A-B4805]
AT89S53@PLCC44 [SA244]
AT89S54
AT89S54@TQFP44 [SA245A-B4805]
AT89S58@PLCC44 [SA244]
AT89S64
AT89S64@TQFP44 [SA245A-B4805]
AT89S8252@PLCC44 [SA244]
AT89S8252@TQFP44 [SA245A-B4805]
AT89S8253@PLCC44 [SA244]
AT90LS2323
AT90LS2333
AT90LS2343
AT90LS4433
AT90LS4434
AT90LS4434@TQFP44 [SA245A-B4805]
AT90LS8535@PLCC44 [SA244]
AT90S1200
AT90S1200@SSOP20 [SA626A]
AT90S1200A@S0IC20 [SA404]
AT90S2313
AT90S2323
AT90S2333
AT90S2343
AT90S4414
AT90S4414@TQFP44 [SA245A-B4805]
AT90S4433@TQFP32 [SA636]
AT90S4434@PLCC44 [SA244]
AT90S8515
AT90S8515@TQFP44 [SA245A-B4805]
AT90S8535@PLCC44 [SA244]
AT90USB162@QFN32 [SA686]
AT90USB82@QFN32 [SA686]
ATC87C51@PLCC44 [SA244]
ATC87C52
ATC87C52@TQFP44 [SA675-B4805]
ATC87C54@PLCC44 [SA244]
ATC87C58
ATC87C58@TQFP44 [SA675-B4805]
ATMEGA16@MLF44 [SA712]
ATMEGA161
ATMEGA161L
ATMEGA162
ATMEGA162@TQFP44 [SA245A-B4805]
ATMEGA162V@MLF44 [SA712]
ATMEGA163

AT89LS52@TQFP44 [SA245A-B4805]
AT89LS53@PLCC44 [SA244]
AT89LS8252
AT89LS8252@TQFP44 [SA245A-B4805]
AT89LV51@PLCC44 [SA244]
AT89LV52
AT89LV52@TQFP44 [SA245A-B4805]
AT89LV55@PLCC44 [SA244]
AT89S2051
AT89S4051
AT89S51
AT89S51@TQFP44 [SA245A-B4805]
AT89S52@PLCC44 [SA244]
AT89S53
AT89S53@TQFP44 [SA245A-B4805]
AT89S54@PLCC44 [SA244]
AT89S58
AT89S58@TQFP44 [SA245A-B4805]
AT89S64@PLCC44 [SA244]
AT89S8252
AT89S8252@PQFP44 [SA675-B4805]
AT89S8253
AT89S8253@TQFP44 [SA245A-B4805]
AT90LS2323@S0IC8 [SA605B]
AT90LS2333@TQFP32 [SA636]
AT90LS2343@S0IC8 [SA605B]
AT90LS4433@TQFP32 [SA636]
AT90LS4434@PLCC44 [SA244]
AT90LS8535
AT90LS8535@TQFP44 [SA245A-B4805]
AT90S1200@S0IC20 [SA404]
AT90S1200A
AT90S1200A@SSOP20 [SA626A]
AT90S2313@S0IC20 [SA404]
AT90S2323@S0IC8 [SA605B]
AT90S2333@TQFP32 [SA636]
AT90S2343@S0IC8 [SA605B]
AT90S4414@PLCC44 [SA244]
AT90S4433
AT90S4434
AT90S4434@TQFP44 [SA245A-B4805]
AT90S8515@PLCC44 [SA244]
AT90S8535
AT90S8535@TQFP44 [SA245A-B4805]
AT90USB162@VQFP32 [SA636]
ATC87C51
ATC87C51@TQFP44 [SA675-B4805]
ATC87C52@PLCC44 [SA244]
ATC87C54
ATC87C54@TQFP44 [SA675-B4805]
ATC87C58@PLCC44 [SA244]
ATMEGA16
ATMEGA16@TQFP44 [SA245A-B4805]
ATMEGA161@TQFP44 [SA675-B4805]
ATMEGA161L@TQFP44 [SA675-B4805]
ATMEGA162@MLF44 [SA712]
ATMEGA162V
ATMEGA162V@TQFP44 [SA245A-B4805]
ATMEGA163@TQFP44 [SA675-B4805]

ATMEGA163L
ATMEGA164
ATMEGA164@TQFP44 [SA245A-B4805]
ATMEGA164A@MLF44 [SA712]
ATMEGA164A@VFBGA49 [SA712]
ATMEGA164P@MLF44 [SA712]
ATMEGA164PA
ATMEGA164PA@TQFP44 [SA245A-B4805]
ATMEGA164PV
ATMEGA164PV@TQFP44 [SA245A-B4805]
ATMEGA164V
ATMEGA164V@TQFP44 [SA245A-B4805]
ATMEGA168@MLF28 [SA780]
ATMEGA168@TQFP32 [SA636]
ATMEGA168P@MLF28 [SA780]
ATMEGA168P@TQFP32 [SA636]
ATMEGA168PA@MLF28 [SA780]
ATMEGA168PA@TQFP32 [SA636]
ATMEGA168PV@MLF28 [SA780]
ATMEGA168PV@TQFP32 [SA636]
ATMEGA168V@MLF28 [SA780]
ATMEGA168V@TQFP32 [SA636]
ATMEGA16A@MLF44 [SA712]
ATMEGA16HVA@TSOP28 [SA430T-B4003]
ATMEGA16HVB@TSSOP44 [SA693]
ATMEGA16L@MLF44 [SA712]
ATMEGA16M1@MLF32 [SA686]
ATMEGA16U2@MLF32 [SA686]
ATMEGA16U4@MLF44 [SA712]
ATMEGA32
ATMEGA32@TQFP44 [SA245A-B4805]
ATMEGA323@TQFP44 [SA675-B4805]
ATMEGA323L@TQFP44 [SA675-B4805]
ATMEGA324@MLF44 [SA712]
ATMEGA324A
ATMEGA324A@TQFP44 [SA245A-B4805]
ATMEGA324P@MLF44 [SA712]
ATMEGA324PA
ATMEGA324PA@TQFP44 [SA245A-B4805]
ATMEGA324PV
ATMEGA324PV@TQFP44 [SA245A-B4805]
ATMEGA324V
ATMEGA324V@TQFP44 [SA245A-B4805]
ATMEGA328P@MLF28 [SA780]
ATMEGA328P@TQFP32 [SA636]
ATMEGA328PV@MLF28 [SA780]
ATMEGA328PV@TQFP32 [SA636]
ATMEGA32A@MLF44 [SA712]
ATMEGA32C1@MLF32 [SA686]
ATMEGA32HVB@TSSOP44 [SA693]
ATMEGA32L@MLF44 [SA712]
ATMEGA32M1@MLF32 [SA686]
ATMEGA32U2@MLF32 [SA686]
ATMEGA32U4@MLF44 [SA712]
ATMEGA48
ATMEGA48@MLF32 [SA686]
ATMEGA48P
ATMEGA48P@MLF32 [SA686]
ATMEGA48PA

ATMEGA163L@TQFP44 [SA675-B4805]
ATMEGA164@MLF44 [SA712]
ATMEGA164A
ATMEGA164A@TQFP44 [SA245A-B4805]
ATMEGA164P
ATMEGA164P@TQFP44 [SA245A-B4805]
ATMEGA164PA@MLF44 [SA712]
ATMEGA164PV@MLF44 [SA712]
ATMEGA164V@MLF44 [SA712]
ATMEGA168
ATMEGA168@MLF32 [SA686]
ATMEGA168P
ATMEGA168P@MLF32 [SA686]
ATMEGA168PA
ATMEGA168PA@MLF32 [SA686]
ATMEGA168PV
ATMEGA168PV@MLF32 [SA686]
ATMEGA168V
ATMEGA168V@MLF32 [SA686]
ATMEGA16A
ATMEGA16A@TQFP44 [SA245A-B4805]
ATMEGA16L
ATMEGA16L@TQFP44 [SA245A-B4805]
ATMEGA16M1@TQFP32 [SA636]
ATMEGA16U2@VQFP32 [SA636]
ATMEGA16U4@TQFP44 [SA245A-B4805]
ATMEGA32@MLF44 [SA712]
ATMEGA323
ATMEGA323L
ATMEGA324
ATMEGA324@TQFP44 [SA245A-B4805]
ATMEGA324A@MLF44 [SA712]
ATMEGA324P
ATMEGA324P@TQFP44 [SA245A-B4805]
ATMEGA324PA@MLF44 [SA712]
ATMEGA324PV@MLF44 [SA712]
ATMEGA324V@MLF44 [SA712]
ATMEGA328P
ATMEGA328P@MLF32 [SA686]
ATMEGA328PV
ATMEGA328PV@MLF32 [SA686]
ATMEGA32A
ATMEGA32A@TQFP44 [SA245A-B4805]
ATMEGA32C1@TQFP32 [SA636]
ATMEGA32L
ATMEGA32L@TQFP44 [SA245A-B4805]
ATMEGA32M1@TQFP32 [SA636]
ATMEGA32U2@VQFP32 [SA636]
ATMEGA32U4@TQFP44 [SA245A-B4805]
ATMEGA48@MLF28 [SA780]
ATMEGA48@TQFP32 [SA636]
ATMEGA48P@MLF28 [SA780]
ATMEGA48P@TQFP32 [SA636]
ATMEGA48PA@MLF28 [SA780]

ATMEGA48PA@MLF32 [SA686]
ATMEGA48PV
ATMEGA48PV@MLF32 [SA686]
ATMEGA48V
ATMEGA48V@MLF32 [SA686]
ATMEGA644
ATMEGA644@TQFP44 [SA245A-B4805]
ATMEGA644A@MLF44 [SA712]
ATMEGA644P
ATMEGA644P@TQFP44 [SA245A-B4805]
ATMEGA644PA@MLF44 [SA712]
ATMEGA644PA@TQFP44 [SA245A-B4805]
ATMEGA644PV
ATMEGA644PV@TQFP44 [SA245A-B4805]
ATMEGA644V
ATMEGA644V@TQFP44 [SA245A-B4805]
ATMEGA8515@MLF44 [SA712]
ATMEGA8515@TQFP44 [SA245A-B4805]
ATMEGA8515L@MLF44 [SA712]
ATMEGA8515L@TQFP44 [SA245A-B4805]
ATMEGA8535
ATMEGA8535@PLCC44 [SA244]
ATMEGA8535L
ATMEGA8535L@PLCC44 [SA244]
ATMEGA8535L@TQFP44 [SA245A-B4805]
ATMEGA88
ATMEGA88@MLF32 [SA686]
ATMEGA88P
ATMEGA88P@MLF32 [SA686]
ATMEGA88PA
ATMEGA88PA@MLF32 [SA686]
ATMEGA88PV
ATMEGA88PV@MLF32 [SA686]
ATMEGA88V
ATMEGA88V@MLF32 [SA686]
ATMEGA8U2@VQFP32 [SA636]
ATtiny10@S0IC8 [SA023A]
ATtiny11
ATtiny11L
ATtiny12
ATtiny12L
ATtiny12V
ATtiny13
ATtiny13@MLF20 [SA692]
ATtiny13@S0IC8(5.5*8.0) [SA023A]
ATtiny13A@MLF10 [SA695A]
ATtiny13A@S0IC8(3.9*6.2) [SA602]
ATtiny13A@S0IC8(5.5*8.0) [SA023A]
ATtiny13V
ATtiny13V@MLF20 [SA692]
ATtiny13V@S0IC8(5.5*8.0) [SA023A]
ATtiny15
ATtiny15L
ATtiny167@QFN32 [SA686]
ATtiny167@TSSOP20 [SA026-B3201]
ATtiny20@S0IC14 [SA602]
ATtiny2313
ATtiny2313@S0IC20 [SA404]
ATtiny2313AMU@MLF20 [SA692]

ATMEGA48PA@TQFP32 [SA636]
ATMEGA48PV@MLF28 [SA780]
ATMEGA48PV@TQFP32 [SA636]
ATMEGA48V@MLF28 [SA780]
ATMEGA48V@TQFP32 [SA636]
ATMEGA644@MLF44 [SA712]
ATMEGA644A
ATMEGA644A@TQFP44 [SA245A-B4805]
ATMEGA644P@MLF44 [SA712]
ATMEGA644PA

ATMEGA644PV@MLF44 [SA712]

ATMEGA644V@MLF44 [SA712]
ATMEGA8515
ATMEGA8515@PLCC44 [SA244]
ATMEGA8515L
ATMEGA8515L@PLCC44 [SA244]

ATMEGA8535@MLF44 [SA712]
ATMEGA8535@TQFP44 [SA245A-B4805]
ATMEGA8535L@MLF44 [SA712]

ATMEGA88@MLF28 [SA780]
ATMEGA88@TQFP32 [SA636]
ATMEGA88P@MLF28 [SA780]
ATMEGA88P@TQFP32 [SA636]
ATMEGA88PA@MLF28 [SA780]
ATMEGA88PA@TQFP32 [SA636]
ATMEGA88PV@MLF28 [SA780]
ATMEGA88PV@TQFP32 [SA636]
ATMEGA88V@MLF28 [SA780]
ATMEGA88V@TQFP32 [SA636]
ATtiny10
ATtiny10@S0T23 [SA717]
ATtiny11@S0IC8 [SA023A]
ATtiny11L@S0IC8 [SA023A]
ATtiny12@S0IC8 [SA023A]
ATtiny12L@S0IC8 [SA023A]
ATtiny12V@S0IC8 [SA023A]
ATtiny13@MLF10 [SA695A]
ATtiny13@S0IC8(3.9*6.2) [SA602]
ATtiny13A
ATtiny13A@MLF20 [SA692]

ATtiny13V@MLF10 [SA695A]
ATtiny13V@S0IC8(3.9*6.2) [SA602]

ATtiny15@S0IC8 [SA023A]
ATtiny15L@S0IC8 [SA023A]
ATtiny167@S0IC20 [SA404]
ATtiny20@QFN20 [\$\$\$\$\$]
ATtiny20@TSSOP14 [SA026-B3201]
ATtiny2313@MLF20 [SA692]
ATtiny2313AMMH@MLF20 [SA692]
ATtiny2313APU

ATtiny2313ASU@S0IC20 [SA404]	ATtiny2313V
ATtiny2313V@MLF20 [SA692]	ATtiny2313V@S0IC20 [SA404]
ATtiny24	ATtiny24@MLF20 [SA692]
ATtiny24@S0IC14 [SA602]	ATtiny24A
ATtiny24A@MLF20 [SA692]	ATtiny24A@S0IC14 [SA602]
ATtiny24V	ATtiny24V@MLF20 [SA692]
ATtiny24V@S0IC14 [SA602]	ATtiny25
ATtiny25@MLF20 [SA692]	ATtiny25@S0IC8 [SA023A]
ATtiny25V	ATtiny25V@MLF20 [SA692]
ATtiny25V@S0IC8 [SA023A]	ATtiny26
ATtiny26(new)	ATtiny26(new)@MLF32 [SA686]
ATtiny26(new)@S0IC20 [SA404]	
ATtiny26(new)@TSSOP20 [SA026-B3201]	ATtiny26@S0IC20 [SA404]
ATtiny26@MLF32 [SA686]	ATtiny261
ATtiny26@TSSOP20 [SA026-B3201]	ATtiny261@S0IC20 [SA404]
ATtiny261@MLF32 [SA686]	ATtiny261A@MLF32 [SA686]
ATtiny261A	ATtiny261A@TSSOP20 [SA026-B3201]
ATtiny261A@S0IC20 [SA404]	ATtiny261V@MLF32 [SA686]
ATtiny261V	ATtiny26L
ATtiny261V@S0IC20 [SA404]	ATtiny26L(new)@MLF32 [SA686]
ATtiny26L(new)	
ATtiny26L(new)@S0IC20 [SA404]	ATtiny26L@S0IC20 [SA404]
ATtiny26L(new)@TSSOP20 [SA026-B3201]	ATtiny28L
ATtiny26L@MLF32 [SA686]	ATtiny28L@TQFP32 [SA636]
ATtiny26L@TSSOP20 [SA026-B3201]	ATtiny28V@MLF32 [SA686]
ATtiny28L@MLF32 [SA686]	ATtiny4@S0T23 [SA717]
ATtiny28V	ATtiny40@S0IC20 [SA404]
ATtiny28V@TQFP32 [SA636]	ATtiny4313MMH@MLF20 [\$\$\$\$\$]
ATtiny40@QFN20 [\$\$\$\$\$]	ATtiny4313PU
ATtiny40@TSSOP20 [SA026-B3201]	ATtiny43U@MLF20 [SA692]
ATtiny4313MU@MLF20 [SA692]	ATtiny44
ATtiny4313SU@S0IC20 [SA404]	ATtiny44@S0IC14 [SA602]
ATtiny43U@S0IC20 [SA404]	ATtiny44A@MLF20 [SA692]
ATtiny44@MLF20 [SA692]	ATtiny44V
ATtiny44A	ATtiny44V@S0IC14 [SA602]
ATtiny44A@S0IC14 [SA602]	ATtiny45@MLF20 [SA692]
ATtiny44V@MLF20 [SA692]	ATtiny45V
ATtiny45	ATtiny45V@S0IC8 [SA023A]
ATtiny45@S0IC8 [SA023A]	ATtiny461@MLF32 [SA686]
ATtiny45V@MLF20 [SA692]	ATtiny461A
ATtiny461	ATtiny461A@S0IC20 [SA404]
ATtiny461@S0IC20 [SA404]	ATtiny461V
ATtiny461A@MLF32 [SA686]	ATtiny461V@S0IC20 [SA404]
ATtiny461A@TSSOP20 [SA026-B3201]	ATtiny48@MLF28 [SA780]
ATtiny461V@MLF32 [SA686]	ATtiny48@TQFP32 [SA636]
ATtiny48	ATtiny48V@MLF28 [SA780]
ATtiny48@MLF32 [SA686]	ATtiny48V@TQFP32 [SA636]
ATtiny48V	ATtiny84
ATtiny48V@MLF32 [SA686]	ATtiny84@S0IC14 [SA602]
ATtiny5@S0T23 [SA717]	ATtiny84V@MLF20 [SA692]
ATtiny84@MLF20 [SA692]	ATtiny85
ATtiny84V	ATtiny85@S0IC8 [SA023A]
ATtiny84V@S0IC14 [SA602]	ATtiny85V@MLF20 [SA692]
ATtiny85@MLF20 [SA692]	ATtiny861
ATtiny85V	ATtiny861@S0IC20 [SA404]
ATtiny85V@S0IC8 [SA023A]	ATtiny861A@MLF32 [SA686]
ATtiny861@MLF32 [SA686]	ATtiny861A@TSSOP20 [SA026-B3201]
ATtiny861A	
ATtiny861A@S0IC20 [SA404]	

ATtiny861V
ATtiny861V@S0IC20 [SA404]
ATtiny87@S0IC20 [SA404]
ATtiny88
ATtiny88@MLF32 [SA686]
ATtiny88V
ATtiny88V@MLF32 [SA686]
ATtiny9@S0T23 [SA717]

ATtiny861V@MLF32 [SA686]
ATtiny87@QFN32 [SA686]
ATtiny87@TSSOP20 [SA026-B3201]
ATtiny88@MLF28 [SA780]
ATtiny88@TQFP32 [SA636]
ATtiny88V@MLF28 [SA780]
ATtiny88V@TQFP32 [SA636]

ATMEL W&M

MICROCONTROLLER

AT89C5115@PLCC28 [SA008A]
AT89C5115@TQFP32 [SA636]
AT89C51CC02@S0IC28 [SA404]
T89C5115@PLCC28 [SA008A]
T89C5115@TQFP32 [SA636]
T89C51AC2@TQFP44 [SA245A-B4805]
T89C51CC01@TQFP44 [SA245A-B4805]
T89C51CC02@S0IC24 [SA404]
T89C51CC02@TQFP32 [SA636]
T89C51IB2@TQFP44 [SA245A-B4805]
T89C51IC2@TQFP44 [SA245A-B4805]
T89C51RB2@PLCC44 [SA244]
T89C51RC2
T89C51RC2@TQFP44 [SA245A-B4805]
T89C51RD2@PLCC44 [SA244]
T89F64
T89F64@TQFP44 [SA245A-B4805]
TS87C51RB2@PLCC44 [SA244]
TS87C51RC2
TS87C51RC2@TQFP44 [SA675-B4805]
TS87C51RD2@PLCC44 [SA244]
TS87C51U2
TS87C51U2@TQFP44 [SA675-B4805]
TS87C52X2@PLCC44 [SA244]
TS87C54X2
TS87C54X2@TQFP44 [SA675-B4805]
TS87C58X2@PLCC44 [SA244]
TSC87251A1@PLCC44 [SA244]
TSC87251G1@PLCC44 [\$\$\$\$\$]
TSC87251G1A@PLCC44 [SA244]
TSC87251G2D@PLCC44 [SA244]
TSC87251G2D@TQFP44 [SA245A-B4805]
TSC87C51
TSC87C51@TQFP44 [SA675-B4805]

AT89C5115@S0IC28 [SA404]
AT89C51CC02@PLCC28 [SA008A]
AT89C51CC02@TQFP32 [SA636]
T89C5115@S0IC28 [SA404]
T89C51AC2@PLCC44 [SA244]
T89C51CC01@PLCC44 [SA244]
T89C51CC02@PLCC28 [SA008A]
T89C51CC02@S0IC28 [SA404]
T89C51IB2@PLCC44 [SA244]
T89C51IC2@PLCC44 [SA244]
T89C51RB2
T89C51RB2@TQFP44 [SA245A-B4805]
T89C51RC2@PLCC44 [SA244]
T89C51RD2
T89C51RD2@TQFP44 [SA245A-B4805]
T89F64@PLCC44 [SA244]
TS87C51RB2
TS87C51RB2@TQFP44 [SA675-B4805]
TS87C51RC2@PLCC44 [SA244]
TS87C51RD2
TS87C51RD2@TQFP44 [SA675-B4805]
TS87C51U2@PLCC44 [SA244]
TS87C52X2
TS87C52X2@TQFP44 [SA675-B4805]
TS87C54X2@PLCC44 [SA244]
TS87C58X2
TS87C58X2@TQFP44 [SA675-B4805]
TSC87251G1
TSC87251G1A
TSC87251G2D

TSC87C51@PLCC44 [SA244]

AUSTIN

E(E) PROM/FRAM/NVRAM

AS8E512K8

AS8E512K8@S0J32 [SA646]

BENCHMARQ

E (E) PROM/FRAM/NVRAM

BQ3285
BQ3287A
BQ4010Y
BQ4011Y
BQ4013Y
BQ4014Y
BQ4015Y
BQ4842Y

BQ3287
BQ4010
BQ4011
BQ4013
BQ4014
BQ4015
BQ4832Y

BMT

E (E) PROM/FRAM/NVRAM

BM29LV160B@TSOP48 [SB247-B4806]

BM29LV160T@TSOP48 [SB247-B4806]

BRIGHT

E (E) PROM/FRAM/NVRAM

BM29F040
BM29F040@TSOP32 [SA410T-B4001]
BM29F400B@TSOP48 [SB247-B4806]
BM29F400T@TSOP48 [SB247-B4806]

BM29F040@PLCC32 [SA015A1T]
BM29F400B@PSOP44 [SA638]
BM29F400T@PSOP44 [SA638]

CATALYST

E (E) PROM/FRAM/NVRAM

CAT1021(L)
CAT1021(R)@MSOP8 [SA026-B3201]
CAT1021(U)@TSSOP8 [SA026-B3201]
CAT1021(Y)@TSSOP8 [SA026-B3201]
CAT1022(L)
CAT1022(R)@MSOP8 [SA026-B3201]
CAT1022(U)@TSSOP8 [SA026-B3201]
CAT1022(Y)@TSSOP8 [SA026-B3201]
CAT1023(L)
CAT1023(R)@MSOP8 [SA026-B3201]
CAT1023(U)@TSSOP8 [SA026-B3201]
CAT1023(Y)@TSSOP8 [SA026-B3201]
CAT1024(L)
CAT1024(R)@MSOP8 [SA026-B3201]
CAT1024(U)@TSSOP8 [SA026-B3201]
CAT1024(Y)@TSSOP8 [SA026-B3201]
CAT1025(L)
CAT1025(R)@MSOP8 [SA026-B3201]
CAT1025(U)@TSSOP8 [SA026-B3201]
CAT1025(Y)@TSSOP8 [SA026-B3201]
CAT1026(L)
CAT1026(R)@MSOP8 [SA026-B3201]
CAT1026(U)@TSSOP8 [SA026-B3201]
CAT1026(Y)@TSSOP8 [SA026-B3201]
CAT1027(L)
CAT1027(R)@MSOP8 [SA026-B3201]

CAT1021(P)
CAT1021(S)@S0IC8 [SA602A]
CAT1021(V)@S0IC8 [SA602A]
CAT1021(Z)@MSOP8 [SA026-B3201]
CAT1022(P)
CAT1022(S)@S0IC8 [SA602A]
CAT1022(V)@S0IC8 [SA602A]
CAT1022(Z)@MSOP8 [SA026-B3201]
CAT1023(P)
CAT1023(S)@S0IC8 [SA602A]
CAT1023(V)@S0IC8 [SA602A]
CAT1023(Z)@MSOP8 [SA026-B3201]
CAT1024(P)
CAT1024(S)@S0IC8 [SA602A]
CAT1024(V)@S0IC8 [SA602A]
CAT1024(Z)@MSOP8 [SA026-B3201]
CAT1025(P)
CAT1025(S)@S0IC8 [SA602A]
CAT1025(V)@S0IC8 [SA602A]
CAT1025(Z)@MSOP8 [SA026-B3201]
CAT1026(P)
CAT1026(S)@S0IC8 [SA602A]
CAT1026(V)@S0IC8 [SA602A]
CAT1026(Z)@MSOP8 [SA026-B3201]
CAT1027(P)
CAT1027(S)@S0IC8 [SA602A]

CAT1027(U)@TSSOP8 [SA026-B3201]
CAT1027(Y)@TSSOP8 [SA026-B3201]
CAT1161(J)@S0IC8 [SA602A]
CAT1162(J)@S0IC8 [SA602A]
CAT1163(J)@S0IC8 [SA602A]
CAT1320
CAT1320@TDFN8
CAT1321
CAT1321@TDFN8
CAT14002@S0IC8 [SA602A]
CAT14008@S0IC8 [SA602A]
CAT15002@S0IC8 [SA602A]
CAT15008@S0IC8 [SA602A]
CAT1640
CAT1640@TDFN8
CAT1641
CAT1641@TDFN8
CAT2210
CAT2210I
CAT2212
CAT2212I
CAT22C10
CAT22C10I
CAT22C12
CAT22C12I
CAT24AA01@S0IC8 [SA602A]
CAT24AA02@S0IC8 [SA602A]
CAT24AA04@S0IC8 [SA602A]
CAT24AA08@S0IC8 [SA602A]
CAT24AA16@S0IC8 [SA602A]
CAT24AC128
CAT24AC128@TSSOP14 [SA026-B3201]
CAT24AC128@UDFN8 [SA724]
CAT24C00@S0IC8 [SA602A]
CAT24C01
CAT24C01@S0IC8 [SA602A]
CAT24C01@TSSOP8 [SA026-B3201]
CAT24C01B(L)
CAT24C01B(R)@MSOP8 [SA026-B3201]
CAT24C01B(U)@TSSOP8 [SA026-B3201]
CAT24C01B(W)@S0IC8 [SA602A]
CAT24C01B(Y)@TSSOP8 [SA026-B3201]
CAT24C01B(Z)@MSOP8 [SA026-B3201]
CAT24C02@S0IC14 [SA602]
CAT24C02@TDFN8 [SA724]
CAT24C021
CAT24C023
CAT24C03@S0IC8 [SA602A]
CAT24C03@TSSOP8 [SA026-B3201]
CAT24C04@S0IC14 [SA602]
CAT24C04@TDFN8 [SA724]
CAT24C041
CAT24C043
CAT24C05@S0IC8 [SA602A]
CAT24C05@TSSOP8 [SA026-B3201]
CAT24C08@S0IC14 [SA602]
CAT24C08@TDFN8 [SA724]
CAT24C081
CAT24C083

CAT1027(V)@S0IC8 [SA602A]
CAT1027(Z)@MSOP8 [SA026-B3201]
CAT1161(P)
CAT1162(P)
CAT1163(P)
CAT1320@S0IC8 [SA602A]
CAT1320@TSSOP8 [SA026-B3201]
CAT1321@S0IC8 [SA602A]
CAT1321@TSSOP8 [SA026-B3201]
CAT14004@S0IC8 [SA602A]
CAT14016@S0IC8 [SA602A]
CAT15004@S0IC8 [SA602A]
CAT15016@S0IC8 [SA602A]
CAT1640@S0IC8 [SA602A]
CAT1640@TSSOP8 [SA026-B3201]
CAT1641@S0IC8 [SA602A]
CAT1641@TSSOP8 [SA026-B3201]
CAT2210@S0IC16 [SA404]
CAT2210I@S0IC16 [SA404]
CAT2212@S0IC20 [SA404]
CAT2212I@S0IC20 [SA404]
CAT22C10@S0IC16 [SA404]
CAT22C10I@S0IC16 [SA404]
CAT22C12@S0IC20 [SA404]
CAT22C12I@S0IC20 [SA404]
CAT24AA01@TSOT-23 [SA717]
CAT24AA02@TSOT-23 [SA717]
CAT24AA04@TSOT-23 [SA717]
CAT24AA08@TSOT-23 [SA717]
CAT24AA16@TSOT-23 [SA717]
CAT24AC128@S0IC8 [SA602A]
CAT24AC128@TSSOP8 [SA026-B3201]
CAT24C00
CAT24C00@TSSOP8 [SA026-B3201]
CAT24C01@S0IC14 [SA602]
CAT24C01@TDFN8 [SA724]
CAT24C01B(J)@S0IC8 [SA602A]
CAT24C01B(P)

CAT24C02
CAT24C02@S0IC8 [SA602A]
CAT24C02@TSSOP8 [SA026-B3201]
CAT24C022
CAT24C03
CAT24C03@TDFN8 [SA724]
CAT24C04
CAT24C04@S0IC8 [SA602A]
CAT24C04@TSSOP8 [SA026-B3201]
CAT24C042
CAT24C05
CAT24C05@TDFN8 [SA724]
CAT24C08
CAT24C08@S0IC8 [SA602A]
CAT24C08@TSSOP8 [SA026-B3201]
CAT24C082
CAT24C08I

CAT24C08I@S0IC8 [SA602A]
CAT24C09@S0IC8 [SA602A]
CAT24C09@TSSOP8 [SA026-B3201]
CAT24C128@S0IC8 [SA602A]
CAT24C128@UDFN8 [SA724]
CAT24C16@S0IC14 [SA602]
CAT24C16@TDFN8 [SA724]
CAT24C161
CAT24C163
CAT24C164@S0IC8 [SA602A]
CAT24C16I
CAT24C208(J)@S0IC8 [SA602A]
CAT24C208(P)
CAT24C208(U)@TSSOP8 [SA026-B3201]
CAT24C208(W)@S0IC8 [SA602A]
CAT24C208(Y)@TSSOP8 [SA026-B3201]
CAT24C208(Z)@MSOP8 [SA666]
CAT24C21@S0IC8 [SA602A]
CAT24C256
CAT24C32
CAT24C44
CAT24C64
CAT24F32
CAT24F32@TSSOP8 [SA026-B3201]
CAT24F32A@S0IC8 [SA602A]
CAT24FC01
CAT24FC01@S0IC8 [SA602A]
CAT24FC01@TSSOP8 [SA026-B3201]
CAT24FC02@S0IC14 [SA602]
CAT24FC02@TDFN8 [SA724]
CAT24FC16
CAT24FC16@S0IC8 [SA602A]
CAT24FC16@TSSOP8 [SA026-B3201]
CAT24FC17@S0IC8 [SA602A]
CAT24FC17@TSSOP8 [SA026-B3201]
CAT24FC256@S0IC8 [SA602A]
CAT24FC256@TSSOP8 [SA026-B3201]
CAT24FC32@S0IC8 [SA602A]
CAT24FC32@TSSOP8 [SA026-B3201]
CAT24FC64@S0IC8 [SA602A]
CAT24FC64@TSSOP8 [SA026-B3201]
CAT24FC65@S0IC8 [SA602A]
CAT24FC65@TSSOP8 [SA026-B3201]
CAT24FC66@S0IC8 [SA602A]
CAT24FC66@TSSOP8 [SA026-B3201]
CAT24LC02@S0IC8 [SA602A]
CAT24LC02@TSSOP8 [SA026-B3201]
CAT24WC01@S0IC8 [SA602A]
CAT24WC02
CAT24WC02@TSSOP8 [SA026-B3201]
CAT24WC03@S0IC8 [SA602A]
CAT24WC04
CAT24WC04@TSSOP8 [SA026-B3201]
CAT24WC05@S0IC8 [SA602A]
CAT24WC08
CAT24WC08@TSSOP8 [SA026-B3201]
CAT24WC09@S0IC8 [SA602A]
CAT24WC128
CAT24WC128@TSSOP8 [SA026-B3201]

CAT24C09
CAT24C09@TDFN8 [SA724]
CAT24C128
CAT24C128@TSSOP8 [SA026-B3201]
CAT24C16
CAT24C16@S0IC8 [SA602A]
CAT24C16@TSSOP8 [SA026-B3201]
CAT24C162
CAT24C164
CAT24C164@TSSOP8 [SA026-B3201]
CAT24C16I@S0IC8 [SA602A]
CAT24C208(L)
CAT24C208(R)@MSOP8 [SA666]

CAT24C21
CAT24C21@TSSOP8 [SA026-B3201]
CAT24C256@S0IC8 [SA602A]
CAT24C32@S0IC8 [SA602A]
CAT24C44@S0IC8 [SA602A]
CAT24C64@S0IC8 [SA602A]
CAT24F32@S0IC8 [SA602A]
CAT24F32A
CAT24F32A@TSSOP8 [SA026-B3201]
CAT24FC01@S0IC14 [SA602]
CAT24FC01@TDFN8 [SA724]
CAT24FC02
CAT24FC02@S0IC8 [SA602A]
CAT24FC02@TSSOP8 [SA026-B3201]
CAT24FC16@S0IC14 [SA602]
CAT24FC16@TDFN8 [SA724]
CAT24FC17
CAT24FC17@TDFN8 [SA724]
CAT24FC256
CAT24FC256@TDFN8 [SA683]
CAT24FC32
CAT24FC32@TDFN8 [SA683]
CAT24FC64
CAT24FC64@TDFN8 [SA683]
CAT24FC65
CAT24FC65@TDFN8 [SA683]
CAT24FC66
CAT24FC66@TDFN8 [SA683]
CAT24LC02
CAT24LC02@TDFN8 [SA724]
CAT24WC01
CAT24WC01@TSSOP8 [SA026-B3201]
CAT24WC02@S0IC8 [SA602A]
CAT24WC03
CAT24WC03@TSSOP8 [SA026-B3201]
CAT24WC04@S0IC8 [SA602A]
CAT24WC05
CAT24WC05@TSSOP8 [SA026-B3201]
CAT24WC08@S0IC8 [SA602A]
CAT24WC09
CAT24WC09@TSSOP8 [SA026-B3201]
CAT24WC128@S0IC8 [SA602A]
CAT24WC129

CAT24WC129@S0IC8 [SA602A]
CAT24WC16@S0IC8 [SA602A]
CAT24WC164
CAT24WC164@TSSOP8 [SA026-B3201]
CAT24WC17@S0IC8 [SA602A]
CAT24WC256
CAT24WC257
CAT24WC32
CAT24WC33
CAT24WC64
CAT24WC64@TSSOP8
CAT24WC65@S0IC8 [SA602A]
CAT24WC66@S0IC8
CAT25010(S)@S0IC8 [SA605B]
CAT25020
CAT25020(U)@TSSOP8 [SA602A]
CAT25040(S)@S0IC8 [SA605B]
CAT25080
CAT25080@TDFN8 [SA724]
CAT25080@UDFN8
CAT25128@S0IC8 [SA602A]
CAT25128@TSSOP8 [SA026-B3201]
CAT25160@S0IC8 [SA602A]
CAT25160@TSSOP8 [SA026-B3201]
CAT25256
CAT25256@TDFN8 [SA724]
CAT25320
CAT25320@TDFN8 [SA724]
CAT25640
CAT25640@TDFN8 [SA724]
CAT25C01
CAT25C01@S0IC8 [SA602A]
CAT25C01@TSSOP8 [SA026-B3201]
CAT25C02@S0IC16 [SA602]
CAT25C02@TSSOP14 [SA026-B3201]
CAT25C03
CAT25C03@TSSOP14 [SA026-B3201]
CAT25C04
CAT25C04@S0IC8 [SA602A]
CAT25C04@TSSOP8 [SA026-B3201]
CAT25C05@S0IC8 [SA602A]
CAT25C05@TSSOP8 [SA026-B3201]
CAT25C08@S0IC16 [SA602]
CAT25C08@TSSOP14 [SA026-B3201]
CAT25C09
CAT25C09@TSSOP14 [SA026-B3201]
CAT25C11
CAT25C11@TSSOP14 [SA026-B3201]
CAT25C128
CAT25C128@S0IC8[150 mil] [SA602A]
CAT25C128@S0IC8[208 mil] [SA605B]
CAT25C128@TSSOP14 [SA026-B3201]
CAT25C16
CAT25C16@S0IC8 [SA602A]
CAT25C16@TSSOP8 [SA026-B3201]
CAT25C17@S0IC8 [SA602A]
CAT25C17@TSSOP8 [SA026-B3201]
CAT25C256@S0IC16 [SA602]
CAT25C256@S0IC8[150 mil] [SA602A]

CAT24WC16
CAT24WC16@TSSOP8 [SA026-B3201]
CAT24WC164@S0IC8 [SA602A]
CAT24WC17
CAT24WC17@TSSOP8 [SA026-B3201]
CAT24WC256@S0IC8 [SA602A]
CAT24WC257@S0IC8 [SA602A]
CAT24WC32@S0IC8 [SA602A]
CAT24WC33@S0IC8 [SA602A]
CAT24WC64@S0IC8 [SA602A]
CAT24WC65
CAT24WC66 [SA602A]
CAT25010
CAT25010(U)@TSSOP8 [SA602A]
CAT25020(S)@S0IC8 [SA605B]
CAT25040
CAT25040(U)@TSSOP8 [SA602A]
CAT25080@S0IC8 [SA602A]
CAT25080@TSSOP8 [SA026-B3201]
CAT25128
CAT25128@TDFN8 [SA724]
CAT25160
CAT25160@TDFN8 [SA724]
CAT25160@UDFN8
CAT25256@S0IC8 [SA602A]
CAT25256@TSSOP8 [SA026-B3201]
CAT25320@S0IC8 [SA602A]
CAT25320@TSSOP8 [SA026-B3201]
CAT25640@S0IC8 [SA602A]
CAT25640@TSSOP8 [SA026-B3201]
CAT25C01@S0IC16 [SA602]
CAT25C01@TSSOP14 [SA026-B3201]
CAT25C02
CAT25C02@S0IC8 [SA602A]
CAT25C02@TSSOP8 [SA026-B3201]
CAT25C03@S0IC8 [SA602A]
CAT25C03@TSSOP8 [SA026-B3201]
CAT25C04@S0IC16 [SA602]
CAT25C04@TSSOP14 [SA026-B3201]
CAT25C05
CAT25C05@TSSOP14 [SA026-B3201]
CAT25C08
CAT25C08@S0IC8 [SA602A]
CAT25C08@TSSOP8 [SA026-B3201]
CAT25C09@S0IC8 [SA602A]
CAT25C09@TSSOP8 [SA026-B3201]
CAT25C11@S0IC8 [SA602A]
CAT25C11@TSSOP8 [SA026-B3201]
CAT25C128@S0IC16 [SA602]

CAT25C128@TSSOP20 [SA026-B3201]
CAT25C16@S0IC16 [SA602]
CAT25C16@TSSOP14 [SA026-B3201]
CAT25C17
CAT25C17@TSSOP14 [SA026-B3201]
CAT25C256

CAT25C256@S0IC8[208 mil] [SA605B]	CAT25C256@TSSOP20 [SA026-B3201]
CAT25C256@TSSOP14 [SA026-B3201]	CAT25C32@S0IC8 [SA602A]
CAT25C32	CAT25C32@TSSOP20 [SA026-B3201]
CAT25C32@TSSOP14 [SA026-B3201]	CAT25C33@S0IC8 [SA602A]
CAT25C33	CAT25C64
CAT25C33@TSSOP14 [SA026-B3201]	CAT25C64@TSSOP14 [SA026-B3201]
CAT25C64@S0IC8 [SA602A]	CAT25C65
CAT25C64@TSSOP20 [SA026-B3201]	CAT25C65@TSSOP14 [SA026-B3201]
CAT25C65@S0IC8 [SA602A]	CAT27010@PLCC32 [SA015A1T]
CAT27010	CAT27128A
CAT27010@TSOP32 [SA410T-B4001]	CAT27512
CAT27256	CAT2764A
CAT27512@PLCC32 [SA015A1T]	CAT27C210
CAT27C16A	CAT27HC256
CAT27C210@PLCC44 [SA244]	CAT27HC256I
CAT27HC256@PLCC32 [SA015A1T]	CAT28C16A
CAT27HC256I@PLCC32 [SA015A1T]	CAT28C16A@S0IC24 [SA404]
CAT28C16A@PLCC32 [SA015A1T]	CAT28C16AI@PLCC32 [SA015A1T]
CAT28C16AI	CAT28C17A
CAT28C16AI@S0IC24 [SA404]	CAT28C17AI
CAT28C17A@PLCC32 [SA015A1T]	CAT28C256
CAT28C17AI@PLCC32 [SA015A1T]	CAT28C256@TSOP28 [SA430T-B4003]
CAT28C256@PLCC32 [SA015A1T]	CAT28C256I@PLCC32 [SA015A1T]
CAT28C256I	CAT28C257
CAT28C256I@TSOP28 [SA430T-B4003]	CAT28C257@TSOP28 [SA430T-B4003]
CAT28C257@PLCC32 [SA015A1T]	CAT28C512@PLCC32 [SA015A1T]
CAT28C512	CAT28C512@TSOP40 [SA409T-B4002]
CAT28C512@TSOP32 [SA410T-B4001]	CAT28C64A
CAT28C513@PLCC32 [SA015A1T]	CAT28C64A@S0IC28 [SA404]
CAT28C64A@PLCC32 [SA015A1T]	CAT28C64AI@PLCC32 [SA015A1T]
CAT28C64AI	CAT28C64B
CAT28C64AI@S0IC28 [SA404]	CAT28C64B@S0IC28 [SA404]
CAT28C64B@PLCC32 [SA015A1T]	CAT28C64BI
CAT28C64B@TSOP28 [SA430T-B4003]	CAT28C64BI@TSOP28 [SA430T-B4003]
CAT28C64BI@PLCC32 [SA015A1T]	CAT28C65B@PLCC32 [SA015A1T]
CAT28C65B	CAT28C65BI
CAT28C65B@TSOP28 [SA430T-B4003]	CAT28C65BI@TSOP28 [SA430T-B4003]
CAT28C65BI@PLCC32 [SA015A1T]	CAT28F001N-T@PLCC32 [SA015A1T]
CAT28F001N-B@PLCC32 [SA015A1T]	CAT28F001P-T
CAT28F001P-B	
CAT28F001T-B@TSOP32 [SA410T-B4001]	
CAT28F001T-T@TSOP32 [SA410T-B4001]	
CAT28F002B	CAT28F002B@TSOP40 [SA409T-B4002]
CAT28F002T	CAT28F002T@TSOP40 [SA409T-B4002]
CAT28F010	
CAT28F010(REVERSE)@TSOP32 [SA410T-B4001]	
CAT28F010@PLCC32 [SA015A1T]	CAT28F010@TSOP32 [SA410T-B4001]
CAT28F010I	
CAT28F010I(REVERSE)@TSOP32 [SA410T-B4001]	
CAT28F010I@PLCC32 [SA015A1T]	CAT28F010I@TSOP32 [SA410T-B4001]
CAT28F020	
CAT28F020(REVERSE)@TSOP32 [SA410T-B4001]	
CAT28F020@PLCC32 [SA015A1T]	CAT28F020@TSOP32 [SA410T-B4001]
CAT28F020I	
CAT28F020I(REVERSE)@TSOP32 [SA410T-B4001]	
CAT28F020I@PLCC32 [SA015A1T]	CAT28F020I@TSOP32 [SA410T-B4001]
CAT28F102	CAT28F102@PLCC44 [SA244]
CAT28F102@TSOP40 [SA623-B4002]	CAT28F512
CAT28F512(REVERSE)@TSOP32 [SA410T-B4001]	

CAT28F512@PLCC32 [SA015A1T]	CAT28F512@TSOP32 [SA410T-B4001]
CAT28F512I	
CAT28F512I(REVERSE)@TSOP32 [SA410T-B4001]	
CAT28F512I@PLCC32 [SA015A1T]	CAT28F512I@TSOP32 [SA410T-B4001]
CAT28LV256	CAT28LV256@PLCC32 [SA015A1T]
CAT28LV256@TSOP28 [SA430T-B4003]	CAT28LV64
CAT28LV64@PLCC32 [SA015A1T]	CAT28LV64@TSOP28 [SA430T-B4003]
CAT28LV65	CAT28LV65@PLCC32 [SA015A1T]
CAT28LV65@TSOP28 [SA430T-B4003]	CAT33C101(08bit)
CAT33C101(08bit)@S0IC8 [SA602A]	CAT33C101(16bit)
CAT33C101(16bit)@S0IC8 [SA602A]	CAT33C101H(08bit)
CAT33C101H(08bit)@S0IC8 [SA602A]	CAT33C101H(16bit)
CAT33C101H(16bit)@S0IC8 [SA602A]	CAT33C101I(08bit)
CAT33C101I(08bit)@S0IC8 [SA602A]	CAT33C101I(16bit)
CAT33C101I(16bit)@S0IC8 [SA602A]	CAT33C104(08bit)
CAT33C104(08bit)@S0IC8 [SA602A]	CAT33C104(16bit)
CAT33C104(16bit)@S0IC8 [SA602A]	CAT33C104I(08bit)
CAT33C104I(08bit)@S0IC8 [SA602A]	CAT33C104I(16bit)
CAT33C104I(16bit)@S0IC8 [SA602A]	CAT34C02
CAT34C02@S0IC8 [SA602A]	CAT34C02@TDFN8 [SA724]
CAT34C02@TSSOP8 [SA026-B3201]	CAT34FC02
CAT34FC02@S0IC8 [SA602A]	CAT34FC02@TDFN8 [SA724]
CAT34FC02@TSSOP8 [SA026-B3201]	CAT34RC02
CAT34RC02@S0IC8 [SA602A]	CAT34RC02@TDFN8 [SA724]
CAT34RC02@TSSOP8 [SA026-B3201]	CAT34TS02@TDFN8 [SA724]
CAT34WC02	CAT34WC02@S0IC8 [SA602A]
CAT34WC02@TDFN8 [SA724]	CAT34WC02@TSSOP8 [SA026-B3201]
CAT35C102	CAT35C102H
CAT35C102I	CAT35C104(08bit)
CAT35C104(08bit)@S0IC8 [SA602A]	CAT35C104(16bit)
CAT35C104(16bit)@S0IC8 [SA602A]	CAT35C104H(08bit)
CAT35C104H(08bit)@S0IC8 [SA602A]	CAT35C104I(08bit)
CAT35C104I(08bit)@S0IC8 [SA602A]	CAT35C104I(16bit)
CAT35C104I(16bit)@S0IC8 [SA602A]	CAT64LC20(J)@S0IC8 [SA602A]
CAT64LC20(P)	CAT64LC20(S)@S0IC8 [SA602A]
CAT64LC20(U)@TSSOP8 [SA026-B3201]	
CAT64LC20(UR)@TSSOP8 [SA026-B3201]	
CAT64LC40(J)@S0IC8 [SA602A]	CAT64LC40(P)
CAT64LC40(S)@S0IC8 [SA602A]	
CAT64LC40(U)@TSSOP8 [SA026-B3201]	
CAT64LC40(UR)@TSSOP8 [SA026-B3201]	
CAT93C46(08bit)	
CAT93C46(08bit)(J)@S0IC8 [SA602A]	
CAT93C46(08bit)(K)@S0IC8 [SA605B]	
CAT93C46(08bit)(S)@S0IC8 [SA602A]	
CAT93C46(08bit)(U)@TSSOP8 [SA026-B3201]	
CAT93C46(16bit)	
CAT93C46(16bit)(J)@S0IC8 [SA602A]	
CAT93C46(16bit)(K)@S0IC8 [SA605B]	
CAT93C46(16bit)(S)@S0IC8 [SA602A]	
CAT93C46(16bit)(U)@TSSOP8 [SA026-B3201]	
CAT93C46A	CAT93C46R(08bit)
CAT93C46R(08bit)(V)@S0IC8 [SA602A]	
CAT93C46R(08bit)(VP2)@TDFN8 [SA724]	
CAT93C46R(08bit)(W)@S0IC8 [SA602A]	
CAT93C46R(08bit)(X)@S0IC8 [SA602A]	
CAT93C46R(08bit)(Y)@TSSOP8 [SA026-B3201]	
CAT93C46R(16bit)(V)@S0IC8 [SA602A]	
CAT93C46R(16bit)(VP2)@TDFN8 [SA724]	

CAT93C46R(16bit)(W)@S0IC8 [SA602A]	
CAT93C46R(16bit)(X)@S0IC8 [SA602A]	
CAT93C46R(16bit)(Y)@TSS0P8 [SA026-B3201]	
CAT93C46R-16	CAT93C56(08bit)
CAT93C56(08bit)@S0IC8 [SA602A]	CAT93C56(16bit)
CAT93C56(16bit)@S0IC8 [SA602A]	CAT93C56A
CAT93C57	CAT93C66(08bit)
CAT93C66(08bit)@S0IC8 [SA602A]	
CAT93C66(08bit)@TSS0P8 [SA026-B3201]	
CAT93C66(16bit)	CAT93C66(16bit)@S0IC8 [SA602A]
CAT93C66(16bit)@TSS0P8	CAT93C66A
CAT93C76(08bit)	
CAT93C76(08bit)(J)@S0IC8 [SA602A]	
CAT93C76(08bit)(K)@S0IC8 [SA605B]	
CAT93C76(08bit)(S)@S0IC8 [SA602A]	
CAT93C76(08bit)(U)@TSS0P8 [SA026-B3201]	
CAT93C76(16bit)	
CAT93C76(16bit)(J)@S0IC8 [SA602A]	
CAT93C76(16bit)(K)@S0IC8 [SA605B]	
CAT93C76(16bit)(S)@S0IC8 [SA602A]	
CAT93C76(16bit)(U)@TSS0P8 [SA026-B3201]	
CAT93C86(08bit)	
CAT93C86(08bit)(J)@S0IC8 [SA602A]	
CAT93C86(08bit)(K)@S0IC8 [SA605B]	
CAT93C86(08bit)(S)@S0IC8 [SA602A]	
CAT93C86(08bit)(U)@TSS0P8 [SA026-B3201]	
CAT93C86(16bit)	
CAT93C86(16bit)(J)@S0IC8 [SA602A]	
CAT93C86(16bit)(K)@S0IC8 [SA605B]	
CAT93C86(16bit)(S)@S0IC8 [SA602A]	
CAT93C86(16bit)(U)@TSS0P8 [SA026-B3201]	
CAT93H46(08bit)	
CAT93H46(08bit)(J)@S0IC8 [SA602A]	
CAT93H46(08bit)(K)@S0IC8 [SA605B]	
CAT93H46(08bit)(S)@S0IC8 [SA602A]	
CAT93H46(08bit)(U)@TSS0P8 [SA026-B3201]	
CAT93H46(16bit)	
CAT93H46(16bit)(J)@S0IC8 [SA602A]	
CAT93H46(16bit)(K)@S0IC8 [SA605B]	
CAT93H46(16bit)(S)@S0IC8 [SA602A]	
CAT93H46(16bit)(U)@TSS0P8 [SA026-B3201]	
CAT93HC46(08bit)	
CAT93HC46(08bit)(J)@S0IC8 [SA602A]	
CAT93HC46(08bit)(K)@S0IC8 [SA605B]	
CAT93HC46(08bit)(S)@S0IC8 [SA602A]	
CAT93HC46(08bit)(U)@TSS0P8 [SA026-B3201]	
CAT93HC46(16bit)	
CAT93HC46(16bit)(J)@S0IC8 [SA602A]	
CAT93HC46(16bit)(K)@S0IC8 [SA605B]	
CAT93HC46(16bit)(S)@S0IC8 [SA602A]	
CAT93HC46(16bit)(U)@TSS0P8 [SA026-B3201]	

CERAMATE

E(E) PROM/FRAM/NVRAM

24LC02	24LC02@S0IC8 [SA602A]
24LC02@TSS0P8 [SA026-B3201]	24LC08

24LC08@S0IC8 [SA602A]
24LC16
24LC16@TSSOP8 [SA026-B3201]
24LLC02@S0IC8 [SA602A]
24LLC08
24LLC08@TSSOP8 [SA026-B3201]
93LC46@S0IC8 [SA602A]
93LC46R@S0IC8 [SA602A]
93LC56@S0IC8 [SA602A]
93LC66@S0IC8 [SA602A]

24LC08@TSSOP8 [SA026-B3201]
24LC16@S0IC8 [SA602A]
24LLC02
24LLC02@TSSOP8 [SA026-B3201]
24LLC08@S0IC8 [SA602A]
93LC46
93LC46R
93LC56
93LC66

CFEON

E(E)PROM/FRAM/NVRAM

EN25F80
EN25F80@VDFN8 [SA683]
EN25T16@VDFN8 [SA683]
EN25T80@SOP8 [SA605B]
EN29F002AB
EN29F002AB@TSOP32 [SA410T-B4001]
EN29F002ANB@PLCC32 [SA015A1T]
EN29F002ANB@TSOP32 [SA410T-B4001]
EN29F002ANT
EN29F002ANT@TSOP32 [SA410T-B4001]
EN29F002AT
EN29F002AT@TSOP32 [SA410T-B4001]
EN29F002B@PLCC32 [SA015A1T]
EN29F002NB
EN29F002NB@TSOP32 [SA410T-B4001]
EN29F002NT@PLCC32 [SA015A1T]
EN29F002T
EN29F002T@TSOP32 [SA410T-B4001]
EN29F010@PLCC32 [SA015A1T]
EN29F010@VSOP32 [SA620-B4807]
EN29F040@PLCC32 [SA015A1T]
EN29F040A
EN29F040A@TSOP32 [SA410T-B4001]
EN29F512
EN29F512@TSOP32 [SA410T-B4001]
EN29F800B@TSOP48 [SB247-B4806]
EN29GL064B@TSOP48 [SB247-B4806]
EN29LV010@PLCC32 [SA015A1T]
EN29LV010@VSOP32 [SA620-B4807]
EN29LV040@TSOP32 [SA410T-B4001]
EN29LV040A
EN29LV040A@TSOP32 [SA410T-B4001]
EN29LV160AB@TSOP48 [SB247-B4806]
EN29LV160B@TSOP48 [SB247-B4806]
EN29LV160BT@TSOP48 [SB247-B4806]
EN29LV320AB@TSOP48 [SB247-B4806]
EN29LV320B@TSOP48 [SB247-B4806]
EN29LV320BT@TSOP48 [SB247-B4806]
EN29LV400AB@TSOP48 [SB247-B4806]
EN29LV400B@TSOP48 [SB247-B4806]
EN29LV512@PLCC32 [SA015A1T]
EN29LV512@VSOP32 [SA620-B4807]
EN29LV640H@TSOP48 [SB247-B4806]

EN25F80@SOP8 [SA605B]
EN25T16@SOP8 [SA605B]
EN25T80
EN25T80@VDFN8 [SA683]
EN29F002AB@PLCC32 [SA015A1T]
EN29F002ANB

EN29F002ANT@PLCC32 [SA015A1T]

EN29F002AT@PLCC32 [SA015A1T]
EN29F002B
EN29F002B@TSOP32 [SA410T-B4001]
EN29F002NB@PLCC32 [SA015A1T]
EN29F002NT
EN29F002NT@TSOP32 [SA410T-B4001]
EN29F002T@PLCC32 [SA015A1T]
EN29F010
EN29F010@TSOP32 [SA410T-B4001]
EN29F040
EN29F040@TSOP32 [SA410T-B4001]
EN29F040A@PLCC32 [SA015A1T]
EN29F080@TSOP40 [SA409T-B4002]
EN29F512@PLCC32 [SA015A1T]
EN29F512@VSOP32 [SA620-B4807]
EN29F800T@TSOP48 [SB247-B4806]
EN29GL064T@TSOP48 [SB247-B4806]
EN29LV010@TSOP32 [SA410T-B4001]
EN29LV040@PLCC32 [SA015A1T]
EN29LV040@VSOP32 [SA620-B4807]
EN29LV040A@PLCC32 [SA015A1T]
EN29LV040A@VSOP32 [SA620-B4807]
EN29LV160AT@TSOP48 [SB247-B4806]
EN29LV160BB@TSOP48 [SB247-B4806]
EN29LV160T@TSOP48 [SB247-B4806]
EN29LV320AT@TSOP48 [SB247-B4806]
EN29LV320BB@TSOP48 [SB247-B4806]
EN29LV320T@TSOP48 [SB247-B4806]
EN29LV400AT@TSOP48 [SB247-B4806]
EN29LV400T@TSOP48 [SB247-B4806]
EN29LV512@TSOP32 [SA410T-B4001]
EN29LV640B@TSOP48 [SB247-B4806]
EN29LV640L@TSOP48 [SB247-B4806]

EN29LV640T@TSOP48 [SB247-B4806]
EN29LV641L@TSOP48 [SB247-B4806]
EN29LV800AT@TSOP48 [SB247-B4806]
EN29LV800BB@TSOP48 [SB247-B4806]
EN29LV800CB@TSOP48 [SB247-B4806]
EN29LV800T@TSOP48 [SB247-B4806]
EN29PL064@TSOP48 [SB247-B4806]
EN29SL160T@TSOP48 [SB247-B4806]
EN29SL400T@TSOP48 [SB247-B4806]
EN29SL800T@TSOP48 [SB247-B4806]
EN39LV010@VSOP32 [SA620-B4807]

EN29LV641H@TSOP48 [SB247-B4806]
EN29LV800AB@TSOP48 [SB247-B4806]
EN29LV800B@TSOP48 [SB247-B4806]
EN29LV800BT@TSOP48 [SB247-B4806]
EN29LV800CT@TSOP48 [SB247-B4806]
EN29PL032@TSOP48 [SB247-B4806]
EN29SL160B@TSOP48 [SB247-B4806]
EN29SL400B@TSOP48 [SB247-B4806]
EN29SL800B@TSOP48 [SB247-B4806]
EN39LV010@PLCC32 [SA015A1T]
EN39SL800@TSOP48 [SA247-B4806]

CHINA CORE

MICROCONTROLLER

CCM89C51
CCM89C51@TQFP44 [SA245A-B4805]
CCM89C52@PLCC44 [SA244]

CCM89C51@PLCC44 [SA244]
CCM89C52
CCM89C52@TQFP44 [SA245A-B4805]

CHINGIS

E(E) PROM/FRAM/NVRAM

PM25LD010@SOP8 [SA602A]
PM25LD010@WSOP8 [SA683]
PM25LD010C@TSSOP8 [SA026-B3201]
PM25LD020@SOP8 [SA602A]
PM25LD020@WSOP8 [SA683]
PM25LD020C@TSSOP8 [SA026-B3201]
PM25LD040(B)@SOIC8 [SA605B]
PM25LD040(S)@SOIC8 [SA602A]
PM25LD512@TSSOP8 [SA026-B3201]
PM25LD512C@SOP8 [SA602A]
PM25LD512C@WSOP8 [SA683]
PM25LV010(Q)@WSOP8 [SA683]
PM25LV020(B)@SOIC8 [SA605B]
PM25LV020(S)@SOIC8 [SA602A]
PM25LV040(Q)@WSOP8 [SA683]
PM25LV512(B)@SOIC8 [SA605B]
PM25LV512(S)@SOIC8 [SA602A]
PM25W020(Q)@WSOP8 [SA683]
PM29F002B
PM29F002T
PM29F004B
PM29F004T
PM29LV002B
PM29LV002B@VSOP32 [SA620-B4807]
PM29LV002T@PLCC32 [SA015A1T]
PM29LV004B@PLCC32 [SA015A1T]
PM29LV004T@PLCC32 [SA015A1T]
PM29LV104RB@PLCC32 [SA015A1T]
PM29LV104RT@PLCC32 [SA015A1T]
PM37LV512
PM37LV512@VSOP32 [SA620-B4807]
PM39F010@PLCC32 [SA015A1T]
PM39F020

PM25LD010@TSSOP8 [SA026-B3201]
PM25LD010C@SOP8 [SA602A]
PM25LD010C@WSOP8 [SA683]
PM25LD020@TSSOP8 [SA026-B3201]
PM25LD020C@SOP8 [SA602A]
PM25LD020C@WSOP8 [SA683]
PM25LD040(Q)@WSOP8 [SA683]
PM25LD512@SOP8 [SA602A]
PM25LD512@WSOP8 [SA683]
PM25LD512C@TSSOP8 [SA026-B3201]
PM25LV010(B)@SOIC8 [SA605B]
PM25LV010(S)@SOIC8 [SA602A]
PM25LV020(Q)@WSOP8 [SA683]
PM25LV040(B)@SOIC8 [SA605B]
PM25LV040(S)@SOIC8 [SA602A]
PM25LV512(Q)@WSOP8 [SA683]
PM25W020(B)@SOIC8 [SA605B]
PM25W020(S)@SOIC8 [SA602A]
PM29F002B@PLCC32 [SA015A1T]
PM29F002T@PLCC32 [SA015A1T]
PM29F004B@PLCC32 [SA015A1T]
PM29F004T@PLCC32 [SA015A1T]
PM29LV002B@PLCC32 [SA015A1T]
PM29LV002T
PM29LV002T@VSOP32 [SA620-B4807]
PM29LV004B@VSOP32 [SA620-B4807]
PM29LV004T@VSOP32 [SA620-B4807]
PM29LV104RB@VSOP32 [SA620-B4807]
PM29LV104RT@VSOP32 [SA620-B4807]
PM37LV512@PLCC32 [SA015A1T]
PM39F010
PM39F010@VSOP32 [SA620-B4807]
PM39F020@PLCC32 [SA015A1T]

PM39F020@VSOP32 [SA620-B4807]
PM39F040@PLCC32 [SA015A1T]
PM39LV010@PLCC32 [SA015A1T]
PM39LV010R@PLCC32 [SA015A1T]
PM39LV020@PLCC32 [SA015A1T]
PM39LV040@PLCC32 [SA015A1T]
PM39LV512@PLCC32 [SA015A1T]
PM39LV512R@PLCC32 [SA015A1T]
PM49FL002T@PLCC32 [SA015A1T]
PM49FL004T@PLCC32 [SA015A1T]
PM49FL008T@PLCC32 [SA015A1T]
PM49LP002T@PLCC32 [SA015A1T]

PM39F040
PM39F040@VSOP32 [SA620-B4807]
PM39LV010@VSOP32 [SA620-B4807]
PM39LV010R@VSOP32 [SA620-B4807]
PM39LV020@VSOP32 [SA620-B4807]
PM39LV040@VSOP32 [SA620-B4807]
PM39LV512@VSOP32 [SA620-B4807]
PM39LV512R@VSOP32 [SA620-B4807]
PM49FL002T@VSOP32 [SA620-B4807]
PM49FL004T@VSOP32 [SA620-B4807]
PM49FL008T@VSOP32 [SA620-B4807]
PM49LP002T@VSOP32 [SA620-B4807]

CHIPON

MICROCONTROLLER

C61F120
C61F120@S0IC8 [SA605B]
C61F121
C61F121@TSSOP14 [SA026-B3201]
C61F132@QFN8 [SA683]
C61F132@SSOP20 [SA626A]
C61F133
C61F133@TSSOP14 [SA026-B3201]
C61F182@QFN28 [SA685]
C61F182@SSOP28 [SA626A]
C61F183@QFN28 [SA685]
C61F183@SSOP28 [SA626A]
C61F184@QFN44 [SA712]
C61F186
C61F186@S0IC28 [SA404]
C61F187
C61F187@QFP44 [SA245A-B4805]
C61F21@QFN8 [SA744]
C61F21@SSOP8 [SA602]
C61F23@QFN16 [SA727]
C61F23@TSSOP14 [SA026-B3201]

C61F120@QFN8 [SA683]
C61F120@SSOP8 [SA602]
C61F121@S0IC14 [SA602]
C61F132
C61F132@S0IC8 [SA605B]
C61F132@SSOP8 [SA602]
C61F133@S0IC14 [SA602]
C61F182
C61F182@S0IC28 [SA404]
C61F183
C61F183@S0IC28 [SA404]
C61F184
C61F184@QFP44 [SA245A-B4805]
C61F186@QFN28 [SA685]
C61F186@SSOP28 [SA626A]
C61F187@QFN44 [SA712]
C61F21
C61F21@S0IC8 [SA605B]
C61F23
C61F23@S0IC14 [SA602]

CHIPSWINNER

MICROCONTROLLER

CW89F51
CW89F51@TQFP44 [SA675-B4805]
CW89F52@PLCC44 [SA244]
CW89F54
CW89F54@TQFP44 [SA675-B4805]

CW89F51@PLCC44 [SA244]
CW89F52
CW89F52@TQFP44 [SA675-B4805]
CW89F54@PLCC44 [SA244]

CWI

E(E) PROM/FRAM/NVRAM

39LV040@VSOP32 [SA620-B4807]

CYPRESS

E (E) PROM/FRAM/NVRAM

CY27C010	CY27C010@PLCC32 [SA015A1T]
CY27C010@TSOP32 [SA410T-B4001]	CY27C020
CY27C020@PLCC32 [SA015A1T]	CY27C020@TSOP32 [SA410T-B4001]
CY27C040	CY27C040@PLCC32 [SA015A1T]
CY27C040@TSOP32 [SA410T-B4001]	CY27C256
CY27C256@PLCC32 [SA015A1T]	CY27C256@TSOP28 [SA430T-B4003]
CY27C512	CY27C512@PLCC32 [SA015A1T]
CY27C512@TSOP28 [SA430T-B4003]	CY27H010
CY27H010@PLCC32 [SA015A1T]	CY27H010@TSOP32 [SA410T-B4001]
CY27H256	CY27H256@PLCC32 [SA015A1T]
CY27H256@TSOP28 [SA430T-B4003]	CY27H512
CY27H512@PLCC32 [SA015A1T]	CY27H512@TSOP28 [SA430T-B4003]
CY7C251	CY7C251@PLCC32 [\$\$\$\$\$]
CY7C254	CY7C254@PLCC32 [\$\$\$\$\$]
CY7C256	CY7C256@PLCC32 [SA015A1T]
CY7C261	CY7C261@PLCC28 [SA008A]
CY7C263	CY7C263@PLCC28 [SA008A]
CY7C264	CY7C264@PLCC28 [SA008A]
CY7C291	CY7C291@PLCC28 [\$\$\$\$\$]
CY7C291A	CY7C291A@PLCC28 [\$\$\$\$\$]
CY7C292	CY7C292@PLCC28 [\$\$\$\$\$]
CY7C292A	CY7C292A@PLCC28 [\$\$\$\$\$]
CY7C293A	CY7C293A@PLCC28 [\$\$\$\$\$]

PLD

PALC22V10D	PALC22V10D@PLCC28 [SA008A]
PALCE16V8	PALCE16V8@PLCC20 [SA001A-B2001]
PALCE20V8	PALCE20V8@PLCC28 [SA008A]
PALCE20V8L	PALCE20V8L@PLCC28 [SA008A]
PALCE22V10	PALCE22V10@PLCC28 [SA008A]
PLDC20G10	PLDC20G10@PLCC28 [SA008A]
PLDC20G10B	PLDC20G10B@PLCC28 [SA008A]
PLDC20RA10	PLDC20RA10@PLCC28

DALLAS

E (E) PROM/FRAM/NVRAM

DS1073M-100	DS1073M-60
DS1073M-66	DS1073M-80
DS1073Z-100@S0IC8 [SA602A]	DS1073Z-60@S0IC8 [SA602A]
DS1073Z-66@S0IC8 [SA602A]	DS1073Z-80@S0IC8 [SA602A]
DS1077LZ-40@S0IC8 [SA602A]	DS1077LZ-50@S0IC8 [SA602A]
DS1077LZ-60@S0IC8 [SA602A]	DS1077LZ-66@S0IC8 [SA602A]
DS1077Z-40@S0IC8 [SA602A]	DS1077Z-50@S0IC8 [SA602A]
DS1077Z-60@S0IC8 [SA602A]	DS1077Z-66@S0IC8 [SA602A]
DS1086U	DS1086Z [SA602A]
DS1220AB	DS1220AD
DS1220Y	DS1225AB
DS1225AD	DS1225D
DS1225E	DS1225Y
DS1230AB	DS1230W

DS1230Y
DS1235Y
DS1244
DS1245AB
DS1245W
DS1248W
DS1249AB
DS1249Y
DS1250W
DS1251AB
DS1251Y
DS1256Y
DS1258W
DS1265AB
DS1265Y
DS1270W
DS1284
DS1284Q@PLCC28 [SA008A]
DS1286
DS1287
DS12887
DS12C887
DS1330AB
DS1345AB
DS1345Y
DS1350W
DS1385
DS1386(8K)
DS14285
DS1485
DS1486
DS1501
DS1553
DS1554
DS1556
DS1630Y
DS1643
DS1645AB
DS1645Y
DS1647
DS1650Y [\$\$\$\$\$\$]
DS1687-5
DS17287-5
DS1742W
DS1743W
DS1744W
DS1747
DS17487-3
DS17887-3
DS2406@T0-92
DS2430A@T0-92
DS2431@T0-92
DS2432P@TSOC6
DS2433S(3.9)@S0IC8 [SA602A]
DS2502
DS2502S@S0IC8 [SA602A]
DS2502UNW@S0IC8 [SA602A]
DS2506
DS4510@uSOP10 [SA602]

DS1235AB
DS1243Y
DS1244Y
DS1245EE
DS1245Y
DS1248Y
DS1249W
DS1250AB
DS1250Y
DS1251W
DS1256W
DS1258AB
DS1258Y
DS1265W
DS1270AB
DS1270Y
DS1284N
DS1284QN@PLCC28 [SA008A]
DS1286I
DS1287A
DS12887A
DS12C887A
DS1330Y
DS1345W
DS1350AB
DS1350Y
DS1386(32K)
DS1387
DS14287
DS1485@S0IC28 [SA630]
DS1488
DS1511
DS1553W
DS1554W
DS1630AB
DS1642
DS1644
DS1645EE
DS1646
DS1650AB
DS1687-3
DS17287-3
DS1742
DS1743
DS1744
DS1746
DS1747W
DS17487-5
DS17887-5
DS2406P@TSOC6
DS2430AP@TSOC6
DS2431P@TSOC6
DS2433@PR-35
DS2433S(5.5)@S0IC8 [SA605B]
DS2502P@TSOC6 [\$\$\$\$\$\$]
DS2502UNW
DS2502UNW@TSOC6 [\$\$\$\$\$\$]
DS2506S@S0IC8 [SA605B]
DS4520@TSSOP16 [SA026-B3201]

DS4550@TSSOP20 [SA026-B3201]

DENSE-PAC

E (E) PROM/FRAM/NVRAM

DPV27C101	DPV27C101@PLCC32 [SA015A1T]
DPV27C256	DPV27C256@PLCC32 [SA015A1T]
DPV27C512	DPV27C512@PLCC32 [SA015A1T]

DEUTRON

E (E) PROM/FRAM/NVRAM

AC25LV010	AC25LV010@S0IC8 [SA602A]
AC25LV512	AC25LV512@S0IC8 [SA602A]
P439LV010@PLCC32 [SA015A1T]	P439LV010@VSOP32 [SA620-B4807]
P439LV040@PLCC32 [SA015A1T]	P439LV040@VSOP32 [SA620-B4807]
P439LV088@TSOP48 [SB247-B4806]	P439VF800@TSOP48 [SB247-B4806]

E-CMOS

E (E) PROM/FRAM/NVRAM

EC24C01	EC24C01@S0IC8 [SA602A]
EC24C01@TSSOP8 [SA026-B3201]	EC24C02
EC24C02@S0IC8 [SA602A]	EC24C02@TSSOP8 [SA026-B3201]
EC24C04	EC24C04@S0IC8 [SA602A]
EC24C04@TSSOP8 [SA026-B3201]	EC24C08
EC24C08@S0IC8 [SA602A]	EC24C08@TSSOP8 [SA026-B3201]
EC24C16	EC24C16@S0IC8 [SA602A]
EC24C16@TSSOP8 [SA026-B3201]	

EFST

E (E) PROM/FRAM/NVRAM

EM25LV010@S0IC8 [SA602A]	EM25LV010@VFQFPN8 [SA684]
EM25LV512@S0IC8 [SA602A]	EM25LV512@VFQFPN8 [SA684]
F49B002UA	F49B002UA@PLCC32 [SA015A1T]
F49L004BA@PLCC32 [SA015A1T]	F49L004BA@TSOP40 [SA409T-B4002]
F49L004UA@PLCC32 [SA015A1T]	F49L004UA@TSOP40 [SA409T-B4002]
F49L040A@PLCC32 [SA015A1T]	F49L040A@VSOP32 [SA620-B4807]
F49L160BA@TSOP48 [SB247-B4806]	F49L160UA@TSOP48 [SB247-B4806]
F49L400BA@TSOP48 [SB247-B4806]	F49L400UA@TSOP48 [SB247-B4806]
F49L800BA@TSOP48 [SB247-B4806]	F49L800UA@TSOP48 [SB247-B4806]

ELECTRONIC ARRAYS

E (E) PROM/FRAM/NVRAM

EA2716

EMTC

E(E) PROM/FRAM/NVRAM

EM24C02	EM24C02@S0IC8 [SA602A]
EM24C02@TSSOP8 [SA026-B3201]	EM24C04
EM24C04@S0IC8 [SA602A]	EM24C04@TSSOP8 [SA026-B3201]
EM24C08	EM24C08@S0IC8 [SA602A]
EM24C08@TSSOP8 [SA026-B3201]	EM24C16
EM24C16@S0IC8 [SA602A]	EM24C16@TSSOP8 [SA026-B3201]
EM25SL512@S0IC8 [SA602A]	EM29SF002AB
EM29SF002AB@PLCC32 [SA015A1T]	
EM29SF002AB@TSOP32 [SA410T-B4001]	EM29SF002AT@PLCC32 [SA015A1T]
EM29SF002AT	
EM29SF002AT@TSOP32 [SA410T-B4001]	EM29SF002NAB@PLCC32 [SA015A1T]
EM29SF002NAB	
EM29SF002NAB@TSOP32 [SA410T-B4001]	EM29SF002NAT@PLCC32 [SA015A1T]
EM29SF002NAT	
EM29SF002NAT@TSOP32 [SA410T-B4001]	

EON

E(E) PROM/FRAM/NVRAM

EN25B05(Bottom Boot)@SOP8(4.0) [SA602A]	
EN25B05(Bottom Boot)@SOP8(5.4) [SA605B]	
EN25B05(Bottom Boot)@VDFN8 [SA683]	
EN25B05(Top Boot)@SOP8(4.0) [SA602A]	
EN25B05(Top Boot)@SOP8(5.4) [SA605B]	
EN25B05(Top Boot)@VDFN8 [SA683]	
EN25B10(Bottom Boot)@SOP8(4.0) [SA602A]	
EN25B10(Bottom Boot)@SOP8(5.4) [SA605B]	
EN25B10(Bottom Boot)@VDFN8 [SA683]	
EN25B10(Top Boot)@SOP8(4.0) [SA602A]	
EN25B10(Top Boot)@SOP8(5.4) [SA605B]	
EN25B10(Top Boot)@VDFN8 [SA683]	
EN25B16(Bottom Boot)@SOP8 [SA605B]	
EN25B16(Bottom Boot)@VFQFPN8 [SA684]	
EN25B16(Top Boot)@SOP8 [SA605B]	
EN25B16(Top Boot)@VFQFPN8 [SA684]	
EN25B20(Bottom Boot)@SOP8(4.0) [SA602A]	
EN25B20(Bottom Boot)@SOP8(5.4) [SA605B]	
EN25B20(Bottom Boot)@VDFN8 [SA683]	
EN25B20(Top Boot)@SOP8(4.0) [SA602A]	
EN25B20(Top Boot)@SOP8(5.4) [SA605B]	
EN25B20(Top Boot)@VDFN8 [SA683]	
EN25B32(Bottom Boot)@SOP16 [SA404]	
EN25B32(Bottom Boot)@SOP8 [SA605B]	
EN25B32(Bottom Boot)@VDFN8 [SA684]	
EN25B32(Top Boot)@SOP16 [SA404]	EN25B32(Top Boot)@SOP8 [SA605B]
EN25B32(Top Boot)@VDFN8 [SA684]	
EN25B40(Bottom Boot)@SOP8(4.0) [SA602A]	
EN25B40(Bottom Boot)@SOP8(5.4) [SA605B]	
EN25B40(Bottom Boot)@VDFN8 [SA683]	
EN25B40(Top Boot)@SOP8(4.0) [SA602A]	
EN25B40(Top Boot)@SOP8(5.4) [SA605B]	
EN25B40(Top Boot)@VDFN8 [SA683]	
EN25B64(Bottom Boot)@SOP16 [SA404]	

EN25B64(Bottom Boot)@VDFN8 [SA684]	
EN25B64(Top Boot)@SOP16 [SA404]	EN25B64(Top Boot)@VDFN8 [SA684]
EN25B80(Bottom Boot)@SOP8(4.0) [SA602A]	
EN25B80(Bottom Boot)@SOP8(5.4) [SA605B]	
EN25B80(Bottom Boot)@VDFN8 [SA683]	
EN25B80(Top Boot)@SOP8(4.0) [SA602A]	
EN25B80(Top Boot)@SOP8(5.4) [SA605B]	
EN25B80(Top Boot)@VDFN8 [SA683]	EN25D16
EN25D16@SOP16 [SA404]	EN25D16@SOP8 [SA605B]
EN25D16@VDFN8 [SA684]	EN25D80
EN25D80@SOP8 [SA605B]	EN25D80@VDFN8 [SA683]
EN25F05@SOP8(4.0) [SA602A]	EN25F05@SOP8(5.4) [SA605B]
EN25F05@VDFN8 [SA683]	EN25F10@SOP8(4.0) [SA602A]
EN25F10@SOP8(5.4) [SA605B]	EN25F10@VDFN8 [SA683]
EN25F16	EN25F16@SOP16 [SA404]
EN25F16@SOP8 [SA605B]	EN25F16@VDFN8 [SA684]
EN25F20@SOP8(4.0) [SA602A]	EN25F20@SOP8(5.4) [SA605B]
EN25F20@VDFN8 [SA683]	EN25F32
EN25F32@SOP16 [SA404]	EN25F32@SOP8 [SA605B]
EN25F32@VDFN8 [SA684]	
EN25F40(fast mode)@SOP8(150mil) [SA602A]	
EN25F40(fast mode)@SOP8(200mil) [SA605B]	
EN25F40(fast mode)@VDFN8 [SA683]	EN25F40@SOP8(150mil) [SA602A]
EN25F40@SOP8(200mil) [SA605B]	EN25F40@VDFN8 [SA683]
EN25F80	EN25F80@SOP8 [SA605B]
EN25F80@VDFN8 [SA683]	EN25LF05@SOP8(4.0) [SA602A]
EN25LF05@SOP8(5.4) [SA605B]	EN25LF05@VDFN8 [SA683]
EN25LF10@SOP8(4.0) [SA602A]	EN25LF10@SOP8(5.4) [SA605B]
EN25LF10@VDFN8 [SA683]	EN25LF20@SOP8 [SA605B]
EN25LF20@VDFN8 [SA683]	EN25LF40
EN25LF40@SOP8(150mil) [SA602A]	EN25LF40@SOP8(200mil) [SA605B]
EN25LF40@VDFN8 [SA683]	EN25LV010@S0IC8 [SA602A]
EN25LV010@VFQFPN8 [SA684]	EN25LV020@S0IC8 [SA602A]
EN25LV020@VFQFPN8 [SA684]	EN25LV040@S0IC8 [SA602A]
EN25LV040@VFQFPN8 [SA684]	EN25LV080@S0IC8 [SA602A]
EN25LV080@VFQFPN8 [SA684]	EN25LV160@S0IC8 [SA602A]
EN25LV160@VFQFPN8 [SA684]	EN25LV512@S0IC8 [SA602A]
EN25LV512@VFQFPN8 [SA684]	EN25P05@SOP8(4.0) [SA602A]
EN25P05@SOP8(5.4) [SA605B]	EN25P05@VDFN8 [SA683]
EN25P10@SOP8(4.0) [SA602A]	EN25P10@SOP8(5.4) [SA605B]
EN25P10@VDFN8 [SA683]	EN25P16@SOP8 [SA605B]
EN25P16@VFQFPN8 [SA684]	EN25P20@SOP8(4.0) [SA602A]
EN25P20@SOP8(5.4) [SA605B]	EN25P20@VDFN8 [SA683]
EN25P32@SOP16 [SA404]	EN25P32@SOP8 [SA605B]
EN25P32@VDFN8 [SA684]	EN25P40@SOP8(4.0) [SA602A]
EN25P40@SOP8(5.4) [SA605B]	EN25P40@VDFN8 [SA683]
EN25P64@SOP16 [SA404]	EN25P64@VDFN8 [SA684]
EN25P80@SOP8(4.0) [SA602A]	EN25P80@SOP8(5.4) [SA605B]
EN25P80@VDFN8 [SA683]	EN25Q16
EN25Q16@SOP16 [SA404]	EN25Q16@SOP8(4.0) [SA602A]
EN25Q16@SOP8(5.4) [SA605B]	EN25Q16@VDFN8 [SA684]
EN25Q32A	EN25Q32A@SOP8 [SA605B]
EN25Q32A@VDFN8 [SA683]	EN25Q40@SOP8 [SA605B]
EN25Q40@VDFN8 [SA683]	EN25Q64@SOP16 [SA404]
EN25Q64@SOP8 [SA605B]	EN25Q64@VDFN8(5*6mm) [SA683]
EN25Q64@VDFN8(6*8mm) [SA684]	EN25Q80A@SOP8(4.0) [SA602A]
EN25Q80A@SOP8(5.4) [SA605B]	EN25Q80A@VDFN8 [SA683]
EN25S10@SOP8 [SA602A]	EN25S10@VDFN8 [SA724]
EN25S16@SOP8 [SA605B]	EN25S16@VFQFPN8 [SA684]

EN25S20@SOP8 [SA602A]
EN25S32(Bottom Boot)@SOP16 [SA404]
EN25S32(Bottom Boot)@SOP8 [SA605B]
EN25S32(Bottom Boot)@VDFN8 [SA684]
EN25S32(Top Boot)@SOP16 [SA404]
EN25S32(Top Boot)@VDFN8 [SA684]
EN25S40@VDFN8(2*3mm) [SA724]
EN25S80@SOP8(150mil) [SA602A]
EN25S80@VDFN8 [SA683]
EN25T16@VFQFPN8 [SA684]
EN25T40@SOP8(209mil) [SA605B]
EN25T80
EN25T80@VDFN8 [SA683]
EN27C010@PLCC32 [SA015A1T]
EN27C512@PLCC32
EN29F002AB@PLCC32 [SA015A1T]
EN29F002ANB
EN29F002ANB@TSOP32 [SA410T-B4001]
EN29F002ANT
EN29F002ANT@TSOP32 [SA410T-B4001]
EN29F002AT
EN29F002AT@TSOP32 [SA410T-B4001]
EN29F002B@PLCC32 [SA015A1T]
EN29F002NB
EN29F002NB@TSOP32 [SA410T-B4001]
EN29F002NT@PLCC32 [SA015A1T]
EN29F002T
EN29F002T@TSOP32 [SA410T-B4001]
EN29F010@PLCC32 [SA015A1T]
EN29F010@VSOP32 [SA620-B4807]
EN29F040@PLCC32 [SA015A1T]
EN29F040A
EN29F040A@TSOP32 [SA410T-B4001]
EN29F512
EN29F512@TSOP32 [SA410T-B4001]
EN29F800B@TSOP48 [SB247-B4806]
EN29LV010@PLCC32 [SA015A1T]
EN29LV010@VSOP32 [SA620-B4807]
EN29LV040@TSOP32 [SA410T-B4001]
EN29LV040A
EN29LV040A@TSOP32 [SA410T-B4001]
EN29LV160AB@TSOP48 [SB247-B4806]
EN29LV160B@TSOP48 [SB247-B4806]
EN29LV160BT@TSOP48 [SB247-B4806]
EN29LV320AB@TSOP48 [SB247-B4806]
EN29LV320B@TSOP48 [SB247-B4806]
EN29LV400AB@TSOP48 [SB247-B4806]
EN29LV400B@TSOP48 [SB247-B4806]
EN29LV512@PLCC32 [SA015A1T]
EN29LV512@VSOP32 [SA620-B4807]
EN29LV640H@TSOP48 [SB247-B4806]
EN29LV640T@TSOP48 [SB247-B4806]
EN29LV641L@TSOP48 [SB247-B4806]
EN29LV800AT@TSOP48 [SB247-B4806]
EN29LV800BB@TSOP48 [SB247-B4806]
EN29LV800CB@TSOP48 [SB247-B4806]
EN29LV800T@TSOP48 [SB247-B4806]
EN29PL064@TSOP48 [SB247-B4806]
EN29SL160T@TSOP48 [SB247-B4806]

EN25S20@VDFN8 [SA724]

EN25S32(Top Boot)@SOP8 [SA605B]
EN25S40@SOP8 [SA602A]
EN25S40@VDFN8(5*6mm) [SA683]
EN25S80@SOP8(200mil) [SA605B]
EN25T16@SOP8 [SA605B]
EN25T40@SOP8(150mil) [SA602A]
EN25T40@VDFN8 [SA683]
EN25T80@SOP8 [SA605B]
EN27C010
EN27C512
EN29F002AB
EN29F002AB@TSOP32 [SA410T-B4001]
EN29F002ANB@PLCC32 [SA015A1T]

EN29F002ANT@PLCC32 [SA015A1T]

EN29F002AT@PLCC32 [SA015A1T]
EN29F002B
EN29F002B@TSOP32 [SA410T-B4001]
EN29F002NB@PLCC32 [SA015A1T]
EN29F002NT
EN29F002NT@TSOP32 [SA410T-B4001]
EN29F002T@PLCC32 [SA015A1T]
EN29F010
EN29F010@TSOP32 [SA410T-B4001]
EN29F040
EN29F040@TSOP32 [SA410T-B4001]
EN29F040A@PLCC32 [SA015A1T]
EN29F080@TSOP40 [SA409T-B4002]
EN29F512@PLCC32 [SA015A1T]
EN29F512@VSOP32 [SA620-B4807]
EN29F800T@TSOP48 [SB247-B4806]
EN29LV010@TSOP32 [SA410T-B4001]
EN29LV040@PLCC32 [SA015A1T]
EN29LV040@VSOP32 [SA620-B4807]
EN29LV040A@PLCC32 [SA015A1T]
EN29LV040A@VSOP32 [SA620-B4807]
EN29LV160AT@TSOP48 [SB247-B4806]
EN29LV160BB@TSOP48 [SB247-B4806]
EN29LV160T@TSOP48 [SB247-B4806]
EN29LV320AT@TSOP48 [SB247-B4806]
EN29LV320T@TSOP48 [SB247-B4806]
EN29LV400AT@TSOP48 [SB247-B4806]
EN29LV400T@TSOP48 [SB247-B4806]
EN29LV512@TSOP32 [SA410T-B4001]
EN29LV640B@TSOP48 [SB247-B4806]
EN29LV640L@TSOP48 [SB247-B4806]
EN29LV641H@TSOP48 [SB247-B4806]
EN29LV800AB@TSOP48 [SB247-B4806]
EN29LV800B@TSOP48 [SB247-B4806]
EN29LV800BT@TSOP48 [SB247-B4806]
EN29LV800CT@TSOP48 [SB247-B4806]
EN29PL032@TSOP48 [SB247-B4806]
EN29SL160B@TSOP48 [SB247-B4806]
EN29SL400B@TSOP48 [SB247-B4806]

EN29SL400T@TSOP48 [SB247-B4806]
EN29SL800T@TSOP48 [SB247-B4806]

EN29SL800B@TSOP48 [SB247-B4806]

ESMT

E(E)PROM/FRAM/NVRAM

EM25LV010@S0IC8 [SA602A]	EM25LV010@VFQFPN8 [SA684]
EM25LV512@S0IC8 [SA602A]	EM25LV512@VFQFPN8 [SA684]
F25L004AB	F25L004AB@S0IC8(150mil) [SA602A]
F25L004AB@S0IC8(200mil) [SA605B]	F25L004AT
F25L004AT@S0IC8(150mil) [SA602A]	F25L004AT@S0IC8(200mil) [SA605B]
F25L008AB@S0IC8 [SA605B]	F25L008AT@S0IC8 [SA605B]
F25L016AB@S0IC8 [SA605B]	F25L016AT@S0IC8 [SA605B]
F25L01PA	F25L01PA@S0IC8(150mil) [SA602A]
F25L01PA@S0IC8(200mil) [SA605B]	F25L02PA
F25L02PA(2F)@S0IC8(150mil) [SA602A]	
F25L02PA(2F)@S0IC8(200mil) [SA605B]	
F25L02PA(2F)@WS0N8 [SA683]	F25L02PA@S0IC8(150mil) [SA602A]
F25L02PA@S0IC8(200mil) [SA605B]	F25L04PA
F25L04PA@S0IC8(150mil) [SA602A]	F25L04PA@S0IC8(200mil) [SA605B]
F25L08PA(2G)	
F25L08PA(2G)@S0IC8(150mil) [SA602A]	
F25L08PA(2G)@S0IC8(200mil) [SA605B]	
F25L08PA(2G)@WS0N8 [SA683]	
F25L08PA(AAI-PROGRAM)@S0IC8 [SA605B]	
F25L08PA(PAGE-PROGRAM)@S0IC8 [SA605B]	
F25L16PA(AAI-PROGRAM)@S0IC8 [SA605B]	
F25L16PA(PAGE-PROGRAM)@S0IC8 [SA605B]	
F25L320PA(4K OTP)@S0IC16	F25L320PA(4K OTP)@S0IC8
F25L320PA@S0IC16 [SA404]	F25L320PA@S0IC8 [SA605B]
F25L32PA(4K OTP)(new)@S0IC16	F25L32PA(4K OTP)(new)@S0IC8
F25L32PA(4K OTP)@S0IC16	F25L32PA(4K OTP)@S0IC8
F25L32PA(new)@S0IC16 [SA404]	F25L32PA(new)@S0IC8 [SA605B]
F25L32PA@S0IC16 [SA404]	F25L32PA@S0IC8 [SA605B]
F25L32QA(4K OTP)@S0IC16	F25L32QA(4K OTP)@S0IC8
F25L32QA@S0IC16 [SA404]	F25L32QA@S0IC8 [SA605B]
F49B002UA	F49B002UA@PLCC32 [SA015A1T]
F49L004BA@PLCC32 [SA015A1T]	F49L004BA@TSOP40 [SA409T-B4002]
F49L004UA@PLCC32 [SA015A1T]	F49L004UA@TSOP40 [SA409T-B4002]
F49L040A@PLCC32 [SA015A1T]	F49L040A@VSOP32 [SA620-B4807]
F49L160BA@TSOP48 [SB247-B4806]	F49L160UA@TSOP48 [SB247-B4806]
F49L320BA@TSOP48 [SB247-B4806]	F49L320UA@TSOP48 [SB247-B4806]
F49L400BA@TSOP48 [SB247-B4806]	F49L400UA@TSOP48 [SB247-B4806]
F49L800BA@TSOP48 [SB247-B4806]	F49L800UA@TSOP48 [SB247-B4806]

EXCELSEMI

E(E)PROM/FRAM/NVRAM

ES25M16	ES25M16@SOP16 [SA404]
ES25M16@SOP8[150 mil] [SA605B]	ES25M16@SOP8[208 mil] [SA602A]
ES25M40	ES25M40@SOP16 [SA404]
ES25M40@SOP8[150 mil] [SA605B]	ES25M40@SOP8[208 mil] [SA602A]
ES25M80	ES25M80@SOP16 [SA404]
ES25M80@SOP8[150 mil] [SA605B]	ES25M80@SOP8[208 mil] [SA602A]
ES25P16@SOP8 [SA605B]	ES25P40@SOP8 [SA605B]

ES25P80@SOP8 [SA605B]
ES29LV160DB@TSOP48 [SB247-B4806]
ES29LV160DT@TSOP48 [SB247-B4806]
ES29LV160ET@TSOP48 [SB247-B4806]
ES29LV160FT@TSOP48 [SB247-B4806]
ES29LV320DT@TSOP48 [SB247-B4806]
ES29LV320ET@TSOP48 [SB247-B4806]
ES29LV320FT@TSOP48 [SB247-B4806]
ES29LV400DT@TSOP48 [SB247-B4806]
ES29LV400ET@TSOP48 [SB247-B4806]
ES29LV800DB@TSOP48 [SB247-B4806]
ES29LV800DT@TSOP48 [SB247-B4806]
ES29LV800ET@TSOP48 [SB247-B4806]

ES29LV160DB@PSOP44 [SA638]
ES29LV160DT@PSOP44 [SA638]
ES29LV160EB@TSOP48 [SB247-B4806]
ES29LV160FB@TSOP48 [SB247-B4806]
ES29LV320DB@TSOP48 [SB247-B4806]
ES29LV320EB@TSOP48 [SB247-B4806]
ES29LV320FB@TSOP48 [SB247-B4806]
ES29LV400DB@TSOP48 [SB247-B4806]
ES29LV400EB@TSOP48 [SB247-B4806]
ES29LV800DB@PSOP44 [SA638]
ES29LV800DT@PSOP44 [SA638]
ES29LV800EB@TSOP48 [SB247-B4806]

EXEL

E(E) PROM/FRAM/NVRAM

XL24C01A
XL24C04
XL24C16@S0IC8 [SA602A]
XL28C256
XL28C256@TSOP28 [SA430T-B4003]
XL9010(F) [SA602A]
XL9020(F) [SA602A]
XL9040(F) [SA602A]
XL9346@S0IC8 [SA602A]
XL93CS56@S0IC8 [SA602A]
XL93CS66
XL93CS66@TSSOP8 [SA026-B3201]
XL93LC46@S0IC8 [SA602A]
XL93LC46A@S0IC8 [SA602A]
XL93LC56@S0IC8 [SA602A]
XL93LC56A@S0IC8 [SA602A]
XL93LC66A@S0IC8 [SA602A]
XLE28C16A
XLE28C16B
XLE28C16B@S0IC24 [SA404]
XLM28C16A@PLCC32 [SA015A1T]
XLS2816A
XLS2817A
XLS28C16A@PLCC32 [SA015A1T]
XLS28C16B@PLCC32 [SA015A1T]
XLS28C64B
XLS28C64B@S0IC28 [SA404]
XLS93C46@S0IC8 [SA602A]
XLS93C56@S0IC8 [SA602A]
XLS93C66@S0IC8 [SA602A]
XLS93CS46@S0IC8 [SA602A]
XLS93LC06
XLS93LC66

XL24C02
XL24C16
XL24C32
XL28C256@PLCC32 [SA015A1T]
XL9010
XL9020
XL9040
XL9346
XL93CS56
XL93CS56@TSSOP8 [SA026-B3201]
XL93CS66@S0IC8 [SA602A]
XL93LC46
XL93LC46A
XL93LC56
XL93LC56A
XL93LC66A
XL9764
XLE28C16A@PLCC32 [SA015A1T]
XLE28C16B@PLCC32 [SA015A1T]
XLM28C16A
XLS2804A
XLS2816A@PLCC32 [SA015A1T]
XLS28C16A
XLS28C16B
XLS28C16B@S0IC24 [SA404]
XLS28C64B@PLCC32 [SA015A1T]
XLS93C46
XLS93C56
XLS93C66
XLS93CS46
XLS93CS46@TSSOP8 [SA026-B3201]
XLS93LC06@S0IC8 [SA602A]
XLS93LC66@S0IC8 [SA602A]

FAIRCHILD

E(E) PROM/FRAM/NVRAM

FM24C02(M8)@S0IC8 [SA602A]

FM24C02(MT8)@TSSOP8 [SA026-B3201]	
FM24C02(N)	FM24C03(M8)@SOIC8 [SA602A]
FM24C03(MT8)@TSSOP8 [SA026-B3201]	
FM24C03(N)	FM24C04(M8)@SOIC8 [SA602A]
FM24C04(MT8)@TSSOP8 [SA026-B3201]	
FM24C04(N)	FM24C05(M8)@SOIC8 [SA602A]
FM24C05(MT8)@TSSOP8 [SA026-B3201]	
FM24C05(N)	FM24C08(M8)@SOIC8 [SA602A]
FM24C08(MT8)@TSSOP8 [SA026-B3201]	
FM24C08(N)	FM24C09(M8)@SOIC8 [SA602A]
FM24C09(MT8)@TSSOP8 [SA026-B3201]	
FM24C09(N)	FM24C128(MT8)@TSSOP8
FM24C128(MW8)@SOIC8 [SA602A]	FM24C128(N)
FM24C16(M8)@SOIC8 [SA602A]	
FM24C16(MT8)@TSSOP8 [SA026-B3201]	
FM24C16(N)	FM24C17(M8)@SOIC8 [SA602A]
FM24C17(MT8)@TSSOP8 [SA026-B3201]	
FM24C17(N)	FM24C256(M8)@SOIC8 [SA602A]
FM24C256(N)	FM24C32(M8)@SOIC8 [SA602A]
FM24C32(N)	FM27C010
FM27C010@PLCC32 [SA015A1T]	FM27C010@TSOP32 [SA410T-B4001]
FM27C040	FM27C040@PLCC32 [SA015A1T]
FM27C040@TSOP32 [SA410T-B4001]	FM27C256
FM27C256@PLCC32 [SA015A1T]	FM27C256Q
FM27C256Q@PLCC32 [SA015A1T]	FM27C512
FM27C512@PLCC32 [SA015A1T]	
FM93C06(M8)(08bit)@SOIC8 [SA602A]	
FM93C06(M8)(16bit)@SOIC8 [SA602A]	
FM93C06(MT8)(08bit)@TSSOP8 [SA026-B3201]	
FM93C06(MT8)(16bit)@TSSOP8 [SA026-B3201]	
FM93C06(N)(08bit)	FM93C06(N)(16bit)
FM93C14(16bit)	FM93C46(M8)@SOIC8 [SA602A]
FM93C46(MT8)@TSSOP8	FM93C46(N)
FM93C46A(M8)(08bit)@SOIC8 [SA602A]	
FM93C46A(M8)(16bit)@SOIC8 [SA602A]	
FM93C46A(MT8)(08bit)@TSSOP8 [SA026-B3201]	
FM93C46A(MT8)(16bit)@TSSOP8 [SA026-B3201]	
FM93C46A(N)(08bit)	FM93C46A(N)(16bit)
FM93C56(M8)@SOIC8 [SA602A]	FM93C56(MT8)@TSSOP8
FM93C56(N)	
FM93C56A(M8)(08bit)@SOIC8 [SA602A]	
FM93C56A(M8)(16bit)@SOIC8 [SA602A]	
FM93C56A(MT8)(08bit)@TSSOP8 [SA026-B3201]	
FM93C56A(MT8)(16bit)@TSSOP8 [SA026-B3201]	
FM93C56A(N)(08bit)	FM93C56A(N)(16bit)
FM93C66(M8)@SOIC8 [SA602A]	FM93C66(MT8)@TSSOP8
FM93C66(N)	
FM93C66A(M8)(08bit)@SOIC8 [SA602A]	
FM93C66A(M8)(16bit)@SOIC8 [SA602A]	
FM93C66A(MT8)(08bit)@TSSOP8 [SA026-B3201]	
FM93C66A(MT8)(16bit)@TSSOP8 [SA026-B3201]	
FM93C66A(N)(08bit)	FM93C66A(N)(16bit)
FM93C76(M8)(16bit)@SOIC8 [SA602A]	
FM93C76(MT8)(16bit)@TSSOP8 [SA026-B3201]	
FM93C76(N)(16bit)	
FM93C76A(M8)(08bit)@SOIC8 [SA602A]	
FM93C76A(M8)(16bit)@SOIC8 [SA602A]	
FM93C76A(MT8)(08bit)@TSSOP8 [SA026-B3201]	
FM93C76A(MT8)(16bit)@TSSOP8 [SA026-B3201]	

FM93C76A(N)(08bit)	FM93C76A(N)(16bit)
FM93C86(M8)(16bit)@S0IC8 [SA602A]	
FM93C86(MT8)(16bit)@TSS0P8 [SA026-B3201]	
FM93C86(N)(16bit)	
FM93C86A(M8)(08bit)@S0IC8 [SA602A]	
FM93C86A(M8)(16bit)@S0IC8 [SA602A]	
FM93C86A(MT8)(08bit)@TSS0P8 [SA026-B3201]	
FM93C86A(MT8)(16bit)@TSS0P8 [SA026-B3201]	
FM93C86A(N)(08bit)	FM93C86A(N)(16bit)
FM93CS06(M8)@S0IC8 [SA602A]	
FM93CS06(MT8)@TSS0P8 [SA026-B3201]	
FM93CS06(N)	FM93CS46(M8)@S0IC8 [SA602A]
FM93CS46(MT8)@TSS0P8 [SA026-B3201]	
FM93CS46(N)	FM93CS56(M8)@S0IC8 [SA602A]
FM93CS56(MT8)@TSS0P8 [SA026-B3201]	
FM93CS56(N)	FM93CS66(M8)@S0IC8 [SA602A]
FM93CS66(MT8)@TSS0P8 [SA026-B3201]	
FM93CS66(N)	FM93S46(M8)@S0IC8 [SA602A]
FM93S46(MT8)@TSS0P8 [SA026-B3201]	
FM93S46(N)	FM93S56(M8)@S0IC8 [SA602A]
FM93S56(MT8)@TSS0P8 [SA026-B3201]	
FM93S56(N)	FM93S66(M8)@S0IC8 [SA602A]
FM93S66(MT8)@TSS0P8 [SA026-B3201]	
FM93S66(N)	MM2716
MM2716E	NM24C02(M8)@S0IC8 [SA602A]
NM24C02(MT8)@TSS0P8 [SA026-B3201]	
NM24C02(N)	NM24C02L(M8)@S0IC8 [SA602A]
NM24C02L(MT8)@TSS0P8 [SA026-B3201]	
NM24C02L(N)	NM24C03(M8)@S0IC8 [SA602A]
NM24C03(MT8)@TSS0P8 [SA026-B3201]	
NM24C03(N)	NM24C04(M8)@S0IC8 [SA602A]
NM24C04(MT8)@TSS0P8 [SA026-B3201]	
NM24C04(N)	NM24C05(M8)@S0IC8 [SA602A]
NM24C05(MT8)@TSS0P8 [SA026-B3201]	
NM24C05(N)	NM24C08(M8)@S0IC8 [SA602A]
NM24C08(MT8)@TSS0P8 [SA026-B3201]	
NM24C08(N)	NM24C09(M8)@S0IC8 [SA602A]
NM24C09(MT8)@TSS0P8 [SA026-B3201]	
NM24C09(N)	NM24C16(M8)@S0IC8 [SA602A]
NM24C16(MT8)@TSS0P8 [SA026-B3201]	
NM24C16(N)	NM24C17(M8)@S0IC8 [SA602A]
NM24C17(MT8)@TSS0P8 [SA026-B3201]	
NM24C17(N)	NM24C65(M8)S0IC8 [SA602A]
NM24C65(N)	NM27C010
NM27C010@PLCC32 [SA015A1T]	NM27C010@TSOP32 [SA410T-B4001]
NM27C020	NM27C020@PLCC32 [SA015A1T]
NM27C020@TSOP32 [SA410T-B4001]	NM27C020Q
NM27C020Q@PLCC32 [SA015A1T]	NM27C020Q@TSOP32 [SA410T-B4001]
NM27C040	NM27C040@PLCC32 [SA015A1T]
NM27C040@TSOP32 [SA410T-B4001]	NM27C128
NM27C128@PLCC32 [SA015A1T]	NM27C210
NM27C210@PLCC44 [SA244]	NM27C240
NM27C240@PLCC44 [SA244]	NM27C256
NM27C256@PLCC32 [SA015A1T]	NM27C512
NM27C512@PLCC32 [SA015A1T]	NM27C64Q
NM27C64Q@PLCC32 [SA015A1T]	NM27LC256
NM27LC256@PLCC32 [SA015A1T]	NM27LC512
NM27LC512@PLCC32 [SA015A1T]	NM27LV010
NM27LV010@PLCC32 [SA015A1T]	NM27LV010@TSOP32 [SA410T-B4001]

NM27LV210	NM27LV210@PLCC44 [SA244]
NM27LV512	NM27LV512@PLCC32 [SA015A1T]
NM27P040	NM27P040@PLCC32 [SA015A1T]
NM27P040@TSOP32 [SA410T-B4001]	NM27P210
NM27P210@PLCC44 [SA244]	NM27P512
NM27P512@PLCC32 [SA015A1T]	
NM93C66(M8)(16bit)@S0IC8 [SA602A]	
NM93C66(MT8)(16bit)@TSSOP8 [SA026-B3201]	
NM93C66(N)(16bit)	NM93CS06(M8)@S0IC8 [SA602A]
NM93CS06(MT8)@TSSOP8 [SA026-B3201]	
NM93CS06(N)	NM93CS46(M8)@S0IC8 [SA602A]
NM93CS46(MT8)@TSSOP8 [SA026-B3201]	
NM93CS46(N)	NM93CS56(M8)@S0IC8 [SA602A]
NM93CS56(MT8)@TSSOP8 [SA026-B3201]	
NM93CS56(N)	NM93CS66(M8)@S0IC8 [SA602A]
NM93CS66(MT8)@TSSOP8 [SA026-B3201]	
NM93CS66(N)	NMC2732
NMC27C010	NMC27C010@PLCC32 [SA015A1T]
NMC27C010@TSOP32 [SA410T-B4001]	NMC27C1024
NMC27C1024@PLCC44 [SA244]	NMC27C128B
NMC27C128B@PLCC32 [SA015A1T]	NMC27C128BN
NMC27C128BN@PLCC32 [SA015A1T]	NMC27C128BQ
NMC27C128BQ@PLCC32 [SA015A1T]	NMC27C128CQ
NMC27C16	NMC27C16BQ
NMC27C16BQE	NMC27C16H
NMC27C16HQ	NMC27C16Q
NMC27C256	NMC27C256@PLCC32 [SA015A1T]
NMC27C256B	NMC27C256B@PLCC32 [SA015A1T]
NMC27C256Q	NMC27C256Q@PLCC32 [SA015A1T]
NMC27C32	NMC27C32B
NMC27C32BQ	NMC27C32E
NMC27C32EH	NMC27C32H
NMC27C512	NMC27C512@PLCC32 [SA015A1T]
NMC27C512A	NMC27C512A@PLCC32 [SA015A1T]
NMC27C512AN	NMC27C512AN@PLCC32 [SA015A1T]
NMC27C64	NMC27C64(BN)
NMC27C64(N)	NMC27CP128
NMC9346(M8)(16bit)@S0IC8 [SA602A]	
NMC9346(MT8)(16bit)@TSSOP8 [SA026-B3201]	
NMC9346(N)(16bit)	
NMC93C46(M8)(16bit)@S0IC8 [SA602A]	
NMC93C46(MT8)(16bit)@TSSOP8 [SA026-B3201]	
NMC93C46(N)(16bit)	
NMC93C46A(M8)(16bit)@S0IC8 [SA602A]	
NMC93C46A(MT8)(16bit)@TSSOP8 [SA026-B3201]	
NMC93C46A(N)(16bit)	
NMC93C56(M8)(16bit)@S0IC8 [SA602A]	
NMC93C56(MT8)(16bit)@TSSOP8 [SA026-B3201]	
NMC93C56(N)(16bit)	
NMC93C66(M8)(16bit)@S0IC8 [SA602A]	
NMC93C66(MT8)(16bit)@TSSOP8 [SA026-B3201]	
NMC93C66(N)(16bit)	NMC93CS06(M8)@S0IC8 [SA602A]
NMC93CS06(MT8)@TSSOP8 [SA026-B3201]	
NMC93CS06(N)	NMC93CS46(M8)@S0IC8 [SA602A]
NMC93CS46(MT8)@TSSOP8 [SA026-B3201]	
NMC93CS46(N)	NMC93CS56(M8)@S0IC8 [SA602A]
NMC93CS56(MT8)@TSSOP8 [SA026-B3201]	
NMC93CS56(N)	NMC93CS66(M8)@S0IC8 [SA602A]
NMC93CS66(MT8)@TSSOP8 [SA026-B3201]	

FIDELIX

E(E) PROM/FRAM/NVRAM

FM25Q16	FM25Q16@SOP8 [SA605B]
FM25Q16@WS0N8 [SA683]	FM25Q16A
FM25Q16A@SOP8 [SA602A]	FM25Q16A@WS0N8 [SA683]

FMD

E(E) PROM/FRAM/NVRAM

FT93C46(08bit)	FT93C46(08bit)@SOP8 [SA602A]
FT93C46(08bit)@TSSOP8 [SA026-B3201]	
FT93C46(16bit)	FT93C46(16bit)@SOP8 [SA602A]
FT93C46(16bit)@TSSOP8 [SA026-B3201]	
FT93C46A(08bit)	FT93C46A(08bit)@SOP8 [SA602A]
FT93C46A(08bit)@TSSOP8 [SA026-B3201]	
FT93C46A(16bit)	FT93C46A(16bit)@SOP8 [SA602A]
FT93C46A(16bit)@TSSOP8 [SA026-B3201]	
FT93C56(08bit)	FT93C56(08bit)@SOP8 [SA602A]
FT93C56(08bit)@TSSOP8 [SA026-B3201]	
FT93C56(16bit)	FT93C56(16bit)@SOP8 [SA602A]
FT93C56(16bit)@TSSOP8 [SA026-B3201]	
FT93C56A(08bit)	FT93C56A(08bit)@SOP8 [SA602A]
FT93C56A(08bit)@TSSOP8 [SA026-B3201]	
FT93C56A(16bit)	FT93C56A(16bit)@SOP8 [SA602A]
FT93C56A(16bit)@TSSOP8 [SA026-B3201]	
FT93C66(08bit)	FT93C66(08bit)@S0IC8 [SA602A]
FT93C66(08bit)@TSSOP8 [SA026-B3201]	
FT93C66(16bit)	FT93C66(16bit)@SOP8 [SA602A]
FT93C66(16bit)@TSSOP8 [SA026-B3201]	
FT93C66A(08bit)	FT93C66A(08bit)@SOP8 [SA602A]
FT93C66A(08bit)@TSSOP8 [SA026-B3201]	
FT93C66A(16bit)	FT93C66A(16bit)@SOP8 [SA602A]
FT93C66A(16bit)@TSSOP8 [SA026-B3201]	
FT93C86(08bit)	FT93C86(08bit)@SOP8 [SA602A]
FT93C86(08bit)@TSSOP8 [SA026-B3201]	
FT93C86(16bit)	FT93C86(16bit)@SOP8 [SA602A]
FT93C86(16bit)@TSSOP8 [SA026-B3201]	
FT93C86A(08bit)	FT93C86A(08bit)@SOP8 [SA602A]
FT93C86A(08bit)@TSSOP8 [SA026-B3201]	
FT93C86A(16bit)	FT93C86A(16bit)@SOP8 [SA602A]
FT93C86A(16bit)@TSSOP8 [SA026-B3201]	

FORCE TECHNOLOGIES

E(E) PROM/FRAM/NVRAM

FT24C01	FT24C01@S0IC8 [SA602A]
FT24C01@TSOP8 [SA026-B3201]	FT24C01A
FT24C01A@S0IC8 [SA602A]	FT24C01A@TSOP8 [SA026-B3201]
FT24C02	FT24C02@S0IC8 [SA602A]
FT24C02@TSOP8 [SA026-B3201]	FT24C02A

FT24C02A@S0IC8 [SA602A]
FT24C04
FT24C04@TSOP8 [SA026-B3201]
FT24C04A@S0IC8 [SA602A]
FT24C08
FT24C08@TSOP8 [SA026-B3201]
FT24C08A@S0IC8 [SA602A]
FT24C128
FT24C128@TSOP8 [SA026-B3201]
FT24C128A@S0IC8 [SA602A]
FT24C16
FT24C16@TSOP8 [SA026-B3201]
FT24C16A@S0IC8 [SA602A]
FT24C256
FT24C256@TSOP8 [SA026-B3201]
FT24C256A@S0IC8 [SA602A]
FT24C32
FT24C32@TSOP8 [SA026-B3201]
FT24C32A@S0IC8 [SA602A]
FT24C64
FT24C64@TSOP8 [SA026-B3201]
FT24C64A@S0IC8 [SA602A]
FT27C010
FT27C010@TSOP32 [SA410T-B4001]
FT27C020@PLCC32 [SA015A1T]
FT27C040
FT27C040@TSOP32 [SA410T-B4001]
FT27C256
FT27C64
FT27HC256
FT27HC64
FT28C010
FT28C010@PLCC32 [SA015A1T]
FT28C010@TSOP32 [SA410T-B4001]
FT28C010E@JLCC32 [SA412A]
FT28C010E@PLCC44 [SA244]
FT28C020
FT28C020@PLCC32 [SA015A1T]
FT28C020@TSOP32 [SA410T-B4001]
FT28C040@JLCC32 [SA412A]
FT28C040@PLCC44 [SA244]
FT28C16
FT28C256
FT28C256@PLCC32 [SA015A1T]
FT28C256@TSOP28 [SA430T-B4003]
FT28C256B@JLCC32 [SA412A]
FT28C256B@S0IC28 [SA404]
FT28C64
FT28C64@S0IC28 [SA404]
FT28C64B
FT28C64B@PLCC32 [SA015A1T]
FT28C64B@TSOP28 [SA430T-B4003]
FT28C64X@PLCC32 [SA015A1T]
FT28C64X@TSOP28 [SA430T-B4003]
FT28HC64@PLCC32 [SA015A1T]
FT58C1001
FT58C1001@VSOP32 [SA620-B4807]

FT24C02A@TSOP8 [SA026-B3201]
FT24C04@S0IC8 [SA602A]
FT24C04A
FT24C04A@TSOP8 [SA026-B3201]
FT24C08@S0IC8 [SA602A]
FT24C08A
FT24C08A@TSOP8 [SA026-B3201]
FT24C128@S0IC8 [SA602A]
FT24C128A
FT24C128A@TSOP8 [SA026-B3201]
FT24C16@S0IC8 [SA602A]
FT24C16A
FT24C16A@TSOP8 [SA026-B3201]
FT24C256@S0IC8 [SA602A]
FT24C256A
FT24C256A@TSOP8 [SA026-B3201]
FT24C32@S0IC8 [SA602A]
FT24C32A
FT24C32A@TSOP8 [SA026-B3201]
FT24C64@S0IC8 [SA602A]
FT24C64A
FT24C64A@TSOP8 [SA026-B3201]
FT27C010@PLCC32 [SA015A1T]
FT27C020
FT27C020@TSOP32
FT27C040@PLCC32 [SA015A1T]
FT27C16
FT27C256@PLCC32 [SA015A1T]
FT27C64@PLCC32 [SA015A1T]
FT27HC256@PLCC32 [SA015A1T]
FT27HC64@PLCC32 [SA015A1T]
FT28C010@JLCC32 [SA412A]
FT28C010@PLCC44 [SA244]
FT28C010E
FT28C010E@PLCC32 [SA015A1T]
FT28C010E@TSOP32 [SA410T-B4001]
FT28C020@JLCC32 [SA412A]
FT28C020@PLCC44 [SA244]
FT28C040
FT28C040@PLCC32 [SA015A1T]
FT28C040@TSOP32 [SA410T-B4001]
FT28C16@PLCC32 [SA015A1T]
FT28C256@JLCC32 [SA412A]
FT28C256@S0IC28 [SA404]
FT28C256B
FT28C256B@PLCC32 [SA015A1T]
FT28C256B@TSOP28 [SA430T-B4003]
FT28C64@PLCC32 [SA015A1T]
FT28C64@TSOP28 [SA430T-B4003]
FT28C64B@JLCC32 [SA412A]
FT28C64B@S0IC28 [SA404]
FT28C64X
FT28C64X@S0IC28 [SA404]
FT28HC64
FT28HC64@TSOP28 [SA430T-B4003]
FT58C1001@SSOP32 [SA687]

FORWARD

E (E) PROM/FRAM/NVRAM

24LC01	24LC01@S0IC8 [SA602A]
24LC02	24LC02@S0IC8 [SA602A]
24LC04	24LC04@S0IC8 [SA602A]
24LC08	24LC08@S0IC8 [SA602A]
24LC16	24LC16@S0IC8 [SA602A]
24LC32	24LC32@S0IC8 [SA602A]
24LC64	24LC64@S0IC8 [SA602A]

Fremont Micro Devices

E (E) PROM/FRAM/NVRAM

FT24C02	FT24C02@SOP8 [SA602A]
FT24C02@TSSOP8 [SA026-B3201]	FT24C02A
FT24C02A@SOP8 [SA602A]	FT24C02A@TSSOP8 [SA026-B3201]
FT24C04	FT24C04@SOP8 [SA602A]
FT24C04@TSSOP8 [SA026-B3201]	FT24C04A
FT24C04A@SOP8 [SA602A]	FT24C04A@TSSOP8 [SA026-B3201]
FT24C08	FT24C08@SOP8 [SA602A]
FT24C08@TSSOP8 [SA026-B3201]	FT24C08A
FT24C08A@SOP8 [SA602A]	FT24C08A@TSSOP8 [SA026-B3201]
FT24C128	FT24C128@SOP8 [SA602A]
FT24C128@TSSOP8 [SA026-B3201]	FT24C128A
FT24C128A@SOP8 [SA602A]	FT24C128A@TSSOP8 [SA026-B3201]
FT24C16	FT24C16@SOP8 [SA602A]
FT24C16@TSSOP8 [SA026-B3201]	FT24C16A
FT24C16A@SOP8 [SA602A]	FT24C16A@TSSOP8 [SA026-B3201]
FT24C256	FT24C256@SOP8 [SA602A]
FT24C256@TSSOP8 [SA026-B3201]	FT24C256A
FT24C256A@SOP8 [SA602A]	FT24C256A@TSSOP8 [SA026-B3201]
FT24C32	FT24C32@SOP8 [SA602A]
FT24C32@TSSOP8 [SA026-B3201]	FT24C32A
FT24C32A@SOP8 [SA602A]	FT24C32A@TSSOP8 [SA026-B3201]
FT24C64	FT24C64@SOP8 [SA602A]
FT24C64@TSSOP8 [SA026-B3201]	FT24C64A
FT24C64A@SOP8 [SA602A]	FT24C64A@TSSOP8 [SA026-B3201]
FT34C02	FT34C02@SOP8 [SA602A]
FT34C02@TSSOP8 [SA026-B3201]	FT34C02A
FT34C02A@SOP8 [SA602A]	FT34C02A@TSSOP8 [SA026-B3201]

FUDAN

E (E) PROM/FRAM/NVRAM

FM24C32A	FM24C32A@S0IC8 [SA602A]
FM24C32A@TSSOP8 [SA026-B3201]	FM24C64A
FM24C64A@S0IC8 [SA602A]	FM24C64A@TSSOP8 [SA026-B3201]

FUJITSU

E (E) PROM/FRAM/NVRAM

MB85R256@SOP28 [SA630]	MB85R256@TSOP28 [SA643]
MB85R256A@SOP28 [SA630]	MB85R256A@TSOP28 [SA643]
MBM2212	MBM271001
MBM271001@PLCC32 [SA015A1T]	MBM271001@TSOP32 [SA410T-B4001]
MBM27128	MBM27128@PLCC32 [SA015A1T]
MBM2716	MBM2716H
MBM27256	MBM27256@PLCC32 [SA015A1T]
MBM2732	MBM2732A
MBM2764	MBM2764@PLCC32 [SA015A1T]
MBM27C1000	MBM27C1000@PLCC32 [SA015A1T]
MBM27C1000@TSOP32 [SA410T-B4001]	MBM27C1001
MBM27C1001@PLCC32 [SA015A1T]	MBM27C1001@TSOP32 [SA410T-B4001]
MBM27C1024	MBM27C1024@PLCC44 [SA244]
MBM27C128	MBM27C128@PLCC32 [SA015A1T]
MBM27C128P	MBM27C128P@PLCC32 [SA015A1T]
MBM27C2000	MBM27C2000@PLCC32 [SA015A1T]
MBM27C2000@TSOP32 [SA410T-B4001]	MBM27C2001
MBM27C2001@PLCC32 [SA015A1T]	MBM27C2001@TSOP32 [SA410T-B4001]
MBM27C2048	MBM27C256
MBM27C256@PLCC32 [SA015A1T]	MBM27C256A
MBM27C256A@PLCC32 [SA015A1T]	MBM27C256AP
MBM27C256AP@PLCC32 [SA015A1T]	MBM27C256H
MBM27C256H@PLCC32 [SA015A1T]	MBM27C32A
MBM27C4001	MBM27C4001@PLCC32 [SA015A1T]
MBM27C4001@TSOP32 [SA410T-B4001]	MBM27C4096
MBM27C512	MBM27C512@PLCC32 [SA015A1T]
MBM27C512P	MBM27C512P@PLCC32 [SA015A1T]
MBM27C64	MBM27C64@PLCC32 [SA015A1T]
MBM28C64	MBM28C65
MBM28F010	
MBM28F010(REVERSE)@TSOP32 [SA410T-B4001]	
MBM28F010@PLCC32 [SA015A1T]	MBM28F010@SOP32 [SA438T]
MBM28F010@TSOP32 [SA410T-B4001]	
MBM29DL161BD(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL161BD@TSOP48 [SB247-B4806]	
MBM29DL161BE(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL161BE@TSOP48 [SB247-B4806]	
MBM29DL161TD(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL161TD@TSOP48 [SB247-B4806]	
MBM29DL161TE(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL161TE@TSOP48 [SB247-B4806]	
MBM29DL162BD(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL162BD@TSOP48 [SB247-B4806]	
MBM29DL162BE(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL162BE@TSOP48 [SB247-B4806]	
MBM29DL162TD(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL162TD@TSOP48 [SB247-B4806]	
MBM29DL162TE(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL162TE@TSOP48 [SB247-B4806]	
MBM29DL163BD(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL163BD@TSOP48 [SB247-B4806]	
MBM29DL163BE(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL163BE@TSOP48 [SB247-B4806]	
MBM29DL163TD(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL163TD@TSOP48 [SB247-B4806]	
MBM29DL163TE(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL163TE@TSOP48 [SB247-B4806]	
MBM29DL164BD(REVERSE)@TSOP48 [SB247-B4806]	
MBM29DL164BD@TSOP48 [SB247-B4806]	

MBM29DL164BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL164BE@TSOP48 [SB247-B4806]
MBM29DL164TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL164TD@TSOP48 [SB247-B4806]
MBM29DL164TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL164TE@TSOP48 [SB247-B4806]
MBM29DL320BF@TSOP48 [SB247-B4806]
MBM29DL320TF@TSOP48 [SB247-B4806]
MBM29DL321BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL321BD@TSOP48 [SB247-B4806]
MBM29DL321BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL321BE@TSOP48 [SB247-B4806]
MBM29DL321TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL321TD@TSOP48 [SB247-B4806]
MBM29DL321TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL321TE@TSOP48 [SB247-B4806]
MBM29DL322BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL322BD@TSOP48 [SB247-B4806]
MBM29DL322BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL322BE@TSOP48 [SB247-B4806]
MBM29DL322TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL322TD@TSOP48 [SB247-B4806]
MBM29DL322TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL322TE@TSOP48 [SB247-B4806]
MBM29DL323BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL323BD@TSOP48 [SB247-B4806]
MBM29DL323BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL323BE@TSOP48 [SB247-B4806]
MBM29DL323BF@TSOP48 [SB247-B4806]
MBM29DL323TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL323TD@TSOP48 [SB247-B4806]
MBM29DL323TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL323TE@TSOP48 [SB247-B4806]
MBM29DL323TF@TSOP48 [SB247-B4806]
MBM29DL324BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL324BD@TSOP48 [SB247-B4806]
MBM29DL324BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL324BE@TSOP48 [SB247-B4806]
MBM29DL324TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL324TD@TSOP48 [SB247-B4806]
MBM29DL324TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL324TE@TSOP48 [SB247-B4806]
MBM29DL32BF@TSOP48 [SB247-B4806] MBM29DL32TF@TSOP48 [SB247-B4806]
MBM29DL34BF@TSOP48 [SB247-B4806] MBM29DL34TF@TSOP48 [SB247-B4806]
MBM29DL400BB@PSOP44 [SA638]
MBM29DL400BB@TSOP48 [SB247-B4806]
MBM29DL400BC(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL400BC@PSOP44 [SA638]
MBM29DL400BC@TSOP48 [SB247-B4806]
MBM29DL400BT@PSOP44 [SA638]
MBM29DL400BT@TSOP48 [SB247-B4806]
MBM29DL400TC(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL400TC@PSOP44 [SA638]
MBM29DL400TC@TSOP48 [SB247-B4806]
MBM29DL640E(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL640E@TSOP48 [SB247-B4806] MBM29DL64DF@TSOP48 [SB247-B4806]
MBM29DL800B@PSOP44 [SA638] MBM29DL800B@TSOP48 [SB247-B4806]
MBM29DL800BA(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL800BA@PSOP44 [SA638]

MBM29DL800BA@TSOP48 [SB247-B4806]
MBM29DL800BB@PSOP44 [SA638]
MBM29DL800BB@TSOP48 [SB247-B4806]
MBM29DL800BT@PSOP44 [SA638]
MBM29DL800BT@TSOP48 [SB247-B4806]
MBM29DL800T@PSOP44 [SA638] MBM29DL800T@TSOP48 [SB247-B4806]
MBM29DL800TA(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL800TA@PSOP44 [SA638]
MBM29DL800TA@TSOP48 [SB247-B4806]
MBM29DS163BE@TSOP48 [SB247-B4806]
MBM29DS163TE@TSOP48 [SB247-B4806]
MBM29F001B MBM29F001B@PLCC32 [SA015A1T]
MBM29F001B@TSOP32 [SA410T-B4001] MBM29F001T
MBM29F001T@PLCC32 [SA015A1T] MBM29F001T@TSOP32 [SA410T-B4001]
MBM29F002B MBM29F002B@PLCC32 [SA015A1T]
MBM29F002B@TSOP32 [SA410T-B4001] MBM29F002NB
MBM29F002NB@PLCC32 [SA015A1T]
MBM29F002NB@TSOP32 [SA410T-B4001]
MBM29F002NT MBM29F002NT@PLCC32 [SA015A1T]
MBM29F002NT@TSOP32 [SA410T-B4001]
MBM29F002T MBM29F002T@PLCC32 [SA015A1T]
MBM29F002T@TSOP32 [SA410T-B4001] MBM29F010
MBM29F010@PLCC32 [SA015A1T] MBM29F010@TSOP32 [SA410T-B4001]
MBM29F010A MBM29F010A@PLCC32 [SA015A1T]
MBM29F010A@TSOP32 [SA410T-B4001] MBM29F016@PSOP44 [SA638]
MBM29F016@TSOP40 [SA409T-B4002] MBM29F016@TSOP48 [SB247-B4806]
MBM29F016A@PSOP44 [SA638] MBM29F016A@TSOP40 [SA409T-B4002]
MBM29F016A@TSOP48 [SB247-B4806] MBM29F016B@PSOP44 [SA638]
MBM29F016B@TSOP40 [SA409T-B4002] MBM29F016B@TSOP48 [SB247-B4806]
MBM29F017A(REVERSE)@TSOP48 [SB247-B4806]
MBM29F017A@TSOP48 [SB247-B4806] MBM29F017B@TSOP48 [SB247-B4806]
MBM29F017D@TSOP40 [SA409T-B4002] MBM29F017D@TSOP48 [SB247-B4806]
MBM29F032B@PSOP44 [SA638] MBM29F032B@TSOP40 [SA409T-B4002]
MBM29F033C@TSOP40 [SA409T-B4002] MBM29F040
MBM29F040@PLCC32 [SA015A1T] MBM29F040@TSOP32 [SA410T-B4001]
MBM29F040B MBM29F040B@PLCC32 [SA015A1T]
MBM29F040B@TSOP32 [SA410T-B4001] MBM29F040C@PLCC32 [SA015A1T]
MBM29F040C@TSOP32 [SA410T-B4001] MBM29F080@PSOP44 [SA638]
MBM29F080@TSOP40 [SA409T-B4002]
MBM29F080A(REVERSE)@TSOP40 [SA409T-B4002]
MBM29F080A(REVERSE)@TSOP48 [SB247-B4806]
MBM29F080A@PSOP44 [SA638] MBM29F080A@TSOP40 [SA409T-B4002]
MBM29F080A@TSOP48 [SB247-B4806] MBM29F080B@PSOP44 [SA638]
MBM29F080B@TSOP40 [SA409T-B4002] MBM29F100B@PSOP44 [SA638]
MBM29F100B@TSOP48 [SB247-B4806] MBM29F100T@PSOP44 [SA638]
MBM29F100T@TSOP48 [SB247-B4806]
MBM29F160BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29F160BE@TSOP48 [SB247-B4806]
MBM29F160TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29F160TE@TSOP48 [SB247-B4806] MBM29F200AB@PSOP44 [SA638]
MBM29F200AB@TSOP48 [SB247-B4806] MBM29F200AT@PSOP44 [SA638]
MBM29F200AT@TSOP48 [SB247-B4806] MBM29F200B@PSOP44 [SA638]
MBM29F200B@TSOP48 [SB247-B4806]
MBM29F200BC(REVERSE)@TSOP48 [SB247-B4806]
MBM29F200BC@PSOP44 [SA638] MBM29F200BC@TSOP48 [SB247-B4806]
MBM29F200T@PSOP44 [SA638] MBM29F200T@TSOP48 [SB247-B4806]
MBM29F200TC(REVERSE)@TSOP48 [SB247-B4806]
MBM29F200TC@PSOP44 [SA638] MBM29F200TC@TSOP48 [SB247-B4806]
MBM29F400AB@PSOP44 [SA638] MBM29F400AB@TSOP48 [SB247-B4806]

MBM29F400AT@PSOP44 [SA638] MBM29F400AT@TSOP48 [SB247-B4806]
MBM29F400B@PSOP44 [SA638] MBM29F400B@TSOP48 [SB247-B4806]
MBM29F400BB@PSOP44 [SA638] MBM29F400BB@TSOP48 [SB247-B4806]
MBM29F400BC(REVERSE)@TSOP48 [SB247-B4806]
MBM29F400BC@PSOP44 [SA638] MBM29F400BC@TSOP48 [SB247-B4806]
MBM29F400BT@PSOP44 [SA638] MBM29F400BT@TSOP48 [SB247-B4806]
MBM29F400T@PSOP44 [SA638] MBM29F400T@TSOP48 [SB247-B4806]
MBM29F400TC(REVERSE)@TSOP48 [SB247-B4806]
MBM29F400TC@PSOP44 [SA638] MBM29F400TC@TSOP48 [SB247-B4806]
MBM29F800B@PSOP44 [SA638] MBM29F800B@TSOP48 [SB247-B4806]
MBM29F800BA(REVERSE)@TSOP48 [SB247-B4806]
MBM29F800BA@PSOP44 [SA638] MBM29F800BA@TSOP48 [SB247-B4806]
MBM29F800BB@PSOP44 [SA638] MBM29F800BB@TSOP48 [SB247-B4806]
MBM29F800BT@PSOP44 [SA638] MBM29F800BT@TSOP48 [SB247-B4806]
MBM29F800T@PSOP44 [SA638] MBM29F800T@TSOP48 [SB247-B4806]
MBM29F800TA(REVERSE)@TSOP48 [SB247-B4806]
MBM29F800TA@PSOP44 [SA638] MBM29F800TA@TSOP48 [SB247-B4806]
MBM29LL800B@TSOP48 [SB247-B4806]
MBM29LL800BB@TSOP48 [SB247-B4806]
MBM29LL800BT@TSOP48 [SB247-B4806]
MBM29LL800T@TSOP48 [SB247-B4806] MBM29LV001B@PLCC32 [SA015A1T]
MBM29LV001BB(REVERSE)@TSOP32 [SA410T-B4001]
MBM29LV001BB@PLCC32 [SA015A1T]
MBM29LV001BB@TSOP32 [SA410T-B4001]
MBM29LV001BC(REVERSE)@TSOP32 [SA410T-B4001]
MBM29LV001BC@PLCC32 [SA015A1T]
MBM29LV001BC@TSOP32 [SA410T-B4001]
MBM29LV001BT(REVERSE)@TSOP32 [SA410T-B4001]
MBM29LV001BT@PLCC32 [SA015A1T]
MBM29LV001BT@TSOP32 [SA410T-B4001]
MBM29LV001T@TSOP32 [SA410T-B4001]
MBM29LV001TC(REVERSE)@TSOP32 [SA410T-B4001]
MBM29LV001TC@PLCC32 [SA015A1T]
MBM29LV001TC@TSOP32 [SA410T-B4001]
MBM29LV002B@TSOP40 [SA409T-B4002]
MBM29LV002T@TSOP40 [SA409T-B4002]
MBM29LV004B@TSOP40 [SA409T-B4002]
MBM29LV004BB@TSOP40 [SA409T-B4002]
MBM29LV004BT@TSOP40 [SA409T-B4002]
MBM29LV004T@TSOP40 [SA409T-B4002]
MBM29LV008B@TSOP40 [SA409T-B4002]
MBM29LV008BB@TSOP40 [SA409T-B4002]
MBM29LV008BT@TSOP40 [SA409T-B4002]
MBM29LV008T@TSOP40 [SA409T-B4002]
MBM29LV016/B@TSOP40 [SA409T-B4002]
MBM29LV016/T@TSOP40 [SA409T-B4002]
MBM29LV016B@TSOP40 [SA409T-B4002]
MBM29LV017@TSOP40 [SA409T-B4002]
MBM29LV017B@TSOP40 [SA409T-B4002]
MBM29LV017E@TSOP40 [SA409T-B4002]
MBM29LV033C@TSOP40 [SA409T-B4002]
MBM29LV080@TSOP40 [SA409T-B4002]
MBM29LV080A@TSOP40 [SA409T-B4002]
MBM29LV081@TSOP40 [SA409T-B4002]
MBM29LV081B@TSOP40 [SA409T-B4002]
MBM29LV116B@TSOP40 [SA409T-B4002]
MBM29LV160B(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV160B@TSOP48 [SB247-B4806]
MBM29LV160BE(REVERSE)@TSOP48 [SB247-B4806]

MBM29LV160BE@PSOP44 [SA638]
MBM29LV160BE@TSOP48 [SB247-B4806]
MBM29LV160BM@TSOP48 [SB247-B4806]
MBM29LV160T(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV160T@TSOP48 [SB247-B4806]
MBM29LV160TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV160TE@PSOP44 [SA638]
MBM29LV160TE@TSOP48 [SB247-B4806]
MBM29LV160TM@TSOP48 [SB247-B4806]
MBM29LV200B@PSOP44 [SA638] MBM29LV200B@TSOP48 [SB247-B4806]
MBM29LV200BB@PSOP44 [SA638]
MBM29LV200BB@TSOP48 [SB247-B4806]
MBM29LV200BC(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV200BC@PSOP44 [SA638]
MBM29LV200BC@TSOP48 [SB247-B4806]
MBM29LV200BT@PSOP44 [SA638]
MBM29LV200BT@TSOP48 [SB247-B4806]
MBM29LV200T@PSOP44 [SA638] MBM29LV200T@TSOP48 [SB247-B4806]
MBM29LV200TC(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV200TC@PSOP44 [SA638]
MBM29LV200TC@TSOP48 [SB247-B4806]
MBM29LV320BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV320BE@TSOP48 [SB247-B4806]
MBM29LV320TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV320TE@TSOP48 [SB247-B4806]
MBM29LV400B@PSOP44 [SA638] MBM29LV400B@TSOP48 [SB247-B4806]
MBM29LV400BB@PSOP44 [SA638]
MBM29LV400BB@TSOP48 [SB247-B4806]
MBM29LV400BC@PSOP44 [SA638]
MBM29LV400BC@TSOP48 [SB247-B4806]
MBM29LV400BT@PSOP44 [SA638]
MBM29LV400BT@TSOP48 [SB247-B4806]
MBM29LV400T@PSOP44 [SA638] MBM29LV400T@TSOP48 [SB247-B4806]
MBM29LV400TC@PSOP44 [SA638]
MBM29LV400TC@TSOP48 [SB247-B4806]
MBM29LV650UE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV650UE@TSOP48 [SB247-B4806]
MBM29LV651UE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV651UE@TSOP48 [SB247-B4806]
MBM29LV800B@PSOP44 [SA638] MBM29LV800B@TSOP48 [SB247-B4806]
MBM29LV800BA(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV800BA@PSOP44 [SA638]
MBM29LV800BA@TSOP48 [SB247-B4806]
MBM29LV800BB@PSOP44 [SA638]
MBM29LV800BB@TSOP48 [SB247-B4806]
MBM29LV800BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV800BE@PSOP44 [SA638]
MBM29LV800BE@TSOP48 [SB247-B4806]
MBM29LV800BT@PSOP44 [SA638]
MBM29LV800BT@TSOP48 [SB247-B4806]
MBM29LV800T@PSOP44 [SA638] MBM29LV800T@TSOP48 [SB247-B4806]
MBM29LV800TA(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV800TA@PSOP44 [SA638]
MBM29LV800TA@TSOP48 [SB247-B4806]
MBM29LV800TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV800TE@PSOP44 [SA638]
MBM29LV800TE@TSOP48 [SB247-B4806]
MBM29PL160BD@TSOP48 [SB247-B4806]
MBM29PL160TD@PSOP44 [SA638]

MBM29PL160TD@TSOP48 [SB247-B4806]
MBM29PL32BM@TSOP48 [SB247-B4806] MBM29PL32TM@TSOP48 [SB247-B4806]
MBM29PL64LM@TSOP48 [SB247-B4806] MBM29PL65LM@TSOP48 [SB247-B4806]
MBM29SL160BD (REVERSE)@TSOP48 [SB247-B4806]
MBM29SL160BD@TSOP48 [SB247-B4806]
MBM29SL160TD (REVERSE)@TSOP48 [SB247-B4806]
MBM29SL160TD@TSOP48 [SB247-B4806]
MBM29SL800BD (REVERSE)@TSOP48 [SB247-B4806]
MBM29SL800BD@TSOP48 [SB247-B4806]
MBM29SL800TD (REVERSE)@TSOP48 [SB247-B4806]
MBM29SL800TD@TSOP48 [SB247-B4806]

GENERAL(GI)

E (E) PROM/FRAM/NVRAM

27256	27C128
27C128@PLCC32 [SA015A1T]	27C256
27C256@PLCC32 [SA015A1T]	27C512
27C513	27C64
27C64@PLCC32 [SA015A1T]	27HC64
27HC641	27HC641L
27HC64L	28C04
28C04A	28C04F
28C16	28C16A
28C16F	28C17
28C17F	GR27C513

GENERIC

E (E) PROM/FRAM/NVRAM

27128(21V)	27128A(12.5V)
2716(25V)	27256(12.5V)
2732(25V)	2732A(21V)
2732B(12.5V)	27512(12.5V)
27512(21V)	2764(21V)
2764A(12.5V)	27C128(12.5V)
27C128(21V)	27C16(25V)
27C256(12.5V)	27C32(25V)
27C512(12.5V)	27C64(12.5V)
27C64(21V)	

GIANTEC

E (E) PROM/FRAM/NVRAM

GT24C01	GT24C01@MSOP8
GT24C01@SOP8 [SA602A]	GT24C01@TSSOP8 [SA026-B3201]
GT24C02	GT24C02@DFN8
GT24C02@MSOP8	GT24C02@SOP8 [SA602A]
GT24C02@TSSOP8 [SA026-B3201]	GT24C04
GT24C04@DFN8	GT24C04@MSOP8
GT24C04@SOP8 [SA602A]	GT24C04@TSSOP8 [SA026-B3201]
GT24C08	GT24C08@DFN8
GT24C08@MSOP8	GT24C08@SOP8 [SA602A]

GT24C08@TSSOP8 [SA026-B3201]	GT24C128
GT24C128@SOP8 [SA602A]	GT24C128@TSSOP14 [SA026-B3201]
GT24C16	GT24C16@MSOP8
GT24C16@SOP8 [SA602A]	GT24C16@TSSOP8 [SA026-B3201]
GT24C256	GT24C256@SOP8 [SA602A]
GT24C256@TSSOP14 [SA026-B3201]	GT24C32
GT24C32@MSOP8 [SA666]	GT24C32@SOP8 [SA602A]
GT24C32@TSSOP8 [SA026-B3201]	GT24C64
GT24C64@MSOP8 [SA666]	GT24C64@SOP8 [SA602A]
GT24C64@TSSOP8 [SA026-B3201]	GT25C01
GT25C01@SOP8 [SA602A]	GT25C01@TSSOP8 [SA026-B3201]
GT25C02	GT25C02@SOP8 [SA602A]
GT25C02@TSSOP8 [SA026-B3201]	GT25C04
GT25C04@SOP8 [SA602A]	GT25C04@TSSOP8
GT25C08	GT25C08@S0IC8 [SA602A]
GT25C08@TSSOP8 [SA026-B3201]	GT25C128@S0IC8 [SA602A]
GT25C128@TSSOP8 [SA026-B3201]	GT25C16
GT25C16@S0IC8 [SA602A]	GT25C16@TSSOP8 [SA026-B3201]
GT25C256@S0IC8 [SA602A]	GT25C256@TSSOP8 [SA026-B3201]
GT25C32	GT25C32@S0IC8 [SA602A]
GT25C32@TSSOP8 [SA026-B3201]	GT25C64
GT25C64@S0IC8 [SA602A]	GT25C64@TSSOP8 [SA026-B3201]
GT34C02	GT34C02@MSOP8
GT34C02@SOP8 [SA602A]	GT34C02@TSSOP8 [SA026-B3201]
GT93C46(08bit)	GT93C46(08bit)@S0IC8 [SA602A]
GT93C46(08bit)@TSSOP8 [SA026-B3201]	GT93C46(16bit)@S0IC8 [SA602A]
GT93C46(16bit)	GT93C56(08bit)@S0IC8 [SA602A]
GT93C46(16bit)@TSSOP8 [SA026-B3201]	GT93C56(16bit)@S0IC8 [SA602A]
GT93C56(08bit)	GT93C66(08bit)@S0IC8 [SA602A]
GT93C56(08bit)@TSSOP8 [SA026-B3201]	GT93C66(16bit)@S0IC8 [SA602A]
GT93C56(16bit)	GT93C76(08bit)@S0IC8 [SA602A]
GT93C56(16bit)@TSSOP8 [SA026-B3201]	GT93C76(16bit)@S0IC8 [SA602A]
GT93C66(08bit)	GT93C86(08bit)@S0IC8 [SA602A]
GT93C66(08bit)@TSSOP8 [SA026-B3201]	GT93C86(16bit)@S0IC8 [SA602A]
GT93C66(16bit)	
GT93C66(16bit)@TSSOP8 [SA026-B3201]	
GT93C76(08bit)	
GT93C76(08bit)@TSSOP8 [SA026-B3201]	
GT93C76(16bit)	
GT93C76(16bit)@TSSOP8 [SA026-B3201]	
GT93C86(08bit)	
GT93C86(08bit)@TSSOP8 [SA026-B3201]	
GT93C86(16bit)	
GT93C86(16bit)@TSSOP8 [SA026-B3201]	

GIGADEVICE

E(E)PROM/FRAM/NVRAM

GD25D40	GD25D40@SOP8 [SA605B]
GD25D80	GD25D80@SOP8 [SA605B]
GD25F40	GD25F40@SOP8 [SA605B]
GD25F80	GD25F80@SOP8 [SA605B]
GD25Q10	GD25Q10@SOP8 [SA605B]
GD25Q16	GD25Q16@SOP8 [SA605B]
GD25Q20	GD25Q20@SOP8 [SA605B]
GD25Q32	GD25Q32(4*256 Security) [SA605B]
GD25Q32@SOP8 [SA605B]	

GD25Q32@SOP8(4*256 Security) [SA605B]	
GD25Q40	GD25Q40@SOP8 [SA605B]
GD25Q512	GD25Q512@SOP8 [SA602A]
GD25Q80	GD25Q80@SOP8 [SA605B]
GD25T80	GD25T80@SOP8 [SA605B]

GOAL

MICROCONTROLLER

VRS1000	VRS1000@PLCC44 [SA244]
VRS1000@TQFP44 [SA245A-B4805]	VRS1050
VRS1050@PLCC44 [SA244]	VRS1050@TQFP44 [SA245A-B4805]
VRS1100	VRS1100@PLCC44 [SA244]
VRS1100@TQFP44 [SA245A-B4805]	VRS540
VRS540@PLCC44 [SA244]	VRS540@TQFP44 [SA245A-B4805]
VRS550	VRS550@PLCC44 [SA244]
VRS550@TQFP44 [SA245A-B4805]	VRS560
VRS560@PLCC44 [SA244]	VRS560@TQFP44 [SA245A-B4805]
VRS570	VRS570@PLCC44 [SA244]
VRS570@TQFP44 [SA245A-B4805]	VRS580
VRS580@PLCC44 [SA244]	VRS580@TQFP44 [SA245A-B4805]
VRS700	VRS700@PLCC44 [SA244]
VRS700@TQFP44 [SA245A-B4805]	VRS900
VRS900@PLCC44 [SA244]	VRS900@TQFP44 [SA245A-B4805]

GREENWICH

E(E) PROM/FRAM/NVRAM

GR27128	GR27256
GR27512	GR2764

HITACHI

E(E) PROM/FRAM/NVRAM

HN27128AG	HN27128AP
HN27256G	HN27256P
HN27512G	HN27512P
HN27C101AG	HN27C101AP
HN27C101G	HN27C101P
HN27C1024HG	HN27C1024HG@PLCC44 [SA244]
HN27C256AG	HN27C256FP
HN27C256G	HN27C256HG
HN27C301AG	HN27C301AP
HN27C301G	HN27C301P
HN27C4000FP	HN27C4000G
HN27C4001	HN27C4001@TSOP32 [SA410T-B4001]
HN27C4001G	HN27C4096A
HN27C4096A@PLCC44 [SA244]	HN27C4096FP
HN27C4096FP@PLCC44 [SA244]	HN27C4096G
HN27C4096G@PLCC44 [SA244]	HN27C512G
HN27C512G@PLCC32 [SA015A1T]	HN27C64G
HN28F101	
HN28F101(REVERSE)@TSOP32 [SA410T-B4001]	

HN28F101@PLCC32 [SA015A1T]
HN28F101@TSOP32 [SA410T-B4001]
HN462732G
HN48016P
HN4827128P
HN482764G
HN58064(FP)@S0IC28 [SA404]
HN58C1001(FP)@SSOP32 [SA687]
HN58C1001(T)@VSOP32 [SA620-B4807]
HN58C256A(FP)@SOP28 [SA404]
HN58C256A(T)@TSOP28 [SA430T-B4003]
HN58C257A(T)@TSOP32 [SA605B]
HN58C65(P)
HN58V24256@S0IC8 [SA602A]
HN58V24512
HN58V256A
HN58V65A
HN58V65A@TSOP28 [SA430T-B4003]
HN58V66A@S0IC28 [SA404]
HN58W241000
HN58X2402
HN58X2402@TSSOP8 [SA026-B3201]
HN58X2404@S0IC8 [SA602A]
HN58X2408
HN58X2408@TSSOP8 [SA026-B3201]
HN58X24128@S0IC8 [SA602A]
HN58X2416@S0IC8 [SA602A]
HN58X24256
HN58X2432
HN58X2432@TSSOP8
HN58X24512@S0IC8 [SA602A]
HN58X2464@S0IC8 [SA602A]
HN58X2502@S0IC8 [SA602A]
HN58X2504@S0IC8 [SA602A]
HN58X25128@S0IC8 [SA602A]
HN58X25256@S0IC8 [SA602A]
HN58X2532@S0IC8 [SA602A]
HN58X2564@S0IC8 [SA602A]
HT29VB800@TSOP48 [SA247-B4806]
HT29WB800@TSOP48 [SA247-B4806]

HN28F101@SOP32 [SA438T]
HN462716G
HN48016
HN4827128G
HN482732AG
HN482764P
HN58064(P)
HN58C1001(P)
HN58C256A(P)
HN58C65(FP)@S0IC28 [SA404]
HN58V24256
HN58V24256@TSSOP14 [SA026-B3201]
HN58V24512@S0IC8 [SA602A]
HN58V256A@TSOP28 [SA430T-B4003]
HN58V65A@S0IC28 [SA404]
HN58V66A
HN58V66A@TSOP28 [SA430T-B4003]
HN58W241000@S0IC8 [SA602A]
HN58X2402@S0IC8 [SA602A]
HN58X2404
HN58X2404@TSSOP8 [SA026-B3201]
HN58X2408@S0IC8 [SA602A]
HN58X24128
HN58X2416
HN58X2416@TSSOP8 [SA026-B3201]
HN58X24256@S0IC8 [SA602A]
HN58X2432@S0IC8 [SA602A]
HN58X24512
HN58X2464
HN58X2464@TSSOP8 [SA026-B3201]
HN58X2502@TSSOP8 [SA026-B3201]
HN58X2504@TSSOP8 [SA026-B3201]
HN58X25128@TSSOP14 [SA026-B3201]
HN58X25256@TSSOP14 [SA026-B3201]
HN58X2532@TSSOP8 [SA026-B3201]
HN58X2564@TSSOP8 [SA026-B3201]
HT29VT800@TSOP48 [SA247-B4806]
HT29WT800@TSOP48 [SA247-B4806]

MICROCONTROLLER

HD64F2357TE@QFP120 [\$\$\$\$\$]

HOLTEK

E(E)PROM/FRAM/NVRAM

HT24C01
HT24C02
HT24C04
HT24C08
HT24LC01
HT24LC01@TSSOP8 [SA026-B3201]
HT24LC02@S0IC8 [SA602A]
HT24LC04

HT24C01@S0IC8 [SA602A]
HT24C02@S0IC8 [SA602A]
HT24C04@S0IC8 [SA602A]
HT24C16
HT24LC01@S0IC8 [SA602A]
HT24LC02
HT24LC02@TSSOP8 [SA026-B3201]
HT24LC04@S0IC8 [SA602A]

HT24LC08	HT24LC08@S0IC8 [SA602A]
HT24LC16	HT24LC16@S0IC8 [SA602A]
HT24LC32	HT24LC32@S0IC8 [SA602A]
HT24LC64	HT24LC64@S0IC8 [SA602A]
HT25LC512@S0IC8 [SA602A]	HT27C010
HT27C010@PLCC32 [SA015A1T]	HT27C010@SOP32 [SA603]
HT27C020	HT27C020@PLCC32 [SA015A1T]
HT27C020@SOP32 [SA603]	HT27C040
HT27C040@PLCC32 [SA015A1T]	HT27C040@SOP32 [SA603]
HT27C4096	HT27C4096@PLCC44 [SA244]
HT27C512	HT27C512@SOP28 [SA404]
HT27C512-A@PLCC32 [SA015A1T]	HT27C512-B@PLCC32 [SA015A1T]
HT27LC010	HT27LC010@PLCC32 [SA015A1T]
HT27LC010@SOP32 [SA603]	HT27LC010@TSOP32 [SA410T-B4001]
HT27LC020	HT27LC020@PLCC32 [SA015A1T]
HT27LC020@SOP32 [SA603]	HT27LC020@TSOP32 [SA410T-B4001]
HT27LC040	HT27LC040@PLCC32 [SA015A1T]
HT27LC040@SOP32 [SA603]	HT27LC040@TSOP32 [SA410T-B4001]
HT27LC4096	HT27LC4096@PLCC44 [SA244]
HT27LC512	HT27LC512@SOP28 [SA404]
HT27LC512@TSOP28 [SA430T-B4003]	HT27LC512-A@PLCC32 [SA015A1T]
HT27LC512-B@PLCC32 [SA015A1T]	HT93C46(16bit)
HT93C46(16bit)@SOP8-A [SA602A]	HT93C46(16bit)@SOP8-B [SA602A]
HT93C46(16bit)@TSSOP8 [SA026-B3201]	HT93C56(16bit)@SOP8-A [SA602A]
HT93C56(16bit)	HT93C66(16bit)@SOP8-A [SA602A]
HT93C56(16bit)@SOP8-B [SA602A]	
HT93C56(16bit)@TSSOP8 [SA026-B3201]	
HT93C66(16bit)	
HT93C66(16bit)@SOP8-B [SA602A]	
HT93C66(16bit)@TSSOP8 [SA026-B3201]	
HT93LC46A(08bit)	HT93LC46A(08bit)@SOP8-A [SA602A]
HT93LC46A(08bit)@SOP8-B [SA602A]	
HT93LC46A(08bit)@TSSOP8 [SA026-B3201]	
HT93LC46A(16bit)	HT93LC46A(16bit)@SOP8-A [SA602A]
HT93LC46A(16bit)@SOP8-B [SA602A]	
HT93LC46A(16bit)@TSSOP8 [SA026-B3201]	
HT93LC46B(08bit)	HT93LC46B(08bit)@SOP8-A [SA602A]
HT93LC46B(08bit)@SOP8-B [SA602A]	
HT93LC46B(08bit)@TSSOP8 [SA026-B3201]	
HT93LC46B(16bit)	HT93LC46B(16bit)@SOP8-A [SA602A]
HT93LC46B(16bit)@SOP8-B [SA602A]	
HT93LC46B(16bit)@TSSOP8 [SA026-B3201]	
HT93LC46B(16bit)	
HT93LC46B(16bit)@SOP8-B [SA602A]	
HT93LC46B(16bit)@TSSOP8 [SA026-B3201]	
HT93LC56A(08bit)	HT93LC56A(08bit)@SOP8-A [SA602A]
HT93LC56A(08bit)@SOP8-B [SA602A]	
HT93LC56A(08bit)@TSSOP8 [SA026-B3201]	
HT93LC56A(16bit)	HT93LC56A(16bit)@SOP8-A [SA602A]
HT93LC56A(16bit)@SOP8-B [SA602A]	
HT93LC56A(16bit)@TSSOP8 [SA026-B3201]	
HT93LC56B(08bit)	HT93LC56B(08bit)@SOP8-A [SA602A]
HT93LC56B(08bit)@SOP8-B [SA602A]	
HT93LC56B(08bit)@TSSOP8 [SA026-B3201]	
HT93LC56B(16bit)	HT93LC56B(16bit)@SOP8-A [SA602A]
HT93LC56B(16bit)@SOP8-B [SA602A]	
HT93LC56B(16bit)@TSSOP8 [SA026-B3201]	
HT93LC66A(08bit)	HT93LC66A(08bit)@SOP8-A [SA602A]
HT93LC66A(08bit)@SOP8-B [SA602A]	
HT93LC66A(08bit)@TSSOP8 [SA026-B3201]	
HT93LC66A(16bit)	HT93LC66A(16bit)@SOP8-A [SA602A]
HT93LC66A(16bit)@SOP8-B [SA602A]	

HT93LC66A(16bit)@TSSOP8 [SA026-B3201]	
HT93LC66B(08bit)	HT93LC66B(08bit)@SOP8-A [SA602A]
HT93LC66B(08bit)@SOP8-B [SA602A]	
HT93LC66B(08bit)@TSSOP8 [SA026-B3201]	
HT93LC66B(16bit)	HT93LC66B(16bit)@SOP8-A [SA602A]
HT93LC66B(16bit)@SOP8-B [SA602A]	
HT93LC66B(16bit)@TSSOP8 [SA026-B3201]	
HT93LC76(08bit)	HT93LC76(08bit)@SOP8-A [SA602A]
HT93LC76(08bit)@SOP8-B [SA602A]	
HT93LC76(08bit)@TSSOP8 [SA026-B3201]	
HT93LC76(16bit)	HT93LC76(16bit)@SOP8-A [SA602A]
HT93LC76(16bit)@SOP8-B [SA602A]	
HT93LC76(16bit)@TSSOP8 [SA026-B3201]	
HT93LC86(08bit)	HT93LC86(08bit)@SOP8-A [SA602A]
HT93LC86(08bit)@SOP8-B [SA602A]	
HT93LC86(08bit)@TSSOP8 [SA026-B3201]	
HT93LC86(16bit)	HT93LC86(16bit)@SOP8-A [SA602A]
HT93LC86(16bit)@SOP8-B [SA602A]	
HT93LC86(16bit)@TSSOP8 [SA026-B3201]	

HONGKONG

E(E)PROM/FRAM/NVRAM

HK1215	HK1225
HK1235	HK1245
HK1255	HK1265
HK1275	HK1285
HK1295	HK12A5
HK12B5	OKS1225
OKS1235	OKS1245
OKS1255	OKS1265
OKS1275	OKS1285
OKS1295	OKS12A5
OKS12B5	

HYNIX

E(E)PROM/FRAM/NVRAM

HY2764	HY27C64A
HY29DL162BT@TSOP48 [SB247-B4806]	HY29DL162TT@TSOP48 [SB247-B4806]
HY29DL163BT@TSOP48 [SB247-B4806]	HY29DL163TT@TSOP48 [SB247-B4806]
HY29DS162BT@TSOP48 [SB247-B4806]	HY29DS162TT@TSOP48 [SB247-B4806]
HY29DS163BT@TSOP48 [SB247-B4806]	HY29DS163TT@TSOP48 [SB247-B4806]
HY29F002T	HY29F002T@PLCC32 [SA015A1T]
HY29F002T@TSOP32 [SA410T-B4001]	HY29F040
HY29F040@PLCC32 [SA015A1T]	HY29F040@TSOP32 [SA410T-B4001]
HY29F040A	HY29F040A@PLCC32 [SA015A1T]
HY29F040A@TSOP32 [SA410T-B4001]	HY29F080@TSOP40 [SA409T-B4002]
HY29F200B@PSOP44 [SA638]	HY29F200B@TSOP48 [SB247-B4806]
HY29F200T@PSOP44 [SA638]	HY29F200T@TSOP48 [SB247-B4806]
HY29F400ABG@PSOP44 [SA638]	HY29F400ABT@TSOP48 [SB247-B4806]
HY29F400ATG@PSOP44 [SA638]	HY29F400ATT@TSOP48 [SB247-B4806]
HY29F400BG@PSOP44 [SA638]	HY29F400BT@TSOP48 [SB247-B4806]
HY29F400TG@PSOP44 [SA638]	HY29F400TT@TSOP48 [SB247-B4806]
HY29F800ABG@PSOP44 [SA638]	HY29F800ABT@TSOP48 [SB247-B4806]

HY29F800ATG@PSOP44 [SA638]
HY29F800BG@PSOP44 [SA638]
HY29F800TG@PSOP44 [SA638]
HY29LV160BT@TSOP48 [SB247-B4806]
HY29LV320BT@TSOP48 [SB247-B4806]
HY29LV400BT@TSOP48 [SB247-B4806]
HY29LV800BG@PSOP44 [SA638]
HY29LV800TG@PSOP44 [SA638]
HY93C46
HY93C56
HY93C66
HY93C76
HY93C86

HY29F800ATT@TSOP48 [SB247-B4806]
HY29F800BT@TSOP48 [SB247-B4806]
HY29F800TT@TSOP48 [SB247-B4806]
HY29LV160TT@TSOP48 [SB247-B4806]
HY29LV320TT@TSOP48 [SB247-B4806]
HY29LV400TT@TSOP48 [SB247-B4806]
HY29LV800BT@TSOP48 [SB247-B4806]
HY29LV800TT@TSOP48 [SB247-B4806]
HY93C46@S0IC8 [SA602A]
HY93C56@S0IC8 [SA602A]
HY93C66@S0IC8 [SA602A]
HY93C76@S0IC8 [SA602A]
HY93C86@S0IC8 [SA602A]

MICROCONTROLLER

GMS97C1051
GMS97C2051
GMS97C51
GMS97C51@TQFP44 [SA675-B4805]
GMS97C52@PLCC44 [SA244]
GMS97C54
GMS97C54@TQFP44 [SA675-B4805]
GMS97C56@PLCC44 [SA244]
GMS97C58
GMS97C58@TQFP44 [SA675-B4805]
GMS97L1051@S0IC20 [SA404]
GMS97L2051@S0IC20 [SA404]
GMS97L51@PLCC44 [SA244]
GMS97L52
GMS97L52@TQFP44 [SA675-B4805]
GMS97L54@PLCC44 [SA244]
GMS97L56
GMS97L56@TQFP44 [SA675-B4805]
GMS97L58@PLCC44 [SA244]
GMS99C51
GMS99C51@TQFP44 [SA675-B4805]
GMS99C52@PLCC44 [SA244]
GMS99C58
GMS99C58@TQFP44 [SA675-B4805]
HMS99C51@PLCC44 [SA244]
HMS99C52
HMS99C52@TQFP44 [SA675-B4805]
HMS99C58@PLCC44 [SA244]

GMS97C1051@S0IC20 [SA404]
GMS97C2051@S0IC20 [SA404]
GMS97C51@PLCC44 [SA244]
GMS97C52
GMS97C52@TQFP44 [SA675-B4805]
GMS97C54@PLCC44 [SA244]
GMS97C56
GMS97C56@TQFP44 [SA675-B4805]
GMS97C58@PLCC44 [SA244]
GMS97L1051
GMS97L2051
GMS97L51
GMS97L51@TQFP44 [SA675-B4805]
GMS97L52@PLCC44 [SA244]
GMS97L54
GMS97L54@TQFP44 [SA675-B4805]
GMS97L56@PLCC44 [SA244]
GMS97L58
GMS97L58@TQFP44 [SA675-B4805]
GMS99C51@PLCC44 [SA244]
GMS99C52
GMS99C52@TQFP44 [SA675-B4805]
GMS99C58@PLCC44 [SA244]
HMS99C51
HMS99C51@TQFP44 [SA675-B4805]
HMS99C52@PLCC44 [SA244]
HMS99C58
HMS99C58@TQFP44 [SA675-B4805]

HYUNDAI

E(E)PROM/FRAM/NVRAM

HY2764
HY29DL162BT@TSOP48 [SB247-B4806]
HY29DL163BT@TSOP48 [SB247-B4806]
HY29DS162BT@TSOP48 [SB247-B4806]
HY29DS163BT@TSOP48 [SB247-B4806]
HY29F002T
HY29F002T@TSOP32 [SA410T-B4001]
HY29F040@PLCC32 [SA015A1T]

HY27C64A
HY29DL162TT@TSOP48 [SB247-B4806]
HY29DL163TT@TSOP48 [SB247-B4806]
HY29DS162TT@TSOP48 [SB247-B4806]
HY29DS163TT@TSOP48 [SB247-B4806]
HY29F002T@PLCC32 [SA015A1T]
HY29F040
HY29F040@TSOP32 [SA410T-B4001]

HY29F040A
HY29F040A@TSOP32 [SA410T-B4001]
HY29F200B@PSOP44 [SA638]
HY29F200T@PSOP44 [SA638]
HY29F400ABG@PSOP44 [SA638]
HY29F400ATG@PSOP44 [SA638]
HY29F400BG@PSOP44 [SA638]
HY29F400TG@PSOP44 [SA638]
HY29F800ABG@PSOP44 [SA638]
HY29F800ATG@PSOP44 [SA638]
HY29F800BG@PSOP44 [SA638]
HY29F800TG@PSOP44 [SA638]
HY29LV160BT@TSOP48 [SB247-B4806]
HY29LV320BT@TSOP48 [SB247-B4806]
HY29LV400BT@TSOP48 [SB247-B4806]
HY29LV800BG@PSOP44 [SA638]
HY29LV800TG@PSOP44 [SA638]
HY93C46
HY93C56
HY93C66
HY93C76
HY93C86

HY29F040A@PLCC32 [SA015A1T]
HY29F080@TSOP40 [SA409T-B4002]
HY29F200B@TSOP48 [SB247-B4806]
HY29F200T@TSOP48 [SB247-B4806]
HY29F400ABT@TSOP48 [SB247-B4806]
HY29F400ATT@TSOP48 [SB247-B4806]
HY29F400BT@TSOP48 [SB247-B4806]
HY29F400TT@TSOP48 [SB247-B4806]
HY29F800ABT@TSOP48 [SB247-B4806]
HY29F800ATT@TSOP48 [SB247-B4806]
HY29F800BT@TSOP48 [SB247-B4806]
HY29F800TT@TSOP48 [SB247-B4806]
HY29LV160TT@TSOP48 [SB247-B4806]
HY29LV320TT@TSOP48 [SB247-B4806]
HY29LV400TT@TSOP48 [SB247-B4806]
HY29LV800BT@TSOP48 [SB247-B4806]
HY29LV800TT@TSOP48 [SB247-B4806]
HY93C46@S0IC8 [SA602A]
HY93C56@S0IC8 [SA602A]
HY93C66@S0IC8 [SA602A]
HY93C76@S0IC8 [SA602A]
HY93C86@S0IC8 [SA602A]

MICROCONTROLLER

GMS97C1051
GMS97C2051
GMS97C51
GMS97C51@TQFP44 [SA675-B4805]
GMS97C52@PLCC44 [SA244]
GMS97C54
GMS97C54@TQFP44 [SA675-B4805]
GMS97C56@PLCC44 [SA244]
GMS97C58
GMS97C58@TQFP44 [SA675-B4805]
GMS97L1051@S0IC20 [SA404]
GMS97L2051@S0IC20 [SA404]
GMS97L51@PLCC44 [SA244]
GMS97L52
GMS97L52@TQFP44 [SA675-B4805]
GMS97L54@PLCC44 [SA244]
GMS97L56
GMS97L56@TQFP44 [SA675-B4805]
GMS97L58@PLCC44 [SA244]
GMS99C51
GMS99C51@TQFP44 [SA675-B4805]
GMS99C52@PLCC44 [SA244]
GMS99C58
GMS99C58@TQFP44 [SA675-B4805]
HMS99C51@PLCC44 [SA244]
HMS99C52
HMS99C52@TQFP44 [SA675-B4805]
HMS99C58@PLCC44 [SA244]

GMS97C1051@S0IC20 [SA404]
GMS97C2051@S0IC20 [SA404]
GMS97C51@PLCC44 [SA244]
GMS97C52
GMS97C52@TQFP44 [SA675-B4805]
GMS97C54@PLCC44 [SA244]
GMS97C56
GMS97C56@TQFP44 [SA675-B4805]
GMS97C58@PLCC44 [SA244]
GMS97L1051
GMS97L2051
GMS97L51
GMS97L51@TQFP44 [SA675-B4805]
GMS97L52@PLCC44 [SA244]
GMS97L54
GMS97L54@TQFP44 [SA675-B4805]
GMS97L56@PLCC44 [SA244]
GMS97L58
GMS97L58@TQFP44 [SA675-B4805]
GMS99C51@PLCC44 [SA244]
GMS99C52
GMS99C52@TQFP44 [SA675-B4805]
GMS99C58@PLCC44 [SA244]
HMS99C51
HMS99C51@TQFP44 [SA675-B4805]
HMS99C52@PLCC44 [SA244]
HMS99C58
HMS99C58@TQFP44 [SA675-B4805]

ICE

E (E) PROM / FRAM / NVRAM

ICE27C010
ICE27C010@TSOP32 [SA410T-B4001]
ICE27C020@PLCC32 [SA015A1T]
ICE27C512
ICE27C512@TSOP28 [SA430T-B4003]
ICE27LC010@PLCC32 [SA015A1T]
ICE27LC020
ICE27LC020@TSOP32 [SA410T-B4001]
ICE27LC512@PLCC32 [SA015A1T]
ICE28LF010
ICE37C512
ICE37C512@TSOP32 [SA410T-B4001]
ICE37LC512@PLCC32 [SA015A1T]

ICE27C010@PLCC32 [SA015A1T]
ICE27C020
ICE27C020@TSOP32 [SA410T-B4001]
ICE27C512@PLCC32 [SA015A1T]
ICE27LC010
ICE27LC010@TSOP32 [SA410T-B4001]
ICE27LC020@PLCC32 [SA015A1T]
ICE27LC512
ICE27LC512@TSOP28 [SA430T-B4003]
ICE28LF010@PLCC32 [SA015A1T]
ICE37C512@PLCC32 [SA015A1T]
ICE37LC512
ICE37LC512@TSOP32 [SA410T-B4001]

ICSI

MICROCONTROLLER

IC89LV51A
IC89LV51A@TQFP44 [SA675-B4805]
IC89LV52A@PLCC44 [SA244]
IS89C51A
IS89C51A@TQFP44 [SA675-B4805]
IS89C52A@PLCC44 [SA244]
IS89C54
IS89C54@TQFP44 [SA675-B4805]
IS89C58@PLCC44 [SA244]
IS89C64
IS89C64@TQFP44 [SA675-B4805]
IS89E54@PLCC44 [SA244]
IS89E58
IS89E58@TQFP44 [SA675-B4805]
IS89E64@PLCC44 [SA244]

IC89LV51A@PLCC44 [SA244]
IC89LV52A
IC89LV52A@TQFP44 [SA675-B4805]
IS89C51A@PLCC44 [SA244]
IS89C52A
IS89C52A@TQFP44 [SA675-B4805]
IS89C54@PLCC44 [SA244]
IS89C58
IS89C58@TQFP44 [SA675-B4805]
IS89C64@PLCC44 [SA244]
IS89E54
IS89E54@TQFP44 [SA675-B4805]
IS89E58@PLCC44 [SA244]
IS89E64
IS89E64@TQFP44 [SA675-B4805]

ICT

E (E) PROM/FRAM/NVRAM

27CX010
27CX010@TSOP32 [SA410T-B4001]
27CX321
27CX641
93C46
93C46A
93C56A
93C66A
93CX46
93CX56
93CX66

27CX010@PLCC32 [SA015A1T]
27CX256
27CX322
27CX642
93C46@S0IC8 [SA602A]
93C46A@S0IC8 [SA602A]
93C56A@S0IC8 [SA602A]
93C66A@S0IC8 [SA602A]
93CX46@S0IC8 [SA602A]
93CX56@S0IC8 [SA602A]
93CX66@S0IC8 [SA602A]

PLD

PEEL18CV8Z
PEEL18CV8Z@S0IC20 [SA404]
PEEL18LV8Z

PEEL18CV8Z@PLCC20 [SA001A-B2001]
PEEL18CV8Z@TSOP20 [SA026-B3201]
PEEL18LV8Z@PLCC20 [SA001A-B2001]

PEEL18LV8Z@S0IC20 [SA404]	PEEL18LV8Z@TSOP20 [SA026-B3201]
PEEL22CV10A	PEEL22CV10A@PLCC28 [SA008A]
PEEL22CV10A@S0IC24 [SA404]	PEEL22CV10A@TSOP24 [SA026-B3201]
PEEL22CV10A+	PEEL22CV10A+@PLCC28 [SA008A]
PEEL22CV10A+@S0IC24 [SA404]	
PEEL22CV10A+@TSOP24 [SA026-B3201]	PEEL22CV10A++@PLCC28 [SA008A]
PEEL22CV10A++	
PEEL22CV10A++@S0IC24 [SA404]	
PEEL22CV10A++@TSOP24 [SA026-B3201]	
PEEL22CV10AZ	PEEL22CV10AZ@PLCC28 [SA008A]
PEEL22CV10AZ@S0IC24 [SA404]	
PEEL22CV10AZ@TSOP24 [SA026-B3201]	
PEEL22CV10AZ+	PEEL22CV10AZ+@PLCC28 [SA008A]
PEEL22CV10AZ+@S0IC24 [SA404]	
PEEL22CV10AZ+@TSOP24 [SA026-B3201]	
PEEL22CV10AZ++	PEEL22CV10AZ++@PLCC28 [SA008A]
PEEL22CV10AZ++@S0IC24 [SA404]	
PEEL22CV10AZ++@TSOP24 [SA026-B3201]	
PEEL22LV10AZ	PEEL22LV10AZ@PLCC28 [SA008A]
PEEL22LV10AZ@S0IC24 [SA404]	
PEEL22LV10AZ@TSOP24 [SA026-B3201]	
PEEL22LV10AZ+	PEEL22LV10AZ+@PLCC28 [SA008A]
PEEL22LV10AZ+@S0IC24 [SA404]	
PEEL22LV10AZ+@TSOP24 [SA026-B3201]	
PEEL22LV10AZ++	PEEL22LV10AZ++@PLCC28 [SA008A]
PEEL22LV10AZ++@S0IC24 [SA404]	
PEEL22LV10AZ++@TSOP24 [SA026-B3201]	

IMT

E(E) PROM/FRAM/NVRAM

IM29F001B	
IM29F001B(REVERSE)@TSOP32 [SA410T-B4001]	
IM29F001B@PLCC32 [SA015A1T]	IM29F001B@TSOP32 [SA410T-B4001]
IM29F001B@VSOP32 [SA620-B4807]	IM29F001T
IM29F001T(REVERSE)@TSOP32 [SA410T-B4001]	
IM29F001T@PLCC32 [SA015A1T]	IM29F001T@TSOP32 [SA410T-B4001]
IM29F001T@VSOP32 [SA620-B4807]	IM29F002B
IM29F002B(REVERSE)@TSOP32 [SA410T-B4001]	
IM29F002B@PLCC32 [SA015A1T]	IM29F002B@TSOP32 [SA410T-B4001]
IM29F002B@VSOP32 [SA620-B4807]	IM29F002T
IM29F002T(REVERSE)@TSOP32 [SA410T-B4001]	
IM29F002T@PLCC32 [SA015A1T]	IM29F002T@TSOP32 [SA410T-B4001]
IM29F002T@VSOP32 [SA620-B4807]	IM29F004B
IM29F004B(REVERSE)@TSOP32 [SA410T-B4001]	
IM29F004B@PLCC32 [SA015A1T]	IM29F004B@TSOP32 [SA410T-B4001]
IM29F004B@VSOP32 [SA620-B4807]	IM29F004T
IM29F004T(REVERSE)@TSOP32 [SA410T-B4001]	
IM29F004T@PLCC32 [SA015A1T]	IM29F004T@TSOP32 [SA410T-B4001]
IM29F004T@VSOP32 [SA620-B4807]	IM29LV004B
IM29LV004B(REVERSE)@TSOP32 [SA410T-B4001]	
IM29LV004B@PLCC32 [SA015A1T]	IM29LV004B@TSOP32 [SA410T-B4001]
IM29LV004B@VSOP32 [SA620-B4807]	IM29LV004T
IM29LV004T(REVERSE)@TSOP32 [SA410T-B4001]	
IM29LV004T@PLCC32 [SA015A1T]	IM29LV004T@TSOP32 [SA410T-B4001]
IM29LV004T@VSOP32 [SA620-B4807]	IM29LV400B@PSOP44 [SA638]
IM29LV400B@TSOP48 [SA247-B4806]	IM29LV400T@PSOP44 [SA638]

INTEL**E(E) PROM/FRAM/NVRAM**

27010	27010@PLCC32 [SA015A1T]
27010@TSOP32 [SA410T-B4001]	27128
27128A	27128B
2716	27210
27256	2732
2732A	27512
2764	2764A
27C010	27C010@PLCC32 [SA015A1T]
27C010@TSOP32 [SA410T-B4001]	27C010A
27C010A@PLCC32 [SA015A1T]	27C010A@TSOP32 [SA410T-B4001]
27C020	27C020@PLCC32 [SA015A1T]
27C020@TSOP32 [SA410T-B4001]	27C040
27C040@PLCC32 [SA015A1T]	27C040@TSOP32 [SA410T-B4001]
27C100	27C100@PLCC32 [SA015A1T]
27C100@TSOP32 [SA410T-B4001]	27C128
27C128@PLCC32 [SA015A1T]	27C210
27C210@PLCC44 [SA244]	27C220
27C220@PLCC44 [SA244]	27C240
27C240@PLCC44 [SA244]	27C256
27C256@PLCC32 [SA015A1T]	27C400
27C400@PLCC44 [SA244]	27C512
27C512@PLCC32 [SA015A1T]	27C64
27C64@PLCC32 [SA015A1T]	27C800
27S512	2816A
2817A	2864A
87C256	87C64
D27011	D27513
D27C011	D27C513
D2816	D28F256
D28F256A	D28F512
E28F001BX-B@TSOP32 [SA410T-B4001]	E28F002BEB@TSOP40 [SA409T-B4002]
E28F001BX-T@TSOP32 [SA410T-B4001]	E28F002BLB@TSOP40 [SA409T-B4002]
E28F002BCT@TSOP40 [SA409T-B4002]	E28F002BVB@TSOP40 [SA409T-B4002]
E28F002BET@TSOP40 [SA409T-B4002]	E28F002BXB@TSOP40 [SA409T-B4002]
E28F002BLT@TSOP40 [SA409T-B4002]	E28F004B5B@TSOP40 [SA409T-B4002]
E28F002BVT@TSOP40 [SA409T-B4002]	E28F004BEB@TSOP40 [SA409T-B4002]
E28F002BXT@TSOP40 [SA409T-B4002]	E28F004BLB@TSOP40 [SA409T-B4002]
E28F004B5T@TSOP40 [SA409T-B4002]	E28F004BVB@TSOP40 [SA409T-B4002]
E28F004BET@TSOP40 [SA409T-B4002]	E28F004BXB@TSOP40 [SA409T-B4002]
E28F004BLT@TSOP40 [SA409T-B4002]	E28F004S3@TSOP40 [SA409T-B4002]
E28F004BVT@TSOP40 [SA409T-B4002]	E28F004SC@TSOP40 [SA409T-B4002]
E28F004BXT@TSOP40 [SA409T-B4002]	E28F008BET@TSOP40 [SA409T-B4002]
E28F004S5@TSOP40 [SA409T-B4002]	E28F008BLT@TSOP40 [SA409T-B4002]
E28F008BEB@TSOP40 [SA409T-B4002]	E28F008BVT@TSOP40 [SA409T-B4002]
E28F008BLB@TSOP40 [SA409T-B4002]	E28F008BXT@TSOP40 [SA409T-B4002]
E28F008BVB@TSOP40 [SA409T-B4002]	E28F008S5@TSOP40 [SA409T-B4002]
E28F008BXB@TSOP40 [SA409T-B4002]	
E28F008S3@TSOP40 [SA409T-B4002]	
E28F008SA@TSOP40 [SA409T-B4002]	
E28F008SA-L@TSOP40 [SA409T-B4002]	
E28F008SC@TSOP40 [SA409T-B4002]	E28F010@TSOP32 [SA410T-B4001]
E28F016S3@TSOP40 [SA409T-B4002]	E28F016S5@TSOP40 [SA409T-B4002]

E28F016SC@TSOP40 [SA409T-B4002]	E28F020@TSOP32 [SA410T-B4001]
E28F200B5B@TSOP48 [SB247-B4806]	E28F200B5T@TSOP48 [SB247-B4806]
E28F200CVB@TSOP48 [SB247-B4806]	E28F200CVT@TSOP48 [SB247-B4806]
E28F256@TSOP32 [SA410T-B4001]	E28F256A@TSOP32 [SA410T-B4001]
E28F400B5B@TSOP48 [SB247-B4806]	E28F400B5T@TSOP48 [SB247-B4806]
E28F400CVB@TSOP48 [SB247-B4806]	E28F400CVT@TSOP48 [SB247-B4806]
E28F512@TSOP32 [SA410T-B4001]	E28F800B5B@TSOP48 [SB247-B4806]
E28F800B5T@TSOP48 [SB247-B4806]	E28F800CEB@TSOP48 [SB247-B4806]
E28F800CET@TSOP48 [SB247-B4806]	E28F800CVB@TSOP48 [SB247-B4806]
E28F800CVT@TSOP48 [SB247-B4806]	E82802AA@TSOP40 [SA409T-B4002]
E82802AB@TSOP40 [SA409T-B4002]	E82802AC@TSOP40 [SA409T-B4002]
F28F008SA@TSOP40(REVERSE) [SA409T-B4002]	
F28F010@TSOP32 [SA410T-B4001]	F28F020@TSOP32 [SA410T-B4001]
F28F020@TSOP32(REVERSE) [SA410T-B4001]	
F28F256@TSOP32 [SA410T-B4001]	F28F256A@TSOP32 [SA410T-B4001]
F28F512@TSOP32 [SA410T-B4001]	
JS28F160B3BD@TSOP48 [SB247-B4806]	
JS28F160B3TD@TSOP48 [SB247-B4806]	
JS28F160C3BD@TSOP48 [SB247-B4806]	
JS28F160C3TD@TSOP48 [SB247-B4806]	
JS28F320B3BD@TSOP48 [SB247-B4806]	
JS28F320B3TD@TSOP48 [SB247-B4806]	
JS28F320C3BD@TSOP48 [SB247-B4806]	
JS28F320C3TD@TSOP48 [SB247-B4806]	
JS28F800C3BD@TSOP48 [SB247-B4806]	
JS28F800C3TD@TSOP48 [SB247-B4806]	
M28F010	M28F010@PLCC32 [SA015A1T]
M28F010@TSOP32 [SA410T-B4001]	N28F001BN-B@PLCC32 [SA015A1T]
N28F001BN-T@PLCC32 [SA015A1T]	N28F001BX-B@PLCC32 [SA015A1T]
N28F001BX-T@PLCC32 [SA015A1T]	N28F010@PLCC32 [SA015A1T]
N28F020@PLCC32 [SA015A1T]	N28F256@PLCC32 [SA015A1T]
N28F256A@PLCC32 [SA015A1T]	N28F512@PLCC32 [SA015A1T]
N82802AA@PLCC32 [SA015A1T]	N82802AB@PLCC32 [SA015A1T]
N82802AC@PLCC32 [SA015A1T]	P27011
P27128A	P27128A@PLCC32 [SA015A1T]
P27128B	P27128B@PLCC32 [SA015A1T]
P27256	P27256@PLCC32 [SA015A1T]
P27512	P27513
P2764A	P2764A@PLCC32 [SA015A1T]
P27C011	P27C128
P27C128@PLCC32 [SA015A1T]	P27C256
P27C256@PLCC32 [SA015A1T]	P27C513
P27C64	P27C64@PLCC32 [SA015A1T]
P28F001BX-B	P28F001BX-T
P28F002BCT	P28F010
P28F020	P28F256
P28F256A	P28F512
P87C64	P87C64@PLCC32 [SA015A1T]
PA28F004S3@PSOP44 [SA638]	PA28F004S5@PSOP44 [SA638]
PA28F004SC@PSOP44 [SA638]	PA28F008S3@PSOP44 [SA638]
PA28F008S5@PSOP44 [SA638]	PA28F008SA@PSOP44 [SA638]
PA28F008SA-L@PSOP44 [SA638]	PA28F008SC@PSOP44 [SA638]
PA28F016S3@PSOP44 [SA638]	PA28F016S5@PSOP44 [SA638]
PA28F016SC@PSOP44 [SA638]	PA28F200B5B@PSOP44 [SA638]
PA28F200B5T@PSOP44 [SA638]	PA28F200BVB@PSOP44 [SA638]
PA28F200BVT@PSOP44 [SA638]	PA28F200BXB@PSOP44 [SA638]
PA28F200BXT@PSOP44 [SA638]	PA28F400B5B@PSOP44 [SA638]
PA28F400B5T@PSOP44 [SA638]	PA28F400BLB@PSOP44 [SA638]
PA28F400BLT@PSOP44 [SA638]	PA28F400BVB@PSOP44 [SA638]

PA28F400BVT@PSOP44 [SA638]
PA28F400BXT@PSOP44 [SA638]
PA28F800B5T@PSOP44 [SA638]
PA28F800BVT@PSOP44 [SA638]
QB25F016S33T60@S0IC8 [SA605B]
QB25F160S33T60@S0IC16 [SA404]
QB25F320S33T60@S0IC16 [SA404]
QB25F640S33T60@S0IC16 [SA404]
QH25F016S33T60@S0IC8 [SA605B]
QH25F160S33T60@S0IC16 [SA404]
QH25F320S33T60@S0IC16 [SA404]
QH25F640S33T60@S0IC16 [SA404]
TB28F004S5@PSOP44 [SA638]
TB28F008S3@PSOP44 [SA638]
TB28F008SA@PSOP44 [SA638]
TB28F008SC@PSOP44 [SA638]
TB28F016S5@PSOP44 [SA638]
TB28F200B5B@PSOP44 [SA638]
TB28F200BVB@PSOP44 [SA638]
TB28F200BXB@PSOP44 [SA638]
TB28F400B5B@PSOP44 [SA638]
TB28F400BVB@PSOP44 [SA638]
TB28F400BXB@PSOP44 [SA638]
TB28F800B5B@PSOP44 [SA638]
TB28F800BVB@PSOP44 [SA638]
TE28F002BEB@TSOP40 [SA409T-B4002]
TE28F002BET@TSOP40 [SA409T-B4002]
TE28F002BVB@TSOP40 [SA409T-B4002]
TE28F002BVT@TSOP40 [SA409T-B4002]
TE28F002BXB@TSOP40 [SA409T-B4002]
TE28F002BXT@TSOP40 [SA409T-B4002]
TE28F004BEB@TSOP40 [SA409T-B4002]
TE28F004BET@TSOP40 [SA409T-B4002]
TE28F004BVB@TSOP40 [SA409T-B4002]
TE28F004BVT@TSOP40 [SA409T-B4002]
TE28F004BXB@TSOP40 [SA409T-B4002]
TE28F004BXT@TSOP40 [SA409T-B4002]
TE28F004S3@TSOP40 [SA409T-B4002]
TE28F004SC@TSOP40 [SA409T-B4002]
TE28F008B3B@TSOP40 [SA409T-B4002]
TE28F008B3BA@TSOP40 [SA409T-B4002]
TE28F008B3T@TSOP40 [SA409T-B4002]
TE28F008B3TA@TSOP40 [SA409T-B4002]
TE28F008BEB@TSOP40 [SA409T-B4002]
TE28F008BET@TSOP40 [SA409T-B4002]
TE28F008BVB@TSOP40 [SA409T-B4002]
TE28F008BVT@TSOP40 [SA409T-B4002]
TE28F008C3BA@TSOP40 [SA409T-B4002]
TE28F008C3TA@TSOP40 [SA409T-B4002]
TE28F008S3@TSOP40 [SA409T-B4002]
TE28F008SA@TSOP40 [SA409T-B4002]
TE28F008SA-L@TSOP40 [SA409T-B4002]
TE28F008SC@TSOP40 [SA409T-B4002]
TE28F016B3B@TSOP40 [SA409T-B4002]
TE28F016B3T@TSOP40 [SA409T-B4002]
TE28F016C3BA@TSOP40 [SA409T-B4002]
TE28F016C3TA@TSOP40 [SA409T-B4002]
TE28F016S3@TSOP40 [SA409T-B4002]
TE28F016SC@TSOP40 [SA409T-B4002]

PA28F400BXB@PSOP44 [SA638]
PA28F800B5B@PSOP44 [SA638]
PA28F800BVB@PSOP44 [SA638]
QB25F016S33B60@S0IC8 [SA605B]
QB25F160S33B60@S0IC16 [SA404]
QB25F320S33B60@S0IC16 [SA404]
QB25F640S33B60@S0IC16 [SA404]
QH25F016S33B60@S0IC8 [SA605B]
QH25F160S33B60@S0IC16 [SA404]
QH25F320S33B60@S0IC16 [SA404]
QH25F640S33B60@S0IC16 [SA404]
TB28F004S3@PSOP44 [SA638]
TB28F004SC@PSOP44 [SA638]
TB28F008S5@PSOP44 [SA638]
TB28F008SA-L@PSOP44 [SA638]
TB28F016S3@PSOP44 [SA638]
TB28F016SC@PSOP44 [SA638]
TB28F200B5T@PSOP44 [SA638]
TB28F200BVT@PSOP44 [SA638]
TB28F200BXT@PSOP44 [SA638]
TB28F400B5T@PSOP44 [SA638]
TB28F400BVT@PSOP44 [SA638]
TB28F400BXT@PSOP44 [SA638]
TB28F800B5T@PSOP44 [SA638]
TB28F800BVT@PSOP44 [SA638]

TE28F004S5@TSOP40 [SA409T-B4002]

TE28F008S5@TSOP40 [SA409T-B4002]

TE28F016S5@TSOP40 [SA409T-B4002]
TE28F160B3B@TSOP48 [SB247-B4806]

TE28F160B3BA@TSOP48 [SB247-B4806]
 TE28F160B3BC@TSOP48 [SB247-B4806]
 TE28F160B3BD@TSOP48 [SB247-B4806]
 TE28F160B3T@TSOP48 [SB247-B4806]
 TE28F160B3TA@TSOP48 [SB247-B4806]
 TE28F160B3TC@TSOP48 [SB247-B4806]
 TE28F160B3TD@TSOP48 [SB247-B4806]
 TE28F160C3BA@TSOP48 [SB247-B4806]
 TE28F160C3BC@TSOP48 [SB247-B4806]
 TE28F160C3BD@TSOP48 [SB247-B4806]
 TE28F160C3TA@TSOP48 [SB247-B4806]
 TE28F160C3TC@TSOP48 [SB247-B4806]
 TE28F160C3TD@TSOP48 [SB247-B4806]
 TE28F200B5B@TSOP48 [SB247-B4806]
 TE28F200CVB@TSOP48 [SB247-B4806]
 TE28F320B3B@TSOP48 [SB247-B4806]
 TE28F320B3BA@TSOP48 [SB247-B4806]
 TE28F320B3BC@TSOP48 [SB247-B4806]
 TE28F320B3BD@TSOP48 [SB247-B4806]
 TE28F320B3T@TSOP48 [SB247-B4806]
 TE28F320B3TA@TSOP48 [SB247-B4806]
 TE28F320B3TC@TSOP48 [SB247-B4806]
 TE28F320B3TD@TSOP48 [SB247-B4806]
 TE28F320C3BA@TSOP48 [SB247-B4806]
 TE28F320C3BC@TSOP48 [SB247-B4806]
 TE28F320C3BD@TSOP48 [SB247-B4806]
 TE28F320C3TA@TSOP48 [SB247-B4806]
 TE28F320C3TC@TSOP48 [SB247-B4806]
 TE28F320C3TD@TSOP48 [SB247-B4806]
 TE28F400B3B@TSOP48 [SB247-B4806]
 TE28F400B5B@TSOP48 [SB247-B4806]
 TE28F400CEB@TSOP48 [SB247-B4806]
 TE28F400CVB@TSOP48 [SB247-B4806]
 TE28F640B3BC@TSOP48 [SB247-B4806]
 TE28F640B3TC@TSOP48 [SB247-B4806]
 TE28F640C3BC@TSOP48 [SB247-B4806]
 TE28F640C3TC@TSOP48 [SB247-B4806]
 TE28F800B3B@TSOP48 [SB247-B4806]
 TE28F800B3BA@TSOP48 [SB247-B4806]
 TE28F800B3T@TSOP48 [SB247-B4806]
 TE28F800B3TA@TSOP48 [SB247-B4806]
 TE28F800B5B@TSOP48 [SB247-B4806]
 TE28F800C3BA@TSOP48 [SB247-B4806]
 TE28F800C3BD@TSOP48 [SB247-B4806]
 TE28F800C3TA@TSOP48 [SB247-B4806]
 TE28F800C3TD@TSOP48 [SB247-B4806]
 TE28F800CEB@TSOP48 [SB247-B4806]
 TE28F800CVB@TSOP48 [SB247-B4806]

TE28F200B5T@TSOP48 [SB247-B4806]
 TE28F200CVT@TSOP48 [SB247-B4806]

TE28F400B3T@TSOP48 [SB247-B4806]
 TE28F400B5T@TSOP48 [SB247-B4806]
 TE28F400CET@TSOP48 [SB247-B4806]
 TE28F400CVT@TSOP48 [SB247-B4806]

TE28F800B5T@TSOP48 [SB247-B4806]

TE28F800CET@TSOP48 [SB247-B4806]
 TE28F800CVT@TSOP48 [SB247-B4806]

MICROCONTROLLER

87C151SA
 87C151SB
 87C251SA
 87C251SB
 87C251SP
 87C251SQ
 87C51
 87C51@TQFP44 [SA675-B4805]

87C151SA@PLCC44 [SA244]
 87C151SB@PLCC44 [SA244]
 87C251SA@PLCC44 [SA244]
 87C251SB@PLCC44 [SA244]
 87C251SP@PLCC44 [SA244]
 87C251SQ@PLCC44 [SA244]
 87C51@PLCC44 [SA244]
 87C51FA

87C51FA@PLCC44 [SA244]
87C51FB
87C51FB@TQFP44 [SA675-B4805]
87C51FC@PLCC44 [SA244]
87C51RA
87C51RA@TQFP44 [SA675-B4805]
87C51RB@PLCC44 [SA244]
87C51RC
87C51RC@TQFP44 [SA245A-B4805]
87C52@PLCC44 [SA244]
87C54
87C54@TQFP44 [SA245A-B4805]
87C58@PLCC44 [SA244]
87L51FA
87L51FA@TQFP44 [SA675-B4805]
87L51FB@PLCC44 [SA244]
87L51FC@PLCC44 [SA244]
87L52
87L52@TQFP44 [SA675-B4805]
87L54@TQFP44 [SA245A-B4805]
87L58@TQFP44 [SA245A-B4805]

87C51FA@TQFP44 [SA675-B4805]
87C51FB@PLCC44 [SA244]
87C51FC
87C51FC@TQFP44 [SA245A-B4805]
87C51RA@PLCC44 [SA244]
87C51RB
87C51RB@TQFP44 [SA675-B4805]
87C51RC@PLCC44 [SA244]
87C52
87C52@TQFP44 [SA675-B4805]
87C54@PLCC44 [SA244]
87C58
87C58@TQFP44 [SA245A-B4805]
87L51FA@PLCC44 [SA244]
87L51FB
87L51FB@TQFP44 [SA675-B4805]
87L51FC@TQFP44 [SA245A-B4805]
87L52@PLCC44 [SA244]
87L54@PLCC44 [SA244]
87L58@PLCC44 [SA244]

INTELSIL

E(E)PROM/FRAM/NVRAM

HS-6617RH
HS-6617RH-T
HS-6664RH
HS-6664RH-T
HS-6883RH
HS-6883RH-T

HS-6617RH@S0IC24 [SA404]
HS-6617RH-T@S0IC24 [SA404]
HS-6664RH@S0IC28 [SA404]
HS-6664RH-T@S0IC28 [SA404]
HS-6883RH@S0IC24 [SA404]
HS-6883RH-T@S0IC24 [SA404]

INTERSIL

E(E)PROM/FRAM/NVRAM

X4043
X4043@S0IC8 [SA602A]
X4045@MSOP8 [SA026-B3201]

X4043@MSOP8 [SA026-B3201]
X4045
X4045@S0IC8 [SA602A]

ISSI

E(E)PROM/FRAM/NVRAM

IS24C01
IS24C01@S0IC8 [SA602A]
IS24C01B
IS24C01B@S0IC8 [SA602A]
IS24C01C
IS24C01C@S0IC8 [SA602A]
IS24C02
IS24C02@S0IC8 [SA602A]
IS24C02A
IS24C02A@MSOP8 [SA666]
IS24C02A@TSSOP8 [SA026-B3201]

IS24C01@MSOP8 [SA666]
IS24C01@TSSOP8 [SA026-B3201]
IS24C01B@MSOP8 [SA666]
IS24C01B@TSSOP8 [SA026-B3201]
IS24C01C@MSOP8 [SA666]
IS24C01C@TSSOP8 [SA026-B3201]
IS24C02@MSOP8 [SA666]
IS24C02@TSSOP8 [SA026-B3201]
IS24C02A@DFN8
IS24C02A@S0IC8 [SA602A]
IS24C02B

IS24C02B@DFN8
IS24C02B@S0IC8 [SA602A]
IS24C02C
IS24C02C@MSOP8 [SA666]
IS24C02C@TSSOP8 [SA026-B3201]
IS24C02E@DFN8
IS24C02E@S0IC8 [SA602A]
IS24C04
IS24C04@S0IC8 [SA602A]
IS24C04A
IS24C04A@MSOP8 [SA666]
IS24C04A@TSSOP8 [SA026-B3201]
IS24C04B@DFN8
IS24C04B@S0IC8 [SA602A]
IS24C08
IS24C08@S0IC8 [SA602A]
IS24C08A
IS24C08A@MSOP8 [SA666]
IS24C08A@TSSOP8 [SA026-B3201]
IS24C08B@DFN8
IS24C08B@S0IC8 [SA602A]
IS24C128
IS24C128@TSSOP14 [SA026-B3201]
IS24C128B@S0IC8 [SA602A]
IS24C16
IS24C16@S0IC8 [SA602A]
IS24C16A
IS24C16A@S0IC8 [SA602A]
IS24C16B
IS24C16B@S0IC8 [SA602A]
IS24C256
IS24C256@TSSOP14 [SA026-B3201]
IS24C256A@S0IC8 [SA602A]
IS24C256C
IS24C256C@TSSOP14 [SA026-B3201]
IS24C32@S0IC8 [SA602A]
IS24C32A
IS24C32A@S0IC8 [SA602A]
IS24C32B
IS24C32B@TSSOP8 [SA026-B3201]
IS24C32C@MSOP8 [SA666]
IS24C32C@TSSOP8 [SA026-B3201]
IS24C64@S0IC8 [SA602A]
IS24C64A
IS24C64A@S0IC8 [SA602A]
IS24C64B
IS24C64B@TSSOP8 [SA026-B3201]
IS24C64C@MSOP8 [SA666]
IS24C64C@TSSOP8 [SA026-B3201]
IS24L128@S0IC8(150mil) [SA602A]
IS24L256
IS24L256@S0IC8(200mil) [SA605B]
IS25C01@S0IC8 [SA602A]
IS25C02
IS25C02@TSSOP8 [SA026-B3201]
IS25C04@S0IC8 [SA602A]
IS25C08
IS25C08@TSSOP8 [SA026-B3201]
IS25C128@TSSOP8 [SA026-B3201]

IS24C02B@MSOP8 [SA666]
IS24C02B@TSSOP8 [SA026-B3201]
IS24C02C@DFN8
IS24C02C@S0IC8 [SA602A]
IS24C02E
IS24C02E@MSOP8 [SA666]
IS24C02E@TSSOP8 [SA026-B3201]
IS24C04@MSOP8 [SA666]
IS24C04@TSSOP8 [SA026-B3201]
IS24C04A@DFN8
IS24C04A@S0IC8 [SA602A]
IS24C04B
IS24C04B@MSOP8 [SA666]
IS24C04B@TSSOP8 [SA026-B3201]
IS24C08@MSOP8 [SA666]
IS24C08@TSSOP8 [SA026-B3201]
IS24C08A@DFN8
IS24C08A@S0IC8 [SA602A]
IS24C08B
IS24C08B@MSOP8 [SA666]
IS24C08B@TSSOP8 [SA026-B3201]
IS24C128@S0IC8 [SA602A]
IS24C128B
IS24C128B@TSSOP14 [SA026-B3201]
IS24C16@MSOP8 [SA666]
IS24C16@TSSOP8 [SA026-B3201]
IS24C16A@MSOP8 [SA666]
IS24C16A@TSSOP8 [SA026-B3201]
IS24C16B@MSOP8 [SA666]
IS24C16B@TSSOP8 [SA026-B3201]
IS24C256@S0IC8 [SA602A]
IS24C256A
IS24C256A@TSSOP14 [SA026-B3201]
IS24C256C@S0IC8 [SA602A]
IS24C32
IS24C32@TSSOP8 [SA026-B3201]
IS24C32A@MSOP8 [SA666]
IS24C32A@TSSOP8 [SA026-B3201]
IS24C32B@S0IC8 [SA602A]
IS24C32C
IS24C32C@S0IC8 [SA602A]
IS24C64
IS24C64@TSSOP8 [SA026-B3201]
IS24C64A@MSOP8 [SA666]
IS24C64A@TSSOP8 [SA026-B3201]
IS24C64B@S0IC8 [SA602A]
IS24C64C
IS24C64C@S0IC8 [SA602A]
IS24L128
IS24L128@S0IC8(200mil) [SA605B]
IS24L256@S0IC8(150mil) [SA602A]
IS25C01
IS25C01@TSSOP8 [SA026-B3201]
IS25C02@S0IC8 [SA602A]
IS25C04
IS25C04@TSSOP8
IS25C08@S0IC8 [SA602A]
IS25C128@S0IC8 [SA602A]
IS25C128A@S0IC8 [SA602A]

IS25C128A@TSSOP8 [SA026-B3201]	IS25C16
IS25C16@S0IC8 [SA602A]	IS25C16@TSSOP8 [SA026-B3201]
IS25C256@S0IC8 [SA602A]	IS25C256@TSSOP8 [SA026-B3201]
IS25C256A@S0IC8 [SA602A]	IS25C256A@TSSOP8 [SA026-B3201]
IS25C32A	IS25C32A@S0IC8 [SA602A]
IS25C32A@TSSOP8 [SA026-B3201]	IS25C32B
IS25C32B@S0IC8 [SA602A]	IS25C32B@TSSOP8 [SA026-B3201]
IS25C64A	IS25C64A@S0IC8 [SA602A]
IS25C64A@TSSOP8 [SA026-B3201]	IS25C64B
IS25C64B@S0IC8 [SA602A]	IS25C64B@TSSOP8 [SA026-B3201]
IS27C010	IS27C010@PLCC32 [SA015A1T]
IS27C010@TSOP32 [SA410T-B4001]	IS27C020
IS27C020@PLCC32 [SA015A1T]	IS27C020@TSOP32 [SA410T-B4001]
IS27C256	IS27C256@PLCC32 [SA015A1T]
IS27C512	IS27C512@PLCC32 [SA015A1T]
IS27C512@TSOP28 [SA430T-B4003]	IS27HC010
IS27HC010@PLCC32 [SA015A1T]	IS27HC010@TSOP32 [SA410T-B4001]
IS27HC020	IS27HC020@PLCC32 [SA015A1T]
IS27HC020@TSOP32 [SA410T-B4001]	IS27HC256
IS27HC256@PLCC32 [SA015A1T]	IS27HC512
IS27HC512@PLCC32 [SA015A1T]	IS27HC512@TSOP28 [SA430T-B4003]
IS27LV010	IS27LV010@PLCC32 [SA015A1T]
IS27LV010@TSOP32 [SA410T-B4001]	IS27LV512
IS27LV512@PLCC32 [SA015A1T]	IS27LV512@TSOP28 [SA430T-B4003]
IS28F010	IS28F010@PLCC32 [SA015A1T]
IS28F010@TSOP32 [SA410T-B4001]	IS28F010A
IS28F010A@PLCC32 [SA015A1T]	IS28F010A@TSOP32 [SA410T-B4001]
IS28F020	IS28F020@PLCC32 [SA015A1T]
IS28F020@TSOP32 [SA410T-B4001]	IS29F010
IS29F010@PLCC32 [SA015A1T]	IS29F010@TSOP32 [SA410T-B4001]
IS34C02	IS34C02@MSOP8 [SA666]
IS34C02@S0IC8 [SA602A]	IS34C02@TSSOP8 [SA026-B3201]
IS34C02B@DFN8	IS34C02B@TSSOP8
IS93C46	IS93C46@S0IC8 [SA602A]
IS93C46A(08bit)	IS93C46A(08bit)@S0IC8 [SA602A]
IS93C46A(08bit)@TSSOP8 [SA026-B3201]	IS93C46A(16bit)@S0IC8 [SA602A]
IS93C46A(16bit)	IS93C46B@S0IC8 [SA602A]
IS93C46A(16bit)@TSSOP8 [SA026-B3201]	IS93C46D(08bit)
IS93C46B	IS93C46D(16bit)@S0IC8 [SA602A]
IS93C46B@TSSOP8	IS93C56@S0IC8 [SA602A]
IS93C46D(08bit)@S0IC8 [SA602A]	IS93C56A(08bit)@S0IC8 [SA602A]
IS93C46D(08bit)@TSSOP8 [SA026-B3201]	IS93C56A(16bit)@S0IC8 [SA602A]
IS93C46D(16bit)	IS93C66@S0IC8 [SA602A]
IS93C46D(16bit)@TSSOP8 [SA026-B3201]	IS93C66A(08bit)@S0IC8 [SA602A]
IS93C56	IS93C66A(16bit)@S0IC8 [SA602A]
IS93C56A(08bit)	IS93C76A(08bit)@S0IC8 [SA602A]
IS93C56A(08bit)@TSSOP8 [SA026-B3201]	IS93C76A(16bit)@S0IC8 [SA602A]
IS93C56A(16bit)	IS93C86A(08bit)@S0IC8 [SA602A]
IS93C56A(16bit)@TSSOP8 [SA026-B3201]	
IS93C66	
IS93C66A(08bit)	
IS93C66A(08bit)@TSSOP8 [SA026-B3201]	
IS93C66A(16bit)	
IS93C66A(16bit)@TSSOP8 [SA026-B3201]	
IS93C76A(08bit)	
IS93C76A(08bit)@TSSOP8 [SA026-B3201]	
IS93C76A(16bit)	
IS93C76A(16bit)@TSSOP8 [SA026-B3201]	
IS93C86A(08bit)	

IS93C86A(08bit)@TSSOP8 [SA026-B3201]
IS93C86A(16bit) IS93C86A(16bit)@SOIC8 [SA602A]
IS93C86A(16bit)@TSSOP8 [SA026-B3201]

MICROCONTROLLER

IS89C51A IS89C51A@PLCC44 [SA244]
IS89C51A@TQFP44 [SA675-B4805] IS89C52A
IS89C52A@PLCC44 [SA244] IS89C52A@TQFP44 [SA675-B4805]

K-LINE

E(E)PROM/FRAM/NVRAM

K24C32 K24C32@SOIC8 [SA602A]
K24C32@TSSOP8 [SA026-B3201] K24C64
K24C64@SOIC8 [SA602A] K24C64@TSSOP8

LATTICE

PLD

GAL16LV8 GAL16LV8@PLCC20 [SA001A-B2001]
GAL16LV8C GAL16LV8C@PLCC20 [SA001A-B2001]
GAL16LV8D GAL16LV8D@PLCC20 [SA001A-B2001]
GAL16LV8Z GAL16LV8Z@PLCC20 [SA001A-B2001]
GAL16LV8ZD GAL16LV8ZD@PLCC20 [SA001A-B2001]
GAL16V8 GAL16V8@PLCC20 [SA001A-B2001]
GAL16V8@SOIC20 [SA404] GAL16V8A
GAL16V8A@PLCC20 [SA001A-B2001] GAL16V8A@SOIC20 [SA404]
GAL16V8B GAL16V8B@PLCC20 [SA001A-B2001]
GAL16V8B@SOIC20 [SA404] GAL16V8C
GAL16V8C@PLCC20 [SA001A-B2001] GAL16V8C@SOIC20 [SA404]
GAL16V8D GAL16V8D@PLCC20 [SA001A-B2001]
GAL16V8D@SOIC20 [SA404] GAL16V8Z
GAL16V8Z@PLCC20 [SA001A-B2001] GAL16V8Z@SOIC20 [SA404]
GAL18V10 GAL18V10@PLCC20 [SA001A-B2001]
GAL18V10B GAL18V10B@PLCC20 [SA001A-B2001]
GAL20LV8 GAL20LV8@PLCC28 [SA008A]
GAL20LV8Z GAL20LV8Z@PLCC28 [SA008A]
GAL20LV8ZD GAL20LV8ZD@PLCC28 [SA008A]
GAL20V8 GAL20V8@PLCC28 [SA008A]
GAL20V8A GAL20V8A@PLCC28 [SA008A]
GAL20V8B GAL20V8B@PLCC28 [SA008A]
GAL20V8C GAL20V8C@PLCC28 [SA008A]
GAL20V8Z GAL20V8Z@PLCC28 [SA008A]
GAL22V10 GAL22V10@PLCC28 [SA008A]
GAL22V10@SOIC24 [SA404] GAL22V10A
GAL22V10A@PLCC28 [SA008A] GAL22V10A@SOIC24 [SA404]
GAL22V10B GAL22V10B@PLCC28 [SA008A]
GAL22V10B@SOIC24 [SA404] GAL22V10BQ
GAL22V10BQ@PLCC28 [SA008A] GAL22V10BQ@SOIC24 [SA404]
GAL22V10C GAL22V10C@PLCC28 [SA008A]
GAL22V10C@SOIC24 [SA404] GAL22V10D
GAL22V10D@PLCC28 [SA008A] GAL22V10D@SOIC24 [SA404]
GAL26CLV12 GAL26CLV12@PLCC28 [SA008A]

GAL26CLV12@S0IC28 [SA404]
GAL26CLV12B
GAL26CLV12B@S0IC28 [SA404]
GAL26CLV12C
GAL26CLV12C@S0IC28 [SA404]
GAL26CLV12D
GAL26CLV12D@S0IC28 [SA404]
GAL26CLV12Z
GAL26CLV12Z@S0IC28 [SA404]
GAL26CLV12ZD
GAL26CLV12ZD@S0IC28 [SA404]
GAL26CV12
GAL26CV12B
GAL26CV12C
GAL26V12C

GAL26CLV12@TSOP28 [SA643]
GAL26CLV12B@PLCC28 [SA008A]
GAL26CLV12B@TSOP28 [SA643]
GAL26CLV12C@PLCC28 [SA008A]
GAL26CLV12C@TSOP28 [SA643]
GAL26CLV12D@PLCC28 [SA008A]
GAL26CLV12D@TSOP28 [SA643]
GAL26CLV12Z@PLCC28 [SA008A]
GAL26CLV12Z@TSOP28 [SA643]
GAL26CLV12ZD@PLCC28 [SA008A]
GAL26CLV12ZD@TSOP28 [SA643]
GAL26CV12@PLCC28 [SA008A]
GAL26CV12B@PLCC28 [SA008A]
GAL26CV12C@PLCC28 [SA008A]
GAL26V12C@PLCC28 [SA008A]

LG Semicon

MICROCONTROLLER

GMS97C1051
GMS97C2051
GMS97C51
GMS97C51@TQFP44 [SA675-B4805]
GMS97C52@PLCC44 [SA244]
GMS97C54
GMS97C54@TQFP44 [SA675-B4805]
GMS97C56@PLCC44 [SA244]
GMS97C58
GMS97C58@TQFP44 [SA675-B4805]
GMS97L1051@S0IC20 [SA404]
GMS97L2051@S0IC20 [SA404]
GMS97L51@PLCC44 [SA244]
GMS97L52
GMS97L52@TQFP44 [SA675-B4805]
GMS97L54@PLCC44 [SA244]
GMS97L56
GMS97L56@TQFP44 [SA675-B4805]
GMS97L58@PLCC44 [SA244]
GMS99C51
GMS99C51@TQFP44 [SA675-B4805]
GMS99C52@PLCC44 [SA244]
GMS99C58
GMS99C58@TQFP44 [SA675-B4805]

GMS97C1051@S0IC20 [SA404]
GMS97C2051@S0IC20 [SA404]
GMS97C51@PLCC44 [SA244]
GMS97C52
GMS97C52@TQFP44 [SA675-B4805]
GMS97C54@PLCC44 [SA244]
GMS97C56
GMS97C56@TQFP44 [SA675-B4805]
GMS97C58@PLCC44 [SA244]
GMS97L1051
GMS97L2051
GMS97L51
GMS97L51@TQFP44 [SA675-B4805]
GMS97L52@PLCC44 [SA244]
GMS97L54
GMS97L54@TQFP44 [SA675-B4805]
GMS97L56@PLCC44 [SA244]
GMS97L58
GMS97L58@TQFP44 [SA675-B4805]
GMS99C51@PLCC44 [SA244]
GMS99C52
GMS99C52@TQFP44 [SA675-B4805]
GMS99C58@PLCC44 [SA244]

LINKSMART

E(E) PROM/FRAM/NVRAM

L24C02
L24C02@TSOP8 [SA026-B3201]
L24C04@SSOP8 [SA602A]
L29004C
L29004C@TSOP32 [SA410T-B4001]
L29S160F-B@TSOP48 [SB247-B4806]
L29S400F@TSOP48 [SB247-B4806]
L29S400F-B@TSOP48 [SB247-B4806]

L24C02@SSOP8 [SA602A]
L24C04
L24C04@TSOP8 [SA026-B3201]
L29004C@PLCC32 [SA015A1T]
L29S160F@TSOP48 [SB247-B4806]
L29S400F@PSOP44 [SA638]
L29S400F-B@PSOP44 [SA638]
L29S800F@TSOP48 [SB247-B4806]

L29S800F-B@TSOP48 [SB247-B4806]	L29W800E@TSOP48 [SB247-B4806]
L29W800E-B@TSOP48 [SB247-B4806]	LST28001
LST28001@PLCC32 [SA015A1T]	LST28001@TSOP32 [SA410T-B4001]
LST28002	LST28002@PLCC32 [SA015A1T]
LST28002@TSOP32 [SA410T-B4001]	LST28004
LST28004@PLCC32 [SA015A1T]	LST28004@TSOP32 [SA410T-B4001]

MACRONIX

E(E) PROM/FRAM/NVRAM

KH25L1005	KH25L1005@SON8 [SA683]
KH25L1005@SOP8 [SA602A]	KH25L1005A
KH25L1005A@SON8 [SA683]	KH25L1005A@SOP8 [SA602A]
KH25L12805D@SON8(Fast Mode) [SA684]	
KH25L12805D@SOP16(Fast Mode) [SA404]	
KH25L12805N@SOP16 [SA404]	
KH25L12805N@SOP16(Fast Mode) [SA404]	
KH25L1605@SON8 [SA684]	
KH25L1605@SON8(Fast Mode) [SA684]	
KH25L1605@SOP16 [SA404]	
KH25L1605@SOP16(Fast Mode) [SA404]	
KH25L1605A@SON8 [SA684]	
KH25L1605A@SON8(Fast Mode) [SA684]	
KH25L1605A@SOP16 [SA404]	
KH25L1605A@SOP16(Fast Mode) [SA404]	
KH25L1605A@SOP8 [SA605B]	
KH25L1605A@SOP8(Fast Mode) [SA605B]	
KH25L1605D@SON8 [SA684]	
KH25L1605D@SON8(Fast Mode) [SA684]	
KH25L1605D@SOP16 [SA404]	
KH25L1605D@SOP16(Fast Mode) [SA404]	
KH25L1605D@SOP8(150)(Fast Mode) [SA602A]	
KH25L1605D@SOP8(200)(Fast Mode) [SA605B]	
KH25L1636D@SOP16 [SA404]	KH25L1636D@SOP8(150mil) [SA602A]
KH25L1636D@SOP8(200mil) [SA605B]	KH25L1636D@WSON8 [SA683]
KH25L2005	KH25L2005@SON8 [SA683]
KH25L2005@SOP8 [SA602A]	KH25L2025
KH25L2025@SON8 [SA683]	KH25L2025@SOP8 [SA602A]
KH25L3205@SOP16 [SA404]	
KH25L3205@SOP16(Fast Mode) [SA404]	
KH25L3205@SOP8 [SA605B]	
KH25L3205@SOP8(Fast Mode) [SA605B]	
KH25L3205A@SON8 [SA684]	
KH25L3205A@SON8(Fast Mode) [SA684]	
KH25L3205A@SOP16 [SA404]	
KH25L3205A@SOP16(Fast Mode) [SA404]	
KH25L3205A@SOP8 [SA605B]	
KH25L3205A@SOP8(Fast Mode) [SA605B]	
KH25L3205D@SON8(Fast Mode) [SA684]	
KH25L3205D@SOP16 [SA404]	
KH25L3205D@SOP16(Fast Mode) [SA404]	
KH25L3205D@SOP8 [SA605B]	
KH25L3205D@SOP8(Fast Mode) [SA605B]	
KH25L3236D@SOP16 [SA404]	KH25L3236D@SOP8(150mil) [SA602A]
KH25L3236D@SOP8(200mil) [SA605B]	KH25L3236D@WSON8 [SA683]
KH25L4005	KH25L4005(150mil)@SOP8 [SA602A]
KH25L4005(209mil)@SOP8 [SA605B]	KH25L4005@SON8 [SA683]

KH25L4005A	KH25L4005A(150mil)@SOP8 [SA602A]
KH25L4005A(209mil)@SOP8 [SA605B]	KH25L4005A@SON8 [SA683]
KH25L4025A	KH25L4025A(150mil)@SOP8 [SA602A]
KH25L4025A(209mil)@SOP8 [SA605B]	KH25L4025A@SON8 [SA683]
KH25L512@SON8 [SA683]	KH25L512@SOP8 [SA602A]
KH25L512A	KH25L512A@SON8 [SA683]
KH25L512A@SOP8 [SA602A]	KH25L6405@SOP16 [SA404]
KH25L6405@SOP16(Fast Mode) [SA404]	
KH25L6405@SOP8 [SA605B]	
KH25L6405@SOP8(Fast Mode) [SA605B]	
KH25L6405D@SON8(Fast Mode) [SA684]	
KH25L6405D@SOP16 [SA404]	
KH25L6405D@SOP16(Fast Mode) [SA404]	
KH25L6405D@SOP8 [SA605B]	KH25L6405MC@SOP16 [SA404]
KH25L6405MC@SOP8 [SA605B]	KH25L8005
KH25L8005(150mil)@SOP8 [SA602A]	KH25L8005(209mil)@SOP8 [SA605B]
KH25L8005@SON8 [SA683]	KH25L8025
KH25L8025(150mil)@SOP8 [SA602A]	KH25L8025(209mil)@SOP8 [SA605B]
KH25L8025@SON8 [SA683]	KH25L8036D
KH25L8036D@SOP16 [SA404]	KH25L8036D@SOP8(150mil) [SA602A]
KH25L8036D@SOP8(200mil) [SA605B]	KH25L8036D@WSON8 [SA683]
KH29LV004CB@PLCC32 [SA015A1T]	
KH29LV004CB@TSOP40 [SA409T-B4002]	
KH29LV004CT@PLCC32 [SA015A1T]	
KH29LV004CT@TSOP40 [SA409T-B4002]	
KH29LV008CB@TSOP40 [SA409T-B4002]	
KH29LV008CT@TSOP40 [SA409T-B4002]	
KH29LV040C	KH29LV040C@PLCC32 [SA015A1T]
KH29LV160CBT@TSOP48 [SB247-B4806]	
KH29LV160CTT@TSOP48 [SB247-B4806]	
KH29LV160DBT@TSOP48 [SB247-B4806]	
KH29LV160DTT@TSOP48 [SB247-B4806]	
KH29LV320CBT@TSOP48 [SB247-B4806]	
KH29LV320CTT@TSOP48 [SB247-B4806]	
KH29LV320DBT@TSOP48 [SB247-B4806]	
KH29LV320DTT@TSOP48 [SB247-B4806]	
KH29LV400CBT@TSOP48 [SB247-B4806]	
KH29LV400CTT@TSOP48 [SB247-B4806]	
KH29LV640DBT@TSOP48 [SB247-B4806]	
KH29LV640DTT@TSOP48 [SB247-B4806]	
KH29LV800CBT@TSOP48 [SB247-B4806]	
KH29LV800CTT@TSOP48 [SB247-B4806]	
MX25L1005	MX25L1005@SON8 [SA683]
MX25L1005@SOP8 [SA602A]	MX25L1005@USON8 [SA724]
MX25L1005A	MX25L1005A@SON8 [SA683]
MX25L1005A@SOP8 [SA602A]	MX25L1005C@SOP8 [SA602A]
MX25L1005C@USON8 [SA724]	MX25L1021E@SOP8 [SA602A]
MX25L1025C@SOP8 [SA602A]	
MX25L12805D@SON8(Fast Mode) [SA684]	
MX25L12805D@SOP16(512bit OTP) [SA404]	
MX25L12805D@SOP16(Fast Mode) [SA404]	
MX25L12805D@WSON8(512bit OTP) [SA684]	
MX25L12805N@SOP16 [SA404]	
MX25L12805N@SOP16(Fast Mode) [SA404]	
MX25L12836E@SOP16 [SA404]	MX25L12836E@SOP8 [SA605B]
MX25L12836E@WSON8 [SA684]	MX25L12845E@SOP16 [SA404]
MX25L12845E@WSON8 [SA684]	MX25L12855E@SOP16 [SA404]
MX25L12865E@SOP16 [SA404]	MX25L12865E@SOP8 [SA605B]
MX25L12865E@WSON8 [SA684]	MX25L1605@SON8 [SA684]

MX25L1605@SON8(Fast Mode) [SA684]	
MX25L1605@SOP16 [SA404]	
MX25L1605@SOP16(Fast Mode) [SA404]	
MX25L1605A@SON8 [SA684]	
MX25L1605A@SON8(Fast Mode) [SA684]	
MX25L1605A@SOP16 [SA404]	
MX25L1605A@SOP16(Fast Mode) [SA404]	
MX25L1605A@SOP8 [SA605B]	
MX25L1605A@SOP8(Fast Mode) [SA605B]	
MX25L1605D(512bit OTP)	MX25L1605D@SON8 [SA684]
MX25L1605D@SON8(Fast Mode) [SA684]	
MX25L1605D@SOP16 [SA404]	
MX25L1605D@SOP16(512bit OTP) [SA404]	
MX25L1605D@SOP16(Fast Mode) [SA404]	
MX25L1605D@SOP8(150)(Fast Mode) [SA602A]	
MX25L1605D@SOP8(200)(Fast Mode) [SA605B]	
MX25L1605D@SOP8(512bit OTP)(150) [SA602A]	
MX25L1605D@SOP8(512bit OTP)(200) [SA605B]	
MX25L1605D@USON8 [SA744]	
MX25L1605D@USON8(512bit OTP) [SA744]	
MX25L1605D@USON8(Fast Mode) [SA744]	
MX25L1605D@WSON8(512bit OTP) [SA683]	
MX25L1606E	MX25L1606E(512bit)
MX25L1606E(512bit)@SOP16 [SA404]	
MX25L1606E(512bit)@SOP8(150mil) [SA602A]	
MX25L1606E(512bit)@SOP8(200mil) [SA605B]	
MX25L1606E(512bit)@USON8 [SA744]	MX25L1606E(512bit)@WSON8 [SA683]
MX25L1606E@SOP16 [SA404]	
MX25L1606E@SOP8(150 mil) [SA602A]	
MX25L1606E@SOP8(200 mil) [SA605B]	
MX25L1606E@USON8 [SA744]	MX25L1606E@WSON8 [SA683]
MX25L1608D	MX25L1608D@SOP16 [SA404]
MX25L1608D@SOP8(150mil) [SA602A]	MX25L1608D@SOP8(200mil) [SA605B]
MX25L1608D@USON8 [SA744]	MX25L1608D@WSON8 [SA683]
MX25L1615D@SOP16 [SA404]	MX25L1615D@SOP8 [SA605B]
MX25L1633E@SOP16 [SA404]	MX25L1633E@SOP8 [SA605B]
MX25L1633E@WSON8 [SA683]	MX25L1635D@SOP16 [SA404]
MX25L1635D@SOP8(150mil) [SA602A]	MX25L1635D@SOP8(200mil) [SA605B]
MX25L1635D@WSON8 [SA683]	MX25L1635E@SOP8 [SA605B]
MX25L1636D@SOP16 [SA404]	MX25L1636D@SOP8(150mil) [SA602A]
MX25L1636D@SOP8(200mil) [SA605B]	MX25L1636D@WSON8 [SA683]
MX25L2005	MX25L2005@SON8 [SA683]
MX25L2005@SOP8 [SA602A]	MX25L2005C@SOP8 [SA602A]
MX25L2005C@USON8 [SA683]	MX25L2006E@SOP8 [SA602A]
MX25L2006E@WSON8 [SA683]	MX25L2025
MX25L2025@SON8 [SA683]	MX25L2025@SOP8 [SA602A]
MX25L2026C@SOP8 [SA602A]	MX25L2026E@SOP8 [SA602A]
MX25L2026E@WSON8 [SA683]	MX25L25635E@SOP16 [SA404]
MX25L25636E@SOP16 [SA404]	MX25L25735E@SOP16 [SA404]
MX25L25735E@WSON8 [SA684]	MX25L3205@SOP16 [SA404]
MX25L3205@SOP16(Fast Mode) [SA404]	
MX25L3205@SOP8 [SA605B]	
MX25L3205@SOP8(Fast Mode) [SA605B]	
MX25L3205A@SON8 [SA684]	
MX25L3205A@SON8(Fast Mode) [SA684]	
MX25L3205A@SOP16 [SA404]	
MX25L3205A@SOP16(Fast Mode) [SA404]	
MX25L3205A@SOP8 [SA605B]	
MX25L3205A@SOP8(Fast Mode) [SA605B]	

MX25L3205D(512bit OTP)	
MX25L3205D@SON8(Fast Mode) [SA684]	
MX25L3205D@SOP16 [SA404]	
MX25L3205D@SOP16(512bit OTP) [SA404]	
MX25L3205D@SOP16(Fast Mode) [SA404]	
MX25L3205D@SOP8 [SA605B]	
MX25L3205D@SOP8(512bit OTP) [SA605B]	
MX25L3205D@SOP8(Fast Mode) [SA605B]	
MX25L3205D@USON8 [SA744]	
MX25L3205D@USON8(512bit OTP) [SA744]	
MX25L3205D@USON8(Fast Mode) [SA744]	
MX25L3205D@WSON8(512bit OTP) [SA683]	
MX25L3206E [SA605B]	MX25L3206E(512bit)
MX25L3206E(512bit)@SOP16 [SA404]	MX25L3206E(512bit)@SOP8 [SA605B]
MX25L3206E(512bit)@USON8 [SA744]	MX25L3206E(512bit)@WSON8 [SA683]
MX25L3206E@SOP16 [SA404]	MX25L3206E@SOP8 [SA605B]
MX25L3206E@USON8 [SA744]	MX25L3206E@WSON8 [SA683]
MX25L3208D	MX25L3208D@SOP16 [SA404]
MX25L3208D@SOP8 [SA605B]	MX25L3208D@USON8 [SA744]
MX25L3208D@WSON8 [SA683]	MX25L3215D@SOP16 [SA404]
MX25L3215D@SOP8 [SA605B]	MX25L3225D@SOP8 [SA605B]
MX25L3235D@SOP16 [SA404]	MX25L3235D@SOP8 [SA605B]
MX25L3235D@WSON8 [SA683]	MX25L3236D@SOP16 [SA404]
MX25L3236D@SOP8(150mil) [SA602A]	MX25L3236D@SOP8(200mil) [SA605B]
MX25L3236D@WSON8 [SA683]	MX25L3237D@SOP16 [SA404]
MX25L3237D@WSON8 [SA683]	MX25L4005
MX25L4005(150mil)@SOP8 [SA602A]	MX25L4005(209mil)@SOP8 [SA605B]
MX25L4005@SON8 [SA683]	MX25L4005A
MX25L4005A(150mil)@SOP8 [SA602A]	MX25L4005A(209mil)@SOP8 [SA605B]
MX25L4005A@SON8 [SA683]	MX25L4005A@USON8 [SA744]
MX25L4005C	MX25L4005C@SOP8 [SA602A]
MX25L4005C@TSSOP8 [SA605B]	MX25L4005C@USON8 [SA683]
MX25L4006E	MX25L4006E@SOP8(150mil) [SA602A]
MX25L4006E@SOP8(200mil) [SA605B]	MX25L4006E@WSON8 [SA683]
MX25L4025@SOP8 [SA602A]	MX25L4025A
MX25L4025A(150mil)@SOP8 [SA602A]	MX25L4025A(209mil)@SOP8 [SA605B]
MX25L4025A@SON8 [SA683]	MX25L4026E@SOP8 [SA602A]
MX25L512@SON8 [SA683]	MX25L512@SOP8 [SA602A]
MX25L512@USON8 [SA724]	MX25L5121E@SOP8 [SA602A]
MX25L5121E@TSSOP8 [SA026-B3201]	MX25L512A
MX25L512A@SON8 [SA683]	MX25L512A@SOP8 [SA602A]
MX25L512C	MX25L512C@TSSOP8 [SA026-B3201]
MX25L512C@USON8 [SA724]	MX25L6405@SOP16 [SA404]
MX25L6405@SOP16(Fast Mode) [SA404]	
MX25L6405@SOP8 [SA605B]	
MX25L6405@SOP8(Fast Mode) [SA605B]	
MX25L6405D@SON8(Fast Mode) [SA684]	
MX25L6405D@SOP16 [SA404]	
MX25L6405D@SOP16(512bit OTP) [SA404]	
MX25L6405D@SOP16(Fast Mode) [SA404]	
MX25L6405D@SOP8 [SA605B]	
MX25L6405D@WSON8(512bit OTP) [SA684]	
MX25L6405MC@SOP16 [SA404]	MX25L6405MC@SOP8 [SA605B]
MX25L6406E@SOP16 [SA404]	MX25L6406E@SOP8 [SA605B]
MX25L6406E@WSON8 [SA684]	MX25L6408D@SOP16 [SA404]
MX25L6408D@WSON8 [SA684]	MX25L6415D@SOP16 [SA404]
MX25L6415D@SOP8 [SA605B]	MX25L6436E@SOP16 [SA404]
MX25L6436E@SOP8 [SA605B]	MX25L6436E@WSON8 [SA684]
MX25L6445E@SOP16 [SA404]	

MX25L6445E@SOP16(4K bit OTP) [SA404]	
MX25L6445E@SOP8 [SA605B]	
MX25L6445E@SOP8(4K bit OTP) [SA605B]	
MX25L6445E@WS0N8 [SA684]	
MX25L6445E@WS0N8(4K bit OTP) [SA684]	
MX25L6446E@SOP16 [SA404]	MX25L6446E@SOP8 [SA605B]
MX25L6446E@WS0N8 [SA684]	MX25L6455E@SOP16 [SA404]
MX25L6455E@SOP8 [SA605B]	MX25L6465E@SOP16 [SA404]
MX25L6465E@SOP8 [SA605B]	MX25L6465E@WS0N8 [SA684]
MX25L8005	MX25L8005(150mil)@SOP8 [SA602A]
MX25L8005(209mil)@SOP8 [SA605B]	MX25L8005@SON8 [SA683]
MX25L8005@US0N8 [SA744]	MX25L8006E
MX25L8006E(512bit)	
MX25L8006E(512bit)@SOP8(150mil) [SA602A]	
MX25L8006E(512bit)@SOP8(200mil) [SA605B]	
MX25L8006E(512bit)@US0N8 [SA744]	MX25L8006E(512bit)@WS0N8 [SA683]
MX25L8006E@SOP8(150 mil) [SA602A]	
MX25L8006E@SOP8(200 mil) [SA605B]	
MX25L8006E@US0N8 [SA744]	MX25L8006E@WS0N8 [SA683]
MX25L8025	MX25L8025(150mil)@SOP8 [SA602A]
MX25L8025(209mil)@SOP8 [SA605B]	MX25L8025@SON8 [SA683]
MX25L8035E@SOP8 [SA605B]	MX25L8036D
MX25L8036D@SOP16 [SA404]	MX25L8036D@SOP8(150mil) [SA602A]
MX25L8036D@SOP8(200mil) [SA605B]	MX25L8036D@WS0N8 [SA683]
MX25L8036E@SOP8 [SA605B]	MX25U1635@S0IC8 [SA602A]
MX25U1635@US0N8(4*4mm) [SA744]	MX25U1635@US0N8(6*5mm) [SA683]
MX25U1635E@SOP8(150mil) [SA602A]	MX25U1635E@SOP8(200mil) [SA605B]
MX25U1635E@US0N8 [SA744]	MX25U1635E@WS0N8 [SA683]
MX25U3235E@SOP8(150mil) [SA602A]	MX25U3235E@SOP8(200mil) [SA605B]
MX25U3235E@US0N8 [SA744]	MX25U3235E@WS0N8 [SA683]
MX25U4035@S0IC8 [SA602A]	MX25U4035@US0N8(4*4mm) [SA744]
MX25U4035@US0N8(6*5mm) [SA683]	MX25U6435E@WS0N8 [SA683]
MX25U8035@S0IC8 [SA602A]	MX25U8035@US0N8(4*4mm) [SA744]
MX25U8035@US0N8(6*5mm) [SA683]	MX25U8035E@SOP8(150mil) [SA602A]
MX25U8035E@SOP8(200mil) [SA605B]	MX25U8035E@US0N8 [SA744]
MX25U8035E@WS0N8 [SA683]	MX25V4005
MX25V4005@US0N8 [SA683]	MX25V4005C@SOP8
MX25V4005C@WS0N8 [SA683]	MX25V4035@SOP8 [SA602A]
MX25V4035@WS0N8 [SA683]	MX25V512@US0N8 [SA724]
MX25V512C@TSSOP8 [SA026-B3201]	MX25V512C@US0N8 [SA724]
MX25V8005@SOP8 [SA602A]	MX25V8005@WS0N8 [SA683]
MX25V8035@SOP8 [SA602A]	MX25V8035@WS0N8 [SA683]
MX26C1000	MX26C1000@PLCC32 [SA015A1T]
MX26C1000@S0IC32 [SA603]	MX26C1000@TSOP32 [SA410T-B4001]
MX26C1000B	MX26C1000B@PLCC32 [SA015A1T]
MX26C1000B@S0IC32 [SA438T]	MX26C1000B@TSOP32 [SA410T-B4001]
MX26C2000B	MX26C2000B@PLCC32 [SA015A1T]
MX26C2000B@S0IC32 [SA438T]	MX26C2000B@TSOP32 [SA410T-B4001]
MX26C512A	MX26C512A@PLCC32 [SA015A1T]
MX26C512A@S0IC28 [SA630]	MX26C512A@TSOP28 [SA430T-B4003]
MX26L12711MC@PSOP44 [SA638]	MX26L12811MC@PSOP44 [SA638]
MX26L6419T@TSOP48 [SB247-B4806]	MX26L6420@PSOP44 [SA638]
MX26L6420@TSOP48 [SA643]	MX26LV004B@PLCC32 [SA015A1T]
MX26LV004B@TSOP40 [SA409T-B4002]	MX26LV004T@PLCC32 [SA015A1T]
MX26LV004T@TSOP40 [SA409T-B4002]	MX26LV008B@TSOP40 [SA409T-B4002]
MX26LV008T@TSOP40 [SA409T-B4002]	MX26LV040
MX26LV040@PLCC32 [SA015A1T]	MX26LV040@TSOP32 [SA410T-B4001]
MX26LV160BT@TSOP48 [SA247-B4806]	MX26LV160TT@TSOP48 [SA247-B4806]
MX26LV400BT@TSOP48 [SA247-B4806]	MX26LV400TT@TSOP48 [SA247-B4806]

MX26LV800BM@PSOP44 [SA638]	MX26LV800BT@TSOP48 [SA247-B4806]
MX26LV800TM@PSOP44 [SA638]	MX26LV800TT@TSOP48 [SA247-B4806]
MX27C1000	MX27C1000@PLCC32 [SA015A1T]
MX27C1000@S0IC32 [SA603]	MX27C1000@TSOP32 [SA410T-B4001]
MX27C1000A	MX27C1000A@PLCC32 [SA015A1T]
MX27C1000A@S0IC32 [SA603]	MX27C1000A@TSOP32 [SA410T-B4001]
MX27C1001	MX27C1001@PLCC32 [SA015A1T]
MX27C1001@S0IC32 [SA603]	MX27C1001@TSOP32 [SA410T-B4001]
MX27C1024	MX27C1024@PLCC44 [SA244]
MX27C1024@SOP40 [SA682]	MX27C1024@VSOP40 [SA623-B4002]
MX27C1024A	MX27C1024A@PLCC44 [SA244]
MX27C1024A@SOP40 [SA682]	MX27C1024A@VSOP40 [SA623-B4002]
MX27C1024B	MX27C1024B@PLCC44 [SA244]
MX27C1024B@SOP40 [SA682]	MX27C1024B@VSOP40 [SA623-B4002]
MX27C1100	MX27C1610
MX27C2000	MX27C2000@PLCC32 [SA015A1T]
MX27C2000@S0IC32 [SA603]	MX27C2000@TSOP32 [SA410T-B4001]
MX27C2000A	MX27C2000A@PLCC32 [SA015A1T]
MX27C2000A@S0IC32 [SA603]	MX27C2000A@TSOP32 [SA410T-B4001]
MX27C2048	MX27C2048@PLCC44 [SA244]
MX27C2048@VSOP40 [SA623-B4002]	MX27C2100
MX27C256	MX27C256@PLCC32 [SA015A1T]
MX27C4000	MX27C4000@PLCC32 [SA015A1T]
MX27C4000@S0IC32 [SA603]	MX27C4000@TSOP32 [SA410T-B4001]
MX27C4000A	MX27C4000A@PLCC32 [SA015A1T]
MX27C4000A@S0IC32 [SA603]	MX27C4000A@TSOP32 [SA410T-B4001]
MX27C4096	MX27C4096@PLCC44 [SA244]
MX27C4100	MX27C4111
MX27C512	MX27C512@PLCC32 [SA015A1T]
MX27C516	MX27C516@PLCC44 [SA244]
MX27C516@VSOP40 [SA623-B4002]	MX27C8000
MX27C8000@PLCC32 [SA015A1T]	MX27C8000@S0IC32 [SA603]
MX27C8000@TSOP32 [SA410T-B4001]	MX27C8000A
MX27C8000A@PLCC32 [SA015A1T]	MX27C8000A@S0IC32 [SA603]
MX27C8000A@TSOP32 [SA410T-B4001]	MX27C8100
MX27C8100@PSOP44 [SA638]	MX27C8111
MX27C8111@PSOP44 [SA638]	MX27L1000
MX27L1000@PLCC32 [SA015A1T]	MX27L1000@TSOP32 [SA410T-B4001]
MX27L2000	MX27L2000@PLCC32 [SA015A1T]
MX27L2000@TSOP32 [SA410T-B4001]	MX27L256
MX27L256@PLCC32 [SA015A1T]	MX27L256@TSOP32 [SA430T-B4003]
MX27L4000	MX27L4000@PLCC32 [SA015A1T]
MX27L4000@TSOP32 [SA410T-B4001]	MX27L4096
MX27L4096@PLCC44 [SA244]	MX27L512
MX27L512@PLCC32 [SA015A1T]	MX27L512@TSOP28 [SA430T-B4003]
MX28F002B@TSOP40 [SA409T-B4002]	MX28F002T@TSOP40 [SA409T-B4002]
MX28F1000	
MX28F1000(REVERSE)@TSOP32 [SA410T-B4001]	
MX28F1000@PLCC32 [SA015A1T]	MX28F1000@SOP32 [SA438T]
MX28F1000@TSOP32 [SA410T-B4001]	MX28F1000P
MX28F1000P(REVERSE)@TSOP32 [SA410T-B4001]	
MX28F1000P@PLCC32 [SA015A1T]	MX28F1000P@TSOP32 [SA410T-B4001]
MX28F160C3BT@TSOP48 [SB247-B4806]	
MX28F160C3TT@TSOP48 [SB247-B4806]	
MX28F2000	
MX28F2000(REVERSE)@TSOP32 [SA410T-B4001]	
MX28F2000@PLCC32 [SA015A1T]	MX28F2000@TSOP32 [SA410T-B4001]
MX28F2000P	
MX28F2000P(REVERSE)@TSOP32 [SA410T-B4001]	

MX28F2000P@PLCC32 [SA015A1T]	MX28F2000P@TSOP32 [SA410T-B4001]
MX28F2100B@PSOP44 [SA638]	MX28F2100B@TSOP48 [SB247-B4806]
MX28F2100T@PSOP44 [SA638]	MX28F2100T@TSOP48 [SB247-B4806]
MX28F4000	MX28F4000@PLCC32 [SA015A1T]
MX28F4000@SOP32 [SA438T]	MX28F4000@TSOP32 [SA410T-B4001]
MX28F640C3BT@TSOP48 [SB247-B4806]	
MX28F640C3TT@TSOP48 [SB247-B4806]	
MX29F001B	MX29F001B@PLCC32 [SA015A1T]
MX29F001B@TSOP32 [SA410T-B4001]	MX29F001T
MX29F001T@PLCC32 [SA015A1T]	MX29F001T@TSOP32 [SA410T-B4001]
MX29F002B	MX29F002B@PLCC32 [SA015A1T]
MX29F002B@TSOP32 [SA410T-B4001]	MX29F002NB
MX29F002NB@PLCC32 [SA015A1T]	MX29F002NB@TSOP32 [SA410T-B4001]
MX29F002NT	MX29F002NT@PLCC32 [SA015A1T]
MX29F002NT@TSOP32 [SA410T-B4001]	MX29F002T
MX29F002T@PLCC32 [SA015A1T]	MX29F002T@TSOP32 [SA410T-B4001]
MX29F004B	MX29F004B@PLCC32 [SA015A1T]
MX29F004B@TSOP32 [SA410T-B4001]	MX29F004T
MX29F004T@PLCC32 [SA015A1T]	MX29F004T@TSOP32 [SA410T-B4001]
MX29F016(REVERSE)@TSOP40 [SA409T-B4002]	
MX29F016(REVERSE)@TSOP48 [SB247-B4806]	
MX29F016@PSOP44 [SA638]	MX29F016@TSOP40 [SA409T-B4002]
MX29F016@TSOP48 [SB247-B4806]	MX29F022B
MX29F022B@PLCC32 [SA015A1T]	MX29F022B@TSOP32 [SA410T-B4001]
MX29F022NB	MX29F022NB@PLCC32 [SA015A1T]
MX29F022NB@TSOP32 [SA410T-B4001]	MX29F022NT
MX29F022NT@PLCC32 [SA015A1T]	MX29F022NT@TSOP32 [SA410T-B4001]
MX29F022T	MX29F022T@PLCC32 [SA015A1T]
MX29F022T@TSOP32 [SA410T-B4001]	MX29F040
MX29F040@PLCC32 [SA015A1T]	MX29F040@TSOP32 [SA410T-B4001]
MX29F040C	MX29F040C@PLCC32 [SA015A1T]
MX29F040C@TSOP32 [SA410T-B4001]	
MX29F080(REVERSE)@TSOP40 [SA409T-B4002]	
MX29F080@PSOP44 [SA638]	MX29F080@TSOP40 [SA409T-B4002]
MX29F100B@PSOP44 [SA638]	MX29F100B@TSOP48 [SB247-B4806]
MX29F100T@PSOP44 [SA638]	MX29F100T@TSOP48 [SB247-B4806]
MX29F1610@PSOP44 [SA638]	MX29F1610@TSOP48 [SB247-B4806]
MX29F1610A@PSOP44 [SA638]	MX29F1610A@TSOP48 [SB247-B4806]
MX29F1610B@TSOP48 [SB247-B4806]	MX29F1611@PSOP44 [SA638]
MX29F1615	
MX29F200B(REVERSE)@TSOP48 [SB247-B4806]	
MX29F200B@PSOP44 [SA638]	MX29F200B@TSOP48 [SB247-B4806]
MX29F200CB@PSOP44 [SA638]	MX29F200CB@TSOP48 [SA247-B4806]
MX29F200CT@PSOP44 [SA638]	MX29F200CT@TSOP48 [SA247-B4806]
MX29F200T(REVERSE)@TSOP48 [SB247-B4806]	
MX29F200T@PSOP44 [SA638]	MX29F200T@TSOP48 [SB247-B4806]
MX29F4000	
MX29F400B(REVERSE)@TSOP48 [SB247-B4806]	
MX29F400B@PSOP44 [SA638]	MX29F400B@TSOP48 [SB247-B4806]
MX29F400CB@PSOP44 [SA638]	MX29F400CB@TSOP48 [SA247-B4806]
MX29F400CT@PSOP44 [SA638]	MX29F400CT@TSOP48 [SA247-B4806]
MX29F400T(REVERSE)@TSOP48 [SB247-B4806]	
MX29F400T@PSOP44 [SA638]	MX29F400T@TSOP48 [SB247-B4806]
MX29F800B(REVERSE)@TSOP48 [SB247-B4806]	
MX29F800B@PSOP44 [SA638]	MX29F800B@TSOP48 [SB247-B4806]
MX29F800CBM@PSOP44 [SA638]	MX29F800CBT@TSOP48 [SA247-B4806]
MX29F800CTM@PSOP44 [SA638]	MX29F800CTT@TSOP48 [SA247-B4806]
MX29F800T(REVERSE)@TSOP48 [SB247-B4806]	
MX29F800T@PSOP44 [SA638]	MX29F800T@TSOP48 [SB247-B4806]

MX29F8100@PSOP44 [SA638]
MX29L1611@PSOP44 [SA638]
MX29L3211@PSOP44 [SA638]
MX29L8100B@TSOP48 [SB247-B4806]
MX29L8100T@TSOP48 [SB247-B4806]
MX29LA320MT@TSOP48 [SB247-B4806]
MX29LV002CB@TSOP32 [SA410T-B4001]
MX29LV002CT@PLCC32 [SA015A1T]
MX29LV002CT@TSOP32 [SA410T-B4001]
MX29LV002NCB@PLCC32 [SA015A1T]
MX29LV002NCB@TSOP32 [SA410T-B4001]
MX29LV002NCT@PLCC32 [SA015A1T]
MX29LV002NCT@TSOP32 [SA410T-B4001]
MX29LV004B@PLCC32 [SA015A1T]
MX29LV004CB@PLCC32 [SA015A1T]
MX29LV004CB@TSOP40 [SA409T-B4002]
MX29LV004CT@PLCC32 [SA015A1T]
MX29LV004CT@TSOP40 [SA409T-B4002]
MX29LV004T@PLCC32 [SA015A1T]
MX29LV008B@TSOP40 [SA409T-B4002]
MX29LV008BB@TSOP40 [SA409T-B4002]
MX29LV008BT@TSOP40 [SA409T-B4002]
MX29LV008CB@TSOP40 [SA409T-B4002]
MX29LV008CT@TSOP40 [SA409T-B4002]
MX29LV008T@TSOP40 [SA409T-B4002]
MX29LV017AT@TSOP40 [SA409T-B4002]
MX29LV017BT@TSOP40 [SA409T-B4002]
MX29LV033AT@TSOP40 [SA409T-B4002]
MX29LV033M@TSOP40 [SA409T-B4002]
MX29LV040@PLCC32 [SA015A1T]
MX29LV040C@PLCC32 [SA015A1T]
MX29LV065BT@TSOP48 [SB247-B4806]
MX29LV081@TSOP40 [SA409T-B4002]
MX29LV128DT@TSOP48 [SB247-B4806]
MX29LV160AB(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV160AB@TSOP48 [SB247-B4806]
MX29LV160AT(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV160AT@TSOP48 [SB247-B4806]
MX29LV160B(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV160B@TSOP48 [SB247-B4806]
MX29LV160BB(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV160BB@TSOP48 [SB247-B4806]
MX29LV160BT(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV160BT@TSOP48 [SB247-B4806]
MX29LV160CBT@TSOP48 [SB247-B4806]
MX29LV160CBXB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV160CBXE(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV160CTM@PSOP44 [SA638]
MX29LV160CTT@TSOP48 [SB247-B4806]
MX29LV160CTXB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV160CTXE(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV160DBT@TSOP48 [SB247-B4806]
MX29LV160DTT@TSOP48 [SB247-B4806]
MX29LV160T(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV160T@PSOP44 [SA638]
MX29LV161DBT@TSOP48 [SB247-B4806]
MX29LV161DTT@TSOP48 [SB247-B4806]
MX29LV320ABT@TSOP48 [SB247-B4806]
MX29LV320ABXB@CSP48 [\$\$\$\$\$\$]

MX29F8100@TSOP48 [SB247-B4806]
MX29L1611@TSOP48 [SB247-B4806]
MX29L3211@TSOP48 [SB247-B4806]
MX29L8100G
MX29LA320MB@TSOP48 [SB247-B4806]
MX29LV002CB@PLCC32 [SA015A1T]

MX29LV004B@TSOP40 [SA409T-B4002]

MX29LV004T@TSOP40 [SA409T-B4002]

MX29LV033T@TSOP40 [SA409T-B4002]
MX29LV040@TSOP32 [SA410T-B4001]
MX29LV040C@TSOP32 [SA410T-B4001]
MX29LV065M@TSOP48 [SB247-B4806]
MX29LV128DB@TSOP48 [SB247-B4806]
MX29LV160AB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV160AB@PSOP44 [SA638]
MX29LV160AT(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV160AT@PSOP44 [SA638]
MX29LV160B(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV160B@PSOP44 [SA638]
MX29LV160BB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV160BB@PSOP44 [SA638]
MX29LV160BT(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV160BT@PSOP44 [SA638]
MX29LV160CBM@PSOP44 [SA638]

MX29LV160T(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV160T@TSOP48 [SB247-B4806]

MX29LV320ABXE@CSP48 [\$\$\$\$\$\$]

MX29LV320ATT@TSOP48 [SB247-B4806]
MX29LV320ATXB@CSP48 [\$\$\$\$\$\$]
MX29LV320BT@TSOP48 [SB247-B4806]
MX29LV320BXE@CSP48 [\$\$\$\$\$\$]
MX29LV320CBT@TSOP48 [SB247-B4806]
MX29LV320CBXB@CSP48 [\$\$\$\$\$\$]
MX29LV320CTT@TSOP48 [SB247-B4806]
MX29LV320CTXB@CSP48 [\$\$\$\$\$\$]
MX29LV320DBT@TSOP48 [SB247-B4806]
MX29LV320DTT@TSOP48 [SB247-B4806]
MX29LV320EBT@TSOP48 [SB247-B4806]
MX29LV320ETT@TSOP48 [SB247-B4806]
MX29LV320MB@PSOP44 [SA638]
MX29LV320MT@PSOP44 [SA638]
MX29LV320TT@TSOP48 [SB247-B4806]
MX29LV320TXE@CSP48 [\$\$\$\$\$\$]
MX29LV321DBT@TSOP48 [SB247-B4806]
MX29LV321DBXB@CSP48 [\$\$\$\$\$\$]
MX29LV321DTT@TSOP48 [SB247-B4806]
MX29LV400B@PSOP44 [SA638]
MX29LV400BX(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV400CBM@PSOP44 [SA638]
MX29LV400CBT@TSOP48 [SB247-B4806]
MX29LV400CBXB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV400CBXE(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV400CTM@PSOP44 [SA638]
MX29LV400CTT@TSOP48 [SB247-B4806]
MX29LV400CTXB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV400CTXE(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV400T@PSOP44 [SA638]
MX29LV400TX(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV640BBT@TSOP48 [SB247-B4806]
MX29LV640BT@TSOP48 [SB247-B4806]
MX29LV640BTT@TSOP48 [SB247-B4806]
MX29LV640BUT@TSOP48 [SB247-B4806]
MX29LV640DBT@TSOP48 [SB247-B4806]
MX29LV640DTT@TSOP48 [SB247-B4806]
MX29LV640EBT@TSOP48 [SB247-B4806]
MX29LV640ETT@TSOP48 [SB247-B4806]
MX29LV640MB@TSOP48 [SB247-B4806]
MX29LV640TT@TSOP48 [SB247-B4806]
MX29LV641MH@TSOP48 [SB247-B4806]
MX29LV800AB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV800AB@PSOP44 [SA638]
MX29LV800AT(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV800AT@PSOP44 [SA638]
MX29LV800B(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV800B@PSOP44 [SA638]
MX29LV800CBM@PSOP44 [SA638]
MX29LV800CBT@TSOP48 [SB247-B4806]
MX29LV800CBXB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV800CBXE(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV800CTM@PSOP44 [SA638]
MX29LV800CTT@TSOP48 [SB247-B4806]
MX29LV800CTXB(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV800CTXE(0.4)@CSP48 [\$\$\$\$\$\$]
MX29LV800T(0.3)@CSP48 [\$\$\$\$\$\$]
MX29LV800T@PSOP44 [SA638]
MX29LW160BT@TSOP48 [SB247-B4806]

MX29LV320ATXE@CSP48 [\$\$\$\$\$\$]
MX29LV320BXB@CSP48 [\$\$\$\$\$\$]

MX29LV320CBXE@CSP48 [\$\$\$\$\$\$]

MX29LV320CTXE@CSP48 [\$\$\$\$\$\$]

MX29LV320MB@TSOP48 [SB247-B4806]

MX29LV320MT@TSOP48 [SB247-B4806]

MX29LV320TXB@CSP48 [\$\$\$\$\$\$]

MX29LV400B@TSOP48 [SB247-B4806]

MX29LV400BX(0.4)@CSP48 [\$\$\$\$\$\$]

MX29LV400T@TSOP48 [SB247-B4806]

MX29LV400TX(0.4)@CSP48 [\$\$\$\$\$\$]

MX29LV640MT@TSOP48 [SB247-B4806]

MX29LV640UT@TSOP48 [SB247-B4806]

MX29LV641ML@TSOP48 [SB247-B4806]

MX29LV800AB(0.4)@CSP48 [\$\$\$\$\$\$]

MX29LV800AB@TSOP48 [SB247-B4806]

MX29LV800AT(0.4)@CSP48 [\$\$\$\$\$\$]

MX29LV800AT@TSOP48 [SB247-B4806]

MX29LV800B(0.4)@CSP48 [\$\$\$\$\$\$]

MX29LV800B@TSOP48 [SB247-B4806]

MX29LV800T(0.4)@CSP48 [\$\$\$\$\$\$]

MX29LV800T@TSOP48 [SB247-B4806]

MX29LW160TT@TSOP48 [SB247-B4806]

MX29LW161BT@TSOP48 [SB247-B4806]
MX29LW320BT@TSOP48 [SB247-B4806]
MX29LW321BT@TSOP48 [SB247-B4806]
MX29SL402CBT@TSOP48 [SB247-B4806]
MX29SL402CTT@TSOP48 [SB247-B4806]
MX29SL800CB@TSOP48 [SB247-B4806]
MX29SL800CBXB(0.30)@CSP48 [\$\$\$\$\$]
MX29SL800CBXE(0.40)@CSP48 [\$\$\$\$\$]
MX29SL800CBXH(0.30)@CSP48 [\$\$\$\$\$]
MX29SL800CT@TSOP48 [SB247-B4806]
MX29SL800CTXB(0.30)@CSP48 [\$\$\$\$\$]
MX29SL800CTXE(0.40)@CSP48 [\$\$\$\$\$]
MX29SL800CTXH(0.30)@CSP48 [\$\$\$\$\$]
MX29SL802CBT@TSOP48 [SB247-B4806]
MX29SL802CTT@TSOP48 [SB247-B4806]

MX29LW161TT@TSOP48 [SB247-B4806]
MX29LW320TT@TSOP48 [SB247-B4806]
MX29LW321TT@TSOP48 [SB247-B4806]

MAGNACHIP

MICROCONTROLLER

GMS97C1051
GMS97C2051
GMS97C51
GMS97C51@TQFP44 [SA675-B4805]
GMS97C51H@PLCC44 [SA244]
GMS97C52
GMS97C52@TQFP44 [SA675-B4805]
GMS97C52H@PLCC44 [SA244]
GMS97C54
GMS97C54@TQFP44 [SA675-B4805]
GMS97C54H@PLCC44 [SA244]
GMS97C56
GMS97C56@TQFP44 [SA675-B4805]
GMS97C56H@PLCC44 [SA244]
GMS97C58
GMS97C58@TQFP44 [SA675-B4805]
GMS97C58H@PLCC44 [SA244]
GMS97L1051
GMS97L2051
GMS97L51
GMS97L51@TQFP44 [SA675-B4805]
GMS97L52@PLCC44 [SA244]
GMS97L54
GMS97L54@TQFP44 [SA675-B4805]
GMS97L56@PLCC44 [SA244]
GMS97L58
GMS97L58@TQFP44 [SA675-B4805]

GMS97C1051@S0IC20 [SA404]
GMS97C2051@S0IC20 [SA404]
GMS97C51@PLCC44 [SA244]
GMS97C51H
GMS97C51H@TQFP44 [SA675-B4805]
GMS97C52@PLCC44 [SA244]
GMS97C52H
GMS97C52H@TQFP44 [SA675-B4805]
GMS97C54@PLCC44 [SA244]
GMS97C54H
GMS97C54H@TQFP44 [SA675-B4805]
GMS97C56@PLCC44 [SA244]
GMS97C56H
GMS97C56H@TQFP44 [SA675-B4805]
GMS97C58@PLCC44 [SA244]
GMS97C58H
GMS97C58H@TQFP44 [SA675-B4805]
GMS97L1051@S0IC20 [SA404]
GMS97L2051@S0IC20 [SA404]
GMS97L51@PLCC44 [SA244]
GMS97L52
GMS97L52@TQFP44 [SA675-B4805]
GMS97L54@PLCC44 [SA244]
GMS97L56
GMS97L56@TQFP44 [SA675-B4805]
GMS97L58@PLCC44 [SA244]

MAXIM

E(E)PROM/FRAM/NVRAM

DS1220AB
DS1220Y
DS1225AD
DS1225E
DS1230AB

DS1220AD
DS1225AB
DS1225D
DS1225Y
DS1230W

DS1230Y
DS1235Y
DS1244
DS1245AB
DS1245W
DS1248W
DS1249AB
DS1249Y
DS1250W
DS1251AB
DS1251Y
DS1256Y
DS1258W
DS1265AB
DS1265Y
DS1270W
DS1284
DS1284Q@PLCC28 [SA008A]
DS1286
DS1287
DS12887
DS12C887
DS1386(32K)
DS1485
DS1488
DS1511
DS1553W
DS1554W
DS1642
DS1644
DS1645EE
DS1646
DS1650AB
DS1687-3
DS17287-3
DS1742
DS1743
DS1744
DS1746
DS1747W
DS17487-5
DS17887-5
DS2430AP@TSOC6
DS2431P@TSOC6
DS2433@PR-35
DS2433S(5.5)@S0IC8 [SA605B]
DS2502P@TSOC6 [\$\$\$\$\$\$]
DS2502UNW
DS2502UNW@TSOC6 [\$\$\$\$\$\$]
DS2506S@S0IC8 [SA602A]
DS4520@TSSOP16 [SA026-B3201]

DS1235AB
DS1243Y
DS1244Y
DS1245EE
DS1245Y
DS1248Y
DS1249W
DS1250AB
DS1250Y
DS1251W
DS1256W
DS1258AB
DS1258Y
DS1265W
DS1270AB
DS1270Y
DS1284N
DS1284QN@PLCC28 [SA008A]
DS1286I
DS1287A
DS12887A
DS12C887A
DS1386(8K)
DS1485@S0IC28 [SA630]
DS1501
DS1553
DS1554
DS1556
DS1643
DS1645AB
DS1645Y
DS1647
DS1650Y
DS1687-5
DS17287-5
DS1742W
DS1743W
DS1744W
DS1747
DS17487-3
DS17887-3
DS2430A@T0-92
DS2431@T0-92
DS2432P@TSOC6
DS2433S(3.9)@S0IC8 [SA602A]
DS2502
DS2502S@S0IC8 [SA602A]
DS2502UNW@S0IC8 [SA602A]
DS2506
DS4510@uSOP10 [SA602]
DS4550@TSSOP20 [SA026-B3201]

MAXWELL

E(E) PROM/FRAM/NVRAM

28C010
28C010@TSOP32 [SA410T-B4001]

28C010@PLCC32 [SA015A1T]
28C010T

28C010T@PLCC32 [SA015A1T]
28C011
28C011@TSOP32 [SA410T-B4001]
28C011T@PLCC32 [SA015A1T]

28C010T@TSOP32 [SA410T-B4001]
28C011@PLCC32 [SA015A1T]
28C011T
28C011T@TSOP32 [SA410T-B4001]

MEGAWIN

E(E) PROM/FRAM/NVRAM

MM25SB512@S0IC8 [SA602A]
MM29F040@PLCC32 [SA015A1T]
MM29LF040
MM29LF040@TSOP32 [SA410T-B4001]

MM29F040
MM29F040@TSOP32 [SA410T-B4001]
MM29LF040@PLCC32 [SA015A1T]

MICROCONTROLLER

MPC89L53AF@PQFP44 [SA675-B4805]

MICROCHIP

E(E) PROM/FRAM/NVRAM

24AA00
24AA00@S0IC8 [SA602A]
24AA00@TSSOP8 [SA026-B3201]
24AA01@DFN8 [SA724]
24AA01@TSSOP8 [SA026-B3201]
24AA014@S0IC8 [SA602A]
24AA02
24AA02@MSOP8 [SA666]
24AA02@SOT-23-5 [SA717]
24AA024
24AA024@MSOP8 [SA666]
24AA024@TSSOP8 [SA026-B3201]
24AA025@DFN8 [SA724]
24AA025@S0IC8 [SA602A]
24AA04
24AA04@S0IC8 [SA602A]
24AA08
24AA08@S0IC8 [SA602A]
24AA1025
24AA1025@TSSOP8 [SA026-B3201]
24AA128@DFN8 [SA724]
24AA128@S0IC8 [SA602A]
24AA128@TSSOP8 [SA026-B3201]
24AA16@DFN8 [SA724]
24AA16@TSSOP8 [SA026-B3201]
24AA164@S0IC8 [SA602A]
24AA174
24AA174@TSSOP8 [SA026-B3201]
24AA256@DFN8 [SA724]
24AA256@S0IC8 [SA602A]
24AA256@TSSOP8 [SA026-B3201]
24AA32(Rotated)@TSSOP8 [SA026-B3201]
24AA32@DFN8 [SA724]
24AA32@S0IC8 [SA602A]

24AA00@DFN8 [SA724]
24AA00@SOT-23 [SA717]
24AA01
24AA01@S0IC8 [SA602A]
24AA014
24AA014@TSSOP8 [SA026-B3201]
24AA02@DFN8 [SA724]
24AA02@S0IC8 [SA602A]
24AA02@TSSOP8 [SA026-B3201]
24AA024@DFN8 [SA724]
24AA024@S0IC8 [SA602A]
24AA025
24AA025@MSOP8 [SA666]
24AA025@TSSOP8 [SA026-B3201]
24AA04@DFN8 [SA724]
24AA04@TSSOP8 [SA026-B3201]
24AA08@DFN8 [SA724]
24AA08@TSSOP8 [SA026-B3201]
24AA1025@S0IC8 [SA605B]
24AA128
24AA128@MSOP8 [SA666]
24AA128@TSSOP14 [SA026-B3201]
24AA16
24AA16@S0IC8 [SA602A]
24AA164
24AA164@TSSOP8 [SA026-B3201]
24AA174@S0IC8 [SA602A]
24AA256
24AA256@MSOP8 [SA666]
24AA256@TSSOP14 [SA026-B3201]
24AA32
24AA32@MSOP8 [SA666]
24AA32@TSSOP8 [SA026-B3201]

24AA32A	
24AA32A(Rotated)@TSSOP8 [SA026-B3201]	
24AA32A@DFN8 [SA724]	24AA32A@MSOP8 [SA666]
24AA32A@S0IC8 [SA602A]	24AA32A@TSSOP8 [SA026-B3201]
24AA512	24AA512@DFN8 [SA683]
24AA512@S0IC8 [SA605B]	24AA512@TSSOP14 [SA602]
24AA52	24AA52@DFN8 [SA724]
24AA52@MSOP8 [SA666]	24AA52@S0IC8 [SA602A]
24AA52@TSSOP8 [SA026-B3201]	24AA64
24AA64(Rotated)@TSSOP8 [SA026-B3201]	
24AA64@DFN8 [SA724]	24AA64@MSOP8 [SA666]
24AA64@S0IC8 [SA602A]	24AA64@TSSOP8 [SA026-B3201]
24AA65	24AA65@DFN8 [SA724]
24AA65@S0IC8 [SA602A]	24AA65@TSSOP8 [SA026-B3201]
24C00	24C00@DFN8 [SA724]
24C00@S0IC8 [SA602A]	24C00@S0T-23 [SA717]
24C00@TSSOP8 [SA026-B3201]	24C01
24C01A	24C01A@S0IC8 [SA602A]
24C01C	24C01C@S0IC8 [SA602A]
24C01C@TSSOP8 [SA026-B3201]	24C02
24C02A	24C02A@S0IC8 [SA602A]
24C02C	24C02C@S0IC8 [SA602A]
24C02C@TSSOP8 [SA026-B3201]	24C04
24C04A	24C04A@S0IC8 [SA602A]
24C04A@TSSOP8 [SA026-B3201]	24C08
24C08@S0IC8 [SA602A]	24C08B
24C08B@S0IC8 [SA602A]	24C16
24C16@S0IC8 [SA602A]	24C16B
24C16B@S0IC8 [SA602A]	24C32
24C32@DFN8 [SA724]	24C32@S0IC8 [SA602A]
24C64	24C64@DFN8 [SA724]
24C64@S0IC8 [SA602A]	24C64@TSSOP8 [SA026-B3201]
24C65	24C65@DFN8 [SA724]
24C65@S0IC8 [SA602A]	24FC1025
24FC1025@S0IC8 [SA605B]	24FC1025@TSSOP8 [SA026-B3201]
24FC128	24FC128@DFN8 [SA724]
24FC128@MSOP8 [SA666]	24FC128@S0IC8 [SA602A]
24FC128@TSSOP14 [SA026-B3201]	24FC128@TSSOP8 [SA026-B3201]
24FC256	24FC256@DFN8 [SA724]
24FC256@MSOP8 [SA666]	24FC256@S0IC8 [SA602A]
24FC256@TSSOP14 [SA026-B3201]	24FC256@TSSOP8 [SA026-B3201]
24FC32	24FC32@DFN8 [SA724]
24FC32@S0IC8 [SA602A]	24FC512
24FC512@DFN8 [SA683]	24FC512@S0IC8 [SA605B]
24FC512@TSSOP14 [SA602]	24FC65
24FC65@DFN8 [SA724]	24FC65@S0IC8 [SA602A]
24LC00	24LC00@DFN8 [SA724]
24LC00@S0IC8 [SA602A]	24LC00@S0T-23 [SA717]
24LC00@TSSOP8	24LC01
24LC014	24LC014@S0IC8 [SA602A]
24LC014@TSSOP8 [SA026-B3201]	24LC01B
24LC01B@DFN8 [SA724]	24LC01B@S0IC8 [SA602A]
24LC01B@TSSOP8 [SA026-B3201]	24LC02
24LC024	24LC024@S0IC8 [SA602A]
24LC024@TSSOP8 [SA026-B3201]	24LC025
24LC025@S0IC8 [SA602A]	24LC025@TSSOP8 [SA026-B3201]
24LC02B	24LC02B@DFN8 [SA724]
24LC02B@MSOP8 [SA666]	24LC02B@S0IC8 [SA602A]
24LC02B@S0T-23-5 [SA717]	24LC02B@TSSOP8 [SA026-B3201]

24LC04	24LC04B
24LC04B@DFN8 [SA724]	24LC04B@S0IC8 [SA602A]
24LC04B@TSSOP8 [SA026-B3201]	24LC08
24LC08B	24LC08B@DFN8 [SA724]
24LC08B@S0IC8 [SA602A]	24LC08B@TSSOP8 [SA026-B3201]
24LC1025	24LC1025@S0IC8 [SA605B]
24LC1025@TSSOP8 [SA026-B3201]	24LC128
24LC128@DFN8 [SA724]	24LC128@MSOP8 [SA666]
24LC128@S0IC8 [SA602A]	24LC128@TSSOP14 [SA026-B3201]
24LC128@TSSOP8 [SA026-B3201]	24LC16
24LC16@MSOP8 [SA666]	24LC16@S0IC8 [SA602A]
24LC164	24LC164@S0IC8 [SA602A]
24LC16B	24LC16B@DFN8 [SA724]
24LC16B@S0IC8 [SA602A]	24LC16B@TSSOP8 [SA026-B3201]
24LC174	24LC174@S0IC8 [SA602A]
24LC21	24LC21@S0IC8 [SA602A]
24LC21A	24LC21A@S0IC8 [SA602A]
24LC22A	24LC22A@S0IC8 [SA602A]
24LC256	24LC256@DFN8 [SA724]
24LC256@MSOP8 [SA666]	24LC256@S0IC8 [SA602A]
24LC256@TSSOP14 [SA026-B3201]	24LC256@TSSOP8 [SA026-B3201]
24LC32	24LC32@S0IC8 [SA602A]
24LC32A	24LC32A@DFN8 [SA724]
24LC32A@S0IC8 [SA602A]	24LC32A@TSSOP8 [SA026-B3201]
24LC512	24LC512@DFN8 [SA683]
24LC512@S0IC8 [SA605B]	24LC512@TSSOP14 [SA602]
24LC64	
24LC64(Rotated)@TSSOP8 [SA026-B3201]	
24LC64@DFN8 [SA724]	24LC64@MSOP8 [SA666]
24LC64@S0IC8 [SA602A]	24LC64@TSSOP8 [SA026-B3201]
24LC65	24LC65@DFN8 [SA724]
24LC65@S0IC8 [SA602A]	24LCS21
24LCS21@S0IC8 [SA602A]	24LCS21A
24LCS21A@S0IC8 [SA602A]	24LCS22
24LCS22@S0IC8 [SA602A]	24LCS22A
24LCS22A@S0IC8 [SA602A]	24LCS52
24LCS52@DFN8 [SA724]	24LCS52@MSOP8 [SA666]
24LCS52@S0IC8 [SA602A]	24LCS52@TSSOP8 [SA026-B3201]
25AA010A	25AA010A@DFN8 [SA683]
25AA010A@MSOP8 [SA605B]	25AA010A@S0IC8 [SA602A]
25AA010A@S0T-23 [SA717]	25AA010A@TSSOP8 [SA026-B3201]
25AA010A[X-Rotated]@TSSOP8 [SA026-B3201]	
25AA020A	25AA020A@DFN8 [SA683]
25AA020A@MSOP8 [SA605B]	25AA020A@S0IC8 [SA602A]
25AA020A@S0T-23 [SA717]	25AA020A@TSSOP8 [SA026-B3201]
25AA020A[X-Rotated]@TSSOP8 [SA026-B3201]	
25AA040	25AA040@S0IC8 [SA602A]
25AA040@TSSOP8 [SA026-B3201]	25AA040A
25AA040A@DFN8 [SA683]	25AA040A@MSOP8 [SA605B]
25AA040A@S0IC8 [SA602A]	25AA040A@S0T-23 [SA717]
25AA040A@TSSOP8 [SA026-B3201]	
25AA040A[X-Rotated]@TSSOP8 [SA026-B3201]	
25AA080	25AA080@S0IC8 [SA602A]
25AA080A	25AA080A@MSOP8 [SA605B]
25AA080A@S0IC8 [SA602A]	25AA080A@TSSOP8 [SA026-B3201]
25AA080B	25AA080B@MSOP8 [SA605B]
25AA080B@S0IC8 [SA602A]	25AA080B@TSSOP8 [SA026-B3201]
25AA1024	25AA1024@DFN8 [SA683]
25AA1024@S0IC8 [SA602A]	25AA1024@S0IJ8 [SA605B]

25AA128	25AA128@DFN8 [SA683]
25AA128@S0IC8(4.0) [SA602A]	25AA128@S0IC8(5.4) [SA605B]
25AA128@TSSOP8 [SA026-B3201]	
25AA128[X-Rotated]@TSSOP8 [SA026-B3201]	
25AA160	25AA160@S0IC8 [SA602A]
25AA160A	25AA160A@MSOP8 [SA605B]
25AA160A@S0IC8 [SA602A]	25AA160A@TSSOP8 [SA026-B3201]
25AA160B	25AA160B@MSOP8 [SA605B]
25AA160B@S0IC8 [SA602A]	25AA160B@TSSOP8 [SA026-B3201]
25AA256	25AA256@DFN8 [SA683]
25AA256@S0IC8(4.0) [SA602A]	25AA256@S0IC8(5.4) [SA605B]
25AA256@TSSOP8 [SA026-B3201]	
25AA256[X-Rotated]@TSSOP8 [SA026-B3201]	
25AA320	25AA320@S0IC8 [SA602A]
25AA320@TSSOP14 [SA026-B3201]	25AA320@TSSOP8 [SA026-B3201]
25AA512	25AA512@DFN8 [SA683]
25AA512@S0IC8 [SA602A]	25AA512@S0IJ8 [SA605B]
25AA640	25AA640@S0IC8 [SA602A]
25AA640@TSSOP8 [SA026-B3201]	
25C040@S0IC8 [SA602A]	25C040
25C080	25C040@TSSOP8 [SA026-B3201]
25C160	25C080@S0IC8 [SA602A]
25C320	25C160@S0IC8 [SA602A]
25C320@TSSOP14 [SA026-B3201]	25C320@S0IC8 [SA602A]
25C640	25C320@TSSOP8 [SA026-B3201]
25C640@TSSOP8 [SA026-B3201]	25C640@S0IC8 [SA602A]
25LC010A@DFN8 [SA683]	25LC010A
25LC010A@S0IC8 [SA602A]	25LC010A@MSOP8 [SA605B]
25LC010A@TSSOP8 [SA026-B3201]	25LC010A@S0T-23 [SA717]
25LC010A[X-Rotated]@TSSOP8 [SA026-B3201]	
25LC020A	25LC020A@DFN8 [SA683]
25LC020A@MSOP8 [SA605B]	25LC020A@S0IC8 [SA602A]
25LC020A@S0T-23 [SA717]	25LC020A@TSSOP8 [SA026-B3201]
25LC020A[X-Rotated]@TSSOP8 [SA026-B3201]	
25LC040	25LC040@S0IC8 [SA602A]
25LC040@TSSOP8	25LC040A
25LC040A@DFN8 [SA683]	25LC040A@MSOP8 [SA605B]
25LC040A@S0IC8 [SA602A]	25LC040A@S0T-23 [SA717]
25LC040A@TSSOP8 [SA026-B3201]	
25LC040A[X-Rotated]@TSSOP8 [SA026-B3201]	
25LC080	25LC080@S0IC8 [SA602A]
25LC080A	25LC080A@MSOP8 [SA605B]
25LC080A@S0IC8 [SA602A]	25LC080A@TSSOP8 [SA026-B3201]
25LC080B	25LC080B@MSOP8 [SA605B]
25LC080B@S0IC8 [SA602A]	25LC080B@TSSOP8 [SA026-B3201]
25LC1024	25LC1024@DFN8 [SA683]
25LC1024@S0IC8 [SA602A]	25LC1024@S0IJ8 [SA605B]
25LC128	25LC128@DFN8 [SA683]
25LC128@S0IC8(4.0) [SA602A]	25LC128@S0IC8(5.4) [SA605B]
25LC128@TSSOP8 [SA026-B3201]	
25LC128[X-Rotated]@TSSOP8 [SA026-B3201]	
25LC160	25LC160@S0IC8 [SA602A]
25LC160A	25LC160A@MSOP8 [SA605B]
25LC160A@S0IC8 [SA602A]	25LC160A@TSSOP8 [SA026-B3201]
25LC160B	25LC160B@MSOP8 [SA605B]
25LC160B@S0IC8 [SA602A]	25LC160B@TSSOP8 [SA026-B3201]
25LC256	25LC256@DFN8 [SA683]
25LC256@S0IC8(4.0) [SA602A]	25LC256@S0IC8(5.4) [SA605B]
25LC256@TSSOP8 [SA026-B3201]	

25LC256[X-Rotated]@TSSOP8 [SA026-B3201]	
25LC320	25LC320(SN)@S0IC8 [SA602A]
25LC320@TSSOP14 [SA026-B3201]	25LC320@TSSOP8 [SA026-B3201]
25LC512	25LC512@DFN8 [SA683]
25LC512@S0IC8 [SA602A]	25LC512@S0IJ8 [SA605B]
25LC640	25LC640@S0IC8 [SA602A]
25LC640@TSSOP8 [SA026-B3201]	27256
27256@PLCC32 [SA015A1T]	27C128
27C128@PLCC32 [SA015A1T]	27C128A
27C128A@PLCC32 [SA015A1T]	27C256
27C256@PLCC32 [SA015A1T]	27C32A
27C512	27C512@PLCC32 [SA015A1T]
27C512A	27C512A@PLCC32 [SA015A1T]
27C513	27C64
27C64@PLCC32 [SA015A1T]	27C64@S0IC28 [SA404]
27HC1616	27HC1616@PLCC44 [SA244]
27HC1616L	27HC1616L@PLCC44 [SA244]
27HC256	27HC256@PLCC32 [SA015A1T]
27HC256L	27HC256L@PLCC32 [SA015A1T]
27HC416	27HC416@PLCC44 [SA244]
27HC64	27HC64@PLCC32 [SA015A1T]
27HC64@S0IC28 [SA404]	27HC641
27HC641@PLCC28 [SA008A]	27HC641@S0IC24 [SA404]
27HC641L	27HC641L@PLCC28 [SA008A]
27HC641L@S0IC24 [SA404]	27HC64L
27HC64L@PLCC32 [SA015A1T]	27HC64L@S0IC28 [SA404]
27LV256	27LV256@PLCC32 [SA015A1T]
27LV64	2817
2864	2864@PLCC32 [SA015A1T]
28C04	28C04@PLCC32 [SA015A1T]
28C04@S0IC24 [SA404]	28C04A
28C04A@PLCC32 [SA015A1T]	28C04A@S0IC24 [SA404]
28C04AF	28C04AF@PLCC32 [SA015A1T]
28C04AF@S0IC24 [SA404]	28C04F
28C04F@PLCC32 [SA015A1T]	28C04F@S0IC24 [SA404]
28C16	28C16@PLCC32 [SA015A1T]
28C16@S0IC24 [SA404]	28C16A
28C16A@PLCC32 [SA015A1T]	28C16A@S0IC24 [SA404]
28C16AF	28C16AF@PLCC32 [SA015A1T]
28C16AF@S0IC24 [SA404]	28C16F
28C16F@PLCC32 [SA015A1T]	28C16F@S0IC24 [SA404]
28C17	28C17@PLCC32 [SA015A1T]
28C17@S0IC28 [SA404]	28C17A
28C17A@PLCC32 [SA015A1T]	28C17A@S0IC28 [SA404]
28C17AF	28C17AF@PLCC32 [SA015A1T]
28C17AF@S0IC28 [SA404]	28C17F
28C17F@PLCC32 [SA015A1T]	28C17F@S0IC28 [SA404]
28C256	28C256@PLCC32 [SA015A1T]
28C256F	28C256F@PLCC32 [SA015A1T]
28C64A	28C64A@PLCC32 [SA015A1T]
28C64A@S0IC28 [SA404]	28C64A@TSOP32 [SA410T-B4001]
28C64AF	28C64AF@PLCC32 [SA015A1T]
28C64AF@S0IC28 [SA404]	28LV64A
28LV64A@PLCC32 [SA015A1T]	28LV64A@S0IC28 [SA404]
28PC64	28PC64@PLCC32 [SA015A1T]
85C72	85C72@S0IC8 [SA602A]
85C82	85C82@S0IC8 [SA602A]
85C92	85C92@S0IC8 [SA602A]
93AA46(08bit)	93AA46(08bit)@S0IC8 [SA602A]

93AA46(16bit)	93AA46(16bit)@S0IC8 [SA602A]
93AA46A(08bit)	93AA46A(08bit)@DFN8
93AA46A(08bit)@MSOP8 [SA666]	93AA46A(08bit)@S0IC8 [SA602A]
93AA46A(08bit)@S0T-23 [SA717]	
93AA46A(08bit)@TSSOP8 [SA026-B3201]	
93AA46B(16bit)	93AA46B(16bit)@DFN8
93AA46B(16bit)@MSOP8 [SA666]	93AA46B(16bit)@S0IC8 [SA602A]
93AA46B(16bit)@S0T-23 [SA717]	
93AA46B(16bit)@TSSOP8 [SA026-B3201]	
93AA46C(08bit)	93AA46C(08bit)@DFN8
93AA46C(08bit)@MSOP8 [SA666]	93AA46C(08bit)@S0IC8 [SA602A]
93AA46C(08bit)@TSSOP8 [SA026-B3201]	
93AA46C(16bit)	93AA46C(16bit)@DFN8
93AA46C(16bit)@MSOP8 [SA666]	93AA46C(16bit)@S0IC8 [SA602A]
93AA46C(16bit)@TSSOP8 [SA026-B3201]	
93AA56(08bit)	93AA56(08bit)@S0IC8 [SA602A]
93AA56(16bit)	93AA56(16bit)@S0IC8 [SA602A]
93AA56A(08bit)	93AA56A(08bit)@DFN8
93AA56A(08bit)@MSOP8 [SA666]	93AA56A(08bit)@S0IC8 [SA602A]
93AA56A(08bit)@S0T-23 [SA717]	
93AA56A(08bit)@TSSOP8 [SA026-B3201]	
93AA56B(16bit)	93AA56B(16bit)@DFN8
93AA56B(16bit)@MSOP8 [SA666]	93AA56B(16bit)@S0IC8 [SA602A]
93AA56B(16bit)@S0T-23 [SA717]	
93AA56B(16bit)@TSSOP8 [SA026-B3201]	
93AA56C(08bit)	93AA56C(08bit)@DFN8
93AA56C(08bit)@MSOP8 [SA666]	93AA56C(08bit)@S0IC8 [SA602A]
93AA56C(08bit)@TSSOP8 [SA026-B3201]	
93AA56C(16bit)	93AA56C(16bit)@DFN8
93AA56C(16bit)@MSOP8 [SA666]	93AA56C(16bit)@S0IC8 [SA602A]
93AA56C(16bit)@TSSOP8 [SA026-B3201]	
93AA66(08bit)	93AA66(08bit)@S0IC8 [SA602A]
93AA66(16bit)	93AA66(16bit)@S0IC8 [SA602A]
93AA66A(08bit)	93AA66A(08bit)@DFN8
93AA66A(08bit)@MSOP8 [SA666]	93AA66A(08bit)@S0IC8 [SA602A]
93AA66A(08bit)@S0T-23 [SA717]	
93AA66A(08bit)@TSSOP8 [SA026-B3201]	
93AA66B(16bit)	93AA66B(16bit)@DFN8
93AA66B(16bit)@MSOP8 [SA666]	93AA66B(16bit)@S0IC8 [SA602A]
93AA66B(16bit)@S0T-23 [SA717]	
93AA66B(16bit)@TSSOP8 [SA026-B3201]	
93AA66C(08bit)	93AA66C(08bit)@DFN8
93AA66C(08bit)@MSOP8 [SA666]	93AA66C(08bit)@S0IC8 [SA602A]
93AA66C(08bit)@TSSOP8 [SA026-B3201]	
93AA66C(16bit)	93AA66C(16bit)@DFN8
93AA66C(16bit)@MSOP8 [SA666]	93AA66C(16bit)@S0IC8 [SA602A]
93AA66C(16bit)@TSSOP8 [SA026-B3201]	
93AA76(08bit)	93AA76(08bit)@S0IC8 [SA602A]
93AA76(16bit)	93AA76(16bit)@S0IC8 [SA602A]
93AA76A(08bit)	93AA76A(08bit)@DFN8
93AA76A(08bit)@MSOP8 [SA666]	93AA76A(08bit)@S0IC8 [SA602A]
93AA76A(08bit)@S0T-23 [SA717]	
93AA76A(08bit)@TSSOP8 [SA026-B3201]	
93AA76B(16bit)	93AA76B(16bit)@DFN8
93AA76B(16bit)@MSOP8 [SA666]	93AA76B(16bit)@S0IC8 [SA602A]
93AA76B(16bit)@S0T-23 [SA717]	
93AA76B(16bit)@TSSOP8 [SA026-B3201]	
93AA76C(08bit)	93AA76C(08bit)@DFN8
93AA76C(08bit)@MSOP8 [SA666]	93AA76C(08bit)@S0IC8 [SA602A]

93AA76C(08bit)@TSSOP8 [SA026-B3201]	
93AA76C(16bit)	93AA76C(16bit)@DFN8
93AA76C(16bit)@MSOP8 [SA666]	93AA76C(16bit)@SOIC8 [SA602A]
93AA76C(16bit)@TSSOP8 [SA026-B3201]	
93AA86(08bit)	93AA86(08bit)@SOIC8 [SA602A]
93AA86(16bit)	93AA86(16bit)@SOIC8 [SA602A]
93AA86A(08bit)	93AA86A(08bit)@DFN8
93AA86A(08bit)@MSOP8 [SA666]	93AA86A(08bit)@SOIC8 [SA602A]
93AA86A(08bit)@SOT-23 [SA717]	
93AA86A(08bit)@TSSOP8 [SA026-B3201]	
93AA86B(16bit)	93AA86B(16bit)@DFN8
93AA86B(16bit)@MSOP8 [SA666]	93AA86B(16bit)@SOIC8 [SA602A]
93AA86B(16bit)@SOT-23 [SA717]	
93AA86B(16bit)@TSSOP8 [SA026-B3201]	
93AA86C(08bit)	93AA86C(08bit)@DFN8
93AA86C(08bit)@MSOP8 [SA666]	93AA86C(08bit)@SOIC8 [SA602A]
93AA86C(08bit)@TSSOP8 [SA026-B3201]	
93AA86C(16bit)	93AA86C(16bit)@DFN8
93AA86C(16bit)@MSOP8 [SA666]	93AA86C(16bit)@SOIC8 [SA602A]
93AA86C(16bit)@TSSOP8 [SA026-B3201]	
93C06(08bit)	93C06(08bit)@SOIC8 [SA602A]
93C06(16bit)	93C06(16bit)@SOIC8 [SA602A]
93C46(08bit)	93C46(08bit)@SOIC8 [SA602A]
93C46(16bit)	93C46(16bit)@SOIC8 [SA602A]
93C46A(08bit)	93C46A(08bit)@DFN8
93C46A(08bit)@MSOP8 [SA666]	93C46A(08bit)@SOIC8 [SA602A]
93C46A(08bit)@SOT-23 [SA717]	
93C46A(08bit)@TSSOP8 [SA026-B3201]	
93C46B(16bit)	93C46B(16bit)@DFN8
93C46B(16bit)@MSOP8 [SA666]	93C46B(16bit)@SOIC8 [SA602A]
93C46B(16bit)@SOT-23 [SA717]	
93C46B(16bit)@TSSOP8 [SA026-B3201]	
93C46C(08bit)	93C46C(08bit)@DFN8
93C46C(08bit)@MSOP8 [SA666]	93C46C(08bit)@SOIC8 [SA602A]
93C46C(08bit)@TSSOP8 [SA026-B3201]	
93C46C(16bit)	93C46C(16bit)@DFN8
93C46C(16bit)@MSOP8 [SA666]	93C46C(16bit)@SOIC8 [SA602A]
93C46C(16bit)@TSSOP8 [SA026-B3201]	
93C56(08bit)	93C56(08bit)@SOIC8 [SA602A]
93C56(16bit)	93C56(16bit)@SOIC8 [SA602A]
93C56A(08bit)	93C56A(08bit)@DFN8
93C56A(08bit)@MSOP8 [SA666]	93C56A(08bit)@SOIC8 [SA602A]
93C56A(08bit)@SOT-23 [SA717]	
93C56A(08bit)@TSSOP8 [SA026-B3201]	
93C56B(16bit)	93C56B(16bit)@DFN8
93C56B(16bit)@MSOP8 [SA666]	93C56B(16bit)@SOIC8 [SA602A]
93C56B(16bit)@SOT-23 [SA717]	
93C56B(16bit)@TSSOP8 [SA026-B3201]	
93C56C(08bit)	93C56C(08bit)@DFN8
93C56C(08bit)@MSOP8 [SA666]	93C56C(08bit)@SOIC8 [SA602A]
93C56C(08bit)@TSSOP8 [SA026-B3201]	
93C56C(16bit)	93C56C(16bit)@DFN8
93C56C(16bit)@MSOP8 [SA666]	93C56C(16bit)@SOIC8 [SA602A]
93C56C(16bit)@TSSOP8 [SA026-B3201]	
93C66(08bit)	93C66(08bit)@SOIC8 [SA602A]
93C66(16bit)	93C66(16bit)@SOIC8 [SA602A]
93C66A(08bit)	93C66A(08bit)@DFN8
93C66A(08bit)@MSOP8 [SA666]	93C66A(08bit)@SOIC8 [SA602A]
93C66A(08bit)@SOT-23 [SA717]	

93C66A(08bit)@TSSOP8 [SA026-B3201]	
93C66B(16bit)	93C66B(16bit)@DFN8
93C66B(16bit)@MSOP8 [SA666]	93C66B(16bit)@SOIC8 [SA602A]
93C66B(16bit)@SOT-23 [SA717]	
93C66B(16bit)@TSSOP8 [SA026-B3201]	
93C66C(08bit)	93C66C(08bit)@DFN8
93C66C(08bit)@MSOP8 [SA666]	93C66C(08bit)@SOIC8 [SA602A]
93C66C(08bit)@TSSOP8 [SA026-B3201]	
93C66C(16bit)	93C66C(16bit)@DFN8
93C66C(16bit)@MSOP8 [SA666]	93C66C(16bit)@SOIC8 [SA602A]
93C66C(16bit)@TSSOP8 [SA026-B3201]	
93C76(08bit)	93C76(08bit)@SOIC8 [SA602A]
93C76(16bit)	93C76(16bit)@SOIC8 [SA602A]
93C76A(08bit)	93C76A(08bit)@DFN8
93C76A(08bit)@MSOP8 [SA666]	93C76A(08bit)@SOIC8 [SA602A]
93C76A(08bit)@SOT-23 [SA717]	
93C76A(08bit)@TSSOP8 [SA026-B3201]	
93C76B(16bit)	93C76B(16bit)@DFN8
93C76B(16bit)@MSOP8 [SA666]	93C76B(16bit)@SOIC8 [SA602A]
93C76B(16bit)@SOT-23 [SA717]	
93C76B(16bit)@TSSOP8 [SA026-B3201]	
93C76C(08bit)	93C76C(08bit)@DFN8
93C76C(08bit)@MSOP8 [SA666]	93C76C(08bit)@SOIC8 [SA602A]
93C76C(08bit)@TSSOP8 [SA026-B3201]	
93C76C(16bit)	93C76C(16bit)@DFN8
93C76C(16bit)@MSOP8 [SA666]	93C76C(16bit)@SOIC8 [SA602A]
93C76C(16bit)@TSSOP8 [SA026-B3201]	
93C86(08bit)	93C86(08bit)@SOIC8 [SA602A]
93C86(16bit)	93C86(16bit)@SOIC8 [SA602A]
93C86A(08bit)	93C86A(08bit)@DFN8
93C86A(08bit)@MSOP8 [SA666]	93C86A(08bit)@SOIC8 [SA602A]
93C86A(08bit)@SOT-23 [SA717]	
93C86A(08bit)@TSSOP8 [SA026-B3201]	
93C86B(16bit)	93C86B(16bit)@DFN8
93C86B(16bit)@MSOP8 [SA666]	93C86B(16bit)@SOIC8 [SA602A]
93C86B(16bit)@SOT-23 [SA717]	
93C86B(16bit)@TSSOP8 [SA026-B3201]	
93C86C(08bit)	93C86C(08bit)@DFN8
93C86C(08bit)@MSOP8 [SA666]	93C86C(08bit)@SOIC8 [SA602A]
93C86C(08bit)@TSSOP8 [SA026-B3201]	
93C86C(16bit)	93C86C(16bit)@DFN8
93C86C(16bit)@MSOP8 [SA666]	93C86C(16bit)@SOIC8 [SA602A]
93C86C(16bit)@TSSOP8 [SA026-B3201]	
93LC46(08bit)	93LC46(08bit)@SOIC8 [SA602A]
93LC46(16bit)	93LC46(16bit)@SOIC8 [SA602A]
93LC46A(08bit)	93LC46A(08bit)@DFN8
93LC46A(08bit)@MSOP8 [SA666]	93LC46A(08bit)@SOIC8 [SA602A]
93LC46A(08bit)@SOT-23 [SA717]	
93LC46A(08bit)@TSSOP8 [SA026-B3201]	
93LC46B(16bit)	93LC46B(16bit)@DFN8
93LC46B(16bit)@MSOP8 [SA666]	93LC46B(16bit)@SOIC8 [SA602A]
93LC46B(16bit)@SOT-23 [SA717]	
93LC46B(16bit)@TSSOP8 [SA026-B3201]	
93LC46BX	93LC46BX@SOIC8 [SA602A]
93LC46C(08bit)	93LC46C(08bit)@DFN8
93LC46C(08bit)@MSOP8 [SA666]	93LC46C(08bit)@SOIC8 [SA602A]
93LC46C(08bit)@TSSOP8 [SA026-B3201]	
93LC46C(16bit)	93LC46C(16bit)@DFN8
93LC46C(16bit)@MSOP8 [SA666]	93LC46C(16bit)@SOIC8 [SA602A]

93LC46C(16bit)@TSSOP8 [SA026-B3201]	
93LC56(08bit)	93LC56(08bit)@SOIC8 [SA602A]
93LC56(16bit)	93LC56(16bit)@SOIC8 [SA602A]
93LC56A(08bit)	93LC56A(08bit)@DFN8
93LC56A(08bit)@MSOP8 [SA666]	93LC56A(08bit)@SOIC8 [SA602A]
93LC56A(08bit)@SOT-23 [SA717]	
93LC56A(08bit)@TSSOP8 [SA026-B3201]	
93LC56B(16bit)	93LC56B(16bit)@DFN8
93LC56B(16bit)@MSOP8 [SA666]	93LC56B(16bit)@SOIC8 [SA602A]
93LC56B(16bit)@SOT-23 [SA717]	
93LC56B(16bit)@TSSOP8 [SA026-B3201]	
93LC56BX	93LC56BX@SOIC8 [SA602A]
93LC56C(08bit)	93LC56C(08bit)@DFN8
93LC56C(08bit)@MSOP8 [SA666]	93LC56C(08bit)@SOIC8 [SA602A]
93LC56C(08bit)@TSSOP8 [SA026-B3201]	
93LC56C(16bit)	93LC56C(16bit)@DFN8
93LC56C(16bit)@MSOP8 [SA666]	93LC56C(16bit)@SOIC8 [SA602A]
93LC56C(16bit)@TSSOP8 [SA026-B3201]	
93LC66(08bit)	93LC66(08bit)@SOIC8 [SA602A]
93LC66(16bit)	93LC66(16bit)@SOIC8 [SA602A]
93LC66A(08bit)	93LC66A(08bit)@DFN8
93LC66A(08bit)@MSOP8 [SA666]	93LC66A(08bit)@SOIC8 [SA602A]
93LC66A(08bit)@SOT-23 [SA717]	
93LC66A(08bit)@TSSOP8 [SA026-B3201]	
93LC66B(16bit)	93LC66B(16bit)@DFN8
93LC66B(16bit)@MSOP8 [SA666]	93LC66B(16bit)@SOIC8 [SA602A]
93LC66B(16bit)@SOT-23 [SA717]	
93LC66B(16bit)@TSSOP8 [SA026-B3201]	
93LC66BX	93LC66BX@SOIC8 [SA602A]
93LC66C(08bit)	93LC66C(08bit)@DFN8
93LC66C(08bit)@MSOP8 [SA666]	93LC66C(08bit)@SOIC8 [SA602A]
93LC66C(08bit)@TSSOP8 [SA026-B3201]	
93LC66C(16bit)	93LC66C(16bit)@DFN8
93LC66C(16bit)@MSOP8 [SA666]	93LC66C(16bit)@SOIC8 [SA602A]
93LC66C(16bit)@TSSOP8 [SA026-B3201]	
93LC76(08bit)	93LC76(08bit)@SOIC8 [SA602A]
93LC76(16bit)	93LC76(16bit)@SOIC8 [SA602A]
93LC76A(08bit)	93LC76A(08bit)@DFN8
93LC76A(08bit)@MSOP8 [SA666]	93LC76A(08bit)@SOIC8 [SA602A]
93LC76A(08bit)@SOT-23 [SA717]	
93LC76A(08bit)@TSSOP8 [SA026-B3201]	
93LC76B(16bit)	93LC76B(16bit)@DFN8
93LC76B(16bit)@MSOP8 [SA666]	93LC76B(16bit)@SOIC8 [SA602A]
93LC76B(16bit)@SOT-23 [SA717]	
93LC76B(16bit)@TSSOP8 [SA026-B3201]	
93LC76C(08bit)	93LC76C(08bit)@DFN8
93LC76C(08bit)@MSOP8 [SA666]	93LC76C(08bit)@SOIC8 [SA602A]
93LC76C(08bit)@TSSOP8 [SA026-B3201]	
93LC76C(16bit)	93LC76C(16bit)@DFN8
93LC76C(16bit)@MSOP8 [SA666]	93LC76C(16bit)@SOIC8 [SA602A]
93LC76C(16bit)@TSSOP8 [SA026-B3201]	
93LC86(08bit)	93LC86(08bit)@SOIC8 [SA602A]
93LC86(16bit)	93LC86(16bit)@SOIC8 [SA602A]
93LC86A(08bit)	93LC86A(08bit)@DFN8
93LC86A(08bit)@MSOP8 [SA666]	93LC86A(08bit)@SOIC8 [SA602A]
93LC86A(08bit)@SOT-23 [SA717]	
93LC86A(08bit)@TSSOP8 [SA026-B3201]	
93LC86B(16bit)	93LC86B(16bit)@DFN8
93LC86B(16bit)@MSOP8 [SA666]	93LC86B(16bit)@SOIC8 [SA602A]

93LC86B(16bit)@SOT-23 [SA717]	
93LC86B(16bit)@TSSOP8 [SA026-B3201]	
93LC86C(08bit)	93LC86C(08bit)@DFN8
93LC86C(08bit)@MSOP8 [SA666]	93LC86C(08bit)@SOIC8 [SA602A]
93LC86C(08bit)@TSSOP8 [SA026-B3201]	
93LC86C(16bit)	93LC86C(16bit)@DFN8
93LC86C(16bit)@MSOP8 [SA666]	93LC86C(16bit)@SOIC8 [SA602A]
93LC86C(16bit)@TSSOP8 [SA026-B3201]	
93LCS46	93LCS46@SOIC14 [SA026-B3201]
93LCS46@SOIC8 [SA602A]	93LCS56
93LCS56@SOIC14 [SA026-B3201]	93LCS56@SOIC8 [SA602A]
93LCS66	93LCS66@SOIC14 [SA026-B3201]
93LCS66@SOIC8 [SA602A]	HCS101
HCS101SN@SOIC8 [SA602A]	HCS200
HCS200SN@SOIC8 [SA602A]	HCS300
HCS300SN@SOIC8 [SA602A]	HCS301
HCS301SN@SOIC8 [SA602A]	HCS320
HCS320SN@SOIC8 [SA602A]	HCS360
HCS360SN@SOIC8 [SA602A]	HCS361
HCS361SN@SOIC8 [SA602A]	

MICROCONTROLLER

PIC10F200	PIC10F200@SOT6 [SA717]
PIC10F202	PIC10F202@SOT6 [SA717]
PIC10F204	PIC10F204@SOT6 [SA717]
PIC10F206	PIC10F206@SOT6 [SA717]
PIC10F220	PIC10F220@SOT6 [SA717]
PIC10F222	PIC10F222@SOT6 [SA717]
PIC12C508	PIC12C508@SOIC8 [SA605B]
PIC12C508A	PIC12C508A(SM)@SOIC8 [SA605B]
PIC12C508A(SN)@SOIC8 [SA602]	PIC12C509
PIC12C509(SM)@SOIC8 [SA605B]	PIC12C509(SN)@SOIC8 [SA602]
PIC12C509A	PIC12C509A(SM)@SOIC8 [SA605B]
PIC12C509A(SN)@SOIC8 [SA602]	PIC12C509A@DFN8 [SA683]
PIC12C671	PIC12C671@DFN8 [SA683]
PIC12C671@SOIC8 [SA605B]	PIC12C672
PIC12C672@DFN8 [SA683]	PIC12C672@SOIC8 [SA605B]
PIC12CE518	PIC12CE518@SOIC8 [SA605B]
PIC12CE519	PIC12CE519(SM)@SOIC8 [SA605B]
PIC12CE519(SN)@SOIC8 [SA602]	PIC12CE673
PIC12CE673@SOIC8 [SA605B]	PIC12CE674
PIC12CE674@SOIC8 [SA605B]	PIC12F1822
PIC12F1822@DFN8 [SA724]	PIC12F1822@SOIC8 [SA602A]
PIC12F508	PIC12F508@MSOP8 [SA666]
PIC12F508@SOIC8 [SA602]	PIC12F509
PIC12F509@MSOP8 [SA666]	PIC12F509@SOIC8 [SA602]
PIC12F510	PIC12F510@MSOP8 [SA666]
PIC12F510@SOIC8 [SA602A]	PIC12F519
PIC12F519@DFN8 [SA724]	PIC12F519@MSOP8 [SA666]
PIC12F519@SOIC8 [SA602A]	PIC12F609
PIC12F609@DFN8 [SA703]	PIC12F609@DFN8-S [SA683]
PIC12F609@MSOP8 [SA666]	PIC12F609@SOIC8 [SA602A]
PIC12F615	PIC12F615@DFN8 [SA703]
PIC12F615@DFN8-S [SA683]	PIC12F615@MSOP8 [SA666]
PIC12F615@SOIC8 [SA602A]	PIC12F617
PIC12F617@DFN8 [SA703]	PIC12F617@DFN8-S [SA683]
PIC12F617@MSOP8 [SA666]	PIC12F617@SOIC8 [SA602A]
PIC12F629	PIC12F629(SM)@SOIC8 [SA605B]

PIC12F629(SN)@S0IC8 [SA602]
PIC12F635
PIC12F635(MF)@DFN8 [SA683]
PIC12F635(SN)@S0IC8 [SA602]
PIC12F675(SM)@S0IC8 [SA605B]
PIC12F675@DFN8 [SA683]
PIC12F683
PIC12F683(MF)@DFN8 [SA683]
PIC12F683(SN)@S0IC8 [SA602]
PIC12HV609@DFN8 [SA703]
PIC12HV609@MSOP8 [SA666]
PIC12HV615
PIC12HV615@DFN8-S [SA683]
PIC12HV615@S0IC8 [SA602A]
PIC12LC508@S0IC8 [SA605B]
PIC12LC508A(SM)@S0IC8 [SA605B]
PIC12LC509
PIC12LC509(SN)@S0IC8 [SA602]
PIC12LC509A(SM)@S0IC8 [SA605B]
PIC12LC671
PIC12LC671@S0IC8 [SA605B]
PIC12LC672@DFN8 [SA683]
PIC12LF1822
PIC12LF1822@S0IC8 [SA602A]
PIC12LF508@MSOP8 [SA666]
PIC12LF509
PIC12LF509@S0IC8 [SA602]
PIC12LF519@DFN8 [SA724]
PIC12LF519@S0IC8 [SA602A]
PIC14000@S0IC28 [SA404]
PIC16C432
PIC16C433
PIC16C505
PIC16C52
PIC16C54
PIC16C54A
PIC16C54A@SSOP20 [SA626A]
PIC16C54B@S0IC18 [SA404]
PIC16C54C
PIC16C54C@SSOP20 [SA626A]
PIC16C55@S0IC28 [SA404]
PIC16C554@S0IC18 [SA404]
PIC16C556
PIC16C558
PIC16C558@SSOP20 [SA626A]
PIC16C55A@S0IC28 [SA404]
PIC16C56
PIC16C56A
PIC16C56A@SSOP20 [SA626A]
PIC16C57@S0IC28 [SA404]
PIC16C57C
PIC16C57C@SSOP28 [SA626A]
PIC16C58@S0IC18 [SA404]
PIC16C58A@S0IC18 [SA404]
PIC16C58B
PIC16C58B@SSOP20 [SA626A]
PIC16C61@S0IC18 [SA404]
PIC16C62@S0IC28 [SA404]
PIC16C620

PIC12F629@DFN8 [SA683]
PIC12F635(MD)@DFN8 [SA744]
PIC12F635(SM)@S0IC8 [SA605B]
PIC12F675
PIC12F675(SN)@S0IC8 [SA602]
PIC12F675@SSOP20 [SA626A]
PIC12F683(MD)@DFN8 [SA744]
PIC12F683(SM)@S0IC8 [SA605B]
PIC12HV609
PIC12HV609@DFN8-S [SA683]
PIC12HV609@S0IC8 [SA602A]
PIC12HV615@DFN8 [SA703]
PIC12HV615@MSOP8 [SA666]
PIC12LC508
PIC12LC508A
PIC12LC508A(SN)@S0IC8 [SA602]
PIC12LC509(SM)@S0IC8 [SA605B]
PIC12LC509A
PIC12LC509A(SN)@S0IC8 [SA602]
PIC12LC671@DFN8 [SA683]
PIC12LC672
PIC12LC672@S0IC8 [SA605B]
PIC12LF1822@DFN8 [SA724]
PIC12LF508
PIC12LF508@S0IC8 [SA602]
PIC12LF509@MSOP8 [SA666]
PIC12LF519
PIC12LF519@MSOP8 [SA666]
PIC14000
PIC14000@SSOP28 [SA626A]
PIC16C432@SSOP20 [SA626A]
PIC16C433@S0IC18
PIC16C505@S0IC14 [SA602]
PIC16C52@S0IC18 [SA404]
PIC16C54@S0IC18 [SA404]
PIC16C54A@S0IC18 [SA404]
PIC16C54B
PIC16C54B@SSOP20 [SA626A]
PIC16C54C@S0IC18 [SA404]
PIC16C55
PIC16C554
PIC16C554@SSOP20 [SA626A]
PIC16C556@S0IC18 [SA404]
PIC16C558@S0IC18 [SA404]
PIC16C55A
PIC16C55A@SSOP28 [SA626A]
PIC16C56@S0IC18 [SA404]
PIC16C56A@S0IC18 [SA404]
PIC16C57
PIC16C57@SSOP28 [SA626A]
PIC16C57C@S0IC28 [SA404]
PIC16C58
PIC16C58A
PIC16C58A@SSOP20 [SA626A]
PIC16C58B@S0IC18 [SA404]
PIC16C61
PIC16C62
PIC16C62@SSOP28 [SA626A]
PIC16C620@S0IC18 [SA404]

PIC16C620A
PIC16C620A@SSOP20 [SA626A]
PIC16C621@S0IC18 [SA404]
PIC16C621A@S0IC18 [SA404]
PIC16C622
PIC16C622A
PIC16C622A@SSOP20 [SA626A]
PIC16C625@S0IC18 [SA404]
PIC16C62A@S0IC28 [SA404]
PIC16C62B
PIC16C62B@SSOP28 [SA626A]
PIC16C63@S0IC28 [SA404]
PIC16C63A@S0IC28 [SA404]
PIC16C64
PIC16C641@S0IC28 [SA404]
PIC16C642
PIC16C642@SSOP28 [SA626A]
PIC16C66@S0IC28 [SA404]
PIC16C70@S0IC18 [SA404]
PIC16C71@S0IC18 [SA404]
PIC16C710@S0IC18 [SA404]
PIC16C711
PIC16C711@SSOP20 [SA626A]
PIC16C712@S0IC18 [SA404]
PIC16C715
PIC16C715@SSOP20 [SA626A]
PIC16C716@S0IC18 [SA404]
PIC16C717
PIC16C717@SSOP20 [SA626A]
PIC16C71A@S0IC18 [SA404]
PIC16C72@S0IC28 [SA404]
PIC16C72A
PIC16C72A@SSOP28 [SA626A]
PIC16C73@S0IC28 [SA404]
PIC16C73A@S0IC28 [SA404]
PIC16C73B@S0IC28 [SA404]
PIC16C745
PIC16C76
PIC16C770
PIC16C770@SSOP20 [SA626A]
PIC16C771@S0IC20
PIC16C773
PIC16C773@SSOP28 [SA626A]
PIC16C781@S0IC20
PIC16C782
PIC16C782@SSOP20 [SA626A]
PIC16C84@S0IC18 [SA404]
PIC16CE623@S0IC18 [SA404]
PIC16CE624@S0IC18 [SA404]
PIC16CE625@S0IC18 [SA404]
PIC16CR83
PIC16CR84
PIC16F1823
PIC16F1823@QFN16(4*4) [SA727]
PIC16F1823@TSSOP14 [SA026-B3201]
PIC16F1826@QFN28 [SA685]
PIC16F1826@SSOP20 [SA626A]
PIC16F1827@QFN28 [SA685]
PIC16F1827@SSOP20 [SA626A]

PIC16C620A@S0IC18 [SA404]
PIC16C621
PIC16C621A
PIC16C621A@SSOP20 [SA626A]
PIC16C622@S0IC18 [SA404]
PIC16C622A@S0IC18 [SA404]
PIC16C625
PIC16C62A
PIC16C62A@SSOP28 [SA626A]
PIC16C62B@S0IC28 [SA404]
PIC16C63
PIC16C63A
PIC16C63A@SSOP28 [SA626A]
PIC16C641
PIC16C641@SSOP28 [SA626A]
PIC16C642@S0IC28 [SA404]
PIC16C66
PIC16C70
PIC16C71
PIC16C710
PIC16C710@SSOP20 [SA626A]
PIC16C711@S0IC18 [SA404]
PIC16C712
PIC16C712@SSOP20 [SA626A]
PIC16C715@S0IC18 [SA404]
PIC16C716
PIC16C716@SSOP20 [SA626A]
PIC16C717@S0IC18
PIC16C71A
PIC16C72
PIC16C72@SSOP28 [SA626A]
PIC16C72A@S0IC28 [SA404]
PIC16C73
PIC16C73A
PIC16C73B
PIC16C73B@SSOP28 [SA626A]
PIC16C745@S0IC28
PIC16C76@S0IC28 [SA404]
PIC16C770@S0IC20
PIC16C771
PIC16C771@SSOP20 [SA626A]
PIC16C773@S0IC28
PIC16C781
PIC16C781@SSOP20 [SA626A]
PIC16C782@S0IC20
PIC16C84
PIC16CE623
PIC16CE624
PIC16CE625
PIC16CE625@SSOP20 [SA626A]
PIC16CR83@S0IC18 [SA404]
PIC16CR84@S0IC18 [SA404]
PIC16F1823@QFN16(3*3) [SA743]
PIC16F1823@S0IC14 [SA602]
PIC16F1826
PIC16F1826@S0IC18 [SA404]
PIC16F1827
PIC16F1827@S0IC18 [SA404]
PIC16F505

PIC16F505@S0IC14 [SA602]
PIC16F506
PIC16F506@TSSOP14 [SA643]
PIC16F526@S0IC14 [SA602]
PIC16F54
PIC16F54@SSOP20 [SA626A]
PIC16F57@S0IC28 [SA404]
PIC16F59
PIC16F59@TQFP44 [SA245A-B4805]
PIC16F610@QFN16 [SA727]
PIC16F610@TSSOP14 [SA026-B3201]
PIC16F616@QFN16 [SA727]
PIC16F616@TSSOP14 [SA026-B3201]
PIC16F627@S0IC18 [SA404]
PIC16F627A
PIC16F627A@SSOP20 [SA626A]
PIC16F628@S0IC18 [SA404]
PIC16F628A
PIC16F628A@SSOP20 [SA626A]
PIC16F630@S0IC14 [SA602]
PIC16F631
PIC16F631@S0IC20 [SA404]
PIC16F636
PIC16F636@S0IC14 [SA602]
PIC16F639
PIC16F639@S0IC20 [SA404]
PIC16F648A
PIC16F648A@SSOP20 [SA626A]
PIC16F676@S0IC14 [SA602]
PIC16F677
PIC16F677@S0IC20 [SA404]
PIC16F684
PIC16F684@S0IC14 [SA602]
PIC16F685
PIC16F685@S0IC20 [SA404]
PIC16F687
PIC16F687@S0IC20 [SA404]
PIC16F688
PIC16F688@S0IC14 [SA602]
PIC16F689
PIC16F689@S0IC20 [SA404]
PIC16F690
PIC16F690@S0IC20 [SA404]
PIC16F716
PIC16F716@SSOP20 [SA626A]
PIC16F72@QFN28 [SA685]
PIC16F72@SSOP28 [SA626A]
PIC16F722@QFN28 [SA685]
PIC16F722@SSOP28 [SA626A]
PIC16F723@QFN28 [SA685]
PIC16F723@SSOP28 [SA626A]
PIC16F726@QFN28 [SA685]
PIC16F726@SSOP28 [SA626A]
PIC16F73@QFN28 [SA685]
PIC16F73@SSOP28 [SA626A]
PIC16F737@S0IC28 [SA404]
PIC16F76
PIC16F76@S0IC28 [SA404]
PIC16F767

PIC16F505@TSSOP14 [SA026-B3201]
PIC16F506@S0IC14 [SA602]
PIC16F526
PIC16F526@TSSOP14 [SA026-B3201]
PIC16F54@S0IC18 [SA404]
PIC16F57
PIC16F57@SSOP28 [SA626A]
PIC16F59@PLCC44 [SA244]
PIC16F610
PIC16F610@S0IC14 [SA602]
PIC16F616
PIC16F616@S0IC14 [SA602]
PIC16F627
PIC16F627@SSOP20 [SA626A]
PIC16F627A@S0IC18 [SA404]
PIC16F628
PIC16F628@SSOP20 [SA626A]
PIC16F628A@S0IC18 [SA404]
PIC16F630
PIC16F630@TSSOP14 [SA026-B3201]
PIC16F631@QFN20 [SA692]
PIC16F631@SSOP20 [SA626A]
PIC16F636@QFN16 [SA727]
PIC16F636@TSSOP14 [SA026-B3201]
PIC16F639@QFN20 [SA692]
PIC16F639@SSOP20 [SA626A]
PIC16F648A@S0IC18 [SA404]
PIC16F676
PIC16F676@TSSOP14 [SA026-B3201]
PIC16F677@QFN20 [SA692]
PIC16F677@SSOP20 [SA626A]
PIC16F684@QFN16 [SA727]
PIC16F684@TSSOP14 [SA026-B3201]
PIC16F685@QFN20 [SA692]
PIC16F685@SSOP20 [SA626A]
PIC16F687@QFN20 [SA692]
PIC16F687@SSOP20 [SA626A]
PIC16F688@QFN16 [SA727]
PIC16F688@TSSOP14 [SA026-B3201]
PIC16F689@QFN20 [SA692]
PIC16F689@SSOP20 [SA626A]
PIC16F690@QFN20 [SA692]
PIC16F690@SSOP20 [SA626A]
PIC16F716@S0IC18 [SA404]
PIC16F72
PIC16F72@S0IC28 [SA404]
PIC16F722
PIC16F722@S0IC28 [SA404]
PIC16F723
PIC16F723@S0IC28 [SA404]
PIC16F726
PIC16F726@S0IC28 [SA404]
PIC16F73
PIC16F73@S0IC28 [SA404]
PIC16F737
PIC16F737@SSOP28 [SA626A]
PIC16F76@QFN28 [SA685]
PIC16F76@SSOP28 [SA626A]
PIC16F767@S0IC28 [SA404]

PIC16F767@SSOP28 [SA626A]
PIC16F77@PLCC44 [SA244]
PIC16F777
PIC16F785
PIC16F785@S0IC20 [SA404]
PIC16F818
PIC16F818@S0IC18 [SA404]
PIC16F819
PIC16F819@S0IC18 [SA404]
PIC16F83
PIC16F84
PIC16F84A
PIC16F84A@SSOP20 [SA626A]
PIC16F87@QFN28 [SA685]
PIC16F87@SSOP20 [SA626A]
PIC16F870@S0IC28 [SA404]
PIC16F872
PIC16F872@SSOP28 [SA626A]
PIC16F873@S0IC28 [SA404]
PIC16F873A@QFN28 [SA685]
PIC16F873A@SSOP28 [SA626A]
PIC16F874@MQFP44 [SA675-B4805]
PIC16F874@TQFP44 [SA245A-B4805]
PIC16F874A@PLCC44 [SA244]
PIC16F876
PIC16F876A
PIC16F876A@S0IC28 [SA404]
PIC16F877
PIC16F877@PLCC44 [SA244]
PIC16F88
PIC16F88@S0IC18 [SA404]
PIC16F882
PIC16F882@S0IC28 [SA404]
PIC16F883
PIC16F883@S0IC28 [SA404]
PIC16F884
PIC16F884@QFN44(ML) [SA737]
PIC16F886
PIC16F886@S0IC28 [SA404]
PIC16F887
PIC16F887@QFN44(ML) [SA737]
PIC16F913
PIC16F913@S0IC28 [SA404]
PIC16F916
PIC16F916@S0IC28 [SA404]
PIC16HV540
PIC16HV540@SSOP20 [SA626A]
PIC16HV610@QFN16 [SA727]
PIC16HV610@TSSOP14 [SA026-B3201]
PIC16HV616@QFN16 [SA727]
PIC16HV616@TSSOP14 [SA026-B3201]
PIC16HV785@QFN20 [SA692]
PIC16HV785@SSOP20 [SA626A]
PIC16LC505@S0IC14 [SA602]
PIC16LC54A@S0IC18 [SA404]
PIC16LC54C
PIC16LC54C@SSOP20 [SA626A]
PIC16LC554@S0IC18 [SA404]
PIC16LC558@S0IC18 [SA404]

PIC16F77
PIC16F77@TQFP44 [SA245A-B4805]
PIC16F777@TQFP44 [SA245A-B4805]
PIC16F785@QFN20 [SA692]
PIC16F785@SSOP20 [SA626A]
PIC16F818@QFN28 [SA685]
PIC16F818@SSOP20 [SA626A]
PIC16F819@QFN28 [SA685]
PIC16F819@SSOP20 [SA626A]
PIC16F83@S0IC18 [SA404]
PIC16F84@S0IC18 [SA404]
PIC16F84A@S0IC18 [SA404]
PIC16F87
PIC16F87@S0IC18 [SA404]
PIC16F870
PIC16F870@SSOP28 [SA626A]
PIC16F872@S0IC28 [SA404]
PIC16F873
PIC16F873A
PIC16F873A@S0IC28 [SA404]
PIC16F874
PIC16F874@PLCC44 [SA244]
PIC16F874A
PIC16F874A@TQFP44 [SA245A-B4805]
PIC16F876@S0IC28 [SA404]
PIC16F876A@QFN28 [SA685]
PIC16F876A@SSOP28 [SA626A]
PIC16F877@MQFP44 [SA675-B4805]
PIC16F877@TQFP44 [SA245A-B4805]
PIC16F88@QFN28 [SA685]
PIC16F88@SSOP20 [SA626A]
PIC16F882@QFN28 [SA685]
PIC16F882@SSOP28 [SA626A]
PIC16F883@QFN28 [SA685]
PIC16F883@SSOP28 [SA626A]
PIC16F884@QFN44 [SA712]
PIC16F884@TQFP44 [SA245A-B4805]
PIC16F886@QFN28 [SA685]
PIC16F886@SSOP28 [SA626A]
PIC16F887@QFN44 [SA712]
PIC16F887@TQFP44 [SA245A-B4805]
PIC16F913@QFN28 [SA685]
PIC16F913@SSOP28 [SA626A]
PIC16F916@QFN28 [SA685]
PIC16F916@SSOP28 [SA626A]
PIC16HV540@S0IC18 [SA404]
PIC16HV610
PIC16HV610@S0IC14 [SA602]
PIC16HV616
PIC16HV616@S0IC14 [SA602]
PIC16HV785
PIC16HV785@S0IC20 [SA404]
PIC16LC505
PIC16LC54A
PIC16LC54A@SSOP20 [SA626A]
PIC16LC54C@S0IC18 [SA404]
PIC16LC554
PIC16LC558
PIC16LC56A

PIC16LC56A@S0IC18 [SA404]
PIC16LC58A
PIC16LC58A@SSOP20 [SA626A]
PIC16LC58B@S0IC18 [SA404]
PIC16LC620
PIC16LC620A
PIC16LC620A@SSOP20 [SA626A]
PIC16LC621A@S0IC18 [SA404]
PIC16LC622
PIC16LC62A
PIC16LC62A@SSOP28 [SA626A]
PIC16LC62B@S0IC28 [SA404]
PIC16LC63
PIC16LC63A
PIC16LC63A@SSOP28 [SA626A]
PIC16LC66@S0IC28 [SA404]
PIC16LC71@S0IC18 [SA404]
PIC16LC710@S0IC18 [SA404]
PIC16LC711
PIC16LC711@SSOP20 [SA626A]
PIC16LC712@S0IC18 [SA404]
PIC16LC715
PIC16LC716
PIC16LC716@SSOP20 [SA626A]
PIC16LC717@S0IC18
PIC16LC72
PIC16LC72@SSOP28 [SA626A]
PIC16LC72A@S0IC28 [SA404]
PIC16LC73A
PIC16LC73B
PIC16LC73B@SSOP28 [SA626A]
PIC16LC76@S0IC28 [SA404]
PIC16LC773@S0IC28
PIC16LC84
PIC16LCE623@S0IC18 [SA404]
PIC16LF1823
PIC16LF1823@QFN16(4*4) [SA727]
PIC16LF1823@TSSOP14 [SA026-B3201]
PIC16LF1826
PIC16LF1826@S0IC18 [SA404]
PIC16LF1827
PIC16LF1827@S0IC18 [SA404]
PIC16LF505
PIC16LF505@TSSOP14 [SA026-B3201]
PIC16LF506@S0IC14 [SA602]
PIC16LF526
PIC16LF526@TSSOP14 [SA026-B3201]
PIC16LF54@S0IC18 [SA404]
PIC16LF57
PIC16LF57@SSOP28 [SA626A]
PIC16LF627@S0IC18 [SA404]
PIC16LF627A
PIC16LF627A@SSOP20 [SA626A]
PIC16LF628@S0IC18 [SA404]
PIC16LF628A
PIC16LF628A@SSOP20 [SA626A]
PIC16LF631@QFN20 [SA692]
PIC16LF631@SSOP20 [SA626A]
PIC16LF639@QFN20 [SA692]

PIC16LC56A@SSOP20 [SA626A]
PIC16LC58A@S0IC18 [SA404]
PIC16LC58B
PIC16LC58B@SSOP20 [SA626A]
PIC16LC620@S0IC18 [SA404]
PIC16LC620A@S0IC18 [SA404]
PIC16LC621A
PIC16LC621A@SSOP20 [SA626A]
PIC16LC622@S0IC18 [SA404]
PIC16LC62A@S0IC28 [SA404]
PIC16LC62B
PIC16LC62B@SSOP28 [SA626A]
PIC16LC63@S0IC28 [SA404]
PIC16LC63A@S0IC28 [SA404]
PIC16LC66
PIC16LC71
PIC16LC710
PIC16LC710@SSOP20 [SA626A]
PIC16LC711@S0IC18 [SA404]
PIC16LC712
PIC16LC712@SSOP20 [SA626A]
PIC16LC715@S0IC18 [SA404]
PIC16LC716@S0IC18 [SA404]
PIC16LC717
PIC16LC717@SSOP20 [SA626A]
PIC16LC72@S0IC28 [SA404]
PIC16LC72A
PIC16LC72A@SSOP28 [SA626A]
PIC16LC73A@S0IC28 [SA404]
PIC16LC73B@S0IC28 [SA404]
PIC16LC76
PIC16LC773
PIC16LC773@SSOP28 [SA626A]
PIC16LC84@S0IC18 [SA404]
PIC16LCE623@SSOP20 [SA626A]
PIC16LF1823@QFN16(3*3) [SA743]
PIC16LF1823@S0IC14 [SA602]

PIC16LF1826@QFN28 [SA685]
PIC16LF1826@SSOP20 [SA626A]
PIC16LF1827@QFN28 [SA685]
PIC16LF1827@SSOP20 [SA626A]
PIC16LF505@S0IC14 [SA602]
PIC16LF506
PIC16LF506@TSSOP14 [SA643]
PIC16LF526@S0IC14 [SA602]
PIC16LF54
PIC16LF54@SSOP20 [SA626A]
PIC16LF57@S0IC28 [SA404]
PIC16LF627
PIC16LF627@SSOP20 [SA626A]
PIC16LF627A@S0IC18 [SA404]
PIC16LF628
PIC16LF628@SSOP20 [SA626A]
PIC16LF628A@S0IC18 [SA404]
PIC16LF631
PIC16LF631@S0IC20 [SA404]
PIC16LF639
PIC16LF639@S0IC20 [SA404]

PIC16LF639@SSOP20 [SA626A]
PIC16LF648A@S0IC18 [SA404]
PIC16LF677
PIC16LF677@S0IC20 [SA404]
PIC16LF685
PIC16LF685@S0IC20 [SA404]
PIC16LF687
PIC16LF687@S0IC20 [SA404]
PIC16LF689
PIC16LF689@S0IC20 [SA404]
PIC16LF690
PIC16LF690@S0IC20 [SA404]
PIC16LF716
PIC16LF716@SSOP20 [SA626A]
PIC16LF72@QFN28 [SA685]
PIC16LF72@SSOP28 [SA626A]
PIC16LF722@QFN28 [SA685]
PIC16LF722@SSOP28 [SA626A]
PIC16LF723@QFN28 [SA685]
PIC16LF723@SSOP28 [SA626A]
PIC16LF726@QFN28 [SA685]
PIC16LF726@SSOP28 [SA626A]
PIC16LF73@QFN28 [SA685]
PIC16LF73@SSOP28 [SA626A]
PIC16LF737@S0IC28 [SA404]
PIC16LF76
PIC16LF76@S0IC28 [SA404]
PIC16LF767
PIC16LF767@SSOP28 [SA626A]
PIC16LF818@QFN28 [SA685]
PIC16LF818@SSOP20 [SA626A]
PIC16LF819@QFN28 [SA685]
PIC16LF819@SSOP20 [SA626A]
PIC16LF83@S0IC18 [SA404]
PIC16LF84@S0IC18 [SA404]
PIC16LF84A@S0IC18 [SA404]
PIC16LF87
PIC16LF87@S0IC18 [SA404]
PIC16LF870
PIC16LF870@SSOP28 [SA626A]
PIC16LF871@MQFP44 [SA675-B4805]
PIC16LF871@TQFP44 [SA245A-B4805]
PIC16LF872@S0IC28 [SA404]
PIC16LF873
PIC16LF873A
PIC16LF873A@S0IC28 [SA404]
PIC16LF876
PIC16LF876A
PIC16LF876A@S0IC28 [SA404]
PIC16LF88
PIC16LF88@S0IC18 [SA404]
PIC16LF913
PIC16LF913@S0IC28 [SA404]
PIC16LV54A
PIC16LV54A@SSOP20 [SA626A]
PIC16LV58A@S0IC18 [SA404]
PIC17C42
PIC17C42@TQFP44 [SA245A-B4805]
PIC17C42A@PLCC44 [SA244]

PIC16LF648A
PIC16LF648A@SSOP20 [SA626A]
PIC16LF677@QFN20 [SA692]
PIC16LF677@SSOP20 [SA626A]
PIC16LF685@QFN20 [SA692]
PIC16LF685@SSOP20 [SA626A]
PIC16LF687@QFN20 [SA692]
PIC16LF687@SSOP20 [SA626A]
PIC16LF689@QFN20 [SA692]
PIC16LF689@SSOP20 [SA626A]
PIC16LF690@QFN20 [SA692]
PIC16LF690@SSOP20 [SA626A]
PIC16LF716@S0IC18 [SA404]
PIC16LF72
PIC16LF72@S0IC28 [SA404]
PIC16LF722
PIC16LF722@S0IC28 [SA404]
PIC16LF723
PIC16LF723@S0IC28 [SA404]
PIC16LF726
PIC16LF726@S0IC28 [SA404]
PIC16LF73
PIC16LF73@S0IC28 [SA404]
PIC16LF737
PIC16LF737@SSOP28 [SA626A]
PIC16LF76@QFN28 [SA685]
PIC16LF76@SSOP28 [SA626A]
PIC16LF767@S0IC28 [SA404]
PIC16LF818
PIC16LF818@S0IC18 [SA404]
PIC16LF819
PIC16LF819@S0IC18 [SA404]
PIC16LF83
PIC16LF84
PIC16LF84A
PIC16LF84A@SSOP20 [SA626A]
PIC16LF87@QFN28 [SA685]
PIC16LF87@SSOP20 [SA626A]
PIC16LF870@S0IC28 [SA404]
PIC16LF871
PIC16LF871@PLCC44 [SA244]
PIC16LF872
PIC16LF872@SSOP28 [SA626A]
PIC16LF873@S0IC28 [SA404]
PIC16LF873A@QFN28 [SA685]
PIC16LF873A@SSOP28 [SA626A]
PIC16LF876@S0IC28 [SA404]
PIC16LF876A@QFN28 [SA685]
PIC16LF876A@SSOP28 [SA626A]
PIC16LF88@QFN28 [SA685]
PIC16LF88@SSOP20 [SA626A]
PIC16LF913@QFN28 [SA685]
PIC16LF913@SSOP28 [SA626A]
PIC16LV54A@S0IC18 [SA404]
PIC16LV58A
PIC16LV58A@SSOP20 [SA626A]
PIC17C42@PLCC44 [SA244]
PIC17C42A
PIC17C42A@TQFP44 [SA245A-B4805]

PIC17C43
PIC17C43@TQFP44 [SA245A-B4805]
PIC17C44@PLCC44 [SA244]
PIC17LC42
PIC17LC42@TQFP44 [SA245A-B4805]
PIC17LC42A@PLCC44 [SA244]
PIC17LC43
PIC17LC43@TQFP44 [SA245A-B4805]
PIC17LC44@PLCC44 [SA244]
PIC18F1220
PIC18F1220@SSOP20 [SA626A]
PIC18F1230@QFN28 [SA685]
PIC18F1230@SSOP20 [SA626A]
PIC18F1320@S0IC18 [SA404]
PIC18F1330
PIC18F1330@S0IC18 [SA404]
PIC18F1330-ICD@QFN28 [SA685]
PIC18F13K22@QFN20 [SA759]
PIC18F13K22@SSOP20 [SA626A]
PIC18F13K50@QFN20 [SA759]
PIC18F13K50@SSOP20 [SA626A]
PIC18F14K22@QFN20 [SA759]
PIC18F14K22@SSOP20 [SA626A]
PIC18F14K50@QFN20 [SA759]
PIC18F14K50@SSOP20 [SA626A]
PIC18F2220@S0IC28 [SA404]
PIC18F2221@QFN28 [SA685]
PIC18F2221@SSOP28 [SA626A]
PIC18F2320@S0IC28 [SA404]
PIC18F2321@QFN28 [SA685]
PIC18F2321@SSOP28 [SA626A]
PIC18F2331@S0IC28 [SA404]
PIC18F23K20@QFN28 [SA685]
PIC18F23K20@SSOP28 [SA626A]
PIC18F23K22@QFN28 [SA685]
PIC18F23K22@SSOP28 [SA626A]
PIC18F2410@QFN28 [SA685]
PIC18F2410@SSOP28 [SA626A]
PIC18F242@S0IC28 [SA404]
PIC18F2420@QFN28 [SA685]
PIC18F2420@SSOP28 [SA626A]
PIC18F2423@QFN28 [SA685]
PIC18F2423@SSOP28 [SA626A]
PIC18F2431@S0IC28 [SA404]
PIC18F2439@S0IC28 [SA404]
PIC18F2450@QFN28 [SA685]
PIC18F2450@SSOP28 [SA626A]
PIC18F2455@S0IC28 [SA404]
PIC18F2458
PIC18F2458@SSOP28
PIC18F248@S0IC28 [SA404]
PIC18F2480@QFN28 [SA685]
PIC18F2480@SSOP28 [SA626A]
PIC18F24J10@QFN28 [SA685]
PIC18F24J10@SSOP28 [SA626A]
PIC18F24J11@QFN28 [SA685]
PIC18F24J11@SSOP28 [SA626A]
PIC18F24J50@QFN28 [SA685]
PIC18F24J50@SSOP28 [SA626A]

PIC17C43@PLCC44 [SA244]
PIC17C44
PIC17C44@TQFP44 [SA245A-B4805]
PIC17LC42@PLCC44 [SA244]
PIC17LC42A
PIC17LC42A@TQFP44 [SA245A-B4805]
PIC17LC43@PLCC44 [SA244]
PIC17LC44
PIC17LC44@TQFP44 [SA245A-B4805]
PIC18F1220@S0IC18 [SA404]
PIC18F1230
PIC18F1230@S0IC18 [SA404]
PIC18F1320
PIC18F1320@SSOP20 [SA626A]
PIC18F1330@QFN28 [SA685]
PIC18F1330@SSOP20 [SA626A]
PIC18F13K22
PIC18F13K22@S0IC20 [SA404]
PIC18F13K50
PIC18F13K50@S0IC20 [SA404]
PIC18F14K22
PIC18F14K22@S0IC20 [SA404]
PIC18F14K50
PIC18F14K50@S0IC20 [SA404]
PIC18F2220
PIC18F2221
PIC18F2221@S0IC28 [SA404]
PIC18F2320
PIC18F2321
PIC18F2321@S0IC28 [SA404]
PIC18F2331
PIC18F23K20
PIC18F23K20@S0IC28 [SA404]
PIC18F23K22
PIC18F23K22@S0IC28 [SA404]
PIC18F2410
PIC18F2410@S0IC28 [SA404]
PIC18F242
PIC18F2420
PIC18F2420@S0IC28 [SA404]
PIC18F2423
PIC18F2423@S0IC28 [SA404]
PIC18F2431
PIC18F2439
PIC18F2450
PIC18F2450@S0IC28 [SA404]
PIC18F2455
PIC18F2455@SSOP28 [SA626A]
PIC18F2458@S0IC28 [SA404]
PIC18F248
PIC18F2480
PIC18F2480@S0IC28 [SA404]
PIC18F24J10
PIC18F24J10@S0IC28 [SA404]
PIC18F24J11
PIC18F24J11@S0IC28 [SA404]
PIC18F24J50
PIC18F24J50@S0IC28 [SA404]
PIC18F24K20

PIC18F24K20@QFN28 [SA685]
PIC18F24K20@SSOP28 [SA626A]
PIC18F24K22@QFN28 [SA685]
PIC18F24K22@SSOP28 [SA626A]
PIC18F2510@QFN28 [SA685]
PIC18F2510@SSOP28 [SA626A]
PIC18F2515@S0IC28 [SA404]
PIC18F252
PIC18F2520
PIC18F2520@S0IC28 [SA404]
PIC18F2523
PIC18F2523@S0IC28 [SA404]
PIC18F2525
PIC18F2525@SSOP28 [SA626A]
PIC18F2539@S0IC28 [SA404]
PIC18F2550@S0IC28 [SA404]
PIC18F2553
PIC18F2553@SSOP28
PIC18F258@S0IC28 [SA404]
PIC18F2580@QFN28 [SA685]
PIC18F2580@SSOP28 [SA626A]
PIC18F2585@SDIP28 [SA653]
PIC18F2585@SSOP28 [SA626A]
PIC18F25J10@QFN28 [SA685]
PIC18F25J10@SSOP28 [SA626A]
PIC18F25J11@QFN28 [SA685]
PIC18F25J11@SSOP28 [SA626A]
PIC18F25J50@QFN28 [SA685]
PIC18F25J50@SSOP28 [SA626A]
PIC18F25K20@QFN28 [SA685]
PIC18F25K20@SSOP28 [SA626A]
PIC18F25K22@QFN28 [SA685]
PIC18F25K22@SSOP28 [SA626A]
PIC18F2610@S0IC28 [SA404]
PIC18F2620
PIC18F2620@SSOP28 [SA626A]
PIC18F2680@SDIP28 [SA653]
PIC18F2680@SSOP28 [SA626A]
PIC18F2682@QFN28 [SA685]
PIC18F2682@SSOP28 [SA626A]
PIC18F2685@QFN28 [SA685]
PIC18F2685@SSOP28 [SA626A]
PIC18F26J11@QFN28 [SA685]
PIC18F26J11@SSOP28 [SA626A]
PIC18F26J50@QFN28 [SA685]
PIC18F26J50@SSOP28 [SA626A]
PIC18F26K20@QFN28 [SA685]
PIC18F26K20@SSOP28 [SA626A]
PIC18F26K22@QFN28 [SA685]
PIC18F26K22@SSOP28 [SA626A]
PIC18LF1220@S0IC18 [SA404]
PIC18LF1320
PIC18LF1320@SSOP20 [SA626A]
PIC18LF13K22@QFN20 [SA759]
PIC18LF13K22@SSOP20 [SA626A]
PIC18LF13K50@QFN20 [SA759]
PIC18LF13K50@SSOP20 [SA626A]
PIC18LF14K22@QFN20 [SA759]
PIC18LF14K22@SSOP20 [SA626A]

PIC18F24K20@S0IC28 [SA404]
PIC18F24K22
PIC18F24K22@S0IC28 [SA404]
PIC18F2510
PIC18F2510@S0IC28 [SA404]
PIC18F2515
PIC18F2515@SSOP28 [SA626A]
PIC18F252@S0IC28 [SA404]
PIC18F2520@QFN28 [SA685]
PIC18F2520@SSOP28 [SA626A]
PIC18F2523@QFN28 [SA685]
PIC18F2523@SSOP28 [SA626A]
PIC18F2525@S0IC28 [SA404]
PIC18F2539
PIC18F2550
PIC18F2550@SSOP28 [SA626A]
PIC18F2553@S0IC28 [SA404]
PIC18F258
PIC18F2580
PIC18F2580@S0IC28 [SA404]
PIC18F2585
PIC18F2585@S0IC28 [SA404]
PIC18F25J10
PIC18F25J10@S0IC28 [SA404]
PIC18F25J11
PIC18F25J11@S0IC28 [SA404]
PIC18F25J50
PIC18F25J50@S0IC28 [SA404]
PIC18F25K20
PIC18F25K20@S0IC28 [SA404]
PIC18F25K22
PIC18F25K22@S0IC28 [SA404]
PIC18F2610
PIC18F2610@SSOP28 [SA626A]
PIC18F2620@S0IC28 [SA404]
PIC18F2680
PIC18F2680@S0IC28 [SA404]
PIC18F2682
PIC18F2682@S0IC28 [SA404]
PIC18F2685
PIC18F2685@S0IC28 [SA404]
PIC18F26J11
PIC18F26J11@S0IC28 [SA404]
PIC18F26J50
PIC18F26J50@S0IC28 [SA404]
PIC18F26K20
PIC18F26K20@S0IC28 [SA404]
PIC18F26K22
PIC18F26K22@S0IC28 [SA404]
PIC18LF1220
PIC18LF1220@SSOP20 [SA626A]
PIC18LF1320@S0IC18 [SA404]
PIC18LF13K22
PIC18LF13K22@S0IC20 [SA404]
PIC18LF13K50
PIC18LF13K50@S0IC20 [SA404]
PIC18LF14K22
PIC18LF14K22@S0IC20 [SA404]
PIC18LF14K50

PIC18LF14K50@QFN20 [SA759]
PIC18LF14K50@SSOP20 [SA626A]
PIC18LF2220@S0IC28 [SA404]
PIC18LF2221@QFN28 [SA685]
PIC18LF2221@SSOP28 [SA626A]
PIC18LF2320@S0IC28 [SA404]
PIC18LF2321@QFN28 [SA685]
PIC18LF2321@SSOP28 [SA626A]
PIC18LF2331@S0IC28 [SA404]
PIC18LF23K22@QFN28 [SA685]
PIC18LF23K22@SSOP28 [SA626A]
PIC18LF2410@QFN28 [SA685]
PIC18LF2410@SSOP28 [SA626A]
PIC18LF242@S0IC28 [SA404]
PIC18LF2420@QFN28 [SA685]
PIC18LF2420@SSOP28 [SA626A]
PIC18LF2423@QFN28 [SA685]
PIC18LF2423@SSOP28 [SA626A]
PIC18LF2431@S0IC28 [SA404]
PIC18LF2439@S0IC28 [SA404]
PIC18LF2450@QFN28 [SA685]
PIC18LF2450@SSOP28 [SA626A]
PIC18LF2455@S0IC28 [SA404]
PIC18LF248
PIC18LF2480
PIC18LF2480@S0IC28 [SA404]
PIC18LF24J10
PIC18LF24J10@S0IC28 [SA404]
PIC18LF24J11
PIC18LF24J11@S0IC28 [SA404]
PIC18LF24J50
PIC18LF24J50@S0IC28 [SA404]
PIC18LF24K22
PIC18LF24K22@S0IC28 [SA404]
PIC18LF2510
PIC18LF2510@S0IC28 [SA404]
PIC18LF2515
PIC18LF2515@SSOP28 [SA626A]
PIC18LF252@S0IC28 [SA404]
PIC18LF2520@QFN28 [SA685]
PIC18LF2520@SSOP28 [SA626A]
PIC18LF2523@QFN28 [SA685]
PIC18LF2523@SSOP28 [SA626A]
PIC18LF2525@S0IC28 [SA404]
PIC18LF2539
PIC18LF2550
PIC18LF2550@SSOP28 [SA626A]
PIC18LF258@S0IC28 [SA404]
PIC18LF2580@QFN28 [SA685]
PIC18LF2580@SSOP28 [SA626A]
PIC18LF2585@SDIP28 [SA653]
PIC18LF2585@SSOP28 [SA626A]
PIC18LF25J10@QFN28 [SA685]
PIC18LF25J10@SSOP28 [SA626A]
PIC18LF25J11@QFN28 [SA685]
PIC18LF25J11@SSOP28 [SA626A]
PIC18LF25J50@QFN28 [SA685]
PIC18LF25J50@SSOP28 [SA626A]
PIC18LF25K22@QFN28 [SA685]

PIC18LF14K50@S0IC20 [SA404]
PIC18LF2220
PIC18LF2221
PIC18LF2221@S0IC28 [SA404]
PIC18LF2320
PIC18LF2321
PIC18LF2321@S0IC28 [SA404]
PIC18LF2331
PIC18LF23K22
PIC18LF23K22@S0IC28 [SA404]
PIC18LF2410
PIC18LF2410@S0IC28 [SA404]
PIC18LF242
PIC18LF2420
PIC18LF2420@S0IC28 [SA404]
PIC18LF2423
PIC18LF2423@S0IC28 [SA404]
PIC18LF2431
PIC18LF2439
PIC18LF2450
PIC18LF2450@S0IC28 [SA404]
PIC18LF2455
PIC18LF2455@SSOP28 [SA626A]
PIC18LF248@S0IC28 [SA404]
PIC18LF2480@QFN28 [SA685]
PIC18LF2480@SSOP28 [SA626A]
PIC18LF24J10@QFN28 [SA685]
PIC18LF24J10@SSOP28 [SA626A]
PIC18LF24J11@QFN28 [SA685]
PIC18LF24J11@SSOP28 [SA626A]
PIC18LF24J50@QFN28 [SA685]
PIC18LF24J50@SSOP28 [SA626A]
PIC18LF24K22@QFN28 [SA685]
PIC18LF24K22@SSOP28 [SA626A]
PIC18LF2510@QFN28 [SA685]
PIC18LF2510@SSOP28 [SA626A]
PIC18LF2515@S0IC28 [SA404]
PIC18LF252
PIC18LF2520
PIC18LF2520@S0IC28 [SA404]
PIC18LF2523
PIC18LF2523@S0IC28 [SA404]
PIC18LF2525
PIC18LF2525@SSOP28 [SA626A]
PIC18LF2539@S0IC28 [SA404]
PIC18LF2550@S0IC28 [SA404]
PIC18LF258
PIC18LF2580
PIC18LF2580@S0IC28 [SA404]
PIC18LF2585
PIC18LF2585@S0IC28 [SA404]
PIC18LF25J10
PIC18LF25J10@S0IC28 [SA404]
PIC18LF25J11
PIC18LF25J11@S0IC28 [SA404]
PIC18LF25J50
PIC18LF25J50@S0IC28 [SA404]
PIC18LF25K22
PIC18LF25K22@S0IC28 [SA404]

PIC18LF25K22@SSOP28 [SA626A]	PIC18LF2610
PIC18LF2610@S0IC28 [SA404]	PIC18LF2610@SSOP28 [SA626A]
PIC18LF2620	PIC18LF2620@S0IC28 [SA404]
PIC18LF2620@SSOP28 [SA626A]	PIC18LF2680
PIC18LF2680@SDIP28 [SA653]	PIC18LF2680@S0IC28 [SA404]
PIC18LF2680@SSOP28 [SA626A]	PIC18LF2682
PIC18LF2682@QFN28 [SA685]	PIC18LF2682@S0IC28 [SA404]
PIC18LF2682@SSOP28 [SA626A]	PIC18LF2685
PIC18LF2685@QFN28 [SA685]	PIC18LF2685@S0IC28 [SA404]
PIC18LF2685@SSOP28 [SA626A]	PIC18LF26J11
PIC18LF26J11@QFN28 [SA685]	PIC18LF26J11@S0IC28 [SA404]
PIC18LF26J11@SSOP28 [SA626A]	PIC18LF26J50
PIC18LF26J50@QFN28 [SA685]	PIC18LF26J50@S0IC28 [SA626A]
PIC18LF26J50@SSOP28	PIC18LF26K22
PIC18LF26K22@QFN28 [SA685]	PIC18LF26K22@S0IC28 [SA404]
PIC18LF26K22@SSOP28 [SA626A]	PIC30F2010
PIC30F2010@SDIP28 [SA653]	PIC30F2010@S0IC28 [SA404]
PIC30F2011	PIC30F2011@QFN28 [SA685]
PIC30F2011@SDIP18 [SA653]	PIC30F2011@S0IC18 [SA404]
PIC30F2012	PIC30F2012@QFN28 [SA685]
PIC30F2012@SDIP28 [SA653]	PIC30F2012@S0IC28 [SA404]
PIC30F3010	PIC30F3010@SDIP28 [SA653]
PIC30F3010@S0IC28 [SA404]	PIC30F3011
PIC30F3011@QFP44 [SA245A-B4805]	PIC30F3012
PIC30F3012@SDIP18 [SA653]	PIC30F3012@S0IC18 [SA404]
PIC30F3013	PIC30F3013@S0IC28 [SA404]
PIC30F3014	PIC30F4012
PIC30F4012@SDIP28 [SA653]	PIC30F4012@S0IC28 [SA404]
PS200	PS200@S0IC20 [SA404]
PS200@SSOP20 [SA626A]	rFPIC12C509AF@SSOP20 [SA626A]
rFPIC12C509AG@S0IC18 [SA404]	rFPIC12LC509AF@SSOP20 [SA626A]
rFPIC12LC509AG@S0IC18 [SA404]	

MICRON

E(E)PROM/FRAM/NVRAM

MT28F002B1VG-B@TSOP40 [SA409T-B4002]
 MT28F002B1VG-T@TSOP40 [SA409T-B4002]
 MT28F002B3VG-B@TSOP40 [SA409T-B4002]
 MT28F002B3VG-T@TSOP40 [SA409T-B4002]
 MT28F002B5VG-B@TSOP40 [SA409T-B4002]
 MT28F002B5VG-T@TSOP40 [SA409T-B4002]
 MT28F002C1VG-T@TSOP40 [SA409T-B4002]
 MT28F002C5VG-T@TSOP40 [SA409T-B4002]
 MT28F002VG-B@TSOP40 [SA409T-B4002]
 MT28F002VG-T@TSOP40 [SA409T-B4002]
 MT28F004B1VG-B@TSOP40 [SA409T-B4002]
 MT28F004B1VG-T@TSOP40 [SA409T-B4002]
 MT28F004B3VG-B@TSOP40 [SA409T-B4002]
 MT28F004B3VG-T@TSOP40 [SA409T-B4002]
 MT28F004B5VG-B@TSOP40 [SA409T-B4002]
 MT28F004B5VG-T@TSOP40 [SA409T-B4002]
 MT28F004VG-B@TSOP40 [SA409T-B4002]
 MT28F004VG-T@TSOP40 [SA409T-B4002]
 MT28F008B1VG-B@TSOP40 [SA409T-B4002]
 MT28F008B1VG-T@TSOP40 [SA409T-B4002]
 MT28F008B3VG-B@TSOP40 [SA409T-B4002]

MT28F008B3VG-T@TSOP40 [SA409T-B4002]	
MT28F008B5VG-B@TSOP40 [SA409T-B4002]	
MT28F008B5VG-T@TSOP40 [SA409T-B4002]	
MT28F016S3VG@TSOP40 [SA409T-B4002]	
MT28F016S5VG@TSOP40 [SA409T-B4002]	
MT28F200B1SGB@PSOP44 [SA638]	MT28F200B1SGT@PSOP44 [SA638]
MT28F200B1WGB@TSOP48 [SB247-B4806]	
MT28F200B1WGT@TSOP48 [SB247-B4806]	
MT28F200B3SGB@PSOP44 [SA638]	MT28F200B3SGT@PSOP44 [SA638]
MT28F200B3WGB@TSOP48 [SB247-B4806]	
MT28F200B3WGT@TSOP48 [SB247-B4806]	
MT28F200B5SGB@PSOP44 [SA638]	MT28F200B5SGT@PSOP44 [SA638]
MT28F200B5WGB@TSOP48 [SB247-B4806]	
MT28F200B5WGT@TSOP48 [SB247-B4806]	
MT28F400B1SGB@PSOP44 [SA638]	MT28F400B1SGT@PSOP44 [SA638]
MT28F400B1WGB@TSOP48 [SB247-B4806]	
MT28F400B1WGT@TSOP48 [SB247-B4806]	
MT28F400B3SGB@PSOP44 [SA638]	MT28F400B3SGT@PSOP44 [SA638]
MT28F400B3WGB@TSOP48 [SB247-B4806]	
MT28F400B3WGT@TSOP48 [SB247-B4806]	
MT28F400B5SGB@PSOP44 [SA638]	MT28F400B5SGT@PSOP44 [SA638]
MT28F400B5WGB@TSOP48 [SB247-B4806]	
MT28F400B5WGT@TSOP48 [SB247-B4806]	
MT28F800B1SGB@PSOP44 [SA638]	MT28F800B1SGT@PSOP44 [SA638]
MT28F800B1WGB@TSOP48 [SB247-B4806]	
MT28F800B1WGT@TSOP48 [SB247-B4806]	
MT28F800B3SGB@PSOP44 [SA638]	MT28F800B3SGT@PSOP44 [SA638]
MT28F800B3WGB@TSOP48 [SB247-B4806]	
MT28F800B3WGT@TSOP48 [SB247-B4806]	
MT28F800B5SGB@PSOP44 [SA638]	MT28F800B5SGT@PSOP44 [SA638]
MT28F800B5WGB@TSOP48 [SB247-B4806]	
MT28F800B5WGT@TSOP48 [SB247-B4806]	

MITSUBISHI

E(E)PROM/FRAM/NVRAM

M5L27128K	M5L2716
M5L27256K	M5L2732
M5L2732A	M5L27512
M5L27512K	M5L2764K
M5L27C512A	M5M27128P
M5M27256P	M5M27512P
M5M2764P	M5M27C100K
M5M27C100K@PLCC32 [SA015A1T]	M5M27C100K@TSOP32 [SA410T-B4001]
M5M27C100P	M5M27C100P@PLCC32 [SA015A1T]
M5M27C100P@TSOP32 [SA410T-B4001]	M5M27C101JK
M5M27C101JK@PLCC32 [SA015A1T]	
M5M27C101JK@TSOP32 [SA410T-B4001]	M5M27C101K@PLCC32 [SA015A1T]
M5M27C101K	M5M27C101P
M5M27C101K@TSOP32 [SA410T-B4001]	M5M27C101P@TSOP32 [SA410T-B4001]
M5M27C101P@PLCC32 [SA015A1T]	M5M27C102K@PLCC44 [SA244]
M5M27C102K	M5M27C102P@PLCC44 [SA244]
M5M27C102P	M5M27C201K
M5M27C128K	M5M27C201K@TSOP32 [SA410T-B4001]
M5M27C201K@PLCC32 [SA015A1T]	M5M27C202K@PLCC44 [SA244]
M5M27C202K	M5M27C256(P)
M5M27C256(K)	

M5M27C256A(FP)	M5M27C256A(K)
M5M27C256A(P)	M5M27C401K
M5M27C401K@PLCC32 [SA015A1T]	M5M27C401K@TSOP32 [SA410T-B4001]
M5M27C402K	M5M27C512(FP)
M5M27C512A(FP)	M5M27C512A(K)
M5M27C512A(P)	M5M28F101
M5M28F101(REVERSE)@TSOP32 [SA410T-B4001]	
M5M28F101@PLCC32 [SA015A1T]	M5M28F101@SOP32 [SA438T]
M5M28F101@TSOP32 [SA410T-B4001]	M5M28F101A
M5M28F101A(REVERSE)@TSOP32 [SA410T-B4001]	
M5M28F101A@PLCC32 [SA015A1T]	M5M28F101A@S0IC32 [SA438T]
M5M28F101A@TSOP32 [SA410T-B4001]	
M5M28FB800(VP)@TSOP48 [SA247-B4806]	
M5M28FT800(VP)@TSOP48 [SA247-B4806]	
M5M29FB160A@TSOP48 [SA247-B4806]	M5M29FB800(FP)@PSOP44 [SA638]
M5M29FB800(VP)@TSOP48 [SA247-B4806]	
M5M29FT160A@TSOP48 [SA247-B4806]	M5M29FT800(FP)@PSOP44 [SA638]
M5M29FT800(VP)@TSOP48 [SA247-B4806]	
M5M29GB160B(VP)@TSOP48 [SA247-B4806]	
M5M29GB320(VP)@TSOP48 [SA247-B4806]	
M5M29GB640VP@TSOP48 [SA247-B4806]	
M5M29GT160B(VP)@TSOP48 [SA247-B4806]	
M5M29GT320(VP)@TSOP48 [SA247-B4806]	
M5M29GT640VP@TSOP48 [SA247-B4806]	
M5M29JB160A@TSOP48 [SA247-B4806]	M5M29JT160A@TSOP48 [SA247-B4806]
M6M80011A	M6M80011A@S0IC10 [SA605B]
M6M80011A@S0IC16 [SA605B]	M6M80021
M6M80021@S0IC10 [SA605B]	M6M80021@S0IC16 [SA605B]
M6M80041	M6M80041@S0IC10 [SA605B]

MOSEL-VITELIC

E (E) PROM / FRAM / NVRAM

V29C31004B	V29C31004B@PLCC32 [SA015A1T]
V29C31004B@TSOP32 [SA410T-B4001]	V29C31004T
V29C31004T@PLCC32 [SA015A1T]	V29C31004T@TSOP32 [SA410T-B4001]
V29C51000B	V29C51000B@PLCC32 [SA015A1T]
V29C51000B@TSOP32 [SA410T-B4001]	V29C51000T
V29C51000T@PLCC32 [SA015A1T]	V29C51000T@TSOP32 [SA410T-B4001]
V29C51001B	V29C51001B@PLCC32 [SA015A1T]
V29C51001B@TSOP32 [SA410T-B4001]	V29C51001T
V29C51001T@PLCC32 [SA015A1T]	V29C51001T@TSOP32 [SA410T-B4001]
V29C51002B	V29C51002B@PLCC32 [SA015A1T]
V29C51002B@TSOP32 [SA410T-B4001]	V29C51002T
V29C51002T@PLCC32 [SA015A1T]	V29C51002T@TSOP32 [SA410T-B4001]
V29C51004B	V29C51004B@PLCC32 [SA015A1T]
V29C51004B@TSOP32 [SA410T-B4001]	V29C51004T
V29C51004T@PLCC32 [SA015A1T]	V29C51004T@TSOP32 [SA410T-B4001]
V29LC51000	V29LC51000@PLCC32 [SA015A1T]
V29LC51000@TSOP32 [SA410T-B4001]	V29LC51001
V29LC51001@PLCC32 [SA015A1T]	V29LC51001@TSOP32 [SA410T-B4001]
V29LC51002	V29LC51002@PLCC32 [SA015A1T]
V29LC51002@TSOP32 [SA410T-B4001]	

MICROCONTROLLER

MSU1958
MSU1958@TQFP44 [SA675-B4805]
MSU2952@PLCC44 [SA244]
MSU2958
MSU2958@TQFP44 [SA675-B4805]
MSU2964@PLCC44 [SA244]

MSU1958@PLCC44 [SA244]
MSU2952
MSU2952@TQFP44 [SA675-B4805]
MSU2958@PLCC44 [SA244]
MSU2964
MSU2964@TQFP44 [SA675-B4805]

MOSTEK

E (E) PROM/FRAM/NVRAM

ET2716
ETC2732
MK2764
MK48C12
MK48T08
MK48T12B
MK48Z02
MK48Z12
MK48Z18

ETC2716
MK2716
MK48C02
MK48T02
MK48T12
MK48T18
MK48Z08
MK48Z12B

MOTOROLA

E (E) PROM/FRAM/NVRAM

MCM2716

NANSI

E (E) PROM/FRAM/NVRAM

N25S32
N25S32@S0IC8 [SA605B]

N25S32@S0IC16 [SA404]
N25S32@WS0N8 [SA683]

NANTRONICS

E (E) PROM/FRAM/NVRAM

N25S32
N25S32@S0IC8 [SA605B]
N25S80
N25S80@S0IC8[200mil] [SA605B]

N25S32@S0IC16 [SA404]
N25S32@WS0N8 [SA683]
N25S80@S0IC8[150mil] [SA602A]
N25S80@WS0N8 [SA683]

NATRONICS

E (E) PROM/FRAM/NVRAM

NS29LV032FB@TSOP48 [SB247-B4806]

NS29LV032FT@TSOP48 [SB247-B4806]

NEC

E (E) PROM/FRAM/NVRAM

D2716D	uPD271000
uPD271000@PLCC32 [SA015A1T]	uPD271000@TSOP32 [SA410T-B4001]
uPD27128	uPD27128(C)
uPD27128(D)	uPD2716
uPD27256	uPD27256(C)
uPD27256(D)	uPD27256A
uPD27256A(C)	uPD27256A(D)
uPD2732	uPD2732A
uPD27512	uPD27512ACT
uPD27512AD	uPD2764
uPD2764C	uPD2764D
uPD27C1000	uPD27C1000@PLCC32 [SA015A1T]
uPD27C1000@TSOP32 [SA410T-B4001]	uPD27C1000A
uPD27C1000A@PLCC32 [SA015A1T]	
uPD27C1000A@TSOP32 [SA410T-B4001]	
uPD27C1000AD	uPD27C1000AD@PLCC32 [SA015A1T]
uPD27C1000AD@TSOP32 [SA410T-B4001]	
uPD27C1001	uPD27C1001@PLCC32 [SA015A1T]
uPD27C1001@TSOP32 [SA410T-B4001]	uPD27C1001A
uPD27C1001A@PLCC32 [SA015A1T]	
uPD27C1001A@TSOP32 [SA410T-B4001]	
uPD27C1001D	uPD27C1001D@PLCC32 [SA015A1T]
uPD27C1001D@TSOP32 [SA410T-B4001]	
uPD27C1024	uPD27C1024A
uPD27C2001	uPD27C2001@PLCC32 [SA015A1T]
uPD27C2001@TSOP32 [SA410T-B4001]	uPD27C2001D
uPD27C2001D@PLCC32 [SA015A1T]	
uPD27C2001D@TSOP32 [SA410T-B4001]	
uPD27C210	uPD27C256
uPD27C256A	uPD27C400
uPD27C4001	uPD27C4001@PLCC32 [SA015A1T]
uPD27C4001@TSOP32 [SA410T-B4001]	uPD27C4096
uPD27C512	uPD27C64(C)
uPD27C64(D)	uPD27C8000
uPD27C8001	uPD27C8001@PLCC32 [SA015A1T]
uPD27C8001@TSOP32 [SA410T-B4001]	uPD28C04
uPD28C04@S0IC24 [SA404]	uPD28C05
uPD28C05@S0IC24 [SA404]	uPD28C256
uPD28C64	uPD28C64@S0IC28 [SA404]
uPD29F008CB@TSOP40 [SA409T-B4002]	
uPD29F008CT@TSOP40 [SA409T-B4002]	

NEXFLASH

E(E)PROM/FRAM/NVRAM

NX25B40(Bottom Boot)@MLP8 [SA683]	
NX25B40(Bottom Boot)@S0IC8 [SA602A]	
NX25B40(Top Boot)@MLP8 [SA683]	NX25B40(Top Boot)@S0IC8 [SA602A]
NX25P10@MLP8 [SA683]	NX25P10@S0IC8 [SA602A]
NX25P16@MLP8 [SA683]	NX25P16@S0IC16 [SA404]
NX25P16@S0IC8 [SA605B]	NX25P20@MLP8 [SA683]
NX25P20@S0IC8 [SA602A]	NX25P32@MLP8 [SA605B]
NX25P32@S0IC16 [SA404]	NX25P40@MLP8 [SA683]
NX25P40@S0IC8 [SA602A]	NX25P64@MLP8 [SA683]
NX25P64@S0IC16 [SA404]	NX25P80@MLP8 [SA683]
NX25P80@S0IC8 [SA602A]	NX29F010
NX29F010@PLCC32 [SA015A1T]	NX29F010@TSOP32 [SA410T-B4001]

NSC

E (E) PROM / FRAM / NVRAM

2864
MM2716E
NM24C02@S0IC8 [SA602A]
NM24C02L
NM24C02L@TSOP8 [SA026-B3201]
NM24C03@S0IC8 [SA602A]
NM24C04
NM24C04@TSOP8 [SA026-B3201]
NM24C05@S0IC8 [SA602A]
NM24C08
NM24C09
NM24C16
NM24C17
NM27C010
NM27C010@TSOP32 [SA410T-B4001]
NM27C010Q@PLCC32 [SA015A1T]
NM27C020
NM27C020@TSOP32 [SA410T-B4001]
NM27C020Q@PLCC32 [SA015A1T]
NM27C040
NM27C040@TSOP32 [SA410T-B4001]
NM27C128
NM27C210
NM27C210Q
NM27C240
NM27C256
NM27C400
NM27C512@PLCC32 [SA015A1T]
NM27C512Q@PLCC32 [SA015A1T]
NM27C64Q@PLCC32 [SA015A1T]
NM27CP256@PLCC32 [SA015A1T]
NM27LC010@PLCC32 [SA015A1T]
NM27LC256
NM27LC512
NM27LC64
NM27LV010
NM27LV010@TSOP32 [SA410T-B4001]
NM27LV210@PLCC44 [SA244]
NM27LV512@PLCC32 [SA015A1T]
NM27P040
NM27P040@TSOP32 [SA410T-B4001]
NM27P210@PLCC44 [SA244]
NM27P512@PLCC32 [SA015A1T]
NM93C06(08bit)@S0IC8 [SA602A]
NM93C06(16bit)@S0IC8 [SA602A]
NM93C46@S0IC8 [SA602A]
NM93C46A(08bit)@S0IC8 [SA602A]
NM93C46A(16bit)@S0IC8 [SA602A]
NM93C46AL(08bit)@S0IC8 [SA602A]
NM93C46AL(16bit)@S0IC8 [SA602A]
NM93C46ALZ(08bit)@S0IC8 [SA602A]
NM93C46ALZ(16bit)@S0IC8 [SA602A]
NM93C46L@S0IC8 [SA602A]

MM2716
NM24C02
NM24C02@TSOP8 [SA026-B3201]
NM24C02L@S0IC8 [SA602A]
NM24C03
NM24C03@TSOP8 [SA026-B3201]
NM24C04@S0IC8 [SA602A]
NM24C05
NM24C05@TSOP8 [SA026-B3201]
NM24C08@S0IC8 [SA602A]
NM24C09@S0IC8 [SA602A]
NM24C16@S0IC8 [SA602A]
NM24C17@S0IC8 [SA602A]
NM27C010@PLCC32 [SA015A1T]
NM27C010Q
NM27C010Q@TSOP32 [SA410T-B4001]
NM27C020@PLCC32 [SA015A1T]
NM27C020Q
NM27C020Q@TSOP32 [SA410T-B4001]
NM27C040@PLCC32 [SA015A1T]
NM27C1023
NM27C128@PLCC32 [SA015A1T]
NM27C210@PLCC44 [SA244]
NM27C210Q@PLCC44 [SA244]
NM27C240@PLCC44 [SA244]
NM27C256@PLCC32 [SA015A1T]
NM27C512
NM27C512Q
NM27C64Q
NM27CP256
NM27LC010
NM27LC010@TSOP32 [SA410T-B4001]
NM27LC256@PLCC32 [SA015A1T]
NM27LC512@PLCC32 [SA015A1T]
NM27LC64@PLCC32 [SA015A1T]
NM27LV010@PLCC32 [SA015A1T]
NM27LV210
NM27LV512
NM27LV512@TSOP32 [SA410T-B4001]
NM27P040@PLCC32 [SA015A1T]
NM27P210
NM27P512
NM93C06(08bit)
NM93C06(16bit)
NM93C46
NM93C46A(08bit)
NM93C46A(16bit)
NM93C46AL(08bit)
NM93C46AL(16bit)
NM93C46ALZ(08bit)
NM93C46ALZ(16bit)
NM93C46L
NM93C46LZ

NM93C46LZ@S0IC8 [SA602A]
NM93C56@S0IC8 [SA602A]
NM93C56A(08bit)@S0IC8 [SA602A]
NM93C56A(16bit)@S0IC8 [SA602A]
NM93C56AL(08bit)@S0IC8 [SA602A]
NM93C56AL(16bit)@S0IC8 [SA602A]
NM93C56ALZ(08bit)@S0IC8 [SA602A]
NM93C56ALZ(16bit)@S0IC8 [SA602A]
NM93C56L@S0IC8 [SA602A]
NM93C56LZ@S0IC8 [SA602A]
NM93C66@S0IC8 [SA602A]
NM93C66A(08bit)
NM93C66A@S0IC8 [SA602A]
NM93C66AL(08bit)@S0IC8 [SA602A]
NM93C66AL(16bit)@S0IC8 [SA602A]
NM93C66ALZ(08bit)@S0IC8 [SA602A]
NM93C66ALZ(16bit)@S0IC8 [SA602A]
NM93C66L@S0IC8 [SA602A]
NM93C66LZ@S0IC8 [SA602A]
NM93C86(16bit)@S0IC8 [SA602A]
NM93C86A(08bit)
NM93C86A@S0IC8 [SA602A]
NM93C86AL(08bit)@S0IC8 [SA602A]
NM93C86AL(16bit)@S0IC8 [SA602A]
NM93C86ALZ(08bit)@S0IC8 [SA602A]
NM93C86ALZ(16bit)@S0IC8 [SA602A]
NM93C86L@S0IC8 [SA602A]
NM93C86LZ@S0IC8 [SA602A]
NM93CS06(MT8)@TSS0P8 [SA026-B3201]
NM93CS06(N)
NM93CS46(MT8)@TSS0P8 [SA026-B3201]
NM93CS46(N)
NM93CS56(MT8)@TSS0P8 [SA026-B3201]
NM93CS56(N)
NM93CS66(MT8)@TSS0P8 [SA026-B3201]
NM93CS66(N)
NMC2732B
NMC27C010
NMC27C010@TS0P32 [SA410T-B4001]
NMC27C1024@PLCC44 [SA244]
NMC27C128B@PLCC32 [SA015A1T]
NMC27C128BN@PLCC32 [SA015A1T]
NMC27C128BQ@PLCC32 [SA015A1T]
NMC27C128Q
NMC27C16BQ
NMC27C16H
NMC27C16Q
NMC27C210@PLCC44 [SA244]
NMC27C210Q@PLCC44 [SA244]
NMC27C256B@PLCC32 [SA015A1T]
NMC27C256BQE
NMC27C256Q
NMC27C32
NMC27C32BQ
NMC27C32EH
NMC27C512
NMC27C512A
NMC27C512AN
NMC27C64

NM93C56
NM93C56A(08bit)
NM93C56A(16bit)
NM93C56AL(08bit)
NM93C56AL(16bit)
NM93C56ALZ(08bit)
NM93C56ALZ(16bit)
NM93C56L
NM93C56LZ
NM93C66
NM93C66A
NM93C66A(08bit)@S0IC8 [SA602A]
NM93C66AL(08bit)
NM93C66AL(16bit)
NM93C66ALZ(08bit)
NM93C66ALZ(16bit)
NM93C66L
NM93C66LZ
NM93C86(16bit)
NM93C86A
NM93C86A(08bit)@S0IC8 [SA602A]
NM93C86AL(08bit)
NM93C86AL(16bit)
NM93C86ALZ(08bit)
NM93C86ALZ(16bit)
NM93C86L
NM93C86LZ
NM93CS06(M8)@S0IC8 [SA602A]
NM93CS46(M8)@S0IC8 [SA602A]
NM93CS56(M8)@S0IC8 [SA602A]
NM93CS66(M8)@S0IC8 [SA602A]
NMC2732
NMC2732H
NMC27C010@PLCC32 [SA015A1T]
NMC27C1024
NMC27C128B
NMC27C128BN
NMC27C128BQ
NMC27C128CQ
NMC27C16
NMC27C16BQE
NMC27C16HQ
NMC27C210
NMC27C210Q
NMC27C256B
NMC27C256BN
NMC27C256BQM
NMC27C256Q@PLCC32 [SA015A1T]
NMC27C32B
NMC27C32E
NMC27C32H
NMC27C512@PLCC32 [SA015A1T]
NMC27C512A@PLCC32 [SA015A1T]
NMC27C512AN@PLCC32 [SA015A1T]
NMC27C64@PLCC32 [SA015A1T]

NMC27C64BN	NMC27C64N
NMC27CP128	NMC27CP256
NMC27CP64	NMC9306
NMC9306@S0IC8 [SA602A]	NMC9307
NMC9307@S0IC8 [SA602A]	NMC9346
NMC9346@S0IC8 [SA602A]	NMC93C56
NMC93C56@S0IC14 [SA602]	NMC93C56@S0IC8 [SA602A]
NMC93C66	NMC93C66@S0IC14 [SA602]
NMC93C86A	NMC93C86A@S0IC14 [SA602]
NMC93C86A@S0IC8 [SA602A]	
NMC93CS06(M14)@S0IC14 [SA026-B3201]	
NMC93CS06(N)	
NMC93CS46(M14)@S0IC14 [SA026-B3201]	
NMC93CS46(N)	
NMC93CS56(M14)@S0IC14 [SA026-B3201]	
NMC93CS56(N)	
NMC93CS66(M14)@S0IC14 [SA026-B3201]	
NMC93CS66(N)	
NMC93S06(M14)@S0IC14 [SA026-B3201]	
NMC93S06(N)	NMC9817
NMC9817A	NS2816A
NS9816A	

PLD

GAL16V8	GAL16V8@PLCC20 [SA001A-B2001]
GAL16V8A	GAL16V8A@PLCC20 [SA001A-B2001]

NTE

E (E) PROM/FRAM/NVRAM

NTE2532	NTE2532A
NTE25L32	

NUMONYX

E (E) PROM/FRAM/NVRAM

JR28F032M29EWB@TSOP48 [SB247-B4806]	
JR28F032M29EWH@TSOP48 [SB247-B4806]	
JR28F032M29EWL@TSOP48 [SB247-B4806]	
JR28F032M29EWT@TSOP48 [SB247-B4806]	
JR28F064M29EWB@TSOP48 [SB247-B4806]	
JR28F064M29EWH@TSOP48 [SB247-B4806]	
JR28F064M29EWL@TSOP48 [SB247-B4806]	
JR28F064M29EWT@TSOP48 [SB247-B4806]	
M25P80	M25P80@S0IC8(150 mil) [SA602A]
M25P80@S0IC8(200 mil) [SA605B]	M25P80@UFD FPN8
M25P80@VDFPN8 [SA683]	M25PX16@S0IC16 [SA404]
M25PX16@S0IC8 [SA602A]	M25PX16@VFQFPN8 [SA683]
M25PX32@S0IC16 [SA404]	M25PX32@S0IC8 [SA605B]
M25PX32@VFQFPN8 [SA683]	M25PX64@S0IC16 [SA404]
M25PX64@VDFPN8 [SA684]	M28W640HCB@TSOP48 [SB247-B4806]
M28W640HCT@TSOP48 [SB247-B4806]	M29F160FB@TSOP48 [SA247-B4806]
M29F160FT@TSOP48 [SA247-B4806]	M29F200FB@PSOP44 [SA638]

M29F200FB@TSOP48 [SA247-B4806]	M29F200FT@PSOP44 [SA638]
M29F200FT@TSOP48 [SA247-B4806]	M29F400FB@PSOP44 [SA638]
M29F400FB@TSOP48 [SA247-B4806]	M29F400FT@PSOP44 [SA638]
M29F400FT@TSOP48 [SA247-B4806]	M29F800FB@PSOP44 [SA638]
M29F800FB@TSOP48 [SA247-B4806]	M29F800FT@PSOP44 [SA638]
M29F800FT@TSOP48 [SA247-B4806]	M29W160DB@PSOP44 [SA638]
M29W160DB@TSOP48 [SB247-B4806]	M29W160DT@PSOP44 [SA638]
M29W160DT@TSOP48 [SB247-B4806]	M29W160EB@PSOP44 [SA638]
M29W160EB@TSOP48 [SB247-B4806]	M29W160ET@PSOP44 [SA638]
M29W160ET@TSOP48 [SB247-B4806]	M29W160FB@TSOP48 [SB247-B4806]
M29W160FT@TSOP48 [SB247-B4806]	M29W320EB@TSOP48 [SB247-B4806]
M29W320ET@TSOP48 [SB247-B4806]	M29W400DB@PSOP44 [SA638]
M29W400DB@TSOP48 [SB247-B4806]	M29W400DT@PSOP44 [SA638]
M29W400DT@TSOP48 [SB247-B4806]	M29W400FB@TSOP48 [SB247-B4806]
M29W400FT@TSOP48 [SB247-B4806]	M29W640DB@TSOP48 [SB247-B4806]
M29W640DT@TSOP48 [SB247-B4806]	M29W641DH@TSOP48 [SB247-B4806]
M29W641DL@TSOP48 [SB247-B4806]	M29W800DB@PSOP44 [SA638]
M29W800DB@TSOP48 [SB247-B4806]	M29W800DT@PSOP44 [SA638]
M29W800DT@TSOP48 [SB247-B4806]	M29W800FB@TSOP48 [SB247-B4806]
M29W800FT@TSOP48 [SB247-B4806]	N25Q032@S0IC8(150mil) [SA602A]
N25Q032@S0IC8(150mil)(fast mode) [SA602A]	
N25Q032@S0IC8(208mil) [SA605B]	
N25Q032@S0IC8(208mil)(fast mode) [SA605B]	
N25Q032@VDFPN8(6*5mm) [SA683]	
N25Q032@VDFPN8(6*5mm)(fast mode) [SA683]	
N25Q032@VDFPN8(8*6mm) [SA684]	
N25Q032@VDFPN8(8*6mm)(fast mode) [SA684]	
N25Q064@S0IC8(150mil) [SA602A]	
N25Q064@S0IC8(150mil)(fast mode) [SA602A]	
N25Q064@S0IC8(208mil) [SA605B]	
N25Q064@S0IC8(208mil)(fast mode) [SA605B]	
N25Q064@VDFPN8(6*5mm) [SA683]	
N25Q064@VDFPN8(6*5mm)(fast mode) [SA683]	
N25Q064@VDFPN8(8*6mm) [SA684]	
N25Q064@VDFPN8(8*6mm)(fast mode) [SA684]	
N25Q128@S0IC16 [SA404]	N25Q128@VDFPN8 [SA684]
N25Q128A11B@S0IC16 [SA404]	N25Q128A11B@VDFPN8 [SA684]
N25Q128A11E@S0IC16 [SA404]	N25Q128A11E@VDFPN8 [SA684]
N25Q128A11T@S0IC16 [SA404]	N25Q128A11T@VDFPN8 [SA684]
N25Q128A13B@S0IC16 [SA404]	N25Q128A13B@VDFPN8 [SA684]
N25Q128A13E@S0IC16 [SA404]	N25Q128A13E@VDFPN8 [SA684]
N25Q128A13T@S0IC16 [SA404]	N25Q128A13T@VDFPN8 [SA684]

NUVOTON

MICROCONTROLLER

W77E516	W77E516@PLCC44 [SA244]
W77E516@TQFP44 [SA675-B4805]	W77E532
W77E532@PLCC44 [SA244]	W77E532@TQFP44 [SA675-B4805]
W77E532A	W77E532A@PLCC44 [SA244]
W77E532A@TQFP44 [SA675-B4805]	W77E58
W77E58@PLCC44 [SA244]	W77E58@TQFP44 [SA675-B4805]
W77IE58	W77IE58@PLCC44 [SA244]
W77IE58@TQFP44 [SA675-B4805]	W77L058A
W77L058A@PLCC44 [SA244]	W77L058A@TQFP44 [SA675-B4805]
W77L516A	W77L516A@PLCC44 [SA244]
W77L516A@TQFP44 [SA675-B4805]	W77L532A

W77L532A@PLCC44 [SA244]
W77LE516
W77LE516@TQFP44 [SA675-B4805]
W77LE532@PLCC44 [SA244]
W77LE58
W77LE58@TQFP44 [SA675-B4805]
W77LE58A@PLCC44 [SA244]
W78E051B
W78E051B@TQFP44 [SA675-B4805]
W78E051C@PLCC44 [SA244]
W78E051DDG
W78E051DLG@LQFP48 [SA248-B4804]
W78E052B
W78E052B@TQFP44 [SA675-B4805]
W78E052C@PLCC44 [SA244]
W78E052DDG
W78E052DLG@LQFP48 [SA248-B4804]
W78E054B
W78E054B@TQFP44 [SA675-B4805]
W78E054C@PLCC44 [SA244]
W78E054DDG
W78E054DLG@LQFP48 [SA248-B4804]
W78E058B
W78E058B@TQFP44 [SA675-B4805]
W78E058DFG@TQFP44 [SA675-B4805]
W78E058DPG@PLCC44 [SA244]
W78E065@PLCC44 [SA244]
W78E365
W78E365@TQFP44 [SA675-B4805]
W78E365A@PLCC44 [SA244]
W78E374B
W78E378E
W78E51
W78E51@TQFP44 [SA675-B4805]
W78E516@PLCC44 [SA244]
W78E516B
W78E516B@TQFP44 [SA675-B4805]
W78E516DFG@TQFP44 [SA675-B4805]
W78E516DPG@PLCC44 [SA244]
W78E51B@PLCC44 [SA244]
W78E51B@TQFP44 [SA245A-B4805]
W78E51C@PLCC44 [SA244]
W78E52
W78E52@TQFP44 [SA675-B4805]
W78E52B@PLCC44 [SA244]
W78E52C
W78E52C@TQFP44 [SA675-B4805]
W78E54@PLCC44 [SA244]
W78E54@TQFP44 [SA245A-B4805]
W78E54B@PLCC44 [SA244]
W78E54C
W78E54C@TQFP44 [SA675-B4805]
W78E58@PLCC44 [SA244]
W78E58@TQFP44 [SA245A-B4805]
W78E58B@PLCC44 [SA244]
W78E62B
W78E62B@TQFP44 [SA675-B4805]
W78E65@PLCC44 [SA244]
W78E858

W77L532A@TQFP44 [SA675-B4805]
W77LE516@PLCC44 [SA244]
W77LE532
W77LE532@TQFP44 [SA675-B4805]
W77LE58@PLCC44 [SA244]
W77LE58A
W77LE58A@TQFP44 [SA675-B4805]
W78E051B@PLCC44 [SA244]
W78E051C
W78E051C@TQFP44 [SA675-B4805]
W78E051DFG@PQFP44 [SA675-B4805]
W78E051DPG@PLCC44 [SA244]
W78E052B@PLCC44 [SA244]
W78E052C
W78E052C@TQFP44 [SA675-B4805]
W78E052DFG@PQFP44 [SA675-B4805]
W78E052DPG@PLCC44 [SA244]
W78E054B@PLCC44 [SA244]
W78E054C
W78E054C@TQFP44 [SA675-B4805]
W78E054DFG@PQFP44 [SA675-B4805]
W78E054DPG@PLCC44 [SA244]
W78E058B@PLCC44 [SA244]
W78E058DDG
W78E058DLG@TQFP48 [SA248-B4804]
W78E065
W78E065@TQFP44 [SA675-B4805]
W78E365@PLCC44 [SA244]
W78E365A
W78E365A@TQFP44 [SA675-B4805]
W78E378
W78E378P@PLCC44 [SA244]
W78E51@PLCC44 [SA244]
W78E516
W78E516@TQFP44 [SA675-B4805]
W78E516B@PLCC44 [SA244]
W78E516DDG
W78E516DLG@TQFP48 [SA248-B4804]
W78E51B
W78E51B@PQFP44 [SA675-B4805]
W78E51C
W78E51C@TQFP44 [SA675-B4805]
W78E52@PLCC44 [SA244]
W78E52B
W78E52B@TQFP44 [SA675-B4805]
W78E52C@PLCC44 [SA244]
W78E54
W78E54@PQFP44 [SA675-B4805]
W78E54B
W78E54B@TQFP44 [SA675-B4805]
W78E54C@PLCC44 [SA244]
W78E58
W78E58@PQFP44 [SA675-B4805]
W78E58B
W78E58B@TQFP44 [SA675-B4805]
W78E62B@PLCC44 [SA244]
W78E65
W78E65@TQFP44 [SA675-B4805]
W78E858@PLCC44 [SA244]

W78E858@TQFP44 [SA675-B4805]
W78ERD2@PLCC44 [SA244]
W78I051DDG
W78I051DLG@LQFP48 [SA248-B4804]
W78I052
W78I052DDG
W78I052DLG@LQFP48 [SA248-B4804]
W78I054
W78I054DDG
W78I054DLG@LQFP48 [SA248-B4804]
W78IE52
W78IE54
W78IRD2
W78IRD2@TQFP44 [SA675-B4805]
W78L051A@PLCC44 [SA244]
W78L051C
W78L051C@TQFP44 [SA675-B4805]
W78L052A@PLCC44 [SA244]
W78L052C
W78L052C@TQFP44 [SA675-B4805]
W78L054A@PLCC44 [SA244]
W78L054C
W78L054C@TQFP44 [SA675-B4805]
W78L058A@PLCC44 [SA244]
W78L365
W78L365@TQFP44 [SA675-B4805]
W78L365A
W78L365A@TQFP44 [SA675-B4805]
W78L516
W78L516@TQFP44 [SA675-B4805]
W78L516A@PLCC44 [SA244]
W78L812A
W78L812A@TQFP44 [SA675-B4805]
W78LE365@PLCC44 [SA244]
W78LE365@TQFP48 [SA248-B4804]
W78LE51@PLCC44 [SA244]
W78LE516
W78LE516@TQFP44 [SA675-B4805]
W78LE51C@PLCC44 [SA244]
W78LE52
W78LE52@TQFP44 [SA675-B4805]
W78LE52C@PLCC44 [SA244]
W78LE54
W78LE54@TQFP44 [SA675-B4805]
W78LE54C@PLCC44 [SA244]
W78LE58
W78LE58@TQFP44 [SA675-B4805]
W78LE812@PLCC44 [SA244]
W79E201@PLCC44 [SA244]
W79E2051(dip14)
W79E2051(dip20)
W79E2051@S0IC16 [SA404]
W79E2051R(dip20)
W79E225ALG@TQFP48 [SA248-B4804]
W79E226ALG@TQFP48 [SA248-B4804]
W79E227ALG@TQFP48 [SA248-B4804]
W79E4051(dip14)
W79E4051(dip20)
W79E4051@S0IC16 [SA404]

W78ERD2
W78ERD2@TQFP44 [SA675-B4805]
W78I051DFG@PQFP44 [SA675-B4805]
W78I051DPG@PLCC44 [SA244]
W78I052@PLCC44 [SA244]
W78I052DFG@PQFP44 [SA675-B4805]
W78I052DPG@PLCC44 [SA244]
W78I054@PLCC44 [SA244]
W78I054DFG@PQFP44 [SA675-B4805]
W78I054DPG@PLCC44 [SA244]
W78IE52@PLCC44 [SA244]
W78IE54@PLCC44 [SA244]
W78IRD2@PLCC44 [SA244]
W78L051A
W78L051A@TQFP44 [SA675-B4805]
W78L051C@PLCC44 [SA244]
W78L052A
W78L052A@TQFP44 [SA675-B4805]
W78L052C@PLCC44 [SA244]
W78L054A
W78L054A@TQFP44 [SA675-B4805]
W78L054C@PLCC44 [SA244]
W78L058A
W78L058A@TQFP44 [SA675-B4805]
W78L365@PLCC44 [SA244]
W78L365@TQFP48 [SA248-B4804]
W78L365A@PLCC44 [SA244]
W78L365A@TQFP48 [SA248-B4804]
W78L516@PLCC44 [SA244]
W78L516A
W78L516A@TQFP44 [SA675-B4805]
W78L812A@PLCC44 [SA244]
W78LE365
W78LE365@TQFP44 [SA675-B4805]
W78LE51
W78LE51@TQFP44 [SA675-B4805]
W78LE516@PLCC44 [SA244]
W78LE51C
W78LE51C@TQFP44 [SA675-B4805]
W78LE52@PLCC44 [SA244]
W78LE52C
W78LE52C@TQFP44 [SA675-B4805]
W78LE54@PLCC44 [SA244]
W78LE54C
W78LE54C@TQFP44 [SA675-B4805]
W78LE58@PLCC44 [SA244]
W78LE812
W78LE812@TQFP44 [SA675-B4805]
W79E201@TQFP44 [SA675-B4805]
W79E2051(dip16)
W79E2051@S0IC14 [SA404]
W79E2051@S0IC20 [SA404]
W79E2051R@S0IC20 [SA404]
W79E225APG@PLCC44 [SA244]
W79E226APG@PLCC44 [SA244]
W79E227APG@PLCC44 [SA244]
W79E4051(dip16)
W79E4051@S0IC14 [SA404]
W79E4051@S0IC20 [SA404]

W79E4051R(dip20)
W79E532
W79E532@TQFP44 [SA675-B4805]
W79E532A@PLCC44 [SA244]
W79E533A@PLCC44 [SA244]
W79E632@PLCC44 [SA244]
W79E632A
W79E632A@TQFP44 [SA675-B4805]
W79E801A
W79E802A
W79E803A
W79E804A
W79E821A
W79E822A
W79E822B
W79E823A
W79E823B
W79E824A
W79E825A
W79E831A
W79E832A
W79E833A
W79E834A
W79L532
W79L532@TQFP44 [SA675-B4805]
W79L632@PLCC44 [SA244]
W79L632A
W79L632A@TQFP44 [SA675-B4805]

W79E4051R@S0IC20 [SA404]
W79E532@PLCC44 [SA244]
W79E532A
W79E532A@TQFP44 [SA675-B4805]
W79E632
W79E632@TQFP44 [SA675-B4805]
W79E632A@PLCC44 [SA244]
W79E633A@PLCC44 [SA244]
W79E801A@S0IC20 [SA404]
W79E802A@S0IC20 [SA404]
W79E803A@S0IC20 [SA404]
W79E804A@S0IC20 [SA404]
W79E821A@S0IC20 [SA404]
W79E822A@S0IC20 [SA404]
W79E822B@S0IC20 [SA404]
W79E823A@S0IC20 [SA404]
W79E823B@S0IC20 [SA404]
W79E824A@S0IC20 [SA404]
W79E825A@S0IC20 [SA404]
W79E831A@S0IC28 [SA404]
W79E832A@S0IC28 [SA404]
W79E833A@S0IC28 [SA404]
W79E834A@S0IC28 [SA404]
W79L532@PLCC44 [SA244]
W79L632
W79L632@TQFP44 [SA675-B4805]
W79L632A@PLCC44 [SA244]
W79L633A@PLCC44 [SA244]

NXP

MICROCONTROLLER

P83C660X2@PLCC44 [SA244]
P83C661X2@PLCC44 [SA244]
P87C51
P87C51@TQFP44 [SA675-B4805]
P87C51FA@PLCC44 [SA244]
P87C51FB
P87C51FB@TQFP44 [SA675-B4805]
P87C51FC@PLCC44 [SA244]
P87C51MA2@PLCC44 [SA244]
P87C51MC2@PLCC44 [SA244]
P87C51RA+@PLCC44 [SA244]
P87C51RA2
P87C51RA2@TQFP44 [SA675-B4805]
P87C51RB+@PLCC44 [SA244]
P87C51RB2
P87C51RB2@TQFP44 [SA675-B4805]
P87C51RC+@PLCC44 [SA244]
P87C51RC2
P87C51RC2@TQFP44 [SA675-B4805]
P87C51RD+@PLCC44 [SA244]
P87C51RD2
P87C51RD2@TQFP44 [SA245A-B4805]
P87C51SB@PLCC44 [SA244]
P87C51SF
P87C51SF@TQFP44 [SA675-B4805]

P83C660X2@TQFP44 [SA245A-B4805]
P83C661X2@TQFP44 [SA245A-B4805]
P87C51@PLCC44 [SA244]
P87C51FA
P87C51FA@TQFP44 [SA675-B4805]
P87C51FB@PLCC44 [SA244]
P87C51FC
P87C51FC@TQFP44 [SA245A-B4805]
P87C51MB2@PLCC44 [SA244]
P87C51RA+
P87C51RA+@TQFP44 [SA245A-B4805]
P87C51RA2@PLCC44 [SA244]
P87C51RB+
P87C51RB+@TQFP44 [SA245A-B4805]
P87C51RB2@PLCC44 [SA244]
P87C51RC+
P87C51RC+@TQFP44 [SA245A-B4805]
P87C51RC2@PLCC44 [SA244]
P87C51RD+
P87C51RD+@TQFP44 [SA245A-B4805]
P87C51RD2@PLCC44 [SA244]
P87C51SB
P87C51SB@TQFP44 [SA675-B4805]
P87C51SF@PLCC44 [SA244]
P87C51UB

P87C51UB@PLCC44 [SA244]
P87C51UF
P87C51UF@TQFP44 [SA675-B4805]
P87C51X2@PLCC44 [SA244]
P87C51X2@TTSOP38 [SA693]
P87C52@PLCC44 [SA244]
P87C524
P87C524@TQFP44 [SA245A-B4805]
P87C528@PLCC44 [SA244]
P87C52SB
P87C52SB@TQFP44 [SA675-B4805]
P87C52SF@PLCC44 [SA244]
P87C52UB
P87C52UB@TQFP44 [SA675-B4805]
P87C52UF@PLCC44 [SA244]
P87C52X2
P87C52X2@TQFP44 [SA245A-B4805]
P87C54
P87C54@TQFP44 [SA675-B4805]
P87C54SB@PLCC44 [SA244]
P87C54SF
P87C54SF@TQFP44 [SA675-B4805]
P87C54UB@PLCC44 [SA244]
P87C54UF
P87C54UF@TQFP44 [SA675-B4805]
P87C54X2@PLCC44 [SA244]
P87C54X2@TTSOP38 [SA693]
P87C550@PLCC44 [SA244]
P87C575@PLCC44 [SA244]
P87C576
P87C576@TQFP44 [SA675-B4805]
P87C58@PLCC44 [SA244]
P87C58SB
P87C58SB@TQFP44 [SA675-B4805]
P87C58UB@PLCC44 [SA244]
P87C58X2
P87C58X2@TQFP44 [SA245A-B4805]
P87C591@PLCC44 [SA244]
P87C652
P87C652@TQFP44 [SA675-B4805]
P87C654@PLCC44 [SA244]
P87C660X2@PLCC44 [SA244]
P87C661X2@PLCC44 [SA244]
P87CL52X2
P87CL52X2@TQFP44 [SA245A-B4805]
P87CL54X2
P87CL54X2@TQFP44 [SA245A-B4805]
P87L51FA
P87L51FA@TQFP44 [SA675-B4805]
P87L51FB@PLCC44 [SA244]
P89C138
P89C138@TQFP44 [SA245A-B4805]
P89C238@PLCC44 [SA244]
P89C51B
P89C51B@TQFP44 [SA245A-B4805]
P89C51RA+@PLCC44 [SA244]
P89C51RA2B
P89C51RA2B@TQFP44 [SA245A-B4805]
P89C51RB+@PLCC44 [SA244]

P87C51UB@TQFP44 [SA675-B4805]
P87C51UF@PLCC44 [SA244]
P87C51X2
P87C51X2@TQFP44 [SA245A-B4805]
P87C52
P87C52@TQFP44 [SA675-B4805]
P87C524@PLCC44 [SA244]
P87C528
P87C528@TQFP44 [SA245A-B4805]
P87C52SB@PLCC44 [SA244]
P87C52SF
P87C52SF@TQFP44 [SA675-B4805]
P87C52UB@PLCC44 [SA244]
P87C52UF
P87C52UF@TQFP44 [SA675-B4805]
P87C52X2@PLCC44 [SA244]
P87C52X2@TTSOP38 [SA693]
P87C54@PLCC44 [SA244]
P87C54SB
P87C54SB@TQFP44 [SA675-B4805]
P87C54SF@PLCC44 [SA244]
P87C54UB
P87C54UB@TQFP44 [SA675-B4805]
P87C54UF@PLCC44 [SA244]
P87C54X2
P87C54X2@TQFP44 [SA245A-B4805]
P87C550
P87C575
P87C575@TQFP44 [SA675-B4805]
P87C576@PLCC44 [SA244]
P87C58
P87C58@TQFP44 [SA675-B4805]
P87C58SB@PLCC44 [SA244]
P87C58UB
P87C58UB@TQFP44 [SA675-B4805]
P87C58X2@PLCC44 [SA244]
P87C58X2@TTSOP38 [SA693]
P87C591@TQFP44 [SA675-B4805]
P87C652@PLCC44 [SA244]
P87C654
P87C654@TQFP44 [SA675-B4805]
P87C660X2@TQFP44 [SA245A-B4805]
P87C661X2@TQFP44 [SA245A-B4805]
P87CL52X2@PLCC44 [SA244]
P87CL52X2@TTSOP38 [SA693]
P87CL54X2@PLCC44 [SA244]
P87CL54X2@TTSOP38 [SA693]
P87L51FA@PLCC44 [SA244]
P87L51FB
P87L51FB@TQFP44 [SA675-B4805]
P89C138@PLCC44 [SA244]
P89C238
P89C238@TQFP44 [SA245A-B4805]
P89C51B@PLCC44 [SA244]
P89C51RA+
P89C51RA+@TQFP44 [SA245A-B4805]
P89C51RA2B@PLCC44 [SA244]
P89C51RB+
P89C51RB+@TQFP44 [SA245A-B4805]

P89C51RB2B
P89C51RB2B@TQFP44 [SA245A-B4805]
P89C51RB2H@PLCC44 [SA244]
P89C51RC+
P89C51RC+@TQFP44 [SA245A-B4805]
P89C51RC2B@PLCC44 [SA244]
P89C51RC2H
P89C51RC2H@TQFP44 [SA675-B4805]
P89C51RD+@PLCC44 [SA244]
P89C51RD2B
P89C51RD2B@TQFP44 [SA245A-B4805]
P89C51RD2H@PLCC44 [SA244]
P89C51UB
P89C51UB@TQFP44 [SA245A-B4805]
P89C51UF@PLCC44 [SA244]
P89C51X2
P89C51X2@TQFP44 [SA245A-B4805]
P89C51X2B@PLCC44 [SA244]
P89C51X2F
P89C51X2F@TQFP44 [SA245A-B4805]
P89C52@PLCC44 [SA244]
P89C52B
P89C52B@TQFP44 [SA245A-B4805]
P89C52UB@PLCC44 [SA244]
P89C52UF
P89C52UF@TQFP44 [SA245A-B4805]
P89C52X2@PLCC44 [SA244]
P89C52X2B
P89C52X2B@TQFP44 [SA245A-B4805]
P89C52X2F@PLCC44 [SA244]
P89C536@PLCC44 [SA244]
P89C54
P89C54@TQFP44 [SA245A-B4805]
P89C54B@PLCC44 [SA244]
P89C54UB
P89C54UB@TQFP44 [SA245A-B4805]
P89C54UF@PLCC44 [SA244]
P89C54X2
P89C54X2@TQFP44 [SA245A-B4805]
P89C54X2B@PLCC44 [SA244]
P89C54X2F
P89C54X2F@TQFP44 [SA245A-B4805]
P89C58@PLCC44 [SA244]
P89C58B
P89C58B@TQFP44 [SA245A-B4805]
P89C58UB@PLCC44 [SA244]
P89C58UF
P89C58UF@TQFP44 [SA245A-B4805]
P89C58X2@PLCC44 [SA244]
P89C58X2B
P89C58X2B@TQFP44 [SA245A-B4805]
P89C58X2F@PLCC44 [SA244]
P89C60X2
P89C60X2@TQFP44 [SA245A-B4805]
P89C61X2@PLCC44 [SA244]
P89C660
P89C660@TQFP44 [SA675-B4805]
P89C662@PLCC44 [SA244]
P89C664

P89C51RB2B@PLCC44 [SA244]
P89C51RB2H
P89C51RB2H@TQFP44 [SA675-B4805]
P89C51RC+@PLCC44 [SA244]
P89C51RC2B
P89C51RC2B@TQFP44 [SA245A-B4805]
P89C51RC2H@PLCC44 [SA244]
P89C51RD+
P89C51RD+@TQFP44 [SA245A-B4805]
P89C51RD2B@PLCC44 [SA244]
P89C51RD2H
P89C51RD2H@TQFP44 [SA675-B4805]
P89C51UB@PLCC44 [SA244]
P89C51UF
P89C51UF@TQFP44 [SA245A-B4805]
P89C51X2@PLCC44 [SA244]
P89C51X2B
P89C51X2B@TQFP44 [SA245A-B4805]
P89C51X2F@PLCC44 [SA244]
P89C52
P89C52@TQFP44 [SA245A-B4805]
P89C52B@PLCC44 [SA244]
P89C52UB
P89C52UB@TQFP44 [SA245A-B4805]
P89C52UF@PLCC44 [SA244]
P89C52X2
P89C52X2@TQFP44 [SA245A-B4805]
P89C52X2B@PLCC44 [SA244]
P89C52X2F
P89C52X2F@TQFP44 [SA245A-B4805]
P89C538@PLCC44 [SA244]
P89C54@PLCC44 [SA244]
P89C54B
P89C54B@TQFP44 [SA245A-B4805]
P89C54UB@PLCC44 [SA244]
P89C54UF
P89C54UF@TQFP44 [SA245A-B4805]
P89C54X2@PLCC44 [SA244]
P89C54X2B
P89C54X2B@TQFP44 [SA245A-B4805]
P89C54X2F@PLCC44 [SA244]
P89C58
P89C58@TQFP44 [SA245A-B4805]
P89C58B@PLCC44 [SA244]
P89C58UB
P89C58UB@TQFP44 [SA245A-B4805]
P89C58UF@PLCC44 [SA244]
P89C58X2
P89C58X2@TQFP44 [SA245A-B4805]
P89C58X2B@PLCC44 [SA244]
P89C58X2F
P89C58X2F@TQFP44 [SA245A-B4805]
P89C60X2@PLCC44 [SA244]
P89C61X2
P89C61X2@TQFP44 [SA245A-B4805]
P89C660@PLCC44 [SA244]
P89C662
P89C662@TQFP44 [SA675-B4805]
P89C664@PLCC44 [SA244]

P89C664@TQFP44 [SA675-B4805]	P89C668
P89C668@PLCC44 [SA244]	P89C668@TQFP44 [SA675-B4805]
P89C669	P89C669@LQFP44 [SA245A-B4805]
P89C669@PLCC44 [SA244]	P89C669X2
P89C669X2@LQFP44 [SA245A-B4805]	P89C669X2@PLCC44 [SA244]
P89C738	P89C738@PLCC44 [SA244]
P89C738@TQFP44 [SA245A-B4805]	P89C838
P89C838@PLCC44 [SA244]	P89C838@TQFP44 [SA245A-B4805]
P89CV51RB2@PLCC44 [SA244]	P89CV51RB2@TQFP44 [SA245A-B4805]
P89CV51RC2@PLCC44 [SA244]	P89CV51RC2@TQFP44 [SA245A-B4805]
P89CV51RD2@PLCC44 [SA244]	P89CV51RD2@TQFP44 [SA245A-B4805]
P89LV51RB2	P89LV51RB2@PLCC44 [SA244]
P89LV51RB2@TQFP44 [SA245A-B4805]	P89LV51RB2FA@PLCC44 [SA244]
P89LV51RB2FBC@TQFP44 [SA245A-B4805]	
P89LV51RB2FN	P89LV51RC2
P89LV51RC2@PLCC44 [SA244]	P89LV51RC2@TQFP44 [SA245A-B4805]
P89LV51RC2FA@PLCC44 [SA244]	
P89LV51RC2FBC@TQFP44 [SA245A-B4805]	P89LV51RD2
P89LV51RC2FN	P89LV51RD2(new)@PLCC44 [SA244]
P89LV51RD2(new)	
P89LV51RD2(new)@TQFP44 [SA245A-B4805]	P89LV51RD2@TQFP44 [SA245A-B4805]
P89LV51RD2@PLCC44 [SA244]	P89LV51RD2BA@PLCC44 [SA244]
P89LV51RD2BA(new)@PLCC44 [SA244]	
P89LV51RD2BBC(new)@TQFP44 [SA245A-B4805]	P89LV51RD2BN(new)
P89LV51RD2BBC@TQFP44 [SA245A-B4805]	P89LV51RD2FA@PLCC44 [SA244]
P89LV51RD2BN	
P89LV51RD2FA(new)@PLCC44 [SA244]	P89LV51RD2FN(new)
P89LV51RD2FBC(new)@TQFP44 [SA245A-B4805]	P89V51RB2@PLCC44 [SA244]
P89LV51RD2FBC@TQFP44 [SA245A-B4805]	P89V51RB2FA@PLCC44 [SA244]
P89LV51RD2FN	
P89V51RB2	P89V51RC2
P89V51RB2@TQFP44 [SA245A-B4805]	P89V51RC2@TQFP44 [SA245A-B4805]
P89V51RB2FBC@TQFP44 [SA245A-B4805]	
P89V51RB2FN	P89V51RD2
P89V51RC2@PLCC44 [SA244]	P89V51RD2(new)@PLCC44 [SA244]
P89V51RC2FA@PLCC44 [SA244]	
P89V51RC2FBC@TQFP44 [SA245A-B4805]	P89V51RD2@TQFP44 [SA245A-B4805]
P89V51RC2FN	P89V51RD2BA@PLCC44 [SA244]
P89V51RD2(new)	
P89V51RD2(new)@TQFP44 [SA245A-B4805]	P89V51RD2BN(new)
P89V51RD2@PLCC44 [SA244]	P89V51RD2FA@PLCC44 [SA244]
P89V51RD2BA(new)@PLCC44 [SA244]	
P89V51RD2BBC(new)@TQFP44 [SA245A-B4805]	P89V51RD2FN(new)
P89V51RD2BBC@TQFP44 [SA245A-B4805]	P89V52X2@PLCC44 [SA244]
P89V51RD2BN	P89V54X2
P89V51RD2FA(new)@PLCC44 [SA244]	P89V54X2@TQFP44 [SA245A-B4805]
P89V51RD2FBC(new)@TQFP44 [SA245A-B4805]	P89V660@TQFP44 [SA245A-B4805]
P89V51RD2FBC@TQFP44 [SA245A-B4805]	P89V662@TQFP44 [SA245A-B4805]
P89V51RD2FN	P89V664@TQFP44 [SA245A-B4805]
P89V52X2	
P89V52X2@TQFP44 [SA245A-B4805]	
P89V54X2@PLCC44 [SA244]	
P89V660@PLCC44 [SA244]	
P89V662@PLCC44 [SA244]	
P89V664@PLCC44 [SA244]	

OKI

E (E) PROM/FRAM/NVRAM

MR27V401D	MR27V401D@PSOP32 [SA638]
MR27V401D@TSOP32 [SA620-B4807]	MR27V401E
MR27V401E@PSOP32 [SA638]	MR27V401E@TSOP32 [SA620-B4807]
MR27V402D	MR27V402D@PSOP40 [SA682]
MR27V402D@TSOP44 [SA638]	MR27V402E
MR27V402E@PSOP40 [SA682]	MR27V402E@TSOP44 [SA638]
MR27V802F@PSOP44 [SA638]	MR27V802F@TSOP44 [\$\$\$\$\$]
MR27V802F@TSOP48 [SB247-B4806]	MSM16812(08bit)
MSM16812(08bit)@S0IC8 [SA602A]	MSM271000
MSM271000@PLCC32 [SA015A1T]	MSM271000@TSOP32 [SA410T-B4001]
MSM271000AS	MSM271000AS@PLCC32 [SA015A1T]
MSM271000AS@TSOP32 [SA410T-B4001]	
MSM27128	MSM27128A
MSM27128AS	MSM27128AZB-RS
MSM2716	MSM27256
MSM27256AS	MSM27256ZB-RS
MSM2732	MSM2732A
MSM27512	MSM27512AS
MSM27512ZB-RS	MSM2764
MSM2764A	MSM2764AS
MSM2764AZB-RS	MSM2764RS
MSM27C1024	MSM27C1024AS
MSM27C128	MSM27C128AZB-RS
MSM27C256	MSM27C256A
MSM27C256H	MSM27C256HZB
MSM27C256ZB	MSM27C64AS
MSM27C802CZ	MSM27C802CZ@PSOP44 [SA638]
MSM27C802CZ@TSOP44 [\$\$\$\$\$]	MSM2816A(RS)
MSM28C16A	

ON Semiconductor

E (E) PROM/FRAM/NVRAM

CAT1320	CAT1320@S0IC8 [SA602A]
CAT1320@TDFN8	CAT1320@TSSOP8 [SA026-B3201]
CAT1321	CAT1321@S0IC8 [SA602A]
CAT1321@TDFN8	CAT1321@TSSOP8 [SA026-B3201]
CAT14002@S0IC8 [SA602A]	CAT14004@S0IC8 [SA602A]
CAT14008@S0IC8 [SA602A]	CAT14016@S0IC8 [SA602A]
CAT15002@S0IC8 [SA602A]	CAT15004@S0IC8 [SA602A]
CAT15008@S0IC8 [SA602A]	CAT15016@S0IC8 [SA602A]
CAT1640	CAT1640@S0IC8 [SA602A]
CAT1640@TDFN8	CAT1640@TSSOP8 [SA026-B3201]
CAT1641	CAT1641@S0IC8 [SA602A]
CAT1641@TDFN8	CAT1641@TSSOP8 [SA026-B3201]
CAT24AA01@S0IC8 [SA602A]	CAT24AA01@TSOT-23 [SA717]
CAT24AA02@S0IC8 [SA602A]	CAT24AA02@TSOT-23 [SA717]
CAT24AA04@S0IC8 [SA602A]	CAT24AA04@TSOT-23 [SA717]
CAT24AA08@S0IC8 [SA602A]	CAT24AA08@TSOT-23 [SA717]
CAT24AA16@S0IC8 [SA602A]	CAT24AA16@TSOT-23 [SA717]
CAT34TS02@TDFN8	CAT93C46R(08bit)
CAT93C46R(08bit)(V)@S0IC8 [SA602A]	
CAT93C46R(08bit)(VP2)@TDFN8 [SA724]	
CAT93C46R(08bit)(W)@S0IC8 [SA602A]	
CAT93C46R(08bit)(X)@S0IC8 [SA602A]	

CAT93C46R(08bit)(Y)@TSSOP8 [SA026-B3201]
CAT93C46R(16bit)(V)@S0IC8 [SA602A]
CAT93C46R(16bit)(VP2)@TDFN8 [SA724]
CAT93C46R(16bit)(W)@S0IC8 [SA602A]
CAT93C46R(16bit)(X)@S0IC8 [SA602A]
CAT93C46R(16bit)(Y)@TSSOP8 [SA026-B3201]
CAT93C46R-16

PHILIPS

E(E)PROM/FRAM/NVRAM

27C010	27C010@PLCC32 [SA015A1T]
27C010@TSOP32 [SA410T-B4001]	27C040
27C040@PLCC32 [SA015A1T]	27C040@TSOP32 [SA410T-B4001]
27C210	27C210@PLCC44 [SA244]
27C240	27C240@PLCC44 [SA244]
27C256	27C256@PLCC32
27C32	27C512
27C512@PLCC32	27C64
27C64@PLCC32 [SA015A1T]	27C64A
27C64A@PLCC32 [SA015A1T]	27C64AF
27C64AF@PLCC32 [SA015A1T]	27HC641
27HC641@PLCC28	27PC32
PCA24S08@S0IC8 [SA602A]	PCA24S08@TSSOP8 [SA026-B3201]
PCA8574(P)	PCA8574(T)@S0IC16 [SA404]
PCA8574(TS)@SSOP20 [SA026-B3201]	PCA8574A(P)
PCA8574A(T)@S0IC16 [SA404]	
PCA8574A(TS)@SSOP20 [SA026-B3201]	
PCA8581	PCA8581@S0IC8 [SA602A]
PCA8581C	PCA8581C@S0IC8 [SA602A]
PCA8582A	PCA8582A@S0IC8 [SA602A]
PCA8582B	PCA8582B@S0IC8 [SA602A]
PCA8582C	PCA8582C@S0IC8 [SA602A]
PCA8582D	PCA8582D@S0IC8 [SA602A]
PCA8582E	PCA8582E@S0IC8 [SA602A]
PCA9500@HQVFN16 [SA747]	PCA9500@S0IC16 [SA404]
PCA9500@TSSOP16 [SA026-B3201]	PCA9501@HQVFN20
PCA9501@S0IC20 [SA404]	PCA9501@TSSOP20 [SA026-B3201]
PCD8581	PCD8581@S0IC8 [SA602A]
PCD8581C	PCD8581C@S0IC8 [SA602A]
PCD8582A	PCD8582A@S0IC8 [SA602A]
PCD8582B	PCD8582B@S0IC8 [SA602A]
PCD8582C	PCD8582C@S0IC8 [SA602A]
PCD8582D	PCD8582D@S0IC8 [SA602A]
PCD8582E	PCD8582E@S0IC8 [SA602A]
PCF85102C	PCF85102C@S0IC8 [SA602A]
PCF85103C	PCF85103C@S0IC8 [SA602A]
PCF85116	PCF85116@S0IC8 [SA602A]
PCF8581	PCF8581@S0IC8 [SA602A]
PCF8581C	PCF8581C@S0IC8 [SA602A]
PCF8582A	PCF8582A@S0IC8 [SA602A]
PCF8582B	PCF8582B@S0IC8 [SA602A]
PCF8582C	PCF8582C@S0IC8 [SA602A]
PCF8582D	PCF8582D@S0IC8 [SA602A]
PCF8582E	PCF8582E@S0IC8 [SA602A]
PCF8594	PCF8594@S0IC8 [SA602A]
PCF8594C	PCF8594C@S0IC8 [SA602A]

PCF8594D
PCF8594E
PCF8598
PCF8598C
PCF8598D
PCF8598E

PCF8594D@S0IC8 [SA602A]
PCF8594E@S0IC8 [SA602A]
PCF8598@S0IC8 [SA605B]
PCF8598C@S0IC8 [SA605B]
PCF8598D@S0IC8 [SA605B]
PCF8598E@S0IC8 [SA605B]

MICROCONTROLLER

P83C660X2@PLCC44 [SA244]
P83C661X2@PLCC44 [SA244]
P87C51
P87C51@TQFP44 [SA675-B4805]
P87C51FA@PLCC44 [SA244]
P87C51FB
P87C51FB@TQFP44 [SA675-B4805]
P87C51FC@PLCC44 [SA244]
P87C51MA2@PLCC44 [SA244]
P87C51MC2@PLCC44 [SA244]
P87C51RA+@PLCC44 [SA244]
P87C51RA2
P87C51RA2@TQFP44 [SA675-B4805]
P87C51RB+@PLCC44 [SA244]
P87C51RB2
P87C51RB2@TQFP44 [SA675-B4805]
P87C51RC+@PLCC44 [SA244]
P87C51RC2
P87C51RC2@TQFP44 [SA675-B4805]
P87C51RD+@PLCC44 [SA244]
P87C51RD2
P87C51RD2@TQFP44 [SA675-B4805]
P87C51SB@PLCC44 [SA244]
P87C51SF
P87C51SF@TQFP44 [SA675-B4805]
P87C51UB@PLCC44 [SA244]
P87C51UF
P87C51UF@TQFP44 [SA675-B4805]
P87C51X2@PLCC44 [SA244]
P87C51X2@TTSOP38 [SA693]
P87C52@PLCC44 [SA244]
P87C524
P87C524@TQFP44 [SA245A-B4805]
P87C528@PLCC44 [SA244]
P87C52SB
P87C52SB@TQFP44 [SA675-B4805]
P87C52SF@PLCC44 [SA244]
P87C52UB
P87C52UB@TQFP44 [SA675-B4805]
P87C52UF@PLCC44 [SA244]
P87C52X2
P87C52X2@TQFP44 [SA245A-B4805]
P87C54
P87C54@TQFP44 [SA675-B4805]
P87C54SB@PLCC44 [SA244]
P87C54SF
P87C54SF@TQFP44 [SA675-B4805]
P87C54UB@PLCC44 [SA244]
P87C54UF
P87C54UF@TQFP44 [SA675-B4805]

P83C660X2@TQFP44 [SA245A-B4805]
P83C661X2@TQFP44 [SA245A-B4805]
P87C51@PLCC44 [SA244]
P87C51FA
P87C51FA@TQFP44 [SA675-B4805]
P87C51FB@PLCC44 [SA244]
P87C51FC
P87C51FC@TQFP44 [SA245A-B4805]
P87C51MB2@PLCC44 [SA244]
P87C51RA+
P87C51RA+@TQFP44 [SA245A-B4805]
P87C51RA2@PLCC44 [SA244]
P87C51RB+
P87C51RB+@TQFP44 [SA245A-B4805]
P87C51RB2@PLCC44 [SA244]
P87C51RC+
P87C51RC+@TQFP44 [SA245A-B4805]
P87C51RC2@PLCC44 [SA244]
P87C51RD+
P87C51RD+@TQFP44 [SA245A-B4805]
P87C51RD2@PLCC44 [SA244]
P87C51SB
P87C51SB@TQFP44 [SA675-B4805]
P87C51SF@PLCC44 [SA244]
P87C51UB
P87C51UB@TQFP44 [SA675-B4805]
P87C51UF@PLCC44 [SA244]
P87C51X2
P87C51X2@TQFP44 [SA245A-B4805]
P87C52
P87C52@TQFP44 [SA675-B4805]
P87C524@PLCC44 [SA244]
P87C528
P87C528@TQFP44 [SA245A-B4805]
P87C52SB@PLCC44 [SA244]
P87C52SF
P87C52SF@TQFP44 [SA675-B4805]
P87C52UB@PLCC44 [SA244]
P87C52UF
P87C52UF@TQFP44 [SA675-B4805]
P87C52X2@PLCC44 [SA244]
P87C52X2@TTSOP38 [SA693]
P87C54@PLCC44 [SA244]
P87C54SB
P87C54SB@TQFP44 [SA675-B4805]
P87C54SF@PLCC44 [SA244]
P87C54UB
P87C54UB@TQFP44 [SA675-B4805]
P87C54UF@PLCC44 [SA244]
P87C54X2

P87C54X2@PLCC44 [SA244]
P87C54X2@TTSOP38 [SA693]
P87C550@PLCC44 [SA244]
P87C575@PLCC44 [SA244]
P87C576
P87C576@TQFP44 [SA675-B4805]
P87C58@PLCC44 [SA244]
P87C58SB
P87C58SB@TQFP44 [SA675-B4805]
P87C58UB@PLCC44 [SA244]
P87C58X2
P87C58X2@TQFP44 [SA245A-B4805]
P87C591@PLCC44 [SA244]
P87C652
P87C652@TQFP44 [SA675-B4805]
P87C654@PLCC44 [SA244]
P87C660X2@PLCC44 [SA244]
P87C661X2@PLCC44 [SA244]
P87CL52X2
P87CL52X2@TQFP44 [SA245A-B4805]
P87CL54X2
P87CL54X2@TQFP44 [SA245A-B4805]
P87L51FA
P87L51FA@TQFP44 [SA675-B4805]
P87L51FB@PLCC44 [SA244]
P89C138
P89C138@TQFP44 [SA245A-B4805]
P89C238@PLCC44 [SA244]
P89C51B
P89C51B@TQFP44 [SA245A-B4805]
P89C51RA+@PLCC44 [SA244]
P89C51RA2B
P89C51RA2B@TQFP44 [SA245A-B4805]
P89C51RB+@PLCC44 [SA244]
P89C51RB2B
P89C51RB2B@TQFP44 [SA245A-B4805]
P89C51RB2H@PLCC44 [SA244]
P89C51RC+
P89C51RC+@TQFP44 [SA245A-B4805]
P89C51RC2B@PLCC44 [SA244]
P89C51RC2H
P89C51RC2H@TQFP44 [SA675-B4805]
P89C51RD+@PLCC44 [SA244]
P89C51RD2B
P89C51RD2B@TQFP44 [SA245A-B4805]
P89C51RD2H@PLCC44 [SA244]
P89C51UB
P89C51UB@TQFP44 [SA245A-B4805]
P89C51UF@PLCC44 [SA244]
P89C51X2
P89C51X2@TQFP44 [SA245A-B4805]
P89C51X2B@PLCC44 [SA244]
P89C51X2F
P89C51X2F@TQFP44 [SA245A-B4805]
P89C52@PLCC44 [SA244]
P89C52B
P89C52B@TQFP44 [SA245A-B4805]
P89C52UB@PLCC44 [SA244]
P89C52UF

P87C54X2@TQFP44 [SA245A-B4805]
P87C550
P87C575
P87C575@TQFP44 [SA675-B4805]
P87C576@PLCC44 [SA244]
P87C58
P87C58@TQFP44 [SA675-B4805]
P87C58SB@PLCC44 [SA244]
P87C58UB
P87C58UB@TQFP44 [SA675-B4805]
P87C58X2@PLCC44 [SA244]
P87C58X2@TTSOP38 [SA693]
P87C591@TQFP44 [SA675-B4805]
P87C652@PLCC44 [SA244]
P87C654
P87C654@TQFP44 [SA675-B4805]
P87C660X2@TQFP44 [SA245A-B4805]
P87C661X2@TQFP44 [SA245A-B4805]
P87CL52X2@PLCC44 [SA244]
P87CL52X2@TTSOP38 [SA693]
P87CL54X2@PLCC44 [SA244]
P87CL54X2@TTSOP38 [SA693]
P87L51FA@PLCC44 [SA244]
P87L51FB
P87L51FB@TQFP44 [SA675-B4805]
P89C138@PLCC44 [SA244]
P89C238
P89C238@TQFP44 [SA245A-B4805]
P89C51B@PLCC44 [SA244]
P89C51RA+
P89C51RA+@TQFP44 [SA245A-B4805]
P89C51RA2B@PLCC44 [SA244]
P89C51RB+
P89C51RB+@TQFP44 [SA245A-B4805]
P89C51RB2B@PLCC44 [SA244]
P89C51RB2H
P89C51RB2H@TQFP44 [SA675-B4805]
P89C51RC+@PLCC44 [SA244]
P89C51RC2B
P89C51RC2B@TQFP44 [SA245A-B4805]
P89C51RC2H@PLCC44 [SA244]
P89C51RD+
P89C51RD+@TQFP44 [SA245A-B4805]
P89C51RD2B@PLCC44 [SA244]
P89C51RD2H
P89C51RD2H@TQFP44 [SA675-B4805]
P89C51UB@PLCC44 [SA244]
P89C51UF
P89C51UF@TQFP44 [SA245A-B4805]
P89C51X2@PLCC44 [SA244]
P89C51X2B
P89C51X2B@TQFP44 [SA245A-B4805]
P89C51X2F@PLCC44 [SA244]
P89C52
P89C52@TQFP44 [SA245A-B4805]
P89C52B@PLCC44 [SA244]
P89C52UB
P89C52UB@TQFP44 [SA245A-B4805]
P89C52UF@PLCC44 [SA244]

P89C52UF@TQFP44 [SA245A-B4805]
P89C52X2@PLCC44 [SA244]
P89C52X2B
P89C52X2B@TQFP44 [SA245A-B4805]
P89C52X2F@PLCC44 [SA244]
P89C536@PLCC44 [SA244]
P89C54
P89C54@TQFP44 [SA245A-B4805]
P89C54B@PLCC44 [SA244]
P89C54UB
P89C54UB@TQFP44 [SA245A-B4805]
P89C54UF@PLCC44 [SA244]
P89C54X2
P89C54X2@TQFP44 [SA245A-B4805]
P89C54X2B@PLCC44 [SA244]
P89C54X2F
P89C54X2F@TQFP44 [SA245A-B4805]
P89C58@PLCC44 [SA244]
P89C58B
P89C58B@TQFP44 [SA245A-B4805]
P89C58UB@PLCC44 [SA244]
P89C58UF
P89C58UF@TQFP44 [SA245A-B4805]
P89C58X2@PLCC44 [SA244]
P89C58X2B
P89C58X2B@TQFP44 [SA245A-B4805]
P89C58X2F@PLCC44 [SA244]
P89C60X2
P89C60X2@TQFP44 [SA245A-B4805]
P89C61X2@PLCC44 [SA244]
P89C660
P89C660@TQFP44 [SA675-B4805]
P89C662@PLCC44 [SA244]
P89C664
P89C664@TQFP44 [SA675-B4805]
P89C668@PLCC44 [SA244]
P89C669
P89C669@PLCC44 [SA244]
P89C669X2@LQFP44 [SA245A-B4805]
P89C738
P89C738@TQFP44 [SA245A-B4805]
P89C838@PLCC44 [SA244]
P89CV51RB2@PLCC44 [SA244]
P89CV51RC2@PLCC44 [SA244]
P89CV51RD2@PLCC44 [SA244]
P89LPC9301(BDH)@TSSOP28 [SA643]
P89LV51RB2@PLCC44 [SA244]
P89LV51RB2FA@PLCC44 [SA244]
P89LV51RB2FBC@TQFP44 [SA245A-B4805]
P89LV51RB2FN
P89LV51RC2@PLCC44 [SA244]
P89LV51RC2FA@PLCC44 [SA244]
P89LV51RC2FBC@TQFP44 [SA245A-B4805]
P89LV51RC2FN
P89LV51RD2(new)
P89LV51RD2(new)@TQFP44 [SA245A-B4805]
P89LV51RD2@PLCC44 [SA244]
P89LV51RD2BA(new)@PLCC44 [SA244]
P89LV51RD2BBC(new)@TQFP44 [SA245A-B4805]

P89C52X2
P89C52X2@TQFP44 [SA245A-B4805]
P89C52X2B@PLCC44 [SA244]
P89C52X2F
P89C52X2F@TQFP44 [SA245A-B4805]
P89C538@PLCC44 [SA244]
P89C54@PLCC44 [SA244]
P89C54B
P89C54B@TQFP44 [SA245A-B4805]
P89C54UB@PLCC44 [SA244]
P89C54UF
P89C54UF@TQFP44 [SA245A-B4805]
P89C54X2@PLCC44 [SA244]
P89C54X2B
P89C54X2B@TQFP44 [SA245A-B4805]
P89C54X2F@PLCC44 [SA244]
P89C58
P89C58@TQFP44 [SA245A-B4805]
P89C58B@PLCC44 [SA244]
P89C58UB
P89C58UB@TQFP44 [SA245A-B4805]
P89C58UF@PLCC44 [SA244]
P89C58X2
P89C58X2@TQFP44 [SA245A-B4805]
P89C58X2B@PLCC44 [SA244]
P89C58X2F
P89C58X2F@TQFP44 [SA245A-B4805]
P89C60X2@PLCC44 [SA244]
P89C61X2
P89C61X2@TQFP44 [SA245A-B4805]
P89C660@PLCC44 [SA244]
P89C662
P89C662@TQFP44 [SA675-B4805]
P89C664@PLCC44 [SA244]
P89C668
P89C668@TQFP44 [SA675-B4805]
P89C669@LQFP44 [SA245A-B4805]
P89C669X2
P89C669X2@PLCC44 [SA244]
P89C738@PLCC44 [SA244]
P89C838
P89C838@TQFP44 [SA245A-B4805]
P89CV51RB2@TQFP44 [SA245A-B4805]
P89CV51RC2@TQFP44 [SA245A-B4805]
P89CV51RD2@TQFP44 [SA245A-B4805]
P89LV51RB2
P89LV51RB2@TQFP44 [SA245A-B4805]

P89LV51RC2
P89LV51RC2@TQFP44 [SA245A-B4805]

P89LV51RD2
P89LV51RD2(new)@PLCC44 [SA244]

P89LV51RD2@TQFP44 [SA245A-B4805]
P89LV51RD2BA@PLCC44 [SA244]

P89LV51RD2BBC@TQFP44 [SA245A-B4805]	
P89LV51RD2BN	P89LV51RD2BN(new)
P89LV51RD2FA(new)@PLCC44 [SA244]	P89LV51RD2FA@PLCC44 [SA244]
P89LV51RD2FBC(new)@TQFP44 [SA245A-B4805]	
P89LV51RD2FBC@TQFP44 [SA245A-B4805]	
P89LV51RD2FN	P89LV51RD2FN(new)
P89V51RB2	P89V51RB2@PLCC44 [SA244]
P89V51RB2@TQFP44 [SA245A-B4805]	P89V51RB2FA@PLCC44 [SA244]
P89V51RB2FBC@TQFP44 [SA245A-B4805]	
P89V51RB2FN	P89V51RC2
P89V51RC2@PLCC44 [SA244]	P89V51RC2@TQFP44 [SA245A-B4805]
P89V51RC2FA@PLCC44 [SA244]	
P89V51RC2FBC@TQFP44 [SA245A-B4805]	
P89V51RC2FN	P89V51RD2
P89V51RD2(new)	P89V51RD2(new)@PLCC44 [SA244]
P89V51RD2(new)@TQFP44 [SA245A-B4805]	
P89V51RD2@PLCC44 [SA244]	P89V51RD2@TQFP44 [SA245A-B4805]
P89V51RD2BA(new)@PLCC44 [SA244]	P89V51RD2BA@PLCC44 [SA244]
P89V51RD2BBC(new)@TQFP44 [SA245A-B4805]	
P89V51RD2BBC@TQFP44 [SA245A-B4805]	
P89V51RD2BN	P89V51RD2BN(new)
P89V51RD2FA(new)@PLCC44 [SA244]	P89V51RD2FA@PLCC44 [SA244]
P89V51RD2FBC(new)@TQFP44 [SA245A-B4805]	
P89V51RD2FBC@TQFP44 [SA245A-B4805]	
P89V51RD2FN	P89V51RD2FN(new)
P89V52X2	P89V52X2@PLCC44 [SA244]
P89V52X2@TQFP44 [SA245A-B4805]	P89V54X2
P89V54X2@PLCC44 [SA244]	P89V54X2@TQFP44 [SA245A-B4805]
P89V660@PLCC44 [SA244]	P89V660@TQFP44 [SA245A-B4805]
P89V662@PLCC44 [SA244]	P89V662@TQFP44 [SA245A-B4805]
P89V664@PLCC44 [SA244]	P89V664@TQFP44 [SA245A-B4805]

PJ

E(E) PROM/FRAM/NVRAM

PJ24C02	PJ24C02@S0IC8 [SA602A]
PJ24C02@TSSOP8	

PMC

E(E) PROM/FRAM/NVRAM

PM24C64	PM24C64@S0IC8 [SA602A]
PM24C64@TSOP8 [SA026-B3201]	PM25LD512(B)@S0IC8 [SA605B]
PM25LD512(Q)@WS0N8 [SA683]	PM25LD512(S)@S0IC8 [SA602A]
PM25LV010(B)@S0IC8 [SA605B]	PM25LV010(Q)@WS0N8 [SA683]
PM25LV010(S)@S0IC8 [SA602A]	PM25LV010A(B)@S0IC8 [SA605B]
PM25LV010A(Q)@WS0N8 [SA683]	PM25LV010A(S)@S0IC8 [SA602A]
PM25LV020(B)@S0IC8 [SA605B]	PM25LV020(Q)@WS0N8 [SA683]
PM25LV020(S)@S0IC8 [SA602A]	PM25LV040(B)@S0IC8 [SA605B]
PM25LV040(Q)@WS0N8 [SA683]	PM25LV040(S)@S0IC8 [SA602A]
PM25LV512(B)@S0IC8 [SA605B]	PM25LV512(Q)@WS0N8 [SA683]
PM25LV512(S)@S0IC8 [SA602A]	PM25LV512A(B)@S0IC8 [SA605B]
PM25LV512A(Q)@WS0N8 [SA683]	PM25LV512A(S)@S0IC8 [SA602A]
PM25LV512A@TSSOP8 [SA026-B3201]	PM29F002B
PM29F002B@PLCC32 [SA015A1T]	PM29F002T

PM29F002T@PLCC32 [SA015A1T]	PM29F004B
PM29F004B@PLCC32 [SA015A1T]	PM29F004T
PM29F004T@PLCC32 [SA015A1T]	PM29LV002B
PM29LV002B@PLCC32 [SA015A1T]	PM29LV002B@VSOP32 [SA620-B4807]
PM29LV002T	PM29LV002T@PLCC32 [SA015A1T]
PM29LV002T@VSOP32 [SA620-B4807]	PM29LV004B@PLCC32 [SA015A1T]
PM29LV004B@VSOP32 [SA620-B4807]	PM29LV004T@PLCC32 [SA015A1T]
PM29LV004T@VSOP32 [SA620-B4807]	PM29LV104RB@PLCC32 [SA015A1T]
PM29LV104RB@VSOP32 [SA620-B4807]	PM29LV104RT@PLCC32 [SA015A1T]
PM29LV104RT@VSOP32 [SA620-B4807]	PM37LV512
PM37LV512@PLCC32 [SA015A1T]	PM37LV512@VSOP32 [SA620-B4807]
PM39F010	PM39F010@PLCC32 [SA015A1T]
PM39F010@VSOP32 [SA620-B4807]	PM39F020
PM39F020@PLCC32 [SA015A1T]	PM39F020@VSOP32 [SA620-B4807]
PM39F040	PM39F040@PLCC32 [SA015A1T]
PM39F040@VSOP32 [SA620-B4807]	PM39LV010@PLCC32 [SA015A1T]
PM39LV010@VSOP32 [SA620-B4807]	PM39LV010R@PLCC32 [SA015A1T]
PM39LV010R@VSOP32 [SA620-B4807]	PM39LV020@PLCC32 [SA015A1T]
PM39LV020@VSOP32 [SA620-B4807]	PM39LV040@PLCC32 [SA015A1T]
PM39LV040@VSOP32 [SA620-B4807]	PM39LV512@PLCC32 [SA015A1T]
PM39LV512@VSOP32 [SA620-B4807]	PM39LV512R@PLCC32 [SA015A1T]
PM39LV512R@VSOP32 [SA620-B4807]	PM49FL002T@PLCC32 [SA015A1T]
PM49FL002T@VSOP32 [SA620-B4807]	PM49FL004T@PLCC32 [SA015A1T]
PM49FL004T@VSOP32 [SA620-B4807]	PM49FL008T@PLCC32 [SA015A1T]
PM49FL008T@VSOP32 [SA620-B4807]	PM49LP002T@PLCC32 [SA015A1T]
PM49LP002T@VSOP32 [SA620-B4807]	

PSS

E (E) PROM/FRAM/NVRAM

PS24C256	PS24C256@S0IC8 [SA602A]
----------	-------------------------

PTC

E (E) PROM/FRAM/NVRAM

PT28C020	PT28C020@PLCC32 [SA015A1T]
PT28C040	PT28C040@PLCC32 [SA015A1T]
PT29C020	PT29C020@PLCC32 [SA015A1T]
PT29C040	PT29C040@PLCC32 [SA015A1T]

QISDA-CUSTOMER

E (E) PROM/FRAM/NVRAM

AT24C32C	BR24S32
RM24C32C	

Quick Pulse

E (E) PROM/FRAM/NVRAM

27010	27011
27040	27128A

27210
27512

27256
2764A

RAMTRON

E(E)PROM/FRAM/NVRAM

FM1208
FM1608
FM1808
FM18L08
FM20L08@TSOP32 [\$\$\$\$\$]
FM24164@S0IC8 [SA602A]
FM24C04(S)@SOP8 [SA602A]
FM24C04A(S)@SOP8 [SA602A]
FM24C08A@SOP8 [SA602A]
FM24C16(S)@SOP8 [SA602A]
FM24C16A(S)@SOP8 [SA602A]
FM24C512@S0IC8
FM24C64@S0IC8 [SA602A]
FM24CL04@S0IC8 [SA602A]
FM24CL16@S0IC8 [SA602A]
FM24V02@S0IC8 [SA602A]
FM25040
FM25160
FM25640
FM25C160
FM25CL04@S0IC8 [SA602A]
FM25CL64@S0IC8 [SA602A]
FM25L16@S0IC8 [SA602A]
FM25L256@S0IC8 [SA602A]
FM25L512
FM25W256@S0IC8 [SA602A]
FM28V020@TSOP32 [\$\$\$\$\$]
FM28V200@TSOP32 [\$\$\$\$\$]
FM3104@S0IC14 [SA602]
FM31256@S0IC14 [SA602]
FM3808

FM1208@S0IC24 [SA404]
FM1608@S0IC28 [SA404]
FM1808@S0IC28 [SA404]
FM18L08@S0IC28 [SA404]
FM24164
FM24C04(P)
FM24C04A(P)
FM24C08A
FM24C16(P)
FM24C16A(P)
FM24C256@S0IC8 [SA602A]
FM24C64
FM24CL04
FM24CL16
FM24CL64@S0IC8 [SA602A]
FM24VN02@S0IC8 [SA602A]
FM25040@S0IC8 [SA602A]
FM25160@S0IC8 [SA602A]
FM25640@S0IC8 [SA602]
FM25C160@S0IC8 [SA602A]
FM25CL64
FM25L16
FM25L256
FM25L256@TDFN8
FM25L512@S0IC8 [SA602A]
FM28V020@S0IC28 [SA404]
FM28V100@TSOP32 [\$\$\$\$\$]
FM30C256@S0IC20 [SA404]
FM3116@S0IC14 [SA602]
FM3164@S0IC14 [SA602]
FM3808@TSOP32 [SA620-B4807]

MICROCONTROLLER

VMX51C900
VMX51C900@TQFP44 [SA245A-B4805]
VRS1000@PLCC44 [SA244]
VRS1100
VRS1100@TQFP44 [SA245A-B4805]
VRS51C1000@PLCC44 [SA244]
VRS51C1100
VRS51C1100@TQFP44 [SA245A-B4805]
VRS51C540@PLCC44 [SA244]
VRS51C550
VRS51C550@TQFP44 [SA245A-B4805]
VRS51C560@PLCC44 [SA244]
VRS51C570
VRS51C570@TQFP44 [SA245A-B4805]
VRS51C580@PLCC44 [SA244]
VRS51C700

VMX51C900@PLCC44 [SA244]
VRS1000
VRS1000@TQFP44 [SA245A-B4805]
VRS1100@PLCC44 [SA244]
VRS51C1000
VRS51C1000@TQFP44 [SA245A-B4805]
VRS51C1100@PLCC44 [SA244]
VRS51C540
VRS51C540@TQFP44 [SA245A-B4805]
VRS51C550@PLCC44 [SA244]
VRS51C560
VRS51C560@TQFP44 [SA245A-B4805]
VRS51C570@PLCC44 [SA244]
VRS51C580
VRS51C580@TQFP44 [SA245A-B4805]
VRS51C700@PLCC44 [SA244]

VRS51C700@TQFP44 [SA245A-B4805]
VRS51L1050@PLCC44 [SA244]
VRS51L540
VRS51L540@TQFP44 [SA245A-B4805]
VRS51L550@PLCC44 [SA244]
VRS51L560
VRS51L560@TQFP44 [SA245A-B4805]
VRS51L570@PLCC44 [SA244]
VRS51L580
VRS51L580@TQFP44 [SA245A-B4805]
VRS51X540@PLCC44 [SA244]
VRS51X550
VRS51X550@TQFP44 [SA245A-B4805]
VRS51X560@PLCC44 [SA244]
VRS51X570
VRS51X570@TQFP44 [SA245A-B4805]
VRS51X580@PLCC44 [SA244]
VRS540
VRS540@TQFP44 [SA245A-B4805]
VRS550@PLCC44 [SA244]
VRS560
VRS560@TQFP44 [SA245A-B4805]
VRS570@PLCC44 [SA244]
VRS580
VRS580@TQFP44 [SA245A-B4805]
VRS700@PLCC44 [SA244]
VRS900
VRS900@TQFP44 [SA245A-B4805]

VRS51L1050
VRS51L1050@TQFP44 [SA245A-B4805]
VRS51L540@PLCC44 [SA244]
VRS51L550
VRS51L550@TQFP44 [SA245A-B4805]
VRS51L560@PLCC44 [SA244]
VRS51L570
VRS51L570@TQFP44 [SA245A-B4805]
VRS51L580@PLCC44 [SA244]
VRS51X540
VRS51X540@TQFP44 [SA245A-B4805]
VRS51X550@PLCC44 [SA244]
VRS51X560
VRS51X560@TQFP44 [SA245A-B4805]
VRS51X570@PLCC44 [SA244]
VRS51X580
VRS51X580@TQFP44 [SA245A-B4805]
VRS540@PLCC44 [SA244]
VRS550
VRS550@TQFP44 [SA245A-B4805]
VRS560@PLCC44 [SA244]
VRS570
VRS570@TQFP44 [SA245A-B4805]
VRS580@PLCC44 [SA244]
VRS700
VRS700@TQFP44 [SA245A-B4805]
VRS900@PLCC44 [SA244]

RATO

E(E) PROM/FRAM/NVRAM

RT24A02
RT24A02@TSSOP8 [SA026-B3201]
RT24A04@S0IC8 [SA602A]
RT24A08
RT24A08@TSSOP8 [SA026-B3201]
RT24A16@S0IC8 [SA602A]
RT93C46B(16bit)
RT93C46B(16bit)@TSSOP8 [SA026-B3201]
RT93LC46(08bit)
RT93LC46(08bit)@TSSOP8 [SA026-B3201]
RT93LC46(16bit)
RT93LC46(16bit)@TSSOP8 [SA026-B3201]
RT24A02@S0IC8 [SA602A]
RT24A04
RT24A04@TSSOP8 [SA026-B3201]
RT24A08@S0IC8 [SA602A]
RT24A16
RT24A16@TSSOP8 [SA026-B3201]
RT93C46B(16bit)@S0IC8 [SA602A]
RT93LC46(08bit)@S0IC8 [SA602A]
RT93LC46(16bit)@S0IC8 [SA602A]

RAYDIUM

E(E) PROM/FRAM/NVRAM

RM24C02@SOP8 [SA602A]
RM24C08@SOP8 [SA602A]
RM24C16@SOP8 [SA602A]
RM24C64@SOP8 [SA602A]
RM24C04@SOP8 [SA602A]
RM24C128@SOP8 [SA602A]
RM24C32@SOP8 [SA602A]

REALTEK

MICROCONTROLLER

RTD2120L@LQFP48 [SA248-B4804]

RTD2120L@PLCC44 [SA244]

RENESAS

E(E)PROM/FRAM/NVRAM

HN58C256A(FP)@SOP28 [SA404]
HN58C256A(T)@TSOP28 [SA430T-B4003]
HN58C257A(T)@TSOP32 [SA605B]
HN58V24256@S0IC8 [SA602A]
HN58V24512
HN58W241000
HN58X2402
HN58X2402@TSSOP8 [SA026-B3201]
HN58X2404@S0IC8 [SA602A]
HN58X2408
HN58X2408@TSSOP8 [SA026-B3201]
HN58X24128@S0IC8 [SA602A]
HN58X2416@S0IC8 [SA602A]
HN58X24256
HN58X2432
HN58X2432@TSSOP8 [SA026-B3201]
HN58X24512@S0IC8 [SA602A]
HN58X2464@S0IC8 [SA602A]
HN58X2502@S0IC8 [SA602A]
HN58X2504@S0IC8 [SA602A]
HN58X2508@S0IC8 [SA602A]
HN58X25128@S0IC8 [SA602A]
HN58X2516@S0IC8 [SA602A]
HN58X25256@S0IC8 [SA602A]
HN58X2532@S0IC8 [SA602A]
HN58X2564@S0IC8 [SA602A]
M5L2732
M5M29KB331(AVP)@TSOP48 [SB247-B4806]
M5M29KB641(AVP)@TSOP48 [SB247-B4806]
M5M29KE131BV@TSOP48 [SB247-B4806]
M5M29KT331(AVP)@TSOP48 [SB247-B4806]
M5M29KT641(AVP)@TSOP48 [SB247-B4806]
R1EX24002A@SOP8 [SA602A]
R1EX24004A@SOP8 [SA602A]
R1EX24008A@SOP8 [SA602A]
R1EX24016A@SOP8 [SA602A]
R1EX24032A@SOP8 [SA602A]
R1EX24064A@SOP8 [SA602A]
R1EX24128A@SOP8 [SA602A]
R1EX24256A@SOP8 [SA602A]
R1EX24512A@SOP8 [SA602A]
R1EX25002A@S0IC8 [SA602A]
R1EX25004A@S0IC8 [SA602A]
R1EX25008A@S0IC8 [SA602A]
R1EX25016A@S0IC8 [SA602A]
R1EX25032A@S0IC8 [SA602A]
R1EX25064A@S0IC8 [SA602A]

HN58C256A(P)
HN58V24256
HN58V24256@TSSOP14 [SA026-B3201]
HN58V24512@S0IC8 [SA602A]
HN58W241000@S0IC8 [SA602A]
HN58X2402@S0IC8 [SA602A]
HN58X2404
HN58X2404@TSSOP8 [SA026-B3201]
HN58X2408@S0IC8 [SA602A]
HN58X24128
HN58X2416
HN58X2416@TSSOP8 [SA026-B3201]
HN58X24256@S0IC8 [SA602A]
HN58X2432@S0IC8 [SA602A]
HN58X24512
HN58X2464
HN58X2464@TSSOP8 [SA026-B3201]
HN58X2502@TSSOP8 [SA026-B3201]
HN58X2504@TSSOP8 [SA026-B3201]
HN58X2508@TSSOP8 [SA026-B3201]
HN58X25128@TSSOP14 [SA026-B3201]
HN58X2516@TSSOP8 [SA026-B3201]
HN58X25256@TSSOP14 [SA026-B3201]
HN58X2532@TSSOP8 [SA026-B3201]
HN58X2564@TSSOP8 [SA026-B3201]
M5L2732A
R1EX24002A@TSSOP8 [SA026-B3201]
R1EX24004A@TSSOP8 [SA026-B3201]
R1EX24008A@TSSOP8 [SA026-B3201]
R1EX24016A@TSSOP8 [SA026-B3201]
R1EX24032A@TSSOP8 [SA026-B3201]
R1EX24064A@TSSOP8 [SA026-B3201]
R1EX24128A@TSSOP8 [SA026-B3201]
R1EX24256A@TSSOP8 [SA026-B3201]
R1EX24512A@TSSOP8 [SA026-B3201]
R1EX25002A@TSSOP8 [SA026-B3201]
R1EX25004A@TSSOP8 [SA026-B3201]
R1EX25008A@TSSOP8 [SA026-B3201]
R1EX25016A@TSSOP8 [SA026-B3201]
R1EX25032A@TSSOP8 [SA026-B3201]
R1EX25064A@TSSOP8 [SA026-B3201]

RICOH

E (E) PROM/FRAM/NVRAM

RD27C256	RD27C32
RD27C64	

ROCKWELL

E (E) PROM/FRAM/NVRAM

R2764	R2764C
R2764P	R27C64
R2816	

ROHM

E (E) PROM/FRAM/NVRAM

BR24A01A(F) [\$\$\$\$\$]	BR24A01A(FJ) [\$\$\$\$\$]
BR24A02(F) [\$\$\$\$\$]	BR24A02(FJ) [\$\$\$\$\$]
BR24A04(F) [\$\$\$\$\$]	BR24A04(FJ) [\$\$\$\$\$]
BR24A08(F) [\$\$\$\$\$]	BR24A08(FJ) [\$\$\$\$\$]
BR24A16(F) [\$\$\$\$\$]	BR24A16(FJ) [\$\$\$\$\$]
BR24A32(F) [SA602A]	BR24A32(FJ) [SA602A]
BR24A64(F) [SA602A]	BR24A64(FJ) [SA602A]
BR24C01@SOP8 [\$\$\$\$\$]	BR24C01@TSSOP8 [SA026-B3201]
BR24C01@TSSOP8(3*3mm) [SA666]	BR24C01A
BR24C01A(F) [\$\$\$\$\$]	BR24C01A(FJ) [\$\$\$\$\$]
BR24C01A(FV) [SA026-B3201]	BR24C02
BR24C02(F) [\$\$\$\$\$]	BR24C02(FJ) [\$\$\$\$\$]
BR24C02(FV) [SA026-B3201]	BR24C02@SOP8 [\$\$\$\$\$]
BR24C02@TSSOP8 [SA026-B3201]	BR24C02@TSSOP8(3*3mm) [SA666]
BR24C04	BR24C04(F) [\$\$\$\$\$]
BR24C04(FJ) [\$\$\$\$\$]	BR24C04(FV) [SA026-B3201]
BR24C04@SOP8 [\$\$\$\$\$]	BR24C04@TSSOP8 [SA026-B3201]
BR24C04@TSSOP8(3*3mm) [SA666]	BR24C08
BR24C08(F) [\$\$\$\$\$]	BR24C08(FJ) [\$\$\$\$\$]
BR24C08(FV) [SA026-B3201]	BR24C08@SOP8 [\$\$\$\$\$]
BR24C08@TSSOP8 [SA026-B3201]	BR24C08@TSSOP8(3*3mm) [SA666]
BR24C16	BR24C16(F) [\$\$\$\$\$]
BR24C16(FJ) [\$\$\$\$\$]	BR24C16(FV) [SA026-B3201]
BR24C21	BR24C21(F) [\$\$\$\$\$]
BR24C21(FJ) [\$\$\$\$\$]	BR24C21(FV) [SA026-B3201]
BR24C32	BR24C32(F) [SA602A]
BR24C64	BR24C64(F) [SA602A]
BR24E16	BR24E16(F) [\$\$\$\$\$]
BR24E16(FJ) [\$\$\$\$\$]	BR24E16(FV) [SA026-B3201]
BR24G32	BR24G32(F) [SA602A]
BR24G32(FJ) [SA602A]	BR24G32(FV) [SA026-B3201]
BR24G32(FVT) [SA026-B3201]	BR24L01A
BR24L01A(F) [\$\$\$\$\$]	BR24L01A(FJ) [\$\$\$\$\$]
BR24L01A(FV) [SA026-B3201]	BR24L01A(FVM) [SA666]
BR24L02	BR24L02(F) [\$\$\$\$\$]
BR24L02(FJ) [\$\$\$\$\$]	BR24L02(FV) [SA026-B3201]
BR24L02(FVM) [SA666]	BR24L04
BR24L04(F) [\$\$\$\$\$]	BR24L04(FJ) [\$\$\$\$\$]

BR24L04(FV) [SA026-B3201]
BR24L08
BR24L08(FJ) [\$\$\$\$\$]
BR24L08(FVM) [SA666]
BR24L16(F) [\$\$\$\$\$]
BR24L16(FV) [SA026-B3201]
BR24L32
BR24L32(FJ) [SA602A]
BR24L64
BR24L64(FJ) [SA602A]
BR24S08(F) [\$\$\$\$\$]
BR24S08(FV) [SA026-B3201]
BR24S08(FVM) [SA666]
BR24S128
BR24S128(FJ) [SA602A]
BR24S16
BR24S16(FJ) [\$\$\$\$\$]
BR24S16(FVM) [SA666]
BR24S256(F) [SA602A]
BR24S256(FV) [SA026-B3201]
BR24S32(F) [SA602A]
BR24S32(FV) [SA026-B3201]
BR24S64(F) [SA602A]
BR24S64(FV) [SA026-B3201]
BR25H010(FJ) [SA602A]
BR25H020(FJ) [SA602A]
BR25H040(FJ) [SA602A]
BR25H080(FJ) [SA602A]
BR25H160(F) [SA602A]
BR25H160(FVT) [SA026-B3201]
BR25H320(FJ) [SA602A]
BR25L010
BR25L010(FJ) [SA602A]
BR25L010(FVM) [SA666]
BR25L020(F) [SA602A]
BR25L020(FV) [SA026-B3201]
BR25L040
BR25L040(FJ) [SA602A]
BR25L040(FVM) [SA666]
BR25L080(F) [SA602A]
BR25L080(FV) [SA026-B3201]
BR25L160(F) [SA602A]
BR25L160(FV) [SA026-B3201]
BR25L320(F) [SA602A]
BR25L320(FV) [SA026-B3201]
BR25L640(F) [SA602A]
BR25L640(FV) [SA026-B3201]
BR9010
BR9010(FV) [SA026-B3201]
BR9010(RFVM) [SA666]
BR9016(F) [SA602A]
BR9016A(F) [SA602A]
BR9016A(RFVM) [SA666]
BR9020(F) [SA602A]
BR9020(RFV) [SA026-B3201]
BR9040
BR9040(FV) [SA026-B3201]
BR9040(RFVM) [SA666]
BR9080(F) [SA602A]

BR24L04(FVM) [SA666]
BR24L08(F) [\$\$\$\$\$]
BR24L08(FV) [SA026-B3201]
BR24L16
BR24L16(FJ) [\$\$\$\$\$]
BR24L16(FVM) [SA666]
BR24L32(F) [SA602A]
BR24L32(FV) [SA026-B3201]
BR24L64(F) [SA602A]
BR24L64(FV) [SA026-B3201]
BR24S08(FJ) [\$\$\$\$\$]
BR24S08(FVJ) [SA026-B3201]
BR24S08(FVT) [SA026-B3201]
BR24S128(F) [SA602A]
BR24S128(FV) [SA026-B3201]
BR24S16(F) [\$\$\$\$\$]
BR24S16(FV) [SA026-B3201]
BR24S256
BR24S256(FJ) [SA602A]
BR24S32
BR24S32(FJ) [SA602A]
BR24S64
BR24S64(FJ) [SA602A]
BR25H010(F) [SA602A]
BR25H020(F) [SA602A]
BR25H040(F) [SA602A]
BR25H080(F) [SA602A]
BR25H080(FVT) [SA026-B3201]
BR25H160(FJ) [SA602A]
BR25H320(F) [SA602A]
BR25H320(FVT) [SA026-B3201]
BR25L010(F) [SA602A]
BR25L010(FV) [SA026-B3201]
BR25L020
BR25L020(FJ) [SA602A]
BR25L020(FVM) [SA666]
BR25L040(F) [SA602A]
BR25L040(FV) [SA026-B3201]
BR25L080
BR25L080(FJ) [SA602A]
BR25L160
BR25L160(FJ) [SA602A]
BR25L320
BR25L320(FJ) [SA602A]
BR25L640
BR25L640(FJ) [SA602A]
BR34C02A [SA026-B3201]
BR9010(F) [SA602A]
BR9010(RFV) [SA026-B3201]
BR9016
BR9016(RFV) [SA026-B3201]
BR9016A(RFV) [SA026-B3201]
BR9020
BR9020(FV) [SA026-B3201]
BR9020(RFVM) [SA666]
BR9040(F) [SA602A]
BR9040(RFV) [SA026-B3201]
BR9080
BR9080(RFV) [SA026-B3201]

BR9080A
BR9080A(FV) [SA026-B3201]
BR9080A(RFVM) [SA666]
BR93A46(FJ) [SA602A]
BR93A46(RFJ) [SA602A]
BR93A56(FJ) [SA602A]
BR93A56(RFJ) [SA602A]
BR93A66(FJ) [SA602A]
BR93A66(RFJ) [SA602A]
BR93A76(FJ) [SA602A]
BR93A76(RFJ) [SA602A]
BR93A86(FJ) [SA602A]
BR93A86(RFJ) [SA602A]
BR93C46(F) [SA602A]
BR93C46(FV) [SA026-B3201]
BR93C46(RFJ) [SA602A]
BR93C56(F) [SA602A]
BR93C56(FV) [SA026-B3201]
BR93C56(RFJ) [SA602A]
BR93C66(F) [SA602A]
BR93C66(FV) [SA026-B3201]
BR93C66(RFJ) [SA602A]
BR93H46(RFJ) [SA605B]
BR93H56(RFJ) [SA605B]
BR93H66(RFJ) [SA605B]
BR93H76(RFJ) [SA605B]
BR93H86(RFJ) [SA605B]
BR93L46(F) [SA602A]
BR93L46(FV) [SA026-B3201]
BR93L46(RFJ) [SA602A]
BR93L56(F) [SA602A]
BR93L56(FV) [SA026-B3201]
BR93L56(RFJ) [SA602A]
BR93L66(F) [SA602A]
BR93L66(FV) [SA026-B3201]
BR93L66(RFJ) [SA602A]
BR93L76(FJ) [SA602A]
BR93L76(RFJ) [SA602A]
BR93L76(RFVJ) [SA666]
BR93L76(RFVT) [SA026-B3201]
BR93L86(FJ) [SA602A]
BR93L86(RFJ) [SA602A]
BR93L86(RFVJ) [SA666]
BR93L86(RFVT) [SA026-B3201]
BR93LC46(F) [SA602A]
BR93LC46(FV) [SA026-B3201]
BR93LC46(RFJ) [SA602A]
BR93LC56(F) [SA602A]
BR93LC56(FV) [SA026-B3201]
BR93LC56(RFJ) [SA602A]
BR93LC66(F) [SA602A]
BR93LC66(FV) [SA026-B3201]
BR93LC66(RFJ) [SA602A]
BR93LL46(FV) [SA026-B3201]

BR9080A(F) [SA602A]
BR9080A(RFV) [SA026-B3201]
BR93A46(F) [SA602A]
BR93A46(RF) [SA602A]
BR93A56(F) [SA602A]
BR93A56(RF) [SA602A]
BR93A66(F) [SA602A]
BR93A66(RF) [SA602A]
BR93A76(F) [SA602A]
BR93A76(RF) [SA602A]
BR93A86(F) [SA602A]
BR93A86(RF) [SA602A]
BR93C46
BR93C46(FJ) [SA602A]
BR93C46(RF) [SA602A]
BR93C56
BR93C56(FJ) [SA602A]
BR93C56(RF) [SA602A]
BR93C66
BR93C66(FJ) [SA602A]
BR93C66(RF) [SA602A]
BR93H46(RF) [SA605B]
BR93H56(RF) [SA605B]
BR93H66(RF) [SA605B]
BR93H76(RF) [SA605B]
BR93H86(RF) [SA605B]
BR93L46
BR93L46(FJ) [SA602A]
BR93L46(RF) [SA602A]
BR93L56
BR93L56(FJ) [SA602A]
BR93L56(RF) [SA602A]
BR93L66
BR93L66(FJ) [SA602A]
BR93L66(RF) [SA602A]
BR93L76(F) [SA602A]
BR93L76(RF) [SA602A]
BR93L76(RFV) [SA026-B3201]
BR93L76(RFVM) [SA666]
BR93L86(F) [SA602A]
BR93L86(RF) [SA602A]
BR93L86(RFV) [SA026-B3201]
BR93L86(RFVM) [SA666]
BR93LC46
BR93LC46(FJ) [SA602A]
BR93LC46(RF) [SA602A]
BR93LC56
BR93LC56(FJ) [SA602A]
BR93LC56(RF) [SA602A]
BR93LC66
BR93LC66(FJ) [SA602A]
BR93LC66(RF) [SA602A]
BR93LL46(F) [SA602A]

SAIFUN

E(E) PROM/FRAM/NVRAM

SA24C1024
SA24C512
SA24C512@TSSOP8 [SA026-B3201]
SA25C020@MLF8 [SA683]
SA25C040
SA25C040@S0IC8 [SA602A]
SA25C080@MLF8 [SA683]
SA25C1024(H)
SA25C1024(H)@S0IC8 [SA602A]
SA25C1024(L)@CSP8 [SA683]
SA25C512(H)
SA25C512(H)@S0IC8 [SA602A]
SA25C512(L)@CSP8 [SA683]
SA25F005
SA25F005@S0IC8 [SA602A]
SA25F010@MLF8 [SA683]
SA25F020
SA25F020@S0IC8 [SA602A]
SA25F040@MLF8 [SA683]
SA25F080
SA25F080@S0IC8 [SA602A]
SA25F160@MLF8 [SA683]

SA24C1024@S0IC8 [SA602A]
SA24C512@S0IC8 [SA602A]
SA25C020
SA25C020@S0IC8 [SA602A]
SA25C040@MLF8 [SA683]
SA25C080
SA25C080@S0IC8 [SA602A]
SA25C1024(H)@CSP8 [SA683]
SA25C1024(L)
SA25C1024(L)@S0IC8 [SA602A]
SA25C512(H)@CSP8 [SA683]
SA25C512(L)
SA25C512(L)@S0IC8 [SA602A]
SA25F005@MLF8 [SA683]
SA25F010
SA25F010@S0IC8 [SA602A]
SA25F020@MLF8 [SA683]
SA25F040
SA25F040@S0IC8 [SA602A]
SA25F080@MLF8 [SA683]
SA25F160
SA25F160@S0IC16 [SA602]

SAMSUNG

E(E) PROM/FRAM/NVRAM

K8D1616UBA@TSOP48 [SB247-B4806]
K8D1716UBA@TSOP48 [SB247-B4806]
K8D1716UTA@TSOP48 [SB247-B4806]
K8D3216UBB@TSOP48 [SB247-B4806]
K8D3216UBM@TSOP48 [SB247-B4806]
K8D3216UTC@TSOP48 [SB247-B4806]
K8D3216UTM@TSOP48(new) [SB247-B4806]
K8D3316UBC@TSOP48 [SB247-B4806]
K8D3316UTC@TSOP48 [SB247-B4806]
K8D6316UBM@TSOP48 [SB247-B4806]
K8P3215UQB@TSOP48 [SB247-B4806]
KM2816A
KM2817A
KM2864A
KM2865A
KM28C16
KM28C16I
KM28C17
KM28C17I
KM28C256
KM28C256I
KM28C64
KM28C64A
KM28C64B
KM28C64I
KM28C65
KM28C65A
KM28C65I
KM93C06(08bit)
KM93C06(G)(08bit)@S0IC8 [SA602A]

K8D1616UTA@TSOP48 [SB247-B4806]
K8D1716UBC@TSOP48 [SB247-B4806]
K8D1716UTC@TSOP48 [SB247-B4806]
K8D3216UBC@TSOP48 [SB247-B4806]
K8D3216UTB@TSOP48 [SB247-B4806]
K8D3216UTM@TSOP48 [SB247-B4806]
K8D3316UBM@TSOP48 [SB247-B4806]
K8D3316UTM@TSOP48 [SB247-B4806]
K8D6316UTM@TSOP48 [SB247-B4806]
K8P6415UQB@TSOP48 [SB247-B4806]
KM2816AI
KM2817AI
KM2864AH
KM2865AH
KM28C16@PLCC32 [SA015A1T]
KM28C16I@PLCC32 [SA015A1T]
KM28C17@PLCC32 [SA015A1T]
KM28C17I@PLCC32 [SA015A1T]
KM28C256@PLCC32 [SA015A1T]
KM28C256I@PLCC32 [SA015A1T]
KM28C64@PLCC32 [SA015A1T]
KM28C64A@PLCC32 [SA015A1T]
KM28C64B@PLCC32 [SA015A1T]
KM28C64I@PLCC32 [SA015A1T]
KM28C65@PLCC32 [SA015A1T]
KM28C65A@PLCC32 [SA015A1T]
KM28C65I@PLCC32 [SA015A1T]
KM93C06(16bit)
KM93C06(G)(16bit)@S0IC8 [SA602A]

KM93C06(GD)(08bit)@S0IC8 [SA602A]
 KM93C06(GD)(16bit)@S0IC8 [SA602A]
 KM93C07(08bit)
 KM93C07(G)(08bit)@S0IC8 [SA602A]
 KM93C07(GD)(08bit)@S0IC8 [SA602A]
 KM93C07(GD)(16bit)@S0IC8 [SA602A]
 KM93C46V
 KM93C46V(GD)@S0IC8 [SA602A]
 KM93C47V(G)@S0IC8 [SA602A]
 KM93C56V
 KM93C56V(GD)@S0IC8 [SA602A]
 KM93C57V(G)@S0IC8 [SA602A]
 KM93C66V
 KM93C66V(GD)@S0IC8 [SA602A]
 KM93C67V(G)@S0IC8 [SA602A]
 KS24C010
 KS24C010@TSSOP8 [SA026-B3201]
 KS24C011@S0IC8 [SA602A]
 KS24C020
 KS24C020@TSSOP8 [SA026-B3201]
 KS24C021@S0IC8 [SA602A]
 KS24C040
 KS24C040@TSSOP8 [SA026-B3201]
 KS24C041@S0IC8 [SA602A]
 KS24C080
 KS24C080@TSSOP8 [SA026-B3201]
 KS24C081@S0IC8 [SA602A]
 S524A40X10
 S524A40X10@TSSOP8 [SA026-B3201]
 S524A40X11@SOP8 [SA602A]
 S524A40X20
 S524A40X20@TSSOP8 [SA026-B3201]
 S524A40X21@SOP8 [SA602A]
 S524A40X40
 S524A40X40@TSSOP8 [SA026-B3201]
 S524A40X41@SOP8 [SA602A]
 S524A60X51
 S524A60X51@TSSOP8 [SA026-B3201]
 S524A60X81@SOP8 [SA602A]
 S524AB0X91
 S524AB0X91@TSSOP8 [SA026-B3201]
 S524AB0XB1@SOP8 [SA602A]
 S524AD0XD1
 S524AD0XD1@TSSOP8 [SA026-B3201]
 S524AD0XF1@SOP8 [SA602A]
 S524C20D11
 S524C20D11@TSSOP8 [SA026-B3201]
 S524C20D21@SOP8 [SA602A]
 S524C80D41
 S524C80D41@TSSOP8 [SA026-B3201]
 S524C80D81@SOP8 [SA602A]
 S524L50X51
 S524L50X51@TSSOP8 [SA026-B3201]
 S524LB0X91@SOP8 [SA602A]
 S524LB0XB1
 S524LB0XB1@TSSOP8 [SA026-B3201]

KM93C07(16bit)
 KM93C07(G)(16bit)@S0IC8 [SA602A]

KM93C46V(G)@S0IC8 [SA602A]
 KM93C47V
 KM93C47V(GD)@S0IC8 [SA602A]
 KM93C56V(G)@S0IC8 [SA602A]
 KM93C57V
 KM93C57V(GD)@S0IC8 [SA602A]
 KM93C66V(G)@S0IC8 [SA602A]
 KM93C67V
 KM93C67V(GD)@S0IC8 [SA602A]
 KS24C010@S0IC8 [SA602A]
 KS24C011
 KS24C011@TSSOP8 [SA026-B3201]
 KS24C020@S0IC8 [SA602A]
 KS24C021
 KS24C021@TSSOP8 [SA026-B3201]
 KS24C040@S0IC8 [SA602A]
 KS24C041
 KS24C041@TSSOP8 [SA026-B3201]
 KS24C080@S0IC8 [SA602A]
 KS24C081
 KS24C081@TSSOP8 [SA026-B3201]
 S524A40X10@SOP8 [SA602A]
 S524A40X11
 S524A40X11@TSSOP8 [SA026-B3201]
 S524A40X20@SOP8 [SA602A]
 S524A40X21
 S524A40X21@TSSOP8 [SA026-B3201]
 S524A40X40@SOP8 [SA602A]
 S524A40X41
 S524A40X41@TSSOP8 [SA026-B3201]
 S524A60X51@SOP8 [SA602A]
 S524A60X81
 S524A60X81@TSSOP8 [SA026-B3201]
 S524AB0X91@SOP8 [SA602A]
 S524AB0XB1
 S524AB0XB1@TSSOP8 [SA026-B3201]
 S524AD0XD1@SOP8 [SA602A]
 S524AD0XF1
 S524AD0XF1@TSSOP8 [SA026-B3201]
 S524C20D11@SOP8 [SA602A]
 S524C20D21
 S524C20D21@TSSOP8 [SA026-B3201]
 S524C80D41@SOP8 [SA602A]
 S524C80D81
 S524C80D81@TSSOP8 [SA026-B3201]
 S524L50X51@SOP8 [SA602A]
 S524LB0X91
 S524LB0X91@TSSOP8 [SA026-B3201]
 S524LB0XB1@SOP8 [SA602A]

E (E) PROM/FRAM/NVRAM

LE24C041	LE24C041@MFP8 [SA654]
LE24C042	LE24C042@MFP8 [SA654]
LE24C081	LE24C081@MFP8 [SA654]
LE24C082	LE24C082@MFP8 [SA654]
LE24C161	LE24C161@MFP8 [SA654]
LE24C162	LE24C162@MFP8 [SA654]
LE24C322@MFP8 [SA654]	LE24C322@WLP6 [SA717]
LE24CB642M [SA605B]	LE24CB642TT [SA602A]
LE24L322@MFP8 [SA654]	LE25FU106BMA@MFP8 [SA654]
LE25FU106BTT@MSOP8 [SA654]	LE25FU406BMA@MFP8 [SA602A]
LE25FU406BTT@MSOP8 [SA654]	LE25FW056FN@VSON8 [SA683]
LE25FW056MA@MFP8 [SA602A]	LE25FW106M@SOP8 [SA602A]
LE25FW106T@MSOP8 [SA654]	LE25FW1606FN@VSON8 [SA683]
LE25FW203ATT@MSOP8 [SA654]	LE25FW206M@SOP8 [SA602A]
LE25FW206T@MSOP8 [SA654]	LE25FW406BMA@MFP8 [SA602A]
LE25FW406BTT@MSOP8 [SA654]	LE25FW406M@SOP8 [SA602A]
LE25FW406T@MSOP8 [SA654]	LE25FW806M@SOP8 [SA602A]
LE25FW806T@MSOP8 [SA654]	LE26CW006@WLP6 [SA717]
LE28BW168T@TSOP48 [SA637B-B4806]	LE28C1001AM@SOP32 [SA687]
LE28C1001AT@TSOP32 [SA410T-B4001]	
LE28C1001ATS@VSOP32 [SA620-B4807]	
LE28C1001DT@TSOP32 [SA410T-B4001]	
LE28C1001DTS@VSOP32 [SA620-B4807]	
LE28CV1001AM@SOP32 [SA687]	
LE28CV1001AT@TSOP32 [SA410T-B4001]	
LE28CV1001ATS@VSOP32 [SA620-B4807]	
LE28CV1001DT@TSOP32 [SA410T-B4001]	
LE28CV1001DTS@VSOP32 [SA620-B4807]	
LE28CW1001DT@TSOP32 [SA410T-B4001]	
LE28CW1001DTS@VSOP32 [SA620-B4807]	
LE28DW1621T@TSOP48 [SB247-B4806]	
LE28DW8102T@TSOP48 [SA637B-B4806]	
LE28DW8163T@TSOP48 [SB247-B4806]	LE28F1101T@TSOP40 [SA623-B4002]
LE28F1601T (REVERSE)@TSOP40 [SA623-B4002]	
LE28F1601T@TSOP40 [SA623-B4002]	
LE28F2001ATS@TSOP32 [SA620-B4807]	
LE28F4001ATS@TSOP32 [SA620-B4807]	
LE28F4001M@SSOP32 [SA438T]	
LE28F8001T (REVERSE)@TSOP40 [SA623-B4002]	
LE28F8001T@TSOP40 [SA623-B4002]	LE28FU4101T@TSOP48 [SB247-B4806]
LE28FV1101T@TSOP40 [SA623-B4002]	
LE28FV1601T (REVERSE)@TSOP40 [SA623-B4002]	
LE28FV1601T@TSOP40 [SA623-B4002]	
LE28FV2001ATS@TSOP32 [SA620-B4807]	
LE28FV4001ATS@TSOP32 [SA620-B4807]	
LE28FV4001CTS@TSOP32 [SA620-B4807]	
LE28FV4001M@SSOP32 [SA438T]	LE28FV4001T@TSOP32 [SA620-B4807]
LE28FV4101T@TSOP48 [SB247-B4806]	
LE28FV8001T (REVERSE)@TSOP40 [SA623-B4002]	
LE28FV8001T@TSOP40 [SA623-B4002]	
LE28FW1633TB@TSOP48 [SB247-B4806]	
LE28FW1633TT@TSOP48 [SB247-B4806]	
LE28FW4101T@TSOP48 [SB247-B4806]	LE28FW8201T@TSOP48 [SB247-B4806]
LE28FW8203TB@TSOP48 [SB247-B4806]	
LE28FW8203TT@TSOP48 [SB247-B4806]	

SEEQ

E (E) PROM/FRAM/NVRAM

27128	27256
2764	27C256
2804	2804A
2816A	2816AH
5516A	5516AH
5517A	5517AH
DE2817A	DE2817A@PLCC32 [SA015A1T]
DE2817AH	DE2817AH@PLCC32 [SA015A1T]
DQ2817A	DQ2817A@PLCC32 [SA015A1T]
DQ2817AH	DQ2817AH@PLCC32 [SA015A1T]
DQ2864	DQ2864@PLCC32 [SA015A1T]
DQ2864H	DQ2864H@PLCC32 [SA015A1T]
DQ28C256	DQ28C256@PLCC32 [SA015A1T]
DQ28C64	DQ28C64@PLCC32 [SA015A1T]
DQ28C64A	DQ28C64A@PLCC32 [SA015A1T]
DQ28C65	DQ28C65@PLCC32 [SA015A1T]
E28C64	E28C64@PLCC32 [SA015A1T]
M28C64	M28C64@PLCC32 [SA015A1T]
PQ2864	PQ2864@PLCC32 [SA015A1T]
PQ2864H	PQ2864H@PLCC32 [SA015A1T]
PQ28C64	PQ28C64@PLCC32 [SA015A1T]
PQ28C65	PQ28C65@PLCC32 [SA015A1T]

SEIKO

E (E) PROM/FRAM/NVRAM

S-22H10	S-22H10@SOP18 [SA404]
S-22H12	S-22H12@SOP18 [SA404]
S-22S10	S-22S10@SOP18 [SA404]
S-22S12	S-22S12@SOP18 [SA404]
S-24C01A(DP)	S-24C01A(DPA)
S-24C01A(FJA)@S0IC8 [SA602A]	S-24C01B(DP)
S-24C01B(FJ)@S0IC8 [SA602A]	S-24C02A(DP)
S-24C02A(DPA)	S-24C02A(FJA)@S0IC8 [SA602A]
S-24C02B(DP)	S-24C02B(FJ)@S0IC8 [SA602A]
S-24C04A(DP)	S-24C04A(DPA)
S-24C04A(FJA)@S0IC8 [SA602A]	S-24C04B(DP)
S-24C04B(FJ)@S0IC8 [SA602A]	S-24C08A(DPA)
S-24C08A(FJA)@S0IC8 [SA602A]	S-24C16A(DPA)
S-24C16A(FJA)@S0IC8 [SA602A]	S-24CS01A(DP)
S-24CS01A(FJ)@S0IC8 [SA602A]	S-24CS01A(FT)@TSSOP8
S-24CS02A(DP)	S-24CS02A(FJ)@S0IC8 [SA602A]
S-24CS02A(FT)@TSSOP8	S-24CS04A(DP)
S-24CS04A(FJ)@S0IC8 [SA602A]	S-24CS04A(FT)@TSSOP8
S-24CS08A(DP)	S-24CS08A(FJ)@S0IC8 [SA602A]
S-24CS08A(FT)@TSSOP8	S-24CS16A(DP)
S-24CS16A(FJ)@S0IC8 [SA602A]	S-24CS16A(FT)@TSSOP8
S-24CS64A(FJ)@S0IC8 [SA602A]	S-24CS64A(FT)@TSSOP8
S-24H30	S-24H30@SOP8 [SA605B]
S-24H45	S-24H45@SOP8 [SA605B]
S-24S30	S-24S30@SOP8 [SA605B]
S-24S45	S-24S45@SOP8 [SA605B]
S-25A010A@SOP8 [SA602A]	S-25A020A@SOP8 [SA602A]

S-25A040A@SOP8 [SA602A]
S-25A160A@SOP8 [SA602A]
S-25A640A@SOP8 [SA602A]
S-25C010A@TSSOP8 [SA026-B3201]
S-25C020A@TSSOP8 [SA026-B3201]
S-25C040A@TSSOP8 [SA026-B3201]
S-25C080A@TSSOP8 [SA026-B3201]
S-25C160A@TSSOP8 [SA026-B3201]
S-25C320A@TSSOP8 [SA026-B3201]
S-25C640A@TSSOP8 [SA026-B3201]
S-2900A(DP)
S-2900A(UP)@SOT-89-5 [SA717]
S-29130A(DFJA)@S0IC8 [SA602A]
S-29130A(FJA)@S0IC8 [SA602A]
S-29131A(FJA)@S0IC8 [SA602A]
S-29190A(FJA)@S0IC8 [SA602A]
S-29191A(FJA)@S0IC8 [SA602A]
S-29194A(FJA)@S0IC8 [SA602A]
S-29220A(DPA)
S-29221A(DPA)
S-29230A(DFJA)@S0IC8 [SA602A]
S-29230A(FJA)@S0IC8 [SA602A]
S-29231A(FJA)@S0IC8 [SA602A]
S-29290A(FJA)@S0IC8 [SA602A]
S-29291A(FJA)@S0IC8 [SA602A]
S-29294A(FJA)@S0IC8 [SA602A]
S-29330A(DPA)
S-29331A(DPA)
S-29390A(DPA)
S-29391A(DPA)
S-29394A(DPA)
S-29430A
S-29530A
S-29630A
S-29L130A(DFE)@S0IC8 [SA602A]
S-29L130A(FS)@SSOP8 [SA026-B3201]
S-29L131A(DFE)@S0IC8 [SA602A]
S-29L131A(FS)@SSOP8 [SA026-B3201]
S-29L194A(DFE)@S0IC8 [SA602A]
S-29L194A(FS)@TSSOP8 [SA026-B3201]
S-29L220A(DFE)@S0IC8 [SA602A]
S-29L220A(FS)@SSOP8 [SA026-B3201]
S-29L221A(DFE)@S0IC8 [SA602A]
S-29L221A(FS)@SSOP8 [SA026-B3201]
S-29L294A(DFE)@S0IC8 [SA602A]
S-29L294A(FS)@TSSOP8 [SA026-B3201]
S-29L330A(DFE)@S0IC8 [SA602A]
S-29L330A(FS)@SSOP8 [SA026-B3201]
S-29L331A(DFE)@S0IC8 [SA602A]
S-29L331A(FS)@SSOP8 [SA026-B3201]
S-29L394A(DFE)@S0IC8 [SA602A]
S-29L394A(FS)@TSSOP8 [SA026-B3201]
S-29U130A(DFE)@S0IC8 [SA602A]
S-29U130A(FS)@SSOP8 [SA026-B3201]
S-29U131A(DFE)@S0IC8 [SA602A]
S-29U131A(FS)@SSOP8 [SA026-B3201]
S-29U194A(DFE)@S0IC8 [SA602A]
S-29U194A(FS)@TSSOP8 [SA026-B3201]
S-29U220A(DFE)@S0IC8 [SA602A]

S-25A080A@SOP8 [SA602A]
S-25A320A@SOP8 [SA602A]
S-25C010A@SOP8 [SA602A]
S-25C020A@SOP8 [SA602A]
S-25C040A@SOP8 [SA602A]
S-25C080A@SOP8 [SA602A]
S-25C160A@SOP8 [SA602A]
S-25C320A@SOP8 [SA602A]
S-25C640A@SOP8 [SA602A]
S-2817A@SOP28 [SA404]
S-2900A(FE)@SOP8 [SA602A]
S-2911(DP)
S-29130A(DPA)
S-29131A(DPA)
S-29190A(DPA)
S-29191A(DPA)
S-29194A(DPA)
S-29220A(DFJA)@S0IC8 [SA602A]
S-29220A(FJA)@S0IC8 [SA602A]
S-29221A(FJA)@S0IC8 [SA602A]
S-29230A(DPA)
S-29231A(DPA)
S-29290A(DPA)
S-29291A(DPA)
S-29294A(DPA)
S-29330A(DFJA)@S0IC8 [SA602A]
S-29330A(FJA)@S0IC8 [SA602A]
S-29331A(FJA)@S0IC8 [SA602A]
S-29390A(FJA)@S0IC8 [SA602A]
S-29391A(FJA)@S0IC8 [SA602A]
S-29394A(FJA)@S0IC8 [SA602A]
S-29430A@S0IC8 [SA602A]
S-29530A@S0IC8 [SA602A]
S-29630A@S0IC8 [SA602A]
S-29L130A(FE)@S0IC8 [SA602A]

S-29L220A(FE)@S0IC8 [SA602A]

S-29L330A(FE)@S0IC8 [SA602A]

S-29U220A(FS)@SSOP8	[SA026-B3201]	
S-29U221A(DFE)@S0IC8	[SA602A]	
S-29U221A(FS)@SSOP8	[SA026-B3201]	
S-29U294A(DFE)@S0IC8	[SA602A]	
S-29U294A(FS)@TSSOP8	[SA026-B3201]	
S-29U330A(DFE)@S0IC8	[SA602A]	
S-29U330A(FS)@SSOP8	[SA026-B3201]	
S-29U331A(DFE)@S0IC8	[SA602A]	
S-29U331A(FS)@SSOP8	[SA026-B3201]	
S-29U394A(DFE)@S0IC8	[SA602A]	
S-29U394A(FS)@TSSOP8	[SA026-B3201]	
S-29Z330A(DFJA)@S0IC8	[SA602A]	
S-29Z330A(FS)@SSOP8	[SA026-B3201]	
S-29Z430A(DFJA)@S0IC8	[SA602A]	
S-29Z430A(FS)@SSOP8	[SA026-B3201]	
S-93A46A(D0A)@S0IC8	[SA602A]	S-93A56A(D0A)@S0IC8 [SA602A]
S-93A66A(D0A)@S0IC8	[SA602A]	S-93A66A(FJ)@S0IC8 [SA602A]
S-93A86A@S0IC8	[SA602A]	S-93C46A(DFJ)@S0IC8 [SA602A]
S-93C46A(DP)		S-93C46A(FJ)@S0IC8 [SA602A]
S-93C46A(FT)@TSSOP8	[SA026-B3201]	
S-93C46B(DP)		S-93C46B(FJ)@S0IC8 [SA602A]
S-93C46B(FT)@TSSOP8	[SA026-B3201]	
S-93C56A(DFJ)@S0IC8	[SA602A]	S-93C56A(DP)
S-93C56A(FJ)@S0IC8	[SA602A]	
S-93C56A(FT)@TSSOP8	[SA026-B3201]	
S-93C56B(DP)		S-93C56B(FJ)@S0IC8 [SA602A]
S-93C56B(FT)@TSSOP8	[SA026-B3201]	
S-93C66A(DFJ)@S0IC8	[SA602A]	S-93C66A(DP)
S-93C66A(FJ)@S0IC8	[SA602A]	
S-93C66A(FT)@TSSOP8	[SA026-B3201]	
S-93C66B(DP)		S-93C66B(FJ)@S0IC8 [SA602A]
S-93C66B(FT)@TSSOP8	[SA026-B3201]	
S-93C76A(DP)		S-93C76A(FJ)@S0IC8 [SA602A]
S-93C76A(FT)@TSSOP8	[SA026-B3201]	
S-93C86A(DP)		S-93C86A(FJ)@S0IC8 [SA602A]
S-93C86A(FT)@TSSOP8	[SA026-B3201]	
S-93C86B@S0IC8	[SA602A]	S-93C86B@TSSOP8
S-93L46A(D0I)@S0IC8	[SA602A]	S-93L56A(D0I)@S0IC8 [SA602A]
S-93L66A(D0I)@S0IC8	[SA602A]	S-93L76A(D0I)@S0IC8 [SA602A]

SGS-THOMSON

E(E) PROM/FRAM/NVRAM

ET2716		ETC2716
ETC2732		M24128
M24128@S0IC8	[SA602A]	M24164
M24164@S0IC8	[SA602A]	M24256
M24256[3.9]@S0IC8	[SA602A]	M24256[5.5]@S0IC8 [SA023A]
M24512		M24512@S0IC8 [SA605B]
M24512@TSOP8	[SA026-B3201]	M24C04
M24C04@S0IC8	[SA602A]	M24C08
M24C08@S0IC8	[SA602A]	M24C08W
M24C08W@S0IC8	[SA602A]	M24C08W@TSOP8
M24C64(BN)		M24C64(DL)@TSSOP14 [SA026-B3201]
M24C64(DW)@TSSOP8	[SA602A]	M24C64(MN)@S0IC8 [SA023A]
M24C64(MW)@S0IC8	[SA602A]	M27128A
M2716		M27256

M27256A	M2732A
M27512	M2764
M2764A	M27C1000
M27C1000@PLCC32 [SA015A1T]	M27C1000@TSOP32 [SA410T-B4001]
M27C1001	M27C1001@PLCC32 [SA015A1T]
M27C1001@TSOP32 [SA410T-B4001]	M27C1024
M27C1024@PLCC44 [SA244]	M27C160
M27C160@PLCC44 [SA244]	M27C160@PSOP44 [SA638]
M27C2001	M27C2001@PLCC32 [SA015A1T]
M27C2001@TSOP32 [SA410T-B4001]	M27C202
M27C202@PLCC44 [SA244]	M27C202@VSOP40 [SA623-B4002]
M27C256B	M27C256B@PLCC32 [SA015A1T]
M27C400	M27C4001
M27C4001@PLCC32 [SA015A1T]	M27C4001@TSOP32 [SA410T-B4001]
M27C4002	M27C4002@PLCC44
M27C405	M27C405@PLCC32 [SA015A1T]
M27C405@TSOP32 [SA410T-B4001]	M27C512
M27C512@PLCC32 [SA015A1T]	M27C516
M27C516@PLCC44 [SA244]	M27C64A
M27C64A@PLCC32 [SA015A1T]	M27C800
M27C800@PLCC44 [SA244]	M27C800@PSOP44 [SA638]
M27C801	M27C801@PLCC32 [SA015A1T]
M27C801@TSOP32 [SA410T-B4001]	M27HC641
M27HC641@PLCC28 [SA008A]	M27HC642
M27HC642@PLCC28 [SA008A]	M27V101
M27V101@PLCC32 [SA015A1T]	M27V101@TSOP32 [SA410T-B4001]
M27V201	M27V201@PLCC32 [SA015A1T]
M27V201@TSOP32 [SA410T-B4001]	M27V401
M27V401@PLCC32 [SA015A1T]	M27V401@TSOP32 [SA410T-B4001]
M27V402	M27V402@PLCC44 [SA244]
M27V402@TSOP40 [SA409T-B4002]	M27V512
M27V512@PLCC32 [SA015A1T]	M27V512@TSOP28 [SA430T-B4003]
M27V800	M27V800@PLCC44 [SA244]
M27V801	M27V801@PLCC32 [SA015A1T]
M27V801@TSOP32 [SA410T-B4001]	M27W201
M27W201@PLCC32 [SA015A1T]	M27W201@TSOP32 [SA410T-B4001]
M28010	M28010@PLCC32 [SA015A1T]
M28010@TSOP32 [SA410T-B4001]	M28C16@PLCC32 [SA015A1T]
M28C64C	M28C64C@PLCC32 [SA015A1T]
M28C64C@S0IC28 [SA404]	M28C64C@TSOP28 [SA430T-B4003]
M28F101	
M28F101(REVERSE)@TSOP32 [SA410T-B4001]	M28F101@TSOP32 [SA410T-B4001]
M28F101@PLCC32 [SA015A1T]	M28F102@PLCC44 [SA244]
M28F102	M28F151
M28F102@TSOP40 [SA623-B4002]	
M28F151(REVERSE)@TSOP32 [SA410T-B4001]	
M28F151@PLCC32 [SA015A1T]	M28F151@TSOP32 [SA410T-B4001]
M28F201	
M28F201(REVERSE)@TSOP32 [SA410T-B4001]	
M28F201@PLCC32 [SA015A1T]	M28F201@TSOP32 [SA410T-B4001]
M28F210@PSOP44 [SA638]	M28F210@TSOP48 [SB247-B4806]
M28F211@TSOP40 [SA409T-B4002]	M28F220@PSOP44 [SA638]
M28F220@TSOP48 [SB247-B4806]	M28F221@TSOP40 [SA409T-B4002]
M28F256	
M28F256(REVERSE)@TSOP32 [SA410T-B4001]	
M28F256@PLCC32 [SA015A1T]	M28F256@TSOP32 [SA410T-B4001]
M28F411@TSOP40 [SA409T-B4002]	M28F421@TSOP40 [SA409T-B4002]
M28F512	
M28F512(REVERSE)@TSOP32 [SA410T-B4001]	

M28F512@PLCC32 [SA015A1T]
M29F002B
M29F002B@TSOP32 [SA410T-B4001]
M29F002T@PLCC32 [SA015A1T]
M29F040
M29F040@TSOP32 [SA410T-B4001]
M29F040B@PLCC32 [SA015A1T]
M29F100B@PSOP44 [SA638]
M29F100T@PSOP44 [SA638]
M29F102B@PLCC44 [SA244]
M29F102BB@PLCC44 [SA244]
M29F200B@PSOP44 [SA638]
M29F200T@PSOP44 [SA638]
M29F400B@PSOP44 [SA638]
M29F400T@PSOP44 [SA638]
M29V040@PLCC32 [SA015A1T]
M29W008B@TSOP40 [SA409T-B4002]
M29W040@PLCC32 [SA015A1T]
M29W400B@PSOP44 [SA638]
M29W400T@PLCC44 [SA638]
M29W512B@PLCC32 [SA015A1T]
M29W800B@PSOP44 [SA638]
M29W800T@PSOP44 [SA638]
M48T35
M48T35Y
M48T59
M48T59Y
M48Z128
M48Z30
M48Z32
M50FW080@PLCC32 [SA015A1T]
M50FW080@VSOP32 [SA620-B4807]
M93C06(08bit)@S0IC8 [SA602A]
M93C06(16bit)@S0IC8 [SA602A]
M93S46@S0IC8 [SA602A]
M95P02
M95P04
M95P08
MK48C02
MK48C12
MK48T02
MK48T08
MK48T12B
MK48Z02
MK48Z08
MK48Z12B
MKI48Z02
MKI48Z12
MKI48Z18
ST24C01@S0IC8 [SA602A]
ST24C02A@S0IC8 [SA602A]
ST24C16@S0IC8 [SA602A]
ST24W01@S0IC8 [SA602A]
ST24W02@S0IC8 [SA602A]
ST24W04C@S0IC8 [SA602A]
ST27256
ST27C256
ST93C06(08bit)@S0IC8 [SA602A]
ST93C06(16bit)@S0IC8 [SA602A]

M28F512@TSOP32 [SA410T-B4001]
M29F002B@PLCC32 [SA015A1T]
M29F002T
M29F002T@TSOP32 [SA410T-B4001]
M29F040@PLCC32 [SA015A1T]
M29F040B
M29F040B@TSOP32 [SA410T-B4001]
M29F100B@TSOP48 [SB247-B4806]
M29F100T@TSOP48 [SB247-B4806]
M29F102B@TSOP40 [SA623-B4002]
M29F102BB@TSOP40 [SA623-B4002]
M29F200B@TSOP48 [SB247-B4806]
M29F200T@TSOP48 [SB247-B4806]
M29F400B@TSOP48 [SB247-B4806]
M29F400T@TSOP48 [SB247-B4806]
M29V040@TSOP32 [SA410T-B4001]
M29W008T@TSOP40 [SA409T-B4002]
M29W040@TSOP32 [SA410T-B4001]
M29W400B@TSOP48 [SB247-B4806]
M29W400T@TSOP48 [SB247-B4806]
M29W512B@TSOP32 [SA620-B4807]
M29W800B@TSOP48 [SB247-B4806]
M29W800T@TSOP48 [SB247-B4806]
M48T35@S0IC28 [SA404]
M48T35Y@S0IC28 [SA404]
M48T59@S0IC28 [SA404]
M48T59Y@S0IC28 [SA404]
M48Z128Y
M48Z30Y
M48Z32Y
M50FW080@TSOP40 [SA409T-B4002]
M93C06(08bit)
M93C06(16bit)
M93S46
M93S46@TSSOP8
M95P02@S0IC8 [SA602A]
M95P04@S0IC8 [SA602A]
M95P08@S0IC8 [SA602A]
MK48C02B
MK48C12B
MK48T02B
MK48T12
MK48T18
MK48Z02B
MK48Z12
MK48Z18
MKI48Z02B
MKI48Z12B
ST24C01
ST24C02A
ST24C16
ST24W01
ST24W02
ST24W04C
ST27128A
ST2764A
ST93C06(08bit)
ST93C06(16bit)
ST93CS46

ST93CS46@S0IC8 [SA602A]	TS27C256
TS27C64	TS27C64@PLCC32 [SA015A1T]
TS27C64A	TS27C64A@PLCC32 [SA015A1T]
TS28C16A	TS28C17A

PLD

GAL16V8	GAL16V8A
---------	----------

SHARP

E(E)PROM/FRAM/NVRAM

LH28F002SCHN@PSOP44 [SA638]	
LH28F002SCHT@TSOP40 [SA409T-B4002]	
LH28F002SCN@PSOP44 [SA638]	
LH28F002SCT@TSOP40 [SA409T-B4002]	
LH28F004BVE(BT)@TSOP40 [SA409T-B4002]	
LH28F004BVE(TT)@TSOP40 [SA409T-B4002]	
LH28F004BVHS(BT)@VSOP40 [SA623-B4002]	
LH28F004BVHS(TT)@VSOP40 [SA623-B4002]	
LH28F004BVT(BT)@TSOP40 [SA409T-B4002]	
LH28F004BVT(TT)@TSOP40 [SA409T-B4002]	
LH28F004SCHN@PSOP44 [SA638]	
LH28F004SCHS@VSOP40 [SA623-B4002]	
LH28F004SCHT@TSOP40 [SA409T-B4002]	
LH28F004SCN@PSOP44 [SA638]	LH28F004SCS@VSOP40 [SA623-B4002]
LH28F004SCT@TSOP40 [SA409T-B4002]	
LH28F008BJT(BTLZ1)@TSOP40 [SA409T-B4002]	
LH28F008BJT(TB)@TSOP40 [SA409T-B4002]	
LH28F008BJT(TT)@TSOP40 [SA409T-B4002]	
LH28F008BJT(TTLZ2)@TSOP40 [SA409T-B4002]	
LH28F008BVT(BT)@TSOP40 [SA409T-B4002]	
LH28F008BVT(TT)@TSOP40 [SA409T-B4002]	
LH28F008SAN@PSOP44 [SA638]	
LH28F008SAR@RTSOP40 [SA409T-B4002]	
LH28F008SAT@TSOP40 [SA409T-B4002]	
LH28F008SCH(L85)@RTSOP40 [SA409T-B4002]	
LH28F008SCH-L@TSOP40 [SA409T-B4002]	
LH28F008SCHN@PSOP44 [SA638]	
LH28F008SCH-V@TSOP40 [SA409T-B4002]	
LH28F008SCH-ZU-120@TSOP40 [SA409T-B4002]	
LH28F008SCN@PSOP44 [SA638]	LH28F008SCN-L@PSOP44 [SA638]
LH28F008SCT@TSOP40 [SA409T-B4002]	
LH28F008SCT-L@TSOP40 [SA409T-B4002]	
LH28F008SCT-V@TSOP40 [SA409T-B4002]	
LH28F008SCV@TSOP40 [SA409T-B4002]	
LH28F016SC@PSOP44 [SA638]	
LH28F016SCR(L95)@RTSOP40 [SA409T-B4002]	
LH28F016SCT-L95@TSOP40 [SA409T-B4002]	
LH28F128BFHE@TSOP48 [SB247-B4806]	
LH28F128BFND@PSOP44 [SA638]	
LH28F160BGE(B)@TSOP48 [SB247-B4806]	
LH28F160BGE(T)@TSOP48 [SB247-B4806]	
LH28F160BHEB@TSOP48 [SB247-B4806]	
LH28F160BHET@TSOP48 [SB247-B4806]	
LH28F160BJD	

LH28F160BJEB@TSOP48 [SB247-B4806]
LH28F160BJET@TSOP48 [SB247-B4806]
LH28F160BVE(BTL)@TSOP48 [SB247-B4806]
LH28F160BVE(TTL)@TSOP48 [SB247-B4806]
LH28F320BJD
LH28F320BJE(PB)(OTP)@TSOP48 [SB247-B4806]
LH28F320BJE(PB)@TSOP48 [SB247-B4806]
LH28F320BJE(PT)(OTP)@TSOP48 [SB247-B4806]
LH28F320BJE(PT)@TSOP48 [SB247-B4806]
LH28F320BJHE(PB)(OTP)@TSOP48 [SB247-B4806]
LH28F320BJHE(PT)(OTP)@TSOP48 [SB247-B4806]
LH28F320BJN@PSOP44 [SA638]
LH28F400BGE(B)@TSOP48 [SB247-B4806]
LH28F400BGE(T)@TSOP48 [SB247-B4806]
LH28F400BGHE(B)@TSOP48 [SB247-B4806]
LH28F400BGHE(T)@TSOP48 [SB247-B4806]
LH28F400BGN(B)@PSOP44 [SA638] LH28F400BGN(T)@PSOP44 [SA638]
LH28F400BVE(B)@TSOP48 [SB247-B4806]
LH28F400BVE(T)@TSOP48 [SB247-B4806]
LH28F400BVHE(B)@TSOP48 [SB247-B4806]
LH28F400BVHE(T)@TSOP48 [SB247-B4806]
LH28F400BVN(B)@PSOP44 [SA638] LH28F400BVN(T)@PSOP44 [SA638]
LH28F640BFE(PB)@TSOP48 [SB247-B4806]
LH28F640BFE(PT)@TSOP48 [SB247-B4806]
LH28F800BGE(B)@TSOP48 [SB247-B4806]
LH28F800BGE(T)@TSOP48 [SB247-B4806]
LH28F800BGHE(B)@TSOP48 [SB247-B4806]
LH28F800BGHE(T)@TSOP48 [SB247-B4806]
LH28F800BGHE(TTL10)@TSOP48 [SB247-B4806]
LH28F800BGN(B)@PSOP44 [SA638] LH28F800BGN(T)@PSOP44 [SA638]
LH28F800BH-B@TSOP48 [SB247-B4806]
LH28F800BJE(PB)(OTP)@TSOP48 [SB247-B4806]
LH28F800BJE(PB)@TSOP48 [SB247-B4806]
LH28F800BJE(PT)(OTP)@TSOP48 [SB247-B4806]
LH28F800BJE(PT)@TSOP48 [SB247-B4806]
LH28F800BJHE(PB)(OTP)@TSOP48 [SB247-B4806]
LH28F800BJHE(PT)(OTP)@TSOP48 [SB247-B4806]
LH28F800BJHG(PB)(OTP)@CSP48 [\$\$\$\$\$]
LH28F800BJR(PT)(OTP)@TSOP48 [SB247-B4806]
LH28F800BV-B@TSOP48 [SB247-B4806]
LH28F800BVE(B)@TSOP48 [SB247-B4806]
LH28F800BVE(T)@TSOP48 [SB247-B4806]
LH28F800BVE(TV85)@TSOP48 [SB247-B4806]
LH28F800BVHB@TSOP48 [SB247-B4806]
LH28F800BVHE(B)@TSOP48 [SB247-B4806]
LH28F800BVHT@TSOP48 [SB247-B4806]
LH28F800BVN(TV85)@PSOP44 [SA638]
LH28F800BV-T@TSOP48 [SB247-B4806]
LHF00L03@PLCC32 [SA015A1T] LHF00L04@TSOP40 [SA409T-B4002]
LHF00L06@TSOP40 [SA409T-B4002] LHF00L07@PLCC32 [SA015A1T]
LHF00L12(LH28F320T)@TSOP48 [SB247-B4806]
LHF00L13(LH28F320B)@TSOP48 [SB247-B4806]
LHF00L14(LH28F320T)@TSOP48 [SB247-B4806]
LHF00L15(LH28F320B)@TSOP48 [SB247-B4806]
LHF00L28(LH28F160T)@TSOP48 [SB247-B4806]
LHF00L29(LH28F160B)@TSOP48 [SB247-B4806]
LHF00L30(LH28F160T)@TSOP48 [SB247-B4806]
LHF00L31(LH28F160B)@TSOP48 [SB247-B4806]

SIEMENS

E (E) PROM/FRAM/NVRAM

SDA2526	SDA2526@S0IC8 [SA602A]
SDA2546	SDA2546@S0IC8 [SA602A]
SDA25X26	SDA25X26@S0IC8 [SA602A]
SDA25X46	SDA25X46@S0IC8 [SA602A]
SDE2526	SDE2526@S0IC8 [SA602A]
SDE2546	SDE2546@S0IC8 [SA602A]
SDE25X26	SDE25X26@S0IC8 [SA602A]
SDE25X46	SDE25X46@S0IC8 [SA602A]
SLA24C01	SLA24C01@S0IC8 [SA602A]
SLA24C02	SLA24C02@S0IC8 [SA602A]
SLA24C04	SLA24C04@S0IC8 [SA602A]
SLA24C08	SLA24C08@S0IC8 [SA602A]
SLA24C16	SLA24C16@S0IC8 [SA602A]
SLA24C164	SLA24C164@S0IC8 [SA602A]
SLA24C32	SLA24C32@S0IC8 [SA602A]
SLA24C64	SLA24C64@S0IC8 [SA602A]
SLA25010	SLA25010@S0IC8 [SA602A]
SLA25020	SLA25020@S0IC8 [SA602A]
SLA25040	SLA25040@S0IC8 [SA602A]
SLA25080	SLA25080@S0IC8 [SA602A]
SLA25160	SLA25160@S0IC8 [SA602A]
SLE24C01	SLE24C01@S0IC8 [SA602A]
SLE24C02	SLE24C02@S0IC8 [SA602A]
SLE24C04	SLE24C04@S0IC8 [SA602A]
SLE24C08	SLE24C08@S0IC8 [SA602A]
SLE24C16	SLE24C16@S0IC8 [SA602A]
SLE24C164	SLE24C164@S0IC8 [SA602A]
SLE24C32	SLE24C32@S0IC8 [SA602A]
SLE24C64	SLE24C64@S0IC8 [SA602A]
SLE25010	SLE25010@S0IC8 [SA602A]
SLE25020	SLE25020@S0IC8 [SA602A]
SLE25040	SLE25040@S0IC8 [SA602A]
SLE25080	SLE25080@S0IC8 [SA602A]
SLE25160	SLE25160@S0IC8 [SA602A]

SIERRA

E (E) PROM/FRAM/NVRAM

SC22101CM [SA404]	SC22101CN
SC22201CM [SA404]	SC22201CN

SIGNETICS

E (E) PROM/FRAM/NVRAM

27C010	27C010@PLCC32 [SA015A1T]
27C010@TSOP32 [SA410T-B4001]	27C040
27C040@PLCC32 [SA015A1T]	27C040@TSOP32 [SA410T-B4001]
27C210	27C210@PLCC44 [SA244]
27C240	27C240@PLCC44 [SA244]
27C256	27C256@PLCC32 [SA015A1T]
27C512	27C512@PLCC32 [SA015A1T]

27C64A
27HC641
27HC642
PCA8582A
PCA8582B
PCA8582C
PCA8582D
PCA8582E
PCD8582A
PCD8582B
PCD8582C
PCD8582D
PCD8582E
PCF8582A
PCF8582B
PCF8582C
PCF8582D
PCF8582E
PCF8594
PCF8594C
PCF8594D
PCF8594E
PCF8598
PCF8598C
PCF8598D
PCF8598E

27C64A@PLCC32 [SA015A1T]
27HC641@PLCC28 [SA008A]
27HC642@PLCC28 [SA008A]
PCA8582A@S0IC8 [SA602A]
PCA8582B@S0IC8 [SA602A]
PCA8582C@S0IC8 [SA602A]
PCA8582D@S0IC8 [SA602A]
PCA8582E@S0IC8 [SA602A]
PCD8582A@S0IC8 [SA602A]
PCD8582B@S0IC8 [SA602A]
PCD8582C@S0IC8 [SA602A]
PCD8582D@S0IC8 [SA602A]
PCD8582E@S0IC8 [SA602A]
PCF8582A@S0IC8 [SA602A]
PCF8582B@S0IC8 [SA602A]
PCF8582C@S0IC8 [SA602A]
PCF8582D@S0IC8 [SA602A]
PCF8582E@S0IC8 [SA602A]
PCF8594@S0IC8 [SA602A]
PCF8594C@S0IC8 [SA602A]
PCF8594D@S0IC8 [SA602A]
PCF8594E@S0IC8 [SA602A]
PCF8598@S0IC8 [SA605B]
PCF8598C@S0IC8 [SA605B]
PCF8598D@S0IC8 [SA605B]
PCF8598E@S0IC8 [SA605B]

MICROCONTROLLER

S87C51
S87C51@TQFP44 [SA675-B4805]
S87C51FA@PLCC44 [SA244]
S87C51FB
S87C51FB@TQFP44 [SA675-B4805]
S87C51FC@PLCC44 [SA244]
S87C52
S87C52@TQFP44 [SA675-B4805]
S87C524@PLCC44 [SA244]
S87C528
S87C528@TQFP44 [SA245A-B4805]
S87C54@PLCC44 [SA244]
S87C550
S87C575
S87C575@TQFP44 [SA675-B4805]
S87C576@PLCC44 [SA244]
S87C58
S87C58@TQFP44 [SA675-B4805]
S87C591@TQFP44 [SA675-B4805]
S87C652@PLCC44 [SA244]
S87C654
S87C654@TQFP44 [SA675-B4805]
S87L51FA@PLCC44 [SA244]
S87L51FB
S87L51FB@TQFP44 [SA675-B4805]

S87C51@PLCC44 [SA244]
S87C51FA
S87C51FA@TQFP44 [SA675-B4805]
S87C51FB@PLCC44 [SA244]
S87C51FC
S87C51FC@TQFP44 [SA245A-B4805]
S87C52@PLCC44 [SA244]
S87C524
S87C524@TQFP44 [SA245A-B4805]
S87C528@PLCC44 [SA244]
S87C54
S87C54@TQFP44 [SA675-B4805]
S87C550@PLCC44 [SA244]
S87C575@PLCC44 [SA244]
S87C576
S87C576@TQFP44 [SA675-B4805]
S87C58@PLCC44 [SA244]
S87C591@PLCC44 [SA244]
S87C652
S87C652@TQFP44 [SA675-B4805]
S87C654@PLCC44 [SA244]
S87L51FA
S87L51FA@TQFP44 [SA675-B4805]
S87L51FB@PLCC44 [SA244]

SIMTEK

E (E) PROM/FRAM/NVRAM

STK10C48	STK10C48@S0IC28(300 mil) [SA404]
STK10C48@S0IC28(350 mil) [SA630]	STK10C68
STK10C68@PLCC28 [SA008A]	STK10C68@S0IC28 [SA630]
STK11C48	STK11C48@S0IC28(300 mil) [SA404]
STK11C48@S0IC28(350 mil) [SA630]	STK11C68
STK11C68@PLCC28 [SA008A]	STK11C68@S0IC28 [SA630]
STK11C88	STK11C88(3V)
STK11C88(3V)@S0IC28(300 mil) [SA404]	
STK11C88(3V)@S0IC28(350 mil) [SA630]	
STK11C88@S0IC28(300 mil) [SA404]	STK11C88@S0IC28(350 mil) [SA630]
STK12C68	STK12C68@PLCC28 [SA008A]
STK12C68@S0IC28 [SA630]	STK14C88
STK14C88(3V)	STK14C88(3V)@PLCC32 [SA015A1T]
STK14C88(3V)@S0IC32(300 mil) [SA715]	
STK14C88(3V)@S0IC32(350 mil) [SA630]	
STK14C88@PLCC32 [SA015A1T]	STK14C88@S0IC32(300 mil) [SA715]
STK14C88@S0IC32(350 mil) [SA630]	STK15C68
STK15C68@S0IC28 [SA630]	STK15C88
STK15C88@S0IC28(300 mil) [SA404]	STK15C88@S0IC28(350 mil) [SA630]
STK16C68	STK16C88
STK16C88(3V)	STK20C04
STK22C48	STK22C48@S0IC28(300 mil) [SA404]
STK22C48@S0IC28(350 mil) [SA630]	STK25C48

SMOS

E (E) PROM/FRAM/NVRAM

SPM27128	SPM27128C
SPM27C256	SPM27C64
SPM27C64H	

SONIX

MICROCONTROLLER

SN8P1504	SN8P1504@SOP18 [SA404]
SN8P1504@SOP28 [SA404]	SN8P1506
SN8P1507@TQFP44 [SA675-B4805]	SN8P1602
SN8P1602@SOP18 [SA404]	SN8P1602@SSOP20 [SA674]
SN8P1603	SN8P1603@SOP18 [SA404]
SN8P1603@SSOP20 [SA674]	SN8P1604
SN8P1604@SOP28 [SA404]	SN8P1702
SN8P1702@SOP18 [SA404]	SN8P1702@SSOP20 [SA674]
SN8P1704A	SN8P1704A@SOP28 [SA404]
SN8P1704B	SN8P1704B@SOP28 [SA404]
SN8P1706A	SN8P1706B
SN8P1707A	SN8P1707A@TQFP44 [SA675-B4805]
SN8P1707B@TQFP44 [SA675-B4805]	SN8P1708A
SN8P1708A@SSOP48 [SA669]	SN8P1708B
SN8P1708B@SSOP48 [SA669]	SN8P1714
SN8P1714@SOP18 [SA404]	SN8P1714@SOP28 [SA404]
SN8P1716	SN8P1717@TQFP44 [SA675-B4805]
SN8P2501AP	SN8P2501AS@SOP14 [SA602]
SN8P2501AX@TSSOP16 [SA026-B3201]	SN8P2501BP

SN8P2501BS@SOP14 [SA602]
SN8P2502AP
SN8P2502AX@TSSOP16 [SA026-B3201]
SN8P2502BS@SOP14 [SA602]
SN8P2504AP
SN8P2504AX@TSSOP16 [SA026-B3201]
SN8P2504BS@SOP14 [SA602]
SN8P2602AP
SN8P2602AX@SSOP20 [SA674]
SN8P2602BS@SOP18 [SA023A]
SN8P2603AP
SN8P2603AX@SSOP20 [SA674]
SN8P2603BS@SOP18 [SA023A]
SN8P26042AP
SN8P26042AX@SSOP20 [SA674]
SN8P26042BS@SOP20 [SA023A]
SN8P26042P
SN8P26042X@SSOP20 [SA674]
SN8P2604AS@SOP28 [SA404]
SN8P2604BK
SN8P2604BX@SSOP28 [SA626A]
SN8P2604S@SOP28 [SA404]
SN8P2606P
SN8P2608X@SSOP48 [SA669]
SN8P2622S@SOP18 [SA023A]
SN8P2624K
SN8P2624X@SSOP28 [SA626A]
SN8P2704AP
SN8P2705AP
SN8P2706AP
SN8P2708AP
SN8P2708AX@SSOP48 [SA669]
SN8P2722S@SOP20 [SA023A]

SN8P2501BX@TSSOP16 [SA026-B3201]
SN8P2502AS@SOP14 [SA602]
SN8P2502BP
SN8P2502BX@TSSOP16 [SA026-B3201]
SN8P2504AS@SOP14 [SA602]
SN8P2504BP
SN8P2504BX@TSSOP16 [SA026-B3201]
SN8P2602AS@SOP18 [SA023A]
SN8P2602BP
SN8P2602BX@SSOP20 [SA674]
SN8P2603AS@SOP18 [SA023A]
SN8P2603BP
SN8P2603BX@SSOP20 [SA674]
SN8P26042AS@SOP20 [SA023A]
SN8P26042BP
SN8P26042BX@SSOP20 [SA674]
SN8P26042S@SOP20 [SA023A]
SN8P2604AK
SN8P2604AX@SSOP28 [SA626A]
SN8P2604BS@SOP28 [SA404]
SN8P2604K
SN8P2604X@SSOP28 [SA626A]
SN8P2608P
SN8P2622P
SN8P2622X@SSOP20 [SA430T-B4003]
SN8P2624S@SOP28 [SA404]
SN8P2704AK@SDIP28 [SA653]
SN8P2704AS@SOP28 [SA723]
SN8P2705AS@SOP32 [SA687]
SN8P2707AQ@QFP44 [SA245A-B4805]
SN8P2708AQ@LQFP48 [SA248-B4804]
SN8P2722P
SN8P2722X@SSOP20 [SA430T-B4003]

SONY

E(E)PROM/FRAM/NVRAM

CXK1011M@S0IC8 [SA602A]
CXK1012P
CXK1023P

CXK1011P
CXK1013P
CXK27C4001

SPACE ELECTRONICS[SEi]

E(E)PROM/FRAM/NVRAM

28C010
28C010@TSOP32 [SA410T-B4001]
28C010T@PLCC32 [SA015A1T]
28C011
28C011@TSOP32 [SA410T-B4001]
28C011T@PLCC32 [SA015A1T]

28C010@PLCC32 [SA015A1T]
28C010T
28C010T@TSOP32 [SA410T-B4001]
28C011@PLCC32 [SA015A1T]
28C011T
28C011T@TSOP32 [SA410T-B4001]

SPANSION

E(E)PROM/FRAM/NVRAM

AM29DL161DB@TSOP48 [SB247-B4806]	AM29DL161DT@TSOP48 [SB247-B4806]
AM29DL162CB@TSOP48 [SB247-B4806]	AM29DL162CT@TSOP48 [SB247-B4806]
AM29DL162DB@TSOP48 [SB247-B4806]	AM29DL162DT@TSOP48 [SB247-B4806]
AM29DL163CB@TSOP48 [SB247-B4806]	AM29DL163CT@TSOP48 [SB247-B4806]
AM29DL163DB@TSOP48 [SB247-B4806]	AM29DL163DT@TSOP48 [SB247-B4806]
AM29DL164CB@TSOP48 [SB247-B4806]	AM29DL164CT@TSOP48 [SB247-B4806]
AM29DL164DB@TSOP48 [SB247-B4806]	AM29DL164DT@TSOP48 [SB247-B4806]
AM29DL320GB@TSOP48 [SB247-B4806]	AM29DL320GT@TSOP48 [SB247-B4806]
AM29DL321CB@TSOP48 [SB247-B4806]	AM29DL321CT@TSOP48 [SB247-B4806]
AM29DL322CB@TSOP48 [SB247-B4806]	AM29DL322CT@TSOP48 [SB247-B4806]
AM29DL322DB@TSOP48 [SB247-B4806]	AM29DL322DT@TSOP48 [SB247-B4806]
AM29DL322GB@TSOP48 [SB247-B4806]	AM29DL322GT@TSOP48 [SB247-B4806]
AM29DL323CB@TSOP48 [SB247-B4806]	AM29DL323CT@TSOP48 [SB247-B4806]
AM29DL323DB@TSOP48 [SB247-B4806]	AM29DL323DT@TSOP48 [SB247-B4806]
AM29DL323GB@TSOP48 [SB247-B4806]	AM29DL323GT@TSOP48 [SB247-B4806]
AM29DL324CB@TSOP48 [SB247-B4806]	AM29DL324CT@TSOP48 [SB247-B4806]
AM29DL324DB@TSOP48 [SB247-B4806]	AM29DL324DT@TSOP48 [SB247-B4806]
AM29DL324GB@TSOP48 [SB247-B4806]	AM29DL324GT@TSOP48 [SB247-B4806]
AM29DL400BB(REVERSE)@TSOP48 [SB247-B4806]	
AM29DL400BB@PSOP44 [SA638]	AM29DL400BB@TSOP48 [SB247-B4806]
AM29DL400BT(REVERSE)@TSOP48 [SB247-B4806]	
AM29DL400BT@PLCC44 [SA638]	AM29DL400BT@TSOP48 [SB247-B4806]
AM29DL640D@TSOP48 [SB247-B4806]	AM29DL640G@TSOP48 [SB247-B4806]
AM29DL800B@PSOP44 [SA638]	AM29DL800B@TSOP48 [SB247-B4806]
AM29DL800BB(REVERSE)@TSOP48 [SB247-B4806]	
AM29DL800BB@PSOP44 [SA638]	AM29DL800BB@TSOP48 [SB247-B4806]
AM29DL800BT(REVERSE)@TSOP48 [SB247-B4806]	
AM29DL800BT@PSOP44 [SA638]	AM29DL800BT@TSOP48 [SB247-B4806]
AM29DL800T@PSOP44 [SA638]	AM29DL800T@TSOP48 [SB247-B4806]
AM29DS163CB@TSOP48 [SB247-B4806]	AM29DS163CT@TSOP48 [SB247-B4806]
AM29DS163DB@TSOP48 [SB247-B4806]	AM29DS163DT@TSOP48 [SB247-B4806]
AM29DS323DB@TSOP48 [SB247-B4806]	AM29DS323DT@TSOP48 [SB247-B4806]
AM29F002B	AM29F002B@PLCC32 [SA015A1T]
AM29F002B@TSOP32 [SA410T-B4001]	AM29F002BB
AM29F002BB@PLCC32 [SA015A1T]	AM29F002BB@TSOP32 [SA410T-B4001]
AM29F002BT	AM29F002BT@PLCC32 [SA015A1T]
AM29F002BT@TSOP32 [SA410T-B4001]	AM29F002NB
AM29F002NB@PLCC32 [SA015A1T]	AM29F002NB@TSOP32 [SA410T-B4001]
AM29F002NBB	AM29F002NBB@PLCC32 [SA015A1T]
AM29F002NBB@TSOP32 [SA410T-B4001]	
AM29F002NBT	AM29F002NBT@PLCC32 [SA015A1T]
AM29F002NBT@TSOP32 [SA410T-B4001]	
AM29F002NT	AM29F002NT@PLCC32 [SA015A1T]
AM29F002NT@TSOP32 [SA410T-B4001]	AM29F002T
AM29F002T@PLCC32 [SA015A1T]	AM29F002T@TSOP32 [SA410T-B4001]
AM29F004BB	AM29F004BB@PLCC32 [SA015A1T]
AM29F004BB@TSOP32 [SA410T-B4001]	AM29F004BT
AM29F004BT@PLCC32 [SA015A1T]	AM29F004BT@TSOP32 [SA410T-B4001]
AM29F016@PSOP44 [SA638]	AM29F016@TSOP40 [SA409T-B4002]
AM29F016@TSOP48 [SB247-B4806]	AM29F016B@PSOP44 [SA638]
AM29F016B@TSOP40 [SA409T-B4002]	AM29F016B@TSOP48 [SB247-B4806]
AM29F016D@PSOP44 [SA638]	AM29F016D@TSOP40 [SA409T-B4002]
AM29F016D@TSOP48 [SB247-B4806]	
AM29F017B(REVERSE)@TSOP40 [SA409T-B4002]	
AM29F017B(REVERSE)@TSOP48 [SB247-B4806]	
AM29F017B@TSOP40 [SA409T-B4002]	AM29F017B@TSOP48 [SB247-B4806]
AM29F017D(REVERSE)@TSOP48 [SB247-B4806]	
AM29F017D@TSOP40 [SA409T-B4002]	AM29F017D@TSOP48 [SB247-B4806]
AM29F032B@PSOP44 [SA638]	AM29F032B@TSOP40 [SA409T-B4002]

AM29F040
AM29F040@TSOP32 [SA410T-B4001]
AM29F040A@PLCC32 [SA015A1T]
AM29F040A@TSOP32 [SA410T-B4001]
AM29F040B
AM29F040B(Reverse)@TSOP32 [SA410T-B4001]
AM29F040B@PLCC32 [SA015A1T]
AM29F040B@TSOP32 [SA410T-B4001]
AM29F080(Reverse)@TSOP40 [SA409T-B4002]
AM29F080@PSOP44 [SA638]
AM29F080@TSOP40 [SA409T-B4002]
AM29F080B@PSOP44 [SA638]
AM29F080B@TSOP40 [SA409T-B4002]
AM29F100B(Reverse)@TSOP48 [SB247-B4806]
AM29F100B@PSOP44 [SA638]
AM29F100B@TSOP48 [SB247-B4806]
AM29F100T(Reverse)@TSOP48 [SB247-B4806]
AM29F100T@PSOP44 [SA638]
AM29F100T@TSOP48 [SB247-B4806]
AM29F160DB(Reverse)@TSOP48 [SB247-B4806]
AM29F160DB@TSOP48 [SB247-B4806]
AM29F160DT(Reverse)@TSOP48 [SB247-B4806]
AM29F160DT@TSOP48 [SB247-B4806]
AM29F200AB(Reverse)@TSOP48 [SB247-B4806]
AM29F200AB@PSOP44 [SA638]
AM29F200AB@TSOP48 [SB247-B4806]
AM29F200AT(Reverse)@TSOP48 [SB247-B4806]
AM29F200AT@PSOP44 [SA638]
AM29F200AT@TSOP48 [SB247-B4806]
AM29F200BB(Reverse)@TSOP48 [SB247-B4806]
AM29F200BB@PSOP44 [SA638]
AM29F200BB@TSOP48 [SB247-B4806]
AM29F200BT(Reverse)@TSOP48 [SB247-B4806]
AM29F200BT@PSOP44 [SA638]
AM29F200BT@TSOP48 [SB247-B4806]
AM29F400AB(Reverse)@TSOP48 [SB247-B4806]
AM29F400AB@PSOP44 [SA638]
AM29F400AB@TSOP48 [SB247-B4806]
AM29F400AT(Reverse)@TSOP48 [SB247-B4806]
AM29F400AT@PSOP44 [SA638]
AM29F400AT@TSOP48 [SB247-B4806]
AM29F400BB(Reverse)@TSOP48 [SB247-B4806]
AM29F400BB@PSOP44 [SA638]
AM29F400BB@TSOP48 [SB247-B4806]
AM29F400BT(Reverse)@TSOP48 [SB247-B4806]
AM29F400BT@PSOP44 [SA638]
AM29F400BT@TSOP48 [SB247-B4806]
AM29F800B(Reverse)@TSOP48 [SB247-B4806]
AM29F800B@PSOP44 [SA638]
AM29F800B@TSOP48 [SB247-B4806]
AM29F800BB(Reverse)@TSOP48 [SB247-B4806]
AM29F800BB@PSOP44 [SA638]
AM29F800BB@TSOP48 [SB247-B4806]
AM29F800BT(Reverse)@TSOP48 [SB247-B4806]
AM29F800BT@PSOP44 [SA638]
AM29F800BT@TSOP48 [SB247-B4806]
AM29F800T(Reverse)@TSOP48 [SB247-B4806]
AM29F800T@PSOP44 [SA638]
AM29F800T@TSOP48 [SB247-B4806]
AM29LL800B@TSOP48 [SB247-B4806]
AM29LL800BB@TSOP48 [SB247-B4806]
AM29LL800BT@TSOP48 [SB247-B4806]
AM29LL800T@TSOP48 [SB247-B4806]
AM29LV001BB(Reverse)@TSOP32 [SA410T-B4001]
AM29LV001BB@PLCC32 [SA015A1T]
AM29LV001BB@TSOP32 [SA410T-B4001]
AM29LV001BT(Reverse)@TSOP32 [SA410T-B4001]
AM29LV001BT@PLCC32 [SA015A1T]
AM29LV001BT@TSOP32 [SA410T-B4001]
AM29LV002@TSOP40 [SA409T-B4002]
AM29LV002B@TSOP40 [SA409T-B4002]
AM29LV002BB@TSOP40 [SA409T-B4002]
AM29LV002BT@TSOP40 [SA409T-B4002]
AM29LV004B@TSOP40 [SA409T-B4002]
AM29LV004BB@TSOP40 [SA409T-B4002]
AM29LV004BT@TSOP40 [SA409T-B4002]
AM29LV004T@TSOP40 [SA409T-B4002]
AM29LV008B@TSOP40 [SA409T-B4002]
AM29LV008BB@TSOP40 [SA409T-B4002]
AM29LV008BT@TSOP40 [SA409T-B4002]
AM29LV008T@TSOP40 [SA409T-B4002]

AM29LV017B(REVERSE)@TSOP40 [SA409T-B4002]
AM29LV017B@TSOP40 [SA409T-B4002]
AM29LV017D(REVERSE)@TSOP40 [SA409T-B4002]
AM29LV017D@TSOP40 [SA409T-B4002] AM29LV033C@TSOP40 [SA409T-B4002]
AM29LV033MU@TSOP40 [SA409T-B4002]
AM29LV065D@TSOP48 [SB247-B4806] AM29LV065MU@TSOP48 [SB247-B4806]
AM29LV080@TSOP40 [SA409T-B4002] AM29LV081@TSOP40 [SA409T-B4002]
AM29LV081B@TSOP40 [SA409T-B4002]
AM29LV116BB@TSOP40 [SA409T-B4002]
AM29LV116BT@TSOP40 [SA409T-B4002]
AM29LV116DB@TSOP40 [SA409T-B4002]
AM29LV116DT@TSOP40 [SA409T-B4002]
AM29LV160BB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160BB@PSOP44 [SA638] AM29LV160BB@TSOP48 [SB247-B4806]
AM29LV160BT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160BT@PSOP44 [SA638] AM29LV160BT@TSOP48 [SB247-B4806]
AM29LV160DB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160DB@PSOP44 [SA638] AM29LV160DB@TSOP48 [SB247-B4806]
AM29LV160DT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160DT@PSOP44 [SA638] AM29LV160DT@TSOP48 [SB247-B4806]
AM29LV160MB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160MB@PSOP44 [SA638] AM29LV160MB@TSOP48 [SB247-B4806]
AM29LV160MT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV160MT@PSOP44 [SA638] AM29LV160MT@TSOP48 [SB247-B4806]
AM29LV200B(REVERSE)@TSOP48 [SB247-B4806]
AM29LV200B@PSOP44 [SA638] AM29LV200B@TSOP48 [SB247-B4806]
AM29LV200BB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV200BB@PSOP44 [SA638] AM29LV200BB@TSOP48 [SB247-B4806]
AM29LV200BT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV200BT@PSOP44 [SA638] AM29LV200BT@TSOP48 [SB247-B4806]
AM29LV200T(REVERSE)@TSOP48 [SB247-B4806]
AM29LV200T@PSOP44 [SA638] AM29LV200T@TSOP48 [SB247-B4806]
AM29LV320DB@TSOP48 [SB247-B4806] AM29LV320DT@TSOP48 [SB247-B4806]
AM29LV320FB@TSOP48 [SB247-B4806] AM29LV320FT@TSOP48 [SB247-B4806]
AM29LV320MB@TSOP48 [SB247-B4806] AM29LV320MT@TSOP48 [SB247-B4806]
AM29LV400B(REVERSE)@TSOP48 [SB247-B4806]
AM29LV400B@PSOP44 [SA638] AM29LV400B@TSOP48 [SB247-B4806]
AM29LV400BB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV400BB@PSOP44 [SA638] AM29LV400BB@TSOP48 [SB247-B4806]
AM29LV400BT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV400BT@PSOP44 [SA638] AM29LV400BT@TSOP48 [SB247-B4806]
AM29LV400T(REVERSE)@TSOP48 [SB247-B4806]
AM29LV400T@PSOP44 [SA638] AM29LV400T@TSOP48 [SB247-B4806]
AM29LV640MB@TSOP48 [SB247-B4806] AM29LV640MT@TSOP48 [SB247-B4806]
AM29LV641DH(REVERSE)@TSOP48 [SB247-B4806]
AM29LV641DH@TSOP48 [SB247-B4806]
AM29LV641DL(REVERSE)@TSOP48 [SB247-B4806]
AM29LV641DL@TSOP48 [SB247-B4806]
AM29LV641GH(REVERSE)@TSOP48 [SB247-B4806]
AM29LV641GH@TSOP48 [SB247-B4806]
AM29LV641GL(REVERSE)@TSOP48 [SB247-B4806]
AM29LV641GL@TSOP48 [SB247-B4806]
AM29LV641MH(REVERSE)@TSOP48 [SB247-B4806]
AM29LV641MH@TSOP48 [SB247-B4806]
AM29LV641ML(REVERSE)@TSOP48 [SB247-B4806]
AM29LV641ML@TSOP48 [SB247-B4806]
AM29LV800B(REVERSE)@TSOP48 [SB247-B4806]
AM29LV800B@PSOP44 [SA638] AM29LV800B@TSOP48 [SB247-B4806]
AM29LV800BB(REVERSE)@TSOP48 [SB247-B4806]

AM29LV800BB@PSOP44 [SA638] AM29LV800BB@TSOP48 [SB247-B4806]
AM29LV800BT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV800BT@PSOP44 [SA638] AM29LV800BT@TSOP48 [SB247-B4806]
AM29LV800DB(REVERSE)@TSOP48 [SB247-B4806]
AM29LV800DB@PSOP44 [SA638] AM29LV800DB@TSOP48 [SB247-B4806]
AM29LV800DT(REVERSE)@TSOP48 [SB247-B4806]
AM29LV800DT@PSOP44 [SA638] AM29LV800DT@TSOP48 [SB247-B4806]
AM29LV800T(REVERSE)@TSOP48 [SB247-B4806]
AM29LV800T@PSOP44 [SA638] AM29LV800T@TSOP48 [SB247-B4806]
AM29PL160CB@PSOP44 [SA638] AM29PL160CB@TSOP48 [SB247-B4806]
AM29PL160CT@PSOP44 [SA638] AM29PL160CT@TSOP48 [SB247-B4806]
AM29SL160BB@TSOP48 [SB247-B4806] AM29SL160BT@TSOP48 [SB247-B4806]
AM29SL160CB@TSOP48 [SB247-B4806] AM29SL160CT@TSOP48 [SB247-B4806]
AM29SL400CB@TSOP48 [SB247-B4806] AM29SL400CT@TSOP48 [SB247-B4806]
AM29SL800BB(REVERSE)@TSOP48 [SB247-B4806]
AM29SL800BB@TSOP48 [SB247-B4806]
AM29SL800BT(REVERSE)@TSOP48 [SB247-B4806]
AM29SL800BT@TSOP48 [SB247-B4806]
AM29SL800CB(REVERSE)@TSOP48 [SB247-B4806]
AM29SL800CB@TSOP48 [SB247-B4806]
AM29SL800CT(REVERSE)@TSOP48 [SB247-B4806]
AM29SL800CT@TSOP48 [SB247-B4806]
AM29SL800DB(REVERSE)@TSOP48 [SB247-B4806]
AM29SL800DB@TSOP48 [SB247-B4806]
AM29SL800DT(REVERSE)@TSOP48 [SB247-B4806]
AM29SL800DT@TSOP48 [SB247-B4806]
MBM29DL161BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL161BD@TSOP48 [SB247-B4806]
MBM29DL161BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL161BE@TSOP48 [SB247-B4806]
MBM29DL161TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL161TD@TSOP48 [SB247-B4806]
MBM29DL161TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL161TE@TSOP48 [SB247-B4806]
MBM29DL162BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL162BD@TSOP48 [SB247-B4806]
MBM29DL162BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL162BE@TSOP48 [SB247-B4806]
MBM29DL162TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL162TD@TSOP48 [SB247-B4806]
MBM29DL162TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL162TE@TSOP48 [SB247-B4806]
MBM29DL163BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL163BD@TSOP48 [SB247-B4806]
MBM29DL163BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL163BE@TSOP48 [SB247-B4806]
MBM29DL163TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL163TD@TSOP48 [SB247-B4806]
MBM29DL163TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL163TE@TSOP48 [SB247-B4806]
MBM29DL164BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL164BD@TSOP48 [SB247-B4806]
MBM29DL164BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL164BE@TSOP48 [SB247-B4806]
MBM29DL164TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL164TD@TSOP48 [SB247-B4806]
MBM29DL164TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL164TE@TSOP48 [SB247-B4806]
MBM29DL320BF@TSOP48 [SB247-B4806]

MBM29DL320TF@TSOP48 [SB247-B4806]
MBM29DL321BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL321BD@TSOP48 [SB247-B4806]
MBM29DL321BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL321BE@TSOP48 [SB247-B4806]
MBM29DL321TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL321TD@TSOP48 [SB247-B4806]
MBM29DL321TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL321TE@TSOP48 [SB247-B4806]
MBM29DL322BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL322BD@TSOP48 [SB247-B4806]
MBM29DL322BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL322BE@TSOP48 [SB247-B4806]
MBM29DL322TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL322TD@TSOP48 [SB247-B4806]
MBM29DL322TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL322TE@TSOP48 [SB247-B4806]
MBM29DL323BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL323BD@TSOP48 [SB247-B4806]
MBM29DL323BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL323BE@TSOP48 [SB247-B4806]
MBM29DL323BF@TSOP48 [SB247-B4806]
MBM29DL323TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL323TD@TSOP48 [SB247-B4806]
MBM29DL323TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL323TE@TSOP48 [SB247-B4806]
MBM29DL323TF@TSOP48 [SB247-B4806]
MBM29DL324BD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL324BD@TSOP48 [SB247-B4806]
MBM29DL324BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL324BE@TSOP48 [SB247-B4806]
MBM29DL324TD(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL324TD@TSOP48 [SB247-B4806]
MBM29DL324TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL324TE@TSOP48 [SB247-B4806]
MBM29DL32BF@TSOP48 [SB247-B4806] MBM29DL32TF@TSOP48 [SB247-B4806]
MBM29DL34BF@TSOP48 [SB247-B4806] MBM29DL34TF@TSOP48 [SB247-B4806]
MBM29DL400BB@PSOP44 [SA638]
MBM29DL400BB@TSOP48 [SB247-B4806]
MBM29DL400BC(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL400BC@PSOP44 [SA638]
MBM29DL400BC@TSOP48 [SB247-B4806]
MBM29DL400BT@PSOP44 [SA638]
MBM29DL400BT@TSOP48 [SB247-B4806]
MBM29DL400TC(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL400TC@PSOP44 [SA638]
MBM29DL400TC@TSOP48 [SB247-B4806]
MBM29DL640E(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL640E@TSOP48 [SB247-B4806] MBM29DL64DF@TSOP48 [SB247-B4806]
MBM29DL800B@PSOP44 [SA638] MBM29DL800B@TSOP48 [SB247-B4806]
MBM29DL800BA(REVERSE)@TSOP48 [SB247-B4806]
MBM29DL800BA@PSOP44 [SA638]
MBM29DL800BA@TSOP48 [SB247-B4806]
MBM29DL800BB@PSOP44 [SA638]
MBM29DL800BB@TSOP48 [SB247-B4806]
MBM29DL800BT@PSOP44 [SA638]
MBM29DL800BT@TSOP48 [SB247-B4806]
MBM29DL800T@PSOP44 [SA638] MBM29DL800T@TSOP48 [SB247-B4806]
MBM29DL800TA(REVERSE)@TSOP48 [SB247-B4806]

MBM29DL800TA@PSOP44 [SA638]
MBM29DL800TA@TSOP48 [SB247-B4806]
MBM29DS163BE@TSOP48 [SB247-B4806]
MBM29DS163TE@TSOP48 [SB247-B4806]
MBM29F001B
MBM29F001B@TSOP32 [SA410T-B4001]
MBM29F001T@PLCC32 [SA015A1T]
MBM29F002B
MBM29F002B@TSOP32 [SA410T-B4001]
MBM29F002NB@PLCC32 [SA015A1T]
MBM29F002NB@TSOP32 [SA410T-B4001]
MBM29F002NT
MBM29F002NT@TSOP32 [SA410T-B4001]
MBM29F002T
MBM29F002T@TSOP32 [SA410T-B4001]
MBM29F010@PLCC32 [SA015A1T]
MBM29F010A
MBM29F010A@TSOP32 [SA410T-B4001]
MBM29F016@TSOP40 [SA409T-B4002]
MBM29F016A@PSOP44 [SA638]
MBM29F016A@TSOP48 [SB247-B4806]
MBM29F016B@TSOP40 [SA409T-B4002]
MBM29F017A(REVERSE)@TSOP48 [SB247-B4806]
MBM29F017A@TSOP48 [SB247-B4806]
MBM29F017D@TSOP40 [SA409T-B4002]
MBM29F032B@PSOP44 [SA638]
MBM29F033C@TSOP40 [SA409T-B4002]
MBM29F040@PLCC32 [SA015A1T]
MBM29F040B
MBM29F040B@TSOP32 [SA410T-B4001]
MBM29F040C@TSOP32 [SA410T-B4001]
MBM29F080@TSOP40 [SA409T-B4002]
MBM29F080A(REVERSE)@TSOP40 [SA409T-B4002]
MBM29F080A(REVERSE)@TSOP48 [SB247-B4806]
MBM29F080A@PSOP44 [SA638]
MBM29F080A@TSOP48 [SB247-B4806]
MBM29F080B@TSOP40 [SA409T-B4002]
MBM29F100B@TSOP48 [SB247-B4806]
MBM29F100T@TSOP48 [SB247-B4806]
MBM29F160BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29F160BE@TSOP48 [SB247-B4806]
MBM29F160TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29F160TE@TSOP48 [SB247-B4806]
MBM29F200AB@TSOP48 [SB247-B4806]
MBM29F200AT@TSOP48 [SB247-B4806]
MBM29F200B@TSOP48 [SB247-B4806]
MBM29F200BC(REVERSE)@TSOP48 [SB247-B4806]
MBM29F200BC@PSOP44 [SA638]
MBM29F200T@PSOP44 [SA638]
MBM29F200TC(REVERSE)@TSOP48 [SB247-B4806]
MBM29F200TC@PSOP44 [SA638]
MBM29F400AB@PSOP44 [SA638]
MBM29F400AT@PSOP44 [SA638]
MBM29F400B@PSOP44 [SA638]
MBM29F400BB@PSOP44 [SA638]
MBM29F400BC(REVERSE)@TSOP48 [SB247-B4806]
MBM29F400BC@PSOP44 [SA638]
MBM29F400BT@PSOP44 [SA638]
MBM29F400T@PSOP44 [SA638]
MBM29F001B@PLCC32 [SA015A1T]
MBM29F001T
MBM29F001T@TSOP32 [SA410T-B4001]
MBM29F002B@PLCC32 [SA015A1T]
MBM29F002NB
MBM29F002NT@PLCC32 [SA015A1T]
MBM29F002T@PLCC32 [SA015A1T]
MBM29F010
MBM29F010@TSOP32 [SA410T-B4001]
MBM29F010A@PLCC32 [SA015A1T]
MBM29F016@PSOP44 [SA638]
MBM29F016@TSOP48 [SB247-B4806]
MBM29F016A@TSOP40 [SA409T-B4002]
MBM29F016B@PSOP44 [SA638]
MBM29F016B@TSOP48 [SB247-B4806]
MBM29F017B@TSOP48 [SB247-B4806]
MBM29F017D@TSOP48 [SB247-B4806]
MBM29F032B@TSOP40 [SA409T-B4002]
MBM29F040
MBM29F040@TSOP32 [SA410T-B4001]
MBM29F040B@PLCC32 [SA015A1T]
MBM29F040C@PLCC32 [SA015A1T]
MBM29F080@PSOP44 [SA638]
MBM29F080A@TSOP40 [SA409T-B4002]
MBM29F080B@PSOP44 [SA638]
MBM29F100B@PSOP44 [SA638]
MBM29F100T@PSOP44 [SA638]
MBM29F200AB@PSOP44 [SA638]
MBM29F200AT@PSOP44 [SA638]
MBM29F200B@PSOP44 [SA638]
MBM29F200BC@TSOP48 [SB247-B4806]
MBM29F200T@TSOP48 [SB247-B4806]
MBM29F200TC@TSOP48 [SB247-B4806]
MBM29F400AB@TSOP48 [SB247-B4806]
MBM29F400AT@TSOP48 [SB247-B4806]
MBM29F400B@TSOP48 [SB247-B4806]
MBM29F400BB@TSOP48 [SB247-B4806]
MBM29F400BC@TSOP48 [SB247-B4806]
MBM29F400BT@TSOP48 [SB247-B4806]
MBM29F400T@TSOP48 [SB247-B4806]

MBM29F400TC(REVERSE)@TSOP48 [SB247-B4806]
MBM29F400TC@PSOP44 [SA638] MBM29F400TC@TSOP48 [SB247-B4806]
MBM29F800B@PSOP44 [SA638] MBM29F800B@TSOP48 [SB247-B4806]
MBM29F800BA(REVERSE)@TSOP48 [SB247-B4806]
MBM29F800BA@PSOP44 [SA638] MBM29F800BA@TSOP48 [SB247-B4806]
MBM29F800BB@PSOP44 [SA638] MBM29F800BB@TSOP48 [SB247-B4806]
MBM29F800BT@PSOP44 [SA638] MBM29F800BT@TSOP48 [SB247-B4806]
MBM29F800T@PSOP44 [SA638] MBM29F800T@TSOP48 [SB247-B4806]
MBM29F800TA(REVERSE)@TSOP48 [SB247-B4806]
MBM29F800TA@PSOP44 [SA638] MBM29F800TA@TSOP48 [SB247-B4806]
MBM29LL800B@TSOP48 [SB247-B4806]
MBM29LL800BB@TSOP48 [SB247-B4806]
MBM29LL800BT@TSOP48 [SB247-B4806]
MBM29LL800T@TSOP48 [SB247-B4806] MBM29LV001B@PLCC32 [SA015A1T]
MBM29LV001BB(REVERSE)@TSOP32 [SA410T-B4001]
MBM29LV001BB@PLCC32 [SA015A1T]
MBM29LV001BB@TSOP32 [SA410T-B4001]
MBM29LV001BC(REVERSE)@TSOP32 [SA410T-B4001]
MBM29LV001BC@PLCC32 [SA015A1T]
MBM29LV001BC@TSOP32 [SA410T-B4001]
MBM29LV001BT(REVERSE)@TSOP32 [SA410T-B4001]
MBM29LV001BT@PLCC32 [SA015A1T]
MBM29LV001BT@TSOP32 [SA410T-B4001]
MBM29LV001T@TSOP32 [SA410T-B4001]
MBM29LV001TC(REVERSE)@TSOP32 [SA410T-B4001]
MBM29LV001TC@PLCC32 [SA015A1T]
MBM29LV001TC@TSOP32 [SA410T-B4001]
MBM29LV002B@TSOP40 [SA409T-B4002]
MBM29LV002T@TSOP40 [SA409T-B4002]
MBM29LV004B@TSOP40 [SA409T-B4002]
MBM29LV004BB@TSOP40 [SA409T-B4002]
MBM29LV004BT@TSOP40 [SA409T-B4002]
MBM29LV004T@TSOP40 [SA409T-B4002]
MBM29LV008B@TSOP40 [SA409T-B4002]
MBM29LV008BB@TSOP40 [SA409T-B4002]
MBM29LV008BT@TSOP40 [SA409T-B4002]
MBM29LV008T@TSOP40 [SA409T-B4002]
MBM29LV016/B@TSOP40 [SA409T-B4002]
MBM29LV016/T@TSOP40 [SA409T-B4002]
MBM29LV016B@TSOP40 [SA409T-B4002]
MBM29LV017@TSOP40 [SA409T-B4002]
MBM29LV017B@TSOP40 [SA409T-B4002]
MBM29LV017E@TSOP40 [SA409T-B4002]
MBM29LV033C@TSOP40 [SA409T-B4002]
MBM29LV080@TSOP40 [SA409T-B4002]
MBM29LV080A@TSOP40 [SA409T-B4002]
MBM29LV081@TSOP40 [SA409T-B4002]
MBM29LV081B@TSOP40 [SA409T-B4002]
MBM29LV116B@TSOP40 [SA409T-B4002]
MBM29LV160B(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV160B@TSOP48 [SB247-B4806]
MBM29LV160BE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV160BE@PSOP44 [SA638]
MBM29LV160BE@TSOP48 [SB247-B4806]
MBM29LV160BM@TSOP48 [SB247-B4806]
MBM29LV160T(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV160T@TSOP48 [SB247-B4806]
MBM29LV160TE(REVERSE)@TSOP48 [SB247-B4806]
MBM29LV160TE@PSOP44 [SA638]

MBM29LV160TE@TSOP48 [SB247-B4806]
MBM29LV160TM@TSOP48 [SB247-B4806]
MBM29LV200B@PSOP44 [SA638] MBM29LV200B@TSOP48 [SB247-B4806]
MBM29LV200BB@PSOP44 [SA638]
MBM29LV200BB@TSOP48 [SB247-B4806]
MBM29LV200BC (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV200BC@PSOP44 [SA638]
MBM29LV200BC@TSOP48 [SB247-B4806]
MBM29LV200BT@PSOP44 [SA638]
MBM29LV200BT@TSOP48 [SB247-B4806]
MBM29LV200T@PSOP44 [SA638] MBM29LV200T@TSOP48 [SB247-B4806]
MBM29LV200TC (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV200TC@PSOP44 [SA638]
MBM29LV200TC@TSOP48 [SB247-B4806]
MBM29LV320BE (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV320BE@TSOP48 [SB247-B4806]
MBM29LV320TE (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV320TE@TSOP48 [SB247-B4806]
MBM29LV400B@PSOP44 [SA638] MBM29LV400B@TSOP48 [SB247-B4806]
MBM29LV400BB@PSOP44 [SA638]
MBM29LV400BB@TSOP48 [SB247-B4806]
MBM29LV400BC@PSOP44 [SA638]
MBM29LV400BC@TSOP48 [SB247-B4806]
MBM29LV400BT@PSOP44 [SA638]
MBM29LV400BT@TSOP48 [SB247-B4806]
MBM29LV400T@PSOP44 [SA638] MBM29LV400T@TSOP48 [SB247-B4806]
MBM29LV400TC@PSOP44 [SA638]
MBM29LV400TC@TSOP48 [SB247-B4806]
MBM29LV650UE (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV650UE@TSOP48 [SB247-B4806]
MBM29LV651UE (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV651UE@TSOP48 [SB247-B4806]
MBM29LV800B@PSOP44 [SA638] MBM29LV800B@TSOP48 [SB247-B4806]
MBM29LV800BA (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV800BA@PSOP44 [SA638]
MBM29LV800BA@TSOP48 [SB247-B4806]
MBM29LV800BB@PSOP44 [SA638]
MBM29LV800BB@TSOP48 [SB247-B4806]
MBM29LV800BE (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV800BE@PSOP44 [SA638]
MBM29LV800BE@TSOP48 [SB247-B4806]
MBM29LV800BT@PSOP44 [SA638]
MBM29LV800BT@TSOP48 [SB247-B4806]
MBM29LV800T@PSOP44 [SA638] MBM29LV800T@TSOP48 [SB247-B4806]
MBM29LV800TA (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV800TA@PSOP44 [SA638]
MBM29LV800TA@TSOP48 [SB247-B4806]
MBM29LV800TE (REVERSE)@TSOP48 [SB247-B4806]
MBM29LV800TE@PSOP44 [SA638]
MBM29LV800TE@TSOP48 [SB247-B4806]
MBM29PL160BD@TSOP48 [SB247-B4806]
MBM29PL160TD@PSOP44 [SA638]
MBM29PL160TD@TSOP48 [SB247-B4806]
MBM29PL32BM@TSOP48 [SB247-B4806] MBM29PL32TM@TSOP48 [SB247-B4806]
MBM29PL64LM@TSOP48 [SB247-B4806] MBM29PL65LM@TSOP48 [SB247-B4806]
MBM29SL160BD (REVERSE)@TSOP48 [SB247-B4806]
MBM29SL160BD@TSOP48 [SB247-B4806]
MBM29SL160TD (REVERSE)@TSOP48 [SB247-B4806]
MBM29SL160TD@TSOP48 [SB247-B4806]

MBM29SL800BD(REVERSE)@TSOP48 [SB247-B4806]
 MBM29SL800BD@TSOP48 [SB247-B4806]
 MBM29SL800TD(REVERSE)@TSOP48 [SB247-B4806]
 MBM29SL800TD@TSOP48 [SB247-B4806]
 S25FL001D@S0IC8 [SA602A] S25FL001D@USON8 [SA683]
 S25FL002A@S0IC8 [SA605B] S25FL002A@USON8 [SA683]
 S25FL002D@S0IC8 [SA602A] S25FL002D@USON8 [SA683]
 S25FL004A@S0IC8 [SA605B] S25FL004A@USON8 [SA683]
 S25FL004D@S0IC8 [SA602A] S25FL004D@USON8 [SA683]
 S25FL008A@S0IC8 [SA605B] S25FL008A@USON8 [SA683]
 S25FL008D@S0IC8 [SA602A] S25FL008D@USON8 [SA683]
 S25FL016A@S0IC16 [SA404]
 S25FL016A@S0IC16(Normal mode) [SA404]
 S25FL016A@S0IC8 [SA605B]
 S25FL016A@S0IC8(Normal mode) [SA605B]
 S25FL016A@WS0N8 [SA684]
 S25FL016A@WS0N8(Normal mode) [SA684]
 S25FL020A@S0IC8(4.0) [SA602A] S25FL020A@S0IC8(5.4) [SA605B]
 S25FL020A@USON8 [SA683] S25FL032A@S0IC16 [SA404]
 S25FL032A@S0IC16(Normal mode) [SA404]
 S25FL032A@WS0N8 [SA684]
 S25FL032A@WS0N8(Normal mode) [SA684]
 S25FL040A(Bottom Boot)@SOP8(4.0) [SA602A]
 S25FL040A(Bottom Boot)@SOP8(5.4) [SA605B]
 S25FL040A(Bottom Boot)@USON8 [SA683]
 S25FL040A(Top Boot)@SOP8(4.0) [SA602A]
 S25FL040A(Top Boot)@SOP8(5.4) [SA605B]
 S25FL040A(Top Boot)@USON8 [SA683]
 S25FL040A@SOP8(4.0) [SA602A] S25FL040A@SOP8(5.4) [SA605B]
 S25FL040A@USON8 [SA683] S25FL064A@S0IC16 [SA404]
 S25FL064A@S0IC16(Normal mode) [SA404]
 S25FL064A@WS0N8 [SA684]
 S25FL064A@WS0N8(Normal mode) [SA684]
 S25FL080A@S0IC8(4.0) [SA602A] S25FL080A@S0IC8(5.4) [SA605B]
 S25FL080A@USON8 [SA683] S25FL128P(256 KB)@S0IC16 [SA404]
 S25FL128P(256 KB)@WS0N8 [SA684] S25FL128P(64 KB)@S0IC16 [SA404]
 S25FL128P(64 KB)@WS0N8 [SA684] S25FLK05D@S0IC8 [SA602A]
 S25FLK05D@USON8 [SA683] S29AD016D11MFA01@PSOP44 [SA638]
 S29AD016D11MFA02@PSOP44 [SA638] S29AD016D11MFB01@PSOP44 [SA638]
 S29AD016D11MFB02@PSOP44 [SA638] S29AD016D11MFI01@PSOP44 [SA638]
 S29AD016D11MFI02@PSOP44 [SA638] S29AD016D11MFV01@PSOP44 [SA638]
 S29AD016D11MFV02@PSOP44 [SA638]
 S29AD016D11TFA01@TSOP48 [SB247-B4806]
 S29AD016D11TFA02@TSOP48 [SB247-B4806]
 S29AD016D11TFB01@TSOP48 [SB247-B4806]
 S29AD016D11TFB02@TSOP48 [SB247-B4806]
 S29AD016D11TFI01@TSOP48 [SB247-B4806]
 S29AD016D11TFI02@TSOP48 [SB247-B4806]
 S29AD016D11TFV01@TSOP48 [SB247-B4806]
 S29AD016D11TFV02@TSOP48 [SB247-B4806]
 S29AL002B55MAI01@PSOP44 [SA638] S29AL002B55MAI02@PSOP44 [SA638]
 S29AL002B55MFI01@PSOP44 [SA638] S29AL002B55MFI02@PSOP44 [SA638]
 S29AL002B55TAI01@TSOP48 [SB247-B4806]
 S29AL002B55TAI02@TSOP48 [SB247-B4806]
 S29AL002B55TFI01@TSOP48 [SB247-B4806]
 S29AL002B55TFI02@TSOP48 [SB247-B4806]
 S29AL004B55MAI01@PSOP44 [SA638] S29AL004B55MAI02@PSOP44 [SA638]
 S29AL004B55MFI01@PSOP44 [SA638] S29AL004B55MFI02@PSOP44 [SA638]
 S29AL004B55TAI01@TSOP48 [SB247-B4806]

S29AL004B55TAI02@TSOP48 [SB247-B4806]
S29AL004B55TFI01@TSOP48 [SB247-B4806]
S29AL004B55TFI02@TSOP48 [SB247-B4806]
S29AL004D55MAI01@PSOP44 [SA638] S29AL004D55MAI02@PSOP44 [SA638]
S29AL004D55MANR1@PSOP44 [SA638] S29AL004D55MANR2@PSOP44 [SA638]
S29AL004D55MFI01@PSOP44 [SA638] S29AL004D55MFI02@PSOP44 [SA638]
S29AL004D55MFNR1@PSOP44 [SA638] S29AL004D55MFNR2@PSOP44 [SA638]
S29AL004D55TAI01@TSOP48 [SB247-B4806]
S29AL004D55TAI02@TSOP48 [SB247-B4806]
S29AL004D55TANR1@TSOP48 [SB247-B4806]
S29AL004D55TANR2@TSOP48 [SB247-B4806]
S29AL004D55TFI01@TSOP48 [SB247-B4806]
S29AL004D55TFI02@TSOP48 [SB247-B4806]
S29AL004D55TFNR1@TSOP48 [SB247-B4806]
S29AL004D55TFNR2@TSOP48 [SB247-B4806]
S29AL004D70MAI01@PSOP44 [SA638] S29AL004D70MAI02@PSOP44 [SA638]
S29AL004D70MAN01@PSOP44 [SA638] S29AL004D70MAN02@PSOP44 [SA638]
S29AL004D70MFI01@PSOP44 [SA638] S29AL004D70MFI02@PSOP44 [SA638]
S29AL004D70MFN01@PSOP44 [SA638] S29AL004D70MFN02@PSOP44 [SA638]
S29AL004D70TAI01@TSOP48 [SB247-B4806]
S29AL004D70TAI02@TSOP48 [SB247-B4806]
S29AL004D70TAN01@TSOP48 [SB247-B4806]
S29AL004D70TAN02@TSOP48 [SB247-B4806]
S29AL004D70TFI01@TSOP48 [SB247-B4806]
S29AL004D70TFI02@TSOP48 [SB247-B4806]
S29AL004D70TFN01@TSOP48 [SB247-B4806]
S29AL004D70TFN02@TSOP48 [SB247-B4806]
S29AL004D90MAI01@PSOP44 [SA638] S29AL004D90MAI02@PSOP44 [SA638]
S29AL004D90MAN01@PSOP44 [SA638] S29AL004D90MAN02@PSOP44 [SA638]
S29AL004D90MFI01@PSOP44 [SA638] S29AL004D90MFI02@PSOP44 [SA638]
S29AL004D90MFN01@PSOP44 [SA638] S29AL004D90MFN02@PSOP44 [SA638]
S29AL004D90TAI01@TSOP48 [SB247-B4806]
S29AL004D90TAI02@TSOP48 [SB247-B4806]
S29AL004D90TAN01@TSOP48 [SB247-B4806]
S29AL004D90TAN02@TSOP48 [SB247-B4806]
S29AL004D90TFI01@TSOP48 [SB247-B4806]
S29AL004D90TFI02@TSOP48 [SB247-B4806]
S29AL004D90TFN01@TSOP48 [SB247-B4806]
S29AL004D90TFN02@TSOP48 [SB247-B4806]
S29AL008D55MAIR1@PSOP44 [SA638] S29AL008D55MAIR2@PSOP44 [SA638]
S29AL008D55MFIR1@PSOP44 [SA638] S29AL008D55MFIR2@PSOP44 [SA638]
S29AL008D55TAIR1@TSOP48 [SB247-B4806]
S29AL008D55TAIR2@TSOP48 [SB247-B4806]
S29AL008D55TFIR1@TSOP48 [SB247-B4806]
S29AL008D55TFIR2@TSOP48 [SB247-B4806]
S29AL008D60MAI01@PSOP44 [SA638] S29AL008D60MAI02@PSOP44 [SA638]
S29AL008D60MAN01@PSOP44 [SA638] S29AL008D60MAN02@PSOP44 [SA638]
S29AL008D60MFI01@PSOP44 [SA638] S29AL008D60MFI02@PSOP44 [SA638]
S29AL008D60MFN01@PSOP44 [SA638] S29AL008D60MFN02@PSOP44 [SA638]
S29AL008D60TAI01@TSOP48 [SB247-B4806]
S29AL008D60TAI02@TSOP48 [SB247-B4806]
S29AL008D60TAN01@TSOP48 [SB247-B4806]
S29AL008D60TAN02@TSOP48 [SB247-B4806]
S29AL008D60TFI01@TSOP48 [SB247-B4806]
S29AL008D60TFI02@TSOP48 [SB247-B4806]
S29AL008D60TFN01@TSOP48 [SB247-B4806]
S29AL008D60TFN02@TSOP48 [SB247-B4806]
S29AL008D70MAI01@PSOP44 [SA638] S29AL008D70MAI02@PSOP44 [SA638]
S29AL008D70MAN01@PSOP44 [SA638] S29AL008D70MAN02@PSOP44 [SA638]

S29AL008D70MFI01@PSOP44	[SA638]	S29AL008D70MFI02@PSOP44	[SA638]
S29AL008D70MFN01@PSOP44	[SA638]	S29AL008D70MFN02@PSOP44	[SA638]
S29AL008D70TAI01@TSOP48	[SB247-B4806]		
S29AL008D70TAI02@TSOP48	[SB247-B4806]		
S29AL008D70TAN01@TSOP48	[SB247-B4806]		
S29AL008D70TAN02@TSOP48	[SB247-B4806]		
S29AL008D70TFI01@TSOP48	[SB247-B4806]		
S29AL008D70TFI02@TSOP48	[SB247-B4806]		
S29AL008D70TFN01@TSOP48	[SB247-B4806]		
S29AL008D70TFN02@TSOP48	[SB247-B4806]		
S29AL008D90MAI01@PSOP44	[SA638]	S29AL008D90MAI02@PSOP44	[SA638]
S29AL008D90MAN01@PSOP44	[SA638]	S29AL008D90MAN02@PSOP44	[SA638]
S29AL008D90MFI01@PSOP44	[SA638]	S29AL008D90MFI02@PSOP44	[SA638]
S29AL008D90MFN01@PSOP44	[SA638]	S29AL008D90MFN02@PSOP44	[SA638]
S29AL008D90TAI01@TSOP48	[SB247-B4806]		
S29AL008D90TAI02@TSOP48	[SB247-B4806]		
S29AL008D90TAN01@TSOP48	[SB247-B4806]		
S29AL008D90TAN02@TSOP48	[SB247-B4806]		
S29AL008D90TFI01@TSOP48	[SB247-B4806]		
S29AL008D90TFI02@TSOP48	[SB247-B4806]		
S29AL008D90TFN01@TSOP48	[SB247-B4806]		
S29AL008D90TFN02@TSOP48	[SB247-B4806]		
S29AL008J55TFIR1@TSOP48	[SA247-B4806]		
S29AL008J55TFIR2@TSOP48	[SA247-B4806]		
S29AL008J55TFNR1@TSOP48	[SA247-B4806]		
S29AL008J55TFNR2@TSOP48	[SA247-B4806]		
S29AL008J70TFI01@TSOP48	[SA247-B4806]		
S29AL008J70TFI02@TSOP48	[SA247-B4806]		
S29AL008J70TFI03@TSOP48	[SA247-B4806]		
S29AL008J70TFI04@TSOP48	[SA247-B4806]		
S29AL008J70TFN01@TSOP48	[SA247-B4806]		
S29AL008J70TFN02@TSOP48	[SA247-B4806]		
S29AL016D70MAI01@PSOP44	[SA638]	S29AL016D70MAI02@PSOP44	[SA638]
S29AL016D70MAN01@PSOP44	[SA638]	S29AL016D70MAN02@PSOP44	[SA638]
S29AL016D70MFI01@PSOP44	[SA638]	S29AL016D70MFI02@PSOP44	[SA638]
S29AL016D70MFN01@PSOP44	[SA638]	S29AL016D70MFN02@PSOP44	[SA638]
S29AL016D70TAI01@TSOP48	[SB247-B4806]		
S29AL016D70TAI02@TSOP48	[SB247-B4806]		
S29AL016D70TAN01@TSOP48	[SB247-B4806]		
S29AL016D70TAN02@TSOP48	[SB247-B4806]		
S29AL016D70TFI01@TSOP48	[SB247-B4806]		
S29AL016D70TFI02@TSOP48	[SB247-B4806]		
S29AL016D70TFN01@TSOP48	[SB247-B4806]		
S29AL016D70TFN02@TSOP48	[SB247-B4806]		
S29AL016D90MAI01@PSOP44	[SA638]	S29AL016D90MAI02@PSOP44	[SA638]
S29AL016D90MAN01@PSOP44	[SA638]	S29AL016D90MAN02@PSOP44	[SA638]
S29AL016D90MFI01@PSOP44	[SA638]	S29AL016D90MFI02@PSOP44	[SA638]
S29AL016D90MFN01@PSOP44	[SA638]	S29AL016D90MFN02@PSOP44	[SA638]
S29AL016D90TAI01@TSOP48	[SB247-B4806]		
S29AL016D90TAI02@TSOP48	[SB247-B4806]		
S29AL016D90TAN01@TSOP48	[SB247-B4806]		
S29AL016D90TAN02@TSOP48	[SB247-B4806]		
S29AL016D90TFI01@TSOP48	[SB247-B4806]		
S29AL016D90TFI02@TSOP48	[SB247-B4806]		
S29AL016D90TFN01@TSOP48	[SB247-B4806]		
S29AL016D90TFN02@TSOP48	[SB247-B4806]		
S29AL016J55TFIR1@TSOP48	[SA247-B4806]		
S29AL016J55TFIR2@TSOP48	[SA247-B4806]		
S29AL016J55TFNR1@TSOP48	[SA247-B4806]		

S29AL016J55TFNR2@TSOP48 [SA247-B4806]
S29AL016J70TFI01@TSOP48 [SA247-B4806]
S29AL016J70TFI02@TSOP48 [SA247-B4806]
S29AL016J70TFI03@TSOP48 [SA247-B4806]
S29AL016J70TFI04@TSOP48 [SA247-B4806]
S29AL016J70TFN01@TSOP48 [SA247-B4806]
S29AL016J70TFN02@TSOP48 [SA247-B4806]
S29AL016M10TAI01@TSOP48 [SB247-B4806]
S29AL016M10TAI02@TSOP48 [SB247-B4806]
S29AL016M10TAIR1@TSOP48 [SB247-B4806]
S29AL016M10TAIR2@TSOP48 [SB247-B4806]
S29AL016M10TFI01@TSOP48 [SB247-B4806]
S29AL016M10TFI02@TSOP48 [SB247-B4806]
S29AL016M10TFIR1@TSOP48 [SB247-B4806]
S29AL016M10TFIR2@TSOP48 [SB247-B4806]
S29AL016M90TAI01@TSOP48 [SB247-B4806]
S29AL016M90TAI02@TSOP48 [SB247-B4806]
S29AL016M90TAIR1@TSOP48 [SB247-B4806]
S29AL016M90TAIR2@TSOP48 [SB247-B4806]
S29AL016M90TFI01@TSOP48 [SB247-B4806]
S29AL016M90TFI02@TSOP48 [SB247-B4806]
S29AL016M90TFIR1@TSOP48 [SB247-B4806]
S29AL016M90TFIR2@TSOP48 [SB247-B4806]
S29AL032D70TAI00@TSOP40 [SA409T-B4002]
S29AL032D70TAI03@TSOP48 [SB247-B4806]
S29AL032D70TAI04@TSOP48 [SB247-B4806]
S29AL032D70TFI00@TSOP40 [SA409T-B4002]
S29AL032D70TFI03@TSOP48 [SB247-B4806]
S29AL032D70TFI04@TSOP48 [SB247-B4806]
S29AL032D90TAI00@TSOP40 [SA409T-B4002]
S29AL032D90TAI03@TSOP48 [SB247-B4806]
S29AL032D90TAI04@TSOP48 [SB247-B4806]
S29AL032D90TAN00@TSOP40 [SA409T-B4002]
S29AL032D90TAN03@TSOP48 [SB247-B4806]
S29AL032D90TAN04@TSOP48 [SB247-B4806]
S29AL032D90TFI00@TSOP40 [SA409T-B4002]
S29AL032D90TFI03@TSOP48 [SB247-B4806]
S29AL032D90TFI04@TSOP48 [SB247-B4806]
S29AL032D90TFN00@TSOP40 [SA409T-B4002]
S29AL032D90TFN03@TSOP48 [SB247-B4806]
S29AL032D90TFN04@TSOP48 [SB247-B4806]
S29AS008J70TFI01@TSOP48 [SB247-B4806]
S29AS008J70TFI02@TSOP48 [SB247-B4806]
S29AS016J70TFI01@TSOP48 [SB247-B4806]
S29AS016J70TFI02@TSOP48 [SB247-B4806]
S29GL016A10TAI01@TSOP48 [SB247-B4806]
S29GL016A10TAI02@TSOP48 [SB247-B4806]
S29GL016A10TAI03@TSOP48 [SB247-B4806]
S29GL016A10TAI04@TSOP48 [SB247-B4806]
S29GL016A10TAIR1@TSOP48 [SB247-B4806]
S29GL016A10TAIR2@TSOP48 [SB247-B4806]
S29GL016A10TAIR3@TSOP48 [SB247-B4806]
S29GL016A10TAIR4@TSOP48 [SB247-B4806]
S29GL016A10TFI01@TSOP48 [SB247-B4806]
S29GL016A10TFI02@TSOP48 [SB247-B4806]
S29GL016A10TFI03@TSOP48 [SB247-B4806]
S29GL016A10TFI04@TSOP48 [SB247-B4806]
S29GL016A10TFIR1@TSOP48 [SB247-B4806]
S29GL016A10TFIR2@TSOP48 [SB247-B4806]

S29GL016A10TFIR3@TSOP48 [SB247-B4806]
S29GL016A10TFIR4@TSOP48 [SB247-B4806]
S29GL016A90TAIR1@TSOP48 [SB247-B4806]
S29GL016A90TAIR2@TSOP48 [SB247-B4806]
S29GL016A90TAIR3@TSOP48 [SB247-B4806]
S29GL016A90TAIR4@TSOP48 [SB247-B4806]
S29GL016A90TFIR1@TSOP48 [SB247-B4806]
S29GL016A90TFIR2@TSOP48 [SB247-B4806]
S29GL016A90TFIR3@TSOP48 [SB247-B4806]
S29GL016A90TFIR4@TSOP48 [SB247-B4806]
S29GL032A10TAIR3@TSOP48 [SB247-B4806]
S29GL032A10TAIR4@TSOP48 [SB247-B4806]
S29GL032A10TFIR3@TSOP48 [SB247-B4806]
S29GL032A10TFIR4@TSOP48 [SB247-B4806]
S29GL032A11TAIR3@TSOP48 [SB247-B4806]
S29GL032A11TAIR4@TSOP48 [SB247-B4806]
S29GL032A11TFIR3@TSOP48 [SB247-B4806]
S29GL032A11TFIR4@TSOP48 [SB247-B4806]
S29GL032A90TAIR3@TSOP48 [SB247-B4806]
S29GL032A90TAIR4@TSOP48 [SB247-B4806]
S29GL032A90TFIR3@TSOP48 [SB247-B4806]
S29GL032A90TFIR4@TSOP48 [SB247-B4806]
S29GL032M10TAIR3@TSOP48 [SB247-B4806]
S29GL032M10TAIR4@TSOP48 [SB247-B4806]
S29GL032M10TBIR3@TSOP48 [SB247-B4806]
S29GL032M10TBIR4@TSOP48 [SB247-B4806]
S29GL032M10TCIR3@TSOP48 [SB247-B4806]
S29GL032M10TCIR4@TSOP48 [SB247-B4806]
S29GL032M10TFIR3@TSOP48 [SB247-B4806]
S29GL032M10TFIR4@TSOP48 [SB247-B4806]
S29GL032M11TAIR3@TSOP48 [SB247-B4806]
S29GL032M11TAIR4@TSOP48 [SB247-B4806]
S29GL032M11TBIR3@TSOP48 [SB247-B4806]
S29GL032M11TBIR4@TSOP48 [SB247-B4806]
S29GL032M11TCIR3@TSOP48 [SB247-B4806]
S29GL032M11TCIR4@TSOP48 [SB247-B4806]
S29GL032M11TFIR3@TSOP48 [SB247-B4806]
S29GL032M11TFIR4@TSOP48 [SB247-B4806]
S29GL032M90TACR0@TSOP40 [SA409T-B4002]
S29GL032M90TACR3@TSOP48 [SB247-B4806]
S29GL032M90TACR4@TSOP48 [SB247-B4806]
S29GL032M90TAIR0@TSOP40 [SA409T-B4002]
S29GL032M90TAIR3@TSOP48 [SB247-B4806]
S29GL032M90TAIR4@TSOP48 [SB247-B4806]
S29GL032M90TBIR3@TSOP48 [SB247-B4806]
S29GL032M90TBIR4@TSOP48 [SB247-B4806]
S29GL032M90TCIR3@TSOP48 [SB247-B4806]
S29GL032M90TCIR4@TSOP48 [SB247-B4806]
S29GL032M90TFCR0@TSOP40 [SA409T-B4002]
S29GL032M90TFCR3@TSOP48 [SB247-B4806]
S29GL032M90TFCR4@TSOP48 [SB247-B4806]
S29GL032M90TFIR0@TSOP40 [SA409T-B4002]
S29GL032M90TFIR3@TSOP48 [SB247-B4806]
S29GL032M90TFIR4@TSOP48 [SB247-B4806]
S29GL032N70TAI03@TSOP48 [SB247-B4806]
S29GL032N70TAI04@TSOP48 [SB247-B4806]
S29GL032N70TAIR3@TSOP48 [SB247-B4806]
S29GL032N70TAIR4@TSOP48 [SB247-B4806]
S29GL032N70TFI03@TSOP48 [SB247-B4806]

S29GL032N70TFI04@TSOP48 [SB247-B4806]
S29GL032N70TFIR3@TSOP48 [SB247-B4806]
S29GL032N70TFIR4@TSOP48 [SB247-B4806]
S29GL032N90TAI03@TSOP48 [SB247-B4806]
S29GL032N90TAI04@TSOP48 [SB247-B4806]
S29GL032N90TAIR3@TSOP48 [SB247-B4806]
S29GL032N90TAIR4@TSOP48 [SB247-B4806]
S29GL032N90TFI03@TSOP48 [SB247-B4806]
S29GL032N90TFI04@TSOP48 [SB247-B4806]
S29GL032N90TFIR3@TSOP48 [SB247-B4806]
S29GL032N90TFIR4@TSOP48 [SB247-B4806]
S29GL064A10TAIR3@TSOP48 [SB247-B4806]
S29GL064A10TAIR4@TSOP48 [SB247-B4806]
S29GL064A10TAIR6@TSOP48 [SB247-B4806]
S29GL064A10TAIR7@TSOP48 [SB247-B4806]
S29GL064A10TAIR8@TSOP48 [SB247-B4806]
S29GL064A10TAIR9@TSOP48 [SB247-B4806]
S29GL064A10TFIR3@TSOP48 [SB247-B4806]
S29GL064A10TFIR4@TSOP48 [SB247-B4806]
S29GL064A10TFIR6@TSOP48 [SB247-B4806]
S29GL064A10TFIR7@TSOP48 [SB247-B4806]
S29GL064A10TFIR8@TSOP48 [SB247-B4806]
S29GL064A10TFIR9@TSOP48 [SB247-B4806]
S29GL064A11TAIR3@TSOP48 [SB247-B4806]
S29GL064A11TAIR4@TSOP48 [SB247-B4806]
S29GL064A11TAIR6@TSOP48 [SB247-B4806]
S29GL064A11TAIR7@TSOP48 [SB247-B4806]
S29GL064A11TAIR8@TSOP48 [SB247-B4806]
S29GL064A11TAIR9@TSOP48 [SB247-B4806]
S29GL064A11TFIR3@TSOP48 [SB247-B4806]
S29GL064A11TFIR4@TSOP48 [SB247-B4806]
S29GL064A11TFIR6@TSOP48 [SB247-B4806]
S29GL064A11TFIR7@TSOP48 [SB247-B4806]
S29GL064A11TFIR8@TSOP48 [SB247-B4806]
S29GL064A11TFIR9@TSOP48 [SB247-B4806]
S29GL064A90TAIR3@TSOP48 [SB247-B4806]
S29GL064A90TAIR4@TSOP48 [SB247-B4806]
S29GL064A90TAIR6@TSOP48 [SB247-B4806]
S29GL064A90TAIR7@TSOP48 [SB247-B4806]
S29GL064A90TAIR8@TSOP48 [SB247-B4806]
S29GL064A90TAIR9@TSOP48 [SB247-B4806]
S29GL064A90TFIR3@TSOP48 [SB247-B4806]
S29GL064A90TFIR4@TSOP48 [SB247-B4806]
S29GL064A90TFIR6@TSOP48 [SB247-B4806]
S29GL064A90TFIR7@TSOP48 [SB247-B4806]
S29GL064A90TFIR8@TSOP48 [SB247-B4806]
S29GL064A90TFIR9@TSOP48 [SB247-B4806]
S29GL064M10TAIR3@TSOP48 [SB247-B4806]
S29GL064M10TAIR4@TSOP48 [SB247-B4806]
S29GL064M10TAIR6@TSOP48 [SB247-B4806]
S29GL064M10TAIR7@TSOP48 [SB247-B4806]
S29GL064M10TBIR6@TSOP48 [SB247-B4806]
S29GL064M10TBIR7@TSOP48 [SB247-B4806]
S29GL064M10TCIR6@TSOP48 [SB247-B4806]
S29GL064M10TCIR7@TSOP48 [SB247-B4806]
S29GL064M10TFIR3@TSOP48 [SB247-B4806]
S29GL064M10TFIR4@TSOP48 [SB247-B4806]
S29GL064M10TFIR6@TSOP48 [SB247-B4806]
S29GL064M10TFIR7@TSOP48 [SB247-B4806]

S29GL064M11TAIR3@TSOP48 [SB247-B4806]
S29GL064M11TAIR4@TSOP48 [SB247-B4806]
S29GL064M11TAIR6@TSOP48 [SB247-B4806]
S29GL064M11TAIR7@TSOP48 [SB247-B4806]
S29GL064M11TBIR6@TSOP48 [SB247-B4806]
S29GL064M11TBIR7@TSOP48 [SB247-B4806]
S29GL064M11TCIR6@TSOP48 [SB247-B4806]
S29GL064M11TCIR7@TSOP48 [SB247-B4806]
S29GL064M11TFIR3@TSOP48 [SB247-B4806]
S29GL064M11TFIR4@TSOP48 [SB247-B4806]
S29GL064M11TFIR6@TSOP48 [SB247-B4806]
S29GL064M11TFIR7@TSOP48 [SB247-B4806]
S29GL064M90TAIR0@TSOP48 [SB247-B4806]
S29GL064M90TAIR3@TSOP48 [SB247-B4806]
S29GL064M90TAIR4@TSOP48 [SB247-B4806]
S29GL064M90TAIR6@TSOP48 [SB247-B4806]
S29GL064M90TAIR7@TSOP48 [SB247-B4806]
S29GL064M90TBIR6@TSOP48 [SB247-B4806]
S29GL064M90TBIR7@TSOP48 [SB247-B4806]
S29GL064M90TCIR6@TSOP48 [SB247-B4806]
S29GL064M90TCIR7@TSOP48 [SB247-B4806]
S29GL064M90TFIR0@TSOP48 [SB247-B4806]
S29GL064M90TFIR3@TSOP48 [SB247-B4806]
S29GL064M90TFIR4@TSOP48 [SB247-B4806]
S29GL064M90TFIR6@TSOP48 [SB247-B4806]
S29GL064M90TFIR7@TSOP48 [SB247-B4806]
S29GL064N70TAI03@TSOP48 [SB247-B4806]
S29GL064N70TAI04@TSOP48 [SB247-B4806]
S29GL064N70TAI06@TSOP48 [SB247-B4806]
S29GL064N70TAI07@TSOP48 [SB247-B4806]
S29GL064N70TAIR3@TSOP48 [SB247-B4806]
S29GL064N70TAIR4@TSOP48 [SB247-B4806]
S29GL064N70TAIR6@TSOP48 [SB247-B4806]
S29GL064N70TAIR7@TSOP48 [SB247-B4806]
S29GL064N70TFI03@TSOP48 [SB247-B4806]
S29GL064N70TFI04@TSOP48 [SB247-B4806]
S29GL064N70TFI06@TSOP48 [SB247-B4806]
S29GL064N70TFI07@TSOP48 [SB247-B4806]
S29GL064N70TFIR3@TSOP48 [SB247-B4806]
S29GL064N70TFIR4@TSOP48 [SB247-B4806]
S29GL064N70TFIR6@TSOP48 [SB247-B4806]
S29GL064N70TFIR7@TSOP48 [SB247-B4806]
S29GL064N90TAI03@TSOP48 [SB247-B4806]
S29GL064N90TAI04@TSOP48 [SB247-B4806]
S29GL064N90TAI06@TSOP48 [SB247-B4806]
S29GL064N90TAI07@TSOP48 [SB247-B4806]
S29GL064N90TAIR3@TSOP48 [SB247-B4806]
S29GL064N90TAIR4@TSOP48 [SB247-B4806]
S29GL064N90TAIR6@TSOP48 [SB247-B4806]
S29GL064N90TAIR7@TSOP48 [SB247-B4806]
S29GL064N90TAIV6@TSOP48 [SB247-B4806]
S29GL064N90TAIV7@TSOP48 [SB247-B4806]
S29GL064N90TFI03@TSOP48 [SB247-B4806]
S29GL064N90TFI04@TSOP48 [SB247-B4806]
S29GL064N90TFI06@TSOP48 [SB247-B4806]
S29GL064N90TFI07@TSOP48 [SB247-B4806]
S29GL064N90TFIR3@TSOP48 [SB247-B4806]
S29GL064N90TFIR4@TSOP48 [SB247-B4806]
S29GL064N90TFIR6@TSOP48 [SB247-B4806]

[illegible]

S29JL032H90TFI01@TSOP48 [SB247-B4806]
S29JL032H90TFI02@TSOP48 [SB247-B4806]
S29JL032H90TFI21@TSOP48 [SB247-B4806]
S29JL032H90TFI22@TSOP48 [SB247-B4806]
S29JL032H90TFI31@TSOP48 [SB247-B4806]
S29JL032H90TFI32@TSOP48 [SB247-B4806]
S29JL032H90TFI41@TSOP48 [SB247-B4806]
S29JL032H90TFI42@TSOP48 [SB247-B4806]
S29JL032J60TFI01@TSOP48 [SB247-B4806]
S29JL032J60TFI02@TSOP48 [SB247-B4806]
S29JL032J60TFI21@TSOP48 [SB247-B4806]
S29JL032J60TFI22@TSOP48 [SB247-B4806]
S29JL032J60TFI31@TSOP48 [SB247-B4806]
S29JL032J60TFI32@TSOP48 [SB247-B4806]
S29JL032J60TFI41@TSOP48 [SB247-B4806]
S29JL032J60TFI42@TSOP48 [SB247-B4806]
S29JL032J70TFI01@TSOP48 [SB247-B4806]
S29JL032J70TFI02@TSOP48 [SB247-B4806]
S29JL032J70TFI21@TSOP48 [SB247-B4806]
S29JL032J70TFI22@TSOP48 [SB247-B4806]
S29JL032J70TFI31@TSOP48 [SB247-B4806]
S29JL032J70TFI32@TSOP48 [SB247-B4806]
S29JL032J70TFI41@TSOP48 [SB247-B4806]
S29JL032J70TFI42@TSOP48 [SB247-B4806]
S29JL064H55TAI00@TSOP48 [SB247-B4806]
S29JL064H55TFI00@TSOP48 [SB247-B4806]
S29JL064H60TAI00@TSOP48 [SB247-B4806]
S29JL064H60TFI00@TSOP48 [SB247-B4806]
S29JL064H70TAI00@TSOP48 [SB247-B4806]
S29JL064H70TAN00@TSOP48 [SB247-B4806]
S29JL064H70TFI00@TSOP48 [SB247-B4806]
S29JL064H70TFN00@TSOP48 [SB247-B4806]
S29JL064H90TAI00@TSOP48 [SB247-B4806]
S29JL064H90TAN00@TSOP48 [SB247-B4806]
S29JL064H90TFI00@TSOP48 [SB247-B4806]
S29JL064H90TFN00@TSOP48 [SB247-B4806]

SST

E(E)PROM/FRAM/NVRAM

SST25LF010@S0IC8(4.0) [SA602A]	SST25LF010@S0IC8(5.4) [SA605B]
SST25LF010@WS0N8 [SA683]	SST25LF010A@S0IC8(4.0) [SA602A]
SST25LF010A@S0IC8(5.4) [SA605B]	SST25LF010A@WS0N8 [SA683]
SST25LF016A@S0IC8(4.0) [SA602A]	SST25LF016A@S0IC8(5.4) [SA023A]
SST25LF016A@WS0N8 [SA683]	SST25LF016B@S0IC8(4.0) [SA602A]
SST25LF016B@S0IC8(5.4) [SA023A]	SST25LF016B@WS0N8 [SA683]
SST25LF020@S0IC8(4.0) [SA602A]	SST25LF020@S0IC8(5.4) [SA605B]
SST25LF020@WS0N8 [SA683]	SST25LF020A@S0IC8(4.0) [SA602A]
SST25LF020A@S0IC8(5.4) [SA605B]	SST25LF020A@WS0N8 [SA683]
SST25LF040@S0IC8(4.0) [SA602A]	SST25LF040@S0IC8(5.4) [SA605B]
SST25LF040@WS0N8 [SA683]	SST25LF040A@S0IC8(4.0) [SA602A]
SST25LF040A@S0IC8(5.4) [SA605B]	SST25LF040A@WS0N8 [SA683]
SST25LF080@S0IC8(4.0) [SA602A]	SST25LF080@S0IC8(5.4) [SA605B]
SST25LF080@WS0N8 [SA683]	SST25LF080A@S0IC8(4.0) [SA602A]
SST25LF080A@S0IC8(5.4) [SA605B]	SST25LF080A@WS0N8 [SA683]
SST25VF010@S0IC8(4.0) [SA602A]	SST25VF010@S0IC8(5.4) [SA605B]
SST25VF010@WS0N8 [SA683]	SST25VF010A@S0IC8(4.0) [SA602A]

SST25VF010A@S0IC8(5.4) [SA605B]
SST25VF016B@S0IC8(4.0) [SA602A]
SST25VF016B@WS0N8 [SA683]
SST25VF020@S0IC8(5.4) [SA605B]
SST25VF020B@S0IC8(4.0) [SA602A]
SST25VF020B@WS0N8 [SA683]
SST25VF032B@S0IC8(4.0) [SA602A]
SST25VF032B@WS0N8 [SA683]
SST25VF040@S0IC8(5.4) [SA605B]
SST25VF040B@S0IC8(4.0) [SA602A]
SST25VF040B@WS0N8 [SA683]
SST25VF064C@WS0N8 [SA684]
SST25VF080@S0IC8(5.4) [SA605B]
SST25VF080B@S0IC8(4.0) [SA602A]
SST25VF080B@WS0N8 [SA683]
SST25VF512@S0IC8(5.4) [SA605B]
SST25VF512A@S0IC8(4.0) [SA602A]
SST25VF512A@WS0N8 [SA683]
SST25WF010@S0IC8(5.4) [SA605B]
SST25WF020@S0IC8(4.0) [SA602A]
SST25WF020@WS0N8 [SA683]
SST25WF040@S0IC8(5.4) [SA605B]
SST25WF080@S0IC8(4.0) [SA602A]
SST25WF080@WS0N8 [SA683]
SST25WF512@S0IC8(5.4) [SA605B]
SST27SF010
SST27SF010@TSOP32 [SA410T-B4001]
SST27SF020@PLCC32 [SA015A1T]
SST27SF256
SST27SF256@VSOP32 [SA620-B4807]
SST27SF512@PLCC32 [SA015A1T]
SST27VF010
SST27VF010@TSOP32 [SA410T-B4001]
SST27VF020@PLCC32 [SA015A1T]
SST27VF040
SST27VF040@TSOP32 [SA410T-B4001]
SST27VF256@PLCC32 [SA015A1T]
SST27VF512
SST27VF512@VSOP32 [SA620-B4807]
SST28EE011@PLCC32 [SA015A1T]
SST28LE011
SST28LE011@TSOP32 [SA410T-B4001]
SST28LF040@PLCC32 [SA015A1T]
SST28SF040
SST28SF040@TSOP32 [SA410T-B4001]
SST28SF040A@PLCC32 [SA015A1T]
SST28SF040A@TSOP32 [SA410T-B4001]
SST28VE011
SST28VE011@TSOP32 [SA410T-B4001]
SST28VF040@PLCC32 [SA015A1T]
SST28VF040A
SST28VF040A@TSOP32 [SA410T-B4001]
SST29EE010
SST29EE010@TSOP32 [SA410T-B4001]
SST29EE020
SST29EE020@TSOP32 [SA410T-B4001]
SST29EE512
SST29EE512@TSOP32 [SA410T-B4001]
SST29LE010

SST25VF010A@WS0N8 [SA683]
SST25VF016B@S0IC8(5.4) [SA023A]
SST25VF020@S0IC8(4.0) [SA602A]
SST25VF020@WS0N8 [SA683]
SST25VF020B@S0IC8(5.4) [SA605B]
SST25VF032B@S0IC16 [SA404]
SST25VF032B@S0IC8(5.4) [SA023A]
SST25VF040@S0IC8(4.0) [SA602A]
SST25VF040@WS0N8 [SA683]
SST25VF040B@S0IC8(5.4) [SA605B]
SST25VF064C@S0IC16 [SA404]
SST25VF080@S0IC8(4.0) [SA602A]
SST25VF080@WS0N8 [SA683]
SST25VF080B@S0IC8(5.4) [SA605B]
SST25VF512@S0IC8(4.0) [SA602A]
SST25VF512@WS0N8 [SA683]
SST25VF512A@S0IC8(5.4) [SA605B]
SST25WF010@S0IC8(4.0) [SA602A]
SST25WF010@WS0N8 [SA683]
SST25WF020@S0IC8(5.4) [SA605B]
SST25WF040@S0IC8(4.0) [SA602A]
SST25WF040@WS0N8 [SA683]
SST25WF080@S0IC8(5.4) [SA605B]
SST25WF512@S0IC8(4.0) [SA602A]
SST25WF512@WS0N8 [SA683]
SST27SF010@PLCC32 [SA015A1T]
SST27SF020
SST27SF020@TSOP32 [SA410T-B4001]
SST27SF256@PLCC32 [SA015A1T]
SST27SF512
SST27SF512@VSOP32 [SA620-B4807]
SST27VF010@PLCC32 [SA015A1T]
SST27VF020
SST27VF020@TSOP32 [SA410T-B4001]
SST27VF040@PLCC32 [SA015A1T]
SST27VF256
SST27VF256@VSOP32 [SA620-B4807]
SST27VF512@PLCC32 [SA015A1T]
SST28EE011
SST28EE011@TSOP32 [SA410T-B4001]
SST28LE011@PLCC32 [SA015A1T]
SST28LF040
SST28LF040@TSOP32 [SA410T-B4001]
SST28SF040@PLCC32 [SA015A1T]
SST28SF040A

SST28VE011@PLCC32 [SA015A1T]
SST28VF040
SST28VF040@TSOP32 [SA410T-B4001]
SST28VF040A@PLCC32 [SA015A1T]

SST29EE010@PLCC32 [SA015A1T]
SST29EE010@VSOP32 [SA620-B4807]
SST29EE020@PLCC32 [SA015A1T]
SST29EE020@VSOP32 [SA620-B4807]
SST29EE512@PLCC32 [SA015A1T]
SST29EE512@VSOP32 [SA620-B4807]
SST29LE010@PLCC32 [SA015A1T]

SST29LE010@TSOP32 [SA410T-B4001]
SST29LE020
SST29LE020@TSOP32 [SA410T-B4001]
SST29LE512
SST29LE512@TSOP32 [SA410T-B4001]
SST29SF010
SST29SF010@VSOP32 [SA620-B4807]
SST29SF020@PLCC32 [SA015A1T]
SST29SF040
SST29SF040@VSOP32 [SA620-B4807]
SST29SF512@PLCC32 [SA015A1T]
SST29VE010
SST29VE010@TSOP32 [SA410T-B4001]
SST29VE020
SST29VE020@TSOP32 [SA410T-B4001]
SST29VE512
SST29VE512@TSOP32 [SA410T-B4001]
SST29VF010
SST29VF010@VSOP32 [SA620-B4807]
SST29VF020@PLCC32 [SA015A1T]
SST29VF040
SST29VF040@VSOP32 [SA620-B4807]
SST29VF512@PLCC32 [SA015A1T]
SST31LF021@VSOP32 [SA620-B4807]
SST31LF041@TSOP40 [SA623-B4002]
SST31LF043@TSOP40 [SA623-B4002]
SST32HF162@TSOP48 [SB247-B4806]
SST34HF1601B@TSOP48 [SB247-B4806]
SST36VF1601@TSOP48 [SB247-B4806]
SST36VF1601C@TSOP48 [SB247-B4806]
SST36VF1601E@TSOP48 [SB247-B4806]
SST36VF1601G@TSOP48 [SB247-B4806]
SST36VF1602@TSOP48 [SB247-B4806]
SST36VF1602C@TSOP48 [SB247-B4806]
SST36VF1602E@TSOP48 [SB247-B4806]
SST36VF1602G@TSOP48 [SB247-B4806]
SST36VF3203@TSOP48 [SB247-B4806]
SST37VF010
SST37VF010@VSOP32 [SA620-B4807]
SST37VF020@PLCC32 [SA015A1T]
SST37VF040
SST37VF040@VSOP32 [SA620-B4807]
SST37VF512@PLCC32 [SA015A1T]
SST38UF166@TSOP48 [SB247-B4806]
SST38VF6401@TSOP48 [SB247-B4806]
SST38VF6403@TSOP48 [SB247-B4806]
SST39LF010@PLCC32 [SA015A1T]
SST39LF016@TSOP40 [SA409T-B4002]
SST39LF020@VSOP32 [SA620-B4807]
SST39LF040@VSOP32 [SA620-B4807]
SST39LF080Q@TSOP40 [SA409T-B4002]
SST39LF100@VSOP40 [SA623-B4002]
SST39LF200@TSOP48 [SA247-B4806]
SST39LF400@TSOP48 [SA247-B4806]
SST39LF512@PLCC32 [SA015A1T]
SST39LF800@TSOP48 [SB247-B4806]
SST39LH010
SST39LH010@TSOP32 [SA410T-B4001]
SST39LH040@PLCC32 [SA015A1T]

SST29LE010@VSOP32 [SA620-B4807]
SST29LE020@PLCC32 [SA015A1T]
SST29LE020@VSOP32 [SA620-B4807]
SST29LE512@PLCC32 [SA015A1T]
SST29LE512@VSOP32 [SA620-B4807]
SST29SF010@PLCC32 [SA015A1T]
SST29SF020
SST29SF020@VSOP32 [SA620-B4807]
SST29SF040@PLCC32 [SA015A1T]
SST29SF512
SST29SF512@VSOP32 [SA620-B4807]
SST29VE010@PLCC32 [SA015A1T]
SST29VE010@VSOP32 [SA620-B4807]
SST29VE020@PLCC32 [SA015A1T]
SST29VE020@VSOP32 [SA620-B4807]
SST29VE512@PLCC32 [SA015A1T]
SST29VE512@VSOP32 [SA620-B4807]
SST29VF010@PLCC32 [SA015A1T]
SST29VF020
SST29VF020@VSOP32 [SA620-B4807]
SST29VF040@PLCC32 [SA015A1T]
SST29VF512
SST29VF512@VSOP32 [SA620-B4807]
SST31LF021E@VSOP32 [SA620-B4807]
SST31LF041A@VSOP32 [SA620-B4807]
SST31LF043A@VSOP32 [SA620-B4807]
SST32HF164@TSOP48 [SB247-B4806]

SST36VF3204@TSOP48 [SB247-B4806]
SST37VF010@PLCC32 [SA015A1T]
SST37VF020
SST37VF020@VSOP32 [SA620-B4807]
SST37VF040@PLCC32 [SA015A1T]
SST37VF512
SST37VF512@VSOP32 [SA620-B4807]
SST38VF166@TSOP48 [SB247-B4806]
SST38VF6402@TSOP48 [SB247-B4806]
SST38VF6404@TSOP48 [SB247-B4806]
SST39LF010@VSOP32 [SA620-B4807]
SST39LF020@PLCC32 [SA015A1T]
SST39LF040@PLCC32 [SA015A1T]
SST39LF080@TSOP40 [SA409T-B4002]

SST39LF160@TSOP48 [SB247-B4806]
SST39LF200A@TSOP48 [SA247-B4806]
SST39LF400A@TSOP48 [SA247-B4806]
SST39LF512@VSOP32 [SA620-B4807]
SST39LF800A@TSOP48 [SB247-B4806]
SST39LH010@PLCC32 [SA015A1T]
SST39LH040
SST39LH040@TSOP32 [SA410T-B4001]

SST39LH512	SST39LH512@PLCC32 [SA015A1T]
SST39LH512@TSOP32 [SA410T-B4001]	SST39SF010
SST39SF010@PLCC32 [SA015A1T]	SST39SF010@VSOP32 [SA620-B4807]
SST39SF010A	SST39SF010A@PLCC32 [SA015A1T]
SST39SF010A@VSOP32 [SA620-B4807]	SST39SF020
SST39SF020@PLCC32 [SA015A1T]	SST39SF020@VSOP32 [SA620-B4807]
SST39SF020A	SST39SF020A@PLCC32 [SA015A1T]
SST39SF020A@VSOP32 [SA620-B4807]	SST39SF020P
SST39SF020P@PLCC32 [SA015A1T]	SST39SF020P@VSOP32 [SA620-B4807]
SST39SF040	SST39SF040@PLCC32 [SA015A1T]
SST39SF040@VSOP32 [SA620-B4807]	SST39SF040P
SST39SF040P@PLCC32 [SA015A1T]	SST39SF040P@VSOP32 [SA620-B4807]
SST39SF512	SST39SF512@PLCC32 [SA015A1T]
SST39SF512@VSOP32 [SA620-B4807]	SST39SF512A
SST39SF512A@PLCC32 [SA015A1T]	SST39SF512A@VSOP32 [SA620-B4807]
SST39VF010	SST39VF010@PLCC32 [SA015A1T]
SST39VF010@VSOP32 [SA620-B4807]	SST39VF016@TSOP40 [SA409T-B4002]
SST39VF016Q@TSOP40 [SA409T-B4002]	
SST39VF020	SST39VF020@PLCC32 [SA015A1T]
SST39VF020@VSOP32 [SA620-B4807]	SST39VF020P
SST39VF020P@PLCC32 [SA015A1T]	SST39VF020P@VSOP32 [SA620-B4807]
SST39VF040	SST39VF040@PLCC32 [SA015A1T]
SST39VF040@VSOP32 [SA620-B4807]	SST39VF040P
SST39VF040P@PLCC32 [SA015A1T]	SST39VF040P@VSOP32 [SA620-B4807]
SST39VF080@TSOP40 [SA409T-B4002]	
SST39VF080Q@TSOP40 [SA409T-B4002]	
SST39VF088@TSOP48 [SB247-B4806]	SST39VF100@VSOP40 [SA623-B4002]
SST39VF160@TSOP48 [SB247-B4806]	
SST39VF160@TSOP48(SLOW) [SA247-B4806]	
SST39VF1601@TSOP48 [SB247-B4806]	
SST39VF1601C@TSOP48 [SB247-B4806]	
SST39VF1602@TSOP48 [SB247-B4806]	
SST39VF1602C@TSOP48 [SB247-B4806]	
SST39VF160Q@TSOP48 [SB247-B4806]	SST39VF1681@TSOP48 [SB247-B4806]
SST39VF1682@TSOP48 [SB247-B4806]	SST39VF200A@TSOP48 [SA247-B4806]
SST39VF320@TSOP48 [SB247-B4806]	SST39VF3201@TSOP48 [SB247-B4806]
SST39VF3201B@TSOP48 [SB247-B4806]	
SST39VF3202@TSOP48 [SB247-B4806]	
SST39VF3202B@TSOP48 [SB247-B4806]	
SST39VF400@TSOP48 [SA247-B4806]	SST39VF400A@TSOP48 [SA247-B4806]
SST39VF400Q@TSOP48 [SA247-B4806]	SST39VF512
SST39VF512@PLCC32 [SA015A1T]	SST39VF512@VSOP32 [SA620-B4807]
SST39VF6401@TSOP48 [SB247-B4806]	
SST39VF6401B@TSOP48 [SB247-B4806]	
SST39VF6402@TSOP48 [SB247-B4806]	
SST39VF6402B@TSOP48 [SB247-B4806]	
SST39VF800@TSOP48 [SB247-B4806]	SST39VF800A@TSOP48 [SB247-B4806]
SST39VF800Q@TSOP48 [SB247-B4806]	SST49LF002@PLCC32 [SA015A1T]
SST49LF002@VSOP32 [SA620-B4807]	SST49LF002A@PLCC32 [SA015A1T]
SST49LF002A@VSOP32 [SA620-B4807]	SST49LF002B@PLCC32 [SA015A1T]
SST49LF003A@PLCC32 [SA015A1T]	SST49LF003A@VSOP32 [SA620-B4807]
SST49LF003B@PLCC32 [SA015A1T]	SST49LF004@PLCC32 [SA015A1T]
SST49LF004@VSOP32 [SA620-B4807]	SST49LF004A@PLCC32 [SA015A1T]
SST49LF004A@VSOP32 [SA620-B4807]	SST49LF004B@PLCC32 [SA015A1T]
SST49LF004B@VSOP32 [SA620-B4807]	
SST49LF004B@VSOP40 [SA409T-B4002]	
SST49LF008@PLCC32 [SA015A1T]	SST49LF008@VSOP32 [SA620-B4807]
SST49LF008A@PLCC32 [SA015A1T]	
SST49LF008A@TSOP40 [SA409T-B4002]	

SST49LF008A@VSOP32 [SA620-B4807]
SST49LF020@VSOP32 [SA620-B4807]
SST49LF020A@VSOP32 [SA620-B4807]
SST49LF030A@VSOP32 [SA620-B4807]
SST49LF040@VSOP32 [SA620-B4807]
SST49LF040A@VSOP32 [SA620-B4807]
SST49LF040B@TSOP40 [SA409T-B4002]
SST49LF040B@VSOP32 [SA620-B4807]
SST49LF080A@VSOP32 [SA620-B4807]

SST49LF020@PLCC32 [SA015A1T]
SST49LF020A@PLCC32 [SA015A1T]
SST49LF030A@PLCC32 [SA015A1T]
SST49LF040@PLCC32 [SA015A1T]
SST49LF040A@PLCC32 [SA015A1T]
SST49LF040B@PLCC32 [SA015A1T]

SST49LF080A@PLCC32 [SA015A1T]

MICROCONTROLLER

SST89C54
SST89C54@TQFP44 [SA245A-B4805]
SST89C58@PLCC44 [SA244]
SST89E516RD
SST89E516RD@TQFP44 [SA245A-B4805]
SST89E516RD2
SST89E516RD2@TQFP44 [SA245A-B4805]
SST89E52RC
SST89E52RC@TQFP44 [SA245A-B4805]
SST89E52RD@PLCC44 [SA244]
SST89E52RD2
SST89E52RD2@TQFP44 [SA245A-B4805]
SST89E54RC
SST89E54RC@TQFP44 [SA245A-B4805]
SST89E54RD@PLCC44 [SA244]
SST89E54RD2
SST89E54RD2@TQFP44 [SA245A-B4805]
SST89E554RC
SST89E554RC@TQFP44 [SA245A-B4805]
SST89E564
SST89E564@TQFP44 [SA245A-B4805]
SST89E564RD@PLCC44 [SA244]
SST89E564RD@TQFP44 [SA245A-B4805]
SST89E58RD
SST89E58RD@TQFP44 [SA245A-B4805]
SST89E58RD2@PLCC44 [SA244]
SST89E58RD2@TQFP44 [SA245A-B4805]
SST89V516RD
SST89V516RD@TQFP44 [SA245A-B4805]
SST89V516RD2
SST89V516RD2@TQFP44 [SA245A-B4805]
SST89V52RD
SST89V52RD@TQFP44 [SA245A-B4805]
SST89V52RD2@PLCC44 [SA244]
SST89V52RD2@TQFP44 [SA245A-B4805]
SST89V54RD2
SST89V54RD2@TQFP44 [SA245A-B4805]
SST89V554RC
SST89V554RC@TQFP44 [SA245A-B4805]
SST89V564
SST89V564@TQFP44 [SA245A-B4805]
SST89V564RD@PLCC44 [SA244]
SST89V564RD@TQFP44 [SA245A-B4805]
SST89V58RD2
SST89V58RD2@TQFP44 [SA245A-B4805]

SST89C54@PLCC44 [SA244]
SST89C58
SST89C58@TQFP44 [SA245A-B4805]
SST89E516RD@PLCC44 [SA244]

SST89E516RD2@PLCC44 [SA244]

SST89E52RC@PLCC44 [SA244]
SST89E52RD
SST89E52RD@TQFP44 [SA245A-B4805]
SST89E52RD2@PLCC44 [SA244]

SST89E54RC@PLCC44 [SA244]
SST89E54RD
SST89E54RD@TQFP44 [SA245A-B4805]
SST89E54RD2@PLCC44 [SA244]

SST89E554RC@PLCC44 [SA244]

SST89E564@PLCC44 [SA244]
SST89E564RD

SST89E58RD@PLCC44 [SA244]
SST89E58RD2

SST89V516RD@PLCC44 [SA244]

SST89V516RD2@PLCC44 [SA244]

SST89V52RD@PLCC44 [SA244]
SST89V52RD2

SST89V54RD2@PLCC44 [SA244]

SST89V554RC@PLCC44 [SA244]

SST89V564@PLCC44 [SA244]
SST89V564RD

SST89V58RD2@PLCC44 [SA244]

SST-CUSTOMER

E(E)PROM/FRAM/NVRAM

SST39SF010A@PLCC32 [SA015A1T]

SST39SF020A@PLCC32 [SA015A1T]

ST

E(E)PROM/FRAM/NVRAM

ET2716

ETC2732

M24128@MLP8 [SA724]

M24128@TSOP8 [SA026-B3201]

M24164@SOIC8 [SA602A]

M24256@MLP8 [SA724]

M24256@SOIC8[5.5] [SA605B]

M24256BF@MLP8 [SA724]

M24256BF@SOIC8[5.5] [SA605B]

M24256BR

M24256BR@SOIC8[3.9] [SA602A]

M24256BR@TSOP8 [SA026-B3201]

M24256BW@MLP8 [SA724]

M24256BW@SOIC8[5.5] [SA605B]

M24512

M24512@TSOP8 [SA026-B3201]

M24C01@MLP8 [SA724]

M24C01R

M24C01R@SOIC8 [SA602A]

M24C01W

M24C01W@SOIC8 [SA602A]

M24C02

M24C02@SOIC8 [SA602A]

M24C02R@MLP8 [SA724]

M24C02R@TSOP8 [SA026-B3201]

M24C02W@MLP8 [SA724]

M24C02W@TSOP8 [SA026-B3201]

M24C04@MLP8 [SA724]

M24C04R

M24C04R@SOIC8 [SA602A]

M24C04W

M24C04W@SOIC8 [SA602A]

M24C08

M24C08@MSOP8 [SA695A]

M24C08@TSOP8 [SA026-B3201]

M24C08R@MLP8 [SA724]

M24C08R@SOIC8 [SA602A]

M24C08W

M24C08W@MSOP8 [SA695A]

M24C08W@TSOP8 [SA026-B3201]

M24C128(MN)@SOIC8 [SA605B]

M24C128@MLP8 [SA724]

M24C128B(MN)@SOIC8 [SA605B]

M24C128B@MLP8 [SA724]

M24C16@MLP8 [SA724]

M24C16R

M24C16R@SOIC8 [SA602A]

M24C16W

ETC2716

M24128

M24128@SOIC8 [SA602A]

M24164

M24256

M24256@SOIC8[3.9] [SA602A]

M24256@TSOP8 [SA026-B3201]

M24256BF@SOIC8[3.9] [SA602A]

M24256BF@TSOP8 [SA026-B3201]

M24256BR@MLP8 [SA724]

M24256BR@SOIC8[5.5] [SA605B]

M24256BW

M24256BW@SOIC8[3.9] [SA602A]

M24256BW@TSOP8 [SA026-B3201]

M24512@SOIC8 [SA605B]

M24C01

M24C01@SOIC8 [SA602A]

M24C01R@MLP8 [SA724]

M24C01R@TSOP8 [SA026-B3201]

M24C01W@MLP8 [SA724]

M24C01W@TSOP8 [SA026-B3201]

M24C02@MLP8 [SA724]

M24C02R

M24C02R@SOIC8 [SA602A]

M24C02W

M24C02W@SOIC8 [SA602A]

M24C04

M24C04@SOIC8 [SA602A]

M24C04R@MLP8 [SA724]

M24C04R@TSOP8 [SA026-B3201]

M24C04W@MLP8 [SA724]

M24C04W@TSOP8 [SA026-B3201]

M24C08@MLP8 [SA724]

M24C08@SOIC8 [SA602A]

M24C08R

M24C08R@MSOP8 [SA695A]

M24C08R@TSOP8 [SA026-B3201]

M24C08W@MLP8 [SA724]

M24C08W@SOIC8 [SA602A]

M24C128(BN)

M24C128(MW)@SOIC8 [SA602A]

M24C128B(BN)

M24C128B(MW)@SOIC8 [SA602A]

M24C16

M24C16@SOIC8 [SA602A]

M24C16R@MLP8 [SA724]

M24C16R@TSOP8 [SA026-B3201]

M24C16W@MLP8 [SA724]

M24C16W@S0IC8 [SA602A]	M24C16W@TSOP8 [SA026-B3201]
M24C256(BN)	M24C256(MN)@S0IC8 [SA605B]
M24C256(MW)@S0IC8 [SA602A]	M24C256@MLP8 [SA724]
M24C256A(BN)	M24C256A(MN)@S0IC8 [SA605B]
M24C256A(MW)@S0IC8 [SA602A]	M24C256A@MLP8 [SA724]
M24C256B(BN)	M24C256B(MN)@S0IC8 [SA605B]
M24C256B(MW)@S0IC8 [SA602A]	M24C256B@MLP8 [SA724]
M24C256W(BN)	M24C256W(MN)@S0IC8 [SA605B]
M24C256W(MW)@S0IC8 [SA602A]	M24C256W@MLP8 [SA724]
M24C32(BN)	M24C32(DL)@TSSOP14 [SA026-B3201]
M24C32(DW)@TSSOP8 [SA026-B3201]	M24C32(MN)@S0IC8 [SA605B]
M24C32(MW)@S0IC8 [SA602A]	M24C32@MLP8 [SA724]
M24C32W(BN)	
M24C32W(DL)@TSSOP14 [SA026-B3201]	M24C32W(MN)@S0IC8 [SA605B]
M24C32W(DW)@TSSOP8 [SA026-B3201]	M24C32W@MLP8 [SA724]
M24C32W(MW)@S0IC8 [SA602A]	M24C64(DL)@TSSOP14 [SA026-B3201]
M24C64(BN)	M24C64(MN)@S0IC8 [SA605B]
M24C64(DW)@TSSOP8 [SA026-B3201]	M24C64@MLP8 [SA724]
M24C64(MW)@S0IC8 [SA602A]	
M24C64W(BN)	
M24C64W(DL)@TSSOP14 [SA026-B3201]	M24C64W(MN)@S0IC8 [SA605B]
M24C64W(DW)@TSSOP8 [SA026-B3201]	M24C64W@MLP8 [SA724]
M24C64W(MW)@S0IC8 [SA602A]	M24CL04B@MLP8 [SA724]
M24CL04B	M24CL04B@TSOP8 [SA026-B3201]
M24CL04B@S0IC8 [SA602A]	M24E32(BN)
M24E16	M24E32(MN)@S0IC8 [SA605B]
M24E32(DW)@TSSOP8 [SA026-B3201]	M24M01@LGA8 [SA684]
M24E32(MW)@S0IC8 [SA602A]	M24W01
M24M01@S0IC8 [SA602A]	M24W02
M24W01@S0IC8 [SA602A]	M24W04
M24W02@S0IC8 [SA602A]	M24W08
M24W04@S0IC8 [SA602A]	M24W16
M24W08@S0IC8 [SA602A]	M25C01
M24W16@S0IC8 [SA602A]	M25C04
M25C02	M25C16
M25C08	M25P05@S0IC8 [SA602A]
M25E16	M25P05-A@S0IC8 [SA602A]
M25P05@VQFPN8 [SA683]	M25P05-A@VDFPN8 [SA683]
M25P05-A@TSSOP8 [SA026-B3201]	M25P10@VQFPN8 [SA683]
M25P10@S0IC8 [SA602A]	M25P10-A@VFQFPN8 [SA683]
M25P10-A@S0IC8 [SA602A]	M25P128@VDFPN8 [SA684]
M25P128@S0IC16 [SA404]	M25P16@S0IC8(150mil) [SA602A]
M25P16@S0IC16 [SA404]	M25P16@VDFPN8 [SA684]
M25P16@S0IC8(200mil) [SA605B]	M25P20@S0IC8 [SA602A]
M25P16@VFQFPN8 [SA683]	M25P32(Fast Mode)@S0IC16 [SA404]
M25P20@VFQFPN8 [SA683]	
M25P32(Fast Mode)@S0IC8(150mil) [SA605B]	M25P32@S0IC16 [SA404]
M25P32(Fast Mode)@S0IC8(200mil) [SA683]	M25P32@VDFPN8 [SA684]
M25P32(Fast Mode)@VQFPN8 [SA684]	M25P40@S0IC8 [SA602A]
M25P32@S0IC8 [SA605B]	M25P64(Fast Mode)@S0IC16 [SA404]
M25P32@VFQFPN8 [SA683]	M25P64@S0IC16 [SA404]
M25P40@VFQFPN8 [SA683]	M25P80@S0IC16 [SA404]
M25P64(Fast Mode)@VDFPN8 [SA684]	M25P80@VFQFPN8 [SA683]
M25P64@VDFPN8 [SA684]	M25PE10@VQFPN8 [SA683]
M25P80@S0IC8 [SA605B]	M25PE16@VQFPN8 [SA683]
M25PE10@S0IC8 [SA602A]	M25PE20@VQFPN8 [SA683]
M25PE16@S0IC8 [SA605B]	M25PE40@VQFPN8 [SA683]
M25PE20@S0IC8 [SA602A]	
M25PE40@S0IC8 [SA605B]	

M25PE80@S0IC8 [SA605B]
M25PX32@S0IC16 [SA404]
M25PX32@VFQFPN8 [SA683]
M25PX64@VDFPN8 [SA684]
M25W02
M25W08
M25W166
M2716
M27256
M2732A
M2764
M27C1000
M27C1000@TSOP32 [SA410T-B4001]
M27C1001@PLCC32 [SA015A1T]
M27C1024
M27C128B
M27C160
M27C160@PSOP44 [SA638]
M27C160K@PLCC44 [SA244]
M27C2001
M27C2001@TSOP32 [SA410T-B4001]
M27C202@PLCC44 [SA244]
M27C256B
M27C32
M27C322@SDIP42 [SA028]
M27C4001
M27C4001@TSOP32 [SA410T-B4001]
M27C4002@PLCC44 [SA244]
M27C405@PLCC32 [SA015A1T]
M27C512
M27C513
M27C516@PLCC44 [SA244]
M27C64A@PLCC32 [SA015A1T]
M27C800@PLCC44 [SA244]
M27C801
M27C801@TSOP32 [SA410T-B4001]
M27HC641@PLCC28 [SA008A]
M27HC642@PLCC28 [SA008A]
M27V101@PLCC32 [SA015A1T]
M27V102
M27V160
M27V160@PSOP44 [SA638]
M27V160K@PLCC44 [SA244]
M27V201
M27V201@TSOP32 [SA410T-B4001]
M27V322
M27V401
M27V401@TSOP32 [SA410T-B4001]
M27V402@PLCC44 [SA244]
M27V405
M27V405@TSOP32 [SA410T-B4001]
M27V512@PLCC32 [SA015A1T]
M27V800
M27V801
M27V801@TSOP32 [SA410T-B4001]
M27W016@PSOP44 [SA638]
M27W016@TSOP48 [SB247-B4806]
M27W032@TSOP48 [SB247-B4806]
M27W064@TSOP48 [SB247-B4806]

M25PE80@VQFPN8 [SA683]
M25PX32@S0IC8 [SA605B]
M25PX64@S0IC16 [SA404]
M25W01
M25W04
M25W16
M27128A
M2716F1
M27256A
M27512
M2764A
M27C1000@PLCC32 [SA015A1T]
M27C1001
M27C1001@TSOP32 [SA410T-B4001]
M27C1024@PLCC44 [SA244]
M27C16
M27C160@PLCC44 [SA244]
M27C160K
M27C160K@PSOP44 [SA638]
M27C2001@PLCC32 [SA015A1T]
M27C202
M27C202@VSOP40 [SA623-B4002]
M27C256B@PLCC32 [SA015A1T]
M27C322
M27C400
M27C4001@PLCC32 [SA015A1T]
M27C4002
M27C405
M27C405@TSOP32 [SA410T-B4001]
M27C512@PLCC32 [SA015A1T]
M27C516
M27C64A
M27C800
M27C800@PSOP44 [SA638]
M27C801@PLCC32 [SA015A1T]
M27HC641
M27HC642
M27V101
M27V101@TSOP32 [SA410T-B4001]
M27V102@PLCC44 [SA244]
M27V160@PLCC44 [SA244]
M27V160K
M27V160K@PSOP44 [SA638]
M27V201@PLCC32 [SA015A1T]
M27V256
M27V322@SDIP42 [SA028]
M27V401@PLCC32 [SA015A1T]
M27V402
M27V402@TSOP40 [SA409T-B4002]
M27V405@PLCC32 [SA015A1T]
M27V512
M27V512@TSOP28 [SA430T-B4003]
M27V800@PLCC44 [SA244]
M27V801@PLCC32 [SA015A1T]
M27W016
M27W016@SDIP42 [SA028]
M27W032@PSOP44 [SA638]
M27W064@PSOP44 [SA638]
M27W101

M27W101@PLCC32 [SA015A1T]	M27W101@TSOP32 [SA410T-B4001]
M27W102	M27W102@PLCC44 [SA244]
M27W160	M27W160@PLCC44 [SA244]
M27W160@PSOP44 [SA638]	M27W201
M27W201@PLCC32 [SA015A1T]	M27W201@TSOP32 [SA410T-B4001]
M27W202	M27W202@PLCC44 [SA244]
M27W202@VSOP40 [SA623-B4002]	M27W400
M27W400@PLCC44 [SA244]	M27W401
M27W401@PLCC32 [SA015A1T]	M27W401@TSOP32 [SA410T-B4001]
M27W402	M27W402@PLCC44 [SA244]
M27W402@TSOP40 [SA409T-B4002]	M27W512
M27W512@PLCC32 [SA015A1T]	M27W512@TSOP28 [SA430T-B4003]
M27W800	M27W800@PLCC44 [SA244]
M27W801	M27W801@PLCC32 [SA015A1T]
M27W801@TSOP32 [SA410T-B4001]	M28010
M28010@PLCC32 [SA015A1T]	M28010@TSOP32 [SA410T-B4001]
M28010R	M28010R@PLCC32 [SA015A1T]
M28010R@TSOP32 [SA410T-B4001]	M28010W
M28010W@PLCC32 [SA015A1T]	M28010W@TSOP32 [SA410T-B4001]
M28256	M28256@PLCC32 [SA015A1T]
M28256@TSOP28 [SA430T-B4003]	M28C010
M28C010@PLCC32 [SA015A1T]	M28C010@TSOP32 [SA410T-B4001]
M28C010R	M28C010R@PLCC32 [SA015A1T]
M28C010R@TSOP32 [SA410T-B4001]	M28C010W
M28C010W@PLCC32 [SA015A1T]	M28C010W@TSOP32 [SA410T-B4001]
M28C16@PLCC32 [SA015A1T]	M28C17@S0IC28 [SA404]
M28C64	M28C64@PLCC32 [SA015A1T]
M28C64@TSOP28 [SA430T-B4003]	M28C64C
M28C64C@PLCC32 [SA015A1T]	M28C64C@S0IC28 [SA404]
M28C64C@TSOP28 [SA430T-B4003]	M28C64X
M28C64X@PLCC32 [SA015A1T]	M28C64X@TSOP28 [SA430T-B4003]
M28F101	
M28F101(REVERSE)@TSOP32 [SA410T-B4001]	
M28F101@PLCC32 [SA015A1T]	M28F101@TSOP32 [SA410T-B4001]
M28F102	M28F102@PLCC44 [SA244]
M28F102@TSOP40 [SA623-B4002]	M28F151
M28F151(REVERSE)@TSOP32 [SA410T-B4001]	
M28F151@PLCC32 [SA015A1T]	M28F151@TSOP32 [SA410T-B4001]
M28F201	
M28F201(REVERSE)@TSOP32 [SA410T-B4001]	
M28F201@PLCC32 [SA015A1T]	M28F201@TSOP32 [SA410T-B4001]
M28F210@PSOP44 [SA638]	M28F210@TSOP48 [SB247-B4806]
M28F211@TSOP40 [SA409T-B4002]	M28F220@PSOP44 [SA638]
M28F220@TSOP48 [SB247-B4806]	M28F221@TSOP40 [SA409T-B4002]
M28F256	
M28F256(REVERSE)@TSOP32 [SA410T-B4001]	
M28F256@PLCC32 [SA015A1T]	M28F256@TSOP32 [SA410T-B4001]
M28F411@TSOP40 [SA409T-B4002]	M28F421@TSOP40 [SA409T-B4002]
M28F512	
M28F512(REVERSE)@TSOP32 [SA410T-B4001]	
M28F512@PLCC32 [SA015A1T]	M28F512@TSOP32 [SA410T-B4001]
M28LV64	M28LV64@PLCC32 [SA015A1T]
M28LV64@TSOP28 [SA430T-B4003]	M28V411@TSOP40 [SA409T-B4002]
M28V421@TSOP40 [SA409T-B4002]	M28W160B@TSOP48 [SB247-B4806]
M28W160BB@TSOP48 [SB247-B4806]	M28W160BT@TSOP48 [SB247-B4806]
M28W160CB@TSOP48 [SB247-B4806]	M28W160CT@TSOP48 [SB247-B4806]
M28W160ECB@TSOP48 [SB247-B4806]	M28W160ECT@TSOP48 [SB247-B4806]
M28W160T@TSOP48 [SB247-B4806]	M28W320CB@TSOP48 [SB247-B4806]
M28W320CT@TSOP48 [SB247-B4806]	M28W320ECB@TSOP48 [SB247-B4806]

M28W320ECT@TSOP48 [SB247-B4806]
M28W320FCT@TSOP48 [SB247-B4806]
M28W640CT@TSOP48 [SB247-B4806]
M28W640ECT@TSOP48 [SB247-B4806]
M28W640FCT@TSOP48 [SB247-B4806]
M28W640HCT@TSOP48 [SB247-B4806]
M28W800BB@TSOP48 [SB247-B4806]
M28W800CB@TSOP48 [SB247-B4806]
M28W800T@TSOP48 [SB247-B4806]
M29DW323DT@TSOP48 [SB247-B4806]
M29DW324DT@TSOP48 [SB247-B4806]
M29DW640F@TSOP48 [SB247-B4806]
M29F002B
M29F002B@TSOP32 [SA410T-B4001]
M29F002BB@PLCC32 [SA015A1T]
M29F002BNT
M29F002BNT@TSOP32 [SA410T-B4001]
M29F002BT@PLCC32 [SA015A1T]
M29F002T
M29F002T@TSOP32 [SA410T-B4001]
M29F010B@PLCC32 [SA015A1T]
M29F016B@PSOP44 [SA638]
M29F016D@PSOP44 [SA638]
M29F032D@TSOP40 [SA409T-B4002]
M29F040@PLCC32 [SA015A1T]
M29F040B
M29F040B@TSOP32 [SA410T-B4001]
M29F080A@TSOP40 [SA409T-B4002]
M29F080D@TSOP40 [SA409T-B4002]
M29F100B@TSOP48 [SB247-B4806]
M29F100T@TSOP48 [SB247-B4806]
M29F102B@TSOP40 [SA623-B4002]
M29F102BB@TSOP40 [SA623-B4002]
M29F160BT@TSOP48 [SB247-B4806]
M29F160FT@TSOP48 [SA247-B4806]
M29F200B@TSOP48 [SB247-B4806]
M29F200BB@TSOP48 [SB247-B4806]
M29F200BT@TSOP48 [SB247-B4806]
M29F200FB@TSOP48 [SA247-B4806]
M29F200FT@TSOP48 [SA247-B4806]
M29F200T@TSOP48 [SB247-B4806]
M29F400B@TSOP48 [SB247-B4806]
M29F400BB@TSOP48 [SB247-B4806]
M29F400BT@TSOP48 [SB247-B4806]
M29F400FB@TSOP48 [SA247-B4806]
M29F400FT@TSOP48 [SA247-B4806]
M29F400T@TSOP48 [SB247-B4806]
M29F512B@TSOP32 [SA620-B4807]
M29F800AB@TSOP48 [SB247-B4806]
M29F800AT@TSOP48 [SB247-B4806]
M29F800DB@TSOP48 [SB247-B4806]
M29F800DT@TSOP48 [SB247-B4806]
M29F800FB@TSOP48 [SA247-B4806]
M29F800FT@TSOP48 [SA247-B4806]
M29KW032E@TSOP48 [SB247-B4806]
M29V040@PLCC32 [SA015A1T]
M29W004B@TSOP40 [SA409T-B4002]
M29W004BT@TSOP40 [SA409T-B4002]
M29W008AB@TSOP40 [SA409T-B4002]

M28W320FCB@TSOP48 [SB247-B4806]
M28W640CB@TSOP48 [SB247-B4806]
M28W640ECB@TSOP48 [SB247-B4806]
M28W640FCB@TSOP48 [SB247-B4806]
M28W640HCB@TSOP48 [SB247-B4806]
M28W800B@TSOP48 [SB247-B4806]
M28W800BT@TSOP48 [SB247-B4806]
M28W800CT@TSOP48 [SB247-B4806]
M29DW323DB@TSOP48 [SB247-B4806]
M29DW324DB@TSOP48 [SB247-B4806]
M29DW640D@TSOP48 [SB247-B4806]
M29DW641F@TSOP48 [SB247-B4806]
M29F002B@PLCC32 [SA015A1T]
M29F002BB
M29F002BB@TSOP32 [SA410T-B4001]
M29F002BNT@PLCC32 [SA015A1T]
M29F002BT
M29F002BT@TSOP32 [SA410T-B4001]
M29F002T@PLCC32 [SA015A1T]
M29F010B
M29F010B@TSOP32 [SA410T-B4001]
M29F016B@TSOP40 [SA409T-B4002]
M29F016D@TSOP40 [SA409T-B4002]
M29F040
M29F040@TSOP32 [SA410T-B4001]
M29F040B@PLCC32 [SA015A1T]
M29F080A@PSOP44 [SA638]
M29F080D@PSOP44 [SA638]
M29F100B@PSOP44 [SA638]
M29F100T@PSOP44 [SA638]
M29F102B@PLCC44 [SA244]
M29F102BB@PLCC44 [SA244]
M29F160BB@TSOP48 [SB247-B4806]
M29F160FB@TSOP48 [SA247-B4806]
M29F200B@PSOP44 [SA638]
M29F200BB@PSOP44 [SA638]
M29F200BT@PSOP44 [SA638]
M29F200FB@PSOP44 [SA638]
M29F200FT@PSOP44 [SA638]
M29F200T@PSOP44 [SA638]
M29F400B@PSOP44 [SA638]
M29F400BB@PSOP44 [SA638]
M29F400BT@PSOP44 [SA638]
M29F400FB@PSOP44 [SA638]
M29F400FT@PSOP44 [SA638]
M29F400T@PSOP44 [SA638]
M29F512B@PLCC32 [SA015A1T]
M29F800AB@PSOP44 [SA638]
M29F800AT@PSOP44 [SA638]
M29F800DB@PSOP44 [SA638]
M29F800DT@PSOP44 [SA638]
M29F800FB@PSOP44 [SA638]
M29F800FT@PSOP44 [SA638]
M29KW016E@TSOP48 [SB247-B4806]
M29KW064E@TSOP48 [SB247-B4806]
M29V040@TSOP32 [SA410T-B4001]
M29W004BB@TSOP40 [SA409T-B4002]
M29W004T@TSOP40 [SA409T-B4002]
M29W008AT@TSOP40 [SA409T-B4002]

M29W008B@TSOP40 [SA409T-B4002]	M29W008T@TSOP40 [SA409T-B4002]
M29W010B@PLCC32 [SA015A1T]	M29W010B@TSOP32 [SA410T-B4001]
M29W017D@TSOP40 [SA409T-B4002]	M29W022BB
M29W022BB@PLCC32 [SA015A1T]	M29W022BB@TSOP32 [SA410T-B4001]
M29W022BT	M29W022BT@PLCC32 [SA015A1T]
M29W022BT@TSOP32 [SA410T-B4001]	M29W040@PLCC32 [SA015A1T]
M29W040@TSOP32 [SA410T-B4001]	M29W040B@PLCC32 [SA015A1T]
M29W040B@TSOP32 [SA410T-B4001]	M29W102BB@TSOP40 [SA623-B4002]
M29W102BT@TSOP40 [SA623-B4002]	M29W116BB@TSOP40 [SA409T-B4002]
M29W116BT@TSOP40 [SA409T-B4002]	M29W160BB@PSOP44 [SA638]
M29W160BB@TSOP48 [SB247-B4806]	M29W160BT@PSOP44 [SA638]
M29W160BT@TSOP48 [SB247-B4806]	M29W160DB@PSOP44 [SA638]
M29W160DB@TSOP48 [SB247-B4806]	M29W160DT@PSOP44 [SA638]
M29W160DT@TSOP48 [SB247-B4806]	M29W160EB@PSOP44 [SA638]
M29W160EB@TSOP48 [SB247-B4806]	M29W160ET@PSOP44 [SA638]
M29W160ET@TSOP48 [SB247-B4806]	M29W160FB@TSOP48 [SB247-B4806]
M29W160FT@TSOP48 [SB247-B4806]	M29W200BB@PSOP44 [SA638]
M29W200BB@TSOP48 [SB247-B4806]	M29W200BT@PSOP44 [SA638]
M29W200BT@TSOP48 [SB247-B4806]	M29W320DB@TSOP48 [SB247-B4806]
M29W320DT@TSOP48 [SB247-B4806]	M29W320EB@TSOP48 [SB247-B4806]
M29W320ET@TSOP48 [SB247-B4806]	M29W320FB@TSOP48 [SB247-B4806]
M29W320FT@TSOP48 [SB247-B4806]	M29W400B@PSOP44 [SA638]
M29W400B@TSOP48 [SB247-B4806]	M29W400BB@PSOP44 [SA638]
M29W400BB@TSOP48 [SB247-B4806]	M29W400BT@PSOP44 [SA638]
M29W400BT@TSOP48 [SB247-B4806]	M29W400DB@PSOP44 [SA638]
M29W400DB@TSOP48 [SB247-B4806]	M29W400DT@PSOP44 [SA638]
M29W400DT@TSOP48 [SB247-B4806]	M29W400T@PSOP44 [SA638]
M29W400T@TSOP48 [SB247-B4806]	M29W512B@PLCC32 [SA015A1T]
M29W512B@TSOP32 [SA620-B4807]	M29W640DB@TSOP48 [SB247-B4806]
M29W640DT@TSOP48 [SB247-B4806]	
M29W640FB(Q_Word)@TSOP48 [SB247-B4806]	
M29W640FB@TSOP48 [SB247-B4806]	
M29W640FT(Q_Word)@TSOP48 [SB247-B4806]	
M29W640FT@TSOP48 [SB247-B4806]	
M29W640GB(Mirror)@TSOP48 [SB247-B4806]	
M29W640GB(Q_Word)@TSOP48 [SB247-B4806]	
M29W640GH(Mirror)@TSOP48 [SB247-B4806]	
M29W640GH(Q_Word)@TSOP48 [SB247-B4806]	
M29W640GL(Mirror)@TSOP48 [SB247-B4806]	
M29W640GL(Q_Word)@TSOP48 [SB247-B4806]	
M29W640GSB(Mirror)@TSOP48 [SB247-B4806]	
M29W640GSB(Q_Word)@TSOP48 [SB247-B4806]	
M29W640GSH(Mirror)@TSOP48 [SB247-B4806]	
M29W640GSH(Q_Word)@TSOP48 [SB247-B4806]	
M29W640GSL(Mirror)@TSOP48 [SB247-B4806]	
M29W640GSL(Q_Word)@TSOP48 [SB247-B4806]	
M29W640GST(Mirror)@TSOP48 [SB247-B4806]	
M29W640GST(Q_Word)@TSOP48 [SB247-B4806]	
M29W640GT(Mirror)@TSOP48 [SB247-B4806]	
M29W640GT(Q_Word)@TSOP48 [SB247-B4806]	
M29W641DH@TSOP48 [SB247-B4806]	M29W641DL@TSOP48 [SB247-B4806]
M29W800AB@PSOP44 [SA638]	M29W800AB@TSOP48 [SB247-B4806]
M29W800AT@PSOP44 [SA638]	M29W800AT@TSOP48 [SB247-B4806]
M29W800B@PSOP44 [SA638]	M29W800B@TSOP48 [SB247-B4806]
M29W800DB@PSOP44 [SA638]	M29W800DB@TSOP48 [SB247-B4806]
M29W800DT@PSOP44 [SA638]	M29W800DT@TSOP48 [SB247-B4806]
M29W800T@PSOP44 [SA638]	M29W800T@TSOP48 [SB247-B4806]
M34C02	M34C02@MSOP8 [SA724]
M34C02@S0IC8 [SA602A]	M34C02@TSOP8

M34D32
M34D32@TSSOP8 [SA026-B3201]
M34D64@S0IC8 [SA602A]
M34E02
M34E02@S0IC8 [SA602A]
M35080
M45PE10@S0IC8 [SA602A]
M45PE16@S0IC8 [SA605B]
M45PE20@S0IC8 [SA602A]
M45PE40@S0IC8 [SA605B]
M45PE80@S0IC16 [SA605B]
M45PE80@VQFPN8 [SA683]
M48C02B
M48C12B
M48T02B
M48T12
M48T128Y
M48T129Y
M48T18
M48T30Y
M48T32Y
M48T35@S0IC28 [SA404]
M48T35AV@S0IC28 [SA404]
M48T35AY@S0IC28 [SA404]
M48T35Y@S0IC28 [SA404]
M48T512AY
M48T512Y
M48T513Y
M48T559@S0IC28 [SA630]
M48T559Y@S0IC28 [SA630]
M48T58@S0IC28 [SA404]
M48T58Y@S0IC28 [SA404]
M48T59@S0IC28 [SA404]
M48T59V@S0IC28 [SA404]
M48T59Y@S0IC28 [SA404]
M48Z02B
M48Z12
M48Z128V
M48Z129V
M48Z12B
M48Z30
M48Z32
M48Z35
M48Z35Y
M48Z512AV
M48Z512V
M48Z513V
M48Z58
M48Z58Y
M48Z59
M48Z59W
M48Z59Y
M50FLW040A@PLCC32 [SA015A1T]
M50FLW040A@VSOP32 [SA620-B4807]
M50FLW040B@TSOP40 [SA409T-B4002]
M50FLW080A@PLCC32 [SA015A1T]
M50FLW080A@VSOP32 [SA620-B4807]
M50FLW080B@TSOP40 [SA409T-B4002]
M50FW002@PLCC32 [SA015A1T]

M34D32@S0IC8 [SA602A]
M34D64
M34D64@TSSOP8 [SA026-B3201]
M34E02@MSOP8
M34E02@TSOP8
M35080@S0IC8 [SA602A]
M45PE10@VQFPN8 [SA683]
M45PE16@VQFPN8 [SA683]
M45PE20@VQFPN8 [SA683]
M45PE40@VQFPN8 [SA683]
M45PE80@S0IC8 [SA605B]
M48C02
M48C12
M48T02
M48T08
M48T128V
M48T129V
M48T12B
M48T30
M48T32
M48T35
M48T35AV
M48T35AY
M48T35Y
M48T512AV
M48T512V
M48T513V
M48T559
M48T559Y
M48T58
M48T58Y
M48T59
M48T59V
M48T59Y
M48Z02
M48Z08
M48Z128
M48Z128Y
M48Z129Y
M48Z18
M48Z30Y
M48Z32Y
M48Z35@S0IC28 [SA404]
M48Z35Y@S0IC28 [SA404]
M48Z512AY
M48Z512Y
M48Z513Y
M48Z58@S0IC28 [SA404]
M48Z58Y@S0IC28 [SA404]
M48Z59@S0IC28 [SA404]
M48Z59W@S0IC28 [SA404]
M48Z59Y@S0IC28 [SA404]
M50FLW040A@TSOP40 [SA409T-B4002]
M50FLW040B@PLCC32 [SA015A1T]
M50FLW040B@VSOP32 [SA620-B4807]
M50FLW080A@TSOP40 [SA409T-B4002]
M50FLW080B@PLCC32 [SA015A1T]
M50FLW080B@VSOP32 [SA620-B4807]
M50FW016@TSOP40 [SA409T-B4002]

M50FW020@PLCC32 [SA015A1T]
M50FW040@TSOP40 [SA409T-B4002]
M50FW080@TSOP40 [SA409T-B4002]
M50LPW002@PLCC32 [SA015A1T]
M50LPW020@PLCC32 [SA015A1T]
M50LPW040@TSOP40 [SA409T-B4002]
M50LPW041@TSOP40 [SA409T-B4002]
M50LPW080@TSOP40 [SA409T-B4002]
M59DR008E@TSOP48 [SB247-B4806]
M59DR032A@TSOP48 [SB247-B4806]
M59PW016
M59PW016@SDIP42 [SA028]
M59PW032@PSOP44 [SA638]
M59PW064@PSOP44 [SA638]
M93C06(08bit)
M93C06(16bit)
M93C46(08bit)
M93C46(08bit)@MSOP8 [SA666]
M93C46(08bit)@TSSOP8 [SA026-B3201]
M93C46(16bit)
M93C46(16bit)@MSOP8 [SA666]
M93C46(16bit)@TSSOP8 [SA026-B3201]
M93C46R(08bit)
M93C46R(08bit)@MSOP8 [SA666]
M93C46R(08bit)@TSSOP8 [SA026-B3201]
M93C46R(16bit)
M93C46R(16bit)@MSOP8 [SA666]
M93C46R(16bit)@TSSOP8 [SA026-B3201]
M93C46W(08bit)
M93C46W(08bit)@MSOP8 [SA666]
M93C46W(08bit)@TSSOP8 [SA026-B3201]
M93C46W(16bit)
M93C46W(16bit)@MSOP8 [SA666]
M93C46W(16bit)@TSSOP8 [SA026-B3201]
M93C56(08bit)
M93C56(08bit)@MSOP8 [SA666]
M93C56(08bit)@TSSOP8 [SA026-B3201]
M93C56(16bit)
M93C56(16bit)@MSOP8 [SA666]
M93C56(16bit)@TSSOP8 [SA026-B3201]
M93C56R(08bit)
M93C56R(08bit)@MSOP8 [SA666]
M93C56R(08bit)@TSSOP8 [SA026-B3201]
M93C56R(16bit)
M93C56R(16bit)@MSOP8 [SA666]
M93C56R(16bit)@TSSOP8 [SA026-B3201]
M93C56W(08bit)
M93C56W(08bit)@MSOP8 [SA666]
M93C56W(08bit)@TSSOP8 [SA026-B3201]
M93C56W(16bit)
M93C56W(16bit)@MSOP8 [SA666]
M93C56W(16bit)@TSSOP8 [SA026-B3201]
M93C66(08bit)
M93C66(08bit)@MSOP8 [SA666]
M93C66(08bit)@TSSOP8 [SA026-B3201]
M93C66(16bit)
M93C66(16bit)@MSOP8 [SA666]
M93C66(16bit)@TSSOP8 [SA026-B3201]
M93C66R(08bit)

M50FW040@PLCC32 [SA015A1T]
M50FW080@PLCC32 [SA015A1T]
M50FW080@VSOP32 [SA620-B4807]
M50LPW012@PLCC32 [SA015A1T]
M50LPW040@PLCC32 [SA015A1T]
M50LPW041@PLCC32 [SA015A1T]
M50LPW080@PLCC32 [SA015A1T]
M50LPW116@TSOP40 [SA409T-B4002]
M59DR008F@TSOP48 [SB247-B4806]
M59DR032B@TSOP48 [SB247-B4806]
M59PW016@PSOP44 [SA638]
M59PW016@TSOP48 [SB247-B4806]
M59PW032@TSOP48 [SB247-B4806]
M59PW1282@PSOP44 [SA638]
M93C06(08bit)@SOIC8 [SA602A]
M93C06(16bit)@SOIC8 [SA602A]
M93C46(08bit)@MLP8 [SA694]
M93C46(08bit)@SOIC8 [SA602A]
M93C46(16bit)@MLP8 [SA694]
M93C46(16bit)@SOIC8 [SA602A]
M93C46R(08bit)@MLP8 [SA694]
M93C46R(08bit)@SOIC8 [SA602A]
M93C46R(16bit)@MLP8 [SA694]
M93C46R(16bit)@SOIC8 [SA602A]
M93C46W(08bit)@MLP8 [SA694]
M93C46W(08bit)@SOIC8 [SA602A]
M93C46W(16bit)@MLP8 [SA694]
M93C46W(16bit)@SOIC8 [SA602A]
M93C56(08bit)@MLP8 [SA694]
M93C56(08bit)@SOIC8 [SA602A]
M93C56(16bit)@MLP8 [SA694]
M93C56(16bit)@SOIC8 [SA602A]
M93C56R(08bit)@MLP8 [SA694]
M93C56R(08bit)@SOIC8 [SA602A]
M93C56R(16bit)@MLP8 [SA694]
M93C56R(16bit)@SOIC8 [SA602A]
M93C56W(08bit)@MLP8 [SA694]
M93C56W(08bit)@SOIC8 [SA602A]
M93C56W(16bit)@MLP8 [SA694]
M93C56W(16bit)@SOIC8 [SA602A]
M93C66(08bit)@MLP8 [SA694]
M93C66(08bit)@SOIC8 [SA602A]
M93C66(16bit)@MLP8 [SA694]
M93C66(16bit)@SOIC8 [SA602A]
M93C66R(08bit)@MLP8 [SA694]

M93C66R(08bit)@MSOP8 [SA666]	M93C66R(08bit)@SOIC8 [SA602A]
M93C66R(08bit)@TSSOP8 [SA026-B3201]	
M93C66R(16bit)	M93C66R(16bit)@MLP8 [SA694]
M93C66R(16bit)@MSOP8 [SA666]	M93C66R(16bit)@SOIC8 [SA602A]
M93C66R(16bit)@TSSOP8 [SA026-B3201]	
M93C66W(08bit)	M93C66W(08bit)@MLP8 [SA694]
M93C66W(08bit)@MSOP8 [SA666]	M93C66W(08bit)@SOIC8 [SA602A]
M93C66W(08bit)@TSSOP8 [SA026-B3201]	
M93C66W(16bit)	M93C66W(16bit)@MLP8 [SA694]
M93C66W(16bit)@MSOP8 [SA666]	M93C66W(16bit)@SOIC8 [SA602A]
M93C66W(16bit)@TSSOP8 [SA026-B3201]	
M93C76(08bit)	M93C76(08bit)@MLP8 [SA694]
M93C76(08bit)@MSOP8 [SA666]	M93C76(08bit)@SOIC8 [SA602A]
M93C76(08bit)@TSSOP8 [SA026-B3201]	
M93C76(16bit)	M93C76(16bit)@MLP8 [SA694]
M93C76(16bit)@MSOP8 [SA666]	M93C76(16bit)@SOIC8 [SA602A]
M93C76(16bit)@TSSOP8 [SA026-B3201]	
M93C76R(08bit)	M93C76R(08bit)@MLP8 [SA694]
M93C76R(08bit)@MSOP8 [SA666]	M93C76R(08bit)@SOIC8 [SA602A]
M93C76R(08bit)@TSSOP8 [SA026-B3201]	
M93C76R(16bit)	M93C76R(16bit)@MLP8 [SA694]
M93C76R(16bit)@MSOP8 [SA666]	M93C76R(16bit)@SOIC8 [SA602A]
M93C76R(16bit)@TSSOP8 [SA026-B3201]	
M93C76W(08bit)	M93C76W(08bit)@MLP8 [SA694]
M93C76W(08bit)@MSOP8 [SA666]	M93C76W(08bit)@SOIC8 [SA602A]
M93C76W(08bit)@TSSOP8 [SA026-B3201]	
M93C76W(16bit)	M93C76W(16bit)@MLP8 [SA694]
M93C76W(16bit)@MSOP8 [SA666]	M93C76W(16bit)@SOIC8 [SA602A]
M93C76W(16bit)@TSSOP8 [SA026-B3201]	
M93C86(08bit)	M93C86(08bit)@MLP8 [SA694]
M93C86(08bit)@MSOP8 [SA666]	M93C86(08bit)@SOIC8 [SA602A]
M93C86(08bit)@TSSOP8 [SA026-B3201]	
M93C86(16bit)	M93C86(16bit)@MLP8 [SA694]
M93C86(16bit)@MSOP8 [SA666]	M93C86(16bit)@SOIC8 [SA602A]
M93C86(16bit)@TSSOP8 [SA026-B3201]	
M93C86R(08bit)	M93C86R(08bit)@MLP8 [SA694]
M93C86R(08bit)@MSOP8 [SA666]	M93C86R(08bit)@SOIC8 [SA602A]
M93C86R(08bit)@TSSOP8 [SA026-B3201]	
M93C86R(16bit)	M93C86R(16bit)@MLP8 [SA694]
M93C86R(16bit)@MSOP8 [SA666]	M93C86R(16bit)@SOIC8 [SA602A]
M93C86R(16bit)@TSSOP8 [SA026-B3201]	
M93C86W(08bit)	M93C86W(08bit)@MLP8 [SA694]
M93C86W(08bit)@MSOP8 [SA666]	M93C86W(08bit)@SOIC8 [SA602A]
M93C86W(08bit)@TSSOP8 [SA026-B3201]	
M93C86W(16bit)	M93C86W(16bit)@MLP8 [SA694]
M93C86W(16bit)@MSOP8 [SA666]	M93C86W(16bit)@SOIC8 [SA602A]
M93C86W(16bit)@TSSOP8 [SA026-B3201]	
M93CS566	M93CS566@SOIC8 [SA602A]
M93S46	M93S46@SOIC8 [SA602A]
M93S46@TSSOP8 [SA026-B3201]	M93S46R
M93S46R@SOIC8 [SA602A]	M93S46R@TSSOP8 [SA026-B3201]
M93S46W	M93S46W@SOIC8 [SA602A]
M93S46W@TSSOP8 [SA026-B3201]	M93S56
M93S56@SOIC8 [SA602A]	M93S56@TSSOP8 [SA026-B3201]
M93S56R	M93S56R@SOIC8 [SA602A]
M93S56R@TSSOP8 [SA026-B3201]	M93S56W
M93S56W@SOIC8 [SA602A]	M93S56W@TSSOP8 [SA026-B3201]
M93S66	M93S66@SOIC8 [SA602A]
M93S66@TSSOP8 [SA026-B3201]	M93S66R

M93S66R@S0IC8 [SA602A]
M93S66W
M93S66W@TSSOP8 [SA026-B3201]
M95010@S0IC8 [SA602A]
M95020
M95020@TSSOP8 [SA026-B3201]
M95040@S0IC8 [SA602A]
M95080
M95080@TSSOP14 [SA026-B3201]
M95128
M95128@TSSOP8 [SA026-B3201]
M95128[200mil]@S0IC8 [SA605B]
M95160@S0IC8 [SA602A]
M95160@TSSOP8 [SA026-B3201]
M95256@TSSOP14 [SA026-B3201]
M95256[150mil]@S0IC8 [SA602A]
M95320
M95320@TSSOP14 [SA026-B3201]
M95512@S0IC8 [SA602A]
M95640
M95640@TSSOP14 [SA026-B3201]
M95P02
M95P04
M95P08
MK48C02
MK48C12
MK48T02
MK48T08
MK48T12B
MK48T32
MK48T35
MK48T35Y
MK48T512V
MK48Z02
MK48Z08
MK48Z12B
MK48Z32
MK48Z35
MK48Z35Y
MK48Z512V
MKI48Z02
MKI48Z12
MKI48Z18
ST24C01@S0IC8 [SA602A]
ST24C02A@S0IC8 [SA602A]
ST24C16@S0IC8
ST24FC21@S0IC8 [SA602A]
ST24FW21@S0IC8 [SA602A]
ST24LC21B@S0IC8 [SA602A]
ST24LW21@S0IC8 [SA602A]
ST24W01@S0IC8
ST24W02@S0IC8
ST24W04C@S0IC8
ST26C201@PLCC32 [SA015A1T]
ST27128A
ST2764A
ST93C06(08bit)
ST93C06(16bit)
ST93C46(08bit)

M93S66R@TSSOP8 [SA026-B3201]
M93S66W@S0IC8 [SA602A]
M95010
M95010@TSSOP8 [SA026-B3201]
M95020@S0IC8 [SA602A]
M95040
M95040@TSSOP8 [SA026-B3201]
M95080@S0IC8 [SA602A]
M95080@TSSOP8 [SA026-B3201]
M95128@TSSOP14 [SA026-B3201]
M95128[150mil]@S0IC8 [SA602A]
M95160
M95160@TSSOP14 [SA026-B3201]
M95256
M95256@TSSOP8 [SA026-B3201]
M95256[200mil]@S0IC8 [SA605B]
M95320@S0IC8 [SA602A]
M95320@TSSOP8 [SA026-B3201]
M95512@TSSOP8 [SA026-B3201]
M95640@S0IC8 [SA602A]
M95640@TSSOP8 [SA026-B3201]
M95P02@S0IC8 [SA602A]
M95P04@S0IC8 [SA602A]
M95P08@S0IC8 [SA602A]
MK48C02B
MK48C12B
MK48T02B
MK48T12
MK48T18
MK48T32Y
MK48T35@S0IC28 [SA404]
MK48T35Y@S0IC28 [SA404]
MK48T512Y
MK48Z02B
MK48Z12
MK48Z18
MK48Z32Y
MK48Z35@S0IC28 [SA404]
MK48Z35Y@S0IC28 [SA404]
MK48Z512Y
MKI48Z02B
MKI48Z12B
ST24C01
ST24C02A
ST24C16
ST24FC21
ST24FW21
ST24LC21B
ST24LW21
ST24W01
ST24W02
ST24W04C
ST26C201
ST26C201@TSOP32 [SA410T-B4001]
ST27256
ST27C256
ST93C06(08bit)@S0IC8 [SA602A]
ST93C06(16bit)@S0IC8 [SA602A]
ST93C46(08bit)@S0IC8 [SA602A]

ST93C46(16bit)	ST93C46(16bit)@S0IC8 [SA602A]
ST93C46A(08bit)	ST93C46A(08bit)@S0IC8 [SA602A]
ST93C46A(16bit)	ST93C46A(16bit)@S0IC8 [SA602A]
ST93C46C(08bit)	ST93C46C(08bit)@S0IC8 [SA602A]
ST93C46C(16bit)	ST93C46C(16bit)@S0IC8 [SA602A]
ST93C46T(08bit)	ST93C46T(08bit)@S0IC8 [SA602A]
ST93C46T(16bit)	ST93C46T(16bit)@S0IC8 [SA602A]
ST93C47C(08bit)	ST93C47C(08bit)@S0IC8 [SA602A]
ST93C47C(16bit)	ST93C47C(16bit)@S0IC8 [SA602A]
ST93C47T(08bit)	ST93C47T(08bit)@S0IC8 [SA602A]
ST93C47T(16bit)	ST93C47T(16bit)@S0IC8 [SA602A]
ST93C56(08bit)	ST93C56(08bit)@S0IC8 [SA602A]
ST93C56(16bit)	ST93C56(16bit)@S0IC8 [SA602A]
ST93C56B(08bit)	ST93C56B(08bit)@S0IC8 [SA602A]
ST93C56B(16bit)	ST93C56B(16bit)@S0IC8 [SA602A]
ST93C56C(08bit)	ST93C56C(08bit)@S0IC8 [SA602A]
ST93C56C(16bit)	ST93C56C(16bit)@S0IC8 [SA602A]
ST93C57C(08bit)	ST93C57C(08bit)@S0IC8 [SA602A]
ST93C57C(16bit)	ST93C57C(16bit)@S0IC8 [SA602A]
ST93C66(08bit)	ST93C66(08bit)@S0IC8 [SA602A]
ST93C66(16bit)	ST93C66(16bit)@S0IC8 [SA602A]
ST93C67(08bit)	ST93C67(08bit)@S0IC8 [SA602A]
ST93C67(16bit)	ST93C67(16bit)@S0IC8 [SA602A]
ST93C76(08bit)	ST93C76(08bit)@S0IC8 [SA602A]
ST93C76(16bit)	ST93C76(16bit)@S0IC8 [SA602A]
ST93C86(08bit)	ST93C86(08bit)@S0IC8 [SA602A]
ST93C86(16bit)	ST93C86(16bit)@S0IC8 [SA602A]
ST93CS46	ST93CS46@S0IC8 [SA602A]
ST93CS47	ST93CS47@S0IC8 [SA602A]
ST93CS56	ST93CS56@S0IC8 [SA602A]
ST93CS566	ST93CS566@S0IC8 [SA602A]
ST93CS57	ST93CS57@S0IC8 [SA602A]
ST93CS66	ST93CS66@S0IC14 [SA602]
ST93CS67	ST93CS67@S0IC14 [SA602]
TS27C256	TS27C64
TS27C64@PLCC32 [SA015A1T]	TS27C64A
TS27C64A@PLCC32 [SA015A1T]	TS28C16A
TS28C17A	

STC

MICROCONTROLLER

STC89LE516AD	STC89LE516AD@PLCC44 [SA244]
STC89LE516AD@TQFP44 [SA245A-B4805]	
STC89LE516X2	STC89LE516X2@PLCC44 [SA244]
STC89LE516X2@TQFP44 [SA245A-B4805]	
STC89LE52AD	STC89LE52AD@PLCC44 [SA244]
STC89LE52AD@TQFP44 [SA245A-B4805]	
STC89LE54AD	STC89LE54AD@PLCC44 [SA244]
STC89LE54AD@TQFP44 [SA245A-B4805]	
STC89LE556AD	STC89LE556AD@PLCC44 [SA244]
STC89LE556AD@TQFP44 [SA245A-B4805]	
STC89LE556X2	STC89LE556X2@PLCC44 [SA244]
STC89LE556X2@TQFP44 [SA245A-B4805]	
STC89LE58AD	STC89LE58AD@PLCC44 [SA244]
STC89LE58AD@TQFP44 [SA245A-B4805]	
STC89LV516RD	STC89LV516RD@PLCC44 [SA244]

STC89LV516RD@TQFP44 [SA245A-B4805]
STC89LV58RD
STC89LV58RD@TQFP44 [SA245A-B4805]

STC89LV58RD@PLCC44 [SA244]

SUMMIT

E(E)PROM/FRAM/NVRAM

S24022	S24022@S0IC8 [SA602A]
S24023	S24023@S0IC8 [SA602A]
S24042	S24042@S0IC8 [SA602A]
S24043	S24043@S0IC8 [SA602A]
S24162	S24162@S0IC8 [SA602A]
S24VP02	S24VP02@S0IC8 [SA602A]
S24VP04	S24VP04@S0IC8 [SA602A]
S24VP08	S24VP08@S0IC8 [SA602A]
S24VP16	S24VP16@S0IC8 [SA602A]
S93462(08bit)	S93462(08bit)@S0IC8 [SA602A]
S93462(16bit)	S93462(16bit)@S0IC8 [SA602A]
S93463(08bit)	S93463(08bit)@S0IC8 [SA602A]
S93463(16bit)	S93463(16bit)@S0IC8 [SA602A]
S93662(08bit)	S93662(08bit)@S0IC8 [SA602A]
S93662(16bit)	S93662(16bit)@S0IC8 [SA602A]
S93663(08bit)	S93663(08bit)@S0IC8 [SA602A]
S93663(16bit)	S93663(16bit)@S0IC8 [SA602A]
S93WD462(08bit)	S93WD462(08bit)@S0IC8 [SA602A]
S93WD462(16bit)	S93WD462(16bit)@S0IC8 [SA602A]
S93WD463(08bit)	S93WD463(08bit)@S0IC8 [SA602A]
S93WD463(16bit)	S93WD463(16bit)@S0IC8 [SA602A]
S93WD662(08bit)	S93WD662(08bit)@S0IC8 [SA602A]
S93WD662(16bit)	S93WD662(16bit)@S0IC8 [SA602A]
S93WD663(08bit)	S93WD663(08bit)@S0IC8 [SA602A]
S93WD663(16bit)	S93WD663(16bit)@S0IC8 [SA602A]

SYNCMOS

E(E)PROM/FRAM/NVRAM

F29C31004B	F29C31004B@PLCC32 [SA015A1T]
F29C31004B@TSOP32 [SA410T-B4001]	F29C31004T
F29C31004T@PLCC32 [SA015A1T]	F29C31004T@TSOP32 [SA410T-B4001]
F29C51000B	F29C51000B@PLCC32 [SA015A1T]
F29C51000B@TSOP32 [SA410T-B4001]	F29C51000T
F29C51000T@PLCC32 [SA015A1T]	F29C51000T@TSOP32 [SA410T-B4001]
F29C51001B	F29C51001B@PLCC32 [SA015A1T]
F29C51001B@TSOP32 [SA410T-B4001]	F29C51001T
F29C51001T@PLCC32 [SA015A1T]	F29C51001T@TSOP32 [SA410T-B4001]
F29C51002B	F29C51002B@PLCC32 [SA015A1T]
F29C51002B@TSOP32 [SA410T-B4001]	F29C51002T
F29C51002T@PLCC32 [SA015A1T]	F29C51002T@TSOP32 [SA410T-B4001]
F29C51004B	F29C51004B@PLCC32 [SA015A1T]
F29C51004B@TSOP32 [SA410T-B4001]	F29C51004T
F29C51004T@PLCC32 [SA015A1T]	F29C51004T@TSOP32 [SA410T-B4001]
F29LC51000	F29LC51000@PLCC32 [SA015A1T]
F29LC51000@TSOP32 [SA410T-B4001]	F29LC51001
F29LC51001@PLCC32 [SA015A1T]	F29LC51001@TSOP32 [SA410T-B4001]
F29LC51002	F29LC51002@PLCC32 [SA015A1T]

F29LC51002@TSOP32 [SA410T-B4001]
S29C31001B@PLCC32 [SA015A1T]
S29C31001T
S29C31001T@TSOP32 [SA410T-B4001]
S29C31002B@PLCC32 [SA015A1T]
S29C31002T
S29C31002T@TSOP32 [SA410T-B4001]
S29C31004B@PLCC32 [SA015A1T]
S29C31004T
S29C31004T@TSOP32 [SA410T-B4001]
S29C51001B@PLCC32 [SA015A1T]
S29C51001T
S29C51001T@TSOP32 [SA410T-B4001]
S29C51002B@PLCC32 [SA015A1T]
S29C51002T
S29C51002T@TSOP32 [SA410T-B4001]
S29C51004B@PLCC32 [SA015A1T]
S29C51004T
S29C51004T@TSOP32 [SA410T-B4001]

S29C31001B
S29C31001B@TSOP32 [SA410T-B4001]
S29C31001T@PLCC32 [SA015A1T]
S29C31002B
S29C31002B@TSOP32 [SA410T-B4001]
S29C31002T@PLCC32 [SA015A1T]
S29C31004B
S29C31004B@TSOP32 [SA410T-B4001]
S29C31004T@PLCC32 [SA015A1T]
S29C51001B
S29C51001B@TSOP32 [SA410T-B4001]
S29C51001T@PLCC32 [SA015A1T]
S29C51002B
S29C51002B@TSOP32 [SA410T-B4001]
S29C51002T@PLCC32 [SA015A1T]
S29C51004B
S29C51004B@TSOP32 [SA410T-B4001]
S29C51004T@PLCC32 [SA015A1T]

MICROCONTROLLER

MSU1958
MSU1958@TQFP44 [SA675-B4805]
MSU2952@PLCC44 [SA244]
MSU2964
MSU2964@TQFP44 [SA675-B4805]
SM2958@PLCC44 [SA244]
SM2965
SM2965@TQFP44 [SA675-B4805]
SM59064@PLCC44 [SA244]
SM59128C
SM59128C@TQFP44 [SA675-B4805]
SM59128L@PLCC44 [SA244]
SM5912C
SM5912C@TQFP44 [SA675-B4805]
SM5912L@PLCC44 [SA244]
SM59164
SM59164@TQFP44 [SA675-B4805]
SM5916C@PLCC44 [SA244]
SM5916L
SM5916L@TQFP44 [SA675-B4805]
SM59264@PLCC44 [SA244]
SM5964
SM5964@TQFP44 [SA675-B4805]
SM5964A@PLCC44 [SA244]
SM5964AC
SM5964AC@TQFP44 [SA675-B4805]
SM5964AL@PLCC44 [SA244]
SM5964C
SM5964C@TQFP44 [SA675-B4805]
SM5964D0@PLCC44 [SA244]
SM5964D0A
SM5964D0A@TQFP44 [SA675-B4805]
SM5964D1A@PLCC44 [SA244]
SM59D02G2C
SM59D02G2C@TQFP44 [SA675-B4805]
SM59D02G2L@PLCC44 [SA244]
SM59D03G2C

MSU1958@PLCC44 [SA244]
MSU2952
MSU2952@TQFP44 [SA675-B4805]
MSU2964@PLCC44 [SA244]
SM2958
SM2958@TQFP44 [SA675-B4805]
SM2965@PLCC44 [SA244]
SM59064
SM59064@TQFP44 [SA675-B4805]
SM59128C@PLCC44 [SA244]
SM59128L
SM59128L@TQFP44 [SA675-B4805]
SM5912C@PLCC44 [SA244]
SM5912L
SM5912L@TQFP44 [SA675-B4805]
SM59164@PLCC44 [SA244]
SM5916C
SM5916C@TQFP44 [SA675-B4805]
SM5916L@PLCC44 [SA244]
SM59264
SM59264@TQFP44 [SA675-B4805]
SM5964@PLCC44 [SA244]
SM5964A
SM5964A@TQFP44 [SA675-B4805]
SM5964AC@PLCC44 [SA244]
SM5964AL
SM5964AL@TQFP44 [SA675-B4805]
SM5964C@PLCC44 [SA244]
SM5964D0
SM5964D0@TQFP44 [SA675-B4805]
SM5964D0A@PLCC44 [SA244]
SM5964D1A
SM5964D1A@TQFP44 [SA675-B4805]
SM59D02G2C@PLCC44 [SA244]
SM59D02G2L
SM59D02G2L@TQFP44 [SA675-B4805]
SM59D03G2C@PLCC44 [SA244]

SM59D03G2C@TQFP44 [SA675-B4805]
SM59D03G2L@PLCC44 [SA244]
SM59D04G2C
SM59D04G2C@TQFP44 [SA675-B4805]
SM59D04G2L@PLCC44 [SA244]
SM59R02A1C
SM59R02A1C@PLCC44 [SA244]
SM59R02A1L
SM59R02A1L@PLCC44 [SA244]
SM59R03A1C
SM59R03A1C@PLCC44 [SA244]
SM59R03A1L
SM59R03A1L@PLCC44 [SA244]
SM59R04A1C
SM59R04A1C@PLCC44 [SA244]
SM59R04A1L
SM59R04A1L@PLCC44 [SA244]
SM59R04A2C
SM59R04A2C@PLCC44 [SA244]
SM59R04A2L
SM59R04A2L@PLCC44 [SA244]
SM59R05A3C
SM59R05A3C@PLCC44 [SA244]
SM59R05A3L
SM59R05A3L@PLCC44 [SA244]
SM59R05A5C
SM59R05A5C@PLCC44 [SA244]
SM59R05A5L
SM59R05A5L@PLCC44 [SA244]
SM59R09A3C
SM59R09A3C@PLCC44 [SA244]
SM59R09A3L
SM59R09A3L@PLCC44 [SA244]
SM59R09A5C
SM59R09A5C@PLCC44 [SA244]
SM59R09A5L
SM59R09A5L@PLCC44 [SA244]
SM59R16A3C
SM59R16A3C@PLCC44 [SA244]
SM59R16A3L
SM59R16A3L@PLCC44 [SA244]
SM59R16A5C
SM59R16A5C@PLCC44 [SA244]
SM59R16A5L
SM59R16A5L@PLCC44 [SA244]
SM7908
SM7908@TQFP44 [SA675-B4805]
SM79108@PLCC44 [SA244]
SM79164
SM79164@TQFP44 [SA675-B4805]
SM79164L@PLCC44 [SA244]
SM79164V
SM79164V@TQFP44 [SA675-B4805]
SM7932@PLCC44 [SA244]
SM7964
SM7964@TQFP44 [SA675-B4805]
SM894051@S0IC20 [SA023A]
SM8951@PLCC44 [SA244]
SM89516

SM59D03G2L
SM59D03G2L@TQFP44 [SA675-B4805]
SM59D04G2C@PLCC44 [SA244]
SM59D04G2L
SM59D04G2L@TQFP44 [SA675-B4805]
SM59R02A1C@LQFP48 [SA248-B4804]
SM59R02A1C@QFP44 [SA675-B4805]
SM59R02A1L@LQFP48 [SA248-B4804]
SM59R02A1L@QFP44 [SA675-B4805]
SM59R03A1C@LQFP48 [SA248-B4804]
SM59R03A1C@QFP44 [SA675-B4805]
SM59R03A1L@LQFP48 [SA248-B4804]
SM59R03A1L@QFP44 [SA675-B4805]
SM59R04A1C@LQFP48 [SA248-B4804]
SM59R04A1C@QFP44 [SA675-B4805]
SM59R04A1L@LQFP48 [SA248-B4804]
SM59R04A1L@QFP44 [SA675-B4805]
SM59R04A2C@LQFP48 [SA248-B4804]
SM59R04A2C@QFP44 [SA675-B4805]
SM59R04A2L@LQFP48 [SA248-B4804]
SM59R04A2L@QFP44 [SA675-B4805]
SM59R05A3C@LQFP48 [SA248-B4804]
SM59R05A3C@QFP44 [SA675-B4805]
SM59R05A3L@LQFP48 [SA248-B4804]
SM59R05A3L@QFP44 [SA675-B4805]
SM59R05A5C@LQFP48 [SA248-B4804]
SM59R05A5C@QFP44 [SA675-B4805]
SM59R05A5L@LQFP48 [SA248-B4804]
SM59R05A5L@QFP44 [SA675-B4805]
SM59R09A3C@LQFP48 [SA248-B4804]
SM59R09A3C@QFP44 [SA675-B4805]
SM59R09A3L@LQFP48 [SA248-B4804]
SM59R09A3L@QFP44 [SA675-B4805]
SM59R09A5C@LQFP48 [SA248-B4804]
SM59R09A5C@QFP44 [SA675-B4805]
SM59R09A5L@LQFP48 [SA248-B4804]
SM59R09A5L@QFP44 [SA675-B4805]
SM59R16A3C@LQFP48 [SA248-B4804]
SM59R16A3C@QFP44 [SA675-B4805]
SM59R16A3L@LQFP48 [SA248-B4804]
SM59R16A3L@QFP44 [SA675-B4805]
SM59R16A5C@LQFP48 [SA248-B4804]
SM59R16A5C@QFP44 [SA675-B4805]
SM59R16A5L@LQFP48 [SA248-B4804]
SM59R16A5L@QFP44 [SA675-B4805]
SM7908@PLCC44 [SA244]
SM79108
SM79108@TQFP44 [SA675-B4805]
SM79164@PLCC44 [SA244]
SM79164L
SM79164L@TQFP44 [SA675-B4805]
SM79164V@PLCC44 [SA244]
SM7932
SM7932@TQFP44 [SA675-B4805]
SM7964@PLCC44 [SA244]
SM894051
SM8951
SM8951@TQFP44 [SA675-B4805]
SM89516@PLCC44 [SA244]

SM89516@TQFP44 [SA675-B4805]
SM89516A@PLCC44 [SA244]
SM89516AL
SM89516AL@TQFP44 [SA675-B4805]
SM89516B@PLCC44 [SA244]
SM89516BL
SM89516BL@TQFP44 [SA675-B4805]
SM89516L@PLCC44 [SA244]
SM8951A
SM8951A@TQFP44 [SA675-B4805]
SM8951AL@PLCC44 [SA244]
SM8951B
SM8951B@TQFP44 [SA675-B4805]
SM8951BL@PLCC44 [SA244]
SM8951L
SM8951L@TQFP44 [SA675-B4805]
SM8952@PLCC44 [SA244]
SM8952A
SM8952A@TQFP44 [SA675-B4805]
SM8952AL@PLCC44 [SA244]
SM8952B
SM8952B@TQFP44 [SA675-B4805]
SM8952BL@PLCC44 [SA244]
SM8952L
SM8952L@TQFP44 [SA675-B4805]
SM8954@PLCC44 [SA244]
SM8954A
SM8954A@TQFP44 [SA675-B4805]
SM8954AL@PLCC44 [SA244]
SM8954B
SM8954B@TQFP44 [SA675-B4805]
SM8954BL@PLCC44 [SA244]
SM8954L
SM8954L@TQFP44 [SA675-B4805]
SM8958@PLCC44 [SA244]
SM8958A
SM8958A@TQFP44 [SA675-B4805]
SM8958AL@PLCC44 [SA244]
SM8958B
SM8958B@TQFP44 [SA675-B4805]
SM8958BL@PLCC44 [SA244]
SM8958L
SM8958L@TQFP44 [SA675-B4805]
SM89S16R1C@PLCC44 [SA244]
SM89T04R1C
SM89T04R1C@TQFP44 [SA675-B4805]
SM89T04R1L@PLCC44 [SA244]
SM89T08R1C
SM89T08R1C@TQFP44 [SA675-B4805]
SM89T08R1L@PLCC44 [SA244]
SM89T16R1C
SM89T16R1C@TQFP44 [SA675-B4805]
SM89T16R1L@PLCC44 [SA244]

SM89516A
SM89516A@TQFP44 [SA675-B4805]
SM89516AL@PLCC44 [SA244]
SM89516B
SM89516B@TQFP44 [SA675-B4805]
SM89516BL@PLCC44 [SA244]
SM89516L
SM89516L@TQFP44 [SA675-B4805]
SM8951A@PLCC44 [SA244]
SM8951AL
SM8951AL@TQFP44 [SA675-B4805]
SM8951B@PLCC44 [SA244]
SM8951BL
SM8951BL@TQFP44 [SA675-B4805]
SM8951L@PLCC44 [SA244]
SM8952
SM8952@TQFP44 [SA675-B4805]
SM8952A@PLCC44 [SA244]
SM8952AL
SM8952AL@TQFP44 [SA675-B4805]
SM8952B@PLCC44 [SA244]
SM8952BL
SM8952BL@TQFP44 [SA675-B4805]
SM8952L@PLCC44 [SA244]
SM8954
SM8954@TQFP44 [SA675-B4805]
SM8954A@PLCC44 [SA244]
SM8954AL
SM8954AL@TQFP44 [SA675-B4805]
SM8954B@PLCC44 [SA244]
SM8954BL
SM8954BL@TQFP44 [SA675-B4805]
SM8954L@PLCC44 [SA244]
SM8958
SM8958@TQFP44 [SA675-B4805]
SM8958A@PLCC44 [SA244]
SM8958AL
SM8958AL@TQFP44 [SA675-B4805]
SM8958B@PLCC44 [SA244]
SM8958BL
SM8958BL@TQFP44 [SA675-B4805]
SM8958L@PLCC44 [SA244]
SM89S16R1C
SM89S16R1C@TQFP44 [SA675-B4805]
SM89T04R1C@PLCC44 [SA244]
SM89T04R1L
SM89T04R1L@TQFP44 [SA675-B4805]
SM89T08R1C@PLCC44 [SA244]
SM89T08R1L
SM89T08R1L@TQFP44 [SA675-B4805]
SM89T16R1C@PLCC44 [SA244]
SM89T16R1L
SM89T16R1L@TQFP44 [SA675-B4805]

SYNERTEK

E(E) PROM/FRAM/NVRAM

TECHCODE

MICROCONTROLLER

T89C516	T89C516@PLCC44 [SA244]
T89C516@TQFP44 [SA675-B4805]	T89C52
T89C52@PLCC44 [SA244]	T89C52@TQFP44 [SA675-B4805]
T89C58	T89C58@PLCC44 [SA244]
T89C58@TQFP44 [SA675-B4805]	

TEKMOS

MICROCONTROLLER

TK87C751	TK87C751@PLCC28 [SA008A]
----------	--------------------------

TEMIC

MICROCONTROLLER

T89C51RD2	T89C51RD2@PLCC44 [SA244]
T89C51RD2@TQFP44 [SA245A-B4805]	T89F64
T89F64@PLCC44 [SA244]	T89F64@TQFP44 [SA245A-B4805]
TS87C51RB2	TS87C51RB2@PLCC44 [SA244]
TS87C51RB2@TQFP44 [SA675-B4805]	TS87C51RC2
TS87C51RC2@PLCC44 [SA244]	TS87C51RC2@TQFP44 [SA675-B4805]
TS87C51RD2	TS87C51RD2@PLCC44 [SA244]
TS87C51RD2@TQFP44 [SA675-B4805]	TS87C51U2
TS87C51U2@PLCC44 [SA244]	TS87C51U2@TQFP44 [SA675-B4805]
TS87C52X2	TS87C52X2@PLCC44 [SA244]
TS87C52X2@TQFP44 [SA675-B4805]	TS87C54X2
TS87C54X2@PLCC44 [SA244]	TS87C54X2@TQFP44 [SA675-B4805]
TS87C58X2	TS87C58X2@PLCC44 [SA244]
TS87C58X2@TQFP44 [SA675-B4805]	TSC71RBX2
TSC71RBX2@PLCC44 [SA244]	TSC71RBX2@TQFP44 [SA675-B4805]
TSC71RCX2	TSC71RCX2@PLCC44 [SA244]
TSC71RCX2@TQFP44 [SA675-B4805]	TSC71RDX2
TSC71RDX2@PLCC44 [SA244]	TSC71RDX2@PLCC68 [\$\$\$\$\$]
TSC71RDX2@TQFP44 [SA675-B4805]	TSC71RDX2@TQFP64 [\$\$\$\$\$]
TSC87251A1@PLCC44 [SA244]	TSC87251G1
TSC87251G1@PLCC44 [\$\$\$\$\$]	TSC87251G1A
TSC87251G1A@PLCC44 [SA244]	TSC87251G2D
TSC87251G2D@PLCC44 [SA244]	
TSC87251G2D@TQFP44 [SA245A-B4805]	
TSC87C51	TSC87C51@PLCC44 [SA244]
TSC87C51@TQFP44 [SA675-B4805]	TSC87C52
TSC87C52@PLCC44 [SA244]	TSC87C52@TQFP44 [SA675-B4805]
TSC87C54	TSC87C54@PLCC44 [SA244]
TSC87C54@TQFP44 [SA675-B4805]	TSC87C58
TSC87C58@PLCC44 [SA244]	TSC87C58@TQFP44 [SA675-B4805]

E (E) PROM/FRAM/NVRAM

TS25L16AP [SA605B]
TS25L80AP [SA605B]

TS25L16AP@SOP8 [SA605B]
TS25L80AP@SOP8 [SA605B]

TI

E (E) PROM/FRAM/NVRAM

BQ3285
BQ3287A
BQ4010Y
BQ4011Y
BQ4013Y
BQ4014Y
BQ4015Y
SMJ2532
SMJ2716
SMJ27C256@PLCC32 [SA015A1T]
SMJ27C512@PLCC32 [SA015A1T]
TMS2516JLW
TMS2532A
TMS27128
TMS2716
TMS2732A
TMS27C010
TMS27C010@TSOP32 [SA410T-B4001]
TMS27C010A@PLCC32 [SA015A1T]
TMS27C020
TMS27C020@TSOP32 [SA410T-B4001]
TMS27C040@PLCC32 [SA015A1T]
TMS27C128
TMS27C2001
TMS27C2001@TSOP32 [SA410T-B4001]
TMS27C210@PLCC44 [SA244]
TMS27C210A@PLCC44 [SA244]
TMS27C240@PLCC44 [SA244]
TMS27C256@PLCC32 [SA015A1T]
TMS27C512
TMS27C64
TMS27LV010A@PLCC32 [SA015A1T]
TMS27LV010A@TSOP32 [SA410T-B4001]
TMS27P32A
TMS27PC010
TMS27PC010@TSOP32 [SA410T-B4001]
TMS27PC010A@PLCC32 [SA015A1T]
TMS27PC010A@TSOP32 [SA410T-B4001]
TMS27PC020
TMS27PC020@TSOP32 [SA410T-B4001]
TMS27PC040@PLCC32 [SA015A1T]
TMS27PC128
TMS27PC210
TMS27PC210A
TMS27PC240
TMS27PC256
TMS27PC32
TMS27PC512
TMS27PC64

BQ3287
BQ4010
BQ4011
BQ4013
BQ4014
BQ4015
SMJ2516
SMJ2532A
SMJ27C256
SMJ27C512
TMS2516
TMS2532
TMS25L32
TMS27128A
TMS2732
TMS2764
TMS27C010@PLCC32 [SA015A1T]
TMS27C010A
TMS27C010A@TSOP32 [SA410T-B4001]
TMS27C020@PLCC32 [SA015A1T]
TMS27C040
TMS27C040@TSOP32 [SA410T-B4001]
TMS27C128@PLCC32
TMS27C2001@PLCC32 [SA015A1T]
TMS27C210
TMS27C210A
TMS27C240
TMS27C256
TMS27C32
TMS27C512@PLCC32 [SA015A1T]
TMS27LV010A

TMS27P64
TMS27PC010@PLCC32 [SA015A1T]
TMS27PC010A

TMS27PC020@PLCC32 [SA015A1T]
TMS27PC040
TMS27PC040@TSOP32 [SA410T-B4001]
TMS27PC128@PLCC32
TMS27PC210@PLCC44 [SA244]
TMS27PC210A@PLCC44 [SA244]
TMS27PC240@PLCC44 [SA244]
TMS27PC256@PLCC32 [SA015A1T]
TMS27PC32A
TMS27PC512@PLCC32 [SA015A1T]
TMS28F010

TMS28F010(REVERSE)@TSOP32 [SA410T-B4001]
TMS28F010@PLCC32 [SA015A1T] TMS28F010@TSOP32 [SA410T-B4001]
TMS28F020
TMS28F020(REVERSE)@TSOP32 [SA410T-B4001]
TMS28F020@PLCC32 [SA015A1T] TMS28F020@TSOP32 [SA410T-B4001]
TMS28F200AF-B@PSOP44 [SA638]
TMS28F200AF-B@TSOP48 [SB247-B4806]
TMS28F200AF-T@PSOP44 [SA638]
TMS28F200AF-T@TSOP48 [SB247-B4806]
TMS28F200BZ-B@PSOP44 [SA638] TMS28F200BZ-T@PSOP44 [SA638]
TMS28F210 TMS28F210@PLCC44 [SA244]
TMS28F210@TSOP40 [SA623-B4002] TMS28F400AE-B@PSOP44 [SA638]
TMS28F400AE-B@TSOP48 [SB247-B4806]
TMS28F400AE-T@PSOP44 [SA638]
TMS28F400AE-T@TSOP48 [SB247-B4806]
TMS28F400AF-B@PSOP44 [SA638]
TMS28F400AF-B@TSOP48 [SB247-B4806]
TMS28F400AF-T@PSOP44 [SA638]
TMS28F400AF-T@TSOP48 [SB247-B4806]
TMS28F400AM-B@PSOP44 [SA638]
TMS28F400AM-B@TSOP48 [SB247-B4806]
TMS28F400AM-T@PSOP44 [SA638]
TMS28F400AM-T@TSOP48 [SB247-B4806]
TMS28F400AS-B@PSOP44 [SA638]
TMS28F400AS-B@TSOP48 [SB247-B4806]
TMS28F400AS-T@PSOP44 [SA638]
TMS28F400AS-T@TSOP48 [SB247-B4806]
TMS28F400AZ-B@PSOP44 [SA638]
TMS28F400AZ-B@TSOP48 [SB247-B4806]
TMS28F400AZ-T@PSOP44 [SA638]
TMS28F400AZ-T@TSOP48 [SB247-B4806]
TMS28F400BZ-B@PSOP44 [SA638] TMS28F400BZ-T@PSOP44 [SA638]
TMS28F512
TMS28F512(REVERSE)@TSOP32 [SA410T-B4001]
TMS28F512@PLCC32 [SA015A1T] TMS28F512@TSOP32 [SA410T-B4001]
TMS28F800AE-B@PSOP44 [SA638]
TMS28F800AE-B@TSOP48 [SB247-B4806]
TMS28F800AE-T@PSOP44 [SA638]
TMS28F800AE-T@TSOP48 [SB247-B4806]
TMS28F800AL-B@PSOP44 [SA638]
TMS28F800AL-B@TSOP48 [SB247-B4806]
TMS28F800AL-T@PSOP44 [SA638]
TMS28F800AL-T@TSOP48 [SB247-B4806]
TMS28F800AS-B@PSOP44 [SA638]
TMS28F800AS-B@TSOP48 [SB247-B4806]
TMS28F800AS-T@PSOP44 [SA638]
TMS28F800AS-T@TSOP48 [SB247-B4806]
TMS28F800AV-B@PSOP44 [SA638]
TMS28F800AV-B@TSOP48 [SB247-B4806]
TMS28F800AV-T@PSOP44 [SA638]
TMS28F800AV-T@TSOP48 [SB247-B4806]
TMS28F800AZ-B@PSOP44 [SA638]
TMS28F800AZ-B@TSOP48 [SB247-B4806]
TMS28F800AZ-T@PSOP44 [SA638]
TMS28F800AZ-T@TSOP48 [SB247-B4806]
TMS28F800SE-B@PSOP44 [SA638]
TMS28F800SE-B@TSOP48 [SB247-B4806]
TMS28F800SE-T@PSOP44 [SA638]
TMS28F800SE-T@TSOP48 [SB247-B4806]

TMS28F800SZ-B@PSOP44 [SA638]	
TMS28F800SZ-B@TSOP48 [SB247-B4806]	
TMS28F800SZ-T@PSOP44 [SA638]	
TMS28F800SZ-T@TSOP48 [SB247-B4806]	
TMS29F040	TMS29F040@PLCC32 [SA015A1T]
TMS29F040@TSOP32 [SA410T-B4001]	

TMC

E (E) PROM/FRAM/NVRAM

24A01	24A01@S0IC8 [SA602A]
24A01@TSSOP8 [SA026-B3201]	24A02
24A02@S0IC8 [SA602A]	24A02@TSSOP8 [SA026-B3201]
24A04	24A04@S0IC8 [SA602A]
24A04@TSSOP8 [SA026-B3201]	24A08
24A08@S0IC8 [SA602A]	24A08@TSSOP8 [SA026-B3201]
24A16	24A16@S0IC8 [SA602A]
24A16@TSSOP8 [SA026-B3201]	93LC46(08bit)
93LC46(08bit)@S0IC8 [SA602A]	
93LC46(08bit)@TSSOP8 [SA026-B3201]	93LC46(16bit)@S0IC8 [SA602A]
93LC46(16bit)	
93LC46(16bit)@TSSOP8 [SA026-B3201]	93LC56(08bit)@S0IC8 [SA602A]
93LC56(08bit)	
93LC56(08bit)@TSSOP8 [SA026-B3201]	93LC56(16bit)@S0IC8 [SA602A]
93LC56(16bit)	
93LC56(16bit)@TSSOP8 [SA026-B3201]	93LC57@S0IC8 [SA602A]
93LC57	93LC66(08bit)
93LC57@TSSOP8 [SA026-B3201]	
93LC66(08bit)@S0IC8 [SA602A]	93LC66(16bit)@S0IC8 [SA602A]
93LC66(08bit)@TSSOP8 [SA026-B3201]	
93LC66(16bit)	93LC86(08bit)@S0IC8 [SA602A]
93LC66(16bit)@TSSOP8 [SA026-B3201]	
93LC86(08bit)	93LC86(16bit)@S0IC8 [SA602A]
93LC86(08bit)@TSSOP8 [SA026-B3201]	
93LC86(16bit)	
93LC86(16bit)@TSSOP8 [SA026-B3201]	

TOSHIBA

E (E) PROM/FRAM/NVRAM

TC541000AF@PLCC32	TC541000AP
TC541001AF@PLCC32	TC541001AP
TC54256AF	TC54256AF@S0IC28
TC54256AP	TC54256AP@S0IC28
TC544000P	TC54512AF
TC54512AP	TC571000
TC571000AD	TC571000D
TC571001AD	TC571001D
TC571024D	TC57256
TC57256A	TC57256AD
TC57256ADI	TC57256D
TC574000D	TC574096D
TC574200D	TC57512
TC57512AD	TC578200D
TC57H1000AD	TC57H1001AD

TC57H256D	TC58F400@PSOP44 [SA638]
TC58F400@TSOP48 [SB247-B4806]	TC58F401@PSOP44 [SA638]
TC58F401@TSOP48 [SB247-B4806]	
TC58FVB004FT@TSOP40 [SA409T-B4002]	
TC58FVB008FT@TSOP40 [SA409T-B4002]	
TC58FVB016FT@TSOP40 [SA409T-B4002]	
TC58FVB160AFT@TSOP48 [SB247-B4806]	
TC58FVB160FT@TSOP48 [SB247-B4806]	
TC58FVB321FT@TSOP48 [SB247-B4806]	
TC58FVB400F@PSOP44 [SA638]	
TC58FVB400FT@TSOP48 [SB247-B4806]	
TC58FVB641FT@TSOP48 [SB247-B4806]	
TC58FVB800F@PSOP44 [SA638]	
TC58FVB800FT@TSOP48 [SB247-B4806]	
TC58FVM5B2AFT@TSOP48 [SB247-B4806]	
TC58FVM5B2ATG@TSOP48 [SB247-B4806]	
TC58FVM5B3AFT@TSOP48 [SB247-B4806]	
TC58FVM5B3ATG@TSOP48 [SB247-B4806]	
TC58FVM5T2AFT@TSOP48 [SB247-B4806]	
TC58FVM5T2ATG@TSOP48 [SB247-B4806]	
TC58FVM5T3AFT@TSOP48 [SB247-B4806]	
TC58FVM5T3ATG@TSOP48 [SB247-B4806]	
TC58FVM6B2AFT@TSOP48 [SB247-B4806]	
TC58FVM6B5BTG@TSOP48 [SB247-B4806]	
TC58FVM6T2AFT@TSOP48 [SB247-B4806]	
TC58FVM6T5BTG@TSOP48 [SB247-B4806]	
TC58FVT004FT@TSOP40 [SA409T-B4002]	
TC58FVT008FT@TSOP40 [SA409T-B4002]	
TC58FVT016FT@TSOP40 [SA409T-B4002]	
TC58FVT160AFT@TSOP48 [SB247-B4806]	
TC58FVT160FT@TSOP48 [SB247-B4806]	
TC58FVT321FT@TSOP48 [SB247-B4806]	
TC58FVT400F@PSOP44 [SA638]	
TC58FVT400FT@TSOP48 [SB247-B4806]	
TC58FVT641FT@TSOP48 [SB247-B4806]	
TC58FVT800F@PSOP44 [SA638]	
TC58FVT800FT@TSOP48 [SB247-B4806]	
TC58FYB160FT@TSOP48 [SB247-B4806]	
TC58FYT160FT@TSOP48 [SB247-B4806]	
TC89101(08bit)	TC89101(16bit)
TC89102(08bit)	TC89102(16bit)
TC89121	TC89121@S0IC8 [SA602A]
TC89122	TC89122@S0IC8 [SA602A]
TC97101	TMM24128
TMM24128A	TMM24128AP
TMM24256	TMM24256A
TMM24256AP	TMM24256B
TMM24512	TMM24512A
TMM24512P	TMM2464AP
TMM27128	TMM27128A
TMM27128ADI	TMM27128AP
TMM27256	TMM27256A
TMM27256AD	TMM27256ADI
TMM27256BD	TMM27256BDI
TMM27256D	TMM27256DI
TMM2732	TMM2732A
TMM2732D	TMM27512
TMM27512AD	TMM27512ADI
TMM27512D	TMM27512DI

TMM2764
TMM2764ADI
TMM2764D

TMM2764AD
TMM2764AP
TMM2764DI

TSI

E (E) PROM/FRAM/NVRAM

TS25L010AP [SA605B]
TS25L020AP [SA605B]

TS25L010AP@SOP8 [SA605B]
TS25L020AP@SOP8 [SA605B]

TURBO IC

E (E) PROM/FRAM/NVRAM

TU24C01
TU24C02
TU24C04
TU24C08
TU24C128
TU24C16
TU24C16@TSSOP8
TU24C256@S0IC8 [SA602A]
TU24C32@S0IC8 [SA602A]
TU24C64@S0IC8 [SA602A]

TU24C01@S0IC8 [SA602A]
TU24C02@S0IC8 [SA602A]
TU24C04@S0IC8 [SA602A]
TU24C08@S0IC8 [SA602A]
TU24C128@S0IC8 [SA602A]
TU24C16@S0IC8 [SA602A]
TU24C256
TU24C32
TU24C64

UMC

E (E) PROM/FRAM/NVRAM

2732

2764

VERSACHIPS

MICROCONTROLLER

V87C54
V87C54@TQFP44 [SA245A-B4805]
V87C58@PLCC44 [SA244]

V87C54@PLCC44 [SA244]
V87C58
V87C58@TQFP44 [SA245A-B4805]

VLSI

E (E) PROM/FRAM/NVRAM

VT27C128
VT27C512
VT28H64

VT27C256
VT27C64
VT28HC64

PLD

GAL16V8

WHITE ELECTRONIC DESIGNS

E (E) PROM/FRAM/NVRAM

WE128K8
WE512K8
WF256K8@CLCC32 [SA015A1T]
WF512K8
WF512K8@CS0J32 [SA646]
WME128K8@CLCC32 [SA015A1T]
WMF128K8
WMF128K8@CS0J32 [SA646]
WMF256K8@CLCC32 [SA015A1T]
WMF512K8
WMF512K8@CS0J32 [SA646]
WMS128K8@CLCC32 [SA015A1T]
WMS256K8
WMS256K8@CS0J32 [SA646]
WMS512K8@CLCC32 [SA015A1T]

WE256K8
WF256K8
WF256K8@CS0J32 [SA646]
WF512K8@CLCC32 [SA015A1T]
WME128K8
WME128K8@CS0J32 [SA646]
WMF128K8@CLCC32 [SA015A1T]
WMF256K8
WMF256K8@CS0J32 [SA646]
WMF512K8@CLCC32 [SA015A1T]
WMS128K8
WMS128K8@CS0J32 [SA646]
WMS256K8@CLCC32 [SA015A1T]
WMS512K8
WMS512K8@CS0J32 [SA646]

WINBOND

E (E) PROM/FRAM/NVRAM

W19B160BBT@TSOP48 [SB247-B4806]
W19B320ABT@TSOP48 [SB247-B4806]
W19B320BBT@TSOP48 [SB247-B4806]
W19B320SBT@TSOP48 [SB247-B4806]
W19B322MBT@TSOP48 [SB247-B4806]
W19B323MBT@TSOP48 [SB247-B4806]
W19B324MBT@TSOP48 [SB247-B4806]
W19L320SBT@TSOP48 [SB247-B4806]
W25B40(Bottom Boot)@MLP8 [SA683]
W25B40(Bottom Boot)@S0IC8 [SA602A]
W25B40(Top Boot)@MLP8 [SA683]
W25B40A(Bottom Boot)@MLP8 [SA683]
W25B40A(Bottom Boot)@S0IC8 [SA602A]
W25B40A(Top Boot)@MLP8 [SA683]
W25D10
W25D10(SS)@S0IC8 [SA605B]
W25D20
W25D20(SS)@S0IC8 [SA605B]
W25D40
W25D40(SS)@S0IC8 [SA605B]
W25D80
W25D80(SS)@S0IC8 [SA605B]
W25P10@MLP8 [SA683]
W25P16@MLP8 [SA683]
W25P16@S0IC8 [SA605B]
W25P20@S0IC8 [SA602A]
W25P32@S0IC16 [SA404]
W25P40@S0IC8 [SA602A]
W25P64@S0IC16 [SA404]
W25P80@S0IC8 [SA602A]
W25Q128BV@WS0N8 [SA684]
W25Q16@S0IC16 [SA404]
W25Q16BV(SF)@S0IC16 [SA404]
W25Q16BV(SS)@S0IC8 [SA605B]

W19B160BTT@TSOP48 [SB247-B4806]
W19B320ATT@TSOP48 [SB247-B4806]
W19B320BTT@TSOP48 [SB247-B4806]
W19B320STT@TSOP48 [SB247-B4806]
W19B322MTT@TSOP48 [SB247-B4806]
W19B323MTT@TSOP48 [SB247-B4806]
W19B324MTT@TSOP48 [SB247-B4806]
W19L320STT@TSOP48 [SB247-B4806]
W25B40(Top Boot)@S0IC8 [SA602A]
W25B40A(Top Boot)@S0IC8 [SA602A]
W25D10(SN)@S0IC8 [SA602A]
W25D10(ZP)@WS0N8 [SA683]
W25D20(SN)@S0IC8 [SA602A]
W25D20(ZP)@WS0N8 [SA683]
W25D40(SN)@S0IC8 [SA602A]
W25D40(ZP)@WS0N8 [SA683]
W25D80(SN)@S0IC8 [SA602A]
W25D80(ZP)@WS0N8 [SA683]
W25P10@S0IC8 [SA602A]
W25P16@S0IC16 [SA404]
W25P20@MLP8 [SA683]
W25P32@MLP8 [SA683]
W25P40@MLP8 [SA683]
W25P64@MLP8 [SA683]
W25P80@MLP8 [SA683]
W25Q128BV@S0IC16 [SA404]
W25Q16@MLP8 [SA683]
W25Q16@S0IC8 [SA605B]
W25Q16BV(SN)@S0IC8 [SA602A]
W25Q16BV(ZP)@WS0N8 [SA683]

W25Q16CV(SF)@S0IC16 [SA404]
W25Q16CV(SS)@S0IC8 [SA605B]
W25Q16V(SF)@S0IC16 [SA404]
W25Q16V(ZP)@WSON8 [SA683]
W25Q32@S0IC16 [SA404]
W25Q32BV(SF)@S0IC16 [SA404]
W25Q32BV(ZP)@WSON8 [SA683]
W25Q32BW(SN)@S0IC8 [SA602A]
W25Q32BW(ZP)@WSON8 [SA683]
W25Q32V(SS)@S0IC8 [SA605B]
W25Q64BV(SF)@S0IC16 [SA404]
W25Q64BV(ZE)@WSON8 [SA684]
W25Q64CV(SS)@S0IC8 [SA605B]
W25Q80@MLP8 [SA683]
W25Q80BV
W25Q80BV@S0IC8[4.0] [SA602A]
W25Q80BV@WSON8 [SA683]
W25X10(SN)@S0IC8 [SA602A]
W25X10(ZP)@WSON8 [SA683]
W25X10AV(SN)@S0IC8 [SA602A]
W25X10AV(ZP)@WSON8 [SA683]
W25X10BV(SN)@S0IC8 [SA602A]
W25X10BV(ZP)@WSON8 [SA683]
W25X10L(SN)@S0IC8 [SA602A]
W25X10V
W25X10V(SS)@S0IC8 [SA605B]
W25X16@S0IC16 [SA404]
W25X16AL
W25X16AL(SN)@S0IC8 [SA602A]
W25X16AL(ZP)@WSON8 [SA683]
W25X16AV(SF)@S0IC16 [SA404]
W25X16AV(SS)@S0IC8 [SA605B]
W25X16BV
W25X16BV(SN)@S0IC8 [SA602A]
W25X16BV(ZP)@WSON8 [SA683]
W25X16V(SF)@S0IC16 [SA404]
W25X16V(ZP)@WSON8 [SA683]
W25X20(SN)@S0IC8 [SA602A]
W25X20(ZP)@WSON8 [SA683]
W25X20AV(SN)@S0IC8 [SA602A]
W25X20AV(ZP)@WSON8 [SA683]
W25X20BV(SN)@S0IC8 [SA602A]
W25X20BV(ZP)@WSON8 [SA683]
W25X20L(SN)@S0IC8 [SA602A]
W25X20V
W25X20V(SS)@S0IC8 [SA605B]
W25X32@S0IC16 [SA404]
W25X32AV(SF)@S0IC16 [SA404]
W25X32AV(ZP)@WSON8 [SA683]
W25X32V(SS)@S0IC8 [SA605B]
W25X40
W25X40(SS)@S0IC8 [SA605B]
W25X40AV
W25X40AV(SS)@S0IC8 [SA605B]
W25X40BV
W25X40BV(SS)@S0IC8 [SA605B]
W25X40L
W25X40L(SS)@S0IC8 [SA605B]
W25X40V

W25Q16CV(SN)@S0IC8 [SA602A]
W25Q16CV(ZP)@WSON8 [SA683]
W25Q16V(SS)@S0IC8 [SA605B]
W25Q32@MLP8 [SA683]
W25Q32BV
W25Q32BV(SS)@S0IC8 [SA605B]
W25Q32BW(SF)@S0IC16 [SA404]
W25Q32BW(SS)@S0IC8 [SA605B]
W25Q32V(SF)@S0IC16 [SA404]
W25Q32V(ZP)@WSON8 [SA683]
W25Q64BV(SS)@S0IC8 [SA605B]
W25Q64CV(SF)@S0IC16 [SA404]
W25Q64CV(ZE)@WSON8 [SA684]
W25Q80@S0IC8 [SA602A]
W25Q80BV@S0IC16 [SA404]
W25Q80BV@S0IC8[5.4] [SA605B]
W25X10
W25X10(SS)@S0IC8 [SA605B]
W25X10AV
W25X10AV(SS)@S0IC8 [SA605B]
W25X10BV
W25X10BV(SS)@S0IC8 [SA605B]
W25X10L
W25X10L(ZP)@WSON8 [SA683]
W25X10V(SN)@S0IC8 [SA602A]
W25X10V(ZP)@WSON8 [SA683]
W25X16@S0IC8 [SA605B]
W25X16AL(SF)@S0IC16 [SA404]
W25X16AL(SS)@S0IC8 [SA605B]
W25X16AV
W25X16AV(SN)@S0IC8 [SA602A]
W25X16AV(ZP)@WSON8 [SA683]
W25X16BV(SF)@S0IC16 [SA404]
W25X16BV(SS)@S0IC8 [SA605B]
W25X16V
W25X16V(SS)@S0IC8 [SA605B]
W25X20
W25X20(SS)@S0IC8 [SA605B]
W25X20AV
W25X20AV(SS)@S0IC8 [SA605B]
W25X20BV
W25X20BV(SS)@S0IC8 [SA605B]
W25X20L
W25X20L(ZP)@WSON8 [SA683]
W25X20V(SN)@S0IC8 [SA602A]
W25X20V(ZP)@WSON8 [SA683]
W25X32@S0IC8 [SA605B]
W25X32AV(SS)@S0IC8 [SA605B]
W25X32V(SF)@S0IC16 [SA404]
W25X32V(ZP)@WSON8 [SA683]
W25X40(SN)@S0IC8 [SA602A]
W25X40(ZP)@WSON8 [SA683]
W25X40AV(SN)@S0IC8 [SA602A]
W25X40AV(ZP)@WSON8 [SA683]
W25X40BV(SN)@S0IC8 [SA602A]
W25X40BV(ZP)@WSON8 [SA683]
W25X40L(SN)@S0IC8 [SA602A]
W25X40L(ZP)@WSON8 [SA683]
W25X40V(SN)@S0IC8 [SA602A]

W25X40V(SS)@S0IC8 [SA605B]
W25X64@S0IC16 [SA404]
W25X64BV(SF)@S0IC16 [SA404]
W25X64BV(ZE)@WS0N8 [SA684]
W25X64V(SS)@S0IC8 [SA605B]
W25X80
W25X80(SS)@S0IC8 [SA605B]
W25X80AV
W25X80AV(SS)@S0IC8 [SA605B]
W25X80L
W25X80L(ZP)@WS0N8 [SA683]
W25X80V(SN)@S0IC8 [SA602A]
W25X80V(ZP)@WS0N8 [SA683]
W27C01@PLCC32 [SA015A1T]
W27C010
W27C010@S0IC32 [SA603]
W27C02@PLCC32 [SA015A1T]
W27C020
W27C020M
W27C257
W27C4096
W27C4096@TSOP40 [SA409T-B4002]
W27C512@PLCC32 [SA015A1T]
W27C520@S0IC20 [SA404]
W27E01
W27E01@VSOP32 [SA620-B4807]
W27E010@PLCC32 [SA015A1T]
W27E02
W27E02@VSOP32 [SA620-B4807]
W27E020@PLCC32 [SA015A1T]
W27E040@PLCC32 [SA015A1T]
W27E257
W27E400
W27E4096@PLCC44 [SA244]
W27E512
W27E512@TSOP28 [SA430T-B4003]
W27E520@TSSOP20 [SA026-B3201]
W27L01@PLCC32 [SA015A1T]
W27L010
W27L02
W27L02@VSOP32 [SA620-B4807]
W27L520@TSSOP20 [SA026-B3201]
W28F321TT@TSOP48 [SB247-B4806]
W28F641TT@TSOP48 [SB247-B4806]
W28J160TT@TSOP48 [SB247-B4806]
W28J320TT@TSOP48 [SB247-B4806]
W28J800TT@TSOP48 [SB247-B4806]
W28V400TT@TSOP48 [SB247-B4806]
W29C010@PLCC32 [SA015A1T]
W29C011A@PLCC32 [SA015A1T]
W29C020@PLCC32 [SA015A1T]
W29C020@TSOP32 [SA410T-B4001]
W29C020C@PLCC32 [SA015A1T]
W29C020C@VSOP32 [SA620-B4807]
W29C040@PLCC32 [SA015A1T]
W29C040@VSOP32 [SA620-B4807]
W29C101@PLCC44 [SA244]
W29C102
W29C102@TSOP40 [SA409T-B4002]

W25X40V(ZP)@WS0N8 [SA683]
W25X64@S0IC8 [SA605B]
W25X64BV(SS)@S0IC8 [SA605B]
W25X64V(SF)@S0IC16 [SA404]
W25X64V(ZE)@WS0N8 [SA684]
W25X80(SN)@S0IC8 [SA602A]
W25X80(ZP)@WS0N8 [SA683]
W25X80AV(SN)@S0IC8 [SA602A]
W25X80AV(ZP)@WS0N8 [SA683]
W25X80L(SS)@S0IC8 [SA605B]
W25X80V
W25X80V(SS)@S0IC8 [SA605B]
W27C01
W27C01@VSOP32 [SA620-B4807]
W27C010@PLCC32 [SA015A1T]
W27C02
W27C02@VSOP32 [SA620-B4807]
W27C020@PLCC32 [SA015A1T]
W27C020M@PLCC32 [SA015A1T]
W27C257@PLCC32 [SA015A1T]
W27C4096@PLCC44 [SA244]
W27C512
W27C512@TSOP28 [SA430T-B4003]
W27C520@TSSOP20 [SA026-B3201]
W27E01@PLCC32 [SA015A1T]
W27E010
W27E010@S0IC32 [SA603]
W27E02@PLCC32 [SA015A1T]
W27E020
W27E040
W27E040@S0IC32 [SA603]
W27E257@PLCC32 [SA015A1T]
W27E4096
W27E4096@TSOP40 [SA409T-B4002]
W27E512@PLCC32 [SA015A1T]
W27E520@S0IC20 [SA404]
W27L01
W27L01@VSOP32 [SA620-B4807]
W27L010@PLCC32 [SA015A1T]
W27L02@PLCC32 [SA015A1T]
W27L520@S0IC20 [SA404]
W28F321BT@TSOP48 [SB247-B4806]
W28F641BT@TSOP48 [SB247-B4806]
W28J160BT@TSOP48 [SB247-B4806]
W28J320BT@TSOP48 [SB247-B4806]
W28J800BT@TSOP48 [SB247-B4806]
W28V400BT@TSOP48 [SB247-B4806]
W29C010
W29C011A
W29C020
W29C020@S0IC32
W29C020C
W29C020C@TSOP32 [SA410T-B4001]
W29C040
W29C040@TSOP32 [SA410T-B4001]
W29C101
W29C101@TSOP40 [SA409T-B4002]
W29C102@PLCC44 [SA244]
W29C102@VSOP40 [SA623-B4002]

W29EE010	W29EE010@PLCC32 [SA015A1T]
W29EE010@TSOP32 [SA410T-B4001]	W29EE011
W29EE011@PLCC32 [SA015A1T]	W29EE011@TSOP32 [SA410T-B4001]
W29EE012	W29EE012@PLCC32 [SA015A1T]
W29EE012@S0IC32 [SA438T]	W29EE512
W29EE512@PLCC32 [SA015A1T]	W29EE512@TSOP32 [SA410T-B4001]
W29F040	W29F040@PLCC32 [SA015A1T]
W29F040@TSOP32 [SA410T-B4001]	W29F102P@PLCC44 [SA244]
W29F102Q@TSOP40 [SA623-B4002]	W29L102P@PLCC44 [SA244]
W29L102Q@TSOP40 [SA623-B4002]	W39F010
W39F010@PLCC32 [SA015A1T]	
W39F010@TSOP32[12.4mm] [SA620-B4807]	
W39F010@TSOP32[18.4mm] [SA410T-B4001]	
W39L010@PLCC32 [SA015A1T]	W39L010@TSOP32 [SA620-B4807]
W39L020@PLCC32 [SA015A1T]	
W39L020@TSOP32[12.4mm] [SA620-B4807]	
W39L020@TSOP32[18.4mm] [SA410T-B4001]	
W39L040@PLCC32 [SA015A1T]	
W39L040@TSOP32[12.4mm] [SA620-B4807]	
W39L040@TSOP32[18.4mm] [SA410T-B4001]	
W39L040A	W39L040A@PLCC32 [SA015A1T]
W39L040A@TSOP32 [SA410T-B4001]	W39L040A@VSOP32 [SA620-B4807]
W39L512@PLCC32 [SA015A1T]	W39L512@TSOP32 [SA620-B4807]
W39V040AP@PLCC32 [SA015A1T]	W39V040AQ@VSOP32 [SA620-B4807]
W39V040B(P)@PLCC32 [SA015A1T]	W39V040B(Q)@VSOP32 [SA620-B4807]
W39V040CP@PLCC32 [SA015A1T]	W39V040CPZ@PLCC32 [SA015A1T]
W39V040CQ@VSOP32 [SA620-B4807]	W39V040CQZ@VSOP32 [SA620-B4807]
W39V040FAP@PLCC32 [SA015A1T]	W39V040FAQ@VSOP32 [SA620-B4807]
W39V040FAT@TSOP40 [SA409T-B4002]	W39V040FB(P)@PLCC32 [SA015A1T]
W39V040FB(Q)@VSOP32 [SA620-B4807]	
W39V040FCP@PLCC32 [SA015A1T]	W39V040FCPZ@PLCC32 [SA015A1T]
W39V040FCQ@VSOP32 [SA620-B4807]	W39V040FCQZ@VSOP32 [SA620-B4807]
W39V080A(P)@PLCC32 [SA015A1T]	W39V080A(Q)@VSOP32 [SA620-B4807]
W39V080A(T)@TSOP40 [SA409T-B4002]	
W39V080FA(P)@PLCC32 [SA015A1T]	
W39V080FA(Q)@VSOP32 [SA620-B4807]	
W39V080FA(T)@TSOP40 [SA409T-B4002]	
W45B012@PLCC32 [SA015A1T]	W45B012@SON8 [SA683]
W45B512@PLCC32 [SA015A1T]	W45B512@SON8 [SA683]
W49F002	W49F002@PLCC32 [SA015A1T]
W49F002@TSOP32 [SA410T-B4001]	W49F002B
W49F002B@PLCC32 [SA015A1T]	W49F002B@TSOP32 [SA410T-B4001]
W49F002N	W49F002N@PLCC32 [SA015A1T]
W49F002N@TSOP32 [SA410T-B4001]	W49F002U
W49F002U@PLCC32 [SA015A1T]	W49F002U@TSOP32 [SA410T-B4001]
W49F020	W49F020@PLCC32 [SA015A1T]
W49F020@TSOP32 [SA410T-B4001]	W49F102P@PLCC44 [SA244]
W49F102Q@TSOP40 [SA623-B4002]	W49F201S@PSOP44 [SA638]
W49F201T@TSOP48 [SB247-B4806]	W49L102P@PLCC44 [SA244]
W49L102Q@TSOP40 [SA623-B4002]	W49L201S@PSOP44 [SA638]
W49L201T@TSOP48 [SB247-B4806]	W49L401S@PSOP44 [SA638]
W49L401T@TSOP48 [SB247-B4806]	W49V002A@PLCC32 [SA015A1T]
W49V002A@VSOP32 [SA620-B4807]	W49V002FA@PLCC32 [SA015A1T]
W49V002FA@VSOP32 [SA620-B4807]	W49V002FP@PLCC32 [SA015A1T]
W49V002FP@VSOP32 [SA620-B4807]	W49V002P@PLCC32 [SA015A1T]
W49V002P@VSOP32 [SA620-B4807]	W55F05
W55F10A	W55F20

W77E516
W77E516@TQFP44 [SA675-B4805]
W77E532@PLCC44 [SA244]
W77E532A
W77E532A@TQFP44 [SA675-B4805]
W77E58@PLCC44 [SA244]
W77IE58
W77IE58@TQFP44 [SA675-B4805]
W77L058A@PLCC44 [SA244]
W77L516A
W77L516A@TQFP44 [SA675-B4805]
W77L532A@PLCC44 [SA244]
W77LE516
W77LE516@TQFP44 [SA675-B4805]
W77LE532@PLCC44 [SA244]
W77LE58
W77LE58@TQFP44 [SA675-B4805]
W77LE58A@PLCC44 [SA244]
W78E051B
W78E051B@TQFP44 [SA675-B4805]
W78E051C@PLCC44 [SA244]
W78E051DDG
W78E051DLG@LQFP48 [SA248-B4804]
W78E052B
W78E052B@TQFP44 [SA675-B4805]
W78E052C@PLCC44 [SA244]
W78E052DDG
W78E052DLG@LQFP48 [SA248-B4804]
W78E054B
W78E054B@TQFP44 [SA675-B4805]
W78E054C@PLCC44 [SA244]
W78E054DDG
W78E054DLG@LQFP48 [SA248-B4804]
W78E058B
W78E058B@TQFP44 [SA675-B4805]
W78E058DFG@TQFP44 [SA675-B4805]
W78E058DPG@PLCC44 [SA244]
W78E065@PLCC44 [SA244]
W78E365
W78E365@TQFP44 [SA675-B4805]
W78E365A@PLCC44 [SA244]
W78E374B
W78E378E
W78E51
W78E51@TQFP44 [SA675-B4805]
W78E516@PLCC44 [SA244]
W78E516B
W78E516B@TQFP44 [SA675-B4805]
W78E516DFG@TQFP44 [SA675-B4805]
W78E516DPG@PLCC44 [SA244]
W78E51B@PLCC44 [SA244]
W78E51B@TQFP44 [SA245A-B4805]
W78E51C@PLCC44 [SA244]
W78E52
W78E52@TQFP44 [SA675-B4805]
W78E52B@PLCC44 [SA244]
W78E52C
W78E52C@TQFP44 [SA675-B4805]
W78E54@PLCC44 [SA244]

W77E516@PLCC44 [SA244]
W77E532
W77E532@TQFP44 [SA675-B4805]
W77E532A@PLCC44 [SA244]
W77E58
W77E58@TQFP44 [SA675-B4805]
W77IE58@PLCC44 [SA244]
W77L058A
W77L058A@TQFP44 [SA675-B4805]
W77L516A@PLCC44 [SA244]
W77L532A
W77L532A@TQFP44 [SA675-B4805]
W77LE516@PLCC44 [SA244]
W77LE532
W77LE532@TQFP44 [SA675-B4805]
W77LE58@PLCC44 [SA244]
W77LE58A
W77LE58A@TQFP44 [SA675-B4805]
W78E051B@PLCC44 [SA244]
W78E051C
W78E051C@TQFP44 [SA675-B4805]
W78E051DFG@PQFP44 [SA675-B4805]
W78E051DPG@PLCC44 [SA244]
W78E052B@PLCC44 [SA244]
W78E052C
W78E052C@TQFP44 [SA675-B4805]
W78E052DFG@PQFP44 [SA675-B4805]
W78E052DPG@PLCC44 [SA244]
W78E054B@PLCC44 [SA244]
W78E054C
W78E054C@TQFP44 [SA675-B4805]
W78E054DFG@PQFP44 [SA675-B4805]
W78E054DPG@PLCC44 [SA244]
W78E058B@PLCC44 [SA244]
W78E058DDG
W78E058DLG@TQFP48 [SA248-B4804]
W78E065
W78E065@TQFP44 [SA675-B4805]
W78E365@PLCC44 [SA244]
W78E365A
W78E365A@TQFP44 [SA675-B4805]
W78E378
W78E378P@PLCC44 [SA244]
W78E51@PLCC44 [SA244]
W78E516
W78E516@TQFP44 [SA675-B4805]
W78E516B@PLCC44 [SA244]
W78E516DDG
W78E516DLG@TQFP48 [SA248-B4804]
W78E51B
W78E51B@PQFP44 [SA675-B4805]
W78E51C
W78E51C@TQFP44 [SA675-B4805]
W78E52@PLCC44 [SA244]
W78E52B
W78E52B@TQFP44 [SA675-B4805]
W78E52C@PLCC44 [SA244]
W78E54
W78E54@PQFP44 [SA675-B4805]

W78E54@TQFP44 [SA245A-B4805]
W78E54B@PLCC44 [SA244]
W78E54C
W78E54C@TQFP44 [SA675-B4805]
W78E58@PLCC44 [SA244]
W78E58@TQFP44 [SA245A-B4805]
W78E58B@PLCC44 [SA244]
W78E62B
W78E62B@TQFP44 [SA675-B4805]
W78E65@PLCC44 [SA244]
W78E858
W78E858@TQFP44 [SA675-B4805]
W78ERD2@PLCC44 [SA244]
W78L051A
W78L051A@TQFP44 [SA675-B4805]
W78L051C@PLCC44 [SA244]
W78L052A
W78L052A@TQFP44 [SA675-B4805]
W78L052C@PLCC44 [SA244]
W78L054A
W78L054A@TQFP44 [SA675-B4805]
W78L054C@PLCC44 [SA244]
W78L058A
W78L058A@TQFP44 [SA675-B4805]
W78L365@PLCC44 [SA244]
W78L365@TQFP48 [SA248-B4804]
W78L365A@PLCC44 [SA244]
W78L365A@TQFP48 [SA248-B4804]
W78L516@PLCC44 [SA244]
W78L516A
W78L516A@TQFP44 [SA675-B4805]
W78L812A@PLCC44 [SA244]
W78LE365
W78LE365@TQFP44 [SA675-B4805]
W78LE51
W78LE51@TQFP44 [SA675-B4805]
W78LE516@PLCC44 [SA244]
W78LE51C
W78LE51C@TQFP44 [SA675-B4805]
W78LE52@PLCC44 [SA244]
W78LE52C
W78LE52C@TQFP44 [SA675-B4805]
W78LE54@PLCC44 [SA244]
W78LE54C
W78LE54C@TQFP44 [SA675-B4805]
W78LE58@PLCC44 [SA244]
W78LE812
W78LE812@TQFP44 [SA675-B4805]
W79E201@TQFP44 [SA675-B4805]
W79E2051(dip16)
W79E2051@S0IC14 [SA404]
W79E2051@S0IC20 [SA404]
W79E2051R@S0IC20 [SA404]
W79E225APG@PLCC44 [SA244]
W79E226APG@PLCC44 [SA244]
W79E227APG@PLCC44 [SA244]
W79E4051(dip16)
W79E4051@S0IC14 [SA404]
W79E4051@S0IC20 [SA404]

W78E54B
W78E54B@TQFP44 [SA675-B4805]
W78E54C@PLCC44 [SA244]
W78E58
W78E58@PQFP44 [SA675-B4805]
W78E58B
W78E58B@TQFP44 [SA675-B4805]
W78E62B@PLCC44 [SA244]
W78E65
W78E65@TQFP44 [SA675-B4805]
W78E858@PLCC44 [SA244]
W78ERD2
W78ERD2@TQFP44 [SA675-B4805]
W78L051A@PLCC44 [SA244]
W78L051C
W78L051C@TQFP44 [SA675-B4805]
W78L052A@PLCC44 [SA244]
W78L052C
W78L052C@TQFP44 [SA675-B4805]
W78L054A@PLCC44 [SA244]
W78L054C
W78L054C@TQFP44 [SA675-B4805]
W78L058A@PLCC44 [SA244]
W78L365
W78L365@TQFP44 [SA675-B4805]
W78L365A
W78L365A@TQFP44 [SA675-B4805]
W78L516
W78L516@TQFP44 [SA675-B4805]
W78L516A@PLCC44 [SA244]
W78L812A
W78L812A@TQFP44 [SA675-B4805]
W78LE365@PLCC44 [SA244]
W78LE365@TQFP48 [SA248-B4804]
W78LE51@PLCC44 [SA244]
W78LE516
W78LE516@TQFP44 [SA675-B4805]
W78LE51C@PLCC44 [SA244]
W78LE52
W78LE52@TQFP44 [SA675-B4805]
W78LE52C@PLCC44 [SA244]
W78LE54
W78LE54@TQFP44 [SA675-B4805]
W78LE54C@PLCC44 [SA244]
W78LE58
W78LE58@TQFP44 [SA675-B4805]
W78LE812@PLCC44 [SA244]
W79E201@PLCC44 [SA244]
W79E2051(dip14)
W79E2051(dip20)
W79E2051@S0IC16 [SA404]
W79E2051R(dip20)
W79E225ALG@TQFP48 [SA248-B4804]
W79E226ALG@TQFP48 [SA248-B4804]
W79E227ALG@TQFP48 [SA248-B4804]
W79E4051(dip14)
W79E4051(dip20)
W79E4051@S0IC16 [SA404]
W79E4051R(dip20)

W79E4051R@S0IC20 [SA404]
W79E532@PLCC44 [SA244]
W79E532A
W79E532A@TQFP44 [SA675-B4805]
W79E632
W79E632@TQFP44 [SA675-B4805]
W79E632A@PLCC44 [SA244]
W79E633A@PLCC44 [SA244]
W79E801A@S0IC20 [SA404]
W79E802A@S0IC20 [SA404]
W79E803A@S0IC20 [SA404]
W79E804A@S0IC20 [SA404]
W79E821A@S0IC20 [SA404]
W79E822A@S0IC20 [SA404]
W79E822B@S0IC20 [SA404]
W79E823A@S0IC20 [SA404]
W79E823B@S0IC20 [SA404]
W79E824A@S0IC20 [SA404]
W79E825A@S0IC20 [SA404]
W79E831A@S0IC28 [SA404]
W79E832A@S0IC28 [SA404]
W79E833A@S0IC28 [SA404]
W79E834A@S0IC28 [SA404]
W79L532@PLCC44 [SA244]
W79L632
W79L632@TQFP44 [SA675-B4805]
W79L632A@PLCC44 [SA244]
W79L633A@PLCC44 [SA244]

W79E532
W79E532@TQFP44 [SA675-B4805]
W79E532A@PLCC44 [SA244]
W79E533A@PLCC44 [SA244]
W79E632@PLCC44 [SA244]
W79E632A
W79E632A@TQFP44 [SA675-B4805]
W79E801A
W79E802A
W79E803A
W79E804A
W79E821A
W79E822A
W79E822B
W79E823A
W79E823B
W79E824A
W79E825A
W79E831A
W79E832A
W79E833A
W79E834A
W79L532
W79L532@TQFP44 [SA675-B4805]
W79L632@PLCC44 [SA244]
W79L632A
W79L632A@TQFP44 [SA675-B4805]

WSI

E (E) PROM/FRAM/NVRAM

WS27C010L
WS27C010L@TSOP32 [SA410T-B4001]
WS27C010R@PLCC32 [SA015A1T]
WS27C040L
WS27C040L@TSOP32 [SA410T-B4001]
WS27C128F@PLCC32 [SA015A1T]
WS27C128L@PLCC32 [SA015A1T]
WS27C210L@PLCC44 [SA244]
WS27C256F@PLCC32 [SA015A1T]
WS27C256L@PLCC32 [SA015A1T]
WS27C512F@PLCC32 [SA015A1T]
WS27C512L@PLCC32 [SA015A1T]
WS27C64@PLCC32 [SA015A1T]
WS27C64F@PLCC32 [SA015A1T]
WS27C64L@PLCC32 [SA015A1T]
WS57C128@PLCC32 [SA015A1T]
WS57C128F@PLCC32 [SA015A1T]
WS57C128FB@PLCC32 [SA015A1T]
WS57C256F@PLCC32 [SA015A1T]
WS57C256FB@PLCC32 [SA015A1T]
WS57C257@PLCC44 [SA244]
WS57C64F@PLCC32 [SA015A1T]

WS27C010L@PLCC32 [SA015A1T]
WS27C010R
WS27C010R@TSOP32 [SA410T-B4001]
WS27C040L@PLCC32 [SA015A1T]
WS27C128F
WS27C128L
WS27C210L
WS27C256F
WS27C256L
WS27C512F
WS27C512L
WS27C64
WS27C64F
WS27C64L
WS57C128
WS57C128F
WS57C128FB
WS57C256F
WS57C256FB
WS57C257
WS57C64F

XELTEK

MICROCONTROLLER

#####222222222222UP
#####888888888888TST

#####333333333333MCU

XICOR

E(E) PROM/FRAM/NVRAM

X2004	X2004@PLCC32 [SA015A1T]
X2004D	X2004D@PLCC32 [SA015A1T]
X2004I	X2004I@PLCC32 [SA015A1T]
X2210	X2210@S0IC16 [SA404]
X2210A	X2210A@S0IC16 [SA404]
X2210I	X2210I@S0IC16 [SA404]
X2212	X2212@S0IC20 [SA404]
X2212A	X2212A@S0IC20 [SA404]
X2212I	X2212I@S0IC20 [SA404]
X22C10	X22C10@S0IC16 [SA404]
X22C10I	X22C10I@S0IC16 [SA404]
X22C12	X22C12@S0IC20 [SA404]
X22C12I	X22C12I@S0IC20 [SA404]
X24012	X24012@S0IC8 [SA602A]
X24022	X24022@S0IC8 [SA602A]
X24026	X24026@S0IC8 [SA602A]
X24042	X24042@S0IC8 [SA602A]
X24164	X24164@S0IC8 [SA602A]
X2444	X2444I
X24C01	X24C01@MSOP8 [SA666]
X24C01@S0IC8 [SA602A]	X24C01A
X24C01A@S0IC8 [SA602A]	X24C01I
X24C01I@S0IC8 [SA602A]	X24C02
X24C02@S0IC8 [SA602A]	X24C02I
X24C02I@S0IC8 [SA602A]	X24C04
X24C04@S0IC14 [SA602]	X24C04@S0IC8 [SA602A]
X24C04I	X24C04I@S0IC14 [SA602]
X24C04I@S0IC8 [SA602A]	X24C08
X24C08@S0IC14 [SA602]	X24C08@S0IC8 [SA602A]
X24C08I	X24C08I@S0IC14 [SA602]
X24C08I@S0IC8 [SA602A]	X24C16
X24C16@S0IC14 [SA602]	X24C16@S0IC8 [SA602A]
X24C16I	X24C16I@S0IC14 [SA602]
X24C16I@S0IC8 [SA602A]	X24C44
X24C44@S0IC8 [SA602A]	X24C44I
X24C44I@S0IC8 [SA602A]	X24C45
X24C45@S0IC8 [SA602A]	X24C45I
X24C45I@S0IC8 [SA602A]	X25020
X25020@S0IC8 [SA602A]	X25021
X25021@S0IC8 [SA602A]	X25040
X25040@S0IC8 [SA602A]	X25041
X25041@S0IC8 [SA602A]	X25043
X25043@MSOP8 [SA666]	X25043@S0IC8 [SA602A]
X25043@TSSOP14 [SA026-B3201]	X25045
X25045@MSOP8 [SA666]	X25045@S0IC8 [SA602A]
X25045@TSSOP14 [SA026-B3201]	X25057@MSOP8 [SA666]
X25057@TSSOP8 [SA026-B3201]	X25080
X25080@S0IC8 [SA602A]	X25080@TSSOP14 [SA026-B3201]

X25097@MSOP8 [SA666]
X25097@TSSOP8 [SA026-B3201]
X25128@S0IC16 [SA602]
X25138@S0IC14 [SA602]
X25138@S0IC8 [SA602A]
X25160
X25160@TSSOP14 [SA026-B3201]
X25163@S0IC8 [SA602A]
X25164
X25164@TSSOP14 [SA026-B3201]
X25165@S0IC8 [SA602A]
X25166
X25166@TSSOP14 [SA026-B3201]
X25168@S0IC8 [SA602A]
X25169
X25169@TSSOP14 [SA026-B3201]
X25256@S0IC8 [SA602A]
X25320
X25323@S0IC8 [SA602A]
X25324@S0IC8 [SA602A]
X25325@S0IC8 [SA602A]
X25326@S0IC8 [SA602A]
X25328@TSSOP14 [SA026-B3201]
X25329@TSSOP14 [SA026-B3201]
X25330@TSSOP14 [SA026-B3201]
X25401@S0IC8 [SA602A]
X25640@S0IC14 [SA602]
X25642@S0IC14 [SA602]
X25642@TSSOP20 [SA026-B3201]
X25644@S0IC14 [SA602]
X25648@S0IC14 [SA602]
X25650
X25650@S0IC8 [SA602A]
X25C02
X25C02@TSSOP8 [SA026-B3201]
X28010@PLCC32 [SA015A1T]
X2804A
X2804A(MB)
X2816A@PLCC32 [SA015A1T]
X2816B@PLCC32 [SA015A1T]
X2816BI@PLCC32 [SA015A1T]
X2816C
X28256
X28256I
X2864A
X2864A(I)@PLCC32 [SA015A1T]
X2864A(M)@PLCC32 [SA015A1T]
X2864A(MB)@PLCC32 [SA015A1T]
X2864A(T)@PLCC32 [SA015A1T]
X2864B
X2864B(I)@PLCC32 [SA015A1T]
X2864B(M)@PLCC32 [SA015A1T]
X2864H
X2864H(I)@PLCC32 [SA015A1T]
X28C010
X28C16A
X28C16B
X28C16C
X28C256

X25097@S0IC8 [SA602A]
X25128
X25138
X25138@S0IC16 [SA602]
X25138@TSSOP8 [SA026-B3201]
X25160@S0IC8 [SA602A]
X25163
X25163@TSSOP14 [SA026-B3201]
X25164@S0IC8 [SA602A]
X25165
X25165@TSSOP14 [SA026-B3201]
X25166@S0IC8 [SA602A]
X25168
X25168@TSSOP14 [SA026-B3201]
X25169@S0IC8 [SA602A]
X25256
X25256@TSSOP20 [SA026-B3201]
X25320@S0IC8 [SA602A]
X25323@TSSOP14 [SA026-B3201]
X25324@TSSOP14 [SA026-B3201]
X25325@TSSOP14 [SA026-B3201]
X25328@S0IC8 [SA602A]
X25329@S0IC8 [SA602A]
X25330@S0IC8 [SA602A]
X25401
X25640
X25642
X25642@S0IC8 [SA602A]
X25643@S0IC14 [SA602]
X25645@S0IC14 [SA602]
X25649@S0IC14 [SA602]
X25650@S0IC14 [SA602]
X25650@TSSOP20 [SA026-B3201]
X25C02@S0IC8 [SA602A]
X28010
X28010@TSOP32 [SA410T-B4001]
X2804A(I)
X2816A
X2816B
X2816BI
X2816BMB
X2816C@PLCC32 [SA015A1T]
X28256@PLCC32 [SA015A1T]
X28256I@PLCC32 [SA015A1T]
X2864A(I)
X2864A(M)
X2864A(MB)
X2864A(T)
X2864A@PLCC32 [SA015A1T]
X2864B(I)
X2864B(M)
X2864B@PLCC32 [SA015A1T]
X2864H(I)
X2864H@PLCC32 [SA015A1T]
X28C010@PLCC32 [SA015A1T]
X28C16A@PLCC32 [SA015A1T]
X28C16B@PLCC32 [SA015A1T]
X28C16C@PLCC32 [SA015A1T]
X28C256@PLCC32 [SA015A1T]

X28C256@TSOP28 [SA430T-B4003]
X28C512@PLCC32 [SA015A1T]
X28C513
X28C64
X28C64@S0IC28 [SA404]
X28HC16
X28HC16@S0IC24 [SA404]
X28HC256@PLCC32 [SA015A1T]
X28HC256@TSOP28 [SA430T-B4003]
X28HC64@PLCC32 [SA015A1T]
X28HC64@TSOP28 [SA430T-B4003]
X28LC512@PLCC32 [SA015A1T]
X28LC513@PLCC32 [SA015A1T]
X28VC256@PLCC32 [SA015A1T]
X40231@S0IC16 [SA404]
X40235@S0IC16 [SA404]
X40239@S0IC16 [SA404]
X4043@MSOP8 [SA026-B3201]
X40430@S0IC14 [SA404]
X40431@S0IC14 [SA404]
X40434@S0IC14 [SA404]
X40435@S0IC14 [SA404]
X4045
X4045@S0IC8 [SA602A]
X5043@MSOP8 [SA666]
X5043@TSSOP14 [SA026-B3201]
X5045@MSOP8 [SA666]
X5045@TSSOP14 [SA026-B3201]
X5083@S0IC8 [SA602A]
X5163
X5163@TSSOP14 [SA026-B3201]
X51638@S0IC8 [SA602A]
X5165
X5165@TSSOP14 [SA026-B3201]
X5168@S0IC8 [SA602A]
X5169
X5169@TSSOP14 [SA026-B3201]
X5323@S0IC8 [SA602A]
X5325
X5325@TSSOP14 [SA026-B3201]
X5328@S0IC8 [SA602A]
X5329
X5329@TSSOP14 [SA026-B3201]
X5643@S0IC14
X5643@TSSOP20 [SA026-B3201]
X5645@S0IC14 [SA602]
X5645@TSSOP20 [SA026-B3201]
X5648@S0IC14 [SA602]
X5649@S0IC14 [SA602]
XD2210@S0IC16 [SA404]
XM28C020

X28C512
X28C512@TSOP40 [SA409T-B4002]
X28C513@PLCC32 [SA015A1T]
X28C64@PLCC32 [SA015A1T]
X28C64@TSOP28 [SA430T-B4003]
X28HC16@PLCC32 [SA015A1T]
X28HC256
X28HC256@S0IC28 [SA404]
X28HC64
X28HC64@S0IC28 [SA404]
X28LC512
X28LC513
X28VC256
X28VC256@TSOP28 [SA430T-B4003]
X40233@S0IC16 [SA404]
X40237@S0IC16 [SA404]
X4043
X4043@S0IC8 [SA602A]
X40430@TSSOP14 [SA026-B3201]
X40431@TSSOP14 [SA026-B3201]
X40434@TSSOP14 [SA026-B3201]
X40435@TSSOP14 [SA026-B3201]
X4045@MSOP8 [SA026-B3201]
X5043
X5043@S0IC8 [SA602A]
X5045
X5045@S0IC8 [SA602A]
X5083
X5083@TSSOP8 [SA026-B3201]
X5163@S0IC8 [SA602A]
X51638
X51638@TSSOP14 [SA026-B3201]
X5165@S0IC8 [SA602A]
X5168
X5168@TSSOP14 [SA026-B3201]
X5169@S0IC8 [SA602A]
X5323
X5323@TSSOP14 [SA026-B3201]
X5325@S0IC8 [SA602A]
X5328
X5328@TSSOP14 [SA026-B3201]
X5329@S0IC8 [SA602A]
X5643
X5643@S0IC8 [SA602A]
X5645
X5645@S0IC8 [SA602A]
X5648
X5649
XD2210
XM28C010
XM28C040

XILINX

E (E) PROM / FRAM / NVRAM

XC1701
XC1701@PLCC44 [SA244]

XC1701@PLCC20 [SA001A-B2001]
XC1701@S0IC20 [SA404]

XC1701L
XC1701L@PLCC44 [SA244]
XC1702L@PLCC44 [SA244]
XC1704L@PLCC44 [SA244]
XC17128D
XC17128D@S0IC8 [SA602A]
XC17128E
XC17128E@V0IC8 [SA602A]
XC17128EL@PLCC20 [SA001A-B2001]
XC17128L
XC17128L@S0IC8 [SA602A]
XC17128X
XC17128X@S0IC8 [SA602A]
XC1718D
XC1718D@S0IC8 [SA602A]
XC1718L
XC1718L@S0IC8 [SA602A]
XC17256D
XC17256D@S0IC8 [SA602A]
XC17256E
XC17256E@V0IC8 [SA602A]
XC17256EL@PLCC20 [SA001A-B2001]
XC17256L
XC17256L@S0IC8 [SA602A]
XC17256X
XC17256X@S0IC8 [SA602A]
XC1736D
XC1736D@S0IC8 [SA602A]
XC1736E
XC1736E@S0IC8 [SA602A]
XC17512L
XC17512L@PLCC44 [SA244]
XC1765D
XC1765D@S0IC8 [SA602A]
XC1765E
XC1765E@S0IC8 [SA602A]
XC1765EL
XC1765EL@S0IC8 [SA602A]
XC1765L
XC1765L@S0IC8 [SA602A]
XC1765X
XC1765X@S0IC8 [SA602A]
XC17S05
XC17S05XL(L)
XC17S10
XC17S100A
XC17S100A@S0IC8 [SA602A]
XC17S100XL(L)@S0IC20 [SA404]
XC17S10XL(L)@S0IC8 [SA602A]
XC17S150A@S0IC20 [SA404]
XC17S150XL(L)
XC17S15A
XC17S15A@S0IC8 [SA602A]
XC17S20@S0IC8 [SA602A]
XC17S200A@S0IC8 [SA602A]
XC17S20XL(L)
XC17S30
XC17S300A@TQFP44 [SA245A-B4805]
XC17S30A@S0IC20 [SA404]

XC1701L@PLCC20 [SA001A-B2001]
XC1701L@S0IC20 [SA404]
XC1702L@TQFP44 [SA245A-B4805]
XC1704L@TQFP44 [SA245A-B4805]
XC17128D@PLCC20 [SA001A-B2001]
XC17128D@V0IC8 [SA602A]
XC17128E@PLCC20 [SA001A-B2001]
XC17128EL
XC17128EL@V0IC8 [SA602A]
XC17128L@PLCC20 [SA001A-B2001]
XC17128L@V0IC8 [SA602A]
XC17128X@PLCC20 [SA001A-B2001]
XC17128X@V0IC8 [SA602A]
XC1718D@PLCC20 [SA001A-B2001]
XC1718D@V0IC8 [SA602A]
XC1718L@PLCC20 [SA001A-B2001]
XC1718L@V0IC8 [SA602A]
XC17256D@PLCC20 [SA001A-B2001]
XC17256D@V0IC8 [SA602A]
XC17256E@PLCC20 [SA001A-B2001]
XC17256EL
XC17256EL@V0IC8 [SA602A]
XC17256L@PLCC20 [SA001A-B2001]
XC17256L@V0IC8 [SA602A]
XC17256X@PLCC20 [SA001A-B2001]
XC17256X@V0IC8 [SA602A]
XC1736D@PLCC20 [SA001A-B2001]
XC1736D@V0IC8 [SA602A]
XC1736E@PLCC20 [SA001A-B2001]
XC1736E@V0IC8 [SA602A]
XC17512L@PLCC20 [SA001A-B2001]
XC17512L@S0IC20 [SA404]
XC1765D@PLCC20 [SA001A-B2001]
XC1765D@V0IC8 [SA602A]
XC1765E@PLCC20 [SA001A-B2001]
XC1765E@V0IC8 [SA602A]
XC1765EL@PLCC20 [SA001A-B2001]
XC1765EL@V0IC8 [SA602A]
XC1765L@PLCC20 [SA001A-B2001]
XC1765L@V0IC8 [SA602A]
XC1765X@PLCC20 [SA001A-B2001]
XC1765X@V0IC8 [SA602A]
XC17S05@S0IC8 [SA602A]
XC17S05XL(L)@S0IC8 [SA602A]
XC17S10@S0IC8 [SA602A]
XC17S100A@S0IC20 [SA404]
XC17S100XL(L)
XC17S10XL(L)
XC17S150A
XC17S150A@S0IC8 [SA602A]
XC17S150XL(L)@S0IC20 [SA404]
XC17S15A@S0IC20 [SA404]
XC17S20
XC17S200A
XC17S200A@TQFP44 [SA245A-B4805]
XC17S20XL(L)@S0IC8 [SA602A]
XC17S30@S0IC8 [SA602A]
XC17S30A
XC17S30A@S0IC8 [SA602A]

XC17S30XL(L)
XC17S40
XC17S40XL(L)
XC17S50A
XC17S50A@S0IC8 [SA602A]
XC17S50XL(L)@S0IC20 [SA404]
XC17V01@S0IC20 [SA404]
XC17V02@PLCC20 [SA001A-B2001]
XC17V02@TQFP44 [SA245A-B4805]
XC17V04@PLCC44 [SA244]
XC17V08@PLCC44 [SA244]
XC17V16@PLCC44 [SA244]
XC18V01@PLCC20 [SA001A-B2001]
XC18V01@TQFP44 [SA245A-B4805]
XC18V02@TQFP44 [SA245A-B4805]
XC18V04@TQFP44 [SA245A-B4805]
XC18V256@S0IC20 [SA404]
XC18V512@PLCC20 [SA001A-B2001]
XC18V512@TQFP44 [SA245A-B4805]

XC17S30XL(L)@S0IC8 [SA602A]
XC17S40@S0IC20 [SA404]
XC17S40XL(L)@S0IC20 [SA404]
XC17S50A@S0IC20 [SA404]
XC17S50XL(L)
XC17V01@PLCC20 [SA001A-B2001]
XC17V01@S0IC8 [SA602A]
XC17V02@PLCC44 [SA244]
XC17V04@PLCC20 [SA001A-B2001]
XC17V04@TQFP44 [SA245A-B4805]
XC17V08@TQFP44 [SA245A-B4805]
XC17V16@TQFP44 [SA245A-B4805]
XC18V01@S0IC20 [SA404]
XC18V02@PLCC44 [SA411A]
XC18V04@PLCC44 [SA411A]
XC18V256@PLCC20 [SA001A-B2001]
XC18V256@TQFP44 [SA245A-B4805]
XC18V512@S0IC20 [SA404]

YMC

E(E) PROM/FRAM/NVRAM

Y24LC01
Y24LC01@TSSOP8 [SA026-B3201]
Y24LC02@S0IC8 [SA602A]
Y24LC02A
Y24LC02A@TSSOP8 [SA026-B3201]
Y24LC04@S0IC8 [SA602A]
Y24LC08
Y24LC08@TSSOP8 [SA026-B3201]
Y24LC16@S0IC8 [SA602A]
Y24LC32
Y24LC32@TSSOP8 [SA026-B3201]
Y24LC64@S0IC8 [SA602A]
Y54LC64
Y54LC64@TSSOP8 [SA026-B3201]
Y93LC46(16bit)@S0IC8 [SA602A]
Y93LC46(16bit)@TSSOP8 [SA026-B3201]
Y93LC46-08
Y93LC46-08-T8 [SA026-B3201]
Y93LC66(08bit)@S0IC8 [SA602A]
Y93LC66(08bit)@TSSOP8 [SA026-B3201]
Y93LC66(16bit)
Y93LC66(16bit)@TSSOP8 [SA026-B3201]
Y93LC86(08bit)
Y93LC86(08bit)@TSSOP8 [SA026-B3201]
Y93LC86(16bit)
Y93LC86(16bit)@TSSOP8 [SA026-B3201]

Y24LC01@S0IC8 [SA602A]
Y24LC02
Y24LC02@TSSOP8 [SA026-B3201]
Y24LC02A@S0IC8 [SA602A]
Y24LC04
Y24LC04@TSSOP8 [SA026-B3201]
Y24LC08@S0IC8 [SA602A]
Y24LC16
Y24LC16@TSSOP8 [SA026-B3201]
Y24LC32@S0IC8 [SA602A]
Y24LC64
Y24LC64@TSSOP8 [SA026-B3201]
Y54LC64@S0IC8 [SA602A]
Y93LC46(16bit)
Y93LC46-08-S8 [SA602A]
Y93LC66(08bit)
Y93LC66(16bit)@S0IC8 [SA602A]
Y93LC86(08bit)@S0IC8 [SA602A]
Y93LC86(16bit)@S0IC8 [SA602A]

YSS

E(E) PROM/FRAM/NVRAM

Y25F05@SOP8 [SA602A]
Y25F10@SOP8 [SA602A]
Y25F05@VQFN8 [SA683]
Y25F10@VQFN8 [SA683]

YXLDZ

E (E) PROM/FRAM/NVRAM

YXL9020F [SA602A]

ZMD

E (E) PROM/FRAM/NVRAM

U62256	U6264
U6264@S0IC28	U6264A
U6264A@S0IC28 [SA630]	U62H256A@S0IC28 [SA630]
U62H256S@S0IC28 [SA630]	U62H64SA@S0IC28 [SA630]
U630H16	U630H16@S0IC28 [SA630]
U630H64	U630H64@S0IC28 [SA630]
U631H16	U631H16@S0IC24 [SA404]
U631H16@S0IC28 [SA630]	U631H256
U631H256@S0IC28 [SA630]	U631H64
U631H64@S0IC28 [SA630]	U632H16
U632H16@S0IC28 [SA630]	U632H64
U632H64@S0IC28 [SA630]	U634H256
U634H256@S0IC32 [SA630]	U635H16
U635H16@S0IC24 [SA404]	U635H256
U635H256@S0IC28 [SA630]	U635H64
U635H64@S0IC28 [SA630]	U63716
U637256	U63764
U637H256	UL62H256A@S0IC28 [SA630]
UL631H256@S0IC28 [SA630]	UL631H256@TSOP32 [SA410T-B4001]
UL634H256@S0IC32 [SA630]	UL634H256@TSOP32 [SA410T-B4001]
UL635H256@S0IC28 [SA630]	UL635H256@S0IC32 [SA410T-B4001]