

NOTES:

- 1) CAPACITANCE (1000hrs.): 8200pF
- 2) CAP TOLERANCE: Z(+80/-20%)
- 3) DISSIPATION FACTOR: 4% MAX.
- 4) INSULATION RESISTANCE: 25°C, 10 GOHM
- 5) 100 VDC RATED @ +85°C
- 6) DIELECTRIC WITHSTANDING VOLTAGE: 250 VDC
- 7) CURRENT RATING: 10 AMPS
- 8) MARKING:



MARKING:
PART: NONE

<u>PACKAGE:</u>	PART NUMBER
	SCI DATE CODE
	QTY


PACKING NOTES:

BULK PACK:
200 PCS/BAG MAX.

9) REFLOW TEMPERATURE LIMIT: +235°C
FOR 5 SEC.

[illegible]

Quality Products From The Specialists In Electro-Magnetic Compatibility



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[SSM1F-822Z-10B](#)