

North America: Danboro, PA • E-mail: info@pemnet.com • Tel: +1-215-766-8853



Europe: Galway, Ireland • E-mail: europe@pemnet.com • Tel: +353-91-751714

Asia/Pacific: Singapore • E-mail: singapore@pemnet.com • Tel: +65-6-745-0660

Shanghai, China • E-mail: china@pemnet.com • Tel: +86-21-5868-3688

Part # PKB-832, Press-in Threaded Inserts, Straight Knurl - Unified

- Press-fit insert with strong, reusable threads. No heat or ultrasonics required.
- Straight knurling at the top end of the insert offers higher torsional resistance.
- Slotted insert compresses allowing easy access into the mounting hole.
- Aluminum inserts ideal for light weight designs.
- Aluminum inserts offer lead-free alternative.




Specifications

Thread Size .164-32 (#8-32)

Type PKB

Thread Code 832

A ± .005 .312 in



E Nom. .219 in

C ± .010 .196 in

B1 ± .010 .094 in

B2 ± .010	.131 in
S Nom.	.235 in
W ± .015	.047 in
Min. Hole Depth	.352 in
Hole Dia. ± .002	.219 in
Thread Specification	2B per ASME B1.1
Standard Material	Free-machining, Leaded Brass
Standard Finish	Plain
CAD Supplier	PennEngineering® (SI®)