

# Monitors

# V Series

The stunning Acer V Series monitor delivers vibrant visuals and comfortable viewing ideal for extended use. Its cinematic widescreen with Full HD1 resolution and superior contrast ratio presents detailed imagery for prolific multitasking. What's more, this display features power-saving technologies to conserve cost and resources.



## Solid, sophisticated look

The panoramic V Series display comes encased in an elegant dark gray bezel matched with a sturdy black stand to form a functional yet stylish design. In addition, smartly positioned controls allow easy maintenance and intuitive use.



## Realistic imagery

Graphics comes alive on the V Series monitor, thanks to a very high contrast ratio and Acer Adaptive Contrast Management. The rapid response time presents fast-moving visuals without ghosting. Furthermore, two built-in speakers (optional) deliver sharp sound, while the DVI interface connects you to the latest high-definition digital video devices.



## Energy-saving, dependable display

The V Series boasts ultra-low power consumption in standby mode, along with ENERGY STAR® certification. Additionally, it uses mercury-free LED backlight technology to consume up to 68% less power. This monitor has also passed a range of quality and reliability tests to guarantee solid performance over time.



## V Series

V173 DJb - ET.BV3RP.D03

USD 110

17" LCD display - 1280 x 1024 resolution - 20,000:1 contrast ratio - 5ms response time - VGA - Windows® 7 32-bit and 64-bit compatibility - adjustable display angle - EPEAT® (Electronic Product Environmental Assessment Tool) Silver rating - 3-year limited warranty



Technical Information		Video	
Number of Screens	1	Maximum Resolution	1280 x 1024
Screen Size	17"	Standard Refresh Rate	75 Hz
Screen Mode	SXGA	Color Supported	16.7 Million Colors
Horizontal Viewing Angle	160°	Contrast Ratio	20,000:1
Vertical Viewing Angle	160°	Brightness	250 Nit
Adjustable Display Angle	Yes		
Mount Type	Wall Mountable		
Interfaces/Ports		Power Description	
VGA	Yes	Input Voltage	220 V AC 110 V AC
		Operating Power Consumption	13.90 W
		Standby Power Consumption	580 mW
Physical Characteristics		Miscellaneous	
VESA Mount Compatible	Yes	Green Compliant	Yes
VESA Mount Standard	100 x 100	Green Compliance Certificate/Authority	Energy Star
Color	Black		EPEAT Silver
Height	14.6"		TCO '03
Width	14.8"		
Depth	6.3"		
Weight (Approximate)	8.38 lb		
Warranty			
Warranty	Three-year Limited Warranty		

Sale subject to Limited Warranty and Terms & Conditions agreement. All offers subject to change without notice or obligation and may not be available at all retail locations. Prices listed are manufacturer suggested retail prices and may vary by retail location. Applicable taxes extra. Not responsible for pricing or other typographical errors.