


Dimensions: mm (in.)

**Electrical Specifications:**

- Rating: 50mA / 12VDC
- Contact Resistance: 100m Ω Max.
- Insulation Resistance: 100M Ω Min.
- Dielectric Strength: 250VAC for 1 Minute

Mechanical Specifications:

- Operating Life: 50,000 Cycles
- Operating Temperature: -25°C to +70°C

Note:

- RoHS Compliant and Process Compatible with 260° solder

Mountain Switch Part No.	Operating Force	Button Height H (mm)
101-TS6211T2601-EV	260gf	4.3
101-TS6211T3201-EV	320gf	4.3
101-TS6211T1603-EV	160gf	8.5
101-TS6211T2603-EV	260gf	8.5
101-TS6211T3203-EV	320gf	8.5

Tactile Switches

101-TS6211T2601-EV, 101-TS6211T3201-EV,
101-TS6211T1603-EV, 101-TS6211T2603-EV,
101-TS6211T3203-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-TS6211T3201-EV](#) [101-TS6211T2601-EV](#) [101-TS6211T1603-EV](#) [101-TS6211T2603-EV](#) [101-TS6211T3203-EV](#)