




4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
AF		50		P	LTR	DESCRIPTION	DATE	DWN	APVD
					D	REVISED PER ECR-08-030838	30MAR09	HMR	GP







SECTION A-A

1

PRODUCT PROVIDED IN STRIP FORM ON REELS, BREAKS MAY BE PRESENT.

2


WIRE RANGE: 3300 TO 9000 CMA

3

CRIMP WIDTH: .140, "F" TYPE
CRIMP HEIGHT (±.002)=(TOTAL CMA+14,600)/223,200
FOR APPLICATOR INFORMATION CALL:1-800-722-1111
FOR PRODUCT INFORMATION CALL:1-800-522-6752

40552

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 18JAN07		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:						CHK G.D.PORTA 18JAN07					
		0 PLC ± -		APVD G.D.PORTA 18JAN07		NAME SPLICE							
		1 PLC ± -		PRODUCT SPEC -									
		2 PLC ± -											
MATERIAL BRASS		3 PLC ± .010		APPLICATION SPEC 114-2088		SIZE A3		CAGE CODE 00779		DRAWING NO C-40552		RESTRICTED TO	
		4 PLC ± -		WEIGHT -		SCALE 10:1		SHEET 1 OF 1		REV D			
		FINISH TIN		CUSTOMER DRAWING									

AMP 1470-19 REV 31MAR2000