



Heyco® Original Series-35 Liquid Tight Cordgrips



Pigtail, NPT Hubs

- **Flexible Pigtail™ extender** prevents sharp bends and extends cable life.
- IP 68 rated.
- Widest range of approved cable diameters.
- For use in clearance or threaded holes.
- Acme threads on body prevent skipping and speed installation.
- All nylon construction with TPE sealing gland resists salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL.)
- Multiple sizes for flexible cord diameters ranging from .069" (1,8 mm) to .709" (18,0 mm).
- We recommend using the fitting with the smallest maximum diameter that will fit your application.
- **Locknuts not included.** For nylon locknut specifications or to order locknuts separately, see page 3-41.
- For Heyco Liquid Tight Threaded Plugs, see page 3-45.
- Consult Heyco for cordgrips molded in other colors.

CABLE DIA. RANGE		PART NO. Locknuts Not Included*		DESCRIPTION	UL or CSA	PART DIMENSIONS		PART DIMENSIONS		PART DIMENSIONS							
Minimum	Maximum	Black	Gray			A Clearance Hole Dia.	B Max. O.A. Length	C Thread Length	D Wrenching Nut Thk.	E Flat Size	in.	mm.	in.	mm.	in.	mm.	
.069	1.8	.187	4.7	3474	3475	FLEX RLTF 3/8	UL	.670	17.0	2.97	75.4	.53	13.5	.20	5.1	.75	19.1
.181	4.6	.312	7.9	3254	3255	FLEX LTF 3/8	UL	.875	22.2	4.09	103.9	.62	15.7	.20	5.1	.95	24.1
.170	4.3	.470	11.9	3251	3252	FLEX LTF 1/2	UL	.875	22.2	4.54	115.3	.62	15.7	.23	5.8	1.05	26.7
.230	5.8	.546	13.9	3266	3267	FLEX LLTF 1/2	UL	1.068	27.1	5.14	130.6	.63	16.0	.23	5.8	1.30	33.0
.250	6.4	.485	12.3	3462	3463	FLEX RLTF 3/4	UL										
.450	11.4	.709	18.0	3239	3242	FLEX LTF 3/4	UL										

Standard colors black and gray.

*To order Nylon or Metal Locknuts separately, see pages 3-XX and 3-XX.



SUGGESTED CLEARANCE HOLE
FOR NONTHEREADED MOUNTING

Material
Certifications

Nylon 6/6 w/TPE Sealing Gland

UL Listed under Underwriters' Laboratories File E51579

CSA Recognized under the Component Program of
Underwriters' Laboratories File E51579

CSA Certified by Canadian Standards Association File 93876C

94V-2

Static -40°F (-40°C) to 239°F (115°C)

Dynamic -4°F (-20°C) to 212°F (100°C)

Flammability Rating
Temperature Range

IP 68 (70 PSI, 5 BAR)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[3251](#) [3254](#) [3239](#) [3266](#) [3242](#) [3252](#) [3255](#) [3267](#) [3463](#) [3475](#) [3474](#) [3462](#)