

Twist-Lock® Devices

20 Ampere, 3Ø Y 120/208, 277/480 and 347/600 Volts AC

4 Pole, 5 Wire Grounding

Insulgrip® Plugs and Flanged Inlets

Fed.Spec.




20A 3ØY
120/208V AC
 NEMA L21-20P
 UL/CSA
 2 HP



20A 3ØY
277/480V AC
 NEMA L22-20P
 UL/CSA
 5 HP



20A 3ØY
347/600V AC
 NEMA L23-20P
 UL/CSA

**HBL2511SW****HBL2511S****HBL2511****HBL2515SW****HBL2515****Plugs****Watertight Safety-Shroud®****IP66 SUITABILITY**

Description	Cord Dia.	Catalog Numbers
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	HBL2511SW - -

Safety-Shroud**IP20 SUITABILITY**

Description	Cord Dia.	Catalog Numbers
Black and white nylon body, white Valox® shroud. Can be used with the Insulgrip Connector Bodies.	.35"-1.15" (9-29)	HBL2511S - -

Accessories on page B-40.

Insulgrip**IP20 SUITABILITY**

Description	Cord Dia.	Catalog Numbers
Black and white nylon.	.35"-1.15" (9-29)	HBL2511 HBL2521 HBL2531
All black nylon.	.35"-1.15" (9-29)	HBL2511BK - -
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	HBL25CM11 - -
Black and white for flat cable.	.35"-1.15" (9-29)	HBL2511FC - -

Accessories on page B-53.

Flanged Inlets**Watertight Safety-Shroud****IP66 SUITABILITY**

Description	Catalog Numbers
Gray Valox® housing and flange.	HBL2515SW - -

Accessories on page B-52.

Insulgrip**IP20 SUITABILITY**

Description	Catalog Numbers
Nylon casing, back wired.	HBL2515 HBL2525 HBL2535

Accessories on page B-52.

Notes: For technical information on Twist-Lock® and Watertight Safety-Shroud Devices see pages B-69 and B-70.

HBLMITL - For use with Watertight Safety-Shroud receptacles, see page B-39.



Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.