

SAC-3P-100,0-800/0,34

Order No.: 1566242

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1566242>

Cable ring, PUR halogen-free, highly flexible, resistant to welding beads, gray, 3-pos., conductor colors: Brown/white/blue/black, cable length: 100 m

Commercial data

GTIN (EAN)	4046356327183
Note	Made-to-order
sales group	D110
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	2.8324 KG

Product notes

WEEE/RoHS-compliant since:
10/30/2007



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Number of positions	3
Length of cable	100 m

Conductor data

Cable type	PUR halogen-free, highly flexible, resistant to welding beads, gray
------------	---

Cable abbreviation	Li12YYTPE-HF
Conductor cross section	0.34 mm ²
AWG signal line	22
Conductor structure signal line	42x 0.10 mm
Core diameter including insulation	Approx. 1.32 mm
External cable diameter	4.50 mm
Wire colors	Brown, blue, black
External sheath, color	Gray RAL 7001
Nominal voltage, conductor	300 V
Test voltage, conductor	2000 V
Overall twist	3 wires, twisted
Outer sheath, material	Special TPE
Material conductor insulation	TPE-E
Conductor material	Bare Cu litz wires
Smallest bending radius, fixed installation	23 mm
Smallest bending radius, movable installation	23 mm
Number of bending cycles	11000000
Bending radius	23 mm
Traversing path	5 m
Traversing rate	3 m/s
Acceleration	20 m/s ²

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;