


**MALLORY****Mallory Sonalert Products Inc.**Part # **PB-1220PE****Sales Outline Drawing**Revision **A****OBSOLETE- USE PB-1220PEQ****Specification**

Oscillation Frequency (Hz)	2048
Operating Voltage (Vp-p)	1.25 ~ 2.5
Rated Voltage (Vp-p)	1.5
Current Consumption Max. (mA)	32 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 10cm at Rated Voltage
Coil Resistance ( $\Omega$ )	16 ± 5
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	PPO plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	2.0
Options	For other options contact factory

PS: Vp-p = 1/2duty, square wave

**Dimensions:** (units: mm)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PB-1220PE](#)