

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50-84-2022](#)
Status: **Active**
Overview: MLX™ Power Connectors
Description: 2.13mm Diameter MLX™ Pin and Socket Receptacle, 2 Circuits

Documents:
[3D Model](#) [Product Specification PS-42022-0001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [42022](#)
Application Power, Wire-to-Wire
Comments Glow Wire Equivalent Part Number [366440002](#). Current – Maximum per contact 20A if used with [36663](#) and [36664](#) terminal
MLX™ Power Connectors
Overview MLX™ Power Connectors
Product Name MLX™
UPC 800754386364

Physical

Circuits (maximum) 2
Circuits Detail 2
Color - Resin Natural
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 2.346/g
Number of Rows 1
Packaging Type Carton
Panel Mount Yes
Pitch - Mating Interface 6.35mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -55°C to +105°C

Electrical

Current - Maximum per Contact 20A

Material Info

Old Part Number 4202202C

Reference - Drawing Numbers

Product Specification PS-42022-0001
Sales Drawing SD-42022-**



EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[42022Series](#)

Mates With
[42021](#) MLX™ Power Crimp Housing Plug

Use With
MLX Crimp Terminal [42023](#) , [42024](#)