

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 176032


Date	Rev.	Description

SPECIFICATION SHEET

PAGE: 1/3

CUSTOMER NAME: GOLDSUN ELECTRONICS CO., LTD.
 TYPE: HN-GH35GMB TYPE
 MODEL: HN-GH24-1640Y-R
 CUSTOMER PART NO.: 176032

I. OUTER DIMENSIONS :



DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO. 176032		GOLDSUN NO. HN-GH24-1640Y-R	
DRWN: Kiki Chen		Description MOTOR GEAR			Rev. 1
VERIFY PEOPLE: Ada Zheng , Ivy Lan		UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No:

Date	Rev.	Description

SPECIFICATION SHEET

PAGE: 2/3

CUSTOMER NAME: GOLDSUN ELECTRONICS CO., LTD.

TYPE: HN-GH35GMB TYPE

MODEL: HN-GH24-1640Y-R

CUSTOMER PART NO.: 176032

II. SPECIFICATIONS :

1. TESTING CONDITIONS:
 ENVIRONMENT TEMPERATURE: 25 DEGREES CELSIUS.
 RELATED HUMIDITY: 60%.
 TESTING POSITION: THE GEARMOTOR LIES IN HORIZONTAL POSITION.
2. RATED VOLTAGE(POWER SUPPLY): DC24V.
 THE POWER SUPPLY MUST BE PURE DC(DIRECT CURRENT) AND CAN NOT CARRY ANY AC(ALTERNATING CURRENT).
3. GEAR RATIO: 90:1.
4. RATED LOAD AT DC24V : 2Kg-cm.
 DON'T EXCEED RATED LOAD. OVERLOADING CAN CAUSE DAMAGE TO GEARMOTOR.
5. NO LOAD SPEED AT DC24V: 64RPM+/-10%.
6. SPEED AT DC24V & RATED LOAD(2Kg-cm): 52RPM+/-10%.
7. NO LOAD CURRENT AT DC24V: LOWER THAN 76mA.
8. CURRENT AT DC24V & RATED LOAD(2Kg-cm): LOWER THAN 156mA.
9. SHAFT END PLAY: MAXIMUM 0.8m/m.
10. INSULATION RESISTANCE: 10M ohm AT DC300V.
11. WITHSTAND VOLTAGE: DC300V FOR ONE SECOND.
12. THE GEARMOTOR IS NOT INTENDED FOR INSTANT REVERSE. BE SURE THE GEARMOTOR IS STOPPED BEFORE REVERSING.
13. THE GEARMOTOR DOESN'T HAVE ANY PROTECTIVE MEASURES LIKE WATER-PROOF, DUST- PROOF, ETC..... PLEASE USE IT IN THE NORMAL ENVIRONMENT AND TEMPERATURE.
14. IF YOU HAVE ANY QUESTIONS ABOUT THE SPECIFICATIONS AND DIMENSIONS, KINDLY PLEASE FEEL FREE TO CONTACT US.

DCC. NO.	MATERIAL	GOLDSUN ELECTRONICS CO., LTD.				
		JAMECO NO.	176032		GOLDSUN NO.	HN-GH24-1640Y-R
	DRWN: Kiki Chen	Description				Rev.
	VERIFY PEOPLE: Ada Zheng , Ivy Lan	MOTOR GEAR				2
A4 DRAWING NO.		UNIT:	SCALE:	SHEET 1 OF 1	CAS No:	ERN No:
		mm				

Date	Rev.	Description

SPECIFICATION SHEET

PAGE: 3/3

CUSTOMER NAME: GOLDSUN ELECTRONICS CO., LTD.
 TYPE: HN-GH35GMB TYPE
 MODEL: HN-GH24-1640Y-R
 CUSTOMER PART NO.: 176032

III. GUARANTEE :

A period of six months from the shipping date shall be provided by us as the guarantee. But our company shall not be liable for any failures which is resulted upon reaching 300 hours of services life or due to improper application, maintenance, installation, man-made negligence and natural disaster.

All our products are made according to the specifications we offered you. Should a problem occur, then the specifications shall be based and no objections shall be held by you. In case if the delivered DC gearmotors are in contradictory with the specifications within the guarantee period, in absence of proviso stated in the aforesaid provision, then our company will accept repair or replacement in our factory and or refund. However, our company shall not be liable for any additional responsibilities.

DCC. NO.	MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
			JAMECO NO.		GOLDSUN NO.	
	DRWN: Kiki Chen		176032		HN-GH24-1640Y-R	
	VERIFY PEOPLE: Ada Zheng , Ivy Lan		Description		Rev.	
A4 DRAWING NO.			MOTOR GEAR		3	
	UNIT:	SCALE:	SHEET 1 OF 1	CAS No:	ERN No:	
	mm					