




MATERIALS:

Connector – 1st End: Triaxial Cable Male (BNC 2 Lug Bayonet Style)

Body and Fittings: Brass, Tarnish Resistant

Intermediate and Center contacts: Gold Plated Brass per MIL-C-39012

Cable: Belden 9222 Triaxial Cable

20 AWG stranding 7x28, T.C. Polyethylene Insulation, 6.15 (.242) O.D. Color: Yellow

Marking: “POMONA ELECTRONICS 5054-XX”

Connector – 2nd End: Same as first.

RATINGS:

Operating Voltage: 500 VRMS

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 5054-XX

XX = Length in inches. Std. Lengths: 36”, 60”

Additional lengths can be quoted upon request.

Ordering Example: 5054-36, Cable length will be 36” long

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA