




FEATURES:

- Replaceable tip probe set includes a full set of ten replacement tips
- Designed for Fluke, Agilent, and Wavetek-Mettermann DMM's with a safety-sheathed banana jack
 - Probe incorporates a two-step mold process. First step is Polypropylene for strength; second step is Santoprene® rubber for handling comfort, added insulation protection and wire strain relief
- Replacement tips can be ordered separately, see model 6475
- Probe and banana plug are molded directly onto the wire for robust pull strength
- Wire is a high strand count silicone wire for extreme flexibility and high temperature resistance
- Banana plug is nickel plated Beryllium Copper for long life

MATERIALS:

Probe: Santoprene® rubber, color: gray

Inner Insulation: Polypropylene, color: one black, one red

Tips: Nickel plated Beryllium Copper, stainless steel and Nickel-plated brass

Wire: 18 AWG, Silicone insulation, length: 48"

Banana Plug: Nickel plated Brass

Spring: Nickel plated Beryllium Copper

Plug Insulation: Polypropylene, color: one black, one red

RATINGS:

IEC 1010-2-031, Category III 1000V

Operating Voltage: 1000 VRMS

Current: 5 Amperes

ORDERING INFORMATION: Model 5676A

Includes a set of one black and one red test lead with ten replaceable tips (two of each shown above)

All dimensions are in inches

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90918 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com