



T50R0UVM4

Standard Cable Tie, 8" Long, 50lb Tensile Strength, PA66UV, Black, 1000/pkg

Article Number: 111-04913

Part Number: T50R0UVM4

Type: T50R

Base Data

Part No.	T50R0UVM4
Type	T50R
Color	Black (BK)
Features	• UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures . • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

Product Dimensions

Min. Tensile Strength	50.0lbs / 225.0N
Length (L)	8.0" / 202.0mm
Width (W) (imperial)	0.18"
Width (W)	4.6mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	1.97" / 50.0mm

Material and Specifications

Material	Polyamide 6.6 UV-resistant (PA66UV)
US MILSPEC	MS3367-1-0
CSA Certified	No
Flammability	UL94 V2
Material Specification	HF
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	 RoHS
Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	1000
Carton Qty.	5000
EAN code	4031026422060
UPC	089306182887