

CAB CAB ABS 604022 T3B



Sample photo

Order symbol: CAB ABS 604022 T3B
Product nbr: 8183072
Description: Cabinet, ABS
Remarks: Locks on the long side

EAN: 6418074020512
El. number:
Finland: 3424378
Denmark: 8212019098
Italy: 7812070
Sweden: 2540055
Norway:

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
mm:		600	400	220	Ingress Protection (EN 60529): IP 65
inch:		23.6	15.7	8.7	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		Smoked grey			Glow Wire Test (IEC 695-2-1) °C: 650
Gasket material:		EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Fimko
Continuous:		-40 ... 60 °C			Europe EN 62208: 2003
Short term:		-40 ... 175 °F			Gost R
Continuous:		-40 ... 140 °F			
Accessories:					
EKIV 64H		Mounting plate			
EKIV 37		DIN-35 Mounting rail			
DS35370E1		DIN-35 Mounting rail			
FP A 64		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 64		Front plate			
FP 18x3-64		Front plate			
DRF 63/64		DIN rail frame set			

