

**Rigid/IMC Conduit Fittings****T&B Catalog Number:**

3870-TB

UPC Number:

78621003870

Status:

Active

Description:

1/2 in. Threaded insulated Grounding Bushing, Aluminum-Electro Zinc Plated, wire range-14-4, thermoplastic insulator. For use with Rigid/IMC Conduit.

Application

For quick installation of bonding jumper to multiple metal conduits (Rigid and IMC).

Designed to bush conductors and prevent insulation damage.

General

Trade Size (inches)	1/2
Material	Malleable Iron
Finish	Electro Zinc Plated
Wire Range	14-4

Dimension Information

Bushing Diameter (inches)	1.125
Throat Diameter (inches)	0.56
Lug Length (inches)	1.31
Swing Radius (inches)	1.212
Bushing Height (inches)	0.657
Conduit Size (inches)	1/2

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	50
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	6 lbs. per 100

Application Support

T&B Instruction Sheets	ta00375-tb2
------------------------	-------------

Notes

Available with DURA-PLATE Finish

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications

File Nbr:

E 3060

For further technical assistance, please contact us...

www.tnb.com

Memphis, TN 38125

Fax: (901) 252-1321
Email:techsupport@tnb.com