

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

50-37-5023

Status:

Active

Overview:

SPOX™

Description:

2.50mm Pitch SPOX™ Wire-to-Board Crimp Housing, Friction Lock, 2 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-5264-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

MolexKits

Overview

Product Name

UPC

Crimp Housings

5264

Signal, Wire-to-Board

Yes

SPOX™

SPOX™

800753578340

Physical

Circuits (maximum)

Flammability

Gender

Glow-Wire Compliant

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

2

94V-0

Female

No

119.300/mg

1

Bag

No

2.50mm

Yes

No

-40°C to +105°C

Material Info

Old Part Number

5264-02


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-5264-001, RPS-5264-001, RPS-5264-002, RPS-5264-003, RPS-5264-004, RPS-5264-005, RPS-5264-006

SD-5264-N



Series

image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5264Series

Mates With

5267 vertical shrouded PCB header, 5268 right angle shrouded PCB header

Use With

5263

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION