




REVISIONS						
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	A	REVISED PER ECR-17-009545	08AUG2017	AS	RS	
01		REVISED PER ECO-09-024606	31OCT09	KK	AEG	



- 1. SEE I.S. 2028-1
- 2. SEE SEPERATE RESTRICTED CUSTOMER DRAWING
- 3. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



DETAIL A
SCALE 2:1



DETAIL B
SCALE 2:1

RECOMMENDED STRIP LENGTH

23	OBSOLETE	—	—	—	—	—	—	—	—	1-5225661-8-	
	OBSOLETE	BELDEN 8214	220015-1	9.53 [.375]	12.70 [.500]	17.45 [.687]	B	9-51713-0	1-51695-2	51701-6	1-5225661-6-
		RG-55A & 223	220045-2	8.71 [.343]	10.31 [.406]	15.09 [.594]	B	9-225382-0	225343-2	225342-3	1-5225661-3
		RG-58A/U & 58C/U	220045-2	8.71 [.343]	10.31 [.406]	15.09 [.594]	B	9-225381-0	225343-2	225342-3	1-5225661-2
	OBSOLETE	RG-213/U	220015-1	9.53 [.375]	12.70 [.500]	17.45 [.687]	B	9-51713-0	2-51695-1	51701-6	—5225661-2-
		RG-9/U & 214/U	220015-1	—	—	—	A	9-51713-0	2-51695-1	51701-6	5225661-1
		CABLE	CRIMPING TOOL	E	D	C	DETAIL	③ FERRULE QTY=1	② CONTACT QTY=1	① PLUG ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± 0.41 [.016]

3 PLC ± -

4 PLC ± -

ANGLES ± -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.41 [.016]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

—

DWN
A. FERNANDEZ-DOCK5
31JAN2005

CHK
J. HAVENER
31JAN2005

APVD
G. MICHAEL
31JAN2005

TE Connectivity

PLUG, SERIES N

SIZE
A1

CAGE CODE
00779

DRAWING NO
5225661

RESTRICTED TO
—

WEIGHT
0.000000

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
A