

Specifications:

Sound level Category	Medium Sound Level
Mode of Operation	Warble
Mounting	Panel (see note B)
Voltage Rating	9 to 30 Vdc
Frequency	1800 Hz $\pm$ 500 Hz to 2800 Hz $\pm$ 500 Hz
Loudness (Min. Voltage)	Typically 65 dB(A) min. @ 2 FT
Loudness (Max Voltage)	Typically 80 dB(A) min. @ 2 FT
Pulse Rate (PPS)	0.5 to 2.0
Current Draw	40 mA Max
Storage Temperature	-40°C to +85°C
Operating Temperature	-30°C to +65°C
Weight (Typical)	1.6 oz (45 g)
Housing	6/6 Nylon, Color Black
Options	For other options contact factory

Dimensions: Inches (mm)

ROHS Compliant

