



Molex Woodhead Express Program
Part Number Reference
www.woodhead.com

Electric Reels

Product Type	Wire Gauge / Conductor	Cord Type	Primary Cord Length (inches)	Secondary Cord End	Secondary Cord Length (feet)	Current Rating (A)	Retraction Weight (lb)	Woodhead No.	Order No.
Cord reel	16 AWG / 3	SJTOW	18.0	Flying Leads	35.0	6.0	2	945-3	130090-0009
Cord reel				Flying Leads	50.0	8.0	6	980	130091-0013
Cord reel				Pendent box with 2 NEMA 5-15 duplex receptacles	50.0	8.0		980-3000	130091-0023
Cord reel	14 AWG / 3			Flying leads	45.0	11.0		990	130091-0045
Cord reel	12 AWG / 3			Flying leads	35.0	15.0		997	130091-0085
Cord reel				Pendent box with 2 NEMA 5-15 duplex receptacles	35.0	15.0		997-3000	130091-0090
Cable reel	12 AWG / 3	S00W		Super-Safeway™ NEMA 5-20 connector	25.0	18	4	9383-1533	130083-0265
Cable reel		S00W		Rubber pendent box with (2) NEMA 5-20 duplex receptacle	25.0	18.0	4	9383-3080	130083-0271
Cable reel	10 AWG / 3	S00W		Flying leads	20.0	22.0	4	9242	130084-0318
Static discharge	3/32"	Galvanized steel cable	N/A	100.0A ground clamp	25.0			143025	130177-0003
Static discharge	3/32"	Galvanized steel cable	N/A	100.0A ground clamp	50.0			143050	130177-0005
Hand wind	Cable not supplied	Cable not supplied	Grounding rod		#16/3 - 200.0' / #14/3 - 125.0' / #12/3 - 100.0' (S00W)			HW100	130087-0071
Ground fault	Cable not supplied	Cable not supplied	Grounding rod					GR1000L	130084-0077

Hose Reels

Product Type	Inlet Hose Fitting (NPT)	Hose Inner Diameter	Length (feet/m)	Pressure	Old Order No.	Order No.
VPR hose reel	3/8"	3/8"	30 / 9.1	300.0	DA330	130161-0007
Premium hose reel	3/8"	3/8"	30 / 9.1	300.0	PAL330	130158-0016
Premium hose reel	3/8"	3/8"	50 / 15.24	300.0	PBL350	130158-0031
Premium hose reel	1/2"	1/2"	50 / 15.24	300.0	PBL450	130158-0038

Safeway® Plugs and Connectors

Connector/Plug	Configuration	Poles/Wires	Voltage	Description	Woodhead No.	Order No.
Connector	NEMA 5-15	2-pole, 3-wire	125V	High impact nylon	5269	130144-0044
Plug					5266	130144-0036

Tool Support

Product Type	Construction	Weight Range (lb/kg)	Travel (feet)	Woodhead No.	Order No.
Positioner	Composite	1.0 - 10.0 / 0.5 - 4.5	4.7	GM31	130169-0002
Retractor	Standard duty composite	0.0 - 2.0 / 0.0 - 0.9	6.6	RB2	130173-0036
		1.0 - 2.0 / 0.5 - 0.9	10.0	RB210	130173-0037
		2.0 - 4.0 / 0.9 - 1.8	6.6	RB4	130173-0048
		2.0 - 4.0 / 0.9 - 1.8	6.6	RB4SC	130173-0050
		4.0 - 6.0 / 1.8 - 2.7	6.6	RF6	130173-0055
		6.0 - 8.0 / 2.7 - 3.6	6.6	RF8	130173-0061
	Heavy duty steel	1.0 - 5.0 / 0.4 - 2.3	8.0	5F	130175-0014
		4.0 - 10.0 / 1.8 - 4.5	8.0	10F	130175-0001
		8.0 - 15.0 / 3.6 - 6.8	8.0	15F	130175-0006
	Severe service	4.0 - 10.0 / 1.8 - 4.5	8.0	10FLRC	130174-0001
		8.0 - 15.0 / 3.6 - 6.8	8.0	15FLRC	130174-0005
		16.0 - 22.0 / 7.3 - 10.0	8.0	22FLRC	130174-0009
Balancer	Standard-duty composite	4.0 - 8.0 / 1.8 - 3.6	4.9	AB8	130237-0002
		4.0 - 8.0 / 1.8 - 3.6	4.9	AB8RL	130237-0005
		8.0 - 11.0 / 3.6 - 5.0	4.9	AB11	130237-0003
		8.0 - 11.0 / 3.6 - 5.0	4.9	AB11RL	130237-0006
		3.0 - 6.0 / 1.4 - 2.7	6.6	BF6	130170-0021
		6.0 - 9.0 / 2.7 - 4.1	6.6	BF9	130170-0023
		6.0 - 9.0 / 2.7 - 4.1	6.6	BFL9	130170-0033
		13.0 - 18.0 / 5.9 - 8.2	6.6	BFL18	130170-0027
		18.0 - 24.0 / 8.2 - 10.9	6.6	BFL24	130170-0030
	Heavy-duty	25.0 - 35.0 / 11.4 - 15.9	6.6	EB3500R	130171-0019
		35.0 - 45.0 / 15.9 - 20.5	6.6	EB4500R	130171-0032
	Severe service	29.0 - 40.0 / 13.0 - 18.0	6.0	40EA	130172-0184
		53.0 - 70.0 / 24.0 - 32.0	7.0	70JA	130172-0221
Static discharge reel	Heavy duty steel	N/A	50.0	2050	130177-0009
Torque reel	Heavy duty steel	15.0 / 6.8	15.0	1515TR	130176-0009
Hose/cable hanger	Standard duty composite	12.50 to 23.00mm (0.49 to 0.91")	N/A	61020	130179-0962

Super-Safeway™ Plugs and Connectors

Connector/Plug	Poles/Wires	Configuration	Voltage	Current	Woodhead No.	Order No.
Connector	2-pole, 3-wire	NEMA 5-20	125V	20.0A	1533	130141-0025
	2-pole, 3-wire	NEMA 5-15		15.0A	1547	130141-0031
	3-pole, 3-wire	Non-NEMA locking			2507	130141-0053
	2-pole, 3-wire	NEMA L5-20		20.0A	2747	130142-0021
	3-pole, 3-wire	Non-NEMA	250V	30.0A	2908	130145-0066
Plug	2-pole, 3-wire	NEMA 5-20	125V	20.0A	1433	130141-0010
	2-pole, 3-wire	NEMA 5-15		15.0A	1447	130141-0015
	3-pole, 3-wire	Non-NEMA locking			2407	130141-0044
	2-pole, 3-wire	NEMA L5-15			2447	130141-0047
	2-pole, 3-wire	NEMA L5-20		20.0A	2647	130141-0062
	3-pole, 3-wire	Non-NEMA	250V	30.0A	2808	130142-0031

Watertite® Connectors and Plugs

Description	Poles/Wires	Configuration	Voltage	Woodhead No.	Order No.
Plug	2-pole, 3-wire	NEMA L5-15	125V	24W47	130146-0082
		NEMA L5-20	125V	26W47	130147-0018
		NEMA L7-15	277V	24W34	130146-0079
		NEMA 5-15	125V	14W47	130146-0031
		NEMA 5-20		14W33	130146-0022
	3-pole, 3-wire,15.0A	Non-NEMA	125V	14W07	130146-0015
	3-pole, 4-wire	NEMA L16-20	480V	26W76	130147-0029
		NEMA L16-30		28W76	130147-0081
Connector	2-pole, 3-wire	NEMA 5-15	125V	15W47	130146-0060
		NEMA 5-20		15W33	130146-0052
		NEMA L5-20		27W47	130147-0044
		NEMA L5-15		25W47	130146-0099
		NEMA L7-15	277V	25W34	130146-0095
	3-pole, 3-wire,15.0A	Non-NEMA	125V	15W07	130146-0050
	3-pole, 4-wire	NEMA L16-30	480V	29W76	130147-0108
		NEMA L16-20		27W76	130147-0059
Duplex flip lid with female 5-15 receptacle	2-pole, 3-wire	NEMA 5-15	125V	60W47DPLX	130146-0131
Duplex flip lid with female 5-20 receptacle		NEMA 5-20		60W33DPLX	130146-0125

Portable Outlet Boxes

Configuration	Description	Woodhead No.	Order No.
N/A	Standard depth two duplex outlet box with coverplate only	3000	130137-0087
Multiple outlet box, shell only	Standard depth outlet box with MAX-LOC® cordgrip (F2)	3059	130137-0149
	Standard depth outlet box with MAX-LOC® cordgrip (F3)	3099	130137-0216
NEMA 5-15R	Standard depth outlet box with(2) duplex	3000-1	130137-0088
Multiple outlet box, shell only	Standard depth outlet box with clamping cordgrip	3050	130137-0147
NEMA 5-20	Deep box with (2) NEMA 5-20 duplex	3085-10	130137-0192
Duplex cover plate with flip lids for portable outlet box	Duplex cover plate with flip lids for portable outlet box	3056	130138-0025
Duplex cover plate for portable outlet box	Duplex cover plate for portable outlet box	3051	130138-0020
Blank cover plate for portable outlet box	Blank cover plate for portable outlet box	3054	130138-0023
3 NEMA 5-15 outlets	Multi-tap outlet box	31593	130136-0033

GFCI

Configuration	Current	Manual/Automatic	Description	Woodhead No.	Order No.
NEMA 5-20	20.0A	Manual	Flying leads	20051-0M	130153-0110
			2' with Watertite® plug and connector	20052-1M	130153-0126
			Manual in-line with Super-Safeway™ plug and connector	20051-1	130153-0111
NEMA 5-15	15.0A		In-line field attachable	20054	130153-0144
			In-line with molded plug and connector	15050-1	130153-0019
			Field attachable plug	15054	130153-0089
			Molded plug and tri-tap connector	15050-3TTT	130153-0028
			In-line with Super-Safeway™ plug and connector	15054-1	130153-0090

Pushbutton/Test Instruments

Description	Woodhead No.	Order No.
Plastic two-button pendant	4052	130126-0231
Two-button station	4022	130126-0199

Cable Grips

Grip Type	Orientation	Cable Diameter Range	Connection Type	Woodhead No.	Order No.
Deluxe cord	Straight	.375-.500"	1/2" NPT Male	36254	130097-0163
		.500-.625"		36256	130097-0165
		.500-.625"	3/4" NPT Male	36261	130097-0168
		.625-.750"		36263	130097-0170
		.875-1.000"	1" NPT Male	36269	130097-0173
Wide-range	Straight, insulated bushing	.300-.430"	1/2" NPT Male	36503	130097-0258
		.400-.540"		36505	130097-0260
		.520-.730"	3/4" NPT Male	36508	130097-0262
		.700-.970"	1" NPT Male	36512	130097-0265
		.940-1.250"	1-1/4" NPT Male	36515	130097-0269
MAX-LOC®	Straight	.125-.187" (F2 1/2")	1/2" NPT Male	5520	130098-0041
		F2 1/2" (.187-.250)	1/2" NPT Male	5522	130098-0046
		F2 1/2" (.250-.312)	1/2" NPT Male	5524	130098-0052
		F2 1/2" (.312-.375)	1/2" NPT Male	5526	130098-0061
		F2 1/2" (.312-.375)	1/2" NPT male with O-ring	5526W	130098-0064
		F2 1/2" (.375-.437)	1/2" NPT Male	5528	130098-0069
		F2 1/2" (.375-.437)	1/2" NPT male with O-ring	5528W	130098-0071
		F2 1/2" (.375-.437)	Black Valox 1/2" NPT male with O-ring	5528WBLK	130098-0072
		F2 1/2" (.437-.500)	1/2" NPT male	5530	130098-0076
		F2 1/2" (.437-.500)	1/2" NPT male with O-ring	5530W	130098-0078
	Right angle	F2 1/2" 90 body (.437-.500)	1/2" NPT Male	5531	130098-0080
	Straight	F2 1/2" (.500-.562)		5532	130098-0082
		F2 1/2" (.562-.625)		5534	130097-0327
	Right angle	F2 1/2" 90 body (.562-.625)		5535	130098-0093
	Straight	F3 3/4" (.437-.562)	3/4" NPT male	5536	130098-0096
		F3 3/4" (.500-.625)		5538	130098-0103
		F3 3/4" (.562-.687)		5540	130098-0112
		F3 3/4" (.625-.750)		5542	130098-0118
		F4 1" (.687-.812)	1" NPT male	5554	1300980150
		F4 1" (.750-.875)		5556	1300980155
	Straight, oval UF cable	F2 1/2" (.218X .421)	1/2" NPT male	5580	1300980185
Bus-drop	Single eye, closed mesh	(.400-.560)	N/A	36564	130094-0493
		(.530-.730)		36567	130094-0495
		(.700-.850)		36569	130094-0497
		(.960-1.250)		36574	130094-0502
Liquid-tight	Straight	1/2 Male	Male	36370	130096-0034
		3/4 Male		36371	130096-0036

Portable Lighting

Type	Description	Light Source	Watts	Voltage	Cord Length (feet)	Guard	Woodhead No.	Order No.
Hand lamp	Cordset with outlet and switch	Incandescent	100W	120V	25.0	Yes	402	130109-0007
	Cordset with outlet and switch				50.0		405	130109-0009
	Cord, switch		20.0		WT3C-20		130109-0017	
	Cord, switch, outlet		150W		WT6C-25		130109-0026	
	With ballast in cordset	Compact Fluorescent	13W		25.0		1086-3	130108-0128
	With ballast in handle						1083-3	130108-0106
Stringlight	12/3, Metal guard, 10 socket	Incandescent	1000W	100.0	No	323126	130106-0107	
	12/3, Without guard, 10 socket		500W			323123	130106-0104	
	12/3, Metal guard, 5 socket					323526	130106-0115	
Haz-duty handlamp	Cord with in-Line XFMR	Compact Fhuorescent	75W	12V	Yes	1635-12B	130105-0046	
	CL1 DIV1		120V	0.0		1090-HZ	130104-0021	
	CL1 DIV1 Cord		12V	50.0		1090-HZ121B163	130104-0026	
Hand lamp	1203 Q-Open with Ground Clip	Incandescent	100W		0.0		1203Q0GC	130103-0038
Guard	Clear Poly Guard	N/A	N/A		N/A	N/A	381R	130112-0171
String light	12/2 Flat Cable	Incandescent	1800W	120V	100.0	Yes	5000	130111-0027
	14/2 SJTW Molded	Incandescent	1500W		100.0		302SRL	130111-0024
Workstation	Four outlet low-volt XFMR workstation	N/A	400W			6.0	N/A	1640-12
Guard	Polycarbonate guard only	N/A	N/A	N/A	N/A	N/A	STR101	1301120246
String light	Temporary light, 14/2 cord	Incandescent	1500W	120V	100.0	Yes	202SRL	1301110023
Wide area light	Pulse start	Metal halide	400W		3.0		8575-MH-PS	1301100050
	Twin tube, feed-through, 60Hz	Fluorescent	64W		25.0		1351	1301080164
Haz-duty handlamp	CL1 DIV1	Incandescent	100W				0.0	