


Type B — Two Row Connectors

[illegible]


Stock No.	Mfr.'s Type	No. of Pos.	Rows Loaded	Dimensions — mm/in.				EACH		
				A	B	C	D	1-24	25-99	100-499
512-2700	536052-5	64	A,B	93.980 3.700	88.900 3.500	85.290 3.358	87.760 3.455	2.00	1.82	1.67



512-9127	650861-5	64	A,B	93.960 3.700	90.000 3.543	78.740 3.100	85.000 3.346	2.36	2.12	1.77
----------	----------	----	-----	-----------------	-----------------	-----------------	-----------------	------	------	------

[illegible]

Standard Size										
Stock No.	Mfr.'s Type	No. of Pos.	Rows Loaded	Dimensions — mm/in.				EACH		
				A	B	C	D	1-24	25-99	100-499
512-9120	650461-5	96	A, B, C	93.870 3.696	88.900 3.500	78.740 3.100	85.000 3.346	3.06	2.75	2.29
512-2719	650870-5	64	A, C	93.870 3.696	88.900 3.500	78.740 3.100	85.000 3.346	2.50	2.25	1.88



Standard Size										
512-2853	650908-5	96	A,B,C	95.000 3.740	90.000 3.543	78.740 3.100	88.010 3.465	2.30	2.07	1.72


Half Size										
512-2856	650479-5	48	A,B,C	54.370 2.140	49.350 1.943	38.100 1.500	47.370 1.865	1.59	1.43	1.19

Standard Size										
512-2721	650470-5	96	A,B,C	95.00 3.740	90.00 3.543	78.740 3.100	88.010 3.465	2.30	2.07	1.72

Stock No.	Mfr.'s Type	No. of Pos.	Rows Loaded	Dimensions — mm/in.				EACH		
				A	B	C	D	1-24	25-99	100-499
512-2702	650473-5	96	A,B,C	93.980 3.700	88.900 3.500	74.740 3.100	87.760 3.455	2.36	2.12	1.77
512-2703	650945-5	64	A,C	93.980 3.700	88.900 3.500	78.740 3.100	87.760 3.455	1.97	1.78	1.48

512-2801	650947-5	96	A,B,C	93.980 3.700	88.900 3.500	74.740 3.100	87.760 3.455	2.36	2.12	1.77
512-2803	650951-5	64	A,C	93.980 3.700	88.900 3.500	78.740 3.100	87.760 3.455	1.97	1.78	1.48

Half Size										
512-2805	650948-5	48	A,B,C	53.340 2.100	48.260 1.900	38.100 1.500	47.120 1.855	1.65	1.48	1.24




Stock No.	Mfr.'s Type	No. of Pos.	Rows Loaded	Dimensions — mm/in.				EACH		
				A	B	C	D	1-24	25-99	100-499
512-2831	535089-5	96	A,B,C	93.98 3.700	90.00 3.543	78.74 3.100	85.00 3.346	2.83	2.54	2.12
512-9113	650458-5	64	A,C	93.98 3.700	90.00 3.543	78.74 3.100	85.00 3.346	2.36	2.12	1.77

512-2741	535090-5	96	A,B,C	93.980 3.700	90.000 3.543	78.740 3.100	85.000 3.346	2.83	2.54	2.12
512-2743	650956-5	64	A,C	93.980 3.700	90.000 3.543	78.740 3.100	85.000 3.346	2.36	2.12	1.77

4.57 (0.180") post length. **Housing:** Polyester, grey, 94V-0 rated. **Contacts:** Phosphor bronze with plating.

512-9124	535043-5	96	A,B,C	93.980 3.700	90.000 3.543	78.740 3.100	85.000 3.346	2.83	2.54	2.12
-----------------	----------	----	-------	-----------------	-----------------	-----------------	-----------------	-------------	-------------	-------------



512-2752	535032-4	96	A,B,C	93.980 3.700	90.000 3.453	78.740 3.100	85.000 3.346	3.07	2.77	2.31
----------	----------	----	-------	-----------------	-----------------	-----------------	-----------------	------	------	------