

# Product Information



## 3477UAR080P62 red


EAN 4031582369724

Swivel castor with total lock, tail end of castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, dustguard, plate fitting. Wheel centre made of Polyamide, Tread: Polyurethane, roller bearing

### Technical Data

|                        |                |
|------------------------|----------------|
| Wheel diameter         | 80 mm          |
| Width of Tread         | 32 mm          |
| Size of Plate          | 105 x 85 mm    |
| Plate hole centres     | 80/77 x 60 mm  |
| Plate hole             | 9 mm           |
| Offset                 | 44.5 mm        |
| Swivel Interference    | 246 mm         |
| Overall height         | 108 mm         |
| Temperature            | - 40 / + 80 °C |
| Standard               | EN 12532       |
| Weight                 | 0.939 kg       |
| Swivel Radius          | 123 mm         |
| Hardness of tread      | D 42 Shore     |
| Load capacity          | 100 kg         |
| Load capacity (static) | 200 kg         |

|                      |   |   |   |   |   |
|----------------------|---|---|---|---|---|
| Roll performance     | + | + | + | + | + |
| Movement noise       | + | + | + | + | + |
| Attrition            | + | + | + | + | + |
| Corrosion resistance | + | + | + | + | + |



## 3477UAR080P62 red

EAN 4031582369724

