


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	S0		D	REV PER ECO-05-002584	07-05	AA	DE

1. MARKED PER MIL-STD-130; .09 HIGH CHARS.
2. TO MATE WITH AMP LGH-1/2 RECEPTACLE WITH .53 [13.4] BARREL DEPTH.
3. OPERATING VOLTAGE: 10 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.
- △4 PIGTAIL IS SOLDER DIPPED. (868399-1,-2, & -3 ONLY)
- △5 TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
- △6 INSULATION CUT BUT NOT REMOVED. (5-868399-3 ONLY)



△6	15.00 [381.0]	5-868399-3
△4	15.00 [381.0]	868399-3
△4	36.00 [914.4]	868399-2
△4	24.00 [609.6]	868399-1
REMARKS	A DIM △5	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 30-JUL-90	tyco Tyco Electronics Corporation Electronics Harrisburg, Pa 17105-3608			
DIMENSIONS: INCHES		CHK D.OPLINGER 28-AUG90				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D.EABY 28-AUG-90	NAME LEAD ASSY POS STOP, SGL END (RED) LGH-1/2			
	0 PLC ± - 1 PLC ± - 2 PLC ± .02 [0.5] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC -				
	MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C=868399
CUSTOMER DRAWING		WEIGHT -	RESTRICTED TO -	SCALE 2:1	SHEET 1 OF 1	REV D