

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0018122221

Status:

Active

Description:

3.18mm Diameter HCS-125 Pin and Socket Crimp Terminal, Series 2046, Male, with Tin (Sn) Plated Brass Contact, 16-18 AWG, Reel

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PSX-42179 (PDF)

Agency Certification

CSA

LR19980

General

Product Family

Series

Application

Crimp Quality Equipment

Packaging Alternative

Product Name

UPC

Crimp Terminals

2046

Power

Yes

18-12-2222 (Loose)

HCS-125

800754202824

Physical

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Male

Brass

Tin

Tin

0.500/g

Reel

0.508µm

0.508µm

Crimp or Compression

3.05mm max.

16, 18

N/A

Material Info

Old Part Number

2046-1P-901


Reference - Drawing Numbers

Product Specification

Sales Drawing

PSX-42179

SD-2046-1*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(2015

June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

2046 Series

Mates With

1901 Series, 2047 Series, 42555 Series

Use With

42179 Plug

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Mini-Mac™

0638928000

Applicator

Terminator Die

0011402164

Extractor Tool

0638240200

for .093 and

This document was generated on 09/10/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION