


Signal-Soffittenlampen

Sockel S8 (11 x 43 mm)





XX= GE - Gelb
RO - Rot
GR - Grün
BL - Blau
OR - Orange

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...	Preis/St. in €
3,5V	200mA	0,7W	00383507	408279	1,25
6V	833mA	5,0W	00380605	408538	1,25
12V	250mA	3,0W	00381203	408200	1,05
	250mA	3,0W	003812G5	409023	1,95
	415mA	5,0W	00381205	408217	1,10
	415mA	5,0W	003812R5	409030	1,95
	833mA	10,0W	00381210	408545	1,45
18V	280mA	5,0W	00381805	408460	1,30
24V	50mA	1,2W	00382412	408552	1,30
	83mA	2,0W	00382402	408569	1,05
	125mA	3,0W	00382403	408224	1,05
		3,0W	003824(XX)		2,25
		5,0W	003825(XX)		2,25
30V	420mA	10,0W	00382410	408576	1,60
	100mA	3,0W	00383003	408583	1,50
42V	165mA	5,0W	00383005	408286	1,50
	120mA	5,0W	00384205	408590	1,70
48V	63mA	3,0W	00384803	408606	1,85
	105mA	5,0W	00384805	408262	1,85
60V	50mA	3,0W	00386003	408293	1,85
	83mA	5,0W	00386005	408453	1,85

Kleinslampen

Signal-Soffittenlampen

Sockel S8 (15 x 43 mm)



XX= GE - Gelb
RO - Rot
GR - Grün
BL - Blau
OR - Orange

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...	Preis/St. in €
6V	500mA	3,0W	00390603	408309	0,95
	830mA	5,0W	00390605	408316	1,80
	1,66A	10,0W	00390610	408613	1,80
12V	250mA	3,0W	00391203	408446	1,05
	415mA	5,0W	00391205	408323	1,05
	833mA	10,0W	00391210	408620	1,65
	Blau	15,0W	003912BL	418018	2,70
24V	125mA	3,0W	00392403	408330	1,10
	210mA	5,0W	00392405	408347	1,10
farbig		5,0W	003924(XX)		2,05
	420mA	10,0W	00392410	408637	1,45
30V	100mA	3,0W	00393003	408378	1,45
	165mA	5,0W	00393005	408385	1,60
	333mA	10,0W	00393010	408644	2,10
36V	140mA	5,0W	00393605	408392	1,90
42V	70mA	3,0W	00394203	408408	1,80
	120mA	5,0W	00394205	408415	1,80
48V	105mA	5,0W	00394805	408422	1,80
60V	80mA	5,0W	00396005	408439	1,95