

## SUB-MINI & MINIATURE TOGGLES



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9



Fig. 10



Fig. 11



Fig. 12

### Sub-Miniature Toggles

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | 125VAC/28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware    | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|--------------|--------------|-------------|----------------|-------------------|----------------|---------------|---------------|-------------|------------------------|
| 35-000          | 35-000-BU     | 1          | On Off           | SPST         | 3A           | 1.5         | Bat            | BCP               | 0.220          | 0.195         | Solder        | 2 N, LR, LW | 267-A                  |
| 35-001          | 35-001-BU     | 2          | On On            | SPDT         | 3A           | 1.5         | Bat            | BCP               | 0.220          | 0.195         | Solder        | 2 N, LR, LW | 267-A                  |
| 35-002          | 35-002-BU     | 3          | On On            | DPDT         | 3A           | 1.5         | Bat            | BCP               | 0.220          | 0.195         | Solder        | 2 N, LR, LW | 267-A                  |

### Miniature Toggles

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | 125VAC/28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware    | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|--------------|--------------|-------------|----------------|-------------------|----------------|---------------|---------------|-------------|------------------------|
| 35-003          | 35-003-BU     | 2          | On (On)          | SPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-B                  |
| 35-004          | 35-004-BU     | 2          | On On            | SPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-B                  |
| 35-005          | 35-005-BU     | 2          | On Off On        | SPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-B                  |
| 35-006          | 35-006-BU     | 4          | On Off           | SPST         | 5            | 2           | Bat with Boot  | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-B                  |
| 35-007          | 35-007-BU     | 2          | On Off (On)      | SPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-B                  |
| 35-008          | 35-008-BU     | 2          | (On) Off (On)    | SPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-B                  |
| 35-009          | 35-009-BU     | 5          | On On On         | DPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-C                  |
| 35-010          | 35-010-BU     | 6          | On On            | DPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-E                  |
| 35-012          | 35-012-BU     | 6          | On Off On        | DPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-E                  |
| 35-014          | 35-014-BU     | 6          | On (On)          | DPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-E                  |
| 35-016          | 35-016-BU     | 6          | On Off (On)      | DPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-E                  |
| 35-018          | 35-018-BU     | 6          | (On) Off (On)    | DPDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-E                  |
| 35-024          | 35-024-BU     | 7          | On On            | 3PDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-D                  |
| 35-026          | 35-026-BU     | 7          | On Off On        | 3PDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-D                  |
| 35-036          | 35-036-BU     | 8          | On On            | 4PDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-E                  |
| 35-038          | 35-038-BU     | 8          | On Off On        | 4PDT         | 5            | 2           | Bat            | BCP               | 0.350          | 0.250         | Solder        | 2 N, LR, LW | 267-E                  |
| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | AMPS 125VAC  | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware    | Spec. Drawing Page No. |
| 35-053          | 35-053-BU     | 9          | On On            | SPDT         | 5            | 2           | Flat Lever     | Metal             | 0.364          | 0.250         | PCB           | 2 N, LR, LW | 267-F                  |
| 35-055          | 35-055-BU     | 9          | On Off On        | SPDT         | 5            | 2           | Flat Lever     | Metal             | 0.364          | 0.250         | PCB           | 2 N, LR, LW | 267-F                  |
| 35-057          | 35-057-BU     | 10         | On On            | DPDT         | 5            | 2           | Flat Lever     | Metal             | 0.364          | 0.250         | PCB           | 2 N, LR, LW | 267-F                  |
| 35-059          | 35-059-BU     | 10         | On Off On        | DPDT         | 5            | 2           | Flat Lever     | Metal             | 0.364          | 0.250         | PCB           | 2 N, LR, LW | 267-F                  |
| 35-070          | 35-070-BU     | 11         | On On            | SPDT         | 6            | 3           | Paddle         | Polyamide         | 0.452          | 0.500         | Solder/QC     | N, KN       | 267-G                  |
| 35-071          | 35-071-BU     | 11         | On Off On        | SPDT         | 6            | 3           | Paddle         | Polyamide         | 0.452          | 0.500         | Solder/QC     | N, KN       | 267-G                  |
| 35-072          | 35-072-BU     | 12         | On On            | DPDT         | 6            | 3           | Paddle         | Polyamide         | 0.452          | 0.500         | Solder/QC     | N, KN       | 267-G                  |
| 35-073          | 35-073-BU     | 12         | On Off On        | DPDT         | 6            | 3           | Paddle         | Polyamide         | 0.452          | 0.500         | Solder/QC     | N, KN       | 267-G                  |







Notes: (On)=Momentary On  
BCP=Brass Chrome Plate

KN=Knurled Nut  
LR=Lock Ring

LW= Lock Washer  
N=Nut(s)

PCB=Printed Circuit Board  
QC=Quick Connect

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

[illegible]

## MINIATURE TOGGLES (Cont.)



Fig. 1



Fig. 2




Fig. 3



Fig. 4

### Miniature Toggles with Printed Circuit Board Terminals

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | 125VAC/28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware    | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|--------------|--------------|-------------|----------------|-------------------|----------------|---------------|---------------|-------------|------------------------|
| 35-087          | 35-087-BU     | 1          | On On            | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-A                  |
| 35-069          | 35-069-BU     | 1          | On (On)          | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-A                  |
| 35-074          | 35-074-BU     | 1          | On Off On        | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-A                  |
| 35-075          | 35-075-BU     | 1          | On Off (On)      | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-A                  |
| 35-077          | 35-077-BU     | 1          | (On) Off (On)    | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-A                  |
| 35-079          | 35-079-BU     | 2          | On On            | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-B                  |
| 35-081          | 35-081-BU     | 2          | On (On)          | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-B                  |
| 35-082          | 35-082-BU     | 2          | On Off On        | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-B                  |
| 35-083          | 35-083-BU     | 2          | On Off (On)      | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-B                  |
| 35-085          |               | 2          | (On) Off (On)    | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB           | 2 N, LR, LW | 269-B                  |

### Miniature Toggles with Printed Circuit Board with Integral Bracket Terminals

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | 125VAC/28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|--------------|--------------|-------------|----------------|-------------------|----------------|---------------|---------------|------------------------|
| 35-088          | 35-088-BU     | 3          | On On            | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-C                  |
| 35-089          | 35-089-BU     | 3          | On (On)          | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-C                  |
| 35-091          | 35-091-BU     | 3          | On Off On        | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-C                  |
| 35-093          | 35-093-BU     | 3          | On Off (On)      | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-C                  |
| 35-095          | 35-095-BU     | 3          | (On) Off (On)    | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-C                  |
| 35-096          | 35-096-BU     | 4          | On On            | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-D                  |
| 35-097          | 35-097-BU     | 4          | On (On)          | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-D                  |
| 35-098          | 35-098-BU     | 4          | On Off On        | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-D                  |
| 35-099          | 35-099-BU     | 4          | On Off (On)      | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-D                  |
| 35-101          | 35-101-BU     | 4          | (On) Off (On)    | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB†          | 269-D                  |

Notes: (On)=Momentary On  
BCP=Brass Chrome Plate


LW= Lock Washer  
N=Nut(s)

LR=Lock Ring  
PCB=Printed Circuit Board  
PCB†=Printed Circuit Board with Integral Bracket


Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

## MINIATURE TOGGLES (Cont.)


**A**




**B**



**C**



**D**



## MINIATURE TOGGLES (Cont.)



Fig. 1



Fig. 2



Fig. 3




Fig. 4

### Miniature Toggles with Printed Circuit Board Right Angle Vertical Mount Terminals

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | 125VAC/28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|--------------|--------------|-------------|----------------|-------------------|----------------|---------------|---------------|------------------------|
| 35-102          | 35-102-BU     | 1          | On On            | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-A                  |
| 35-103          | 35-103-BU     | 1          | On (On)          | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-A                  |
| 35-104          | 35-104-BU     | 1          | On Off On        | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-A                  |
| 35-105          | 35-105-BU     | 1          | On Off (On)      | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-A                  |
| 35-106          | 35-106-BU     | 1          | (On) Off (On)    | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-A                  |
| 35-107          | 35-107-BU     | 2          | On On            | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-B                  |
| 35-108          | 35-108-BU     | 2          | On (On)          | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-B                  |
| 35-109          | 35-109-BU     | 2          | On Off On        | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-B                  |
| 35-111          | 35-111-BU     | 2          | On Off (On)      | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-B                  |
| 35-113          | 35-113-BU     | 2          | (On) Off (On)    | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB++         | 271-B                  |

### Miniature Toggles with Printed Circuit Board Right Angle Horizontal Mount Terminals

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | 125VAC/28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|--------------|--------------|-------------|----------------|-------------------|----------------|---------------|---------------|------------------------|
| 35-115          | 35-115-BU     | 3          | On On            | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-C                  |
| 35-121          | 35-121-BU     | 3          | On (On)          | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-C                  |
| 35-122          | 35-122-BU     | 3          | On Off On        | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-C                  |
| 35-123          | 35-123-BU     | 3          | On Off (On)      | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-C                  |
| 35-125          | 35-125-BU     | 3          | (On) Off (On)    | SPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-C                  |
| 35-127          | 35-127-BU     | 4          | On On            | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-D                  |
| 35-129          | 35-129-BU     | 4          | On (On)          | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-D                  |
| 35-131          | 35-131-BU     | 4          | On Off On        | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-D                  |
| 35-133          | 35-133-BU     | 4          | On Off (On)      | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-D                  |
| 35-135          | 35-135-BU     | 4          | (On) Off (On)    | DPDT         | 5            | 2           | Bat            | BCP               | 0.350"         | 0.250"        | PCB+++        | 271-D                  |

Notes: (On)=Momentary On  
BCP=Brass Chrome Plate

KN=Knurled Nut  
LR=Lock Ring

LW= Lock Washer  
N=Nut(s)

PCB=Printed Circuit Board  
PCB+=Printed Circuit Board with Integral Bracket  
QC=Quick Connect  
PCB++=Printed Circuit Board Right Angle Vertical Mount  
PCB+++=Printed Circuit Board Right Angle Horizontal Mount



Fig. 5



Fig. 6



Fig. 7



Fig. 8

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/Throws | AMPS 125VAC | AMPS 250VAC | AMPS 12VDC | HP 125-250VAC | Actuator Style | Color     | Bushing Length | Mounting Hole | Terminal Type | Hardware | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|--------------|-------------|-------------|------------|---------------|----------------|-----------|----------------|---------------|---------------|----------|------------------------|
| 35-090          | 35-090-BU     | 5          | On Off           | SPST         |             |             | 16         |               | Paddle*        | Red       | 0.342          | 0.500         | QC .250"      | N, LN    | 271-E                  |
| 35-092          | 35-092-BU     | 5          | On Off           | SPST         |             |             | 16         |               | Paddle*        | Green     | 0.342          | 0.500         | QC .250"      | N, LN    | 271-E                  |
| 35-094          | 35-094-BU     | 5          | On Off           | SPST         |             |             | 16         |               | Paddle*        | Amber     | 0.342          | 0.500         | QC .250"      | N, LN    | 271-E                  |
| 35-3008         | 35-3008-BU    | 6          | On Off           | SPST         | 15          | 10          |            | 3/4           | Paddle         | Black     |                | 0.550 x 1.125 | QC .250"      | N, LN    | 271-F                  |
| 35-3091         | 35-3091-BU    | 7          | On Off           | SPST         | 15          | 10          |            | 3/4           | Paddle**       | Amber     |                | 0.550 x 1.125 | QC .250"      | N, LN    | 271-F                  |
| 35-3092         | 35-3092-BU    | 7          | On Off           | SPST         | 15          | 10          |            | 3/4           | Paddle**       | Red       |                | 0.550 x 1.125 | QC .250"      | N, LN    | 271-F                  |
| 35-3140         | 35-3140-BU    | 8          | On Off           | SPST         | 15          | 10          |            | 3/4           | Paddle*        | Red/Green | 0.379          | 0.500         | QC .250"      | N, FN    | 271-G                  |

Notes: \*Lighted Paddles (12V Incandescent)

\*\*Lighted Base (125 V Neon)

FN=Face Nut

HP=Horse Power





LN=Locking Nut

N=Nut




QC=Quick Connect

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

## MINIATURE TOGGLES (Cont.)



## MEDIUM DUTY TOGGLES



## MEDIUM DUTY TOGGLES (Cont.)



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9









| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/Throws | Amps 125VAC | Amps 250VAC | HP 125-250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware      | Spec. Drawing Page No. |
|-----------------|---------------|----------|------------------|--------------|-------------|-------------|---------------|----------------|-------------------|----------------|---------------|---------------|---------------|------------------------|
| 35-132          | 35-132-BU     | 1        | On On            | DPDT         | 3           |             |               | Bat            | Metal             | 0.418          | 0.500         | Solder        | 2 N, ID       | 273-A                  |
| 35-064          | 35-064-BU     | 2        | On Off           | SPST         | 4           | 2           |               | Bat            | Metal             | 0.418          | 0.500         | Solder        | 2 N, ID       | 273-A                  |
| 35-076          | 35-076-BU     | 3        | Off (On)         | SPST         | 6           | 3           | 1/4           | Bat            | Metal             | 0.465          | 0.500         | Solder        | N, KN         | 273-B                  |
| 35-086          | 35-086-BU     | 3        | On Off (On)      | SPDT         | 6           | 3           | 1/4           | Bat            | Metal             | 0.465          | 0.500         | Solder        | N, KN         | 273-B                  |
| 35-114          | 35-114-BU     | 3        | On On            | SPDT         | 6           | 3           | 1/4           | Bat            | Metal             | 0.465          | 0.500         | Solder        | N, KN         | 273-B                  |
| 35-116          | 35-116-BU     | 3        | On (On)          | SPDT         | 6           | 3           | 1/4           | Bat            | Metal             | 0.465          | 0.500         | Solder        | N, KN         | 273-B                  |
| 35-117          | 35-117-BU     | 4        | On On            | DPDT         | 6           | 3           | 1/4           | Bat            | Metal             | 0.468          | 0.500         | QC .250"      | N, KN         | 273-C                  |
| 35-118          | 35-118-BU     | 4        | On Off           | DPST         | 6           | 3           |               | Bat            | Metal             | 0.468          | 0.500         | QC .250"      | N, KN         | 273-C                  |
| 35-154          | 35-154-BU     | 5        | On (On)          | DPDT         | 6           | 3           | 1/4           | Bat            | Metal             | 0.465          | 0.500         | Solder        | N, KN         | 273-D                  |
| 35-160          | 35-160-BU     | 6        | On Off           | SPST         | 6           | 3           |               | Bat            | Metal             | 0.465          | 0.500         | Solder        | N, KN         | 273-E                  |
| 35-167          | 35-167-BU     | 7        | On Off           | SPST         | 6           | 3           |               | Bat            | Metal             | 0.470          | 0.500         | Screw         | N, KN, Sc     | 273-F                  |
| 35-171          | 35-171-BU     | 8        | On Off           | SPST         | 6           | 3           |               | Ball           | Metal             | 0.276          | 0.500         | Screw         | N, KN, Sc, ID | 273-G                  |
| 35-186          | 35-186-BU     | 9        | On On            | DPDT         | 6           | 3           | 3/4           | Paddle         | Black Plastic     | 0.379          | 0.500         | Solder        | N, KN         | 273-H                  |
| 35-188          | 35-188-BU     | 9        | On Off On        | DPDT         | 6           | 3           | 3/4           | Paddle         | Black Plastic     | 0.379          | 0.500         | Solder        | N, KN         | 273-H                  |

Notes: (On)=Momentary On  
 \*Rated 20A @ 125-277VAC  
 HP=Horse Power  
 ID=ID Plate  
 KN=Knurled Nut

NN=Nickel Nut  
 N=Nut(s)  
 QC=Quick Connect  
 WL=Wire Lead  
 Sc=Screw

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

## MEDIUM DUTY TOGGLES (Cont.)



## MEDIUM DUTY TOGGLES (Cont.)



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9



Fig. 10



Fig. 11

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/Throws | Amps 125VAC | Amps 250VAC | HP 125-250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware      | Spec. Drawing Page No. |
|-----------------|---------------|----------|------------------|--------------|-------------|-------------|---------------|----------------|-------------------|----------------|---------------|---------------|---------------|------------------------|
| 35-854          | 35-854-BU     | 1        | On Off           | SPST         | 6           | 3           |               | Bat            | Black Plastic     | 0.342          | 0.500         | WL            | KN, ID        | 275-A                  |
| 35-1076         | 35-1076-BU    | 2        | Off (On)         | SPST         | 6           | 3           | 1/4           | Bat            | Metal             | 0.465          | 0.500         | Screw         | N, KN, FN, Sc | 275-B                  |
| 35-1114         | 35-1114-BU    | 2        | On On            | SPDT         | 6           | 3           | 1/4           | Bat            | Metal             | 0.465          | 0.500         | Screw         | N, KN, FN, Sc | 275-B                  |
| 35-1116         | 35-1116-BU    | 2        | On (On)          | SPDT         | 6           | 3           | 1/4           | Bat            | Brass             | 0.465          | 0.500         | Screw         | N, KN, FN, Sc | 275-B                  |
| 35-3035         | 35-3035-BU    | 3        | On Off           | SPST         | 6           | 3           |               | Bat            | Brass             | 0.325          | 0.500         | Screw         | 2 N           | 275-C                  |
| 35-119          | 35-119-BU     | 4        | On Off           | SPST         | 10          | 5           | 1/2           | Bat            | Metal             | 0.500          | 0.500         | QC .250"      | N, KN         | 275-D                  |
| 35-120          | 35-120-BU     | 4        | On On            | SPDT         | 10          | 5           | 1/2           | Bat            | Metal             | 0.500          | 0.500         | QC .250"      | N, KN         | 275-D                  |
| 35-180          | 35-180-BU     | 5        | On Off           | SPST         | 10          | 5           | 1/2           | Paddle         | Black Plastic     | 0.280          | 0.500         | QC .250"/Sd   | FN, NN        | 275-E                  |
| 35-182          | 35-182-BU     | 5        | On On            | SPDT         | 10          | 5           | 1/2           | Paddle         | Black Plastic     | 0.280          | 0.500         | QC .250"/Sd   | FN, NN        | 275-E                  |
| 35-184          | 35-184-BU     | 5        | On Off On        | SPDT         | 10          | 5           | 1/2           | Paddle         | Black Plastic     | 0.280          | 0.500         | QC .250"/Sd   | FN, NN        | 275-E                  |
| 35-3050         | 35-3050-BU    | 6        | On Off           | SPST         | 10          | 4           | 1/3           | Bat            | Brass             | 0.325          | 0.500         | WL            | 2 N           | 275-F                  |
| 35-112          | 35-112-BU     | 7        | On Off           | DPST         | 15          | 10          |               | Bat            | Metal             | 0.468          | 0.500         | Solder        | N, KN         | 275-G                  |
| 35-152          | 35-152-BU     | 7        | On On            | DPDT         | 15          | 10          |               | Bat            | Metal             | 0.468          | 0.500         | Solder        | N, KN         | 275-G                  |
| 35-3127         | 35-3127-BU    | 11       | (On) Off (On)†   | DPDT         | 15          | 10          | 1/2           | Bat            | Metal             | 0.465          | 0.500         | QC .250"      | FN, N         | 275-H                  |
| 35-3153         | 35-3153-BU    | 8        | (On) Off (On)    | SPDT         | 15          | 10          | 3/4           | Paddle         | Black Nylon       | 0.379          | 0.500         | QC .250"      | FN, NN        | 275-I                  |
| 35-3169         | 35-3169-BU    | 9        | (On) Off (On)    | SPDT         | 15          | 10          | 3/4           | Paddle         | Black Nylon       | 0.379          | 0.500         | Screw         | FN, NN, Sc    | 275-J                  |
| 35-178          | 35-178-BU     | 10       | On Off           | SPST         | 20          | 20          | **            | Paddle         | Black Plastic     | 0.342          | 0.500         | QC .250"/Sd   | N, BFN        | 275-K                  |
| 35-3009         | 35-3009-BU    | 5        | On Off           | SPST         | 20          | 10          | 1-1/2         | Paddle         | Black Nylon       | 0.280          | 0.500         | QC .250"/Sd   | KN            | 275-E                  |
| 35-3150         | 35-3150-BU    | 8        | On Off On        | SPDT         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | QC .250"      | FN, NN        | 275-I                  |
| 35-3154         | 35-3154-BU    | 8        | On Off           | DPST         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | QC .250"      | FN, NN        | 275-I                  |
| 35-3156         | 35-3156-BU    | 8        | On On            | DPDT         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | QC .250"      | FN, NN        | 275-I                  |
| 35-3158         | 35-3158-BU    | 8        | On Off On        | DPDT         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | QC .250"      | FN, NN        | 275-I                  |
| 35-3160         | 35-3160-BU    | 9        | On Off           | SPST         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | Screw         | FN, NN, Sc    | 275-J                  |
| 35-3162         | 35-3162-BU    | 9        | On On            | SPDT         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | Screw         | FN, NN, Sc    | 275-J                  |
| 35-3164         | 35-3164-BU    | 9        | On Off           | DPST         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | Screw         | FN, NN, Sc    | 275-J                  |
| 35-3166         | 35-3166-BU    | 9        | On On            | DPDT         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | Screw         | FN, NN, Sc    | 275-J                  |
| 35-3168         | 35-3168-BU    | 9        | On Off On        | DPDT         | 20*         |             | 1-1/2         | Paddle         | Black Nylon       | 0.379          | 0.500         | Screw         | FN, NN, Sc    | 275-J                  |

Notes: (On)=Momentary On  
 \*Rated 20A @ 125-277VAC  
 BFN=Brass Face Nut  
 FN=Face Nut  
 HP=Horse Power  
 ID=ID Plate  
 KN=Knurled Nut

NN=Nickel Nut  
 N=Nut(s)  
 QC=Quick Connect  
 Sc=Screw  
 Sd=Solder  
 WL=Wire Lead  
 †=Reversing Toggle  
 \*\*=1/2 HP@125V, 1 HP@250V

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

