



TFT LCD MONITOR



Operating instructions

Before operating this set, please read these instructions completely


Appearance and function




1. Remote Window 3. V1/V2 Switch
2. Power on/off

Function parameter

Screen size: 7 inches
 Display format: 16:9
 Power supply: DC 12V
 Power consumption: About 7.5W
 Video: Dual video input
 System: NTSC/PAL
 Pixels: 480(W) × RGB × 240=345600 dots
 Blue screen appears when no signal.



OPERATIONS OF REMOTE CONTROL



Basic operation

○ Basic operation

1. Connect the attached cable to the power source and signal cable.
 One tip of the cable is connected to the female socket of the monitor, another tip is to the video out line of VCD or DVD. The black cable is connected to ground, red cable is to positive pole. Please mind to connect the black and red cable correctly, or the safety fuse in the disaster box will melt protectively.
2. When power on, the monitor shows VCD or DVD signal. If no signal, then blue screen appears.
3. Brightness, contrast, color, tint can be adjusted from the function menu. Just press the "Analog decrease" and "Analog increase", adjust to the best quality of the images.