

Wood twist drills for machines chrome vanadium steel

Point cut: center point and 2 shoulder cutting edges
 Surface: black steam tempered ground pilot point
 Shank: straight shank

Highly efficient wood drill made of abrasion-proof chrome vanadium steel. The center point guarantees precise drilling. Exact and non-splintering drilling with the shoulder cutting edges. Ideal suitable for dowel-hole drillings.

Applications: for drilling in soft wood, hard wood, plywood, hardboards and veneer wood

Right-hand cutting

Packing unit: in plastic bags of 1



Ø mm	Total length mm	Working length mm	Article no.	Price / each €
3,0	61	46	208 030	
4,0	73	52	208 040	
5,0	86	60	208 050	
6,0	91	66	208 060	
7,0	107	72	208 070	
8,0	116	80	208 080	
9,0	124	84	208 090	
10,0	132	90	208 100	
11,0	132	100	208 110	
12,0	150	102	208 120	
13,0	152	112	208 130	
14,0	159	112	208 140	
15,0	167	112	208 150	
16,0	168	112	208 160	
18,0	184	130	208 180	
20,0	200	130	208 200	
22,0	200	130	208 220	
24,0	200	130	208 240	
26,0	200	130	208 260	
28,0	200	130	208 280	
30,0	200	130	208 300	

