


## Dimensions: mm (In)



| POS.1 | POS.2 | POS.3 |
|-------|-------|-------|
|       |       |       |
| ON    | OFF   | ON    |
| 2-3   | OPEN  | 2-1   |
|       |       |       |

Switch Function

**Electrical Specifications:**

- Rating: 1A/250VAC, 3A/120VAC or 28 VDC
- Contact Resistance: 20mΩ max. initial @ 2-4 VDC 100mA
- Insulation Resistance: 1000MΩ min.
- Dielectric Strength: 1000 V RMS @ sea level

**Mechanical Specifications:**

- Mechanical Life: 30,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

**Materials:**

- Case and Bushing: Glass filled nylon 6/6, flame retardant, heat stabilized
- Actuator: nylon, black std. internal o-ring seal standard with all actuators.
- Switch Support: Brass or steel, tin plated
- Terminals/Contact: gold plated contact

**Note:**

- RoHS Compliant by exemption

**Sealed Sub-Miniature Rocker Switch**

103-7027-EVX

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7027-EVX](#)