

TK-type Twin Wheel Caster




Characteristic

Caster with cover, drivability, stability, and smooth turning are excellent.

Application

Lighter devices / TV tables




caster with stopper
(applicable for
both truck and bolt types)

Bolt Type Specification

Model No.	A	D	E	d	H2	K	L	W	Allowable Load (kg)	Code No.
TK30N6	29	φ30	11	M6×1.0	39	10	14	33	20	19034
TK40N8	39.5	φ42	14	M8×1.25	55	14	15	39	30	19037
TK40N8S	47			M10×1.5						19050
TK40N10	39.5									19038
TK40N10S	47			W5/16×-18						19051
TK40N2.5	39.5									19039
TK40N2.5S	47			W3/8×-16						19052
TK40N3	39.5									19040
TK40N3S	47			19053						
TK50N8	51.5	φ52	21	M8×1.25	65	14	15	46.5	40	19042
TK50N8S	59			M10×1.5						19055
TK50N10	51.5									M12×1.25
TK50N10S	59			W5/16×-18		19056				
TK50N12	51.5					14				19044
TK50N12S	59			19057						
TK50N2.5	51.5			W3/8×-16	19045					
TK50N2.5S	59				19058					
TK50N3	51.5				19046					
TK50N3S	59			19059						

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.

Bolt type




Truck Type Specification

Model No.	A	D	E	G	H1	L1	L2	P1	P2	W	Allowable Load (kg)	Code No.
TK30	29	φ30	11	φ5	42.5	28	28	18	18	33	20	19031
TK40	39.5	φ42	14		58.5	38	38	26	26	40.5	30	19032
TK40S	47											19047
TK50	52.5	φ52	21		68.5					47	40	19033
TK50S	59											19048

※Caster with stopper has S at the end of the model No.

Truck type



Model No.	Material	
	Body	Wheel
TK-Type	PA	PA