

# TWINAX / N TYPE CONNECTORS & ADAPTORS

## TWINAX CONNECTORS

### TWINAX CONNECTORS



Male for IBM cable type 7362211, Belden 8227 & 9207. Equal to Amphenol No. 82-5589 and IBM 736229.

No. 610 - Male Connector  
No. 610B PIN - Extra Center Pins  
No. 609 - Male Crimp Type w/cover

### TWINAX FEMALE INLINE Connectors



No. 613

### DUAL FEMALE ADAPTOR

Dual Female Adaptor Equivalent to Amphenol 82-5588 and IBM 7362230



### TWINAX FEMALE CONNECTORS CHASSIS

Solder Terminals w/ mounting Hardware Equivalent to Amphenol 82-5646 and IBM 7364498



### TWINAX DUAL FEMALE Chassis Mount



No. 614

### TWINAX "T" ADAPTOR 3 Females



No. 615

### TWINAX "T" ADAPTOR Male to 2 Females



No. 617

Note: Unless otherwise stated, all items are Nickel Plated Brass with Delrin Insulators.

## N TYPE CONNECTORS AND ADAPTORS

### SPECIFICATIONS:

Impedance: 50 ohms  
Frequency Range: 0-11GHz  
Voltage Rating: 1500V PEAK  
Vswr: 1.3Max  
0.11GHz

### MALE N CONNECTORS

#### MALE N CONNECTOR

Clamp type with solder pin.



| Mil equiv. | Cable Type | Part Number |
|------------|------------|-------------|
| UG-536B    | RG58/U     | 708         |
| UG-21B     | RG8/U      | 709         |

#### N FEMALE IN-LINE CONNECTOR

Clamp-Type, Solderless



| Mil. equiv. | Cable Type | Part Number |
|-------------|------------|-------------|
| N/A         | RG58/U     | 710         |
| UG-23       | RG8/U      | 711         |

#### N DUAL MALE ADAPTOR

Mil Equiv. UG-57B



No. 714

#### N FEMALE Chassis Mount

Mil Equiv. UG-58



No. 713

#### N DUAL FEMALE ADAPTOR

Mil Equiv. UG-29



No. 712

### TNC MALE to N FEMALE ADAPTOR

No. 885



### N RIGHT ANGLE MALE to FEMALE

Mil Equiv. UG-27B

No. 715



### N RIGHT ANGLE MALE to MALE

No. 716



### N MALE to F FEMALE ADAPTOR

No. 717



### N FEMALE to F MALE ADAPTOR

No. 718

