







LOC	DIST	REVISIONS					
		REV	DATE	BY	APP'D	DESCRIPTION	
CM	53	V3	25MAY2017	BW	KR	REVISED PER ECR-17-006277	




1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 – 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. OPTIONAL FOR KEYING HOUSING IN PANEL.
5. CIRCUIT NUMBER 1 LOCATION.
6. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
7. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
8. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.



DETAIL A
OPTIONAL CONSTRUCTIONS



RECOMMENDED PANEL CUT OUT



3-DIMENSIONAL MODEL
NTS

4.45	.175	27.43	1.080
2.79	.110	14.35	.565
2.54	.100	13.97	.550
2.41	.095	13.46	.530
2.29	.090	13.21	.520
0.76	.030	8.64	.340
0.38	.015	8.13	.320
0.25	.010	7.62	.300
0.13	.005	6.35	.250
MM	IN	MM	IN

CONVERSION TABLE

BLACK	1-350778-9
GRAY	1-350778-8
BLUE	1-350778-6
GREEN	1-350778-5
YELLOW	1-350778-4
ORANGE	1-350778-3
RED	1-350778-2
BROWN	1-350778-1
NATURAL	350778-1
COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN K. WHITAKER	24JUL92	 TE Connectivity													
			CHK R. SWING	24JUL92														
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME	CAP.2 CIRCUIT, UNIVERSAL MATE-N-LOK™												
		0 PLC	±	—					AP'D D. SELF	27JUL92								
		1 PLC	±	—							PRODUCT SPEC							
		2 PLC	±	0.13														
		3 PLC	±	—														
		4 PLC	±	—														
ANGLES		± 1°		APPLICATION SPEC														
FINISH		—			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO										
MATERIAL		—							A1	00779	C=350778	—						
NYLON,UL 94V-0		—																
													CUSTOMER DRAWING	SCALE	4:1	SHEET	1 OF 1	REV