

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300680034

Status:


Active

Overview:

BradPower Cordsets and Receptacles

Description:

BradPower D-Size (1 3/8"–M35) 3-Pole Reducing Tee, with 3-Pole BradPower A-Size (7/8"–M22) Drop, Gray



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                    |
|-------------------------------|------------------------------------|
| Agency Certification          |                                    |
| UL                            | E258922                            |
| General                       |                                    |
| Product Family                | Industrial Tees and Splitters      |
| Series                        | 130068                             |
| IP Rating                     | IP67                               |
| Overview                      | BradPower Cordsets and Receptacles |
| Product Name                  | BradPower D-Size                   |
| Type                          | Power Tap Tee                      |
| UPC                           | 78678877133                        |
| Physical                      |                                    |
| Drop Connector                | BradPowerA-Size (7/8"–M22)         |
| Drop Gender                   | Female                             |
| Keyway                        | Single                             |
| Left Trunk Connector          | BradPower D-Size (1 3/8"–M35)      |
| Left Trunk Gender             | Female                             |
| Leg 1 Length                  | N/A                                |
| Leg 2 Length                  | N/A                                |
| Material - Cable Jacket       | N/A                                |
| Material - Connector Body     | PVC                                |
| Material - Coupling Nut       | Anodized Aluminum                  |
| Poles                         | 3                                  |
| Right Trunk Connector         | BradPower D-Size (1 3/8"–M35)      |
| Right Trunk Gender            | Male                               |
| Temperature Range - Operating | -20°C to +90°C                     |
| Electrical                    |                                    |
| Current - Maximum per Contact | 15.0A, 30.0A                       |
| Voltage - Maximum             | 600V AC/DC                         |
| Material Info                 |                                    |
| Engineering Number            | TC30130-200                        |
| Reference - Drawing Numbers   |                                    |
| Sales Drawing                 | SD-130068-005                      |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Reviewed                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Reviewed |
| ELV                                                           | Not Reviewed |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

130068 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION