

# Screwdrivers, Nut Drivers & Accessories

Offering a variety of tip types, hex sizes, shaft lengths, and handle designs, Klein has the screwdrivers and nut drivers professionals demand to get the job done with comfort and ease of use.

F O R P r o f e s s i o n a l s . . . s i n c e 1 8 5 7 ®



Screwdrivers, Nut Drivers  
& Accessories




# Introduction – Screwdrivers, Nut Drivers & Accessories

Klein screwdrivers give professionals extra-quality features that have made the Klein name famous for hand tools – features that assure greater convenience, comfort and efficiency in use, plus exceptional strength and durability.

All Klein drivers are made of the highest quality tempered steel, carefully heat-treated for maximum strength. Shafts have integral flanges that provide an extra-strong, torque-proof anchor in the handle. Strong, durable black tips are forged and precision ground with square edges to fit screw openings securely. They resist slippage and provide positive turning action.

Cushion-Grip screwdrivers feature super-comfortable, sure-grip handles on top-quality blades for the professional. All Klein screwdrivers meet or exceed applicable ANSI and MIL specifications.



## Using screwdrivers

The size of the screw and the type of opening it has determines which driver to use. But there are a few tips on how to use a driver that can be of benefit, because screwdrivers are the most often misused and abused hand tools of all.

1. **Never use a driver to do another tool's job.** Using a driver as a pry bar, scraper, or a chisel can ruin the tool, spoil the work and cause injury.
2. **Never push a driver beyond its capacity.** Make a pilot hole for the screw for easier driving. Use square-shank drivers for heavy work.
3. **Never expose a driver to excessive heat.** Direct flame can draw the temper from the metal, weakening and possibly warping it, making it unsafe and inefficient to use.

4. **Never use a driver at an angle to the screw.** Always keep the shank perpendicular to the screw head. Driving at an angle or using a point that is too small can spoil the screw or slip and damage the work.

5. **Never depend on a driver's handle or covered blade to insulate you from electricity.** Plastic and Cushion-Grip handles are intended only to provide a firm, comfortable grip. Insulated blades are intended only as a protective measure against shorting out components. Only use insulated tools that are marked with the official international 1000-volt rating symbol if there is any chance that the tool will make contact with an energized source.

6. **Discard damaged or worn drivers.**

*TORX® is a registered trademark of Acument Intellectual Properties, LLC.*

## Journeyman™ Screwdriver Sets

### Features:

**JOURNEYMAN**™

**Sleek new tri-lobed handle** features an ultra comfortable soft-grip material molded over a solid inner core to create exceptional control, grip, and balance.

**Hex-shaped welded bolster** offers additional strength between the blade and handle.

**Precision-machined tip** for exact fit into the fastener.

**Exceptionally hard steel shaft** efficiently transfers every bit of torque generated into the tip.

**Patented Tip-Ident®** quickly identifies the type of screwdriver and screwdriver tip orientation.



**Meets or exceeds** applicable ASME / ANSI specifications.

All dimensions are in inches and (millimeters).

**⚠ WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠ WARNING:** Always wear approved eye protection.

**⚠ WARNING:** Do NOT use to pry or chisel.

## 5-Piece Journeyman™ Screwdriver Set

**JOURNEYMAN**

Additional Features:

- General purpose selection of the most frequently used screwdrivers.

| Cat. No. | Set Contains | Weight (lbs.)                  |              |                  |
|----------|--------------|--------------------------------|--------------|------------------|
| JSDS01   |              | 1.15                           |              |                  |
|          | Cat. No.     | Description                    | Shaft Length | Overall Length   |
|          | JSD6C06      | 3/16" cabinet-tip screwdriver  | 6" (152 mm)  | 10-1/4" (260 mm) |
|          | JSD4K08      | 1/4" keystone-tip screwdriver  | 4" (102 mm)  | 9" (228 mm)      |
|          | JSD6K09      | 5/16" keystone-tip screwdriver | 6" (152 mm)  | 11" (279 mm)     |
|          | JSD4PH1      | #1 Phillips-tip screwdriver    | 4" (102 mm)  | 8-1/4" (210 mm)  |
|          | JSD4PH2      | #2 Phillips-tip screwdriver    | 4" (102 mm)  | 9" (228 mm)      |



JSDS01

## 7-Piece Journeyman™ Screwdriver Set

**JOURNEYMAN**

Additional Features:

- Accommodates a broad range of standard fastener sizes.

| Cat. No. | Set Contains                   |              |                  | Weight (lbs.) |
|----------|--------------------------------|--------------|------------------|---------------|
| JSDS02   |                                |              |                  | 1.65          |
| Cat. No. | Description                    | Shaft Length | Overall Length   |               |
| JSD4C06  | 3/16" cabinet-tip screwdriver  | 4" (102 mm)  | 8-1/4" (210 mm)  |               |
| JSD6C06  | 3/16" cabinet-tip screwdriver  | 6" (152 mm)  | 10-1/4" (260 mm) |               |
| JSD4K08  | 1/4" keystone-tip screwdriver  | 4" (102 mm)  | 9" (228 mm)      |               |
| JSD6K09  | 5/16" keystone-tip screwdriver | 6" (152 mm)  | 11" (279 mm)     |               |
| JSD4PH1  | #1 Phillips-tip screwdriver    | 4" (102 mm)  | 8-1/4" (210 mm)  |               |
| JSD4PH2  | #1 Phillips-tip screwdriver    | 4" (102 mm)  | 9" (228 mm)      |               |
| JSD6PH3  | #2 Phillips-tip screwdriver    | 6" (152 mm)  | 11" (279 mm)     |               |



JSDS02

## Journeyman™ Screwdrivers

### Journeyman™ Cabinet-Tip Screwdrivers – Round Shaft

**JOURNEYMAN**

Additional Features:

- Narrow cabinet-tip permits blade access where space is limited.
- Exceptionally hard steel shaft efficiently transfers torque into the tip.



JSD6C06

| Cat. No. | Shaft Tip Width | Shaft Length | Overall Length   | Weight (lbs.) |
|----------|-----------------|--------------|------------------|---------------|
| JSD4C06  | 3/16" (5 mm)    | 4" (102 mm)  | 8-1/4" (210 mm)  | 0.15          |
| JSD6C06  | 3/16" (5 mm)    | 6" (152 mm)  | 10-1/4" (260 mm) | 0.15          |

All dimensions are in inches and (millimeters).

**⚠ WARNING:** Always wear approved eye protection.

**⚠ WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠ WARNING:** Do NOT use to pry or chisel.



# Journeyman™ Screwdrivers

## Journeyman™ Phillips-Tip Screwdrivers – Round Shaft

**JOURNEYMAN**

Additional Features:

- Tips are precision machined to provide a consistent symmetry.
- Provides accurate fit and torque without slippage.



JSD4PH2

| Cat. No. | Tip Size | Shaft Length | Overall Length  | Weight (lbs.) |
|----------|----------|--------------|-----------------|---------------|
| JSD4PH1  | No. 1    | 4" (102 mm)  | 8-1/4" (210 mm) | 0.15          |
| JSD4PH2  | No. 2    | 4" (102 mm)  | 9" (228 mm)     | 0.25          |
| JSD6PH3  | No. 3    | 6" (152 mm)  | 11" (279 mm)    | 0.35          |



## Journeyman™ Keystone-Tip Screwdrivers – Round Shaft

**JOURNEYMAN**

Additional Features:

- The most popular flat tip style used in high torque applications.
- Hex bolster reinforces blade for hard use and shows for wrench assisted turning.




JSD6K09

| Cat. No. | Shaft Tip Width | Shaft Length | Overall Length | Weight (lbs.) |
|----------|-----------------|--------------|----------------|---------------|
| JSD4K08  | 1/4" (6 mm)     | 4" (102 mm)  | 9" (228 mm)    | 0.25          |
| JSD6K09  | 5/16" (8 mm)    | 6" (152 mm)  | 11" (279 mm)   | 0.35          |



## Cushion-Grip Screwdriver Sets

Features:



All dimensions are in inches and (millimeters).

**⚠ WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠ WARNING:** Always wear approved eye protection.

**⚠ WARNING:** Do NOT use to pry or chisel.



# Cushion-Grip Screwdriver Sets

## 5-Piece Cushion-Grip Screwdriver Set

Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes two cabinet-tip, one Phillips-tip and two keystone-tip screwdrivers.

| Cat. No. | Set Contains                    |              |                    | Weight (lbs.)                                                                     |
|----------|---------------------------------|--------------|--------------------|-----------------------------------------------------------------------------------|
| 85075    |                                 |              |                    | 1.30                                                                              |
| Cat. No. | Description                     | Blade Length | Overall Length     |  |
| 600-4    | square-shank, keystone-tip*     | 4" (102 mm)  | 8-11/32" (212 mm)  |                                                                                   |
| 601-6    | round-shank, cabinet-tip        | 6" (152 mm)  | 9-3/4" (248 mm)    |                                                                                   |
| 602-6    | round-shank, keystone-tip*      | 6" (152 mm)  | 10-15/16" (278 mm) |                                                                                   |
| 603-4    | round-shank, No. 2 Phillips-tip | 4" (102 mm)  | 8-5/16" (211 mm)   |                                                                                   |
| 605-6    | round-shank, cabinet-tip*       | 6" (152 mm)  | 10-11/32" (263 mm) |                                                                                   |

\* Heavy-duty models



## 7-Piece Cushion-Grip Screwdriver Set

Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes three cabinet-tip, two Phillips-tip and two keystone-tip styles.

| Cat. No. | Set Contains |                                 |              | Weight (lbs.)      |
|----------|--------------|---------------------------------|--------------|--------------------|
| 85076    |              |                                 |              | 1.50               |
|          | Cat. No.     | Description                     | Blade Length | Overall Length     |
|          | 600-4        | square-shank, keystone-tip*     | 4" (102 mm)  | 8-11/32" (212 mm)  |
|          | 602-6        | round-shank, keystone-tip*      | 6" (152 mm)  | 10-15/16" (278 mm) |
|          | 601-3        | round-shank, cabinet-tip        | 3" (76 mm)   | 6-3/4" (171 mm)    |
|          | 601-6        | round-shank, cabinet-tip        | 6" (152 mm)  | 9-3/4" (248 mm)    |
|          | 605-4        | round-shank, cabinet-tip*       | 4" (102 mm)  | 8-11/32" (212 mm)  |
|          | 603-3        | round-shank, No. 1 Phillips-tip | 3" (76 mm)   | 6-3/4" (171 mm)    |
|          | 603-4        | round-shank, No. 2 Phillips-tip | 4" (102 mm)  | 8-5/16" (211 mm)   |

\* Heavy-duty models



## 7-Piece Multiple-Application Screwdriver Set

Additional Features:

- Specialty set for a wide variety of applications.
- Includes two cabinet-tip, one Phillips-tip, two keystone-tip, one rotary and one screw-holding screwdriver.

| Cat.No. | Set Contains |                                   |              | Weight (lbs.)      |
|---------|--------------|-----------------------------------|--------------|--------------------|
| 85077   |              |                                   |              | 1.65               |
|         | Cat. No.     | Description                       | Blade Length | Overall Length     |
|         | 600-4        | square-shank, keystone-tip*       | 4" (102 mm)  | 8-11/32" (212 mm)  |
|         | 601-6        | round-shank, cabinet-tip          | 6" (152 mm)  | 9-3/4" (248 mm)    |
|         | 602-6        | round-shank, keystone-tip*        | 6" (152 mm)  | 10-15/16" (278 mm) |
|         | 603-4        | round-shank, No. 2 Phillips-tip   | 4" (102 mm)  | 8-5/16" (211 mm)   |
|         | 605-6        | round-shank, cabinet-tip*         | 6" (152 mm)  | 10-11/32" (263 mm) |
|         | 670-6        | cabinet-tip rotary screwdriver    | 6" (152 mm)  | 9-3/4" (248 mm)    |
|         | K36          | slotted screw-holding screwdriver | 6" (152 mm)  | 9-3/4" (248 mm)    |

\* Heavy-duty model



All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.

Screwdrivers, Nut Drivers  
& Accessories



# Cushion-Grip Screwdriver Sets

## 7-Piece Multiple-Application Screwdriver & Nut Driver Set

Additional Features:

- Specialty set for a wide variety of applications.
- Includes one keystone-tip, two cabinet-tip, one Phillips-tip and three nut drivers.

| Cat. No. | Set Contains                    |              |                    | Weight (lbs.) |
|----------|---------------------------------|--------------|--------------------|---------------|
| 55152    |                                 |              |                    | 2.00          |
| Cat. No. | Description                     | Shank Length | Overall Length     |               |
| 600-4    | square-shank, keystone-tip*     | 4" (102 mm)  | 8-11/32" (212 mm)  |               |
| 601-6    | round-shank, cabinet-tip        | 6" (152 mm)  | 9-3/4" (248 mm)    |               |
| 603-4    | round-shank, No. 2 Phillips-tip | 4" (102 mm)  | 8-5/16" (211 mm)   |               |
| 605-6    | round-shank, cabinet-tip*       | 6" (152 mm)  | 10-11/32" (263 mm) |               |
| 630-1/4  | 1/4" hex nut driver             | 3" (76 mm)   | 6-3/4" (171 mm)    |               |
| 630-5/16 | 5/16" hex nut driver            | 3" (76 mm)   | 6-3/4" (171 mm)    |               |
| 630-3/8  | 3/8" hex nut driver             | 3" (76 mm)   | 6-3/4" (171 mm)    |               |

\* Heavy-duty models



55152

## 8-Piece Cushion-Grip Screwdriver Set

Additional Features:

- General purpose selection of the most frequently used screwdrivers.
- Includes one cabinet-tip, three keystone-tip, four Phillips-tip styles.

| Cat. No. | Set Contains |                                 |                | Weight (lbs.)      |
|----------|--------------|---------------------------------|----------------|--------------------|
| 85078    |              |                                 |                | 1.65               |
|          | Cat. No.     | Description                     | Shank Length   | Overall Length     |
|          | 600-1        | round-shank, keystone-tip       | 1-1/2" (38 mm) | 3-7/16" (87 mm)    |
|          | 601-3        | round-shank, cabinet-tip        | 3" (76 mm)     | 6-3/4" (171 mm)    |
|          | 600-4        | square-shank, keystone-tip*     | 4" (102 mm)    | 8-11/32" (212 mm)  |
|          | 602-6        | round-shank, keystone-tip*      | 6" (152 mm)    | 10-15/16" (278 mm) |
|          | 603-1        | round-shank, No. 2 Phillips-tip | 1-1/2" (38 mm) | 3-7/16" (87 mm)    |
|          | 603-3        | round-shank, No. 1 Phillips-tip | 3" (76 mm)     | 6-3/4" (171 mm)    |
|          | 603-4        | round-shank, No. 2 Phillips-tip | 4" (102 mm)    | 8-5/16" (211 mm)   |
|          | 603-6        | round-shank, No. 3 Phillips-tip | 6" (152 mm)    | 11" (279 mm)       |

\* Heavy-duty models



85078


## 6-Piece Cushion-Grip Screwdriver Set

Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes one cabinet-tip, two keystone-tip and three Phillips-tip styles.

| Cat. No. | Set Contains                    |              |                    | Weight (lbs.)                                                                                                                                                            |
|----------|---------------------------------|--------------|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 85074    |                                 |              |                    | 1.50                                                                                                                                                                     |
| Cat. No. | Description                     | Blade Length | Overall Length     |   |
| 601-3    | round-shank, cabinet-tip        | 3" (76 mm)   | 6-3/4" (171 mm)    |                                                                                                                                                                          |
| 600-4    | square-shank, keystone-tip*     | 4" (102 mm)  | 8-11/32" (212 mm)  |                                                                                                                                                                          |
| 600-6    | square-shank, keystone-tip*     | 6" (152 mm)  | 10-15/16" (278 mm) |                                                                                                                                                                          |
| 603-3    | round-shank, No. 1 Phillips-tip | 3" (76 mm)   | 6-3/4" (171 mm)    |                                                                                                                                                                          |
| 603-4    | round-shank, No. 2 Phillips-tip | 4" (102 mm)  | 8-5/16" (211 mm)   |                                                                                                                                                                          |
| 603-6    | round-shank, No. 3 Phillips-tip | 6" (152 mm)  | 11" (279 mm)       |                                                                                                                                                                          |

\* Heavy-duty models



85074

All dimensions are in inches and (millimeters).

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Always wear approved eye protection.

**WARNING:** Do NOT use to pry or chisel.



# Cushion-Grip Screwdriver Sets

## 4-Piece Cushion-Grip Screwdriver Set

Additional Features:

- The screwdrivers Professionals carry most often.
- Includes one Phillips-tip, two keystone-tip, one cabinet-tip screwdrivers.

**NEW!**

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 85105    |              | 1.50          |

| Cat. No. | Description                     | Blade Length | Overall Length     |
|----------|---------------------------------|--------------|--------------------|
| 603-4    | round-shank, No. 2 Phillips-tip | 4" (102 mm)  | 8-5/16" (211 mm)   |
| 600-4    | square-shank, keystone-tip*     | 4" (102 mm)  | 8-11/32" (212 mm)  |
| 601-6    | round-shank, cabinet-tip        | 6" (152 mm)  | 9-3/4" (248 mm)    |
| 600-6    | square-shank, keystone-tip*     | 6" (152 mm)  | 10-15/16" (278 mm) |

\* Heavy-duty models



85105



## 2-Piece 10" Long Blade Screwdriver Set

Additional Features:

- Phillips-tip is precision-machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Precision-ground narrow cabinet-tip permits blade access where space is limited.
- Ideal for hard-to-reach places where added length is necessary.
- Includes one Phillips-tip and one cabinet-tip.

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 85072    |              | .70           |

| Cat. No. | Description                          | Shank Tip Size | Shank Length | Overall Length    |
|----------|--------------------------------------|----------------|--------------|-------------------|
| 603-10   | round-shank, profilated Phillips-tip | No. 2          | 10" (254 mm) | 14-5/16" (363 mm) |
| 605-10   | round-shank, cabinet-tip             | 1/4" (6 mm)    | 10" (254 mm) | 14-5/16" (363 mm) |



85072



## 4-Piece Miniature Cushion-Grip Screwdriver Set

Additional Feature:

- Precision tips for exact fit and rigorous applications.

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 85484    |              | .14           |

| Cat. No. | Tip Type Size | Shank Tip Size | Shank Length | Overall Length  |
|----------|---------------|----------------|--------------|-----------------|
| 604-3    | Phillips-tip  | No. 0          | 3" (76 mm)   | 5-3/4" (146 mm) |
| 606-2    | keystone-tip  | 1/16" (1.6 mm) | 2" (51 mm)   | 4-3/4" (121 mm) |
| 607-3    | cabinet-tip   | 3/32" (2.4 mm) | 3" (76 mm)   | 5-3/4" (146 mm) |
| 608-3    | cabinet-tip   | 1/8" (3.2 mm)  | 3" (76 mm)   | 5-3/4" (146 mm) |



85484



All dimensions are in inches and (millimeters).

**⚠ WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠ WARNING:** Always wear approved eye protection.

**⚠ WARNING:** Do NOT use to pry or chisel.



# Cushion-Grip Screwdriver Sets

## 4-Piece Square Recess Cushion-Grip Screwdriver Set

Additional Features:

- Color-coded handle ends with Tip-Ident® for quick and easy identification.
- Round shank with square-recess tip.
- Chrome-plated shank for corrosion resistance.
- Cushion-grip handle for greater torque and comfort.
- Works on most combination head receptacle, switch and panel screws.

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 85664    |              | 1.50          |

| Cat. No. | Point Size | Color Code | Shank Length | Overall Length   |
|----------|------------|------------|--------------|------------------|
| 660      | No. 0      | yellow     | 4" (102 mm)  | 7-3/4" (197 mm)  |
| 661      | No. 1      | green      | 4" (102 mm)  | 7-3/4" (197 mm)  |
| 662      | No. 2      | red        | 4" (102 mm)  | 8-5/16" (211 mm) |
| 663      | No. 3      | black      | 4" (102 mm)  | 8-5/16" (211 mm) |



85664

## 5-Piece TORX® Cushion-Grip Screwdriver Set

Additional Features:

- Color-coded handle ends with Tip-Ident® for quick and easy identification.
- TORX® drive systems transmit more torque to the work and reduce slippage, saving fasteners.
- Chrome plated shank for corrosion resistance.
- Cushion-Grip handle for greater torque and comfort.

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 19555    |              | 1.20          |

| Cat. No. | TORX® Size | Color Code | Shank Length | Overall Length   |
|----------|------------|------------|--------------|------------------|
| 19542    | T15        | yellow     | 4" (102 mm)  | 7-3/4" (197 mm)  |
| 19543    | T20        | green      | 4" (102 mm)  | 7-3/4" (197 mm)  |
| 19544    | T25        | blue       | 4" (102 mm)  | 7-3/4" (197 mm)  |
| 19545    | T27        | brown      | 4" (102 mm)  | 8-5/16" (211 mm) |
| 19546    | T30        | red        | 4" (102 mm)  | 8-5/16" (211 mm) |



19555

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

## 2-Piece Stubby Screwdriver Set

Additional Feature:

- Double wings inside handle provide solid, twist-resistant blade anchor.



85071



| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 85071    |              | .30           |

| Cat. No. | Description               | Shank Length   | Overall Length  |
|----------|---------------------------|----------------|-----------------|
| 600-1    | round-shank, keystone-tip | 1-1/2" (38 mm) | 3-7/16" (87 mm) |
| 603-1    | round-shank, Phillips-tip | 1-1/2" (38 mm) | 3-7/16" (87 mm) |

## Stubby Square-Recess Tip Cushion-Grip Screwdrivers

Additional Features:

- Double wings inside handle provide solid, twist-resistant blade anchor.
- Works on most combination head receptacle and switch screws.
- Color-coded handle ends for quick and easy identification.



85155

| Cat. No. | Description                          | Color Code | Shank Length   | Overall Length  | Weight (lbs.) |
|----------|--------------------------------------|------------|----------------|-----------------|---------------|
| 668      | round-shank, No. 1 square-recess tip | green      | 1-1/2" (38 mm) | 3-7/16" (87 mm) | .15           |
| 669      | round-shank, No. 2 square-recess tip | red        | 1-1/2" (38 mm) | 3-7/16" (87 mm) | .15           |

### Stubby Square-Recess Cushion-Grip Screwdriver Set

| Cat. No. | Description                                               | Color Code                               | Shank Length   | Overall Length  | Weight (lbs.) |
|----------|-----------------------------------------------------------|------------------------------------------|----------------|-----------------|---------------|
| 85155    | 2-piece stubby square-recess cushion-grip screwdriver set | green (Cat. No. 668), red (Cat. No. 669) | 1-1/2" (38 mm) | 3-7/16" (87 mm) | .30           |

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.



## Keystone-Tip Screwdrivers – Heavy-Duty Square-Shanks

Additional Features:

- Heavy-duty square shank for wrench-assisted turning.
- Bolster reinforces shank for hard use.
- Designed for the most demanding uses.

| Cat. No. | Tip Size     | Shank Length | Overall Length     | Weight (lbs.) |
|----------|--------------|--------------|--------------------|---------------|
| 600-4    | 1/4" (6 mm)  | 4" (102 mm)  | 8-11/32" (212 mm)  | .25           |
| 600-6    | 5/16" (8 mm) | 6" (152 mm)  | 10-15/16" (278 mm) | .40           |
| 600-8    | 3/8" (10 mm) | 8" (203 mm)  | 13-7/16" (341 mm)  | .65           |
| 600-12   | 1/2" (13 mm) | 12" (305 mm) | 17-7/16" (443 mm)  | .80           |



600-4

## Keystone-Tip Screwdrivers – Heavy-Duty Round-Shanks

Additional Features:

- Built to handle the tough jobs with ease.
- Hex bolster reinforces shank for hard use and allows wrench assisted turning.

| Cat. No. | Tip Size     | Shank Length   | Overall Length     | Weight (lbs.) |
|----------|--------------|----------------|--------------------|---------------|
| 600-1*   | 1/4" (6 mm)  | 1-1/2" (38 mm) | 3-7/16" (87 mm)    | .10           |
| 602-3    | 7/32" (6 mm) | 3" (76 mm)     | 6-3/4" (171 mm)    | .15           |
| 602-4    | 1/4" (6 mm)  | 4" (102 mm)    | 8-11/32" (212 mm)  | .25           |
| 602-6    | 5/16" (8 mm) | 6" (152 mm)    | 10-15/16" (278 mm) | .35           |
| 602-8    | 3/8" (10 mm) | 8" (203 mm)    | 13-7/16" (341 mm)  | .55           |
| 602-10   | 3/8" (10 mm) | 10" (254 mm)   | 15-7/16" (392 mm)  | .60           |
| 602-12   | 3/8" (10 mm) | 12" (305 mm)   | 17-7/16" (443 mm)  | .65           |



602-6

\* Bolster not available on 600-1.  
Refer to the insulated section for insulated screwdrivers.

## Cabinet-Tip Screwdrivers – Round-Shanks

Additional Feature:

- Narrow cabinet-tip permits blade access where space is limited.

| Cat. No. | Tip Size     | Shank Length | Overall Length   | Weight (lbs.) |
|----------|--------------|--------------|------------------|---------------|
| 601-3    | 3/16" (5 mm) | 3" (76 mm)   | 6-3/4" (171 mm)  | .10           |
| 601-4    | 3/16" (5 mm) | 4" (102 mm)  | 7-3/4" (197 mm)  | .15           |
| 601-6    | 3/16" (5 mm) | 6" (152 mm)  | 9-3/4" (248 mm)  | .15           |
| 601-8    | 3/16" (5 mm) | 8" (203 mm)  | 11-3/4" (298 mm) | .20           |
| 601-10   | 3/16" (5 mm) | 10" (254 mm) | 13-3/4" (349 mm) | .20           |



601-6

| Cat. No.                 | Tip Size    | Shank Length | Overall Length     | Weight (lbs.) |
|--------------------------|-------------|--------------|--------------------|---------------|
| <b>Heavy-Duty Shanks</b> |             |              |                    |               |
| 605-4                    | 1/4" (6 mm) | 4" (102 mm)  | 8-11/32" (212 mm)  | .25           |
| 605-6                    | 1/4" (6 mm) | 6" (152 mm)  | 10-11/32" (263 mm) | .30           |
| 605-8                    | 1/4" (6 mm) | 8" (203 mm)  | 12-11/32" (314 mm) | .30           |
| 605-10                   | 1/4" (6 mm) | 10" (254 mm) | 14-11/32" (365 mm) | .35           |

Refer to the insulated section for insulated screwdrivers.

## Profilated Phillips-Tip Screwdrivers – Round-Shanks

Additional Features:

- Tips are precision-machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Provides accurate fit and torque without slippage.



603-7

| Cat. No. | Tip Size | Shank Length   | Overall Length    | Weight (lbs.) |
|----------|----------|----------------|-------------------|---------------|
| 603-1    | No. 2    | 1-1/2" (38 mm) | 3-7/16" (87 mm)   | .10           |
| 603-3    | No. 1    | 3" (76 mm)     | 6-3/4" (171 mm)   | .15           |
| 603-4    | No. 2    | 4" (102 mm)    | 8-5/16" (211 mm)  | .25           |
| 603-6    | No. 3    | 6" (152 mm)    | 11" (279 mm)      | .35           |
| 603-7    | No. 2    | 7" (178 mm)    | 11-5/16" (287 mm) | .30           |
| 603-10   | No. 2    | 10" (254 mm)   | 14-5/16" (364 mm) | .35           |

Refer to the insulated section for insulated screwdrivers.

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.



# Cushion-Grip Screwdrivers

## Miniature Cushion-Grip Screwdrivers



Additional Feature:

- Precision tip for exact fit and rigorous applications.

| Cat. No. | Tip Type     | Tip Size       | Shank Length | Overall Length   | Weight (lbs.) |
|----------|--------------|----------------|--------------|------------------|---------------|
| 604-3    | Phillips-tip | No. 0          | 3" (76 mm)   | 5-3/4" (146 mm)  | .04           |
| 606-2    | keystone-tip | 1/16" (1.6 mm) | 2" (51 mm)   | 4-3/4" (121 mm)  | .03           |
| 607-2    | cabinet-tip  | 3/32" (2.4 mm) | 2" (51 mm)   | 4-3/4" (121 mm)  | .03           |
| 607-3    | cabinet-tip  | 3/32" (2.4 mm) | 3" (76 mm)   | 5-3/4" (146 mm)  | .04           |
| 607-4    | cabinet-tip  | 3/32" (2.4 mm) | 4" (102 mm)  | 6-3/4" (171 mm)  | .04           |
| 608-2    | cabinet-tip  | 1/8" (3.2 mm)  | 2" (51 mm)   | 4-3/4" (121 mm)  | .03           |
| 608-3    | cabinet-tip  | 1/8" (3.2 mm)  | 3" (76 mm)   | 5-3/4" (146 mm)  | .04           |
| 608-4    | cabinet-tip  | 1/8" (3.2 mm)  | 4" (102 mm)  | 6-3/4" (171 mm)  | .05           |
| 608-6    | cabinet-tip  | 1/8" (3.2 mm)  | 6" (152 mm)  | 8-3/4" (222 mm)  | .05           |
| 608-8    | cabinet-tip  | 1/8" (3.2 mm)  | 8" (203 mm)  | 10-3/4" (273 mm) | .05           |
| 608-10   | cabinet-tip  | 1/8" (3.2 mm)  | 10" (254 mm) | 12-3/4" (324 mm) | .05           |

## Square-Recess Tip Screwdrivers – Round-Shanks



Additional Features:

- Color-coded handle ends for quick and easy identification.
- Round shank with Square-Recess tip.
- Chrome plated shank for corrosion resistance.

| Cat. No. | Tip Size | Color Code | Shank Length | Overall Length   | Weight (lbs.) |
|----------|----------|------------|--------------|------------------|---------------|
| 660      | No. 0    | yellow     | 4" (102 mm)  | 7-3/4" (197 mm)  | .20           |
| 661      | No. 1    | green      | 4" (102 mm)  | 7-3/4" (197 mm)  | .20           |
| 662      | No. 2    | red        | 4" (102 mm)  | 8-1/4" (210 mm)  | .30           |
| 663      | No. 3    | black      | 4" (102 mm)  | 8-1/4" (210 mm)  | .30           |
| 665      | No. 1    | green      | 8" (203 mm)  | 11-3/4" (298 mm) | .30           |
| 666      | No. 2    | red        | 8" (203 mm)  | 12-1/4" (311 mm) | .40           |
| 667      | No. 3    | black      | 8" (203 mm)  | 12-1/4" (311 mm) | .40           |

Refer to the insulated section for insulated screwdrivers.

## Terminal Block Screwdriver

**NEW!**

Additional Features:

- Precision-machined tip provides exact fit for terminal block screws.
- Tip is up to 19% stronger than competitors.
- Tip provides 76% higher torque value than the required ASME B107 Standard.
- Cushion-Grip handle offers greater torque comfort.

| Cat. No. | Shank Top Width | Shank Length | Overall Length  | Weight (lbs.) |
|----------|-----------------|--------------|-----------------|---------------|
| 612-4    | 1/8" (3.2 mm)   | 4" (100 mm)  | 7-3/4" (200 mm) | 0.15          |

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

## Coated Cabinet-Tip Screwdrivers – Round-Shanks



Additional Features:

- Plastic coated for circuit protection only. **NOT INSULATED.**
- Special plastic coating resists cutting, cracking and chipping.
- Thin coating permits use in confined areas.

| Cat. No.                 | Tip Size     | Shank Length | Overall Length     | Weight (lbs.) |
|--------------------------|--------------|--------------|--------------------|---------------|
| 620-3                    | 3/16" (5 mm) | 3" (76 mm)   | 6-3/4" (171 mm)    | .15           |
| 621-6                    | 3/16" (5 mm) | 6" (152 mm)  | 9-3/4" (248 mm)    | .20           |
| 621-8                    | 3/16" (5 mm) | 8" (203 mm)  | 11-3/4" (298 mm)   | .20           |
| 621-10                   | 3/16" (5 mm) | 10" (254 mm) | 13-3/4" (349 mm)   | .25           |
| <b>Heavy-Duty Shanks</b> |              |              |                    |               |
| 620-4                    | 1/4" (6 mm)  | 4" (102 mm)  | 8-11/32" (212 mm)  | .20           |
| 620-6                    | 5/16" (8 mm) | 6" (152 mm)  | 10-15/16" (278 mm) | .40           |
| 620-8                    | 3/8" (10 mm) | 8" (203 mm)  | 13-7/16" (341 mm)  | .60           |

## TORX® Screwdrivers – Round-Shanks



Additional Features:

- Color-coded handle ends for quick and easy identification.
- TORX® tip drive cuts slippage, saves fasteners and transmits more torque to the work.
- Chrome-plated shank for corrosion resistance.

| Cat. No. | TORX® Size | Color Code | Shank Length | Overall Length   | Weight (lbs.) |
|----------|------------|------------|--------------|------------------|---------------|
| 19542    | T15        | yellow     | 4" (102 mm)  | 8-5/16" (211 mm) | .20           |
| 19543    | T20        | green      | 4" (102 mm)  | 8-5/16" (211 mm) | .25           |
| 19544    | T25        | blue       | 4" (102 mm)  | 8-5/16" (211 mm) | .25           |
| 19545    | T27        | brown      | 4" (102 mm)  | 8-5/16" (211 mm) | .25           |
| 19546    | T30        | red        | 4" (102 mm)  | 8-5/16" (211 mm) | .25           |

TORX® is a registered trademark of Acument Intellectual Properties, LLC.



**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.



## Cushion-Grip Screwdrivers

### Conduit-Fitting and Reaming Screwdriver

#### Additional Features:

- Hooded-blade design keeps tip from slipping out of screws, especially when tightening hard-to-reach conduit fittings. Thicker hood is designed for rugged use.
- Reams and smooths 1/2" (13 mm), 3/4" (19 mm), and 1" (25 mm) thin-wall conduit ends to protect wire and permit correct installation of fittings.
- Reams both the inside and outside of the conduit at the same time.
- Longer Cushion-Grip handle provides comfort and more torque for reaming.
- Replaceable reaming blade is now held in place with a 1/16" set screw.



| Cat. No. | Tip Size                             | Shank Length   | Overall Length  | Weight (lbs.) |
|----------|--------------------------------------|----------------|-----------------|---------------|
| 85191    | 5/16" (8 mm)                         | 2-1/2" (64 mm) | 7-1/2" (191 mm) | .50           |
| 19353    | conduit reamer replacement blade kit |                |                 | .01           |

### Conduit Reamer

- Locks onto screwdrivers; reams and smooths thin-wall conduit.
- Reams ID and OD at the same time.
- Two set-screws for round- and square-shank screwdrivers.



| Cat. No. | Conduit Capacity                               | Weight (lbs.) |
|----------|------------------------------------------------|---------------|
| 19352    | 1/2", 3/4", 1"                                 | .20           |
| 19353    | conduit reamer replacement blade kit for 19352 | .01           |
| 19351    | conduit reamer replacement blade for 19350     | .01           |

- Fits up to 3/8" (10 mm) keystone-tip screwdrivers.
- NOT for use on power tools.


## Rapi-Drive® Screwdrivers

### Cabinet-Tip Screwdrivers – Rapi-Drive®

#### Additional Features:

- Crank-action handle spins screws fast with one hand.
- Saves time and effort, especially on long-threaded screws in switch plates, light fixtures, etc.

| Cat. No. | Tip Size     | Shank Length | Overall Length  | Weight (lbs.) |
|----------|--------------|--------------|-----------------|---------------|
| 670-3    | 3/16" (5 mm) | 4" (102 mm)  | 7-3/4" (197 mm) | .15           |
| 670-6    | 3/16" (5 mm) | 6" (152 mm)  | 9-3/4" (248 mm) | .20           |
| 671-6    | 1/4" (6 mm)  | 6" (152 mm)  | 9-3/4" (248 mm) | .20           |




### Phillips Screwdrivers – Rapi-Drive®

#### Additional Features:

- Crank-action handle spins screws fast with one hand.
- Saves time and effort, especially on long-threaded screws in switch plates, light fixtures, etc.

| Cat. No. | Tip Size | Shank Length | Overall Length  | Weight (lbs.) |
|----------|----------|--------------|-----------------|---------------|
| 681-6    | No. 1    | 6" (152 mm)  | 9-3/4" (248 mm) | .20           |
| 682-6    | No. 2    | 6" (152 mm)  | 9-3/4" (248 mm) | .25           |




### Square-Recess Screwdrivers – Rapi-Drive®

#### Additional Features:

- Crank-action handle spins screws fast with one hand.
- Color-coded handle ends for quick and easy identification.

| Cat. No. | Tip Size | Shank Length | Overall Length  | Weight (lbs.) |
|----------|----------|--------------|-----------------|---------------|
| 691-6    | No. 1    | 6" (152 mm)  | 9-3/4" (248 mm) | .35           |
| 692-6    | No. 2    | 6" (152 mm)  | 9-3/4" (248 mm) | .35           |



All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.



# Rapi-Driv® Screwdrivers

## Interchangeable Rapi-Driv®

- The original Klein Cushion-Grip handle for superior comfort and torque!
- Interchangeable bit holder allows quick switching between tip styles and works with other standard size bits.
- Crank-action handle allows you to spin screws fast with one hand.
- Blast finish bit provides firm grip on fasteners to reduce cam out.


| Cat. No. | Contains                   | Shaft Length | Overall Length  | Weight (lbs.) |
|----------|----------------------------|--------------|-----------------|---------------|
| 67100    | 3/16" slotted, #2 Phillips | 6" (152 mm)  | 9-3/4" (248 mm) | .26           |

### 2-in-1 Replacement Bit

| Cat. No. | Fits                                             | Description                                | Quantity        | Weight (lbs.) |
|----------|--------------------------------------------------|--------------------------------------------|-----------------|---------------|
| 67101    | 2-in-1 Rapi-Driv®, 10-in-1, 11-in-1 and 10-Fold™ | 3/16" slotted, #2 Phillips replacement bit | contains 2 bits | .012          |



67100



## Specialty Screwdrivers

### Slotted Screw-Holding Screwdrivers

Additional Features:

- Starts and drives screws with one hand when working in hard-to-reach spaces.
- Cushion-Grip handle provides superior torque and comfort with non-slip grip.

| Cat. No. | Screwdriver Type | Shank Length | Overall Length   | Weight (lbs.) |
|----------|------------------|--------------|------------------|---------------|
| 32215    | 1/4" cabinet     | 7" (178 mm)  | 11-1/4" (276 mm) | 0.32          |
| 32216    | #2 Phillips      | 7" (178 mm)  | 11-1/4" (276 mm) | 0.32          |



32215



**NEW!**

### Wire Bending Cabinet-Tip Screwdrivers – Round-Shank

Additional Feature:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.

| Cat. No. | Tip Size    | Shank Length | Overall Length     | Bends AWG Gauges | Finish        | Weight (lbs.) |
|----------|-------------|--------------|--------------------|------------------|---------------|---------------|
| 605-4B   | 1/4" (6 mm) | 4" (102 mm)  | 8-11/32" (212 mm)  | Nos. 10, 12, 14  | chrome-plated | 0.25          |
| 605-6B   | 1/4" (6 mm) | 6" (152 mm)  | 10-11/32" (263 mm) | Nos. 10, 12, 14  | chrome-plated | 0.30          |



605-6B



### Wire Bending Phillips-Tip Screwdrivers – Round-Shanks

Additional Feature:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.

| Cat. No. | Tip Size | Shank Length | Overall Length   | Bends AWG Gauges | Finish        | Weight (lbs.) |
|----------|----------|--------------|------------------|------------------|---------------|---------------|
| 603-3B   | No. 1    | 3" (76 mm)   | 6-3/4" (171 mm)  | Nos. 12 and 14   | chrome-plated | 0.15          |
| 603-4B   | No. 2    | 4" (102 mm)  | 8-5/16" (211 mm) | Nos. 10, 12, 14  | chrome-plated | 0.25          |



603-4B



### Wire Bending Square-Recess Tip Screwdrivers – Round Shanks

Additional Feature:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.

| Cat. No. | Tip Size | Shank Length | Overall Length  | Bends AWG Gauges | Finish        | Weight (lbs.) |
|----------|----------|--------------|-----------------|------------------|---------------|---------------|
| 661B     | No. 1    | 4" (102 mm)  | 8-1/4" (210 mm) | Nos. 10, 12, 14  | chrome-plated | 0.20          |
| 662B     | No. 2    | 4" (102 mm)  | 8-1/4" (210 mm) | Nos. 10, 12, 14  | chrome-plated | 0.30          |



661B



All dimensions are in inches and (millimeters).

**⚠WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠WARNING:** Always wear approved eye protection.

**⚠WARNING:** Do NOT use to pry or chisel.



# Multi-Bit Screwdrivers/Nut Drivers

## Heavy-Duty Multi-Bit Screwdriver/Nut Driver

- Klein's Heavy-Duty Multi-Bit driver has improved design and construction for greater strength and Cushion-Grip handles for superior torque and comfort.
- Shaft holds 6 universal tips; converts to 3 nut driver sizes and 1 hex driver
- Strong, heat-treated nut drivers for improved torque



32557

| Cat. No. | Shaft Length  | Overall Length | Weight |
|----------|---------------|----------------|--------|
| 32557    | 2.95" (75 mm) | 7.9" (201 mm)  | 0.48   |

NEW!

## Ratcheting Multi-Bit Screwdriver/Nut Driver

- Klein's Heavy-Duty Ratcheting Multi-Bit driver provides high-torque capability and comfortable Cushion-Grip handles.
- Shaft holds 6 universal tips; converts to 3 nut driver sizes and 1 hex driver
- Strong, heat-treated nut drivers for improved torque
- 3-way ratcheting mechanism for forward, reverse and locked positions



32558

| Cat. No. | Shaft Length  | Overall Length | Weight |
|----------|---------------|----------------|--------|
| 32558    | 2.95" (75 mm) | 8.0" (203 mm)  | 0.71   |

NEW!

## Extended-Reach Multi-Bit Screwdrivers/Nut Drivers

- Klein's Extended-Reach Multi-Bit drivers have extended shafts and blades that provide 39% longer reach, and Cushion-Grip handles for superior torque and comfort.
- Shaft holds 4 universal tips and converts to 2 nut driver sizes
- Extra-long shaft provides full reach of 4" standard-blade screwdriver
- Small diameter shaft for comfortable grip and quick, easy turning



Cat. No. 32560



Cat. No. 32559



32559

| Cat. No. | Shaft Length   | Overall Length | Weight |
|----------|----------------|----------------|--------|
| 32559    | 4.11" (104 mm) | 9.1" (231 mm)  | 0.41   |
| 32560    | 4.11" (104 mm) | 9.1" (231 mm)  | 0.41   |

NEW!

## Stubby Multi-Bit Screwdriver/Nut Driver

- Klein's Stubby Multi-Bit driver allows you to work in tight spaces.
- Shaft holds 4 universal tips and converts to 2 nut driver sizes
- Compact design features standard 1-1/4" shaft



| Cat. No. | Shaft Length  | Overall Length | Weight |
|----------|---------------|----------------|--------|
| 32561    | 1.27" (32 mm) | 3.2" (81 mm)   | 0.16   |

NEW!



32561

All dimensions are in inches and (millimeters).

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Always wear approved eye protection.

**WARNING:** Do NOT use to pry or chisel.



# Multi-Bit Screwdrivers/Nut Drivers

## 5-in-1 Screwdriver/Nut Driver

Additional Feature:

- End of handle is marked to quickly identify tool.



32476

| Cat. No. | Contains                                                              | Weight (lbs.) |
|----------|-----------------------------------------------------------------------|---------------|
| 32476    | 5/16" nut driver, #1 and #2 Phillips, 9/32" slotted and 3/16" slotted | .35           |

## 10-in-1 Screwdriver/Nut Driver

Additional Feature:

- End of handle is marked to quickly identify tool.



TORX® is a registered trademark of Acument Intellectual Properties, LLC.



32477

| Cat. No. | Contains                                                                                                           | Weight (lbs.) |
|----------|--------------------------------------------------------------------------------------------------------------------|---------------|
| 32477    | 5/16" and 1/4" nut drivers, #1 and #2 Phillips, 1/4" and 3/16" slotted, T10 and T15 TORX®, #1 and #2 square-recess | .35           |

## 11-in-1 Screwdriver/Nut Driver

Additional Feature:

- Integrated screwdriver/nut driver shaft holds 8 popular tips and converts to 3 nut driver sizes.
- End of handle is marked to quickly identify tool.



TORX® is a registered trademark of Acument Intellectual Properties, LLC.



32500

| Cat. No. | Contains                                                                                                                 | Weight (lbs.) |
|----------|--------------------------------------------------------------------------------------------------------------------------|---------------|
| 32500    | 3/8", 5/16" and 1/4" nut drivers, #1 and #2 Phillips, 1/4" and 3/16" slotted, T10 and T15 TORX®, #1 and #2 square-recess | .44           |

## 11-in-1 Screwdriver/Nut Driver with Schrader® Valve Removal/ Installation Bit

Additional Features:

- Versatile 11-in-1 tool for the professional.
- Includes unique style bit for installation/removal of common TR-4 Schrader® valves and aggressive thread extractor tip for backing out broken cores.
- Great for HVAC and other industrial applications.
- Cushion-Grip handle for superior torque and comfort.

Schrader® is a registered trademark of Schrader International, Inc.



32527

| Cat. No. | Contains                                                                                                                                                     | Weight (lbs.) |
|----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| 32527    | 3/8", 5/16" and 1/4" nut drivers, #1 and #2 Phillips, #1 square and #2 square, 1/4" and 3/16" slotted, Schrader® valve core removal/installation – extractor | .44           |

## 10-in-1 Folding Screwdriver/Nut Driver

10-FOLD®

- Conveniently folds up for easy storage or to fit into your pocket.
- Each driver arm contains four interchangeable bit styles and two nut drivers.
- Unfold each driver arm up to a full 180° for straight on driving power, or at 90° for extra leverage on stubborn fasteners.
- The quick release button easily unlocks a fully extended driver arm.

TORX®



32536

TAMPERPROOF TORX®



32537

FRACTIONAL HEX



32538

METRIC HEX



32539

TORX® is a registered trademark of Acument Intellectual Properties, LLC.



32535

| Cat. No. | Handle Color | Description                                                                                                      | Weight (lbs.) |
|----------|--------------|------------------------------------------------------------------------------------------------------------------|---------------|
| 32535    | black        | 5/16" & 1/4" nut drivers, #1 and #2 Phillips, 1/4" & 3/16" slotted, T10 & T15 TORX®, and #1 and #2 square-recess | 0.37          |
| 32536    | green        | 5/16" & 1/4" nut drivers, T6, T7, T8, T10, T15, T20, T25, T27 TORX®                                              | 0.37          |
| 32537    | green        | 5/16" & 1/4" nut drivers, T7, T8, T9, T10, T15, T20, T25, T27 TORX®                                              | 0.37          |
| 32538    | red          | 5/16" & 1/4" nut drivers, 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16" standard hex                     | 0.37          |
| 32539    | blue         | 5/16" & 1/4" nut drivers, .9 mm, 1.3 mm, 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm metric hex                       | 0.37          |

All dimensions are in inches and (millimeters).

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Always wear approved eye protection.

**WARNING:** Do NOT use to pry or chisel.



# Replacement Parts Multi-Bit Screwdriver/Nut Drivers

## Replacement Bits for Screwdriver/Nut Drivers

- Precision-machined tips for exact fit into fastener.



32484



32482



32483

### Replacement Bits for Multi-Bit Interchangeable Screwdriver/Nut Drivers (32557, 32558, 32559, 32560, 32561)

| Cat. No. | Fits                   | Description                                           | Quantity         |
|----------|------------------------|-------------------------------------------------------|------------------|
| 32392    | 32557 and 32558        | Heavy Duty Main Blade Barrel                          | contains 1 unit  |
| 32394    | 32557 and 32558        | Heavy Duty Secondary Blade Barrel                     | contains 2 units |
| 32395    | 32559 and 32560        | Extended Blade Barrel                                 | contains 1 unit  |
| 32396    | 32561                  | Stubby Blade Barrel                                   | contains 1 unit  |
| 32397    | 32557 and 32558        | Screwdriver Bit & #2 PH x #1 Square                   | contains 2 bits  |
| 32398    | 32557, 32558 and 32561 | Screwdriver Bit & #1 PH x 1/4 Slotted                 | contains 2 bits  |
| 32399    | 32557 and 32558        | Screwdriver Bit & #2 Square x 3/16 Slotted            | contains 2 bits  |
| 32400    | 32559                  | Extended Screwdriver Bit & #2 PH x #1 PH              | contains 2 bits  |
| 32401    | 32559                  | Extended Screwdriver Bit & 3/16 Slotted x 1/4 Slotted | contains 2 bits  |
| 32410    | 32560                  | Extended Screwdriver Bit & #2 Square x #2 PH          | contains 2 bits  |
| 32411    | 32560                  | Extended Screwdriver Bit & #1 Square x 1/4 Slotted    | contains 2 bits  |
| 32412    | 32561                  | Screwdriver Bit & #2 PH x 3/16 Slotted                | contains 2 bits  |

### Replacement Bits for 5-in-1 Interchangeable Screwdriver/Nut Drivers

| Cat. No. | Fits                    | Description                 | Quantity       |
|----------|-------------------------|-----------------------------|----------------|
| 32478    | 5-in-1 (Cat. No. 32476) | #1 Phillips – 3/16" slotted | contains 1 bit |
| 32479    | 5-in-1 (Cat. No. 32476) | #2 Phillips – 9/32" slotted | contains 1 bit |

### Replacement Bits for 10-in-1, 11-in-1 and 10-Fold® Interchangeable Screwdriver/Nut Drivers

| Cat. No. | Fits                          | Description                   | Quantity        |
|----------|-------------------------------|-------------------------------|-----------------|
| 32482    | 10-in-1, 11-in-1 and 10-Fold™ | #1 Phillips & 3/16" Slotted   | contains 2 bits |
| 32483    | 10-in-1, 11-in-1 and 10-Fold™ | #2 Phillips & 1/4" Slotted    | contains 2 bits |
| 32484    | 10-in-1, 11-in-1 and 10-Fold™ | #1 Square & #2 Square         | contains 2 bits |
| 67101    | 10-in-1, 11-in-1 and 10-Fold™ | #2 Phillips & 3/16" Slotted   | contains 2 bits |
| 32540    | 10-in-1, 11-in-1 and 10-Fold™ | TT7 & TT8 Tamperproof TORX®   | contains 2 bits |
| 32541    | 10-in-1, 11-in-1 and 10-Fold™ | TT9 & TT10 Tamperproof TORX®  | contains 2 bits |
| 32542    | 10-in-1, 11-in-1 and 10-Fold™ | TT15 & TT20 Tamperproof TORX® | contains 2 bits |
| 32543    | 10-in-1, 11-in-1 and 10-Fold™ | TT25 & TT27 Tamperproof TORX® | contains 2 bits |
| 32544    | 10-in-1, 11-in-1 and 10-Fold™ | #6 TORX® & #7 TORX®           | contains 2 bits |
| 32485    | 10-in-1, 11-in-1 and 10-Fold™ | #10 TORX® & #15 TORX®         | contains 2 bits |
| 32545    | 10-in-1, 11-in-1 and 10-Fold™ | #T8 TORX® & #10 TORX®         | contains 2 bits |
| 32546    | 10-in-1, 11-in-1 and 10-Fold™ | #T25 TORX® & #T27 TORX®       | contains 2 bits |
| 32547    | 10-in-1, 11-in-1 and 10-Fold™ | 3/32" Hex & 7/64" Hex         | contains 2 bits |
| 32548    | 10-in-1, 11-in-1 and 10-Fold™ | 5/32" Hex & 3/16" Hex         | contains 2 bits |
| 32549    | 10-in-1, 11-in-1 and 10-Fold™ | 1/16" Hex & 5/64" Hex         | contains 2 bits |
| 32550    | 10-in-1, 11-in-1 and 10-Fold™ | 1/8" Hex & 9/64" Hex          | contains 2 bits |
| 32551    | 10-in-1, 11-in-1 and 10-Fold™ | .9 mm Hex & 1.3 mm Hex        | contains 2 bits |
| 32552    | 10-in-1, 11-in-1 and 10-Fold™ | 1.5 mm Hex & 2 mm Hex         | contains 2 bits |
| 32553    | 10-in-1, 11-in-1 and 10-Fold™ | 2.5 mm Hex & 3 mm Hex         | contains 2 bits |
| 32554    | 10-in-1, 11-in-1 and 10-Fold™ | 4 mm Hex & 5 mm Hex           | contains 2 bits |

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

All dimensions are in inches and (millimeters).

**⚠ WARNING:** Always wear approved eye protection.

**⚠ WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠ WARNING:** Do NOT use to pry or chisel.

Screwdrivers, Nut Drivers  
& Accessories



# Multi-Bit Screwdrivers/Nut Drivers

## Non-Ratcheting Magnetic Screwdriver with 32-Piece Tamperproof Bit Set

- Cushion-Grip handle for superior torque and comfort.
- Sturdy bit and screw holding magnet allows for screws to fit securely in place for easy use.
- Includes complete tamperproof bit set in block.



32510

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 32510    |              | .71           |

### Bits Included


TORX® – T7, T8, T10, T15, T20, T25, T27, T30 and T40  
 Fraction Hex – 3/32", 7/64", 1/8", 9/64", 5/32", and 3/16"  
 Metric Hex – 2 mm, 2.5 mm, 3 mm, 4 mm, and 5 mm  
 Spanner – 4, 6, 8, and 10  
 Tri-Wing® – 1, 2, 3 and 4  
 TORQ-SET® – 6, 8 and 10  
 1/4" square to 1/4" hex adapter to drive sockets

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.

## Magnetic Screwdriver Bit Sets

### 32-Piece Standard Tip Bit Set

- Durable PVC black block allows for easy storage of standard bits.
- Block slides over most screwdriver shafts for easy bit access and storage.
- Industrial strength, heat-treated steel bits for long lasting use.



32526

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 32526    |              | .425          |


### Bits Included

Hex – 5/64", 3/32", 7/64", 1/8", 9/64", 5/32" and 3/16"  
 Phillips – #0, #1, #2 (Qty. 3), and #3  
 Square Recess – #1, #2, and #3  
 TORX® – T6, T7, T8, T10, T15, T20 and T25  
 Slotted – 3-4, 5-6, 6-8, 8-10, 10-12, 12-14 screw sizes  
 Clutch – 5/32" and 3/16"  
 1/4" square to 1/4" hex adapter to drive sockets

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.

### 32-Piece Tamperproof Tip Bit Set

- Durable PVC gray block allows for easy storage of tamperproof bits.
- Block slides over most screwdriver shafts for easy bit access and storage.
- Industrial strength, heat-treated steel bits for long lasting use.



32525

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 32525    |              | .425          |

### Bits Included

TORX® – T7, T8, T10, T15, T20, T25, T27, T30 and T40  
 Fraction Hex – 3/32", 7/64", 1/8", 9/64", 5/32", and 3/16"  
 Metric Hex – 2 mm, 2.5 mm, 3 mm, 4 mm, and 5 mm  
 Spanner – 4, 6, 8, and 10  
 Tri-Wing® – 1, 2, 3 and 4  
 TORQ-SET® – 6, 8 and 10  
 1/4" square to 1/4" hex adapter to drive sockets

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.



## Features:

Handle size and shape provide greater contact area with hand for maximum turning power and a more comfortable grip.

**Patented, oil-resistant, anti-slip, plastic flock** on handle helps prevent slippage.



## Grip-It® Keystone-Tip Screwdrivers – Hex-Shanks

*Additional Feature:*

- Hex-shaped bolster and shaft for wrench-assisted turning

| Cat. No. | Tip Size       | Shank Length      | Overall Length     | Weight (lbs.) |
|----------|----------------|-------------------|--------------------|---------------|
| 19435    | 7/32" (5.5 mm) | 3-15/16" (100 mm) | 8-1/16" (205 mm)   | .20           |
| 19436    | 5/16" (8 mm)   | 5-7/8" (150 mm)   | 10-13/16" (275 mm) | .35           |



## Grip-It® Keystone-Tip Screwdrivers – Round-Shanks

*Additional Feature:*

- Hex-shaped bolster for wrench-assisted turning.

| Cat. No. | Tip Size       | Shank Length      | Overall Length     | Weight (lbs.) |
|----------|----------------|-------------------|--------------------|---------------|
| 19427    | 7/32" (5.5 mm) | 3-15/16" (100 mm) | 8-1/16" (205 mm)   | .15           |
| 19428    | 5/16" (8 mm)   | 5-7/8" (150 mm)   | 10-13/16" (275 mm) | .30           |



## Grip-It® Cabinet-Tip Screwdrivers – Round-Shanks

*Additional Feature:*

- Narrow cabinet-tip permits blade access where space is limited.

| Cat. No. | Tip Size       | Shank Length      | Overall Length    | Weight (lbs.) |
|----------|----------------|-------------------|-------------------|---------------|
| 19405    | 7/32" (5.5 mm) | 3-15/16" (100 mm) | 7-11/16" (195 mm) | .15           |



## Grip-It® Profilated Phillips-Tip Screwdrivers – Round-Shanks

*Additional Features:*

- Tips are precision machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Provides accurate fit and torque without slippage.

| Cat. No. | Tip Size | Shank Length      | Overall Length   | Weight (lbs.) |
|----------|----------|-------------------|------------------|---------------|
| 19445    | No. 1    | 3-1/8" (80 mm)    | 6-7/8" (175 mm)  | .10           |
| 19446    | No. 2    | 3-15/16" (100 mm) | 8-1/16" (205 mm) | .15           |



All dimensions are in inches and (millimeters).

**⚠ WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠ WARNING:** Always wear approved eye protection.

**⚠ WARNING:** Do NOT use to pry or chisel.



# Plastic-Handle Screwdriver Set

## Features:

Meets or exceeds applicable ASME / ANSI specifications.

Nickel-chrome, precision-forged and polished blades with black tips.

Tough amber plastic handle.

Smooth Comfordome® handles fit the palm of the hand comfortably.

Chrome-plated shank helps prevent corrosion.

Internal flanges provide solid, twist-resistant shaft anchor.



## 7-Piece Combination Screwdriver Set

Additional Features:

- Set contains two Phillips-tip screwdrivers, two slotted keystone-tip screwdrivers and three popular cabinet-tip screwdrivers.

| Cat. No. | Set Contains                     | Weight (lbs.) |
|----------|----------------------------------|---------------|
| 85276    |                                  | 1.10          |
| Cat. No. | Description                      | Shank Length  |
| BD111    | No. 1 Phillips-tip               | 3" (76 mm)    |
| BD122    | No. 2 Phillips-tip               | 4" (102 mm)   |
| BD284    | 1/4" square-shank, keystone-tip  | 4" (102 mm)   |
| BD306    | 5/16" square-shank, keystone-tip | 6" (152 mm)   |
| A216-3   | 1/8" round-shank, cabinet-tip    | 3" (76 mm)    |
| A216-4   | 1/8" round-shank, cabinet-tip    | 4" (102 mm)   |
| A216-6   | 1/8" round-shank, cabinet-tip    | 6" (152 mm)   |




85276

## Pocket-Clip Screwdrivers

Additional Features:

- Round-shank screwdrivers ranging from 3-1/4" (82 mm) to 6-7/16" (164 mm) long.
- Convenient pocket clip.
- Cat. No. A010 has keystone-tip, Cat. No. P12 has Phillips-tip, and all others have cabinet-tip.



A116-4

P12

| Cat. No.                                                      | Tip Size       | Shank Length   | Overall Length   | Weight(lbs.) |
|---------------------------------------------------------------|----------------|----------------|------------------|--------------|
| <b>Keystone-Tip and Cabinet-Tip, Pocket-Clip Screwdrivers</b> |                |                |                  |              |
| A010                                                          | 3/32" (2.4 mm) | 1-3/8" (35 mm) | 3-1/4" (82 mm)   | .03          |
| A130-2                                                        | 1/8" (3.2 mm)  | 2" (51 mm)     | 3-7/8" (98 mm)   | .05          |
| A130-3                                                        | 1/8" (3.2 mm)  | 3" (76 mm)     | 4-7/8" (124 mm)  | .04          |
| A116-2                                                        | 3/32" (2.4 mm) | 2" (51 mm)     | 4-7/16" (113 mm) | .05          |
| A116-3                                                        | 3/32" (2.4 mm) | 3" (76 mm)     | 5-7/16" (138 mm) | .03          |
| A116-4                                                        | 3/32" (2.4 mm) | 4" (102 mm)    | 6-7/16" (164 mm) | .03          |
| A131-2                                                        | 1/8" (3.2 mm)  | 2" (51 mm)     | 4-7/16" (113 mm) | .05          |

| Cat. No.                                                 | Tip Size | Shank Length   | Overall Length | Weight(lbs.) |
|----------------------------------------------------------|----------|----------------|----------------|--------------|
| <b>Phillips-Tip, Pocket-Clip Round-Shank Screwdriver</b> |          |                |                |              |
| P12                                                      | No. 0    | 2 1/2" (63 mm) | 5" (124 mm)    | .05          |

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.



# Plastic-Handle Screwdrivers

## Midget Screwdriver

Additional Features:

- Specially designed for delicate instrument work.
- Keystone-tip screwdriver.



A000

| Cat. No. | Tip Size     | Shank Length   | Overall Length | Weight (lbs.) |
|----------|--------------|----------------|----------------|---------------|
| A000     | 3/32" (2 mm) | 1-1/2" (38 mm) | 2-7/8" (73 mm) | .02           |

## Keystone-Tip Screwdrivers – Square-Shanks

Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.



BD306

| Cat. No. | Tip Size       | Shank Length | Overall Length    | Weight(lbs.) |
|----------|----------------|--------------|-------------------|--------------|
| BD284    | 1/4" (6.3 mm)  | 4" (102 mm)  | 8-1/2" (216 mm)   | .25          |
| BD286    | 1/4" (6.3 mm)  | 6" (152 mm)  | 10-1/2" (267 mm)  | .30          |
| BD306    | 5/16" (7.9 mm) | 6" (152 mm)  | 11-3/16" (284 mm) | .35          |
| BD308    | 5/16" (7.9 mm) | 8" (203 mm)  | 13-3/16" (335 mm) | .40          |

| Cat. No. | Tip Size       | Shank Length | Overall Length    | Weight(lbs.) |
|----------|----------------|--------------|-------------------|--------------|
| BD310    | 5/16" (7.9 mm) | 10" (254 mm) | 15-3/16" (385 mm) | .50          |
| BD410    | 3/8" (9.5 mm)  | 10" (254 mm) | 15-3/16" (385 mm) | .60          |
| BD412    | 3/8" (9.5 mm)  | 12" (305 mm) | 17-3/16" (437 mm) | .75          |
| C718     | 3/8" (9.5 mm)  | 18" (457 mm) | 23-5/16" (592 mm) | .95          |

## Keystone-Tip Screwdrivers – Round-Shanks

Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.



BD156

| Cat. No. | Tip Size       | Shank Length | Overall Length    | Weight(lbs.) |
|----------|----------------|--------------|-------------------|--------------|
| BD143    | 7/32" (5.6 mm) | 3" (76 mm)   | 7-1/2" (190 mm)   | .20          |
| BD144    | 1/4" (6.3 mm)  | 4" (102 mm)  | 8-1/2" (216 mm)   | .25          |
| BD146    | 1/4" (6.3 mm)  | 6" (152 mm)  | 10-1/2" (267 mm)  | .25          |
| BD156    | 5/16" (7.9 mm) | 6" (152 mm)  | 11-3/16" (284 mm) | .35          |

| Cat. No. | Tip Size       | Shank Length | Overall Length    | Weight(lbs.) |
|----------|----------------|--------------|-------------------|--------------|
| BD158    | 5/16" (7.9 mm) | 8" (203 mm)  | 13-3/16" (335 mm) | .40          |
| BD408    | 3/8" (9.5 mm)  | 8" (203 mm)  | 13-3/16" (335 mm) | .50          |
| BD510    | 3/8" (9.5 mm)  | 10" (254 mm) | 15-3/16" (386 mm) | .55          |
| 70155    | 1/4" (6.3 mm)  | 20" (508 mm) | 24-1/2" (622 mm)  | .45          |

## Cabinet-Tip Screwdrivers – Round-Shanks

Additional Features:

- Small-diameter shank for use in recessed holes or tight places.
- Well-suited for electrical and telecommunications work.



A216-6

| Cat. No. | Tip Size      | Shank Length | Overall Length | Weight(lbs.) |
|----------|---------------|--------------|----------------|--------------|
| A230-2   | 1/8" (3.2 mm) | 2" (51 mm)   | 5" (127 mm)    | .05          |
| A216-2   | 1/8" (3.2 mm) | 2" (51 mm)   | 5" (127 mm)    | .05          |
| A216-3   | 1/8" (3.2 mm) | 3" (76 mm)   | 6" (152 mm)    | .05          |
| A216-4   | 1/8" (3.2 mm) | 4" (102 mm)  | 7" (178 mm)    | .05          |
| A216-6   | 1/8" (3.2 mm) | 6" (152 mm)  | 9" (228 mm)    | .05          |
| A216-8   | 1/8" (3.2 mm) | 8" (203 mm)  | 11" (279 mm)   | .05          |

| Cat. No. | Tip Size       | Shank Length | Overall Length   | Weight(lbs.) |
|----------|----------------|--------------|------------------|--------------|
| A216-10  | 1/8" (3.2 mm)  | 10" (254 mm) | 13" (330 mm)     | .05          |
| A316-3   | 3/16" (4.8 mm) | 3" (76 mm)   | 6-5/8" (168 mm)  | .10          |
| A316-4   | 3/16" (4.8 mm) | 4" (102 mm)  | 7-5/8" (194 mm)  | .10          |
| A316-6   | 3/16" (4.8 mm) | 6" (152 mm)  | 9-5/8" (244 mm)  | .10          |
| A316-8   | 3/16" (4.8 mm) | 8" (203 mm)  | 11-5/8" (295 mm) | .15          |
| A316-10  | 3/16" (4.8 mm) | 10" (254 mm) | 13-5/8" (346 mm) | .20          |

## Profiliated Phillips-Tip Screwdrivers – Round-Shanks

Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.



BD122

| Cat. No. | Tip Size | Shank Length | Overall Length    | Weight(lbs.) |
|----------|----------|--------------|-------------------|--------------|
| BD111    | No. 1    | 3" (76 mm)   | 6-5/8" (168 mm)   | .10          |
| BD122    | No. 2    | 4" (102 mm)  | 8-1/2" (216 mm)   | .20          |
| BD133    | No. 3    | 6" (152 mm)  | 11-3/16" (284 mm) | .35          |
| P18      | No. 1    | 8" (203 mm)  | 11-1/2" (292 mm)  | .15          |

| Cat. No. | Tip Size | Shank Length | Overall Length   | Weight(lbs.) |
|----------|----------|--------------|------------------|--------------|
| P28      | No. 2    | 8" (203 mm)  | 11-5/8" (295 mm) | .20          |
| P212     | No. 2    | 12" (305 mm) | 15-5/8" (397 mm) | .25          |
| P202     | No. 2    | 20" (508 mm) | 24-1/2" (622 mm) | .55          |

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.

Screwdrivers, Nut Drivers & Accessories



# Specialty Plastic-Handle Screwdrivers

## Magnetic Screwdriver Set

- Each screwdriver has a powerful magnet built into its shank to hold interchangeable bits and also screws.
- Comfortable handle for easier driving.
- Interchangeable bits store inside handle for quick access.
- Wide selection of bits for different screw types.



| Cat. No. | Bits Included                                        | Shank Length with Bits | Overall Length  | Weight (lbs.) |
|----------|------------------------------------------------------|------------------------|-----------------|---------------|
| 70035    | 3/16" and 9/32" slotted and No. 1 and No. 2 Phillips | 3-3/4" (95 mm)         | 7-1/4" (184 mm) | .25           |

## Ratcheting Screwdriver Set

- Slotted and Phillips-tip set.
- Contains a unique 3-position ratcheting screwdriver plus an assortment of blade types and/or sizes.
- Comfortable handle with an easy-to-open snap top.
- Interchangeable bits store inside the handle for quick access.



| Cat. No. | Bits Included                                         | Shank Length with Bits | Overall Length  | Weight (lbs.) |
|----------|-------------------------------------------------------|------------------------|-----------------|---------------|
| 32473    | 3/16" and 9/32" slotted plus No. 1 and No. 2 Phillips | 4-1/4" (108 mm)        | 8-3/4" (222 mm) | .40           |

## Screwdriver Replacement Bits

- These precision-milled bits are 1" in length and are 1/4" hex.
- Fits replaceable-bit screwdrivers and other sockets that accept 1/4" hex bits.



| Cat. No. | Bit Type      | Tip Size | Weight (lbs.) |
|----------|---------------|----------|---------------|
| 4HS316   | slotted       | 3/16"    | .02           |
| 4HS932   | slotted       | 9/32"    | .02           |
| 4H1P2    | Phillips      | No. 2    | .02           |
| 4H1R1    | square-recess | No. 1    | .01           |
| 4H1R2    | square-recess | No. 2    | .01           |
| 4H1R3    | square-recess | No. 3    | .01           |
| 4HT15    | TORX®         | T15      | .02           |
| 4HT20    | TORX®         | T20      | .01           |
| 4HT25    | TORX®         | T25      | .02           |

| Cat. No. | Bit Type | Tip Size | Weight (lbs.) |
|----------|----------|----------|---------------|
| 4HT27    | TORX®    | T27      | .02           |
| 4HT30    | TORX®    | T30      | .02           |


| Cat. No.        | Weight (lbs.)                                               |
|-----------------|-------------------------------------------------------------|
| <b>Bit Sets</b> | <b>Bit Selection</b>                                        |
| 70036           | 3/16", 9/32" slotted plus No. 1 and No. 2 Phillips tips .05 |
| 70283           | No. 1, No. 2, No. 3 square-recess tips .05                  |
| 70432           | T15, T20, T25, T27, T30 TORX® tips .05                      |

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

## 4-in-1 Screwdriver

- Versatile screwdriver with interchangeable, snap-in blades.
- Tool supplied with four different tips on two reversible blades.

| Cat. No. | Description                             | Overall Length  | Weight (lbs.) |
|----------|-----------------------------------------|-----------------|---------------|
| 32460    | screwdriver with two dual-tipped blades | 7-5/8" (194 mm) | .370          |
| 32478    | #1 Phillips & 3/16" slotted             | -               | .036          |
| 32479    | #2 Phillips & 9/32" slotted             | -               | .044          |



## 3-Piece Slotted Screw-Holding Screwdriver Set

- Not designed for torquing or tightening.

| Cat. No.        | Set Contains                | Weight (lbs.) |
|-----------------|-----------------------------|---------------|
| SK234           |                             | .40           |
| <b>Cat. No.</b> | <b>Shank Size</b>           |               |
| K23             | 3/16" x 3" (5 mm x 76 mm)   |               |
| K34             | 1/4" x 4" (6.3 mm x 102 mm) |               |
| K46             | 5/16" x 6" (8 mm x 152 mm)  |               |



All dimensions are in inches and (millimeters).

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Always wear approved eye protection.

**WARNING:** Do NOT use to pry or chisel.



# Specialty Plastic-Handle Screwdrivers

## Slotted Screw-Holding Screwdrivers

- Split-blade screw-holding driver wedges into screw slot.
- Positive gripping action holds, starts, and drives slotted screws in awkward, hard-to-reach places.
- Not designed for torquing or tightening.

| Cat. No. | Tip Size       | Shank Length | Overall Length   | Weight (lbs.) |
|----------|----------------|--------------|------------------|---------------|
| K21†     | 1/16" (1.6 mm) | 3" (76 mm)   | 5-1/4" (133 mm)  | .05           |
| K23      | 3/16" (5 mm)   | 3" (76 mm)   | 5-1/4" (133 mm)  | .05           |
| K28      | 3/16" (5 mm)   | 8" (203 mm)  | 10-1/4" (260 mm) | .10           |
| K34‡     | 1/4" (6.3 mm)  | 4" (102 mm)  | 7-3/4" (197 mm)  | .10           |
| K36‡     | 1/4" (6.3 mm)  | 6" (152 mm)  | 9-3/4" (247 mm)  | .15           |

† Precision blade for use with small precision screws. Blade thickness of .028" expanding to .045".

‡ Blade thickness of .043" expanding to .085".

Note: K21 and K23 have pocket clips.



| Cat. No. | Tip Size      | Shank Length | Overall Length   | Weight (lbs.) |
|----------|---------------|--------------|------------------|---------------|
| K38‡     | 1/4" (6.3 mm) | 8" (203 mm)  | 11-3/4" (298 mm) | .20           |
| K44      | 5/16" (8 mm)  | 4" (102 mm)  | 8-1/4" (209 mm)  | .25           |
| K46      | 5/16" (8 mm)  | 6" (152 mm)  | 10-1/4" (260 mm) | .25           |
| K48      | 5/16" (8 mm)  | 8" (203 mm)  | 12-1/4" (311 mm) | .30           |

## Screw-Holding Screwdrivers

### Phillips-Tip Screw-Holding Screwdrivers

- Blade separates to hold the fastener.
- Not designed for torquing or tightening.
- Positive gripping action holds and starts Phillips screws in awkward, hard-to-reach places.

| Cat. No. | Overall Length               | Weight (lbs.) |
|----------|------------------------------|---------------|
| K14      | 5" (127 mm) with pocket clip | .05           |
| K16      | 7" (178 mm)                  | .05           |
| K19      | 9" (229 mm)                  | .05           |




## Offset Screwdrivers

### Slotted-Tip Offset Screwdrivers

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

| Cat. No. | For Screw Nos. | Overall Length  | Tip Width     | Weight (lbs.) |
|----------|----------------|-----------------|---------------|---------------|
| V01      | 2 to 6         | 3" (76 mm)      | 3/16" (5 mm)  | .01           |
| V02      | 6 to 10        | 4-1/4" (108 mm) | 1/4" (6.3 mm) | .05           |
| V03      | 8 to 12        | 5" (127 mm)     | 5/16" (8 mm)  | .11           |
| V04      | 12 to 16       | 6" (152 mm)     | 3/8" (9.5 mm) | .25           |



### Phillips-Tip Offset Screwdrivers

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

| Cat. No. | Point Nos.      | Overall Length  | Weight (lbs.) |
|----------|-----------------|-----------------|---------------|
| P120     | No. 1 and No. 2 | 4-3/4" (121 mm) | .05           |
| P340     | No. 3 and No. 4 | 6" (152 mm)     | .20           |



### Combination-Tip Offset Screwdriver

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

| Cat. No. | For Screw Nos.                 | Overall Length | Tip Width     | Weight (lbs.) |
|----------|--------------------------------|----------------|---------------|---------------|
| V05      | 1/4" slotted<br>No. 2 Phillips | 5" (127 mm)    | 1/4" (6.3 mm) | .05           |



All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.




## Offset Screwdrivers

### 2-Piece Offset Screwdriver Set

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.


| Cat. No. | Set Contains                                                            | Weight (lbs.) |
|----------|-------------------------------------------------------------------------|---------------|
| 210122   | P120 (No. 1 and No. 2 Phillips-tip) and V02 (1/4" to 5/16" slotted tip) | .10           |



## Specialty Driver Set

### Reversible Impact-Driver Set

- Rugged, hand-impact driver turns rusted, frozen, or other stubborn screws.
- Can also be used with 3/8" square-drive impact sockets.
- Internal, spring-loaded, helical design transforms the impact of a hammer blow to up to 200 ft.-lbs. of shock torque.
- Easily reverses for tightening or loosening screws.
- Constructed of high-grade alloy steel that has been heat-treated for added strength.
- Reclosable, seal-tight vinyl pouch with hang-up grommet.



| Cat. No.                            | Description                                                                                                                                                                             | Weight (lbs.) |
|-------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| 70220                               | pouched impact-driver set with 3/8"-square-drive fitting adapter for 5/16" hex bits, 4 assorted hex screwdriver bits (5/16" and 1/2" regular slotted tip, No. 2 and No. 4 Phillips-tip) | 2.15          |
| <b>Replacement Screwdriver Bits</b> |                                                                                                                                                                                         |               |
| 70229                               | replacement set of 5/16"-drive screwdriver bits (5/16" and 1/2" regular slotted tip, No. 2 and No. 4 Phillips-tip) packed in reclosable, seal-tight vinyl pouch                         | .25           |

## Torque Screwdrivers

### Torque-Screwdriver Set

- Compact, easy to use set.
- Form-fitted storage box to keep set organized.

| Cat. No. | Contains                                                                                          | Weight (lbs.) |
|----------|---------------------------------------------------------------------------------------------------|---------------|
| 57034    | torque screwdriver Cat. No. 57035, 8-piece bit set Cat. No. 57036, rugged form-fitted storage box | 1.0           |



### Torque Screwdriver

- Adjustable, torque-limiting screwdriver with calibrated micrometer scale.
- Torqued to micrometer accuracy. Accurate to  $\pm 6^\circ$  plus 1/2 graduation.
- Graduated in 2 in.-lbs. (.2 NM) increments.
- Torques either clockwise or counter-clockwise.
- Can be preset and sealed for production use.
- Meets MIL-H26497 specifications.
- Easy-release bit holder. Bits are held securely during operation, yet are easily removed when released.
- Aluminum outside construction for light weight and non-magnetic characteristics.
- Non-slip grip.
- Bits not included.



| Cat. No. | Range        | Drive Size  | Overall Length | Weight (lbs.) |
|----------|--------------|-------------|----------------|---------------|
| 57035    | 2-36 in.-lb. | 1/4" female | 8" (203 mm)    | .50           |

### 8-Piece Torque-Screwdriver Bits Set

- Set of eight bits for Cat. No. 57035 torque screwdriver.

| Cat. No. | Contains                                                                                                                                                                             | Weight (lbs.) |
|----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| 57036    | Phillips No. 1 and No. 2; slotted No. 4 (3/16" x .034"), No. 5 (7/32" x .036"), No. 6 (1/4" x .038"), No. 10 (5/16" x .046"), No. 12 (3/8" x .050"); 1/4" hex-to-square male adapter | .50           |



All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** Never use on or near live electrical circuits.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

**WARNING:** Do NOT use to pry or chisel.



# Cushion-Grip Nut Driver Sets

## Features:



**Patented Tip-Ident®**  
quickly identifies nut  
driver and size.

**Internal flanges** provide solid,  
twist-resistant shaft anchor.

**Full hollow shafts** facilitate work  
on stacked circuit boards or other  
long bolt applications.

**Premium chrome-plated  
shaft** for smooth feel and  
corrosion resistance.

Handle end is also color  
coded for easy identification.

**Cushion-Grip handle**  
allows for greater  
torque and comfort.

**Meets or exceeds** applicable  
ASME / ANSI specifications.



## 7-Piece Cushion-Grip Nut Driver Set – 3" Shafts

- Set contains 630-3/16, 630-1/4, 630-5/16, 630-11/32, 630-3/8, 630-7/16, and 630-1/2. (See individual tool listings for more details.)

| Cat. No. | Weight (lbs.) |
|----------|---------------|
| 631      | 1.50          |



## 7-Piece Hollow-Shaft\* Magnetic Tip Cushion-Grip Nut Driver Set – 3" Shafts

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Set contains 630-3/16M, 630-1/4M, 630-5/16M, 630-11/32M, 630-3/8M, 630-7/16M, and 630-1/2M. (See individual tool listings for more details.)

| Cat. No. | Weight (lbs.) |
|----------|---------------|
| 631M     | 1.50          |

\*3/16" magnetic nut driver does not have hollow shaft



631M

## 7-Piece Cushion-Grip Nut Driver Set – 6" Shafts

- Set contains 646-3/16, 646-1/4, 646-5/16, 646-11/32, 646-3/8, 646-7/16, and 646-1/2. (See individual tool listings for more details.)

| Cat. No. | Weight (lbs.) |
|----------|---------------|
| 647      | 1.55          |




## 7-Piece Hollow-Shaft\* Magnetic Tip Cushion-Grip Nut Driver Set – 6" Shafts

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Set contains 646-3/16M, 646-1/4M, 646-5/16M, 646-11/32M, 646-3/8M, 646-7/16M, 646-1/2M. (See individual tool listings for more details.)

| Cat. No. | Weight (lbs.) |
|----------|---------------|
| 647M     | 1.55          |

\*3/16" magnetic nut driver does not have hollow shaft



647M

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.



# Cushion-Grip Nut Driver Sets

## 4-Piece Cushion-Grip Nut Driver Set

Additional Features:

- Set contains: 630-1/4, 630-5/16, 630-3/8, 630-9/16.  
(See individual tool listings for more details.)

NEW!

| Cat. No. | Set Contains |                 |              |                 |                                                                                   | Weight (lbs.) |
|----------|--------------|-----------------|--------------|-----------------|-----------------------------------------------------------------------------------|---------------|
| 633      |              |                 |              |                 |                                                                                   | 1.30          |
| Cat. No. | Color Code   | Hex Size Metric | Shaft Length | Overall Length  |  |               |
| 630-1/4  | red          | 1/4"            | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                   |               |
| 630-5/16 | yellow       | 5/16"           | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                   |               |
| 630-3/8  | blue         | 3/8"            | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                   |               |
| 630-9/16 | orange       | 9/16"           | 4" (102 mm)  | 9-3/8" (238 mm) |                                                                                   |               |



633

## 2-Piece Cushion-Grip Stubby Nut Driver Set – 1-1/2" Shafts

- Stubby nut drivers allow for work in close quarters.
- Set contains: 610-1/4, 610-5/16.  
(See individual tool listings for more details.)



610

| Cat. No. | Weight (lbs.) |
|----------|---------------|
| 610      | .20           |

## 2-Piece Hollow-Shaft Magnetic Tip Cushion-Grip Stubby Nut Driver Set – 1-1/2" Shafts

Additional Features:

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Stubby nut drivers allow for work in close quarters.
- Set contains: 610-1/4M, 610-5/16M.  
(See individual tool listings for more details.)



| Cat. No. | Weight (lbs.) |
|----------|---------------|
| 610M     | .20           |

## 2-Piece Magnetic Tip Cushion-Grip Nut Driver Sets

Additional Features:

- General purpose selection of the most frequently used nut drivers.  
(See individual tool listings for more details.)

| Cat. No. | Set Contains        | Weight (lbs.) |
|----------|---------------------|---------------|
| 630M     | 630-1/4M, 630-5/16M | .40           |
| 646M     | 646-1/4M, 646-5/16M | .50           |



630M

## 7-Piece Metric Cushion-Grip Nut Driver Set – 3" Shafts

Additional Features:

- Standard length for most applications.
- Fits over long bolts and studs.

| Cat. No.  | Set Contains |                 |              |                 |                                                                                     | Weight (lbs.) |
|-----------|--------------|-----------------|--------------|-----------------|-------------------------------------------------------------------------------------|---------------|
| 65160     |              |                 |              |                 |                                                                                     | 1.50          |
| Cat. No.  | Color Code   | Hex Size Metric | Shaft Length | Overall Length  |  |               |
| 630-5mm   | black        | 5 mm            | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                     |               |
| 630-5.5mm | brown        | 5.5 mm          | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                     |               |
| 630-6mm   | red          | 6 mm            | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                     |               |
| 630-7mm   | orange       | 7 mm            | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                     |               |
| 630-8mm   | yellow       | 8 mm            | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                     |               |
| 630-9mm   | green        | 9 mm            | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                     |               |
| 630-10mm  | blue         | 10 mm           | 3" (76 mm)   | 6-3/4" (171 mm) |                                                                                     |               |



65160

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.



## Cushion-Grip Stubby Nut Drivers – 1-1/2" Shafts

Additional Features:

- Full hollow shaft for long bolts or studs.
- Stubby nut drivers allow for work in close quarters.
- Meets or exceeds applicable ASME / ANSI specifications.



610-5/16

| Cat. No. | Color Code | Hex Size | Shaft Length   | Overall Length | Weight (lbs.) |
|----------|------------|----------|----------------|----------------|---------------|
| 610-1/4  | red        | 1/4"     | 1-1/2" (38 mm) | 3-1/2" (89 mm) | .10           |
| 610-5/16 | yellow     | 5/16"    | 1-1/2" (38 mm) | 3-1/2" (89 mm) | .10           |

## Cushion-Grip Hollow-Shaft Nut Drivers – 3" Shafts



630-1/2

Additional Features:

- Standard length for most applications.
- Fits over long bolts and studs.

| Cat. No.  | Color Code | Hex Size | Shaft Length | Overall Length   | Weight (lbs.) |
|-----------|------------|----------|--------------|------------------|---------------|
| 630-3/16  | black      | 3/16"    | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-1/4   | red        | 1/4"     | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-5/16  | yellow     | 5/16"    | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-11/32 | green      | 11/32"   | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-3/8   | blue       | 3/8"     | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-7/16  | brown      | 7/16"    | 3" (76 mm)   | 7-5/16" (186 mm) | .25           |
| 630-1/2   | red        | 1/2"     | 3" (76 mm)   | 7-5/16" (186 mm) | .25           |
| 630-9/16  | orange     | 9/16"    | 4" (102 mm)  | 9-3/8" (238 mm)  | .35           |
| 630-5/8   | yellow     | 5/8"     | 4" (102 mm)  | 9-3/8" (238 mm)  | .35           |

Refer to the insulated section for insulated nut drivers.

## Metric Cushion-Grip Hollow-Shaft Nut Drivers – 3" Shafts



630-11mm

Additional Features:

- Standard length for most applications.
- Fits over long bolts and studs.

| Cat. No.  | Color Code | Hex Size Metric | Shaft Length | Overall Length   | Weight (lbs.) |
|-----------|------------|-----------------|--------------|------------------|---------------|
| 630-4mm   | red        | 4 mm            | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-4.5mm | yellow     | 4.5 mm          | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-5mm   | black      | 5 mm            | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-6mm   | red        | 6 mm            | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-7mm   | orange     | 7 mm            | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-8mm   | yellow     | 8 mm            | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-10mm  | blue       | 10 mm           | 3" (76 mm)   | 6-3/4" (171 mm)  | .20           |
| 630-11mm  | brown      | 11 mm           | 3" (76 mm)   | 7-5/16" (186 mm) | .20           |

## Cushion-Grip Hollow-Shaft Nut Drivers – 6" Shafts

Additional Features:

- Reaches into deep recesses.
- Fits over extra-long bolts and studs.



646-1/2

| Cat. No.  | Color Code | Hex Size | Shaft Length | Overall Length  | Weight (lbs.) |
|-----------|------------|----------|--------------|-----------------|---------------|
| 646-3/16  | black      | 3/16"    | 6" (152 mm)  | 9-3/4" (248 mm) | .25           |
| 646-1/4   | red        | 1/4"     | 6" (152 mm)  | 9-3/4" (248 mm) | .25           |
| 646-5/16  | yellow     | 5/16"    | 6" (152 mm)  | 9-3/4" (248 mm) | .25           |
| 646-11/32 | green      | 11/32"   | 6" (152 mm)  | 9-3/4" (248 mm) | .25           |
| 646-3/8   | blue       | 3/8"     | 6" (152 mm)  | 9-3/4" (248 mm) | .30           |

| Cat. No. | Color Code | Hex Size | Shaft Length | Overall Length    | Weight (lbs.) |
|----------|------------|----------|--------------|-------------------|---------------|
| 646-7/16 | brown      | 7/16"    | 6" (152 mm)  | 10-5/16" (262 mm) | .35           |
| 646-1/2  | red        | 1/2"     | 6" (152 mm)  | 10-5/16" (262 mm) | .35           |
| 646-9/16 | orange     | 9/16"    | 6" (152 mm)  | 11-3/8" (289 mm)  | .40           |
| 646-5/8  | yellow     | 5/8"     | 6" (152 mm)  | 11-3/8" (289 mm)  | .40           |

All dimensions are in inches and (millimeters).

**⚠WARNING:** Always wear approved eye protection.

**⚠WARNING:** NOT insulated. Will NOT protect against electrical shock.



# Cushion-Grip Nut Drivers

## Magnetic Tip Nut Drivers – Hollow Shafts\*

Additional Feature:

- Exclusive hollow shaft\* design with Rare Earth magnetic tip features unobstructed pass-through, even on long bolts.



630-3/8M



| Cat. No.   | Color Code | Hex Size | Shaft Length   | Overall Length   | Weight (lbs.) |
|------------|------------|----------|----------------|------------------|---------------|
| 610-1/4M   | 1/4"       | red      | 1-1/2" (38 mm) | 1-1/2" (89 mm)   | .10           |
| 610-5/16M  | 5/16"      | yellow   | 1-1/2" (38 mm) | 1-1/2" (89 mm)   | .10           |
| 610-3/8M   | 3/8"       | blue     | 1-1/2" (38 mm) | 1-1/2" (89 mm)   | .10           |
| 630-3/16M* | 3/16"      | black    | 3" (76 mm)     | 6-3/4" (171 mm)  | .20           |
| 630-1/4M   | 1/4"       | red      | 3" (76 mm)     | 6-3/4" (171 mm)  | .20           |
| 630-5/16M  | 5/16"      | yellow   | 3" (76 mm)     | 6-3/4" (171 mm)  | .20           |
| 630-11/32M | 11/32"     | green    | 3" (76 mm)     | 6-3/4" (171 mm)  | .20           |
| 630-3/8M   | 3/8"       | blue     | 3" (76 mm)     | 6-3/4" (171 mm)  | .20           |
| 630-7/16M  | 7/16"      | brown    | 3" (76 mm)     | 7-5/16" (186 mm) | .25           |
| 630-1/2M   | 1/2"       | red      | 3" (76 mm)     | 7-5/16" (186 mm) | .25           |

| Cat. No.   | Color Code | Hex Size | Shaft Length | Overall Length    | Weight (lbs.) |
|------------|------------|----------|--------------|-------------------|---------------|
| 646-3/16M* | 3/16"      | black    | 6" (152 mm)  | 9-3/4" (248 mm)   | .25           |
| 646-1/4M   | 1/4"       | red      | 6" (152 mm)  | 9-3/4" (248 mm)   | .25           |
| 646-5/16M  | 5/16"      | yellow   | 6" (152 mm)  | 9-3/4" (248 mm)   | .25           |
| 646-11/32M | 11/32"     | green    | 6" (152 mm)  | 9-3/4" (248 mm)   | .25           |
| 646-3/8M   | 3/8"       | blue     | 6" (152 mm)  | 9-3/4" (248 mm)   | .30           |
| 646-7/16M  | 7/16"      | brown    | 6" (152 mm)  | 10-5/16" (262 mm) | .35           |
| 646-1/2M   | 1/2"       | red      | 6" (152 mm)  | 10-5/16" (262 mm) | .35           |
| 618-1/4M   | 1/4"       | red      | 18" (457 mm) | 21-3/4" (552 mm)  | .50           |
| 618-5/16M  | 5/16"      | yellow   | 18" (457 mm) | 21-3/4" (552 mm)  | .50           |

\*3/16" magnetic nut driver does not have a hollow shaft.

## Drive-A-Matic Cushion-Grip Nut Driver



632

Additional Features:

- Automatically fits 15 different nut and screw sizes.
- Hex head adjusts to the proper size as you turn it.
- Will drive or loosen hex nuts from 1/4" (6.4 mm) to 7/16" (11.1 mm), hex-head screws from No. 6 to 1/4" (6.4 mm), and socket-head cap screws from No. 8 to 5/16" (7.9 mm).

| Cat. No. | Overall Length                                     | Weight (lbs.) |
|----------|----------------------------------------------------|---------------|
| 632      | 7" (178 mm) when open, 6-3/4" (171 mm) when closed | .35           |

## Coated Hollow-Shaft Nut Drivers



640-1/2

Additional Features:

- Entire shaft plastic coated for circuit protection only. NOT INSULATED.
- Special plastic coating resists cutting, cracking and chipping.
- Thin coating permits use in confined areas.

| Cat. No. | Color Code | Hex Size | Shaft Length | Overall Length   | Weight (lbs.) |
|----------|------------|----------|--------------|------------------|---------------|
| 640-3/16 | black      | 3/16"    | 3" (76 mm)   | 6-3/4" (171 mm)  | .25           |
| 640-1/4  | red        | 1/4"     | 3" (76 mm)   | 6-3/4" (171 mm)  | .25           |
| 640-5/16 | yellow     | 5/16"    | 3" (76 mm)   | 6-3/4" (171 mm)  | .25           |
| 640-3/8  | blue       | 3/8"     | 3" (76 mm)   | 6-3/4" (171 mm)  | .25           |
| 640-7/16 | brown      | 7/16"    | 3" (76 mm)   | 7-5/16" (186 mm) | .30           |
| 640-1/2  | red        | 1/2"     | 3" (76 mm)   | 7-5/16" (186 mm) | .25           |
| 640-9/16 | orange     | 9/16"    | 4" (102 mm)  | 9-3/8" (238 mm)  | .40           |
| 640-5/8  | yellow     | 5/8"     | 4" (102 mm)  | 9-3/8" (238 mm)  | .40           |

**⚠ WARNING:** NOT insulated. Coating is intended for protection of circuits only.



All dimensions are in inches and (millimeters).

**⚠ WARNING:** Always wear approved eye protection.

**⚠ WARNING:** NOT insulated. Will NOT protect against electrical shock.



# Plastic-Handle, Hollow-Shaft Nut Driver Sets

## Features:

**Meets or exceeds** applicable ASME / ANSI specifications.

**Smooth Comfordome® handles** fit the palm of the hand comfortably.

**Chrome-plated shaft** helps prevent corrosion.

**Hollow shafts** facilitate work on stacked circuit boards or other long bolt applications.

**Internal flanges** provide solid, twist-resistant shaft anchor.

**Handles are color-coded** for easy identification.




## 4-Piece Nut Driver Set – 3" Shafts

*Additional Feature:*

- *Standard length works for most applications.*

| Cat. No. | Set Contains |          |              |                 |  | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|--|---------------|
| 70084    |              |          |              |                 |  | .60           |
| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  |  |               |
| S8       | red          | 1/4"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S10      | amber        | 5/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S11      | green        | 11/32"   | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S12      | blue         | 3/8"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |



## 5-Piece Nut Driver Set – 3" Shafts

*Additional Features:*

- *Standard length works for most applications.*
- *Comes in a hang-up box.*

| Cat. No. | Set Contains |          |              |                 |  | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|--|---------------|
| 89969    |              |          |              |                 |  | .70           |
| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  |  |               |
| S6       | black        | 3/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S8       | red          | 1/4"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S10      | amber        | 5/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S11      | green        | 11/32"   | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S12      | blue         | 3/8"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |



All dimensions are in inches and (millimeters).

**⚠WARNING:** Always wear approved eye protection.

**⚠WARNING:** NOT insulated. Will NOT protect against electrical shock.



# Plastic-Handle, Hollow Shaft Nut Driver Sets

## 7-Piece Nut Driver Set – 3" Shafts

Additional Feature:

- Set contains seven hollow-shaft nut drivers in the most popular hex sizes.

| Cat. No. | Set Contains |          |              |                 |  | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|--|---------------|
| 89004    |              |          |              |                 |  | 1.10          |
| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  |  |               |
| S6       | black        | 3/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S8       | red          | 1/4"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S10      | amber        | 5/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S11      | green        | 11/32"   | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S12      | blue         | 3/8"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S14      | brown        | 7/16"    | 3" (76 mm)   | 7" (178 mm)     |  |               |
| S16      | red          | 1/2"     | 3" (76 mm)   | 7" (178 mm)     |  |               |



89004

## 7-Piece Nut Driver Set – 3" Shafts

Additional Features:

- Set contains seven hollow-shaft nut drivers in the most popular hex sizes.
- Convenient vinyl pouch hangs up or rolls up.

| Cat. No. | Set Contains |          |              |                 |  | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|--|---------------|
| K7       |              |          |              |                 |  | 1.15          |
| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  |  |               |
| S6       | black        | 3/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S8       | red          | 1/4"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S10      | amber        | 5/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S11      | green        | 11/32"   | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S12      | blue         | 3/8"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S14      | brown        | 7/16"    | 3" (76 mm)   | 7" (178 mm)     |  |               |
| S16      | red          | 1/2"     | 3" (76 mm)   | 7" (178 mm)     |  |               |



K7

## 7-Piece Nut Driver Set With Metal Stand – 3" Shafts

Additional Features:

- Set contains seven hollow-shaft nut drivers in the most popular hex sizes.
- Metal holder stands freely or hangs on wall.

| Cat. No. | Set Contains |          |              |                 |  | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|--|---------------|
| S700     |              |          |              |                 |  | 1.60          |
| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  |  |               |
| S6       | black        | 3/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S8       | red          | 1/4"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S10      | amber        | 5/16"    | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S11      | green        | 11/32"   | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S12      | blue         | 3/8"     | 3" (76 mm)   | 6-5/8" (168 mm) |  |               |
| S14      | brown        | 7/16"    | 3" (76 mm)   | 7" (178 mm)     |  |               |
| S16      | red          | 1/2"     | 3" (76 mm)   | 7" (178 mm)     |  |               |



S700

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.



# Plastic-Handle, Hollow Shaft Nut Driver Sets

## 10-Piece Metric Nut Driver Set With Stand – 3" Shafts

Additional Features:

- White enameled metal stand holds all ten 3"-shaft metric nut drivers.
- Identification label makes individual size selection easy.

| Cat. No. | Set Contains |          |              |                 | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|---------------|
| 70200    |              |          |              |                 | 1.85          |
| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  |               |
| 70204    | black        | 4 mm     | 3" (76 mm)   | 6-5/8" (168 mm) |               |
| 70245    | black        | 4.5 mm   | 3" (76 mm)   | 6-5/8" (168 mm) |               |
| 70205    | black        | 5 mm     | 3" (76 mm)   | 6-5/8" (168 mm) |               |
| 70255    | black        | 5.5 mm   | 3" (76 mm)   | 6-5/8" (168 mm) |               |
| 70206    | black        | 6 mm     | 3" (76 mm)   | 6-5/8" (168 mm) |               |
| 70207    | black        | 7 mm     | 3" (76 mm)   | 6-5/8" (168 mm) |               |
| 70208    | black        | 8 mm     | 3" (76 mm)   | 6-5/8" (168 mm) |               |
| 70209    | black        | 9 mm     | 3" (76 mm)   | 6-5/8" (168 mm) |               |
| 70210    | black        | 10 mm    | 3" (76 mm)   | 7" (178 mm)     |               |
| 70211    | black        | 11 mm    | 3" (76 mm)   | 7" (178 mm)     |               |



70200



## 7-Piece Nut-Driver Set – 6" Shafts

Additional Feature:

- Contains seven 6"-shaft nut drivers that reach into deep recesses.

| Cat. No. | Set Contains |          |              |                 | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|---------------|
| 89904    |              |          |              |                 | 1.15          |
| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  |               |
| S66      | black        | 3/16"    | 6" (152 mm)  | 9-5/8" (244 mm) |               |
| S86      | red          | 1/4"     | 6" (152 mm)  | 9-5/8" (244 mm) |               |
| S106     | amber        | 5/16"    | 6" (152 mm)  | 9-5/8" (244 mm) |               |
| S116     | green        | 11/32"   | 6" (152 mm)  | 9-5/8" (244 mm) |               |
| S126     | blue         | 3/8"     | 6" (152 mm)  | 9-5/8" (244 mm) |               |
| S146     | brown        | 7/16"    | 6" (152 mm)  | 10" (254 mm)    |               |
| S166     | red          | 1/2"     | 6" (152 mm)  | 10" (254 mm)    |               |



89904



# Plastic-Handle, Hollow Shaft Nut Drivers

## Stubby Nut Drivers – 1-1/2" Shafts

Additional Feature:

- Stubby nut drivers allow for work in close quarters.

| Cat. No. | Handle Color | Hex Size | Shaft Length   | Overall Length | Weight (lbs.) |
|----------|--------------|----------|----------------|----------------|---------------|
| SS8      | red          | 1/4"     | 1-1/2" (38 mm) | 3-3/4" (95 mm) | .15           |
| SS10     | amber        | 5/16"    | 1-1/2" (38 mm) | 3-3/4" (95 mm) | .15           |
| SS12     | blue         | 3/8"     | 1-1/2" (38 mm) | 3-3/4" (95 mm) | .15           |



SS10



All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

Screwdrivers, Nut Drivers  
& Accessories



# Plastic-Handle Nut Drivers

## Hollow-Shaft Nut Drivers – 3" & 4" Shafts



Additional Features:

- Standard length works for most applications.
- Fits over long bolts and studs.

S10

| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|---------------|
| S5       | amber        | 5/32"    | 3" (76 mm)   | 6-1/2" (165 mm) | .10           |
| S6       | black        | 3/16"    | 3" (76 mm)   | 6-5/8" (168 mm) | .10           |
| S7       | brown        | 7/32"    | 3" (76 mm)   | 6-5/8" (168 mm) | .10           |
| S8       | red          | 1/4"     | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| S9       | orange       | 9/32"    | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| S10      | amber        | 5/16"    | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| S11      | green        | 11/32"   | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| S12      | blue         | 3/8"     | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| S14      | brown        | 7/16"    | 3" (76 mm)   | 7" (178 mm)     | .20           |
| S16      | red          | 1/2"     | 3" (76 mm)   | 7" (178 mm)     | .20           |
| S18      | red          | 9/16"    | 4" (102 mm)  | 8-1/2" (216 mm) | .30           |
| S20      | red          | 5/8"     | 4" (102 mm)  | 8-1/2" (216 mm) | .30           |

## Metric Nut Drivers – 3" Shafts



Additional Features:

- Standard length works for most applications.
- Fits over long bolts and studs.

70209

| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|---------------|
| 70204    | black        | 4 mm     | 3" (76 mm)   | 6-5/8" (168 mm) | .10           |
| 70245    | black        | 4.5 mm   | 3" (76 mm)   | 6-5/8" (168 mm) | .10           |
| 70205    | black        | 5 mm     | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| 70255    | black        | 5.5 mm   | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| 70206    | black        | 6 mm     | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| 70207    | black        | 7 mm     | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| 70208    | black        | 8 mm     | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| 70209    | black        | 9 mm     | 3" (76 mm)   | 6-5/8" (168 mm) | .15           |
| 70210    | black        | 10 mm    | 3" (76 mm)   | 7" (178 mm)     | .15           |
| 70211    | black        | 11 mm    | 3" (76 mm)   | 7" (178 mm)     | .20           |

## Nut Drivers – 6" Shafts




Additional Features:

- Reaches into deep recesses.
- Fits over extra-long bolts and studs.

S86

| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length  | Weight (lbs.) |
|----------|--------------|----------|--------------|-----------------|---------------|
| S66      | black        | 3/16"    | 6" (152 mm)  | 9-5/8" (244 mm) | .15           |
| S86      | red          | 1/4"     | 6" (152 mm)  | 9-5/8" (244 mm) | .15           |
| S106     | amber        | 5/16"    | 6" (152 mm)  | 9-5/8" (244 mm) | .15           |
| S116     | green        | 11/32"   | 6" (152 mm)  | 9-5/8" (244 mm) | .15           |
| S126     | blue         | 3/8"     | 6" (152 mm)  | 9-5/8" (244 mm) | .15           |
| S146     | brown        | 7/16"    | 6" (152 mm)  | 10" (254 mm)    | .20           |

## Magnetic Nut Drivers – Solid Shafts



Additional Feature:

- Powerful nut-holding magnet built into solid shaft.

S106M

| Cat. No. | Handle Color | Hex Size | Shaft Length | Overall Length   | Weight (lbs.) |
|----------|--------------|----------|--------------|------------------|---------------|
| S8M      | red          | 1/4"     | 3" (76 mm)   | 6-5/8" (168 mm)  | .15           |
| S10M     | amber        | 5/16"    | 3" (76 mm)   | 6-5/8" (168 mm)  | .15           |
| S86M     | red          | 1/4"     | 6" (152 mm)  | 9-5/8" (244 mm)  | .15           |
| S106M    | amber        | 5/16"    | 6" (152 mm)  | 9-5/8" (244 mm)  | .15           |
| S126M    | blue         | 3/8"     | 6" (152 mm)  | 9-5/8" (244 mm)  | .15           |
| S818M    | red          | 1/4"     | 18" (457 mm) | 21-5/8" (549 mm) | .25           |
| S1018M   | amber        | 5/16"    | 18" (457 mm) | 21-5/8" (549 mm) | .25           |

## Super-Long Nut Drivers – 18" Shafts



Additional Features:

- Heavy-duty, long-reach nut drivers.
- Ideal for reaching into walls and other hard-to-reach places where added length is necessary.
- Available in magnetic and non-magnetic tip.

S1018

| Cat. No. | Handle Color | Hex Size       | Shaft Length | Type     | Overall Length   | Weight (lbs.) |
|----------|--------------|----------------|--------------|----------|------------------|---------------|
| S818     | red          | 1/4" (6.3 mm)  | 18" (457 mm) | standard | 21-5/8" (549 mm) | .25           |
| S818M    | red          | 1/4" (6.3 mm)  | 18" (457 mm) | magnetic | 21-5/8" (549 mm) | .25           |
| S1018    | amber        | 5/16" (7.9 mm) | 18" (457 mm) | standard | 21-5/8" (549 mm) | .25           |
| S1018M   | amber        | 5/16" (7.9 mm) | 18" (457 mm) | magnetic | 21-5/8" (549 mm) | .25           |

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.



## Cushion-Grip Triple Taps and Six-in-One Tap Tool

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.

| Cat. No. | Tap Sizes                                          | Overall Length | Weight (lbs.) |
|----------|----------------------------------------------------|----------------|---------------|
| 623-20   | Triple Tap 10-24, 12-24, 1/4-20                    | 7-3/4"         | .25           |
| 623-24   | Triple Tap 6-32, 8-32, 10-24                       | 7-3/4"         | .25           |
| 623-32   | Triple Tap 6-32, 8-32, 10-32                       | 7-3/4"         | .25           |
| 626      | 6-in-1 Tap 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20 | 7-3/4"         | .25           |



626

| Replacement Taps |                      |                             |
|------------------|----------------------|-----------------------------|
| 628-20           | 10-24, 12-24, 1/4-20 | replacement for 623-20, 626 |
| 626-24           | 6-32, 8-32, 10-24    | replacement for 623-24      |
| 626-32           | 6-32, 8-32, 10-32    | replacement for 623-32, 626 |

## Six-in-One Tapping Tool




627-20

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.
- Two high-carbon steel taps are secured in reversible holder.

| Cat. No. | Tap Sizes                               | Overall Length  | Weight (lbs.) |
|----------|-----------------------------------------|-----------------|---------------|
| 627-20   | 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20 | 7-5/8" (194 mm) | 0.35          |

| Replacement Taps |                      |
|------------------|----------------------|
| 626-32           | 10-32, 8-32, 6-32    |
| 628-20           | 10-24, 12-24, 1/4-20 |

## Triple Taps



625-24

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.

| Cat. No. | Tap Sizes         | Color Code | Overall Length  | Weight (lbs.) |
|----------|-------------------|------------|-----------------|---------------|
| 625-24   | 6-32, 8-32, 10-24 | blue       | 7-1/8" (181 mm) | 0.20          |
| 625-32   | 6-32, 8-32, 10-32 | orange     | 7-1/8" (181 mm) | 0.20          |

| Replacement Taps |                     |
|------------------|---------------------|
| 626-24           | for Cat. No. 625-24 |
| 626-32           | for Cat. No. 625-32 |

## Cushion-Grip Scratch Awl



650

- Professional, heavy-duty, hard-pointed awl.
- Scribes metal, starts screw holes, performs a variety of piercing and punching jobs.
- Rigid, chrome-plated, heat-treated, tempered-steel shank has full reinforcing bolster at handle for extra strength and for handle impact reinforcement.
- Internal flanges provide solid shank anchor.
- Cushion-Grip handle allows for greater comfort.

| Cat. No. | Blade Length   | Overall Length  | Weight (lbs.) |
|----------|----------------|-----------------|---------------|
| 650      | 3-1/2" (89 mm) | 7-7/8" (200 mm) | .25           |

**⚠ WARNING:** Do NOT hammer on tool.

## Steel Scratch Awl



66385

- One-piece forged-steel blade and bolstered shank.
- Heat treated for long life.
- Well-balanced for top efficiency during use.
- Black finish for rust resistance.

| Cat. No. | Blade Length   | Overall Length | Weight (lbs.) |
|----------|----------------|----------------|---------------|
| 66385    | 3-1/2" (89 mm) | 7" (178 mm)    | .30           |

**⚠ WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠ WARNING:** Never use on or near live electrical circuits.

All dimensions are in inches and (millimeters).

**⚠ WARNING:** Always wear approved eye protection.



## Spring Tools

### Cushion-Grip Spring Tool



ST4

- Installs or removes small-diameter coil springs on motors, brake shoes, headlights, relays, installing recessed can lighting, solenoids, and hundreds of other applications.
- Great for rod and leaf springs.
- Unique C-tip prevents spring slippage.
- Cushion-Grip handle for greater comfort.

| Cat. No. | Shank Length | Overall Length  | Weight (lbs.) |
|----------|--------------|-----------------|---------------|
| ST4      | 4" (102 mm)  | 7-3/4" (197mm)  | .17           |
| ST6      | 6" (152 mm)  | 9-3/4" (248 mm) | .19           |

### Spring Tool



ST49

- Installs or removes small-diameter coil springs on motors, brake shoes, headlights, relays, can lighting, solenoids, and hundreds of other applications.
- Great for rod and leaf springs.
- Unique C-tip prevents spring slippage.

| Cat. No. | Overall Length  | Weight (lbs.) |
|----------|-----------------|---------------|
| ST49     | 7-1/2" (191 mm) | .10           |

## Spring Tool Set

### 2-Piece Recessed Can Light Tool Set

- Contains the two tools needed for finishing can light installations in record time.
- Long reach, spring tool (Cat. No. ST6) makes attaching difficult springs easy.
- Compact, stubby nut driver (Cat. No. 610-1/4) even fits in smaller cans to tighten hard to reach ceiling height adjustment screws.
- Cushion-Grip handles for greater torque and comfort.



65020

| Cat. No. | Set Contains | Weight (lbs.) |
|----------|--------------|---------------|
| 65020    |              | .36           |

| Cat. No. | Description            | Shank Length   | Overall Length  |
|----------|------------------------|----------------|-----------------|
| ST6      | 6" spring tool         | 6" (152 mm)    | 9-3/4" (248 mm) |
| 610-1/4  | 1/4" stubby nut driver | 1-1/2" (38 mm) | 3-1/2" (89 mm)  |

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Will NOT protect against electrical shock.

