

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0482300001](#)
Status: **Obsolete**
Description: 1.00mm (.039") Pitch, Express Module Connector, 98 Circuits, Nylon 4/6 Glass-filled, Black Housing, Gold (Au) Flash, with Beveled Metal Pins, 2.30mm (.091") Solder tail, Lead Free


Documents:
[Drawing \(PDF\)](#)

General
Product Family Edge Card Connectors
Series [48230](#)
Component Type Edgecard to PCB
Product Name Edge Card, Express Module (SIOM)

Physical
(p)ower-(s)ignal Configuration 98s - 0p
Circuits (Loaded) 98
Circuits (maximum) 98
Durability (mating cycles max) 50
Entry Angle Vertical (Top Entry)
Keying to Mating Part Yes
Material - Plating Mating Gold
Material - Plating Termination Tin
PC Tail Length 2.30mm (.091")
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm (.063")
Packaging Type Tray
Pitch - Mating Interface 1.00mm (.039")
Plating min - Mating 0.051µm (2µ")
Plating min - Termination 2.540µm (100µ")
Polarized to Mating Part Yes
Temperature Range - Operating -55°C to +85°C
Termination Interface: Style Through Hole

Electrical
Current - Maximum per Contact 1.1A
Voltage - Maximum 50V

Material Info



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[48230Series](#)

Mates With
1.60mm (.063") Thick Edge Card Module