

Series PRA, PRB and PRD

Product Facts

- Full line of single or double-pole power rocker switches for three different industry compatible panel cut-out sizes
- Easy to install snap-in mounting
- Dust resistant
- Dual color rocker option
- Full-illuminated rocker option
- LED or neon window illuminated option
- Wide range of marking options and functions available
- Solder lugs or .187 & .250 FASTON Tab terminals
- Cost competitive



Electrical Characteristics

Current: 16A@125 VAC 1/3 HP

10A@250 VAC 1/2 HP

PRA Series Double Pole:

7A@125 VAC

6A@250 VAC

PRA Series Single Pole:

6 (3)A 250V ~ 10A 125V ~

μ 25T85

Inrush Current: 50A/3msec

(capacitive load)

Contact Resistance (initial): <50m

Ohms

Dielectric Strength (initial): >1000

VAC, 1 min.

Insulation Resistance (initial):

>100Mohms min.

Electrical Life Endurance:

>6000 operations

Voltage drop <100 mV

Mechanical Characteristics

Operating Life Endurance: up to

>100,000 operations

Actuating Force:

Series PRA 150g min., 650g max.

Series PRB 300g min., 700g max.

Series PRD 850g min., 1250g max.

Materials and Finish

Housing: Nylon 6/6 UL 94V-2

Rocker: Nylon 6/6 UL 94V-2 or

Polycarbonate UL 94V-2

Contact: Silver-tin Oxide

Terminals, Active Contactor: Silver

plated copper alloy

Plunger: Nickel plated copper alloy

Spring: Steel Wire

Standards & Specs

UL Approved - File No. E46765

ENEC/VDE approval - File No.

40006757 (PRA Single Pole Series

only)


South America: 55-11-3611-1514
Hong Kong: 852-2735-1628
Japan: 81-44-844-8013
UK: 44-141-810-8967

1.00 [25.4] x 1.09 [27.6] Panel Cutout



Product Facts

- Easy to install snap-in mounting
- Full illuminated rocker option
- Wide range of marking options and functions available
- FASTON .250 Tab terminals
- Cost competitive



* Refer to Pages F21 for Product Specifications

Alcoswitch Part Number

Switch Type	PR	D	D	XX	XX	X	X	X	X	X	X
PR Power Rockers											
Panel Cut-out Size											
B 1.00 [25.4] x 1.09 [27.6]											
Number of Poles											
S Double Pole											
Switch Functions											
A1 ON-OFF; opaque, single-color rocker button											
B1 ON-OFF; transparent, lamp-illuminated rocker button (100-125 V lamp voltage)											
B3 ON-OFF; transparent, lamp-illuminated rocker button (200-250 V lamp voltage)											
D1 ON-ON; opaque, single-color rocker button											
D3 ON-OFF-ON; opaque, single-color rocker button											
Power Rating											
16 16A, 1/3 Hp @ 125 VAC											
10A, 1/2 Hp @ 250 VAC											
Terminal Type											
F FASTON Tab											
Legend Text Color											
0 Not Applicable											
B Black											
G Green											
R Red											
W White											
Legend Text Pattern											
0 Not Applicable											
A Dot											
B o -											
C o											
D -											
E											
F - o -											
G o											
H ON OFF											
Secondary Rocker Color, Window Color, or LED Color											
0 Not Applicable											
Rocker Color											
A Amber											
B Black											
C Clear											
G Green											
R Red											
W White											
Frame Color											
B Black											
W White											

Part No.

Tyco Electronics	Alcoswitch
1571103-1	PRDDA1-16F-BB000
1571103-2	PRDDA1-16F-BB0BW
1571103-3	PRDDA1-16F-BB0CW
1571103-4	PRDDA1-16F-BR000
1571103-5	PRDDA1-16F-BB0HW
1571103-6	PRDDA1-16F-BR0HW
1571113-7	PRDDD3-16F-BR000

Tyco Electronics	Alcoswitch
1571112-1	PRddb1-16F-BR000
1571112-2	PRddb1-16F-BA000
1571113-1	PRddd1-16F-BB000
1571113-2	PRddd1-16F-BB0DW
1571113-3	PRddd1-16F-BB0EW
1571113-4	PRddd3-16F-BB000
1571113-5	PRddd3-16F-BB0FW
1571113-6	PRddd3-16F-BB0GW