

1-outlet, Direct plug-in, 600 joule Surge Suppressor

MODEL NUMBER: **SPIKECUBE**



Highlights

- 1 outlet / direct plug-in
- 600 joule rating
- Diagnostic LEDs
- \$5000 Ultimate Lifetime connected equipment (USA and Canada Only)

Applications

- Ideal for laptop computers, video projectors, office machines, and appliances

Package Includes

- SPIKECUBE Surge Suppressor
- Warranty and instruction information

Description

The SPIKECUBE Surge Suppressor from Tripp Lite is a direct plug-in suppressor providing protection on one AC outlet. Its small size makes it ideal for protecting laptop computers, projectors and other portable electronics. A green "Protected" and red "Grounded" LED illuminates to indicate that adequate surge suppression is available. The unit has 600 joules of surge energy absorption. \$5,000 Ultimate Lifetime Insurance (USA and Canada Only).

Features

- 1 outlet; direct plug-in
- Surge energy absorption: 600 joules; 6,500 amps
- Diagnostic LEDs indicate protection present (green) and ground present (red)
- \$5,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Specifications

OVERVIEW	
Intended Application	Home/Office, Travel
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	1 NEMA 5-15R
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P input plug
Input cord length details	Direct Plug-In
Voltage compatibility (VAC)	120
Maximum Surge Amps	36000
UPC ASSIGNMENT	
Unit Carton UPC#	037332010643
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	Protected (green) & Grounded (red)
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	600
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	400, 500, 500
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (HWD/in)	6.50 x 4.10 x 2.50
Shipping Dimensions (HWD/cm)	16.51 x 10.41 x 6.35
Shipping weight (lbs)	.150
Shipping weight (kg)	0.07
Unit Dimensions (HWD/in)	2.50 x 1.90 x 1.80
Unit Dimensions (HWD/cm)	6.35 x 4.83 x 4.57
Unit weight (lbs)	.100
Unit weight (kg)	0.05
Material of construction	Plastic
Housing Color	Light Gray
Receptacle Color	Light Gray



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

AC line cord color	Light Gray
Style	Direct plug-in
Form factors supported	Direct plug in suppressor supports wall-mounting directly into AC receptacle
SPECIAL FEATURES	
Appearance	Ultra-compact portable direct plug-in protector in an attractive, grey lightweight enclosure
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)
[SPIKECUBE](#)