


# OA92 Series



AC Fan - 115V, 230V, Dual Voltage  
92 x 25mm(3.62" x 1.0")



|                       |                                                |                                                                                                                                                                                                                                                                                                                                        |  |
|-----------------------|------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| Frame                 | Diecast Aluminum                               | <u>Operating Temperature</u><br>Ball Bearing<br>-20C ~ +80C<br>Sleeve Bearing<br>-10C ~ +50C<br><br><u>Life Expectancy</u><br>Ball Bearing<br>60,000 hours (L10 at 40C)<br>Sleeve Bearing<br>30,000 hours (L10 at 40C)<br><br><u>Dual Voltage</u><br>Connection via 4x leads.<br>Fans can be configured for<br>115V or 230V operation. |  |
| Impeller              | PBT, UL94V-O plastic                           |                                                                                                                                                                                                                                                                                                                                        |  |
| Connection            | 2x Lead Wires 22 AWG (~300mm) or terminals     |                                                                                                                                                                                                                                                                                                                                        |  |
| Motor                 | Shaded pole, impedance protected               |                                                                                                                                                                                                                                                                                                                                        |  |
| Bearing System        | Dual ball or Sleeve                            |                                                                                                                                                                                                                                                                                                                                        |  |
| Insulation Resistance | >100M ohm between lead-wire and frame (500VDC) |                                                                                                                                                                                                                                                                                                                                        |  |
| Dielectric Strength   | 1 min at 1500 VAC, 50/60Hz                     | m0                                                                                                                                                                                                                                                                                                                                     |  |

| Model Number      | Speed (RPM) | Airflow (CFM) | Noise (dB) | Volts AC | Voltage Range | Watts | Max. Static Pressure (\"H2O) |
|-------------------|-------------|---------------|------------|----------|---------------|-------|------------------------------|
| OA92AP-11-1*      | 3000        | 35            | 30         | 115      | 80~130        | 13    | .20                          |
| OA92AP-11-2*      | 2300        | 27            | 22         | 115      | 80~130        | 10    | .14                          |
| OA92AP-11-3*      | 1900        | 22            | 19         | 115      | 80~130        | 6     | .09                          |
| OA92AP-22-1*      | 3000        | 35            | 30         | 230      | 160~260       | 13    | .20                          |
| OA92AP-22-2*      | 2300        | 27            | 22         | 230      | 160~260       | 10    | .14                          |
| OA92AP-22-3*      | 1900        | 22            | 19         | 230      | 160~260       | 6     | .09                          |
| OA92AP-11/22-1W** | 3000        | 35            | 30         | 115/230  | 80~260        | 13    | .20                          |
| OA92AP-11/22-2W** | 2300        | 27            | 22         | 115/230  | 80~260        | 10    | .14                          |
| OA92AP-11/22-3W** | 1900        | 22            | 19         | 115/230  | 80~260        | 6     | .09                          |

\* Indicate "TB" (Terminal Ball Bearing), "WB" (12" Wire Leads, Ball Bearing), "TS" (Terminal, Sleeve Bearing), "WS" (12" Wire Leads, Sleeve Bearing)  
 \*\* Indicate "B" (Ball Bearing) or "S" (Sleeve Bearing)