


Product Description**Note****Scope of delivery:**

including SILVYN® EE-K inner sleeve

Application

The conduit gland SILVYN® USK-M is a proven safety conduit gland. The inner and outer sleeves of the gland can only be fitted in the correct sequence, a special safety factor. The TPE sealing ring provides a good seal. The increased width across flats means that the forces are safely transmitted during installation. The connection between conduit and machine is made by this vibration-resistant special gland to a great extent.

UL FILENUMBER:

E308201

Technical Data

Colour delivered

RAL 7001, silver grey

Material

PP

Degree of protection

IP 65

Range of temperature

-10°C up to +110°C

Article List

Part number	Connection thread M	Clear opening mm	Overall length C mm	Thread length D mm	SW 1/2 mm	Suitable for SILVYN® FD-PU/FPS	Suitable for SILVYN® SP	Suitable for SILVYN® SP-PU	Pieces / VPE
SILVYN® USK-M M									
55501300	10 x 1,0	6	40	10	18 / 16	7 x 10			50
55501310	12 x 1,5	9	43	12	23 / 21	10 x 14	10 x 14	10 x 14	50
55501320	16 x 1,5	13	43	12	27 / 24	13 x 17	12 x 16	12 x 16	50
55501330	20 x 1,5	14.5	44	13	32 / 29	16 x 21	16 x 20	16 x 20	50
55501340	25 x 1,5	19.5	50	13	40 / 36	22 x 27	22 x 27	22 x 27	25
55501350	32 x 1,5	27	51	15	49 / 45	29 x 36	30 x 36	30 x 36	25
55501360	40 x 1,5	36	51	15	58 / 53	38 x 45	38 x 44	38 x 44	25
55501370	50 x 1,5	46	58	16	70 / 65	48 x 56	50 x 56		10