



IFM

IFM Magnifiers - ideal light-duty magnifiers for low-power inspection. With a sturdy, stamped steel shade, these magnifiers feature a 5" diameter, 3-diopter (1.75X) or 5-diopter (2.25X) lens and choice of 45" or 30" arm lengths. IFM Magnifiers are a smart, economical choice for tight budgets.



- 30" or 45" external spring arm
- Edge clamp or base mount
- 5" diameter, 3-diopter (1.75X) or 5-diopter (2.25X) lens
- Expanded model range
- Lamp diffuser cover
- 22-Watt circline fluorescent lamp provides 360° shadow-free illumination
- Built-in starter switch
- 3-wire cord
- Operates on 115VAC
- 30" arm models are available with a weighted base
- 3-wire single outlet receptacle is provided at the base of the arm for models 16345WT, and 16346WT
- UL/CUL listed
- 5 year warranty

RELATED PRODUCTS



KFM



Wave+Plus Magnifiers

CODES

IFM MAGNIFIERS - 3-DIOPTER

Article Number	Light Source	Watt	Arm Length	Mount	Ctn. Colors
16345LG	Circline Fluorescent	22W	45.0/1143	Edge mount 1	■
16345WT	Circline Fluorescent	22W	45.0/1143	Edge mount 1	□
16350LG	Circline Fluorescent	22W	30.0/762	Edge mount 1	■
16351LG	Circline Fluorescent	22W	30.0/762	Base mount 2	■

IFM MAGNIFIERS - 5-DIOPTER

Article Number	Light Source	Watt	Arm Length	Mount	Ctn. Colors
16346LG	Circline Fluorescent	22W	45.0/1143	Edge mount 1	■
16346WT	Circline Fluorescent	22W	45.0/1143	Edge mount 1	□
16352LG	Circline Fluorescent	22W	30.0/762	Edge mount 1	■
16353LG	Circline Fluorescent	22W	30.0/762	Base mount 2	■

LENS DATA

Code	Diopter primary	Total Magnification (x)	Total Magnification (%)	Focal Length (mm)
16345LG	3.00	1.8	175	333.3
16345WT	3.00	1.8	175	333.3
16346LG	5.00	2.3	225	200.0
16346WT	5.00	2.3	225	200.0
16350LG	3.00	1.8	175	333.3
16351LG	3.00	1.8	175	333.3
16352LG	5.00	2.3	225	200.0
16353LG	5.00	2.3	225	200.0

ACCESSORIES

34" Floor Stand	50036
Flush/Surface Mount Bushing	31639
C Surface Mount	50005
B Wall Mount	50003
A Edge Mount Bracket	60001

DESIGNATION