

E

ENG. NO: A-42375-0212/0246					
HEADER NUMBER:			42312-0036		
PIN NUMBER:			42663-AMA154		
PIN LENGTH: L			.505 / 12.83		
MATING LENGTH: M			.295 / 7.49		
GOLD POINT: G			N/A		
PC TAIL LENGTH: P			.120 / 3.05		
TIN: T			OVERALL		
CKTS:			2-36		
KINKS:			NO		
VOIDED CKTS:			NONE		
PACKAGING:			BULK PK-40873-0041		
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
2	22-28-4022	A-42375-0212	20	22-28-4202	A-42375-0230
3	22-28-4032	A-42375-0213	21	22-28-4212	A-42375-0231
4	22-28-4042	A-42375-0214	22	22-28-4222	A-42375-0232
5	22-28-4052	A-42375-0215	23	22-28-4232	A-42375-0233
6	22-28-4062	A-42375-0216	24	22-28-4242	A-42375-0234
7	22-28-4072	A-42375-0217	25	22-28-4252	A-42375-0235
8	22-28-4082	A-42375-0218	26	22-28-4262	A-42375-0236
9	22-28-4092	A-42375-0219	27	22-28-4272	A-42375-0237
10	22-28-4102	A-42375-0220	28	22-28-4282	A-42375-0238
11	22-28-4112	A-42375-0221	29	22-28-4292	A-42375-0239
12	22-28-4122	A-42375-0222	30	22-28-4302	A-42375-0240
13	22-28-4132	A-42375-0223	31	22-28-4312	A-42375-0241
14	22-28-4142	A-42375-0224	32	22-28-4322	A-42375-0242
15	22-28-4152	A-42375-0225	33	22-28-4332	A-42375-0243
16	22-28-4162	A-42375-0226	34	22-28-4342	A-42375-0244
17	22-28-4172	A-42375-0227	35	22-28-4352	A-42375-0245
18	22-28-4182	A-42375-0228	36	22-28-4362	A-42375-0246
19	22-28-4192	A-42375-0229			

D

C

B

A

DOCUMENT STATUS	P1	RELEASE DATE	2021/12/20	12:18:33
-----------------	----	--------------	------------	----------

FORMAT: Eng-lega-master-tb-prod-B
REVISION: D

REVISION: D
DATE: 2018/01/18

9

8

7

6

5

4

3

2

1

E

D

C

B

A

ENG. NO: A-42375-0247/0281					
HEADER NUMBER:			42312-0036		
PIN NUMBER:			42663-ATB208		
PIN LENGTH: L			.505 / 12.83		
MATING LENGTH: M			.295 / 7.49		
GOLD POINT: G			.140 / 3.56		
PC TAIL LENGTH: P			.120 / 3.05		
TIN: T			.135 / 3.43		
CKTS:			2-36		
KINKS:			NO		
VOIDED CKTS:			NONE		
PACKAGING:			BULK PK-40873-0041		
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
2	22-28-4025	A-42375-0247	20	22-28-4205	A-42375-0265
3	22-28-4035	A-42375-0248	21	22-28-4215	A-42375-0266
4	22-28-4045	A-42375-0249	22	22-28-4225	A-42375-0267
5	22-28-4055	A-42375-0250	23	22-28-4235	A-42375-0268
6	22-28-4065	A-42375-0251	24	22-28-4245	A-42375-0269
7	22-28-4075	A-42375-0252	25	22-28-4255	A-42375-0270
8	22-28-4085	A-42375-0253	26	22-28-4265	A-42375-0271
9	22-28-4095	A-42375-0254	27	22-28-4275	A-42375-0272
10	22-28-4105	A-42375-0255	28	22-28-4285	A-42375-0273
11	22-28-4115	A-42375-0256	29	22-28-4295	A-42375-0274
12	22-28-4125	A-42375-0257	30	22-28-4305	A-42375-0275
13	22-28-4135	A-42375-0258	31	22-28-4315	A-42375-0276
14	22-28-4145	A-42375-0259	32	22-28-4325	A-42375-0277
15	22-28-4155	A-42375-0260	33	22-28-4335	A-42375-0278
16	22-28-4165	A-42375-0261	34	22-28-4345	A-42375-0279
17	22-28-4175	A-42375-0262	35	22-28-4355	A-42375-0280
18	22-28-4185	A-42375-0263	36	22-28-4365	A-42375-0281
19	22-28-4195	A-42375-0264			

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
DIMENSION UNITS		SCALE		CURRENT REV DESC: GOLD LENGTH SPEC CHANGED AS MIN 2.54- MAX 5.54 FOR A-42375-0037/0071				molex											
MM/IN		1:1																	
GENERAL TOLERANCES (UNLESS SPECIFIED)																			
				EC NO: 689596				KK 100 HEADER ASSY FLAT VERTICAL BREAKAWAY											
				DRWN: SHRUTJ 2021/09/14															
				CHK'D: SHRUTJ 2021/12/20															
				APPR: ISHWARG 2021/12/20															
				INITIAL REVISION:				PRODUCT CUSTOMER DRAWING											
				DRWN: SCHAFFER 2003/02/11				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION					
				APPR: MARGULIS 2004/02/27				SD-42375-001		PSD		001		V					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
										B-SIZE		42375		SEE CHART		GENERAL MARKET		5 OF 35	

9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																															
E									E																																																																																																																																																																																																																														
D									D																																																																																																																																																																																																																														
C									C																																																																																																																																																																																																																														
B									B																																																																																																																																																																																																																														
A									A																																																																																																																																																																																																																														
<table><tr><td colspan="6">ENG. NO: A-42375-0422/0456</td></tr><tr><td colspan="3">HEADER NUMBER:</td><td colspan="3">42312-0036</td></tr><tr><td colspan="3">PIN NUMBER:</td><td colspan="3">42663-AYA154</td></tr><tr><td colspan="3">PIN LENGTH: L</td><td colspan="3">.545 / 13.84</td></tr><tr><td colspan="3">MATING LENGTH: M</td><td colspan="3">.320 / 8.13</td></tr><tr><td colspan="3">GOLD POINT: G</td><td colspan="3">N/A</td></tr><tr><td colspan="3">PC TAIL LENGTH: P</td><td colspan="3">.135 / 3.43</td></tr><tr><td colspan="3">TIN: T</td><td colspan="3">OVERALL</td></tr><tr><td colspan="3">CKTS:</td><td colspan="3">2-36</td></tr><tr><td colspan="3">KINKS:</td><td colspan="3">SMES-42003</td></tr><tr><td colspan="3">VOIDED CKTS:</td><td colspan="3">NONE</td></tr><tr><td colspan="3">PACKAGING:</td><td colspan="3">BULK PK-40873-0041</td></tr><tr><td>CKTS</td><td>MATERIAL NUMBER</td><td>ENG NUMBER</td><td>CKTS</td><td>MATERIAL NUMBER</td><td>ENG NUMBER</td></tr><tr><td>2</td><td>22-28-5021</td><td>A-42375-0422</td><td>20</td><td>22-28-5201</td><td>A-42375-0440</td></tr><tr><td>3</td><td>22-28-5031</td><td>A-42375-0423</td><td>21</td><td>22-28-5211</td><td>A-42375-0441</td></tr><tr><td>4</td><td>22-28-5041</td><td>A-42375-0424</td><td>22</td><td>22-28-5221</td><td>A-42375-0442</td></tr><tr><td>5</td><td>22-28-5051</td><td>A-42375-0425</td><td>23</td><td>22-28-5231</td><td>A-42375-0443</td></tr><tr><td>6</td><td>22-28-5061</td><td>A-42375-0426</td><td>24</td><td>22-28-5241</td><td>A-42375-0444</td></tr><tr><td>7</td><td>22-28-5071</td><td>A-42375-0427</td><td>25</td><td>22-28-5251</td><td>A-42375-0445</td></tr><tr><td>8</td><td>22-28-5081</td><td>A-42375-0428</td><td>26</td><td>22-28-5261</td><td>A-42375-0446</td></tr><tr><td>9</td><td>22-28-5091</td><td>A-42375-0429</td><td>27</td><td>22-28-5271</td><td>A-42375-0447</td></tr><tr><td>10</td><td>22-28-5101</td><td>A-42375-0430</td><td>28</td><td>22-28-5281</td><td>A-42375-0448</td></tr><tr><td>11</td><td>22-28-5111</td><td>A-42375-0431</td><td>29</td><td>22-28-5291</td><td>A-42375-0449</td></tr><tr><td>12</td><td>22-28-5121</td><td>A-42375-0432</td><td>30</td><td>22-28-5301</td><td>A-42375-0450</td></tr><tr><td>13</td><td>22-28-5131</td><td>A-42375-0433</td><td>31</td><td>22-28-5311</td><td>A-42375-0451</td></tr><tr><td>14</td><td>22-28-5141</td><td>A-42375-0434</td><td>32</td><td>22-28-5321</td><td>A-42375-0452</td></tr><tr><td>15</td><td>22-28-5151</td><td>A-42375-0435</td><td>33</td><td>22-28-5331</td><td>A-42375-0453</td></tr><tr><td>16</td><td>22-28-5161</td><td>A-42375-0436</td><td>34</td><td>22-28-5341</td><td>A-42375-0454</td></tr><tr><td>17</td><td>22-28-5171</td><td>A-42375-0437</td><td>35</td><td>22-28-5351</td><td>A-42375-0455</td></tr><tr><td>18</td><td>22-28-5181</td><td>A-42375-0438</td><td>36</td><td>22-28-5361</td><td>A-42375-0456</td></tr><tr><td>19</td><td>22-28-5191</td><td>A-42375-0439</td><td></td><td></td><td></td></tr></table>									ENG. NO: A-42375-0422/0456						HEADER NUMBER:			42312-0036			PIN NUMBER:			42663-AYA154			PIN LENGTH: L			.545 / 13.84			MATING LENGTH: M			.320 / 8.13			GOLD POINT: G			N/A			PC TAIL LENGTH: P			.135 / 3.43			TIN: T			OVERALL			CKTS:			2-36			KINKS:			SMES-42003			VOIDED CKTS:			NONE			PACKAGING:			BULK PK-40873-0041			CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	2	22-28-5021	A-42375-0422	20	22-28-5201	A-42375-0440	3	22-28-5031	A-42375-0423	21	22-28-5211	A-42375-0441	4	22-28-5041	A-42375-0424	22	22-28-5221	A-42375-0442	5	22-28-5051	A-42375-0425	23	22-28-5231	A-42375-0443	6	22-28-5061	A-42375-0426	24	22-28-5241	A-42375-0444	7	22-28-5071	A-42375-0427	25	22-28-5251	A-42375-0445	8	22-28-5081	A-42375-0428	26	22-28-5261	A-42375-0446	9	22-28-5091	A-42375-0429	27	22-28-5271	A-42375-0447	10	22-28-5101	A-42375-0430	28	22-28-5281	A-42375-0448	11	22-28-5111	A-42375-0431	29	22-28-5291	A-42375-0449	12	22-28-5121	A-42375-0432	30	22-28-5301	A-42375-0450	13	22-28-5131	A-42375-0433	31	22-28-5311	A-42375-0451	14	22-28-5141	A-42375-0434	32	22-28-5321	A-42375-0452	15	22-28-5151	A-42375-0435	33	22-28-5331	A-42375-0453	16	22-28-5161	A-42375-0436	34	22-28-5341	A-42375-0454	17	22-28-5171	A-42375-0437	35	22-28-5351	A-42375-0455	18	22-28-5181	A-42375-0438	36	22-28-5361	A-42375-0456	19	22-28-5191	A-42375-0439																																								
ENG. NO: A-42375-0422/0456																																																																																																																																																																																																																																							
HEADER NUMBER:			42312-0036																																																																																																																																																																																																																																				
PIN NUMBER:			42663-AYA154																																																																																																																																																																																																																																				
PIN LENGTH: L			.545 / 13.84																																																																																																																																																																																																																																				
MATING LENGTH: M			.320 / 8.13																																																																																																																																																																																																																																				
GOLD POINT: G			N/A																																																																																																																																																																																																																																				
PC TAIL LENGTH: P			.135 / 3.43																																																																																																																																																																																																																																				
TIN: T			OVERALL																																																																																																																																																																																																																																				
CKTS:			2-36																																																																																																																																																																																																																																				
KINKS:			SMES-42003																																																																																																																																																																																																																																				
VOIDED CKTS:			NONE																																																																																																																																																																																																																																				
PACKAGING:			BULK PK-40873-0041																																																																																																																																																																																																																																				
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER																																																																																																																																																																																																																																		
2	22-28-5021	A-42375-0422	20	22-28-5201	A-42375-0440																																																																																																																																																																																																																																		
3	22-28-5031	A-42375-0423	21	22-28-5211	A-42375-0441																																																																																																																																																																																																																																		
4	22-28-5041	A-42375-0424	22	22-28-5221	A-42375-0442																																																																																																																																																																																																																																		
5	22-28-5051	A-42375-0425	23	22-28-5231	A-42375-0443																																																																																																																																																																																																																																		
6	22-28-5061	A-42375-0426	24	22-28-5241	A-42375-0444																																																																																																																																																																																																																																		
7	22-28-5071	A-42375-0427	25	22-28-5251	A-42375-0445																																																																																																																																																																																																																																		
8	22-28-5081	A-42375-0428	26	22-28-5261	A-42375-0446																																																																																																																																																																																																																																		
9	22-28-5091	A-42375-0429	27	22-28-5271	A-42375-0447																																																																																																																																																																																																																																		
10	22-28-5101	A-42375-0430	28	22-28-5281	A-42375-0448																																																																																																																																																																																																																																		
11	22-28-5111	A-42375-0431	29	22-28-5291	A-42375-0449																																																																																																																																																																																																																																		
12	22-28-5121	A-42375-0432	30	22-28-5301	A-42375-0450																																																																																																																																																																																																																																		
13	22-28-5131	A-42375-0433	31	22-28-5311	A-42375-0451																																																																																																																																																																																																																																		
14	22-28-5141	A-42375-0434	32	22-28-5321	A-42375-0452																																																																																																																																																																																																																																		
15	22-28-5151	A-42375-0435	33	22-28-5331	A-42375-0453																																																																																																																																																																																																																																		
16	22-28-5161	A-42375-0436	34	22-28-5341	A-42375-0454																																																																																																																																																																																																																																		
17	22-28-5171	A-42375-0437	35	22-28-5351	A-42375-0455																																																																																																																																																																																																																																		
18	22-28-5181	A-42375-0438	36	22-28-5361	A-42375-0456																																																																																																																																																																																																																																		
19	22-28-5191	A-42375-0439																																																																																																																																																																																																																																					
<table><tr><td colspan="6">ENG. NO: A-42375-0457/0491</td></tr><tr><td colspan="3">HEADER NUMBER:</td><td colspan="3">42312-0036</td></tr><tr><td colspan="3">PIN NUMBER:</td><td colspan="3">42663-ADB208</td></tr><tr><td colspan="3">PIN LENGTH: L</td><td colspan="3">.545 / 13.84</td></tr><tr><td colspan="3">MATING LENGTH: M</td><td colspan="3">.320 / 8.13</td></tr><tr><td colspan="3">GOLD POINT: G</td><td colspan="3">.140 / 3.56</td></tr><tr><td colspan="3">PC TAIL LENGTH: P</td><td colspan="3">.135 / 3.43</td></tr><tr><td colspan="3">TIN: T</td><td colspan="3">.135 / 3.43</td></tr><tr><td colspan="3">CKTS:</td><td colspan="3">2-36</td></tr><tr><td colspan="3">KINKS:</td><td colspan="3">SMES-42003</td></tr><tr><td colspan="3">VOIDED CKTS:</td><td colspan="3">NONE</td></tr><tr><td colspan="3">PACKAGING:</td><td colspan="3">BULK PK-40873-0041</td></tr><tr><td>CKTS</td><td>MATERIAL NUMBER</td><td>ENG NUMBER</td><td>CKTS</td><td>MATERIAL NUMBER</td><td>ENG NUMBER</td></tr><tr><td>2</td><td>22-28-5024</td><td>A-42375-0457</td><td>20</td><td>22-28-5204</td><td>A-42375-0475</td></tr><tr><td>3</td><td>22-28-5034</td><td>A-42375-0458</td><td>21</td><td>22-28-5214</td><td>A-42375-0476</td></tr><tr><td>4</td><td>22-28-5044</td><td>A-42375-0459</td><td>22</td><td>22-28-5224</td><td>A-42375-0477</td></tr><tr><td>5</td><td>22-28-5054</td><td>A-42375-0460</td><td>23</td><td>22-28-5234</td><td>A-42375-0478</td></tr><tr><td>6</td><td>22-28-5064</td><td>A-42375-0461</td><td>24</td><td>22-28-5244</td><td>A-42375-0479</td></tr><tr><td>7</td><td>22-28-5074</td><td>A-42375-0462</td><td>25</td><td>22-28-5254</td><td>A-42375-0480</td></tr><tr><td>8</td><td>22-28-5084</td><td>A-42375-0463</td><td>26</td><td>22-28-5264</td><td>A-42375-0481</td></tr><tr><td>9</td><td>22-28-5094</td><td>A-42375-0464</td><td>27</td><td>22-28-5274</td><td>A-42375-0482</td></tr><tr><td>10</td><td>22-28-5104</td><td>A-42375-0365</td><td>28</td><td>22-28-5284</td><td>A-42375-0483</td></tr><tr><td>11</td><td>22-28-5114</td><td>A-42375-0466</td><td>29</td><td>22-28-5294</td><td>A-42375-044</td></tr><tr><td>12</td><td>22-28-5124</td><td>A-42375-0467</td><td>30</td><td>22-28-5304</td><td>A-42375-0485</td></tr><tr><td>13</td><td>22-28-5134</td><td>A-42375-0468</td><td>31</td><td>22-28-5314</td><td>A-42375-0486</td></tr><tr><td>14</td><td>22-28-5144</td><td>A-42375-0469</td><td>32</td><td>22-28-5324</td><td>A-42375-0487</td></tr><tr><td>15</td><td>22-28-5154</td><td>A-42375-0470</td><td>33</td><td>22-28-5334</td><td>A-42375-0488</td></tr><tr><td>16</td><td>22-28-5164</td><td>A-42375-0471</td><td>34</td><td>22-28-5344</td><td>A-42375-0489</td></tr><tr><td>17</td><td>22-28-5174</td><td>A-42375-0472</td><td>35</td><td>22-28-5354</td><td>A-42375-0490</td></tr><tr><td>18</td><td>22-28-5184</td><td>A-42375-0473</td><td>36</td><td>22-28-5364</td><td>A-42375-0491</td></tr><tr><td>19</td><td>22-28-5194</td><td>A-42375-0474</td><td></td><td></td><td></td></tr></table>									ENG. NO: A-42375-0457/0491						HEADER NUMBER:			42312-0036			PIN NUMBER:			42663-ADB208			PIN LENGTH: L			.545 / 13.84			MATING LENGTH: M			.320 / 8.13			GOLD POINT: G			.140 / 3.56			PC TAIL LENGTH: P			.135 / 3.43			TIN: T			.135 / 3.43			CKTS:			2-36			KINKS:			SMES-42003			VOIDED CKTS:			NONE			PACKAGING:			BULK PK-40873-0041			CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	2	22-28-5024	A-42375-0457	20	22-28-5204	A-42375-0475	3	22-28-5034	A-42375-0458	21	22-28-5214	A-42375-0476	4	22-28-5044	A-42375-0459	22	22-28-5224	A-42375-0477	5	22-28-5054	A-42375-0460	23	22-28-5234	A-42375-0478	6	22-28-5064	A-42375-0461	24	22-28-5244	A-42375-0479	7	22-28-5074	A-42375-0462	25	22-28-5254	A-42375-0480	8	22-28-5084	A-42375-0463	26	22-28-5264	A-42375-0481	9	22-28-5094	A-42375-0464	27	22-28-5274	A-42375-0482	10	22-28-5104	A-42375-0365	28	22-28-5284	A-42375-0483	11	22-28-5114	A-42375-0466	29	22-28-5294	A-42375-044	12	22-28-5124	A-42375-0467	30	22-28-5304	A-42375-0485	13	22-28-5134	A-42375-0468	31	22-28-5314	A-42375-0486	14	22-28-5144	A-42375-0469	32	22-28-5324	A-42375-0487	15	22-28-5154	A-42375-0470	33	22-28-5334	A-42375-0488	16	22-28-5164	A-42375-0471	34	22-28-5344	A-42375-0489	17	22-28-5174	A-42375-0472	35	22-28-5354	A-42375-0490	18	22-28-5184	A-42375-0473	36	22-28-5364	A-42375-0491	19	22-28-5194	A-42375-0474																																								
ENG. NO: A-42375-0457/0491																																																																																																																																																																																																																																							
HEADER NUMBER:			42312-0036																																																																																																																																																																																																																																				
PIN NUMBER:			42663-ADB208																																																																																																																																																																																																																																				
PIN LENGTH: L			.545 / 13.84																																																																																																																																																																																																																																				
MATING LENGTH: M			.320 / 8.13																																																																																																																																																																																																																																				
GOLD POINT: G			.140 / 3.56																																																																																																																																																																																																																																				
PC TAIL LENGTH: P			.135 / 3.43																																																																																																																																																																																																																																				
TIN: T			.135 / 3.43																																																																																																																																																																																																																																				
CKTS:			2-36																																																																																																																																																																																																																																				
KINKS:			SMES-42003																																																																																																																																																																																																																																				
VOIDED CKTS:			NONE																																																																																																																																																																																																																																				
PACKAGING:			BULK PK-40873-0041																																																																																																																																																																																																																																				
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER																																																																																																																																																																																																																																		
2	22-28-5024	A-42375-0457	20	22-28-5204	A-42375-0475																																																																																																																																																																																																																																		
3	22-28-5034	A-42375-0458	21	22-28-5214	A-42375-0476																																																																																																																																																																																																																																		
4	22-28-5044	A-42375-0459	22	22-28-5224	A-42375-0477																																																																																																																																																																																																																																		
5	22-28-5054	A-42375-0460	23	22-28-5234	A-42375-0478																																																																																																																																																																																																																																		
6	22-28-5064	A-42375-0461	24	22-28-5244	A-42375-0479																																																																																																																																																																																																																																		
7	22-28-5074	A-42375-0462	25	22-28-5254	A-42375-0480																																																																																																																																																																																																																																		
8	22-28-5084	A-42375-0463	26	22-28-5264	A-42375-0481																																																																																																																																																																																																																																		
9	22-28-5094	A-42375-0464	27	22-28-5274	A-42375-0482																																																																																																																																																																																																																																		
10	22-28-5104	A-42375-0365	28	22-28-5284	A-42375-0483																																																																																																																																																																																																																																		
11	22-28-5114	A-42375-0466	29	22-28-5294	A-42375-044																																																																																																																																																																																																																																		
12	22-28-5124	A-42375-0467	30	22-28-5304	A-42375-0485																																																																																																																																																																																																																																		
13	22-28-5134	A-42375-0468	31	22-28-5314	A-42375-0486																																																																																																																																																																																																																																		
14	22-28-5144	A-42375-0469	32	22-28-5324	A-42375-0487																																																																																																																																																																																																																																		
15	22-28-5154	A-42375-0470	33	22-28-5334	A-42375-0488																																																																																																																																																																																																																																		
16	22-28-5164	A-42375-0471	34	22-28-5344	A-42375-0489																																																																																																																																																																																																																																		
17	22-28-5174	A-42375-0472	35	22-28-5354	A-42375-0490																																																																																																																																																																																																																																		
18	22-28-5184	A-42375-0473	36	22-28-5364	A-42375-0491																																																																																																																																																																																																																																		
19	22-28-5194	A-42375-0474																																																																																																																																																																																																																																					
<table><tr><td colspan="4">SYMBOLS</td><td colspan="12">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td rowspan="2"> ⌵ = 0 ⌴ = 0 ⌶ = 0 ⌷ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 </td><td colspan="2">DIMENSION UNITS</td><td colspan="2">SCALE</td><td colspan="8" rowspan="2">CURRENT REV DESC: GOLD LENGTH SPEC CHANGED AS MIN 2.54- MAX 5.54 FOR A-42375-0037/0071</td><td colspan="3" rowspan="9"> molex KK 100 HEADER ASSY FLAT VERTICAL BREAKAWAY </td></tr><tr><td colspan="2" rowspan="13">MM/IN</td><td colspan="13">1:1</td></tr><tr><td colspan="4"></td><td colspan="4">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="8">EC NO: 689596 DRWN: SHRUTJ 2021/09/14 CHK'D: SHRUTJ 2021/12/20 APPR: ISHWARG 2021/12/20</td></tr><tr><td colspan="4"></td><td>4 PLACES</td><td>±</td><td></td><td>±</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td>3 PLACES</td><td>±</td><td></td><td>± 0.01</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td>2 PLACES</td><td>±</td><td>0.25</td><td>±</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td>1 PLACE</td><td>±</td><td>0.38</td><td>±</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td>0 PLACES</td><td>±</td><td></td><td>±</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td colspan="4">ANGULAR TOL</td><td>± 0.5 °</td><td colspan="7"></td></tr><tr><td colspan="4"></td><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="4"></td><td>THIRD ANGLE PROJECTION</td><td>DRAWING</td><td>SERIES</td><td></td></tr><tr><td colspan="4"></td><td colspan="4"></td><td colspan="4"></td><td></td><td>B-SIZE</td><td>42375</td><td></td></tr><tr><td colspan="4"></td><td colspan="4"></td><td colspan="4"></td><td colspan="2">MATERIAL NUMBER</td><td>CUSTOMER</td><td>SHEET NUMBER</td></tr><tr><td colspan="4"></td><td colspan="4" rowspan="2"></td><td colspan="4"></td><td colspan="2">SEE CHART</td><td>GENERAL MARKET</td><td>8 OF 35</td></tr></table>									SYMBOLS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												⌵ = 0 ⌴ = 0 ⌶ = 0 ⌷ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: GOLD LENGTH SPEC CHANGED AS MIN 2.54- MAX 5.54 FOR A-42375-0037/0071								molex KK 100 HEADER ASSY FLAT VERTICAL BREAKAWAY			MM/IN		1:1																	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 689596 DRWN: SHRUTJ 2021/09/14 CHK'D: SHRUTJ 2021/12/20 APPR: ISHWARG 2021/12/20												4 PLACES	±		±													3 PLACES	±		± 0.01													2 PLACES	±	0.25	±													1 PLACE	±	0.38	±													0 PLACES	±		±													ANGULAR TOL				± 0.5 °												DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								THIRD ANGLE PROJECTION	DRAWING	SERIES															B-SIZE	42375														MATERIAL NUMBER		CUSTOMER	SHEET NUMBER													SEE CHART		GENERAL MARKET	8 OF 35
SYMBOLS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																																																			
⌵ = 0 ⌴ = 0 ⌶ = 0 ⌷ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0 ⏏ = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: GOLD LENGTH SPEC CHANGED AS MIN 2.54- MAX 5.54 FOR A-42375-0037/0071								molex KK 100 HEADER ASSY FLAT VERTICAL BREAKAWAY																																																																																																																																																																																																																										
	MM/IN		1:1																																																																																																																																																																																																																																				
				GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 689596 DRWN: SHRUTJ 2021/09/14 CHK'D: SHRUTJ 2021/12/20 APPR: ISHWARG 2021/12/20																																																																																																																																																																																																																															
				4 PLACES	±		±																																																																																																																																																																																																																																
				3 PLACES	±		± 0.01																																																																																																																																																																																																																																
				2 PLACES	±	0.25	±																																																																																																																																																																																																																																
				1 PLACE	±	0.38	±																																																																																																																																																																																																																																
				0 PLACES	±		±																																																																																																																																																																																																																																
				ANGULAR TOL				± 0.5 °																																																																																																																																																																																																																															
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								THIRD ANGLE PROJECTION	DRAWING	SERIES																																																																																																																																																																																																																									
													B-SIZE	42375																																																																																																																																																																																																																									
												MATERIAL NUMBER		CUSTOMER	SHEET NUMBER																																																																																																																																																																																																																								
												SEE CHART		GENERAL MARKET	8 OF 35																																																																																																																																																																																																																								
<table><tr><td>DOCUMENT STATUS</td><td>P1</td><td>RELEASE DATE</td><td>2021/12/20</td><td>12:18:33</td><td colspan="11"></td></tr></table>									DOCUMENT STATUS	P1	RELEASE DATE	2021/12/20	12:18:33																																																																																																																																																																																																																										
DOCUMENT STATUS	P1	RELEASE DATE	2021/12/20	12:18:33																																																																																																																																																																																																																																			
9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																															

E

ENG. NO: A-42375-0871/0904					
HEADER NUMBER:			42312-0036		
PIN NUMBER:			42663-ATA154		
PIN LENGTH: L			.530 / 13.46		
MATING LENGTH: M			.320 / 8.13		
GOLD POINT: G			N/A		
PC TAIL LENGTH: P			.120 / 3.05		
TIN: T			OVERALL		
CKTS:			3-36		
KINKS:			NO		
VOIDED CKTS:			2		
PACKAGING:			BULK PK-40873-0041		
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
2			20	22-30-3204	A-42375-0888
3	22-28-3034	A-42375-0871	21	22-30-3214	A-42375-0889
4	22-28-3044	A-42375-0872	22	22-30-3224	A-42375-0890
5	22-28-3054	A-42375-0873	23	22-30-3234	A-42375-0891
6	22-28-3064	A-42375-08474	24	22-30-3244	A-42375-0892
7	22-28-3074	A-42375-0875	25	22-30-3254	A-42375-0893
8	22-28-3084	A-42375-0876	26	22-30-3264	A-42375-0894
9	22-28-3094	A-42375-0877	27	22-30-3274	A-42375-0895
10	22-30-3104	A-42375-0878	28	22-30-3284	A-42375-0896
11	22-30-3114	A-42375-0879	29	22-30-3294	A-42375-0897
12	22-30-3124	A-42375-0880	30	22-30-3304	A-42375-0898
13	22-30-3134	A-42375-0881	31	22-30-3314	A-42375-0899
14	22-30-3144	A-42375-0882	32	22-30-3324	A-42375-0900
15	22-30-3154	A-42375-0883	33	22-30-3334	A-42375-0901
16	22-30-3164	A-42375-0884	34	22-30-3344	A-42375-0902
17	22-30-3174	A-42375-0885	35	22-30-3354	A-42375-0903
18	22-30-3184	A-42375-0886	36	22-30-3364	A-42375-0904
19	22-30-3194	A-42375-0887			

D

C

B

A

DOCUMENT STATUS	P1	RELEASE DATE	2021/12/20	12:18:33
-----------------	----	--------------	------------	----------

ENG. NO: A-42375-0973/1001					
HEADER NUMBER:			42312-0036		
PIN NUMBER:			42663-ABA154		
PIN LENGTH: L			.455 / 11.56		
MATING LENGTH: M			.240 / 6.09		
GOLD POINT: G			N/A		
PC TAIL LENGTH: P			.125 / 3.18		
TIN: T			OVERALL		
CKTS:			8-36		
KINKS:			NO		
VOIDED CKTS:			3,8		
PACKAGING:			BULK PK-40873-0041		
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
2			20	42375-0985	A-42375-0985
3			21	42375-0986	A-42375-0986
4			22	42375-0987	A-42375-0987
5			23	42375-0988	A-42375-0988
6			24	42375-0989	A-42375-0989
7			25	42375-0990	A-42375-0990
8	42375-0973	A-42375-0973	26	42375-0991	A-42375-0991
9	42375-0974	A-42375-0974	27	42375-0992	A-42375-0992
10	22-30-3107	A-42375-0975	28	42375-0993	A-42375-0993
11	42375-0976	A-42375-0976	29	42375-0994	A-42375-0994
12	42375-0977	A-42375-0977	30	42375-0995	A-42375-0995
13	42375-0978	A-42375-0978	31	42375-0996	A-42375-0996
14	42375-0979	A-42375-0979	32	42375-0997	A-42375-0997
15	42375-0980	A-42375-0980	33	42375-0998	A-42375-0998
16	42375-0981	A-42375-0981	34	42375-0999	A-42375-0999
17	42375-0982	A-42375-0982	35	42375-1000	A-42375-1000
18	42375-0983	A-42375-0983	36	42375-1001	A-42375-1001
19	42375-0984	A-42375-0984			

E

D

C

B

A

[illegible]

9

8

7

6

5

4

3

2

1

E

ENG. NO: A-42375-1105/1139					
HEADER NUMBER:			42312-0036		
PIN NUMBER:			42663-ABB208		
PIN LENGTH: L			.455 / 11.56		
MATING LENGTH: M			.240 / 6.09		
GOLD POINT: G			.100 / 2.54		
PC TAIL LENGTH: P			.125 / 3.18		
TIN: T			.100 / 2.54		
CKTS:			2-36		
KINKS:			NO		
VOIDED CKTS:			4		
PACKAGING:			BULK PK-40873-0041		
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
2	42375-1105	A-42375-1105	20	42375-1123	A-42375-1123
3	42375-1106	A-42375-1106	21	42375-1124	A-42375-1124
4	42375-1107	A-42375-1107	22	42375-1125	A-42375-1125
5	42375-1108	A-42375-1108	23	42375-1126	A-42375-1126
6	42375-1109	A-42375-1109	24	42375-1127	A-42375-1127
7	42375-1110	A-42375-1110	25	42375-1128	A-42375-1128
8	42375-1111	A-42375-1111	26	42375-1129	A-42375-1129
9	42375-1112	A-42375-1112	27	42375-1130	A-42375-1130
10	42375-1113	A-42375-1113	28	42375-1131	A-42375-1131
11	42375-1114	A-42375-1114	29	42375-1132	A-42375-1132
12	42375-1115	A-42375-1115	30	42375-1133	A-42375-1133
13	42375-1116	A-42375-1116	31	42375-1134	A-42375-1134
14	42375-1117	A-42375-1117	32	42375-1135	A-42375-1135
15	42375-1118	A-42375-1118	33	42375-1136	A-42375-1136
16	42375-1119	A-42375-1119	34	42375-1137	A-42375-1137
17	42375-1120	A-42375-1120	35	42375-1138	A-42375-1138
18	42375-1121	A-42375-1121	36	42375-1139	A-42375-1139
19	42375-1122	A-42375-1122			

D

C

B

A

ENG. NO: 42375-1244/1278			
HEADER NUMBER:		42312-0036	
PIN NUMBER:		42663-ABA154	
PIN LENGTH: L		.455 / 11.56	
MATING LENGTH: M		.240 / 6.09	
GOLD POINT: G		N/A	
PC TAIL LENGTH: P		.125 / 3.18	
TIN: T		OVERALL	
CKTS:		2-36	
KINKS:		NO	
VOIDED CKTS:		2	
PACKAGING:		BULK	PK-40873-0041
CKTS	ITEM NUMBER	CKTS	MATERIAL NUMBER
2	42375-1244	20	42375-1262
3	42375-1245	21	42375-1263
4	42375-1246	22	42375-1264
5	42375-1247	23	42375-1265
6	42375-1248	24	42375-1266
7	42375-1249	25	42375-1267
8	42375-1250	26	42375-1268
9	42375-1251	27	42375-1269
10	42375-1252	28	42375-1270
11	42375-1253	29	42375-1271
12	42375-1254	30	42375-1272
13	42375-1255	31	42375-1273
14	42375-125 6	32	42375-1274
15	42375-1257	33	42375-1275
16	42375-1258	34	42375-1276
17	42375-1259	35	42375-1277
18	42375-1260	36	42375-1278
19	42375-1261		


E

D

C

B

A

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
A = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: GOLD LENGTH SPEC CHANGED AS MIN 2.54- MAX 5.54 FOR A-42375-0037/0071			molex						
	MM/IN		1:1											
	GENERAL TOLERANCES (UNLESS SPECIFIED)													
E = 0					EC NO: 689596 DRWN: SHRUTJ 2021/09/14 CHK'D: SHRUTJ 2021/12/20 APPR: ISHWARG 2021/12/20			KK 100 HEADER ASSY FLAT VERTICAL BREAKAWAY						
F = 0														
S = 0	4 PLACES ±		±		INITIAL REVISION: DRWN: SCHAFER 2003/02/11 APPR: MARGULIS 2004/02/27			PRODUCT CUSTOMER DRAWING						
▽ = 0	3 PLACES ±		± 0.01											
▽ = 0	2 PLACES ± 0.25		±											
▽ = 0	1 PLACES ± 0.38		±		DOCUMENT NUMBER SD-42375-001			DOC TYPE PSD		DOC PART 001		REVISION V		
⊠ = 0	0 PLACES ±		±											
■ = 0	ANGULAR TOL ± 0.5 °													
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
					B-SIZE		42375		SEE CHART		GENERAL MARKET		14 OF 35	

DOCUMENT STATUS	P1	RELEASE DATE	2021/12/20	12:18:33
-----------------	----	--------------	------------	----------

9

8

7

6

5

4

3

2

1

FORMAT: Eng-lega-master-tb-prod-B
REVISION: D
DATE: 2018/01/18

ENG. NO: 42375-1349/1382			
HEADER NUMBER:		42312-0036	
PIN NUMBER:		42663-ABA154	
PIN LENGTH: L		.455 / 11.56	
MATING LENGTH: M		.230 / 5.84	
GOLD POINT: G		N/A	
PC TAIL LENGTH: P		.135 / 3.43	
TIN: T		OVERALL	
CKTS:		3-36	
KINKS:		SMES-42003	
VOIDED CKTS:		2	
PACKAGING:		BULK PK-40873-0041	
CKTS	ITEM NUMBER	CKTS	ITEM NUMBER
2		20	42375-1366
3	42375-1349	21	42375-1367
4	42375-1350	22	42375-1368
5	42375-1351	23	42375-1369
6	42375-1352	24	42375-1370
7	42375-1353	25	42375-1371
8	42375-1354	26	42375-1372
9	42375-1355	27	42375-1373
10	42375-1356	28	42375-1374
11	42375-1357	29	42375-1375
12	42375-1358	30	42375-1376
13	42375-1359	31	42375-1377
14	42375-1360	32	42375-1378
15	42375-1361	33	42375-1379
16	42375-1362	34	42375-1380
17	42375-1363	35	42375-1381
18	42375-1364	36	42375-1382
19	42375-1365		

ENG. NO: 42375-1515/1548			
HEADER NUMBER:		42312-0036	
PIN NUMBER:		42663-ABB208	
PIN LENGTH: L		.455 / 11.56	
MATING LENGTH: M		.230 / 5.84	
GOLD POINT: G		.140 / 3.56	
PC TAIL LENGTH: P		.135 / 3.43	
TIN: T		.100 / 2.54	
CKTS:		3-36	
KINKS:		SMES-42003	
VOIDED CKTS:		2	
PACKAGING:		BULK PK-40873-0041	
CKTS	ITEM NUMBER	CKTS	ITEM NUMBER
2		20	42375-1532
3	42375-1515	21	42375-1533
4	42375-1516	22	42375-1534
5	42375-1517	23	42375-1535
6	42375-1518	24	42375-1536
7	42375-1519	25	42375-1537
8	42375-1520	26	42375-1538
9	42375-1521	27	42375-1539
10	42375-1522	28	42375-1540
11	42375-1523	29	42375-1541
12	42375-1524	30	42375-1542
13	42375-1525	31	42375-1543
14	42375-1526	32	42375-1544
15	42375-1527	33	42375-1545
16	42375-1528	34	42375-1546
17	42375-1529	35	42375-1547
18	42375-1530	36	42375-1548
19	42375-1531		

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
= 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: GOLD LENGTH SPEC CHANGED AS MIN 2.54- MAX 5.54 FOR A-42375-0037/0071					molex						
	MM/IN		1:1													
= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 689596					KK 100 HEADER ASSY FLAT VERTICAL BREAKAWAY						
= 0																
= 0	MM		INCH		DRWN: SHRUTJ 2021/09/14					PRODUCT CUSTOMER DRAWING						
= 0	4 PLACES ±		±												CHK'D: SHRUTJ 2021/12/20	
= 0	3 PLACES ±		± 0.01		APPR: ISHWARG 2021/12/20											
= 0	2 PLACES ±		0.25 ±							INITIAL REVISION:						
= 0	1 PLACE ±		0.38 ±		DRWN: SCHAFFER 2003/02/11											
= 0	0 PLACES ±		±							APPR: MARGULIS 2004/02/27						
= 0	ANGULAR TOL ±		0.5 °		THIRD ANGLE PROJECTION											
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE
= 0					B-SIZE		42375		SD-42375-001		PSD		001		V	
= 0									MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
= 0									SEE CHART		GENERAL MARKET		15 OF 35			

DOCUMENT STATUS	P1	RELEASE DATE	2021/12/20	12:18:33
-----------------	----	--------------	------------	----------

ENG. NO: 42375-2486/2520			
HEADER NUMBER:		42312-0036	
PIN NUMBER:		42663-AFB208	
PIN LENGTH: L		.475 / 12.07	
MATING LENGTH: M		.232 / 5.89	
GOLD POINT: G		.150 / 3.81	
PC TAIL LENGTH: P		.153 / 3.89	
TIN: T		.100 / 2.54	
CKTS:		2-36	
KINKS:		NO	
VOIDED CKTS:		NONE	
PACKAGING:		BULK PK-40873-0041	
CKTS	ITEM NUMBER	CKTS	ITEM NUMBER
2	42375-2486	19	42375-2503
3	42375-2487	20	42375-2504
	68300-2008	21	42375-2505
4	42375-2488	22	42375-2506
5	42375-2489	23	42375-2507
6	42375-2490	24	42375-2508
7	42375-2491	25	42375-2509
8	42375-2492	26	42375-2510
9	42375-2493	27	42375-2511
10	42375-2494	28	42375-2512
11	42375-2495	29	42375-2513
12	42375-2496	30	42375-2514
13	42375-2497	31	42375-2515
14	42375-2498	32	42375-2516
15	42375-2499	33	42375-2517
16	42375-2500	34	42375-2518
17	42375-2501	35	42375-2519
18	42375-2502	36	42375-2520

ENG. NO: 42375-2521/2555			
HEADER NUMBER:		42312-0036	
PIN NUMBER:		42663-AFB228	
PIN LENGTH: L		.475 / 12.07	
MATING LENGTH: M		.232 / 5.89	
GOLD POINT: G		.150 / 3.81	
PC TAIL LENGTH: P		.153 / 3.89	
TIN: T		.100 / 2.54	
CKTS:		2-36	
KINKS:		NO	
VOIDED CKTS:		NONE	
PACKAGING:		BULK PK-40873-0041	
CKTS	ITEM NUMBER	CKTS	ITEM NUMBER
2	42375-2521	20	42375-2539
3	42375-2522	21	42375-2540
4	42375-2523	22	42375-2541
5	42375-2524	23	42375-2542
6	42375-2525	24	42375-2543
7	42375-2526	25	42375-2544
8	42375-2527	26	42375-2545
9	42375-2528	27	42375-2546
10	42375-2529	28	42375-2547
11	42375-2530	29	42375-2548
12	42375-2531	30	42375-2549
13	42375-2532	31	42375-2550
14	42375-2533	32	42375-2551
15	42375-2534	33	42375-2552
16	42375-2535	34	42375-2553
17	42375-2536	35	42375-2554
18	42375-2537	36	42375-2555
19	42375-2539		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: GOLD LENGTH SPEC CHANGED AS MIN 2.54- MAX 5.54 FOR A-42375-0037/0071				molex KK 100 HEADER ASSY FLAT VERTICAL BREAKAWAY				
▽ = 0	MM/IN		1:1										
▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)												
▽ = 0			MM	INCH	EC NO: 689596 DRWN: SHRUTJ 2021/09/14 CHK'D: SHRUTJ 2021/12/20 APPR: ISHWARG 2021/12/20				PRODUCT CUSTOMER DRAWING				
▽ = 0	4 PLACES	±		±									
▽ = 0	3 PLACES	±		± 0.01									
▽ = 0	2 PLACES	±	0.25	±	INITIAL REVISION: DRWN: SCHAFER 2003/02/11 APPR: MARGULIS 2004/02/27				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
▽ = 0	1 PLACE	±	0.38	±					SD-42375-001		PSD	001	V
▽ = 0	0 PLACES	±		±	THIRD ANGLE PROJECTION DRAWING B-SIZE				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
▽ = 0				ANGULAR TOL					± 0.5 °	SEE CHART		GENERAL MARKET	
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SERIES 42375						

DOCUMENT STATUS	P1	RELEASE DATE	2021/12/20	12:18:33
-----------------	----	--------------	------------	----------

ENG. NO: A-42375-1622			
HEADER NUMBER:		42312-0036	
PIN NUMBER:		42663-AYB208	
PIN LENGTH: L		.545 / 13.84	
MATING LENGTH: M		.320 / 8.13	
GOLD POINT: G		.140 / 3.56	
PC TAIL LENGTH: P		.135 / 3.43	
TIN: T		.135 / 3.43	
CKTS:		2-36	
KINKS:		SMES-42003	
VOIDED CKTS:		3	
PACKAGING:		BULK	PK-40873-0041
CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER
2		20	
3		21	
4		22	
5		23	
6		24	
7		25	
8		26	
9	42375-1622	27	
10		28	
11		29	
12		30	
13		31	
14		32	
15		33	
16		34	
17		35	
18		36	
19			

ENG. NO: A-42375-4199			
HEADER NUMBER:		42312-0036	
PIN NUMBER:		42663-ARB228	
PIN LENGTH: L		.520 / 13.21	
MATING LENGTH: M		.230 / 5.84	
GOLD POINT: G		.140 / 3.56	
PC TAIL LENGTH: P		.200 / 5.08	
TIN: T		.135 / 3.43	
CKTS:		2-36	
KINKS:		NO	
VOIDED CKTS:		NONE	
PACKAGING:		BULK	PK-40873-0041
CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER
2	42375-4199	20	
3		21	
4		22	
5		23	
6		24	
7		25	
8		26	
9		27	
10		28	
11		29	
12		30	
13		31	
14		32	
15		33	
16		34	
17		35	
18		36	
19			

ENG. NO: A-42375-4200			
HEADER NUMBER:		42312-0036	
PIN NUMBER:		42663-ADB208	
PIN LENGTH: L		.465 / 11.81	
MATING LENGTH: M		.240 / 6.09	
GOLD POINT: G		.100 / 2.54	
PC TAIL LENGTH: P		.135 / 3.43	
TIN: T		.100 / 2.54	
CKTS:		2-36	
KINKS:		SMES-42003	
VOIDED CKTS:		3, 4	
PACKAGING:		BULK	PK-40873-0041
CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER
2		20	
3		21	
4		22	
5	42375-4200	23	
6		24	
7		25	
8		26	
9		27	
10		28	
11		29	
12		30	
13		31	
14		32	
15		33	
16		34	
17		35	
18		36	
19			

DOCUMENT STATUS	P1	RELEASE DATE	2021/12/20	12:18:33
-----------------	----	--------------	------------	----------

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: GOLD LENGTH SPEC CHANGED AS MIN 2.54- MAX 5.54 FOR A-42375-0037/0071				molex				
MM/IN		1:1										
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 689596				KK 100 HEADER ASSY FLAT VERTICAL BREAKAWAY				
		MM INCH		DRWN: SHRUTJ 2021/09/14				PRODUCT CUSTOMER DRAWING				
4 PLACES ± ±		± 0.01		CHK'D: SHRUTJ 2021/12/20				DOCUMENT NUMBER SD-42375-001				
3 PLACES ± ±		± 0.01										
2 PLACES ± 0.25 ±				APPR: ISHWARG 2021/12/20				DOC TYPE PSD				
1 PLACE ± 0.38 ±												
INITIAL REVISION:		DRWN: SCHAFFER 2003/02/11				DOC PART 001						
DRWN: SCHAFFER 2003/02/11		APPR: MARGULIS 2004/02/27				REVISION V						
APPR: MARGULIS 2004/02/27												
ANGULAR TOL ± 0.5 °				THIRD ANGLE PROJECTION				MATERIAL NUMBER SEE CHART				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRAWING B-SIZE		SERIES 42375		CUSTOMER GENERAL MARKET				
								SHEET NUMBER 33 OF 35				

FORMAT: Eng-legal-master-00-prod-0 REVISION: D DATE: 20100118										9	8	7	6	5	4	3	2	1
---	--	--	--	--	--	--	--	--	--	---	---	---	---	---	---	---	---	---

