

Grommet - HC-DR-PG36 - 1686614

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Notched seals/2 washers, for pressure screws, type Pg36



Key commercial data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	22.38 GRM
Custom tariff number	40169300
Country of origin	Germany

Technical data

Dimensions

External cable diameter	24 mm ... 33 mm
Conductor sealing range	24.00 mm ... 33.00 mm

Ambient conditions

Degree of protection	IP65
	IP54
Ambient temperature (operation)	-20 °C ... 80 °C

General

Cable seal material	Perbunan
Thread type on connection side	Pg36

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109

Grommet - HC-DR-PG36 - 1686614

Classifications

eCl@ss

eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC002498
ETIM 5.0	EC002498

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST



