

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 19203-0063
Status: Active
Overview: High-Temperature Temp Terms Terminals and Splices
Description: VersaKrimp™ Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5)

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
Series 19203
Comments 650° F (343° C)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview High-Temperature Temp Terms Terminals and Splices
Product Name Temp-Terms, VersaKrimp™
Type Ring
UPC 800755059311

Physical

Barrel Type Closed - Brazed
Insulation None
Material - Plating Mating Tin
Net Weight 0.620/g
Packaging Type Bag
Stud Size 10 (M5)
Wire Size AWG 14, 16
Wire Size mm² 1.00 - 2.50

Material Info

Old Part Number BB-T-337-10

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing BBTCD30101



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19203Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640070100
PremiumGrade™ Hand Crimp Tool	0640030100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0063](#)