

## Fuse monitors

Disconnect  
switches  
Fusible



OFM\_

### Fuse monitors

For switch size	Rated voltage	Weight (lbs.)	Catalog number	List price
OS30-100 and OES400-800	100 - 240 380 - 600	0.31 0.31	OFM240 OFM600	\$ 290
OS200	100 - 240 380 - 600	0.35	OFS240 OFS600	

Suitable for 3 phase circuits. Includes 1 N.O. & 1 N.C. auxiliary contacts and red & green LED lights.

### Mounting accessories

For switch size	Crimp terminal size (mm)	Catalog number	List price
OS30 - 200	2.8 - 0.8	OFMZX2	\$ 20
OES400 - 800	6.3 - 0.8	OFMZX4	70

Includes 6 crimp terminals.

### Description

- Indicates single phasing
- Operates with all fuse types
- No need for external supply voltage
- Wide voltage range, 100-240VAC and 380-600VAC
- UL Listed, EMC tested
- Fuse monitor is automatically reset after the blown fuses have been replaced
- One trip contact, one alarm contact and two LEDs (red and green)
- Phase imbalance immune
- Compact size
- Snap-on and screw-on mounting for OS disconnects
- Suitable to be used as a standalone device

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cooper Bussmann:](#)

[OFM240](#) [OFM600](#)