




Type C Vertical Pin Housing for Crimp Snap-In Pin Contacts



Material

Housing — Glass filled polymer

Related Product Data

DIN Performance Levels — Page 6

Performance Specifications —
Page 7

Mateable Connectors — Pages 20,
21, 23, 24, 29-31, 55, 56

Accessories — Pages 64, 66

Application Tooling — See below

Technical Documents — Page 74:

DIN Specification 41612

IEC Specification 60603-2

Standard Size

Number of Positions	Dimensions				Part Number
	A	B	C	D	
96	93.70 3.689	90.00 3.543	78.74 3.100	83.00 3.268	166467-1

**AMPMODU Mod. IV
Crimp Snap-In
Pin Contacts**

Material

Contacts — Copper alloy


Hand Tool

Part Number 91517-1

Instruction Sheet 408-8547

Extraction Tool

Part Number 166645-1



Wire Size Range		Insulation Diameter (Max.)	DIN Levels	Part Number	
mm ²	AWG			Strip Form*	Loose Piece
0.12 - 0.4	26-22	1.60 [.063]	II	102095-3	166679-1
					102107-2
			III	102095-2	166679-4
					102107-1

* Strip form, 12,000 pieces per reel. For automatic tooling recommendation, consult Tyco Electronics at the numbers listed below.