



Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDF-PViQ TX6 PLU ..
  - DXF-PViQ TX6 PLU ..
  - DWG-PViQ TX6 PLU ..
  - Specification Sheets
  - PDF-PanView iQ ( ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) [Search Tips](#)

**Text Search: 'CJQ688TGBL'**

Your search criteria matched only one product, shown below

**CJQ688TGBL**



- Mechanical keyed configurations prevent unintentional insertion into adjacent ports (4 versions)
- Meet requirements of IEEE 802.af and IEEE 802.3at for PoE applications
- Contacts plate with 50 microinches of gold for superior performance
- No punchdown tool required; termination tool (EGJT) ensures conductors are fully terminated by utilizing a smooth forward motion without impact on critical internal components for maximum reliability
- Optional termination tool (TGJT) reduces termination time by 25%, ideal for high volume installations
- Termination cap is color-coded for T568A and T568B wiring schemes
- Each jack is 100% tested to ensure NEXT and RL performance
- Can be clearly identified with optional labels and icons
- Compatible with PanView iQ™ PViQ™ Patch Panels

▪ Part Number	CJQ688TGBL
▪ RoHS Compliance Status	Compliant
▪ Part Description	Keyed, PanView iQ™ (PViQ™) Category 6, RJ45, 8-position, 8-wire, UTP black module.
▪ Product Type	Keyed UTP Jack Module
▪ Color	Black
▪ CE Compliant	No
▪ No. of Module Spaces	1
▪ Performance Level	Category 6/Class E
▪ Pricing Description	PanView iQ Keyed Module, Cat 6, UTP, 8 pos 8 wire, Black
▪ Wiring Scheme	T568A/T568B
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.