


TOLERANCE UNLESS SPECIFIED =

.XXX = +/- .005


.XX = +/- .015

FRACTIONS = +/- .032


24-2330.DC2



115/230V
50/60 HZ



PC PINS .045 SQ



PRODUCTION TESTS

Turns Ratio = 100%

DC
RESISTANCE
IN OHMS

1-3 =	21.5 NOM
4-6 =	26.5 NOM
7-9 =	.32 NOM
10-12 =	.39 NOM

MAX EXCITATION CURRENT = 75 MA

APPLY 230V 60HZ 1-6 (3+4)

PRI WDGS 114.5 TO 115.5 V

SEC WDGS 13.6 TO 14.4 V

HIPOT: 4000V P-S

4000V P,S, TO CORE

600V P-P, S-S

FINAL ASSEMBLY NOTES

1

MagneTek

VPP24-2330

LEAVE OFF LAST "I" PCS