


## Front panels, U profile, shieldable



Part no.: 30848-380

### Features:

- High stability through U profile
- Front panel, U profile, Al, front anodised, rear conductive, 2 alignment pins pressed-in, stainless steel
- Differences in the finish between 2 ... 12 HP and 14 ... 84 HP

[Add to basket](#)



Standard pack quantity 5



### Technical Information:

Description	Height	Width	Height	B
Front panels, U profile, shieldable	3 U	6 HP	128.4 mm	30.1 mm

### Downloads:

Download CAD data in DWG/DXF/PDF format ([Log in](#) required) 

To gain access to the additional information you must log in.  
If you do not yet have a user name, you may register here.

### Accessories:

Part no.	Description	<a href="#">Add to basket</a>
21101-853	Textile EMC gasket 3 U, PU 10 pieces	<a href="#">Add to basket</a>
21101-854	Textile EMC gasket 3 U, PU 100 pieces	<a href="#">Add to basket</a>

### Note:

- Standard pack quantity:  
2 to 28 HP: 5 pieces,  
42 to 84 HP: 1 piece,  
supplied in standard pack quantities (SPQ) only
- Please order EMC profile seal and fixing materials separately